

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

BIPOLAR ANALOG INTEGRATED CIRCUIT

Phase-out/Discontinued

μPC8220T5A

Tx AND Rx MCP IC FOR 1.9 GHz PHS

DESCRIPTION

The μPC8220T5A is MCP (Multi Chip Packaging) IC consisted of silicon germanium (SiGe) bipolar process and LDMOS designed for use as transmitting and receiving for 1.9 GHz PHS.

This device is packaged in surface mount 16-pin plastic TSON (Thin Small Outline Non-leaded) package.

This IC manufactured using our 50 GHz f_{max} UHS2 (Ultra High Speed Process) SiGe bipolar process and LDMOS (Lateral Diffusion MOS FET Process).

FEATURES

– Tx Block –

- Circuit Current (DRV + PA) : $I = 160$ mA TYP. @ $V_{CC} = V_{ds} = 3.0$ V, $f = 1.9$ GHz, $P_{in} = -19$ dBm, $P_{out} = +20.5$ dBm
- Output Power : $P_{out} = +20.5$ dBm MIN. @ $V_{CC} = V_{ds} = 3.0$ V, $f = 1.9$ GHz, $P_{in} = -19$ dBm
- Power Gain : $G_P = 39.5$ dB MIN. @ $V_{CC} = V_{ds} = 3.0$ V, $f = 1.9$ GHz, $P_{in} = -19$ dBm
- Adjacent Channel Power : $P_{adj1} = -65$ dBc TYP. @ $V_{CC} = V_{ds} = 3.0$ V, $f = 1.9$ GHz, $P_{out} = +20.5$ dBm, $\Delta \pm 600$ kHz
: $P_{adj2} = -70$ dBc TYP. @ $V_{CC} = V_{ds} = 3.0$ V, $f = 1.9$ GHz, $P_{out} = +20.5$ dBm, $\Delta \pm 900$ kHz
- Harmonics Frequency Level : $2f_0 = -45$ dBc TYP. @ $V_{CC} = V_{ds} = 3.0$ V, $P_{out} = +20.5$ dBm
: $3f_0 = -60$ dBc TYP. @ $V_{CC} = V_{ds} = 3.0$ V, $P_{out} = +20.5$ dBm
- Gain 1 dB Compression Output Power : $P_O (1 \text{ dB}) = +21$ dBm TYP. @ $V_{CC} = V_{ds} = 3.0$ V

– Rx Block –

- Circuit Current : $I_{CC} = 11.5$ mA TYP. @ $V_{CC} = 3.0$ V
- Conversion Gain : $CG = 21.5$ dB TYP. @ $f_{RF} = 1.9$ GHz, $f_{IF} = 240$ MHz, $f_{LO} = 1.66$ GHz
- Noise Figure : $NF = 3.1$ dB TYP. @ SSB
- Input 3rd Order Distortion : $IIP_3 = -14.5$ dBm TYP. @ $f_{RF1} = 1.9$ GHz, $f_{RF2} = 1.9006$ GHz, $P_{RF} = -35$ dBm/tone Intercept Point
- Image Rejection Ratio : $IMR = 40$ dBc TYP. @ $f_{RF1} = 1.9$ GHz, $f_{RF2} = 1.42$ GHz, $P_{RF} = -35$ dBm/tome
- High-density Surface Mounting : 16-pin plastic TSON package ($3.3 \times 2.3 \times 0.6$ mm)

APPLICATION

- PHS

ORDERING INFORMATION

Part Number	Order Number	Package	Marking	Supplying Form
μPC8220T5A-E1	μPC8220T5A-E1-A	16-pin plastic TSON (Pb-Free) ^{Note}	8220	<ul style="list-style-type: none"> • Embossed tape 12 mm wide • Pin 8, 9 face the perforation side of the tape • Qty 3 kpcs/reel


Note With regards to terminal solder (the solder contains lead) plated products (conventionally plated), contact your nearby sales office.

Remark To order evaluation samples, contact your nearby sales office.
Part number for sample order: μPC8220T5A

Caution Observe precautions when handling because these devices are sensitive to electrostatic discharge.

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.
Not all devices/types available in every country. Please check with local NEC Compound Semiconductor Devices representative for availability and additional information.

PIN CONNECTIONS AND INTERNAL BLOCK DIAGRAM



Pin No.	Pin Name	Pin No.	Pin Name
1	RF _{in}	9	INPUT2
2	LNA _{out}	10	OUTPUT1
3	GND (LNA)	11	V _{CC} (TX)
4	LNA _{in}	12	GND (DRV)
5	GND (DRV)	13	INPUT1
6	GND (DRV)	14	IF OUT
7	OUT2 (PA)	15	V _{CC} (RX)
8	OUT2 (PA)	16	Lo IN

NOTE ON CORRECT USE

Exposed heatsink at bottom on package that is combined with GND (ground) must be soldered to PCB RF/DC ground.

ABSOLUTE MAXIMUM RATINGS (T_A = +25°C, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
LNA Output Voltage	V _{LNAout}	4.0	V
Mixer Output Voltage	V _{CC} , IF _{out}	4.0	V
Driver Output Voltage	V _{CC} , V _{out1}	4.0	V
PA Drain-Source Voltage	V _{ds}	8.0	V
PA Gate-Source Voltage	V _{gs}	8.0	V
Input Power 1	P _{in1}	+10	dBm
Input Power 2	P _{in2}	+16	dBm
LNA Input Power	P _{LNAin}	+10	dBm
Local Input Power	P _{LoIn}	+10	dBm
Channel Temperature	T _{ch}	150	°C
Operating Ambient Temperature	T _A	−30 to +70	°C
Storage Temperature	T _{stg}	−55 to +150	°C
Power Dissipation of Package	P _D	5.33 ^{Note}	W
Circuit Current 1 (LNA + Mixer)	I _{CC1}	21	mA
Circuit Current 2 (PA Driver)	I _{CC2}	70	mA
Circuit Current 3 (PA)	I _{ds}	259	mA

Note Mounted on 33 × 21 × 0.4 mm polyimide PCB

RECOMMENDED OPERATING RANGE (T_A = +25°C, unless otherwise specified)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
LNA Output Voltage	V _{LNAout}	2.7	3.0	3.3	V
Mixer Output Voltage	V _{CC} , I _{Fout}	2.7	3.0	3.3	V
Driver Output Voltage	V _{CC} , V _{out1}	2.7	3.0	3.3	V
PA Drain-Source Voltage	V _{ds}	2.7	3.0	3.5	V
PA Gate-Source Voltage	V _{gs}	0	2.0	2.5	V
Operating Ambient Temperature	T _A	−30	+25	+70	°C
RF Input Frequency	f _{RF}	1.8	1.9	2.0	GHz
Local Input Power	P _{Loin}	−20	−15	−10	dBm

ELECTRICAL CHARACTERISTICS

– Tx Block – ($T_A = +25^\circ\text{C}$, $V_{CC} = V_{ds} = 3.0\text{ V}$, $Z_s = Z_L = 50\ \Omega$, unless otherwise specified)


Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
Threshold Voltage	V_{th}	$I_{ds} = 8\text{ mA}$, $V_{ds} = 3.5\text{ V}$	1.15	1.4	1.65	V
Gate-Source Voltage	V_{gs}	$f = 1.9\text{ GHz}$, $P_{in} = -19\text{ dBm}$, $P_{out} = +20.5\text{ dBm}$	1.5	1.8	2.1	V
Circuit Current (DRV + PA)	I		–	160	190	mA
Input Return Loss	RL_{in}	$f = 1.9\text{ GHz}$, $P_{in} = -19\text{ dBm}$	–	10	–	dB
Output Return Loss	RL_{out}		–	5	–	dB
Output Power	P_{out}	$f = 1.9\text{ GHz}$, $P_{in} = -19\text{ dBm}$, V_{gs} adjusting	+20.5	–	–	dBm
Power Gain (DRV + PA)	G_P		39.5	40.5	–	dB
Power Gain (DRV)	$G_P\text{ (DRV)}$		–	31	–	dB
Power Gain (PA)	$G_P\text{ (PA)}$		–	9.5	–	dB
Liner Gain	G_L	$P_{in} = -20\text{ dBm}$	–	40.5	–	dB
Adjacent Channel Power 1	P_{adj1}	$f = 1.9\text{ GHz}$, $P_{out} = +20.5\text{ dBm}$ $\Delta 600\text{ kHz}$ ^{Note}	–	–65	–58	dBc
Adjacent Channel Power 2	P_{adj2}	$f = 1.9\text{ GHz}$, $P_{out} = +20.5\text{ dBm}$ $\Delta 900\text{ kHz}$ ^{Note}	–	–70	–60	dBc
Occupied Band Width	OBW	$P_{out} = +20.5\text{ dBm}$ ^{Note}	–	250	270	kHz
2nd Harmonics Frequency Level	$2f_0$	$P_{out} = +20.5\text{ dBm}$	–40	–45	–	dBc
3rd Harmonics Frequency Level	$3f_0$	$P_{out} = +20.5\text{ dBm}$	–55	–60	–	dBc
Gain 1 dB Compression Output Power	$P_{O(1\text{ dB})}$		–	+21.0	–	dBm

Note $P_{in} = -19\text{ dBm}$, CW: Measure by changing to modulation wave, after setting from adjusting by V_{gs} to $P_{out} = +20.5\text{ dBm}$.

– Rx Block – ($T_A = +25^\circ\text{C}$, $V_{CC} = 3.0\text{ V}$, $f_{RF} = 1.9\text{ GHz}$, $f_{IF} = 240\text{ MHz}$, $f_{Lo} = 1.66\text{ GHz}$, $P_{LoIn} = -15\text{ dBm}$, $Z_s = Z_L = 50\ \Omega$, unless otherwise specified)

Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
Circuit Current	I_{cc}	No Signal	8.9	11.5	15.0	mA
Circuit Current (LNA)	I_{cCLNA}	No Signal	1.25	1.8	–	mA
Conversion Gain (LNA + Mixer)	CG	$P_{RF} = -35\text{ dBm}$	19.0	21.5	25.5	dB
Conversion Gain (LNA)	CG (LNA)	$P_{RF} = -35\text{ dBm}$	–	15.5	–	dB
Conversion Gain (Mixer)	CG (Mixer)	$P_{RF} = -20\text{ dBm}$	–	6.0	–	dB
Noise Figure	NF	SSB	–	3.1	4.5	dB
Input 3rd Order Distortion Intercept Point	IIP_3	$f_{RF1} = 1.9\text{ GHz}$, $f_{RF2} = 1.9006\text{ GHz}$, $P_{RF} = -35\text{ dBm/tone}$	–16.5	–14.5	–	dBm
Image Rejection Ratio	IMR	$f_{RF1} = 1.9\text{ GHz}$, $f_{RF2} = 1.42\text{ GHz}$, $P_{RF} = -35\text{ dBm/tone}$	30	40	–	dBc
1/2 IF Ratio	1/2 IFR	$f_{RF1} = 1.9\text{ GHz}$, $f_{RF2} = 1.78\text{ GHz}$, $P_{RF} = -35\text{ dBm/tone}$, $f_{IF} = 240\text{ MHz}$	40	50	–	dBc
Local Leak	LO_{Leak}	$LO_{in} \rightarrow LNA_{in}\text{ Leak}$	–	–62	–50	dBm



EVALUATION CIRCUIT ($V_{CC} = V_{ds} = 3.0$ V)



The application circuits and their parameters are for reference only and are not intended for use in actual design-ins.

TYPICAL CHARACTERISTICS ($T_A = +25^\circ\text{C}$, unless otherwise specified)


– Tx Block – ($V_{CC} = V_{ds} = 3.0\text{ V}$, $f = 1.9\text{ GHz}$, $P_{in} = -19\text{ dBm}$, $P_{out} = +20.5\text{ dBm}$)




Remark The graphs indicate nominal characteristics.

– Rx Block – ($V_{CC} = 3.0\text{ V}$, $f_{RF1} = 1.90\text{ GHz}$, $P_{RF1} = -35\text{ dBm}$, $f_{RF2} = 1.9006\text{ GHz}$, $P_{RF2} = -35\text{ dBm}$, $f_{LO} = 1.66\text{ GHz}$)


CONVERSION GAIN
vs. LOCAL INPUT POWER



NOISE FIGURE
vs. LOCAL INPUT POWER




IIP₃ vs. LOCAL INPUT POWER



Remark The graphs indicate nominal characteristics.

PACKAGE DIMENSIONS

16-PIN PLASTIC TSON (UNIT: mm)



Remark () : Reference value

RECOMMENDED SOLDERING CONDITIONS

This product should be soldered and mounted under the following recommended conditions. For soldering methods and conditions other than those recommended below, contact your nearby sales office.

Soldering Method	Soldering Conditions	Condition Symbol
Infrared Reflow	Peak temperature (package surface temperature) : 260°C or below Time at peak temperature : 10 seconds or less Time at temperature of 220°C or higher : 60 seconds or less Preheating time at 120 to 180°C : 120±30 seconds Maximum number of reflow processes : 3 times Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	IR260
Wave Soldering	Peak temperature (molten solder temperature) : 260°C or below Time at peak temperature : 10 seconds or less Preheating temperature (package surface temperature) : 120°C or below Maximum number of flow processes : 1 time Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	WS260
Partial Heating	Peak temperature (terminal temperature) : 350°C or below Soldering time (per side of device) : 3 seconds or less Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	HS350

Caution Do not use different soldering methods together (except for partial heating).

- **The information in this document is current as of November, 2004. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC's data sheets or data books, etc., for the most up-to-date specifications of NEC semiconductor products. Not all products and/or types are available in every country. Please check with an NEC sales representative for availability and additional information.**
- No part of this document may be copied or reproduced in any form or by any means without prior written consent of NEC. NEC assumes no responsibility for any errors that may appear in this document.
- NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC semiconductor products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of customer's equipment shall be done under the full responsibility of customer. NEC assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC endeavours to enhance the quality, reliability and safety of NEC semiconductor products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC semiconductor products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment, and anti-failure features.
- NEC semiconductor products are classified into the following three quality grades:
 "Standard", "Special" and "Specific". The "Specific" quality grade applies only to semiconductor products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of a semiconductor product depend on its quality grade, as indicated below. Customers must check the quality grade of each semiconductor product before using it in a particular application.
 "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots
 "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)
 "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.
 The quality grade of NEC semiconductor products is "Standard" unless otherwise expressly specified in NEC's data sheets or data books, etc. If customers wish to use NEC semiconductor products in applications not intended by NEC, they must contact an NEC sales representative in advance to determine NEC's willingness to support a given application.
 (Note)
 (1) "NEC" as used in this statement means NEC Corporation, NEC Compound Semiconductor Devices, Ltd. and also includes its majority-owned subsidiaries.
 (2) "NEC semiconductor products" means any semiconductor product developed or manufactured by or for NEC (as defined above).

M8E 00.4-0110

► For further information, please contact

NEC Compound Semiconductor Devices, Ltd. <http://www.ncsd.necel.com/>

E-mail: salesinfo@ml.ncsd.necel.com (sales and general)

techinfo@ml.ncsd.necel.com (technical)

Sales Division TEL: +81-44-435-1588 FAX: +81-44-435-1579

NEC Compound Semiconductor Devices Hong Kong Limited

E-mail: ncsd-hk@elhk.nec.com.hk (sales, technical and general)

Hong Kong Head Office TEL: +852-3107-7303 FAX: +852-3107-7309

Taipei Branch Office TEL: +886-2-8712-0478 FAX: +886-2-2545-3859

Korea Branch Office TEL: +82-2-558-2120 FAX: +82-2-558-5209

NEC Electronics (Europe) GmbH <http://www.ee.nec.de/>

TEL: +49-211-6503-0 FAX: +49-211-6503-1327

California Eastern Laboratories, Inc. <http://www.cel.com/>

TEL: +1-408-988-3500 FAX: +1-408-988-0279