

DA14592

DA14592 Errata

The document contains the known errata for the DA14592 along with recommended workarounds.

1. Information

Table 1. Information table

Datasheet	DA14592_Datasheet_3v0.pdf
Package(s)	WLCSP39, FCQFN52

2. Identifying the Silicon Revision

Silicon Revision is 0xAE, 0xAF (Register CHIP_REVISION_REG and CHIP_TEST1_REG).

3. Errata Summary

Table 2. Errata summary

Issue #	Issue title
1	Increased current consumption when LDO_IO bypass mode is used.

4. Errata Details

Table 3. Increased current consumption when LDO_IO bypass mode is used

Issue #	Effect
1.	Increased current consumption on V _{BAT} rail.
	Conditions
	When LDO_IO bypass mode is used. (POWER_CTRL_REG[LDO_IO_BYPASS_ACTIVE] = 1, POWER_CTRL_REG[LDO_IO_RET_ENABLE_SLEEP] = 1).
	Technical description
	A hardware design flaw in the LDO_IO bypass mode causes an increased current consumption on V _{BAT} rail. The increased current is in the range of hundreds of μA (typically around 300 μA).
	Workaround
	When IOs are required to operate at V _{BAT} level, an external PCB trace (connection) between V _{BAT} and V _{DDIO} is required. LDO_IO should be disabled (POWER_CTRL_REG[LDO_IO_ENABLE] = 0). Note that P0_01 will be pulled up to V _{DDIO} level during hibernation mode.

5. Revision History

Revision	Date	Description
1.0	Mar 19, 2024	Initial release.

STATUS DEFINITIONS

Status	Definition
DRAFT	The content of this document is under review and subject to formal approval, which may result in modifications or additions.
APPROVED or unmarked	The content of this document has been approved for publication.

ROHS COMPLIANCE

Renesas Electronics' suppliers certify that its products are in compliance with the requirements of Directive 2011/65/EU of the European Parliament on the restriction of the use of certain hazardous substances in electrical and electronic equipment. RoHS certificates from our suppliers are available on request.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.