

ISL74422ARH

Radiation Hardened 9A, Non-Inverting Power MOSFET Drivers

FN9031
Rev 2.00
April 1, 2010

The Radiation Hardened ISL74422ARH is a non-inverting, monolithic high-speed MOSFET driver designed to convert a CMOS level input signal into a high current output at voltages up to 18V. Its fast rise times and high current output allow very quick control of even the largest power MOSFETs in high frequency applications.

The input of the ISL74422ARH can be directly driven by our HS-1825ARH and IS-1845ASRH PWM devices. The 9A high current output minimizes power losses in MOSFETs by rapidly charging and discharging high gate capacitances.

Constructed with the Intersil dielectrically isolated Rad Hard Silicon Gate (RSG) BiCMOS process, these devices are immune to Single Event Latch-up and have been specifically designed to provide highly reliable performance in harsh radiation environments.

Specifications for Rad Hard QML devices are controlled by the Defense Supply Center in Columbus (DSCC). The SMD numbers listed here must be used when ordering.

Detailed Electrical Specifications for these devices are contained in SMD 5962-01521. A link is provided on our website for downloading.

Features


- QML Qualified per MIL-PRF-38535 Requirements
- Electrically Screened to DSCC SMD # 5962-01521
- Radiation Environment
 - Total Dose (Max) 300krad(SI)
 - Latch-Up Immune
- I_{PEAK} 9A(Min)
- T_F (C_L = 10,000pF) 70ns(Typ); 90ns(Max)
- T_R (C_L = 10,000pF) 90ns(Typ); 105ns(Max)
- Prop Delay High-Low (C_L = 10,000pF) 75ns(Max), 55ns(Typ)
- Prop Delay Low-High (C_L = 10,000pF) 50ns(Max), 30ns(Typ)
- Consistent Delay Times with V_{CC} Changes
- Wide Supply Voltage Range 7V to 18V
- Low Stand-by Power Consumption
 - Input Low <2mW(Max)
 - Inputs High <18mW(Max)
- ESD Protected >1750V

Applications

- Switching Power Supplies
- DC/DC Converters
- Motor Controllers

Pin Configuration

ISL74422ARH-F
(FLATPACK CDFP4-F16)
TOP VIEW



Pin Descriptions

| PIN(s) | SYMBOL | DESCRIPTION |
|------------------------|--------|---|
| 1, 2, 6, 7, 10, 11, 14 | NC | NO Connect. |
| 3 | LVS | Provides the supply voltage for the control logic. It is not internally connected to Pins 15 and 16 for noise immunity purposes, but may be connected externally. |
| 4 | IN | Input voltage to the driver. |
| 5 | LGND | Control logic return. It is not internally connected to Pins 8 and 9 for noise immunity purposes, but may be connected externally. |
| 8, 9 | GND | Pins must be connected to GND. |
| 12, 13 | OUT | Pins must be connected to output. |
| 15, 16 | VS | Pins must be connected to VS. |

Ordering Information

| ORDERING NUMBER | PART NUMBER (Note) | PART MARKING | TEMP. RANGE (°C) | PACKAGE (RoHS COMPLIANT) |
|---------------------|-----------------------|----------------------|---------------------|-----------------------------|
| 5962F0152101VXC | ISL74422ARHVF | Q5962F01 52101VXC | -55 to +125 | 16 LD Flatpack |
| 5962F0152101QXC | ISL74422ARHQF | Q5962F01 52101QXC | -55 to +125 | 16 LD Flatpack |
| 5962F0152101V9A | ISL74422ARHVX | | -55 to +125 | DIE |
| ISL74422ARHF/PROTO | ISL74422ARHF/PROTO | ISL7 4422ARHF /PROTO | -55 to +125 | 16 LD Flatpack |
| ISL74422ARHY/SAMPLE | ISL74422ARHY/SAMPLE | | -55 to +125 | DIE SAMPLE |

NOTE: These Intersil Pb-free Hermetic packaged products employ 100% Au plate - e4 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations.

Die Characteristics

DIE DIMENSIONS:

3838 μm x 4829 μm (151.1 mils x 190.1mils)
 Thickness: 483 μm \pm 25.4 μm (19 mils \pm 1 mil)

INTERFACE MATERIALS:

Glassivation:

Type: PSG (Phosphorous Silicon Glass)
 Thickness: 8.0kÅ \pm 1.0kÅ

Top Metallization:

Type: AlSiCu
 Thickness: 16.0kÅ \pm 2kÅ

Substrate:

Radiation Hardened Silicon Gate,
 Dielectric Isolation

Backside Finish:

Silicon

ASSEMBLY RELATED INFORMATION:

Substrate Potential:

Unbiased (DI)

ADDITIONAL INFORMATION:


Worst Case Current Density:

$< 2.0 \times 10^5 \text{ A/cm}^2$

Transistor Count:

30

Metallization Mask Layout



© Copyright Intersil Americas LLC 2007-2010. All Rights Reserved.
 All trademarks and registered trademarks are the property of their respective owners.

For additional products, see www.intersil.com/en/products.html

Intersil products are manufactured, assembled and tested utilizing ISO9001 quality systems as noted in the quality certifications found at www.intersil.com/en/support/qualandreliability.html

Intersil products are sold by description only. Intersil may modify the circuit design and/or specifications of products at any time without notice, provided that such modification does not, in Intersil's sole judgment, affect the form, fit or function of the product. Accordingly, the reader is cautioned to verify that datasheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.

For information regarding Intersil Corporation and its products, see www.intersil.com