

## ISL9491, ISL9491A

Single Output LNB Supply Voltage Regulator for Satellite Set-Top Box Applications

FN6531  
Rev 1.00  
August 12, 2015

These devices are designed for supplying power and control signals from advanced satellite set-top box (STB) modules to the low noise blocks (LNBS) of single antenna ports. Each device consists of a current-mode boost converter and a low-noise linear regulator along with the circuitry required for tone injection and pin controllable interface. The device makes the total LNB supply design simple, efficient and compact with low external component count.

The current-mode boost converters provide the linear regulator with input voltage that is set to the voltage at the VOUT pin plus a minimal drop to insure minimum power dissipation across the internal LDO. This maintains constant voltage drop across the linear pass element while permitting adequate voltage range for tone injection.

The final regulated output voltage is available at the cathode of the back diode to support the operation of an antenna port for a single tuner. The outputs can be set to various voltage level for the desired polarization reception by means of the logic presented to the VSET0 and VSET1 pins. An EN pin is to be driven high to enable the outputs for the PWM and linear combination; setting EN low disables the output, forcing a shutdown mode.

The external modulation input (EXTM) can accept a tone modulated DiSEqC command and transfer it symmetrically to the output to meet DiSEqC 1.x protocol. An external DiSEqC tank circuit can also be implemented to support DiSEqC 2.x.

### Ordering Information

| PART NUMBER (Note) | PART MARKING | TEMP. RANGE (°C) | PACKAGE (Pb-free) | PKG. DWG. # |
|--------------------|--------------|------------------|-------------------|-------------|
| ISL9491ERZ*        | 94 91ERZ     | -20 to +85       | 16 Ld QFN         | L16.4x4     |
| ISL9491AERZ*       | 94 91AERZ    | -20 to +85       | 16 Ld QFN         | L16.4x4     |

\*Add "-T" suffix for tape and reel. Please refer to TB347 for details on reel specifications.

NOTE: These Intersil Pb-free plastic packaged products employ special Pb-free material sets, molding compounds/die attach materials, and 100% matte tin plate plus anneal (e3 termination finish, which is RoHS compliant and compatible with both SnPb and Pb-free soldering operations). Intersil Pb-free products are MSL classified at Pb-free peak reflow temperatures that meet or exceed the Pb-free requirements of IPC/JEDEC J STD-020.


### Features

- Single Chip Power Solution
  - Operation for 1-Tuner/1-Dish Applications
- Switch-Mode Power Converter for Lowest Dissipation
  - Boost PWMs with >92% Efficiency
  - Pin Controllable Enable and Output
- 2.5V/3.3V/5V Logic Compatible
- FAULT Signal
- DIRECTV SWM Compliant
- VSET Pin to Toggle between Vertical and Horizontal Polarizations
- External Tone Input
- Internal Overcurrent and Over-Temperature Protection
- Pb-Free (ROHs Compliant)

### Applications

- LNB Power Supply and Control for Satellite Set-Top Box


### Pin Configuration



## Functional Pin Description

| SYMBOL          | FUNCTION  |
|-----------------|---|
| VSW             | Input of the linear post-regulator.   |
| PGND            | Dedicated ground for the output gate driver of respective PWM.  |
| CS              | Current sense input; connect the sense resistor $R_{SC}$ at this pin for desired peak overcurrent value for the boost FET.                    |
| SGND            | Small signal ground for the IC.   |
| TCAP            | Capacitor for setting rise and fall time of the output voltage. Typical value is 0.1 $\mu$ F.   |
| BYPASS          | Connect a bypass capacitor of 1 $\mu$ F for the internal 5V.  |
| VCC             | Main power supply to the chip.  |
| GATE            | This pin connects to the Gate of the Boost FET.   |
| VOUT            | Output voltage for the LNB meant to be connected to the anode of a back diode in series with the LNB output.                                  |
| VSENSE          | This pin provides for a sensing and pull-down function for the VLNB and is meant to be connected to the cathode of the back diode.            |
| EXTM            | This is an input for externally modulated DiSEqC tone signal, which is transferred symmetrically onto VLNB.                                   |
| VSET0,<br>VSET1 | Output voltage selection pins.  |
| EN              | When this pin is low, the output is disabled in a low power standby state. Setting EN = 1 enables the output voltage.                         |
| FAULT           | This an open drain output to be pulled up to the logic high through a resistor. A low indicates that the output voltage is out of regulation. |
| ILIMIT          | The ILIMIT is used to set the value of the output current limit from the linear. A resistor from ILIMIT to GND programs this limit.           |

# Block Diagram





**Absolute Maximum Ratings**

|  |               |
|--|---------------|
| VCC (Input Voltage)                    | 8.0V to 18.0V |
| VOUT, VSW                              | -0.3V to 24V  |
| BYPASS                                 | -0.3V to 5.5V |
| EN, VSET0/1, EXTM (Logic Control Pins) | -0.3V to 5.5V |
| All Pins Referenced to Ground          |               |

**Thermal Information**

|                                       |   |                      |
|---------------------------------------|---|----------------------|
| Thermal Resistance (Typical)          | $\theta_{JA}$ (°C/W)  | $\theta_{JC}$ (°C/W) |
| QFN Package (Notes 2, 3)              | 47  | 9.5                  |
| Maximum Junction Temperature (Note 4) | +150°C  |                      |
| Maximum Storage Temperature Range     | -40°C to +150°C   |                      |
| Pb-Free Reflow Profile                | see link below  |                      |
|                                       | <a href="http://www.intersil.com/pbfree/Pb-FreeReflow.asp">http://www.intersil.com/pbfree/Pb-FreeReflow.asp</a> |                      |

**Recommended Operating Conditions**

|             |                |
|-------------|----------------|
| Temperature | -20°C to +85°C |
|-------------|----------------|

**CAUTION:** Do not operate at or near the maximum ratings listed for extended periods of time. Exposure to such conditions may adversely impact product reliability and result in failures not covered by warranty.

**NOTES:**

- $\theta_{JA}$  is measured in free air with the component mounted on a high effective thermal conductivity test board with "direct attach" features. See Tech Brief TB379.
- For  $\theta_{JC}$ , the "case temp" location is the center of the exposed metal pad on the package underside.
- The device junction temperature should be kept below +150°C. Thermal shut-down circuitry turns off the device if junction temperature exceeds +130°C typical.

**Electrical Specifications**  $V_{CC} = 12V$ ,  $T_A = -20^\circ C$  to  $+85^\circ C$ , unless otherwise noted. Typical values are at  $T_A = +25^\circ C$ .

| PARAMETER                                 | SYMBOL                                 | TEST CONDITIONS   | MIN  | TYP  | MAX  | UNITS |
|---|--|---|------|------|------|-------|
| Operating Supply Voltage Range            |  | ISL9491   | 8    | 12   | 14   | V     |
|   |  | ISL9491A  | 8    | 10   | 11   | V     |
| Supply Current (I <sub>vcc</sub> current) | I <sub>IN</sub>                        | EN = 1, Boost disconnected, and ext. 14.5V supply on VSW when V <sub>OUT</sub> = 13.3V, No Load | -    | 4    | 8    | mA    |
| <b>UNDERVOLTAGE LOCKOUT</b>               |  |   |      |      |      |       |
| Stop Threshold                            |  | Input voltage falling from above 8V   | -    | 4.4  | -    | V     |
| Start Threshold                           |  | Input voltage rising from 0V  | -    | 4.9  | -    | V     |
| Output Voltage, ISL9491                   | V <sub>O</sub>                         | EN = 1, VSET1 = 0, VSET0 = 0  | 12.8 | 13.3 | 13.6 | V     |
|   |  | EN = 1, VSET1 = 0, VSET0 = 1  | 17.7 | 18.3 | 18.7 | V     |
|   |  | EN = 1, VSET1 = 1, VSET0 = 0  | 13.8 | 14.3 | 14.6 | V     |
|   |  | EN = 1, VSET1 = 1, VSET0 = 1  | 19.4 | 20.0 | 20.4 | V     |
| Output Voltage, ISL9491A                  | V <sub>O</sub>                         | EN = 1, VSET1 = 0, VSET0 = 0  | 10.5 | 11.0 | 11.3 | V     |
|   |  | EN = 1, VSET1 = 0, VSET0 = 1  | 14.5 | 15.0 | 15.3 | V     |
|   |  | EN = 1, VSET1 = 1, VSET0 = 0  | 11.5 | 12.0 | 12.3 | V     |
|   |  | EN = 1, VSET1 = 1, VSET0 = 1  | 15.5 | 16.0 | 16.3 | V     |
| Line Regulation                           | DV <sub>O1</sub> ,<br>DV <sub>O2</sub> | V <sub>IN</sub> = 8V to 14V; V <sub>O</sub> = 13.30V  | -    | 4    | 40   | mV    |
|   |  | V <sub>IN</sub> = 8V to 14V; V <sub>O</sub> = 18.30V  | -    | 4    | 60   | mV    |
| Load Regulation                           | DV <sub>O1</sub> ,<br>DV <sub>O2</sub> | I <sub>O</sub> = 0mA to 350mA, V <sub>OUT</sub> = 13.3V   | -    | 125  | 180  | mV    |
|   |  | I <sub>O</sub> = 0mA to 500mA, V <sub>OUT</sub> = 13.3V (Note 4)                                | -    | 190  | 260  | mV    |
| Output Overcurrent Threshold              | I <sub>OCT</sub>                       | R at I <sub>LIMIT</sub> = 148k (Note 8)   | 270  | 350  | 435  | mA    |
| Internal Regulator Overcurrent Clamp      | I <sub>OCLMP</sub>                     | Output Shorted to GND, R <sub>LIM</sub> = 0   |      |      | 860  | mA    |

**Electrical Specifications**  $V_{CC} = 12V$ ,  $T_A = -20^{\circ}C$  to  $+85^{\circ}C$ , unless otherwise noted. Typical values are at  $T_A = +25^{\circ}C$ . **(Continued)**


| PARAMETER                                    | SYMBOL       | TEST CONDITIONS   | MIN | TYP | MAX | UNITS   |
|--|--------------|---|-----|-----|-----|---------|
| Dynamic Overload Protection Off-Time         | $t_{OFF}$    | Output Shorted to GND (Note 6)  | -   | 900 | -   | ms      |
| Dynamic Overload Protection On-Time          | $t_{ON}$     |   | -   | 50  | -   | ms      |
| TCAP Charging Current                        | $TCAP_C$     | TCAP Pin = 0V   | -   | 22  | -   | $\mu A$ |
| TCAP Discharging Current                     | $TCAP_D$     | TCAP Pin = 2V   | -   | 21  | -   | $\mu A$ |
| <b>LINEAR REGULATOR</b>                      |              |   |     |     |     |         |
| Drop-out Voltage                             |              | $I_{OUT} = 500mA$ , with a Schottky b/w $V_{sw}$ and $V_{OUT}$ (Note 4)                           | -   | 1.2 | 1.4 | V       |
| Output Backward Leakage Current              | $I_{BKLK}$   | $EN = 0$ ; $V_{OBK} = 24V$ (Note 9)   | -   | 2.0 | 3.0 | mA      |
| Output Undervoltage (After Initial Power-up) |              | $\overline{FAULT}$ asserted for typical $V_{OUT} = 13.3V$   | -12 | -   | -1  | %       |
| Output Overvoltage (After Initial Power-up)  |              | $\overline{FAULT}$ asserted for typical $V_{OUT} = 13.3V$   | +1  | -   | +12 | %       |
| <b>EN, VSET, EXTM INPUT PINS (Note 5)</b>    |              |   |     |     |     |         |
| Asserted LOW                                 |              |   | -   | -   | 0.8 | V       |
| Asserted HIGH                                |              |   | 2.5 | -   | -   | V       |
| Input Current                                |              |   | -   | 25  | -   | $\mu A$ |
| Tone Input Frequency                         | ISL9491      | EXTM input  |     | 22  |     | kHz     |
|  | ISL9491A     | EXTM input  |     | 44  |     | kHz     |
| $V_{OUT}$ Tone Amplitude                     | ISL9491      | EXTM input = 22kHz square wave<br>$V_{max} = 2.5V$ , $V_{min} = 0V$ , Duty = 50%,                 | 400 | 650 | 900 | mV      |
|  | ISL9491A     | EXTM input = 44kHz square wave<br>$V_{max} = 2.5V$ , $V_{min} = 0V$ , Duty = 50%                  | 400 | 650 | 900 | mV      |
| $V_{OUT}$ Tone Rise (Note 10)                | ISL9491      | EXTM input = 22kHz square wave<br>$V_{Hmax} = 2.5V$ , $V_{Lmin} = 0V$ , $R_L = 1k$                | 5   | 10  | 15  | $\mu s$ |
|  | ISL9491A     | EXTM input = 44kHz square wave<br>$V_{Hmax} = 2.5V$ , $V_{Lmin} = 0V$ , $R_L = 1k$                | 4   | 6   | 8   | $\mu s$ |
| $V_{OUT}$ Tone Fall (Note 10)                | ISL9491      | EXTM input = 22kHz square wave<br>$V_{Hmax} = 2.5V$ , $V_{Lmin} = 0V$ , Duty = 50%,<br>$R_L = 1k$ | 5   | 10  | 15  | $\mu s$ |
|  | ISL9491A     | EXTM input = 44kHz square wave<br>$V_{Hmax} = 2.5V$ , $V_{Lmin} = 0V$ , Duty = 50%,<br>$R_L = 1k$ | 4   | 6   | 8   | $\mu s$ |
| <b>CURRENT SENSE (CS PIN)</b>                |              |   |     |     |     |         |
| Overcurrent Threshold                        | $V_{CS}$     |   | 380 | 445 | 510 | mV      |
| <b>BYPASS</b>                                |              |   |     |     |     |         |
| Voltage at BYPASS pin                        | $V_{BYPASS}$ | (Note 7)  | -   | 5   | -   | V       |
| <b>PWM</b>                                   |              |   |     |     |     |         |
| Maximum Duty Cycle                           |              |   | 90  | 93  | -   | %       |
| Minimum Pulse Width                          |              |   | -   | 20  | -   | ns      |

**Electrical Specifications**  $V_{CC} = 12V, T_A = -20^{\circ}C$  to  $+85^{\circ}C$ , unless otherwise noted. Typical values are at  $T_A = +25^{\circ}C$ . (Continued)

| PARAMETER                       | SYMBOL   | TEST CONDITIONS           | MIN | TYP | MAX | UNITS       |
|---------------------------------|----------|---------------------------|-----|-----|-----|-------------|
| <b>OSCILLATOR</b>               |          |                           |     |     |     |             |
| Oscillator Frequency            | $f_{sw}$ | Boost switching frequency | 380 | 440 | 480 | kHz         |
| Thermal Shutdown                |          |                           |     |     |     |             |
| Temperature Shutdown Threshold  |          | (Note 4)                  | -   | 130 | -   | $^{\circ}C$ |
| Temperature Shutdown Hysteresis |          | (Note 4)                  | -   | 20  | -   | $^{\circ}C$ |

- VSET, EXTM, EN pins have 200kΩ internal pull-down resistors.
- In the Dynamic current limit mode, the output is ON for 50ms and OFF for 900ms but it remains continuously ON when RILIM=0.
- This pin is to connect a bypass capacitor in order to decouple the internal LDO and is not designed to source external circuits.
- The value of the  $R_{LIMIT}$  resistor will determine the overcurrent threshold at which the 50ms timer is activated.
- This defines the back voltage applicable to the VSENSE pin. The VOUT pin will not support back bias and hence will need the use of a back diode for protection.

**Tone Waveform**



NOTES:

- The tone rise and fall times are not shown due to resolution of graphics. It is 5/10µs typical.
- The EXTM pins have input thresholds of  $V_{il(max)} = 0.8V$  and  $V_{ih(min)} = 2.5V$

FIGURE 1. TONE WAVEFORM

**Typical Performance Curves**




FIGURE 2. BOOST EFFICIENCY FOR 12VIN TO 14.3VOUT




FIGURE 3. SYSTEM EFFICIENCY (BOOST + LDO) FOR 12VIN TO 13.3VOUT

## Typical Performance Curves (Continued)




FIGURE 4. V\_LNB RISE TIME WITH T\_CAP = 0.22µF is 13ms




FIGURE 5. V\_LNB RISE TIME WITH T\_CAP = 0.44µF is 32ms




FIGURE 6. BOOST SWITCH NODE AT 0A (DISCONTINUOUS)




FIGURE 7. BOOST SWITCH NODE AT 100mA (PARTIAL CONTINUOUS)




FIGURE 8. BOOST SWITCH NODE AT 300mA (CONTINUOUS MODE)




FIGURE 9. V\_LNB TRANSITIONS FROM 13.3V TO 18.3V



## Typical Performance Curves (Continued)




FIGURE 10. VLNB TRANSITIONS FROM 18.3V TO 13.3V




FIGURE 11. 22kHz TONE ON 13.3V<sub>OUT</sub> WITH 50mA LOAD




FIGURE 12. 22kHz TONE ON 13.3V<sub>OUT</sub> WITH 500mA LOAD




FIGURE 13. AC NOISE ON 13.3V<sub>OUT</sub> AT 500mA OF LOAD




FIGURE 14. VLNB CONNECTED TO 350mA LOAD WITH  $R_{LIM} = 148k$




FIGURE 15. VLNB SHORTED TO GND, 200mA<sup>2</sup>

## Typical Performance Curves (Continued)




FIGURE 16. OUTPUT CURRENT AND VOLTAGE WITH OUTPUT SHORTED TO GND,  $R_{ILIM} = 0$




FIGURE 17. THE ISL9491 ENTERING THERMAL SHUTDOWN WITH  $R_{ILIM} = 0$




FIGURE 18. THE ISL9491 IN THERMAL EQUILIBRIUM WITH  $R_{ILIM} = 0$

## Functional Description

The ISL9491 or ISL9491A single output voltage regulator makes an ideal choice for advanced satellite set-top box and personal video recorder applications. The device utilizes built-in DC/DC step-up converters, which operate from a single supply source ranging from 8V to 14V and generate the voltage needed to enable the linear post-regulator to work with minimum dissipated power. An undervoltage lockout circuit disables the device when VCC drops below a fixed threshold (4.5V typical).

### DiSEqC Encoding

The EXTM accepts an externally modulated tone command and in turn modulates the  $V_{LNB}$  symmetrically to meet the DiSEqC 1.0 and DiSEqC 2.0 transmit protocol. Burst coding of the tone can be accomplished due to the fast response of the EXTM pin.

### Linear Regulator

The output linear regulator is designed to source 500mA continuous current and 750mA peak. The sink feature is limited and thus requires a bleeder resistor of 3.3k $\Omega$  to be connected at the VLNB to enable proper tone modulation capability into capacitive loads as high as 0.22 $\mu$ F. In order to minimize the power dissipation, the output voltage of the internal step-up converter is adjusted to allow the linear regulator to work at a minimum dropout of 1.2V typical (Load current = 500mA) between the VSW and VOUT pin. The VOUT pin drives the anode of the back diode and the VSENSE pin drives the cathode of the back diode. The VSENSE pin is capable of withstanding a back voltage of 24V.

When the device is put in the shutdown mode (EN = LOW), the PWM power block is disabled. When the regulator blocks are active (EN = HIGH), the output can be controlled by the VSET0 and VSET1 pins to be 13.3V, 14.3V, 18.3V or 20V (typical ISL9491) or 11V, 12V, 15V, or 16V (typical ISL9491A) for remote controlling of non-DiSEqC LNBS.

A separate open-drain FAULT pin serves as an interrupt and is driven low by undervoltage, overvoltage and linear overcurrent and over-temperature faults.

### Output Voltage Rise and Fall Time Timing

The output voltage rise and fall times or soft-start time can be set by an external capacitor on the TCAP pin. The output rise and fall times are given by Equation 1:

$$C = \frac{220t_{rise}}{\Delta V} \quad (\text{EQ. 1})$$

Where C is the TCAP value in nF,  $t_{rise}$  the required transition time in ms and  $\Delta V$  is the differential transition voltage from low output voltage range to the high output range in Volts.

Too large a value of TCAP prevents the output from rising to the nominal value, within a reasonable time. Too small a value of the TCAP can cause high peak currents in the boost circuit. Figures 4 and 5 show the output voltage rise time for TCAP value of 0.22 $\mu$ F and 0.44 $\mu$ F as 13.6ms and 32ms which according to Equation 1 should be

13.3ms and 26.6ms. The difference between measured and calculated values is due to capacitor tolerance of  $\pm 20\%$ . Since the output voltage uses TCAP voltage as a reference, it is recommended to use a 10k $\Omega$  resistor in series to filter out some of the switching noise from injecting on this pin.

### Dynamic and Static Current Limiting

When the LDO current exceeds the preset overcurrent threshold set by means of a resistor from the ILIMIT pin to GND for a period of 50ms, the device enters a  $t_{ON} = 50\text{ms}/t_{OFF} = 900\text{ms}$  routine. This type of current limiting is also called "Dynamic Current Limiting", which is used extensively on other Intersil LNB controllers. A linear overcurrent will drive the FAULT pin low during the  $t_{OFF} = 900\text{ms}$  period. This operation continues until the fault is removed. Upon removal of the fault, the device returns to normal operation after a successful soft-start cycle. Figure 14 shows the output current and voltage waveforms with an  $I_{LIMIT}$  resistor of 148k $\Omega$  and a load current of 350mA. It can be seen that under this loading condition, the chip stays powered up and sources load current for 50ms and turns-off for approximately 900ms. The output voltage ramps up to programmed output voltage during the on time. This cycle repeats itself until load current is reduced below the current limit value of 350mA. Equation 2 shows the relationship between  $I_{LIMIT}$  resistor and load current:

$$I_{LIMIT} = 52,000 \times \frac{\alpha}{R_{LIMIT}} \quad (\text{EQ. 2})$$

$I_{LIMIT}$  is the programmed load current in mA before the chip goes into current limit where  $R_{LIMIT}$  is in k $\Omega$ . Alpha ( $\alpha$ ) is a gain term which is shown in Figure 19 and has a value of one at 350mA. It is a good design practice to use a 1% tolerance resistor and allow for at least 20% higher margin on the maximum load current when calculating the  $R_{LIMIT}$  resistor value.




FIGURE 19. ALPHA CONSTANT

Figure 15 shows the output current and voltage for  $R_{LIMIT} = 148\text{k}\Omega$  when the output voltage is shorted to GND. Under this condition, the chip still exhibits the 50ms on and 900ms off pulse to minimize power dissipation, however, current gets internally clamped to approximately 750mA. The output voltage stays at 0V

due to hard short on the output. The current limiting described so far is called “Dynamic Current” limiting which limits current to approximately 750mA for 50ms and turns off the output for 900ms.  $R_{ILIMIT}$  is used to program the current level at which the ISL9491 enters into this protection mode. On the other hand, the ISL9491 can also be programmed in “Static Current Limit” mode which defeats the 50ms/900ms(on/off) pulse by delivering constant 750mA load current to the system by using a  $0\Omega$   $R_{ILIMIT}$  resistor. In this mode the chip will deliver this current to the load for as long as the die junction temperature is less than 130°C. Figure 16 shows the static current limit by shorting the output to GND. It also shows that initially the chip delivers 750mA but the junction starts heating up since approximately 10W ( $13.3V \times 0.75A$ ) is being dissipated internally. The thermal shutdown circuitry takes over and shuts the output LDO stage-off after approximately 50ms and the load current drops to zero as seen in Figure 17. The chip restarts as soon as the junction temperature drops below the thermal shutdown level but quickly shuts off in 15ms as seen in Figure 18.

The CS pin provides peak current protection for the Boost FET on a pulse-by-pulse basis. Once the voltage on the FET source sense resistor crosses 0.45V typical, the Boost FET drive is set to low. The sense resistor can be sized to limit the peak current through the FET. It is highly recommended to have a boost current limit of 200% when sizing the sense resistor to accommodate high current transients in the boost circuit.

### Thermal Protection

This IC is protected against overheating. When the junction temperature exceeds +130°C (typical), the step-up converter and the linear regulator are shut-off. When the junction is cooled down to +110°C (typical), normal operation is resumed.

### External Output Voltage Selection

The pin VSET0 and VSET1 are provided for switching between typical output voltages, as indicated in Table 1.

TABLE 1.

| EN | VSET1 | VSET0 | VLNB<br>ISL9491 | VLNB<br>ISL9491A |
|----|-------|-------|-----------------|------------------|
| 0  | X     | X     | Disabled        | Disabled         |
| 1  | 0     | 0     | 13.3V           | 11.0V            |
| 1  | 0     | 1     | 18.3V           | 15.0V            |
| 1  | 1     | 0     | 14.3V           | 12.0V            |
| 1  | 1     | 1     | 20.0V           | 16.0V            |

### Output Over/Undervoltage Fault and EXTM

The recommended start-up sequence is Vcc going high followed by ENABLE while EXTM is pulled low. This will start the output voltage to ramp up with a dv/dt which is based on the TCAP value. Once ENABLE is pulled high, allow a 50ms delay before applying 22kHz/44kHz, 50% square pulse on EXTM pin to generate the DISEQ tone on the output. At this point, FAULT should also be high, indicating that output voltage is in regulation. FAULT is designed to stay high when the output voltage is commanded to transition between the values listed in Table 1, and also when passing the DiSEQ tone on the output. FAULT will immediately pull low if there is a short on the output or if the voltage falls outside the  $\pm 10\%$  window indicating that the voltage is out of regulation. FAULT signal is armed after the first initial power-up when output voltage is in steady-state. If tone is applied to the EXTM pin before the chip is ENABLED, it causes the FAULT to remain low even after the output voltage reaches steady state. This issue can be resolved by pulling the EXTM low for 2 cycles which is 90ms of ISL9491 and 45ms for ISL9491A.

© Copyright Intersil Americas LLC 2009-2015. All Rights Reserved.

All trademarks and registered trademarks are the property of their respective owners.

For additional products, see [www.intersil.com/en/products.html](http://www.intersil.com/en/products.html)

Intersil products are manufactured, assembled and tested utilizing ISO9001 quality systems as noted in the quality certifications found at [www.intersil.com/en/support/qualandreliability.html](http://www.intersil.com/en/support/qualandreliability.html)

*Intersil products are sold by description only. Intersil may modify the circuit design and/or specifications of products at any time without notice, provided that such modification does not, in Intersil's sole judgment, affect the form, fit or function of the product. Accordingly, the reader is cautioned to verify that datasheets are current before placing orders. Information furnished by Intersil is believed to be accurate and reliable. However, no responsibility is assumed by Intersil or its subsidiaries for its use; nor for any infringements of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Intersil or its subsidiaries.*

For information regarding Intersil Corporation and its products, see [www.intersil.com](http://www.intersil.com)

---

## Revision History

The revision history provided is for informational purposes only and is believed to be accurate, but not warranted. Please go to the web to make sure that you have the latest revision.

| DATE            | REVISION | CHANGE   |
|-----------------|----------|--|
| August 12, 2015 | FN6531.1 | Updated Ordering Information table on page 1.<br>Added Revision History and About Intersil sections. |

---

## About Intersil

Intersil Corporation is a leading provider of innovative power management and precision analog solutions. The company's products address some of the largest markets within the industrial and infrastructure, mobile computing and high-end consumer markets.

For the most updated datasheet, application notes, related documentation and related parts, please see the respective product information page found at [www.intersil.com](http://www.intersil.com).

You may report errors or suggestions for improving this datasheet by visiting [www.intersil.com/ask](http://www.intersil.com/ask).


Reliability reports are also available from our website at [www.intersil.com/support](http://www.intersil.com/support)

# Package Outline Drawing

## L16.4x4

### 16 LEAD QUAD FLAT NO-LEAD PLASTIC PACKAGE

Rev 6, 02/08



**NOTES:**

1. Dimensions are in millimeters.  
Dimensions in ( ) for Reference Only.
2. Dimensioning and tolerancing conform to AMSE Y14.5m-1994.
3. Unless otherwise specified, tolerance : Decimal ± 0.05
4. Dimension b applies to the metallized terminal and is measured between 0.15mm and 0.30mm from the terminal tip.
5. Tiebar shown (if present) is a non-functional feature.
6. The configuration of the pin #1 identifier is optional, but must be located within the zone indicated. The pin #1 identifier may be either a mold or mark feature.