



Test Report

Report No. A2210106001101

Page 1 of 14

Company Name MITSUI HIGH-TEC (SHANGHAI) CO.,LTD
shown on Report

Address NO.2001 XINJIN QIAO ROAD EXPORT PROCESSING ZONE PUDONG SHANGHAI
CHINA

The following sample(s) and sample information was/were submitted and identified by/on the behalf of the applicant

Sample Name(s) C7025+Ag
Sample Received Date Mar. 26, 2021
Testing Period Mar. 26, 2021 to Apr. 8, 2021

Test Requested As specified by client, to test Lead (Pb), Cadmium (Cd), Mercury (Hg), Hexavalent Chromium (Cr(VI)), Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs), Arsenic(As), Beryllium(Be), Antimony(Sb), Hexabromocyclododecane (HBCDD), Fluorine (F), Chlorine (Cl), Bromine (Br), Iodine (I), Short Chain Chlorinated Paraffins (SCCPs), Polychlorinated Naphthalenes (PCNs), Polychlorinated terphenyls (PCTs), Polychlorinated Biphenyls(PCBs), Perfluorooctane Sulfonates(PFOS), Perfluorooctanoic Acid(PFOA), Organotin compounds, Phthalates, Polyvinyl Chloride (PVC) , Phosphorus(P) in the submitted sample(s).

Test Method/Test Result(s) Please refer to the following page(s).

Tested by

Yang Huifeng

Reviewed by

Summer Xu

Approved by

Chen Kaimin

Date

Apr. 8, 2021

Chen kaimin
Lab Manager

No. R396661059

Centre Testing International Pinbiao(Shanghai) Co., Ltd.

No.1351, Wanfang Road, Minhang District, Shanghai, China



Test Report

Report No. A2210106001101

Page 2 of 14

Conclusion

<u>Tested Sample</u>	<u>According to standard/directive</u>	<u>Result</u>
Submitted Sample	RoHS Directive 2011/65/EU with amendment (EU) 2015/863	PASS

PASS means that the results shown on the report comply with the limits set by RoHS Directive 2011/65/EU with amendment (EU) 2015/863.

Test Report

Report No. A2210106001101

Page 3 of 14

Test Method

Tested Item(s)	Test Method	Measured Equipment(s)
Lead (Pb)	IEC 62321-5:2013	ICP-OES
Cadmium (Cd)	IEC 62321-5:2013	ICP-OES
Mercury (Hg)	IEC 62321-4:2013+AMD1:2017 CSV	ICP-OES
Hexavalent Chromium (Cr(VI))	IEC 62321-7-1:2015	UV-Vis
Polybrominated Biphenyls (PBBs)	IEC 62321-6:2015	GC-MS
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321-6:2015	GC-MS
Phthalates (DBP, BBP, DEHP, DIBP)	IEC 62321-8:2017	GC-MS
Arsenic(As)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES
Beryllium(Be)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES
Antimony(Sb)	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES
Hexabromocyclododecane (HBCDD)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS
Fluorine (F)	Refer to EN 14582:2016	IC
Chlorine (Cl)	Refer to EN 14582:2016	IC
Bromine (Br)	Refer to EN 14582:2016	IC
Iodine (I)	Refer to EN 14582:2016	IC
Short Chain Chlorinated Paraffins (SCCPs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS(NCI)
Polychlorinated Naphthalenes (PCNs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2018*	GC-MS
Polychlorinated terphenyls (PCTs)	Refer to US EPA 3550C:2007 & US EPA 8270D:2014*	GC-MS
Polychlorinated Biphenyls(PCBs)	Refer to US EPA 3550C:2007 & US EPA 8270E:2017*	GC-MS
Perfluorooctane Sulfonates(PFOS)	Refer to US EPA 3550C:2007 & US EPA 8321B:2007*	LC-MS-MS/LC-MS
Perfluorooctanoic Acid(PFOA)	Refer to US EPA 3550C:2007 & US EPA 8321B:2007*	LC-MS-MS/LC-MS
Organotin compounds	Refer to US EPA 3550C:2007 & ISO 17353:2004*	GC-MS
Phthalates (BBP,DEHP,DBP,DNHP,DPP, DIBP,DIDP,DINP,DNOP)	Refer to EN 14372:2004(E)*	GC-MS
Polyvinyl Chloride (PVC)	Refer to JY/T 001-1996*	FT-IR

Test Report

Report No. A2210106001101

Page 4 of 14

Tested Item(s)	Test Method	Measured Equipment(s)
Phosphorus(P) #	Refer to US EPA 3050B:1996 & US EPA 6010D:2018*	ICP-OES

Test Result(s)

Tested Item(s)	Result	MDL	Limit
Lead (Pb)	30 mg/kg	2 mg/kg	1000 mg/kg
Cadmium (Cd)	N.D.	2 mg/kg	100 mg/kg
Mercury (Hg)	N.D.	2 mg/kg	1000 mg/kg
Hexavalent Chromium (Cr(VI))	N.D. ▼	0.10 µg/cm ² (LOQ)	1000 mg/kg

Tested Item(s)	Result	MDL	Limit
Polybrominated Biphenyls (PBBs)			
Monobromobiphenyl	N.D.	5 mg/kg	1000 mg/kg
Dibromobiphenyl	N.D.	5 mg/kg	
Tribromobiphenyl	N.D.	5 mg/kg	
Tetrabromobiphenyl	N.D.	5 mg/kg	
Pentabromobiphenyl	N.D.	5 mg/kg	
Hexabromobiphenyl	N.D.	5 mg/kg	
Heptabromobiphenyl	N.D.	5 mg/kg	
Octabromobiphenyl	N.D.	5 mg/kg	
Nonabromobiphenyl	N.D.	5 mg/kg	
Decabromobiphenyl	N.D.	5 mg/kg	

Test Report

Report No. A2210106001101

Page 5 of 14

Tested Item(s)	Result	MDL	Limit
Polybrominated Diphenyl Ethers (PBDEs)			
Monobromodiphenyl ether	N.D.	5 mg/kg	1000 mg/kg
Dibromodiphenyl ether	N.D.	5 mg/kg	
Tribromodiphenyl ether	N.D.	5 mg/kg	
Tetrabromodiphenyl ether	N.D.	5 mg/kg	
Pentabromodiphenyl ether	N.D.	5 mg/kg	
Hexabromodiphenyl ether	N.D.	5 mg/kg	
Heptabromodiphenyl ether	N.D.	5 mg/kg	
Octabromodiphenyl ether	N.D.	5 mg/kg	
Nonabromodiphenyl ether	N.D.	5 mg/kg	
Decabromodiphenyl ether	N.D.	5 mg/kg	

Tested Item(s)	Result	MDL	Limit
Phthalates (DBP, BBP, DEHP, DIBP)			
Dibutyl phthalate (DBP) CAS#:84-74-2	N.D.	50 mg/kg	1000 mg/kg
Butyl benzyl phthalate (BBP) CAS#:85-68-7	N.D.	50 mg/kg	1000 mg/kg
Di-(2-ethylhexyl) phthalate (DEHP) CAS#:117-81-7	N.D.	50 mg/kg	1000 mg/kg
Diisobutyl phthalate (DIBP) CAS#:84-69-5	N.D.	50 mg/kg	1000 mg/kg

Tested Item(s)	Result	MDL
Arsenic (As)	N.D.	10 mg/kg

Tested Item(s)	Result	MDL
Beryllium (Be)	N.D.	10 mg/kg

Test Report

Report No. A2210106001101

Page 6 of 14

Tested Item(s)	Result	MDL
Antimony (Sb)	N.D.	10 mg/kg

Tested Item(s)	Result	MDL
Hexabromocyclododecane (HBCDD)	N.D.	5 mg/kg

Tested Item(s)	Result	MDL
Fluorine (F)	N.D.	10 mg/kg
Chlorine (Cl)	N.D.	10 mg/kg
Bromine (Br)	N.D.	10 mg/kg
Iodine (I)	N.D.	10 mg/kg

Tested Item(s)	Result	MDL
Short Chain Chlorinated Paraffins (SCCPs)	N.D.	100 mg/kg

Tested Item(s)	Result	MDL
Polychlorinated Naphthalenes (PCNs)	N.D.	5 mg/kg

Tested Item(s)	Result	MDL
Polychlorinated Triphenyls (PCTs)	N.D.	5 mg/kg

Test Report

Report No. A2210106001101

Page 7 of 14

Tested Item(s)	Result	MDL
Polychlorinated Biphenyls(PCBs)		
Monochlorobiphenyl	N.D.	5 mg/kg
Dichlorobiphenyl	N.D.	5 mg/kg
Trichlorobiphenyl	N.D.	5 mg/kg
Tetrachlorobiphenyl	N.D.	5 mg/kg
Pentachlorobiphenyl	N.D.	5 mg/kg
Hexachlorobiphenyl	N.D.	5 mg/kg
Heptachlorobiphenyl	N.D.	5 mg/kg
Octachlorobiphenyl	N.D.	5 mg/kg
Nonachlorobiphenyl	N.D.	5 mg/kg
Decachlorobiphenyl	N.D.	5 mg/kg

Tested Item(s)	Result	MDL
Perfluorooctane Sulfonates (PFOS)	N.D.	5 mg/kg

Tested Item(s)	Result	MDL
Perfluorooctanoic Acid (PFOA)	N.D.	5 mg/kg

Tested Item(s)	Result	MDL
Organotin compounds		
Dibutyltin (DBT)	N.D.	5 mg/kg
Diocetyl tin (DOT)	N.D.	5 mg/kg
Tributyltin (TBT)	N.D.	5 mg/kg
Triphenyltin (TPHT)	N.D.	5 mg/kg
Tributyltin oxide (TBTO)* ¹	N.D.	5 mg/kg

Test Report

Report No. A2210106001101

Page 8 of 14

Tested Item(s)	Result	MDL
Phthalates		
Dibutyl phthalate (DBP) CAS#:84-74-2	N.D.	50 mg/kg
Butyl benzyl phthalate (BBP) CAS#:85-68-7	N.D.	50 mg/kg
Di-(2-ethylhexyl) phthalate (DEHP) CAS#:117-81-7	N.D.	50 mg/kg
Di-n-octyl phthalate (DNOP) CAS#:117-84-0	N.D.	50 mg/kg
Di-isononyl phthalate (DINP) CAS#:28553-12-0,68515-48-0	N.D.	50 mg/kg
Di-iso-decyl phthalate (DIDP) CAS#:26761-40-0,68515-49-1	N.D.	50 mg/kg
Diisobutyl phthalate (DIBP) CAS#:84-69-5	N.D.	50 mg/kg
Dipentyl phthalate (DPP) CAS#:131-18-0	N.D.	50 mg/kg
Di-n-hexyl phthalate (DNHP) CAS#:84-75-3	N.D.	50 mg/kg

Tested Item(s)	Result	MDL
Polyvinyl Chloride (PVC)	Negative	/

Tested Item(s)	Result	MDL
Phosphorus (P) #	N.D.	20 mg/kg

Test Report

Report No. A2210106001101

Page 9 of 14

Sample/Part Description Silvery/cupreous metal

Remark: The sample(s) had been dissolved totally tested for Lead, Cadmium, Mercury, Arsenic, Beryllium, Antimony, Phosphorus.

-MDL = Method Detection Limit

-N.D. = Not Detected (<MDL or LOQ)

-mg/kg = ppm = parts per million

-1000 mg/kg = 0.1%

-Negative = Not contained Polyvinyl Chloride (PVC)

-LOQ = Limit of Quantification, The LOQ of Hexavalent chromium is $0.10 \mu\text{g}/\text{cm}^2$

- ∇ The sample is negative for Cr(VI) – The Cr(VI) concentration is below $0.10 \mu\text{g}/\text{cm}^2$. The coating is considered a non-Cr(VI) based coating.

-*¹=concentration value of Tributyltin oxide by the conversion from the test results of Tributyl Tins.

Note: “*” indicates the method(s) is (are) not in CNAS accreditation scope.

“#” indicates the testing item(s) was (were) fulfilled by subcontracted lab , and not in CNAS accreditation scope.


Test Report

Report No. A2210106001101


Page 10 of 14

Test Process


1. Lead (Pb), Cadmium (Cd)




2. Mercury (Hg)



3. Hexavalent Chromium (Cr(VI))



4. Polybrominated Biphenyls (PBBs), Polybrominated Diphenyl Ethers (PBDEs)




Test Report


Report No. A2210106001101

Page 11 of 14


5. Phthalates




6. Arsenic(As), Beryllium(Be), Antimony(Sb)



7. Hexabromocyclododecane (HBCDD)



8. Fluorine (F), Chlorine (Cl), Bromine (Br), Iodine (I)




Test Report


Report No. A2210106001101

Page 12 of 14


9. Short Chain Chlorinated Paraffins (SCCPs)




10. Polychlorinated Naphthalenes (PCNs)



11. Polychlorinated terphenyls (PCTs)



12. Polychlorinated Biphenyls(PCBs)




Test Report


Report No. A2210106001101

Page 13 of 14


13. Perfluorooctane Sulfonates(PFOS), Perfluorooctanoic Acid(PFOA)




14. Organotin compounds



15. Polyvinyl Chloride (PVC)



16. Phosphorus (P)




Test Report

Report No. A2210106001101

Page 14 of 14

Photo(s) of the sample(s)



Statement:

1. This report is considered invalid without approved signature, special seal and the seal on the perforation;
2. The Company Name shown on Report and Address, the sample(s) and sample information was/were provided by the applicant who should be responsible for the authenticity which CTI hasn't verified;
3. The result(s) shown in this report refer(s) only to the sample(s) tested;
4. Without written approval of CTI, this report can't be reproduced except in full;
5. In case of any discrepancy between the English version and Chinese version of the testing reports (if generated), the Chinese version shall prevail.

*** End of Report ***