

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

InGaAsP MQW-DC-PBH HIGH POWER PULSED LASER DIODE
1 310 nm OTDR APPLICATION

DESCRIPTION

NDL7111 is a 1 310 nm pulsed laser diode especially designed for optical measurement equipment (OTDR). The newly developed Multiple Quantum Well (MQW) structure LD chip can achieve high output power in wide temperature range. This device is also available up to 20 μ s pulse width as customizing.

FEATURES

- High output power. $P_o = 120 \text{ mW} @ I_{FP} = 400 \text{ mA}^{*1}$
- Long wavelength. $\lambda_c = 1 310 \text{ nm}$
- Hermetically sealed.
- High reliability.

QUALITY GRADE


PART NUMBER	QUALITY GRADE
NDL7111	Standard

Please refer to "Quality grade on NEC Semiconductor Devices" (Document number IEI-1209) published by NEC Corporation to know the specification of quality grade on the devices and its recommended applications.

ABSOLUTE MAXIMUM RATINGS ($T_c = 25 \text{ }^\circ\text{C}$)

Optical output power	P_o	150	mW
Pulsed Forward Current ^{*1}	I_{FP}	600	mA
Reverse Voltage	V_R	2.0	V
Operating Case Temperature	T_c	-40 to +70	$^\circ\text{C}$
Storage Temperature	T_{stg}	-55 to +125	$^\circ\text{C}$
Lead Soldering Temperature (10 sec)	T_{slid}	260	$^\circ\text{C}$

^{*1} Pulse Conditions: Pulse Width(PW) = 1 μ s, Duty = 1 %





ELECTRO-OPTICAL CHARACTERISTICS (T_c = 25 °C)

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDECTIONS
Forward Voltage	V _{FP}		2.5	4.0	V	I _{FP} = 400 mA, PW = 1 μs, Duty = 1 %
Threshold Current	I _{th}		20	30	mA	
Optical Output Power	P _o	100	120		mW	I _{FP} = 400 mA, PW = 1 μs, Duty = 1 %
RMS Center Wavelength	λ _c	1290	1310	1330	nm	I _{FP} = 400 mA, PW = 1 μs, Duty = 1 %
RMS Spectral Width	σ			10	nm	I _{FP} = 400 mA, PW = 1 μs, Duty = 1 %
Rise Time	t _r		0.5	1.0	ns	10 – 90 %
Fall Time	t _f		0.7	1.0	ns	90 – 10 %
Lateral Beam Angle	θ _∥		30	40	deg	
Vertical Beam Angle	θ _⊥		35	45	deg	

ELECTRO-OPTICAL CHARACTERISTICS (T_c = 0 to + 60 °C)

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITIONS
Threshold Current	I _{th}		30	50	mA	
Optical Output Power	P _o	80	90		mW	I _{FP} = 400 mA, PW = 1 μs, Duty = 1 %
RMS Center Wavelength	λ _c	1265		1350	nm	I _{FP} = 400 mA, PW = 1 μs, Duty = 1 %
Temperature Dependency of Center Wavelength	Δλ/ΔT		0.35		nm / °C	
RMS Spectral Width	σ			15	nm	I _{FP} = 400 mA, PW = 1 μs, Duty = 1 %

TYPICAL CHARACTERISTICS



OTDR / MQW HIGH POWER PULSED LD FAMILY (T_c = 25 °C)

FEATURES PACKAGE	1.3 μm		1.55 μm		I _{FP} *1 (mA)	REMARKS
	PART NUMBER	P _o , P _f (mW)	PART NUMBER	P _o , P _f (mW)		
SMALL CAN	NDL7101	260	NDL7151	160	1000	
	NDL7111	120	NDL7161	65	400	
14-pin DIP MODULE with SMF	NDL7500P	120	NDL7550P	70	1000	with TEC , thermistor
	NDL7510P	55	NDL7560P	30	400	
4-pin COAXIAL MODULE with SMF	NDL7501P NDL7501P1	100	NDL7551P NDL7551P1	70	1000	P1 : with flange
	NDL7511P NDL7511P1	45	NDL7561P NDL7561P1	25	400	

*1 Pulse Conditions: PW = 1 μs , Duty = 1 %

These modules are also available with FC-PC connector, NDL75xxPC or NDL75xxP1C.

Discontinued Product




INVISIBLE LASER RADIATION
AVOID DIRECT EXPOSURE TO BEAM



OUT PUT POWER _____mw MAX.
WAVELENGTH _____nm
CLASS IIIb LASER PRODUCT

SEMICONDUCTOR LASER



AVOID EXPOSURE-Invisible
Laser Radition is emitted from
this aperture

NEC Corporation

NEC Building, 7-1, Shiba 5-chome
Minato-ku, Tokyo 108-01, Japan

Type number: _____
Manufactured: _____
Serial number: _____

This product conforms to DHHS
regulations as applicable
to standards 21 CFR Chapter I,
Subchapter J.

No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Corporation. NEC Corporation assumes no responsibility for any errors which may appear in this document.

NEC Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Corporation or others.

The devices listed in this document are not suitable for use in aerospace equipment, submarine cables, nuclear reactor control systems and life support systems. If customers intend to use NEC devices for above applications or they intend to use "Standard" quality grade NEC devices for applications not intended by NEC, please contact our sales people in advance.

Application examples recommended by NEC Corporation

Standard: Computer, Office equipment, Communication equipment, Test and Measurement equipment, Machine tools, Industrial robots, Audio and Visual equipment, Other consumer products, etc.

Special: Automotive and Transportation equipment, Traffic control systems, Antidisaster systems, Anticrime systems, etc.