
CCE4510 Evaluation Board

1. ABSTACT

The CCE4510 evaluation board is designed to evaluate and demonstrate the CCE4510 IO-Link Master IC with integrated frame handler.

Contents

| | |
|--|-----------|
| 1. ABSTACT | 1 |
| 2. INTRODUCTION | 2 |
| 3. SYSTEM REQUIREMENTS | 2 |
| 4. FEATURE OVERVIEW | 3 |
| 5. GETTING STARTED | 3 |
| 6. POWER SUPPLY | 3 |
| 7. SECTIONS OF THE CCE4510 EVALUATION BOARD | 4 |
| IO-Link Section | 4 |
| MCU Section..... | 4 |
| 8. SCHEMATIC AND LAYOUT | 5 |
| Connectors..... | 5 |
| Schematic | 6 |
| Layout | 8 |
| 9. BILL OF MATERIALS | 11 |
| 10. REVISION HISTORY | 12 |
| 11. REFERENCES | 12 |
| 12. STATUS DEFINITIONS | 12 |
| Corporate Headquarters | 12 |
| Contact information | 12 |
| Trademarks | 12 |

2. INTRODUCTION

The board is divided into two sections:

- **IO-Link Section**

The IO-Link section contains two CCE4510 including all necessary periphery to use the two CCE4510 for IO-Link communication.

- **MCU Section**

The MCU section contains a LPC1549 32-bit ARM Cortex-M3 microcontroller from NXP to control the CCE4510 Master ICs. The MCU is powered by an LDO with 3.3 V output voltage.

For maximum flexibility, the sections can be used separately and independently from each other. This allows to evaluate the CCE4510 Master IC with every suitable MCU.

The evaluation board is compliant to IO-Link Interface and System Specification V1.1.2




Figure 1: System Diagram

3. SYSTEM REQUIREMENTS

The CCE4510 evaluation board is ready to use with a preinstalled IO-Link master stack.

To get started, the following tools are required:

- Power Supply 24V
- USB Cable (Micro USB type B)
- Debug probe (for programming via SWD)

4. FEATURE OVERVIEW

- ARM Cortex-M3 Microcontroller
- On-Board 3.3 V LDO
- 16 kB EEPROM
- Programmable via USB or Serial Wire Debug (SWD)
- Status LED indicator
- External NMOS gate drivers
- 24 V supply voltage
- Two CCE4510 IO-Link Master Transceiver ICs
- 4 IO-Link channels
- 4 Status LED indicators for IO-Link channels
- Additional on-board protection circuitry
- All pins accessible via pin-headers
 - For microcontroller and IO-Link Master ICs
- Independent use of sections

5. GETTING STARTED

There are two different possibilities to program the CCE4510 evaluation board:

- Programming via USB
- Programming via SWD

To program via USB:

1. Connect pin MAS_INT (JP1 pin 5) to GND
2. Connect USB to PC
3. Power on the Evaluation Board (24V)
4. The microcontroller will now be recognized as USB mass storage
5. Copy any program on the microcontroller

To program via SWD

1. Connect debug probe to SWD connector
2. Connect USB to PC (USB 5V supply is needed) OR Connect USB_VBUS (JP1 pin 3) to +3.3V
3. Power on the Evaluation Board (24V)
4. Start programming with your preferred SDK

6. POWER SUPPLY

The CCE4510 Evaluation Board needs a 24 V power supply connected to JP2 pins 23 / 24. An on-board 3.3 V LDO (placed on the MCU section) supplies the microcontroller as well as the CCE4510 ICs.

When using the IO-Link section independently from the MCU section it must be ensured that both voltages (3.3 V and 24 V) are present at the IO-Link section.

7. SECTIONS OF THE CCE4510 EVALUATION BOARD

The CCE4510 Evaluation Board is divided into two sections.

Both sections can be used in combination with an IO-Link Master software stack to evaluate a fully functional, ready-to-use IO-Link Master.

If required, both sections can also be used independently of each other. The connection between the sections can be disconnected by cutting them open between the cutting marks (see Figure 2). Make sure not to break the evaluation board in this process.

To reestablish the connections, pin-headers with 2.54 mm pitch can be used.




Figure 2: Cutting Marks

IO-Link Section

The IO-Link section contains two CCE4510 IO-Link master ICs, external NMOS gate drivers (U4, U6), four LED indicators for channel activities and protection circuitry. Each IO-Link channel (L+, CQ, L-) can be accessed via a terminal block (X2, X3, X4, X5). For maximum accessibility to the CCE4510 IO-Link Master ICs, all relevant pins of the CCE4510 ICs are connected to pin-headers JP3 and JP4.

MCU Section

The MCU section contains an ARM Cortex-M3 processor from NXP (LPC1549), a 3.3 V LDO (U2) for power supply, a 16 kB EEPROM (U7) and a status LED (LED5). The microcontroller can be programmed via USB (mass storage device) or via SWD. For maximum accessibility of the LPC1549, all relevant pins are connected to pin-headers JP1 and JP2.

8. SCHEMATIC AND LAYOUT

Connectors

Figure 3 shows all connectors of the CCE4510 Evaluation Board. It is possible to access all pins of the MCU and the CCE4510 master ICs through these connectors.




Figure 3: Connectors

Schematic




Figure 4: Schematic 1




Figure 5: Schematic 2

CREATIVECHIPS®
MICROELECTRONICS

CCE4510_Evaboard_V2
03.01.2020 2:50

Sheet: 2/2

Layout




Figure 6: Layout TOP




Figure 7: Layout MID1 (Supply)




Figure 8: Layout MID2 (GND)




Figure 9: Layout BOTTOM




Figure 10: Layout Assembly

9. BILL OF MATERIALS

| Part | Value / Description | Manufacturer | Manufacturer Part Number |
|--|-------------------------------|-----------------------------------|---------------------------|
| C1,C2,C20,C21 | 18 pF 50V C0G 5 % 0603 | Any | Any |
| C3,C4,C9,C10 | 10 nF 50V X7R 10 % 0603 | Any | Any |
| C5,C6,C11,C12, C15,C17,C18,C19, C22,C23 | 100 nF 50V X7R 10 % 0603 | Any | Any |
| C7,C8,C13,C14 | 4.7 nF 50V X7R 10 % 0805 | Any | Any |
| C16 | 1 μ F 50V X5R 10 % 0603 | Any | Any |
| D1 | Shottky-Diode 40V 2A | NXP | PMEG4020ER,115 |
| D2, D3, D4, D5, D6, D7, D8, D9, D10, D11, D12, D13 | TVS-Diode 33V | NXP | PTVS33VS1UR,115 |
| JP1,JP2 | Pin Header 24-Pin 2.54 mm | Any | Any |
| JP3,JP4 | Pin Header 16-Pin 2.54 mm | Any | Any |
| LED1, LED2,LED3, LED4 | LED Orange | OSRAM Opto Semiconductors Inc. | LO L29K-H2L1-24-Z |
| LED5 | LED Green | OSRAM Opto Semiconductors Inc. | LG L29K-F2J1-24-Z |
| R1,R2,R3,R4 | 0.5R 100V 100 mW 1 % 0603 | Any | Any |
| R5,R6 | 2 k 75 V 100 mW 1 % 0603 | Any | Any |
| R7,R8,R9 | 1 k 75 V 100 mW 1 % 0603 | Any | Any |
| R10 | 12 k 75 V 100 mW 1 % 0603 | Any | Any |
| U1 | Microcontroller LPC1549 | NXP | LPC1549JBD48QL |
| U2 | LDO TDA3663 3.3 V SOT223-1 | NXP | TDA3663/N1,135 |
| U3,U5 | IO-Link Master Transceiver | Dialog Semiconductor | CCE4510_QFN48 |
| U4,U6 | Dual-MOSFET n-channel 60 V | NXP | PMGD780SN |
| U7 | EEPROM 16 kB I ² C | ON Semiconductor | CAT24C128HU4IGT3 |
| USB | Micro USB-B Connector | WURTH Elektronik | 629105150521 |
| X1 | SMT Micro Header | SAMTEC | FTSH-105-01-F-DV-K |
| X2,X3,X4,X5 | Wire-to-Board Connector | METZ CONNECT | 31059103 |
| Y1 | Crystal 14.7456 MHz | ABRACON | ABM8G-14.7456MHZ-18-D2Y-T |
| Y2 | Crystal 12 MHz | ABRACON | ABM8G-12.000MHZ-18-D2Y-T |

10. REVISION HISTORY

| Revision | Date | Description |
|----------|-------------|------------------|
| 1 | 03-Mar-2020 | Initial version. |
| 2 | 28-Jan-2022 | Rebrand |

11. REFERENCES

- [1] CCE4510, Datasheet, Dialog Semiconductor.
- [2] LPC1549JBD48QL, Datasheet, NXP.
- [3] IO-Link Interface and System Specification V1.1.2, IO-Link Community.

12. STATUS DEFINITIONS

| Status | Definition |
|-------------------------|--|
| DRAFT | The content of this document is under review and subject to formal approval, which may result in modifications or additions. |
| APPROVED or unmarked | The content of this document has been approved for publication. |

Rev.5.0-1 October 2020

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:
www.renesas.com/contact/

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES (“RENESAS”) PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES “AS IS” AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01 Jan 2024)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.