


## 32-bit MCU Family

# RENESAS RA8M1 GROUP

### 480 MHz Arm® Cortex®-M85 Based High-Performance Microcontroller with Helium™ and TrustZone®

The new Renesas RA8M1 group features the industry's first 32-bit MCUs based on the new Arm® Cortex®-M85 core and delivers breakthrough performance of over 3000 Coremark points at 480 MHz to meet the most demanding application needs. RA8M1 MCUs integrate the high performance Cortex-M85 core with large memory, multiple external interfaces and a rich peripheral set optimized to address diverse application requirements and are available in packages from 100 to 224 pins, to enable a broad range of high-performance applications. Secure Element-like functionality is built in with advanced cryptographic Security IP, immutable storage and tamper protection for truly secure IoT.




### Key Features

- 480MHz Arm Cortex-M85 with Helium™ MVE
- 1MB - 2MB Flash and 1MB SRAM including TCM
- 32KB I/D Caches and 12KB Data Flash
- Renesas Security IP and Armv8-M TrustZone
- Immutable storage for First Stage Bootloader
- xSPI compliant Octal SPI with XIP & DOTF
- 32/16-bit timers, 32-bit ultra-low-power timer
- 12-bit ADC, 12-bit DAC, HS comparator
- Ethernet, USB2.0 HS/FS, CAN-FD, SCI, SPI/I2C/I3C
- Camera Interface, external memory interfaces (CS/SDRAM)

### Target Applications

- Industrial applications
- Consumer products
- Smart Home and Building Automation
- Office Automation
- Medical and Healthcare
- Predictive Maintenance and Voice AI applications

### Block Diagram




# RENESAS RA8M1 GROUP

## Software Package

The Renesas Flexible Software Package (FSP) is designed to provide easy-to-use, scalable, high-quality software for embedded system designs using RA MCUs.

The FSP is based on an open software ecosystem of production-ready drivers, supporting Azure® RTOS, FreeRTOS™ or bare-metal programming. It also includes a selection of other middleware stacks, providing great flexibility for migrating code from older systems or developing new applications from scratch.



## Tools and Support

The e<sup>2</sup> studio IDE provides support with intuitive configurators and intelligent code generation to make programming and debugging easier and faster.

IDE	Renesas e <sup>2</sup> studio	Keil MDK	IAR EWARM
Compiler	<ul style="list-style-type: none"> <li>• GCC</li> <li>• LLVM</li> <li>• Arm Compiler*</li> <li>• IAR Arm Compiler*</li> </ul>	<ul style="list-style-type: none"> <li>• Arm Compiler*</li> </ul>	<ul style="list-style-type: none"> <li>• IAR Arm Compiler*</li> </ul>
Debug Probe	<ul style="list-style-type: none"> <li>• Renesas E2/E2 Lite</li> <li>• SEGGER J-Link</li> </ul>	<ul style="list-style-type: none"> <li>• SEGGER J-Link</li> <li>• Keil ULINK / CMSIS-DAP (limited support)</li> </ul>	<ul style="list-style-type: none"> <li>• IAR I-jet</li> <li>• SEGGER J-Link</li> <li>• Renesas E2/E2 Lite</li> <li>• CMSIS-DAP (limited support)</li> </ul>
Production Programmer	<ul style="list-style-type: none"> <li>• Renesas PG-FP6</li> <li>• SEGGER J-Flash</li> <li>• Partner solutions</li> </ul>		

\* Compiler must be purchased and licensed directly from third party

## Evaluation Kit

- Easily evaluate key features of the RA8M1 MCU and develop sophisticated IoT and embedded systems applications
- On-board debugging using SEGGER-J-Link®
- Order the kit and download documentation, design package, development tools and software at: [renesas.com/ek-ra8m1](https://renesas.com/ek-ra8m1)
- Orderable part number: **RTK7EKA8M1S00001BE**



## Ordering References

Flash/RAM	Tj				
2MB/1MB	-40 to 125 °C	<b>R7FA8M1AHECFP</b>	<b>R7FA8M1AHECFB</b>	<b>R7FA8M1AHECFC</b>	<b>R7FA8M1AHECBD</b>
1MB/1MB	-40 to 125 °C	<b>R7FA8M1AFECFP</b>	<b>R7FA8M1AFECFB</b>	<b>R7FA8M1AFECFC</b>	<b>R7FA8M1AFECBD</b>
Pin Count		100-pin	144-pin	176-pin	224-pin
Package		LQFP	LQFP	LQFP	BGA
Package size (body)		14 x 14 mm	20 x 20 mm	24 x 24 mm	13 x 13 mm
Pitch		0.5 mm	0.5 mm	0.5 mm	0.8 mm

For more details, please visit: [renesas.com/ra8m1](https://renesas.com/ra8m1)



**renesas.com**

Corporate Headquarters  
TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan  
[www.renesas.com](http://www.renesas.com)

Trademarks  
Arm® and Cortex® are registered trademarks of Arm Limited. Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact information  
For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit:  
[www.renesas.com/contact/](http://www.renesas.com/contact/)