

RX72T handbook for engineers

The information/materials required at the time of product development summarized and listed for each development phase.

Please use it as a handbook when developing.

Table of contents:

[Step1: MCU selection](#)

[Step2: Designing and evaluating](#)

[Step3: Mass production](#)

Step1: MCU selection

Item		Content	Link
1	Hardware information	Datasheet	Doc
2	Products & Solutions	Video	Web site
3		Blog	Web site
4		Reference designs (Winning combination)	Web site
5	Product longevity program (PLP)	Overview of product longevity program (PLP)	Web site
6		Product selection (product selector) Note: Refer to PLP column in the chart.	Web site
7	Replacement information	Differences of specification among RX products	Doc
8		[SH/H8/H8S/H8SX/M16C/V850] → RX microcontroller migration guide	Web site
9		Design guide for migration between RX family differences in package external form	Doc

[Go to Top](#)

Step2: Designing and evaluating

Item			Content	Link
Common				
1	Hardware information		User's manual: Hardware	Doc
2			RX family hardware manual guidance (how to read user's manual: hardware)	Doc
3			Technical update (errata information)	Web site
4			Product change notice (PCN)	Web site
5			Part number guide for RX family product (the meaning of character in part number)	Doc
6			Semiconductor reliability handbook	Doc
7			RELIABILITY REPORT	Doc
8				
9	Software information		Instruction set for RXv3 core architecture (user's manual)	Doc
10	Evaluation board (for general purpose)		Renesas starter kit for RX72T (all functions could be evaluated)	Web site
11	Evaluation board (for general purpose)	Communication board	MC-COM renesas flexible motor control communication board	Web site
12	Solution board	Inverter board	Evaluation system for BLDC motor	Web site
13		CPU card	CPU card for motor control	Web site
14			User's manual	Doc
15	Partner information		Partner products (system solutions provider)	Web site
16			Partner products (trusted technology partners that deliver commercial-grade building blocks)	Web site
Hardware design				
1	Design information		Hardware design guide	Web site
2			Design guide for main clock circuit and Sub-Clock circuit	Doc
3			Notes regarding high-temperature operation	Doc
4			Guidelines for full-speed USB2.0 board design	Doc
5	Board simulates		ECAD, board simulation model (IBIS) Note: ECAD can be found by clicking on the respective part number of the product options.▶	Web site
6	Other		Resonator and matching circuit information	Web site
7			Package information (package outline information, mount manual, etc.)	Web site

	Item		Content	Link
Hardware design				
8	Development environment		Supplemental user's manual for E1/E20/E2 Lite/E2 emulator	Doc
Software design				
1	Software information		Getting started with the RX family development environment	Web site
2			Development tools for RX family	Web site
3			Software environment (OS, middleware, drivers)	Web site
4			RX smart configurator user's guide (tools for code generation)	Doc
5	Training information		Smart configurator tutorial - create a LED blinking program using RX family MCU	Web site
6			How to use tools and solutions (video clips)	Web site
7			CC-RX compiler tutorial - How to use trigonometric function unit (TFU) of RX	Web site
Solution				
1	Motor and Inverter	Portal page	Motor and inverter control solutions	Web site
2	Control	Application notes	Vector control for permanent magnet synchronous motor with encoder (algorithm)	Doc
3			Sensorless vector control for permanent magnet synchronous motor (algorithm)	Doc
4			Vector control for permanent magnet synchronous motor with encoder for evaluation system for BLDC motor	Doc Sample
5			Sensorless vector control of a permanent magnet synchronous motor for the evaluation system for BLDC motor	Doc Sample
6			Vector control for permanent magnet synchronous motor with encoder (implementation) (control over three motors) for evaluation system for BLDC motor	Doc Sample
7			Sensorless vector control for permanent magnet synchronous motor (implementation) (control over four motors) for evaluation system for BLDC motor	Doc Sample

Item		Content		Link
Solution				
8	Motor and Inverter Control	Application notes	Vector control for permanent magnet synchronous motor with magnet sensor and inductive sensor (for evaluation system for BLDC motor, structure update version)	Doc Sample
9			Digital power conversion (totem pole interleaved PFC)	Doc Sample
10			Digital power conversion (uninterruptible power system (UPS))	Doc Sample
11		Tool	Renesas motor workbench	Web site
12		Other information	Position control of 3 motors with a single MCU (video)	Web site
13			Speed control of 4 motors with a single MCU (video)	Web site
14	Security	Portal page	RX security solutions	Web site
15		Manual	Security key management tool manual	Web site
16		Application notes	How to manage the access control for flash memory	Doc
17			TSIP (Trusted Secure IP) driver (binary version)	Doc Sample
18			How to use AES cryptography with Trusted Secure IP(TSIP)	Doc
19			Renesas MCU firmware update design policy	Doc
20		Other information	Video	Web site
21	GUI	Portal page	Graphical user interface (GUI) solutions	Web site
22		Support information	RX family LCD-related FAQ list	Web site
23		Application notes	QE for display GUI display application development guide using serial connection LCD	Doc
24			GUI sample program using serial LCD and emWin library	Doc Sample
25			Module for image rendering (emWin)	Doc Sample
26	Functional safety	Portal page	IEC61508 functional safety solutions for industry	Web site
27		Other information	Functional safety solution for industrial automation	Doc
28			Introduction to renesas functional safety (video)	Web site

Item		Content	Link
Support			
1	Support information	FAQ (frequently asked inquiries)	Web site
2		RX forum (community)	Web site
3		Ask to technical support Note: Please click login in the upper right corner	Web site

[Go to Top](#)

Step3: Mass production

Item		Content	Link
1	Writing a program	Programmer	PG-FP6
2		Writing tool	Renesas flash programmer (GUI tool for PC)
3	inspection	Design information	Boundary scan description language (BSDL) file
			Not available

[Go to Top](#)