

TEST REPORT

Report No: AR-21-SV-023611-01
Customer: UNISEM (M) BERHAD
Date of Issue: 11/06/2021



Batch No: EUMYBM-00084765
Sample No: 138-2021-06000572

To: UNISEM (M) BERHAD
 1, Persiaran Pulau Jaya 9,
 Kawasan Perindustrian Pulau Jaya,
 31300 Kampung Kepayang
 Perak MALAYSIA

Attn: Ms Miza

Date Sample Received: 04/06/2021
Date of Testing: 09/06/2021 to 11/06/2021

The following sample was identified by the customer as :
 LEADFRAME C7025

Objective (s):

- 1.Determination of Cadmium (Cd), Hexavalent Chromium (Cr6+), Lead (Pb), Mercury (Hg), Phthalates, Polybrominated Biphenyl (PBBs), Polybrominated Diphenyl Ether (PBDEs) with RoHS Directive 2011/65/EU and (EU) 2015/863 (amendment in Annex II)
- 2.Determination of Phthalate (USEPA 3540C; GC-MS) for above sample.
- 3.Determination of Hexabromocyclododecane (HBCDD), Bromine (Br), Chlorine (Cl), Antimony (Sb), Beryllium (Be), Screening of PFOA (as F) and Screening of PFOS (as F) for above sample.

Conclusion :

Test(s) Required	Compliance with Objective(s)
Cadmium (Cd), Lead (Pb), Mercury (Hg), Hexavalent Chromium (Cr6+), Monobromobiphenyl, Dibromobiphenyls, Tribromo biphenyls, Tetrabromo biphenyls, Pentabromo biphenyls, Hexabromo biphenyls, Heptabromobiphenyl, Octabromo biphenyls, Nonabromo biphenyls, Decabromo biphenyls, Sum Polybrominated Biphenyls (PBB), Monobromodiphenyl ether, Dibromodiphenylether, Tribromo diphenylethers, Tetrabromo diphenyl ethers, Pentabromodiphenyl ether, Hexabromo diphenyl ethers, Heptabromodiphenyl ethers, Octabromo diphenyl ethers, Nonabromo diphenyl ethers, Decabromo diphenyl ethers, Sum Polybrominated Diphenyl Ether (PBDE), Benzyl butyl phthalate (BBP), Bis(2-ethylhexyl)phthalate (DEHP), Dibutyl phthalate (DBP), Di-isobutyl phthalate (DiBP),	Comply
Hexabromocyclododecane (HBCDD), Di-n-octylphthalate (DNOP), Diisodecyl phthalate (DIDP), Diisononyl phthalate (DINP), Bromine (Br), Chlorine (Cl), Antimony (Sb), Beryllium (Be)	-
Screening of PFOS (as F), Screening of PFOA (as F)	Flourine is not detected thus PFOA & PFOS is absent

Test Result(s):

Analysis	Industrial Products Analysis	Unit	Result	LOQ	Test Method	Specification
SVK51	Cadmium (Cd)	mg/kg	ND(<LOQ)	1	IEC 62321-5	≤100mg/kg
SVL03	Lead (Pb)	mg/kg	ND(<LOQ)	10	IEC 62321-5	≤1000mg/kg
SVK82	Mercury (Hg)	mg/kg	ND(<LOQ)	5	IEC 62321-4	≤1000mg/kg
SVK66	Hexavalent Chromium (Cr6+)	-	negative	-	IEC 62321-7-1	≤1000mg/kg (Refer Note 2)
SVK16	Polybrominated Biphenyl (PBBs)				IEC 62321-6	
	Monobromobiphenyl	mg/kg	ND(<LOQ)	20		Refer Note 3
	Dibromo biphenyls	mg/kg	ND(<LOQ)	20		Refer Note 3
	Tribromo biphenyls	mg/kg	ND(<LOQ)	20		Refer Note 3
	Tetrabromo biphenyls	mg/kg	ND(<LOQ)	20		Refer Note 3
	Pentabromo biphenyls	mg/kg	ND(<LOQ)	20		Refer Note 3
	Hexabromo biphenyls	mg/kg	ND(<LOQ)	20		Refer Note 3
	Heptabromobiphenyl	mg/kg	ND(<LOQ)	20		Refer Note 3

TEST REPORT

Page No: 2/4

Report No: AR-21-SV-023611-01
Customer: UNISEM (M) BERHAD
Date of Issue: 11/06/2021



Batch No: EUMYBM-00084765
Sample No: 138-2021-06000572

Analysis	Industrial Products Analysis	Unit	Result	LOQ	Test Method	Specification
	Octabromo biphenyls	mg/kg	ND(<LOQ)	20		Refer Note 3
	Nonabromo biphenyls	mg/kg	ND(<LOQ)	20		Refer Note 3
	Decabromo biphenyls	mg/kg	ND(<LOQ)	20		Refer Note 3
	Sum Polybrominated Biphenyls (PBB)	mg/kg	ND(<LOQ)	20		≤1000mg/kg
SVK17	Polybrominated Diphenyl Ether (PBDEs)				IEC 62321-6	
	Monobromodiphenyl ether	mg/kg	ND(<LOQ)	20		Refer Note 3
	Dibromodiphenylether	mg/kg	ND(<LOQ)	20		Refer Note 3
	Tribromo diphenyl ethers	mg/kg	ND(<LOQ)	20		Refer Note 3
	Tetrabromo diphenyl ethers	mg/kg	ND(<LOQ)	20		Refer Note 3
	Pentabromodiphenyl ether	mg/kg	ND(<LOQ)	20		Refer Note 3
	Hexabromo diphenyl ethers	mg/kg	ND(<LOQ)	20		Refer Note 3
	Heptabromo diphenyl ethers	mg/kg	ND(<LOQ)	20		Refer Note 3
	Octabromo diphenyl ethers	mg/kg	ND(<LOQ)	20		Refer Note 3
	Nonabromo diphenyl ethers	mg/kg	ND(<LOQ)	20		Refer Note 3
	Decabromo diphenyl ethers	mg/kg	ND(<LOQ)	20		Refer Note 3
	Sum Polybrominated Diphenyl Ether (PBDE)	mg/kg	ND(<LOQ)	20		≤1000mg/kg
SVV1Q	Phthalates				IEC 62321-8	
	Benzyl butyl phthalate (BBP)	% (w/w)	ND(<LOQ)	0.02		≤0.1%
	Bis(2-ethylhexyl)phthalate (DEHP)	% (w/w)	ND(<LOQ)	0.02		≤0.1%
	Dibutyl phthalate (DBP)	% (w/w)	ND(<LOQ)	0.02		≤0.1%
	Di-isobutyl phthalate (DiBP)	% (w/w)	ND(<LOQ)	0.02		≤0.1%
SVM48	◆ Hexabromocyclododecane (HBCDD)	mg/kg	ND(<LOQ)	5	In-house Method, GC-MS	-
SV01M	Di-n-octylphthalate (DNOP)	% (w/w)	ND(<LOQ)	0.01	In-House Method based on USEPA 3540C, GC-MS	-
SV01N	Diisodecyl phthalate (DIDP)	% (w/w)	ND(<LOQ)	0.02	In-House Method based on USEPA 3540C, GC-MS	-
SV01R	Diisononyl phthalate (DINP)	% (w/w)	ND(<LOQ)	0.02	In-House Method based on USEPA 3540C, GC-MS	-
SVL43	Bromine (Br)	mg/kg	ND(<LOQ)	50	BS EN 14582 (Calorimetric Bomb/Ion Chromatography)	-
SVL44	Chlorine (Cl)	mg/kg	ND(<LOQ)	50	BS EN 14582 (Calorimetric Bomb/Ion Chromatography)	-
SVL57	Screening of PFOS (as F)	mg/kg	ND(<LOQ)	50	BS EN 14582 (Calorimetric Bomb/Ion Chromatography)	-
SVL56	Screening of PFOA (as F)	mg/kg	ND(<LOQ)	50	BS EN 14582 (Calorimetric Bomb/Ion Chromatography)	-
SVK18	Antimony (Sb)	mg/kg	ND(<LOQ)	10	US EPA 6010C	-
SVK41	Beryllium (Be)	mg/kg	ND(<LOQ)	5	US EPA 6010C	-

TEST REPORT

Report No: AR-21-SV-023611-01
Customer: UNISEM (M) BERHAD
Date of Issue: 11/06/2021



Batch No: EUMYBM-00084765
Sample No: 138-2021-06000572

Analysis	Industrial Products Analysis	Unit	Result	LOQ	Test Method	Specification
SVK03	Microwave Assisted Acid Digestion	-	Done	-	US EPA 3052	-

Specification Note

1. RoHS Directive 2011/65/EU and (EU) 2015/863 (amendment in Annex II)
2. Expression result for Hexavalent Chromium
 - i. Concentration of Hexavalent chromium ($<0.10\mu\text{g}/\text{cm}^2$) = Negative (sample coating is consider non Cr(VI) based coating)
 - ii. Concentration of Hexavalent chromium (≥ 0.10 and $\leq 0.13\mu\text{g}/\text{cm}^2$) = Inconclusive (Unavoidable coating variations may influence the determination)
 - iii. Concentration of Hexavalent chromium ($\geq 0.13\mu\text{g}/\text{cm}^2$) = Positive (Sample coating is consider to contain Cr(VI))
3. Based on sum amount of PBB/PBDE limit, which is $\leq 1000\text{mg}/\text{kg}$

Remark

1. The test portion was totally dissolved for cadmium, lead & mercury test by using pre-conditioning method as mentioned above.
2. IEC 62321 flowchart can be obtained from <https://admin.apac-websites.eurofins.com/media/606192/efctm001-issue-2.pdf>
3. USEPA 3540C/GC-MS Flowchart can be obtained <https://cdnmedia.eurofins.com/apac/media/601323/efctm005issue01.pdf>
4. BS EN 14582:2007 flowchart can be obtained from <https://cdnmedia.eurofins.com/apac/media/601321/efctm003issue01.pdf>

This 4 page(s) of report and its attachment(s), if relevant, has/have been validated by



Chow Khim Tan, M.Sc. in Chemistry
IKM Registered Chemist
Registered No.:M/3944/6697/13

TEST REPORT

Page No: 4/4

Report No: AR-21-SV-023611-01
Customer: UNISEM (M) BERHAD
Date of Issue: 11/06/2021




Batch No: EUMYBM-00084765
Sample No: 138-2021-06000572

EXPLANATORY NOTE

This analytical report shall not be reproduced except in full, without approval of Eurofins NM Laboratory Sdn Bhd.
The result(s) relate(s) only to the item(s) tested.
Eurofins general terms and conditions of sales (Malaysia) apply.

- ◆ Test result is not SAMM accredited.
 - Test result is externally provided within Eurofins group and is accredited.
 - Test result is externally provided within Eurofins group but is not accredited.
 - Test result is externally provided outside Eurofins group and is accredited.
 - Test result is externally provided outside Eurofins group but is not accredited.
- N/A** means not applicable.
ND means not detected for value obtained is less than the Limit of Detection (LOD).
<LOD means not detected at or below the Limit of Detection (LOD).
<LOQ means below the Limit of Quantification (LOQ)

Sample Photograph(S)



- End of Report -