

Product Change Notice (PCN)

Subject: Alternate assembly facility of the listed Renesas PDIP packaged products

Publication Date: 11/21/2018

Effective Date: 2/19/2019

Revision Description:

Initial Release

Description of Change:

Alternate assembly facility of the listed Renesas PDIP packaged products

- *Greatek Electronics Inc., Taiwan R.O.C*

Affected Product List : -

CA3140AEZ	ICL7667CPAZ
CA3240AEZ	ISL81487LIPZ
CMP82C55AZ	X28HC64PZ-12

Reason for Change:

This notice is to inform you that Renesas Electronics America Inc will begin using Greatek Electronics Inc., Taiwan facility as alternate assembly facility of the listed Renesas PDIP packaged products. This action will expand current capabilities and capacities to optimize Renesas’s ability to meet customer’s delivery requirements.

Impact on fit, form, function, quality & reliability:

The Greatek Taiwan facility is ISO9001:2015 and IATF16949:2016 certified. There is no change in the manufacturing process flow, Form, Fit, Function, or interchangeability of the product.

Product Identification:

Product affected by this change is identifiable via Renesas’s internal traceability system. In addition, product assembled at Greatek may also be identified by the assembly site code (country of assembly) when marked on the devices. The site code for product assembled at Greatek is “Z”.

Qualification status: Completed, see attached

Sample availability: 12/3/2018



Device material declaration: Available upon request

Questions or requests pertaining to this change notice, including additional data or samples, must be sent to Renesas within 30 days of the publication date.



For additional information regarding this notice, please contact your regional change coordinator (below)			
Americas: PCN-US@RENESAS.COM	Europe: PCN-EU@RENESAS.COM	Japan: PCN-JP@RENESAS.COM	Asia Pac: PCN-APAC@RENESAS.COM

Appendix A - Qualification Results (see attached)

Test Description	Condition	CA3140EZ 8 Leads PDIP, 9.65mm x 6.60mm(300mil) package	ISL81487EIPZ 8 Leads PDIP, 9.65mm x 6.60mm (300mil) Package	EL7242CNZ 8 Leads PDIP, 9.65mm x 6.60mm (300mil) Package
Biased HAST +130 °C / 85% RH	96 hrs	N = 80 Acc = 0	N = 80 Acc = 0	N = 80 Acc = 0
Unbiased HAST (u-HAST) +130 °C / 85% RH	96 hrs	N = 85 Acc = 0	N = 85 Acc = 0	N = 85 Acc = 0
Hot Temperature Storage (HTS) +150 °C	500 hrs	N = 79 Acc = 0	N = 85 Acc = 0	N = 85 Acc = 0
Hot Temperature Storage (HTS) +150 °C	1000 hrs	N = 79 Acc = 0	N = 85 Acc = 0	N = 85 Acc = 0
Temperature Cycle (TCT) -65 °C / +150 °C	500 cyc	N = 80 Acc = 0	N = 85 Acc = 0	N = 85 Acc = 0

 Qualified by Extension
 Completed and Passed

Test Description	Condition	HIP4081AIPZ 20 Leads PDIP, 26.16mm x 6.60mm (300mil) Package	ICL7107CPLZ 40 Leads PDIP, 52.07mm x 13.97mm (600mil) Package	CP82C55AZ 40 Leads PDIP, 52.07mm x 13.97mm (600mil) Package
Biased HAST +130 °C / 85% RH	96 hrs	N = 80 Acc = 0	N = 80 Acc = 0	N = 80 Acc = 0
Unbiased HAST (u-HAST) +130 °C / 85% RH	96 hrs	N = 85 Acc = 0	N = 85 Acc = 0	N = 85 Acc = 0
Hot Temperature Storage (HTS) +150 °C	500 hrs	N = 85 Acc = 0	N = 85 Acc = 0	N = 85 Acc = 0
Hot Temperature Storage (HTS) +150 °C	1000 hrs	N = 85 Acc = 0	N = 85 Acc = 0	N = 85 Acc = 0
Temperature Cycle (TCT) -65 °C / +150 °C	500 cyc	N = 85 Acc = 0	N = 85 Acc = 0	N = 85 Acc = 0

 Qualified by Extension
 Completed and Passed