

# I<sub>cc</sub> vs V<sub>cc</sub> (High-speed on-chip oscillator mode)

Prepared on Oct. 20, 2006

R5F21248SNFP(Topr=-20 to 85degrees C)

R5F21248SDFP(Topr=-40 to 85degrees C)

divide-by-8

XIN clock off


High-speed on-chip oscillator on f<sub>OCO</sub> = 10 MHz

Low-speed on-chip oscillator on = 125 kHz

— 85degreesC

— 25degreesC

— -40degreesC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.