


# Icc vs Topr

## (Low-Speed On-Chip Oscillator mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)  
R5F21258SDFP(Topr=-40 to 85degrees C)  
divide-by-8  
XIN clock off  
High-speed on-chip oscillator off  
Low-speed on-chip oscillator on = 125 kHz  
FMR47 = 1

— Vcc=5V — Vcc=3V — Vcc=2.2V



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.