

I_{CC} vs V_{CC}

(High-speed on-chip oscillator mode)

Prepared on Oct. 20, 2006

R5F21258SNFP(Topr=-20 to 85degrees C)

R5F21258SDFP(Topr=-40 to 85degrees C)

divide-by-8

XIN clock off


High-speed on-chip oscillator on fOCO = 10 MHz

Low-speed on-chip oscillator on = 125 kHz

— 85degreesC

— 25degreesC

— -40degreesC



The mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics.