

Product Change Notice (PCN)

Subject: Notice of Change in 14 x 14 mm LQFP Tape & Reel Packaging Components for RX100/200/600 Products

Publication Date: 7/22/2022

Effective Date: 11/1/2022

Revision Description: Initial Release

Description of Change:

Affected Products: RX100/200/600 Package dimensions 14 x 14 mm LQFP

Target location (assembly and testing base): Renesas Semiconductor (Beijing) Co., Ltd (hereafter referred to as RSB) The embossed tape width was changed for the shipment of tape & reel, manufactured at RSB.

Before change: 32 mm

After change: 24 mm

The pocket width, pocket depth, feed hole, dimension between feed hole and pocket center, reel width, and cover tape width change due to the change in tape width.

Affected Product List:

RX100/200/600 14 x 14 mm LQFP packaged products. For detailed type names, see Page 2 and the following pages

| Product Group | Package | Embossed Tape Width |
|---------------|------------------------------------|-----------------------------|
| RX110 | 14 × 14 mm 64 pin | Changed from 32 mm to 24 mm |
| RX111 | 14 × 14 mm 64 pin | |
| RX113 | 14 × 14 mm 100 pin | |
| RX130 | 14 × 14 mm 64 pin, 100 pin | |
| RX140 | 14 × 14 mm 64 pin | |
| RX210 | 14 × 14 mm 100 pin | |
| RX231 | 14 × 14 mm 100 pin | |
| RX24T/RX24U | 14 × 14 mm 64 pin, 80 pin, 100 pin | |
| RX63T | 14 × 14 mm 100 pin | |

Reason for Change:

The embossed tape width will be changed to 24 mm to maintain a stable supply.

Impact on Fit, Form, Function, Quality & Reliability:

Form and fit of the device: No change

Function, quality, and reliability: No influence

Outline of the embossed tape: Changed

Product Identification:

The 24-mm width will be applied to products with the date "2022/11/01" or later on the upper left of the barcode on the packing label. The 24-mm width can be identified by this date.

Qualification Status: Not applicable

Sample Availability Date: Not applicable

Device Material Declaration: Please contact our sales representatives or distributors.

Note:

1. Acknowledgement must be received by Renesas within 30 days or Renesas will consider the change as approved.
2. If timely acknowledgement is provided by Customer, then Customer shall have 90 days from the date of receipt of this PCN to make any objections to this PCN. If Customer fails to make objections to this PCN within 90 days of the receipt of the PCN then Renesas will consider the PCN changes as approved.
3. If customer cannot accept the PCN then customer must provide Renesas with a last time buy demand and purchase order.

For additional information regarding this notice, please contact your Renesas sales representative.

List of Type Names:

| | | | |
|--------------------|-----------------|--------------------|--------------------|
| R5F51101ADFK#50 | R5F51137ADFP#5A | R5F52305ADFP#50 | R5F524TBADFP#51 |
| R5F51101AGFK#50 | R5F51137AGFP#5A | R5F52305AGFP#50 | R5F524TBAD***FP#5C |
| R5F51103ADFK#50 | R5F51138ADFP#5A | R5F52306ADFP#50 | R5F524TBAGFP#51 |
| R5F51103AGFK#50 | R5F51138AGFP#5A | R5F52306AGFP#50 | R5F524TBAG***FP#5C |
| R5F51104ADFK#50 | R5F51303ADFK#50 | R5F52315ADFP#50 | R5F524TCADFP#51 |
| R5F51104AGFK#50 | R5F51303AGFK#50 | R5F52315AGFP#50 | R5F524TCAD***FP#5C |
| R5F51105ADFK#50 | R5F51305ADFK#50 | R5F52315CDFP#50 | R5F524TCAGFP#51 |
| R5F51105AGFK#50 | R5F51305ADFP#50 | R5F52315CGFP#50 | R5F524TCAG***FP#5C |
| R5F5110JADFK#50 | R5F51305AGFK#50 | R5F52316ADFP#50 | R5F524TEADFP#51 |
| R5F5110JAGFK#50 | R5F51305AGFP#50 | R5F52316AGFP#50 | R5F524TEAD***FP#5C |
| R5F51111ADFK#5A | R5F51305BDFP#50 | R5F52316CDFP#50 | R5F524TEAGFP#51 |
| R5F51111AD***FK#5A | R5F51305BGFP#50 | R5F52316CGFP#50 | R5F524TEAG***FP#5C |
| R5F51111AGFK#5A | R5F51306ADFK#50 | R5F52317ADFP#50 | R5F524UBADFP#50 |
| R5F51111AG***FK#5A | R5F51306ADFP#50 | R5F52317AGFP#50 | R5F524UBAD***FP#5C |
| R5F51113ADFK#5A | R5F51306AGFK#50 | R5F52317BDFP#50 | R5F524UBAGFP#50 |
| R5F51113AD***FK#5A | R5F51306AGFP#50 | R5F52317BGFP#50 | R5F524UBAG***FP#5C |
| R5F51113AGFK#5A | R5F51306BDFK#50 | R5F52318ADFP#50 | R5F524UCADFP#50 |
| R5F51113AG***FK#5A | R5F51306BDFP#50 | R5F52318AGFP#50 | R5F524UCAD***FP#5C |
| R5F51114ADFK#5A | R5F51306BGFK#50 | R5F52318BDFP#50 | R5F524UCAGFP#50 |
| R5F51114AD***FK#5A | R5F51306BGFP#50 | R5F52318BGFP#50 | R5F524UCAG***FP#5C |
| R5F51114AGFK#5A | R5F51307ADFK#50 | R5F524T8ADFF#51 | R5F524UEADFP#50 |
| R5F51114AG***FK#5A | R5F51307ADFP#50 | R5F524T8ADFK#51 | R5F524UEAD***FP#5C |
| R5F51115ADFK#5A | R5F51307AGFK#50 | R5F524T8ADFP#51 | R5F524UEAGFP#50 |
| R5F51115AD***FK#5A | R5F51307AGFP#50 | R5F524T8AD***FF#5C | R5F524UEAG***FP#5C |
| R5F51115AGFK#5A | R5F51308ADFK#50 | R5F524T8AD***FP#5C | R5F563TBAGFP#X1 |

| | | |
|--------------------|-----------------|--------------------|
| R5F51115AG***FK#5A | R5F51308ADFP#50 | R5F524T8AGFF#51 |
| R5F51116ADFK#5A | R5F51308AGFK#50 | R5F524T8AGFK#51 |
| R5F51116AGFK#5A | R5F51308AGFP#50 | R5F524T8AGFP#51 |
| R5F51117ADFK#5A | R5F51403ADFK#50 | R5F524T8AG***FF#5C |
| R5F51117AGFK#5A | R5F51403AGFK#50 | R5F524T8AG***FP#5C |
| R5F51118ADFK#5A | R5F51405ADFK#50 | R5F524TAADFF#51 |
| R5F51118AGFK#5A | R5F51405AGFK#50 | R5F524TAADFK#51 |
| R5F5111JADFK#5A | R5F51405BDFK#50 | R5F524TAADFP#51 |
| R5F5111JAD***FK#5A | R5F51405BGFK#50 | R5F524TAAD***FF#5C |
| R5F5111JAGFK#5A | R5F51406ADFK#50 | R5F524TAAD***FP#5C |
| R5F5111JAG***FK#5A | R5F51406AGFK#50 | R5F524TAAGFF#51 |
| R5F51135ADFP#5A | R5F51406BDFK#50 | R5F524TAAGFK#51 |
| R5F51135AGFP#5A | R5F51406BGFK#50 | R5F524TAAGFP#51 |
| R5F51136ADFP#5A | R5F52107CGFP#50 | R5F524TAAG***FF#5C |
| R5F51136AGFP#5A | R5F52108CGFP#50 | R5F524TAAG***FP#5C |

※***: Reserved for ROM code.

change Tape & Reel packaging for RX LQFP PRODUCTS DIFFERENCE DOCUMENT

JULY 15, 2022

IOT PLATFORM BUSINESS DIVISION

IOT AND INFRASTRUCTURE BUSINESS UNIT

RENESAS ELECTRONICS CORPORATION

IMO-AB-22-0089

PC-MCU-A005A/E

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev. 5.0-1 October 2020)

(Rev. 5.0-1 2020.10)

Content

◆ Overview

- 1 . Difference of specification's outline
- 2 . Difference of specification's detail
- 3 . 4M changing points

Overview

Thank you for continuously using our products.

For RX microcomputer products, we change Tape & Reel packaging materials are change.

Therefore, we would like to ask for your kind understanding and cooperation in order to make the procedure smoothly completed.

Yours sincerely,

Change points are reported in the following pages.

1 . DIFFERENCE OF SPECIFICATION'S OUTLINE

| Item | Before | After | Note |
|--|--|---|-------------------------|
| Assembly factory | Renesas Semiconductor (Beijing) Co., Ltd | - | - |
| Tape & Reel / Reel type 14x14mm package | Embossed tape width 32 mm Reel type: For 32-mm width tape | Embossed tape width 24 mm Reel type : For 24-mm width tape | Refer to page 6 to 7 |

※ There is no impact on reliability and specification

2. Difference of specification's detail (1)


Comparison of tape & reel material details: 14x14mm LQFP Tape & Reel packaging

| Packing material | Item | Before | After |
|------------------|---------------------------------|----------------------|----------------------|
| Emboss tape | Taping code | MTE3224H-100P6Q-A | E2424Q14RA |
| | Sprocket hole | Both side | One side |
| | Tape width | 32mm | 24mm |
| | Tape thickness | 0.3mm | 0.3mm |
| | Cavity size | 17.3x17.3 | 16.5x16.5 |
| | Cavity depth | 1.55mm | 1.4mm |
| | Distance between cavity centers | 24mm | 24mm |
| | Material | PS | PS |
| Reel | Reel diameter | 330mm | 330mm |
| | Core diameter | 100mm | 100mm |
| | Reel width | For 32-mm width tape | For 24-mm width tape |


2. Difference of specification's detail (2)

Comparison of tape & reel dimension: 14mm x14mm Tape & Reel LQFP Tape & Reel packaging

Before (W:32mm)



After (W:24mm)



3. 4M changing points (Change of packing materials)

| Item | Check result | Judgement |
|-----------------|--|----------------|
| Machine | The same as current products. | No risk |
| Method | The same as current products. | No risk |
| Man | The same as current products. | No risk |
| Material | Only use certificated materials. It has been confirmed that this product is equivalent to the current product and has no problem. | No risk |

[Renesas.com](https://www.renesas.com)