


- NOTES:
1. ALL DIMENSIONS ARE IN MILLIMETERS.
 2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.



SYMBOL	MILLIMETER		
	MIN.	NOM.	MAX.
A	—	—	4.10
A1	0.25	—	—
A2	3.20	3.32	3.60
D E	31.20	BSC.	—
D1 E1	28.00	BSC.	—
R2	0.13	—	0.30
R1	0.13	—	—
θ	0°	—	7°
θ1	0°	—	—
θ2 θ3	8°	REF	—
c	0.11	0.15	0.23
L	0.73	0.88	1.03
L1	1.60	REF	—
S	0.20	—	—
b	0.22	0.30	0.38
e	0.65	BSC.	—
D2	25.35	—	—
E2	25.35	—	—
ooo	0.25	—	—
bbb	0.20	—	—
ccc	0.10	—	—
ddd	0.13	—	—

REVISIONS				
DCN	REV	DESCRIPTION	DATE	APPROVED
	00	INITIAL RELEASE	07/13/09	P.PAIK

TOLERANCES UNLESS SPECIFIED		6024 SILVER CREEK VALLEY ROAD, SAN JOSE, CA 95138	
DECIMAL ANGULAR ±1°		PHONE: (408) 284-8200	
XX± .1 .05		FAX: (408) 284-3572	
XXX± .030		www.IDT.com	
APPROVALS	DATE	TITLE EA/EAR/EAG 160 PACKAGE OUTLINE	
DRAWN: <i>QAG</i>	7/13/09	28 x 28 mm BODY	
CHECKED		0.65 mm PITCH PQFP	
SIZE	DRAWING No.	REV	
C	PSC-4256	00	

DO NOT SCALE DRAWING

SHEET 1 OF 1