







TOP VIEW




SECTION B-B




SECTION C-C




SIDE VIEW
(SECTION A-A 1)



SIDE VIEW
(SECTION A-A 2)



SIDE VIEW
(SECTION A-A 3)



BOTTOM VIEW

SYMBOL	RENEAS SENSOR			NOTE
	MINIMUM	NOMINAL	MAXIMUM	
A	4.20	4.35	4.50	
A1	2.60	2.65	2.70	
A2	1.40	1.45	1.50	
b	0.95	1.00	1.05	
C	0.25 Ref.			
D	9.95	10.00	10.05	
E	8.95	9.00	9.05	
e	2.00 BSC			
L	3.50	3.60	3.70	
d1	7.60	7.70	7.80	
d2	6.30	6.40	6.50	
d3	2.70	2.80	2.90	
d4	6.35	6.45	6.55	
d5	7.44	7.54	7.64	
T1	1.00	--	1.05	
T2	1.00	--	1.05	
T3	2.18	2.23	2.28	
T4	2.60	2.65	2.70	
T5	0.40	0.45	0.50	

NOTES

- ALL DIMENSIONS IN MM.
- DIMENSION "b" APPLIES TO THE METALLIZED LEAD. IT DOES NOT INCLUDE DAMBAR PROTRUSION.
- DIMENSION "E" DOES NOT INCLUDE MOLD FLASHES, PROTRUSIONS OR GATE BURRS AND SHALL NOT EXCEED 0.15mm PER END DIMENSIONS.
- DIMENSION "D" DOES NOT INCLUDE INTERLEAD FLASHES OR PROTRUSION AND SHALL NOT EXCEED 0.25mm PER SIDE.
- TOP MOLD SURFACE ROUGHNESS (Ra) : 0.15±0.13µm (GLOSSY SURFACE)
BOTTOM MOLD SURFACE ROUGHNESS (Ra) : 0.4~0.8µm
- LEAD CUT DAMBAR PROTRUSION AROUND PACKAGE EDGE WILL BE 0.03-0.07mm.