

IS-1715ARH

Single Event Testing

TR045

Rev 0.00

February 2, 2017

Introduction

The intense heavy ion environment encountered in space applications can cause a variety of transient and destructive effects in analog circuits, including Single Event Latchup (SEL), Single Event Transient (SET), and Single Event Burnout (SEB). These effects can lead to system-level failures including disruption and permanent damage. For predictable space system operation, these components have to be specifically designed for SEE hardness, followed by SEE testing to validate the design. This report describes the detailed results of single event phenomena testing of the complementary FET driver (IS-1715ARH) to determine its susceptibility to the effects of heavy ions.

Product Description

The Intersil [IS-1715ARH](#) is a high speed, high voltage, complementary power MOSFET driver designed for use in synchronous rectification applications. It has a single TTL compatible input and can run at frequencies up to 1MHz. It is constructed in the Intersil Radiation-hardened Silicon Gate (RSG) process for superior hardness in total dose and SEE environments. This process uses dielectrically isolated substrates and is SEL immune as a result. It is hardened to 300krad(Si) and features greatly enhanced low dose rate (ELDRS) hardness.

Related Literature

- For a full list of related documents, visit our website
- [IS-1715ARH](#) product page

SEE Test Procedure

This testing was done at Texas A&M University on August 15-18, 2000. The Cyclotron facility at Texas A&M University was used to provide the heavy ions. The facility, coupled to a K500 superconducting cyclotron, is capable of providing a wide range of test particles and energies for advanced radiation testing.

The instrumentation used to control and monitor the IS-1715ARH while it was under test consisted of the following:

- DVM
- Regulated power supply
- DC current meter
- 2-Channel storage oscilloscope
- 2 High-speed counters

The DVM was used to monitor the regulated power supply voltage before and after exposure. The DC current meter was used to monitor the current drawn by the device under test. In addition to supplying power to the device, the regulated power supply also supplied the input bias conditions. The oscilloscope was used to continuously monitor the two device

outputs during exposure, triggering on a transient, and then storing the output. Transients were then observed by setting the oscilloscope's persistence to infinity so any transient would be captured and stored. The counters were also connected to the two outputs and were used to count transients that were of sufficient magnitude to be recognized as a change in logic state.

Test Devices and Set-Up

Seven fully functional parts, packaged in 24 Ld DIPs with die exposed were tested. The parts were biased with the regulated supply between V_{CC} and GND, with the DC current meter monitoring the current between V_{CC} and GND. 10k resistors were placed from T1 and T2 to GND. Toggle switches controlled the bias condition on ENBL and INPUT. The outputs were PWR and AUX.

The truth table for the IS-1715ARH is shown in [Table 1](#). When ENBL is HIGH, the part is enabled and PWR follows the INPUT signal. When ENBL is LOW, the part is disabled and both outputs are held LOW. In addition, when V_{CC} is less than 8V, the Low Voltage Lockout (LVLO) circuitry ensures that both outputs are held low.

The design goal for the part was to have no LOW to HIGH (LH) glitches on the outputs as this could prove catastrophic to the MOSFET devices being driven. Therefore, four conditions were tested, with the first two being the most important.

1. ENBL HIGH/INPUT HIGH - To check if AUX goes from LOW to HIGH during exposure.
2. ENBL HIGH/INPUT LOW - To check if PWR goes from LOW to HIGH during exposure.
3. ENBL LOW/INPUT LOW - To check if AUX and/or PWR go HIGH during exposure.
4. ENBL LOW/INPUT HIGH - To check if AUX and/or PWR go HIGH during exposure.

TABLE 1. IS-1715ARH TRUTH TABLE

ENBL	INPUT	PWR	AUX
LOW	LOW	LOW	LOW
LOW	HIGH	LOW	LOW
HIGH	LOW	LOW	HIGH
HIGH	HIGH	HIGH	LOW

The toggle switches were used to provide the appropriate levels on ENBL and INPUT. The outputs (PWR and AUX) were connected through scope probe connectors to oscilloscopes and through BNC connectors to pulse counters.

Test Procedure

Several devices were first exposed to Au ions at an incident angle of 60° under dynamic operating conditions and at maximum supply voltage at temperatures of approximately +27°C and +125°C, for determination of latchup or burnout. During and after exposure, the devices were monitored for excessive current with the DVM.

Next, while maintaining the appropriate static input conditions from Table 1, additional devices were exposed to gold ions at an incident angle of 60° and temperatures of approximately +27°C and +125°C and minimum supply voltage (and one at maximum voltage), to determine single event upset and/or transients. During and after exposure, the devices were monitored for excessive current with the DVM and for upset with the oscilloscope.

Results

No latchup or burnout was observed on three parts tested dynamically at +27°C and one part at +125°C at maximum voltage (V_{CC} = 20V) using Au ions (LET_{init} = 90.9MeV/mg/cm²) at 60° incidence from perpendicular (an effective LET of 181.8 as compared to testing with normal incidence). All exposures were run to a fluence of 1x10⁷ particles/cm². Parts were toggled at 1kHz, 50% duty cycle. Supply current was measured pre-radiation and post-radiation and the results are shown in Table 2. As can be seen, there was little or no difference in the pre- and post-radiation supply currents. The total accumulated dose for these parts was about 1.4x10⁴rad(Si). An oscilloscope trace of Unit 2, showing high to low glitches, but no low to high glitches, is shown in Figure 1.

TABLE 2. IS-1715ARH DYNAMIC SEE LATCHUP/BURNOUT TEST RESULTS

UNIT	SUPPLY CURRENT		CONDITIONS AND COMMENTS
	PRE (mA)	POST (mA)	
1	3.54	3.54	No Latchup or Burnout
2	3.56	3.56	No Latchup or Burnout (see Figure 1)
3	3.53	3.53	No Latchup or Burnout
4	3.18	3.13	No Latchup or Burnout

Three parts were then tested for single event transients per Table 1, with some units being tested under several conditions. These results are shown in Table 3. The conditions with ENBL low were only recorded for Unit 5 at 10V and +27°C because the part was totally insensitive to radiation under those conditions. The conditions for the INPUT STATES and corresponding OUTPUT STATES are shown, along with the pre- and post-radiation currents. The columns for PWR SET and AUX SET are to indicate if any transients were seen on the PWR or AUX outputs. For all practical purposes, none were recorded. The only anomaly of that type that was seen was on Unit 5 at +27°C, 20V. That scope

trace is shown in Figure 2. The top trace is INPUT, the middle trace is PWR and the bottom trace is AUX.

Based on the results from Tables 2 and 3 at +27°C, a conservative transient cross section and minimum LET can be estimated. Using a very conservative estimate of 100 transients (more than were seen) at a fluence of 1 x 10⁶ particles/cm², the saturated cross section would be 1 x 10⁻⁴cm². Because no counted transients were recorded using Au ions, the minimum LET number can be established at 90MeV/mg/cm², which again is very conservative but basically SEE immune.




FIGURE 1. IS-1715ARH SCOPE TRACES DURING DYNAMIC EXPOSURE AT 20V, Au AT LET = 90




FIGURE 2. IS-1715ARH SCOPE TRACES DURING STATIC EXPOSURE AT 20V, Au AT LET = 90

Conclusion

As expected, SEE testing of the IS-1715ARH did not produce any latchup or destructive effects even at a high LET of 90MeV/mg/cm². Additionally, no potentially destructive (at the system level) LOW to HIGH (LH) transients were encountered, validating the SEE hardness of this part.

TABLE 3. IS-1715ARH DYNAMIC SEE LATCHUP/BURNOUT TEST RESULTS

UNIT	INPUT STATES		OUTPUT STATES				CURRENT		CONDITIONS AND COMMENTS
	ENBL	INPUT	PWR	PWR SET?	AUX	AUX SET?	PRE (mA)	POST (mA)	
									V_{CC} = 10V AND 20V; TEMPERATURE = +27 °C AND +125 °C ION = GOLD, 90MeV/mg/cm² FLUENCE = 1x10⁶; FLUX = 1x10⁴ ANGLE = 60 °; LET_{EFF} = 181.8
5	LOW	LOW	LOW	NO	LOW	NO	0.46	0.46	Temperature = +27 °C, V _{CC} = 10V - This is the only device these two conditions were tested on - No glitches. No glitches of sufficient magnitude to be counted were observed.
	LOW	HIGH	LOW	NO	LOW	NO	0.47	0.47	
	HIGH	LOW	LOW	NO	HIGH	NO	2.98	2.98	
	HIGH	HIGH	HIGH	NO	LOW	NO	3.69	3.69	
5	HIGH	LOW	LOW	NO	HIGH	YES	3.18	3.19	Temperature = +27 °C, V _{CC} = 20V - Same device tested at 20V saw some high to low glitches - saved on scope.
	HIGH	HIGH	HIGH	NO	LOW	NO	3.93	3.92	
5	HIGH	LOW	LOW	NO	HIGH	NO	2.99	2.99	Temperature = +27 °C, V _{CC} = 10V - No glitches but a slight logic dip on output
	HIGH	HIGH	HIGH	NO	LOW	NO	3.70	3.69	
6	HIGH	LOW	LOW	NO	HIGH	NO	2.99	2.99	Temperature = +27 °C, V _{CC} = 10V - No glitches
	HIGH	HIGH	HIGH	NO	LOW	NO	3.69	3.69	
7	HIGH	LOW	LOW	NO	HIGH	NO	2.97	2.96	Temperature = +27 °C, V _{CC} = 10V - No glitches
	HIGH	HIGH	HIGH	NO	LOW	NO	3.68	3.68	
7	HIGH	LOW	LOW	NO	HIGH	NO	2.74	2.73	Temperature = +125 °C, V _{CC} = 10V - No glitches
	HIGH	HIGH	HIGH	NO	LOW	NO	3.45	3.44	

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.
Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
6. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.4.0-1 November 2017)



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.
1001 Murphy Ranch Road, Milpitas, CA 95035, U.S.A.
Tel: +1-408-432-8888, Fax: +1-408-434-5351

Renesas Electronics Canada Limited
9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3
Tel: +1-905-237-2004

Renesas Electronics Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH
Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.
Room 1709 Quantum Plaza, No.27 ZhichunLu, Haidian District, Beijing, 100191 P. R. China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, 200333 P. R. China
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2265-6688, Fax: +852-2886-9022

Renesas Electronics Taiwan Co., Ltd.
13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

Renesas Electronics Singapore Pte. Ltd.
80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics India Pvt. Ltd.
No.777C, 100 Feet Road, HAL 2nd Stage, Indiranagar, Bangalore 560 038, India
Tel: +91-80-67208700, Fax: +91-80-67208777

Renesas Electronics Korea Co., Ltd.
17F, KAMCO Yangjae Tower, 262, Gangnam-daero, Gangnam-gu, Seoul, 06265 Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5338