


Evaluation of Subsystem Clock Oscillation Circuit

[R5F212D8SNFP-80P] LQFP(12x12) 0.5mm pitch

Measurement conditions :3.3V





Model :SP-T2A
 Frequency :Fo=32.768kHz
 Frequency tolerance :dF/Fo= +/-20x10⁶
 Load capacitance :CL=12.5pF
 Equivalent series resistance :R1=50k ohm max
 Max. Drive level :DL=1x10⁶W max
 Recommended drive level :DL=0.1x10⁶W typ

FEATURES

1. Plastic mold package incorporated tubular type quartz crystal.
2. Suitable for automatic and high density surface mounting.
3. Excellent shock and heat resistance
4. Real time clocks, Timers, Portable applications, Clock source for Micro-Computers

RECOMMENDED SOLDERING PATTERN



Remark) Ix : current through crystal

MODEL:SP-T2A 12.5pF with R5F212D8SNFP at 25°C

Key specifications	Low	High	Remarks
Negative feedback resistance : Rf (M ohm)	Built_in	Built_in	
Current control resistance : Rd (k ohm)	0	0	Control drive level & secure phase margin
Capacitance at gate : Cg (pF)	15	18	Optimal capacity in response to CL
Capacitance at drain : Cd (pF)	15	18	(CL = Cd // Cg + stray capacitance)

Circuit characteristics (at 25°C)	Low	High	Remarks
Matching Accuracy : df / f (x10 ⁻⁶)	-0.9	0.0	Frequency offset volume at specified Vdd
Voltage Fluctuation : +/-df / V (x10 ⁻⁶)	0.0	0.1	Vdd +/-10% (Standard operating voltage range)
Drive Level : DL (x10 ⁻⁶ W)	0.14	0.13	DL=Ix ² Re < 1x10 ⁶ W, Re=R1(1 + Co / CL) ²
Negative resistance : - RL (kohm)	150	1140	5 times larger than R _{1MAX}
Oscillation allowance : M (times)	3.0	22.8	Judgemental standard of oscillation stability
Voltage of oscillation start : Vstrat (V)	1.77	1.77	
Voltage of oscillation stop : Vstop (V)	1.74	1.74	
Oscillation start up time : Ts (sec)	1.32	0.47	Time to reach 90% of output level

Temperature characteristics of circuit		Low	High	Remarks
at -40°C	Variation : df / T (x10 ⁻⁶)	-130	-131	Typ.Tp=25°C (K = -3.5x10 ⁻⁸ / °C ²)
at +85°C	Variation : df / T (x10 ⁻⁶)	-127	-128	Typ.Tp=25°C (K = -3.5x10 ⁻⁸ / °C ²)

The above mentioned value is only for your reference. The value is for the arbitrary samples and does not guarantee the product's characteristics. Please review and check above parameters at customer's end.

Seiko Instruments USA Inc.

2990, West Lomita Blvd., Torrance, CA 90505, U.S.A
 Telephone :+1 310-517-7771 Facsimile :+1 310-517-7792
 Email :crystals@siu-la.com

Seiko Instruments GmbH

Siemensstrasse 9, D-63263 Neu-Isenburg, Germany
 Telephone :+49-6102-297-0 Facsimile :+49-6102-297-320
 Email :info@seiko-instruments.de

Seiko Instruments Inc.

1-8, Nakase, Mihama-ku, Chiba-shi, Chiba 261-8507, Japan
 Facsimile :+81-43-211-8030
 E-mail :component@sii.co.jp



We value the "takumi" spirit.







Seiko Instruments Inc.
 Phone:+81-43-211-1207(Direct)

Evaluation of Subsystem Clock Oscillation Circuit

[R5F212D8SNFP] LQFP(12x12) 0.5mm pitch
 Measurement conditions :3.3V



Test Data at 25°C








Evaluation of Subsystem Clock Oscillation Circuit

[R5F212D8SNFP] LQFP(12x12) 0.5mm pitch

Measurement conditions :3.3V



Test Data : Temperature characteristics



Evaluation of Subsystem Clock Oscillation Circuit

[R5F212D8SNFP-80P] LQFP(12x12) 0.5mm pitch

Measurement conditions :3.3V



Referencial components layout(see Figure 1)




Figure 1 Referencial components layout

Notes Board Design

When using a crystal resonator, place the resonator and its load capacitors as close as possible to SUB_in and SUB_out pins.

Other signal lines should be routed away from the resonator circuit to prevent induction from interfering with correct oscillation (see figure 2).




Figure 2 Example of Incorrect Board Design

Evaluation of Subsystem Clock Oscillation Circuit

[R5F212D8SNFP-80P] LQFP(12x12) 0.5mm pitch

Measurement conditions :3.3V



[Evaluation Sample : SP-T2A 12.5pF at 25°C]


SAMPLE	No.	CL (pF)	Fo(Hz)	fr(Hz)	R1(kohm)	Co(pF)	C1(fF)	Q(k)
SP-T2A 12.5pF	1	12.5	32768.40	32765.68	33.9	1.02	2.245	63.9
	2	12.5	32768.13	32765.43	36.9	1.01	2.227	59.2
	3	12.5	32768.05	32765.35	32.4	1.01	2.227	67.4

[IC Test Data : IC samples Rd=0 ohm,Cg=15 to 18pF,Cd=15 to 18pF at 25°C]

MODE	IC samples	Fosc(Hz)	df / f(x10 ⁻⁶)	DL(x10 ⁻⁶ W)	-RL (kohm)	Vstart(V)	Ts(sec)
High	TYP	32768.400	0.00	0.13	1140	1.77	0.47
	HH	32768.415	0.46	0.14	1240	1.77	0.52
	HL	32768.472	2.20	0.13	1240	1.70	0.60
	LH	32768.405	0.15	0.13	1140	1.68	0.58
	LL	32768.425	0.76	0.12	1140	1.72	0.51
Low	TYP	32768.370	-0.92	0.14	150	1.77	1.32
	HH	32768.372	-0.85	0.16	140	1.77	1.26
	HL	32768.424	0.73	0.15	370	1.70	0.88
	LH	32768.355	-1.37	0.13	122	1.68	1.50
	LL	32768.390	-0.31	0.13	220	1.72	1.27

Remark (see figure 3)

$$F_o = f_r \times \{ C_1 / (2 \times (C_o + C_L)) + 1 \} \text{ (Hz)}$$



Fo : Load resonance frequency
 fr : Resonance frequency
 R1 : Motional resistance
 C1 : Motional capacitance
 Co : Shunt capacitance
 CL : Load Capacitance


Figure 3 Equivalent circuit of crystal unit, and CL

Remark (see figure 4)

Approximate formula of the load capacitance of the circuit CL.

$$CL = C_g \times C_d / (C_g + C_d) + C_s \text{ (pF)}$$

Where Cs(=2 to 4pF) Stands for stray capacity of the circuit.



Cos : X1_X2 Stray capacitance
 Cgs : X1_Vss Stray capacitance
 Cds : X2_Vss Stray capacitance

Figure 4 Stray capacitance Cos,Cgs,Cds of the circuit

Resonator circuit constants will differ depending on the resonator element, stray capacitance in its interconnecting circuit, and other factors. Suitable constants should be determined in consultation with the resonator element manufacturer.


Evaluation of Subsystem Clock Oscillation Circuit

[R5F212D8SNFP] LQFP(12x12) 0.5mm pitch


Measurement conditions : Vdd=1.8V to 5.5V at 25°C

Referential Data : Voltage characteristics


Frequency / voltage coefficient
MODEL : SP-T2A 12.5pF with R5F212D8SNFP




SUB_Vout / voltage coefficient
MODEL : SP-T2A 12.5pF with R5F212D8SNFP



Negative resistance / voltage coefficient
MODEL : SP-T2A 12.5pF with R5F212D8SNFP



Start up time / voltage coefficient
MODEL : SP-T2A 12.5F with R5F212D8SNFP



Cd charge current / voltage coefficient
MODEL : SP-T2A 12.5pF with R5F212D8SNFP

