


Recommended Use of Finger Holder during Reflective PPG Measurements

1. Overview

Reflective PPG is measured against the skin with an emitter and receiver on the same side. The light entering the skin gets diffused, absorbed, and reflected by the tissue and the blood. The reflected light is detected by the sensor.



The observed signal has a large static or DC component on which the small AC cardiovascular signal appears. The ratio of AC/DC is relative to the tissue perfusion and is used for blood oxygen saturation calculations.



For reliable measurements, the preference is for a low noise AC signal, a good AC to DC ratio, and a stable DC signal.

2. Good AC Signal

In order to get a good AC signal, illuminate as much tissue as possible. Lay the finger flat on the sensor / finger rest with the center of the fingerprint about on top of the sensor.




Figure 1. *Recommended* Finger Position Relative to Sensor




Figure 2. *Not Recommended* Finger Position Relative to Sensor




Figure 3. *Not Recommended* Finger Position Relative to Sensor

3. Stable DC Signal

Even slight finger movements or changes in the pressure between finger and finger rest can result in dramatic changes in the DC signal. In order to minimize movements:

- Place the sensor board on a firm surface.
- Rest your hand and elbow on that surface.



- Lay the finger flat on the finger rest and press down on it by about 1 mm to stabilize the finger position. This may also result in a better AC signal bringing the blood vessels closer to the sensor without restricting the blood flow.
- Avoid moving your body during the measurement.
- Avoid talking during the Respiration Rate measurement.

4. Revision History

Revision	Date	Description
1.0	Mar 15, 2021	Initial release.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.