

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

RENESAS TECHNICAL UPD

Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan
Renesas Technology Corp.

Product Category	User Development Environment		Document No.	TN-EML-114A/EA	Rev.	1.0
Title	Problem with the H8S/2378F E10A Emulator System Software V2.0.01 and V2.1.00		Information Category	Usage Limitation		
Applicable Product	H8S/2378F E10A Emulator HS2378KCM01H HS2378KCI01H	Lot No.	Reference Document	H8S Family E10A Emulator Additional Document for User's Manual Specific Guide for the H8S/2378F E10A Emulator (REJ10B0035-0200H)		
		V2.0.01 V2.1.00				

Please note that the H8S/2378F E10A emulator system software V2.0.01 and V2.1.00 have the following problem.

[Problem]

If you use the H8S/2378F E10A emulator system software V2.0.01 or V2.1.00, the emulator will rewrite the memory contents in the range of H'FF6800 to H'FF69FF of the user RAM area. This problem occurs when the H8S/2377F, H8S/2367F, or H8S/2377RF is selected as the device for use with the emulator. If the H8S/2368F, H8S/2378F, or H8S/2378RF is selected, no problem occurs.

[Solution]

This problem will be fixed in the next version (V2.1.02).

The update program will be available on the following website in April 2004.

<http://www.renesas.com/eng/products/mpumcu/tool/download/emulator/e10a/index.html#hew>

Currently, use the user RAM area other than H'FF6800 to H'FF69FF.

Selectable RAM area: H'FF6000 to H'FF67FF and H'FF6A00 to H'FFBFFF