Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.

													Date:	
QzROM PROGRAMMING CONFIRMATION FORM SINGLE-CHIP 8-BIT MICROCOMPUTER M37549G2-XXXFP RENESAS TECHNOLOGY						Receipt	Section head signature	Supervisor signature						
						Note	: Plea	se fill i	n all ite	ms ma	rked*.			
Customer	Company name										se re	Supervisor		
	Telephone number	Deter	()								Issuance signature			
	Date issued	Date:												
	ne number of		sk files	must			oppy di XXXFI				1			
File code											(he	exadec	xadecimal notation)	
Mask file name											.M	SK (eq	ual or less th	an eight chara
	RON Note2: <u>Th</u>	A option	data a on set F	rea: Ad <u>ROM da</u>	dresses ata 0 to	s 10 ₁₆ 2 (addr	ess FFI	08 ₁₆ to	FFDA ₁₆) must	be set a	accordin	FFDC ₁₆ to FF	
Not	tes (RENES					561 10 11		3 11103	5 361 74			01 0.		
Note Q2 in me the <u>St</u>	e 1 : ROM da zROM progra the case whe entioned mas e ROM data a nould you find enesas will au	ta confii mming n ROM k file, R at the re any pro	rmatio will be data p enesa ceipt c oblem,	n requ proce progran s take of the I <u>pleas</u>	est ssed ba mmed i s the re nitial pr <u>e returr</u>	n the a spons oduct	actual r ibility. deliver ediately	nass p There i y. <u>⁄. Two</u>	roduce s no Er weeks	d prod nginee	uct diff ring Sa	ers fror mple, t	m that of above thus please c	/e onfirm
Ei	e 2 : ROM op ther of the fol dered. <u>When</u>	lowing c	data sł	nould b	e set to	o the R	OM op	otion da	ata add	ress (1		f the m	ask file you h	ave
	When the R	OM data	a is pr	otecte	d							00 ₁₆	Address	10 ₁₆
When the ROM da			a is not protected							FF ₁₆	Address	10 ₁₆		
	you set excep ata. Then we i	request	to sub	mit the	e data a	again.								
<u>da</u> W R(<u>'hen Renesas</u> OM code prot nerefore, set F	ect add	ress (F	FDB ₁		he RO	M data	regar	diess o	f the n	resence	e or ah	sence of a pr	

be a standard mark. Please fill out the 24P2Q MARK SPECIFICATION FORM and attach it when you submit the QzROM PROGRAMMING CONFIRMATION FORM. We can't deal with special font marking (customer's trademark etc.) in QzROM microcomputer.

QzROM PROGRAMMING CONFIRMATION FORM SINGLE-CHIP 8-BIT MICROCOMPUTER M37549G2-XXXFP RENESAS TECHNOLOGY

ROM-Protection-Area

F000 ₁₆ F080 ₁₆	Reserved ROM area				
FFD3 ₁₆ FFD4 ₁₆ FFD7 ₁₆ FFD8 ₁₆ FFDA ₁₆ FFDB ₁₆	Reserved ROM area Function set ROM Reserved ROM area (ROM code protect)	All a	irea		
FFDC ₁₆				NOTE:	
FFFD ₁₆ FFFE ₁₆		•		Do not set any data to address FFDB	6.
FFFF ₁₆	Reserved ROM area				

*2. Usage conditions

For our reference of new products, please reply to the following questions about the sage of the products you ordered.

(1) Which operation source main clock do you use?

Ceramic resonator	RC oscillation	High-speed on-chip oscillator
Quartz-crystal oscillation	External clock input	Low-speed on-chip oscillator
Other ()	
At what frequ	ency? f(X _{IN})=	MHz
(2) What is the voltage of power supp	bly (V _{DD}) you use?	
Typ.=	Min.=	V Max.=
(3) What is the ambient temperature	you use?	
Typ.=	Min.=	C Max.=
(4) Which clock division ratio mode d	o you use?	
Double-speed mode (f(ϕ)= ϕ S	OURCE/1) High-speed n	node (f(ϕ)= ϕ SOURCE/2)
Middle-speed mode (f(ϕ)= ϕ S	OURCE/4) Low-speed m	node (f(ϕ)= ϕ SOURCE/8)
(5) Which function of P2 $_0$ / X _{OUT} / X _{COU}	$_{\rm IT},$ P2 ₁ / X _{IN} / X _{CIN} pins do you us	se?
Clock pins not used (P2 ₀ and	P2 ₁ are used as I/O ports)	X _{IN} , X _{OUT}
X_{CIN} , X_{COUT}		External clock input (P2 ₁ is used as I/O port)

QZROM PROGRAMMING CONFIRMATION FORM SINGLE-CHIP 8-BIT MICROCOMPUTER M37549G2-XXXFP RENESAS TECHNOLOGY

(6) Please reply to the following questions about timer function.

(i) Which timer do you use?									
Timer1 Timer2 TimerA									
(ii) Which count source of timer do you use?									
• Timer2 📕 🗍									
TimerA underflow signal									
- TimerA \$\phiSOURCE/16 \$\phiSOURCE/2 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32 \$\phiSOURCE/32									
\$OURCE/64 \$\$OURCE/128 \$									
Low-speed on-chip oscillator output									
(iii) Do you use the Output compare?									
Use () channel Not use									
(iv) Do you use the Input capture?									
Use Not use									
(7) Do you use the Serial I/O?									
Use Not use									
(Clock synchronous Serial I/O mode Asynchronous Serial I/O(UART) mode)									
(8) Do you use the A/D converter?									
Use Not use									
(9) Do you use the Watchdog timer?									
Use Not use									
(10) Do you use the oscillation stop detection circuit?									
Use Not use									
Thank you cooperation									

*3. Comments