



REVISIONS			DATE	APPROVED
REV	DESCRIPTION			
00	INITIAL RELEASE		21/02/12	M. ROY



DIMENSIONS			
SYMBOL	MIN	NOM	MAX
A	0.85	0.95	1.05
A1	0.10	0.15	0.20
phi b	0.20	0.25	0.30
e	0.50 BSC		
D	5.00 BSC		
D1	4.50 BSC		
E	5.00 BSC		
E1	4.50 BSC		
n	71		
f	0.15	0.25	0.35
TOLERANCE OF FORM & POSITION			
aaa	0.10		
bbb	0.15		
ccc	0.10		
ddd	0.05		
eee	0.08		



NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. 'e' REPRESENT THE BASIC LAND GRID PITCH .
3. 'n' IS THE TOTAL NUMBER OF I/O.
4. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
5. SEATING PLANE AND PRIMARY DATUM -C- ARE DEFINED BY THE CONTACT POINTS OF THREE OR MORE SOLDER PADS THAT SUPPORT THE DEVICE WHEN PLACED ON A TOP OF A PLANAR SURFACE.

TOLERANCES UNLESS SPECIFIED		www.IDT.com	
DECIMAL	ANGULAR	6024 Silver Creek Valley Rd San Jose, CA 95138	
xxx± 0.05	±	PHONE: (408) 284-8200	
xxxx±		FAX: (408) 284-2775	
APPROVALS	DATE	TITLE NAG71 PACKAGE OUTLINE	
DRAWN 77102	19/07/11	5X3mm BODY size, 0.5mm Pitch	
CHECKED		SIZE	DRAWING No. PSC-4404
			REV 00
		DO NOT SCALE DRAWING	SHEET 1 OF 1