

The M3016-EVK evaluation kit contains the 16Mbit MRAM device and enables users to develop interactive hardware solutions using an Arduino UNO Rev3 host board connected through a standard SPI interface. The Arduino UNO host board communicates with a computer using a USB 2.0 cable type A/B and terminal emulator software. Software bundled APIs and a test program from Avalanche provide basic access to the MRAM device's functionality.

Kit Contents

The M3016 Evaluation Kit includes:

- One Arduino UNO Rev3 board
- One SPI evaluation board with Arduino UNO compatible R3 headers
 - One populated 16Mbit MRAM device in a 8-pin SOIC package
- One USB 2.0 cable type A/B

Hardware Requirements

- A PC system with one available USB 2.0/3.0 port
- Windows 7/8/10 with 32/64-bit operation system

Technical Documents

Download the User Guide and Test Program from <http://www.avalanche-technology.com/support/documentation-software>.

Follow the instructions outlined in the *Evaluation Board User Guide* on how to connect the evaluation board to the PC.

Revision History

Revision	Date	Description
1.0	May.20.20	Initial release.

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.