

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

740 Simulator Debugger V.1.02.00

Release Notes

This document describes the notes of this debugger, and please read before you start to use this debugger.

And also, please refer to the “High-performance Embedded Workshop Release Notes” about the notes of High-performance Embedded Workshop IDE.

Contents

1	Notes	2
1.1	Line Assembly	2
1.2	Event Setting.....	2
1.3	Output Port	2
1.4	Data Trace	2
1.5	Trace.....	2
1.6	RAM Monitor.....	2
1.7	Memory	3
1.8	Script.....	3
1.9	Macro recording function.....	3
1.10	Test facility function	3
1.11	Using cast operators for the member variable	3
1.12	Download module dialog box	3
1.13	Notes on Debugging (740 Simulator Debugger).....	3
1.13.1	About the program that exceeds the address space of 64 Kbyte	3
1.13.2	Executed time span and executed cycles	3
2	System Requirements.....	4
2.1	740 Simulator Debugger.....	4
3	Version Report.....	5
3.1	740 Simulator Debugger V.1.02.00.....	5
3.1.1	Revisions to Restrictions.....	5
3.1.2	Functional Extensions and Modifications.....	5

1 Notes

1.1 Line Assembly

Regardless of the Radix setting, the default for line assembly input is decimal. Specify H as the radix for a hexadecimal input.

1.2 Event Setting

1. TAB order in Set Event Status dialog box
Even when you press [TAB] key, the next input control may not be focused on the Set Event Status dialog boxes opened from Trace Point.
2. In-place-edit mode on event list
On event list in Trace Point, High-performance Embedded Workshop will not escape from in-place-edit mode even when you press the [ESC] key.
3. Event setting by BIT SYMBOL
When the specified address is odd numbers, the setting by BIT SYMBOL can not set the correct condition. Use DATA ACCESS setting and specify the compared data with the data mask. For details about how to set the conditions for odd number addresses, refer to the online help.
4. Event detection for BIT SYMBOL
When the event is set to detect the access to specified bit, it will be detected even if the other bit of the same address as the specified bit is accessed. This is because the access to the bit from MCU is byte access.

1.3 Output Port

1. Use of Symbol
If you use a symbol to specify an address in the Set Port Dialog box, an error “Can’t find symbol.” will occur, when you restart the HEW or get back to the session.

1.4 Data Trace

1. Split-bar behavior when double-clicking
If you double-click the split-bar, which divides view up and down, the horizontal scroll-bar, vertical scroll-bar, and tabs in the upper view will vanish. Drag the split-bar to display them again.

1.5 Trace

1. Specifying function in SRC mode
In the SRC mode, when you specify a function to display it, if the current displayed source file includes the function, the top of the source file will be displayed.
2. Saving of tracing result in text
 - When you save a tracing result in text with only “BUS” and “DATA” buttons ON, the vertical position of some headers will shifts from the corresponding data. Check “Tab Separated Format” and open it with spreadsheet applications to display them correctly.
 - When you save a tracing result that includes BUS and DATA access information in text, some headers can not be correct. When you check “Tab Separated Format”, the headers will be correct.
3. Time concerned data
Displayed time concerned data is not measured, though time concerned buttons and items in pop-up menu are active.(Time measurement is not supported.)
4. Loading the trace image file
Trace window can not load the trace image file saved by PDxx debuggers. And also, trace window can not load the trace image file saved by the different target from the current target.

1.6 RAM Monitor

1. Proportional Fonts
When a proportional font is selected, a part of the characters in the view may be hidden. Fixed fonts are recommended.

1.7 Memory

1. 8 bytes data operations
To set, fill, and copy 8 bytes data are not supported.

1.8 Script

1. Result of interactive command
When you invoke an interactive command, for example, Assemble and setMemoryByte, the running dialog box will appear and may hide the view of the results.

1.9 Macro recording function

The debug windows which support the macro recording function are memory, registers, and IO. And also, the debug operations which support this are Reset CPU, Go, Reset Go, Go To Cursor, Step In, Step Over, Step Out, Add/Delete a break point, and Download the target program.

1.10 Test facility function

The contents to be compared by the test facility functions are memory, registers, I/O, Output, and stack trace window.

1.11 Using cast operators for the member variable

When you use cast operators for the member variable to refer to it as the pointer of the structure, you would not refer to it correctly.

1.12 Download module dialog box

This debugger does not support the setting of "Offset", "Memory verify on download", and "Access Size" in the download module setting dialog box. These are always treated as "Offset: 0", "Memory verify: off", and "Access Size: 1".

1.13 Notes on Debugging (740 Simulator Debugger)

1.13.1 About the program that exceeds the address space of 64 Kbyte

740 emulator debugger doesn't correspond to the program that exceeds 64 Kbyte that ICC740 generated.

1.13.2 Executed time span and executed cycles

The displayed cycles for execution are calculated by the value described in the software manuals of the micro computer. And the displayed time span for execution is calculated from the cycles and the frequency which is specified in the INIT dialog. The external bus width, the state of instruction queues, or the software wait for instructions are not considered, so the value will be different from the value of the actual MCUs.

To calculate the actual cycles, use the full-spec emulator or the compact emulator.

2 System Requirements

2.1 740 Simulator Debugger

Target host PC	
PC	IBM PC/AT compatible with Pentium III 600MHz or higher
OS	Windows XP Windows 2000 Windows Me Windows 98 Second Edition
Memory	128MB (ten times the size of the target load module file recommended)
HDD	Hard disk available capacity for installation: 100MB or more. Prepare an area at least double the memory capacity (four-times or more recommended) as the swap area.
Display Resolution	1024 x 768 or higher recommended

3 Version Report

This section describes the specification of the changed software.

3.1 740 Simulator Debugger V.1.02.00

In this version, the following specifications were changed from the previous version 740 Simulator Debugger V.1.00.00.

This version supports all of the function extensions and the revisions to the restrictions in the High-performance Embedded Workshop V.4.01.00 and V.4.01.01. For more details, please refer to RENESAS TOOL NEWS “060701/tn1” issued on July 1, 2006 and “060801/tn1” issued on August 1, 2006.

3.1.1 Revisions to Restrictions

1. A limitation has been corrected: The structure member variables, union member variables, or class member variables whose name begins with a letter of ‘e’ or ‘E’ immediately followed by a numeral, are not referenced.

For more details, refer to the RENESAS TOOL NEWS RSO-M3T-PD32RM-060116D issued on January 16, 2006.

3.1.2 Functional Extensions and Modifications

1. These commands, which can be invoked in Command Line, have been supported:
breakpoint, breakpoint_disable, breakpoint_display, breakpoint_clear
register_display, register_set
disassemble, assemble