



Note: 27 ohm plus 43.2 ohm resistors may be used instead of 69.8 ohm.

Tri-Level

SMB_A1	SMB_A0	Add
0	0	D8
0	0	DA
0	1	DE
0	1	C2
1	0	C4
1	0	C6
1	1	CA
1	1	CC
1	1	CE

HiBW BypM LoBW# MODE
 Low PLL Lo BW
 Mid Bypass
 High PLL Hi BW

NOTE: PLL is OFF in Bypass Mode

NOTE:FERRITE BEADS =

Manufacture	Part Number	Z@100MHz	PkgSz	DC res.	Current (Ma)
muRata	BLM21A601R	600	0805	0.30	600
TDK	MMZ2012S601A	600	0805	0.30	600
STEWART	HZ0805E601R	600	0805	0.30	600
AssocCmpTch	CBG0805-600-50	600	0805	0.30	600

Impedance dependent resistor values

Resistor	Zdiff = 100 ohm	Zdiff = 85 ohm
IREF	475 1%	412 1%
Series	33 5%	27 5%
Shunt	49.9 1%	43.2 1%
Feedback	82.5 1%	69.8 1%

Revision history

Rev	Change
0.1	First publication
0.2	Correct IREF resistor value.
0.3	Add pin 37 to symbol.
0.4	Update feedback R value.

Integrated Device Technology
 6024 Silver Creek Valley Road
 San Jose, CA

Title: ICS9ZX21201	
Size: B	Document Number: _____
Date: Wednesday, June 08, 2011	Rev: 0.4
Sheet: 1	of 1