



LAYOUT NOTE:
R2 to be placed close to U1.






SCHEMATIC TEMPLATE REV PA2 (November 30, 2011) DIALOG DOCUMENT NUMBER 31-902-03

CONFIDENTIAL INFORMATION		TITLE: DA9066 Performance Board		
		PREPARED: TG	DATED: 13-Jun-2017	
RESPONSIBLE: xxx	DATED: xx/xx/xxxx	SHEET NAME: DA9066_AUDIO		PAGE: 2 OF 4

Connections to Motherboard



DESIGN NOTE:
J62, J63, J64 and J65 to match the locations
of J62, J63, J64 and J65 on 44--179-170-01-A



LAYOUT NOTE:
For connectors J1-J6, pin 1 is a sense output
(kelvin connection), pin 2 is a load connection.


CONFIDENTIAL INFORMATION		TITLE: DA9066 Performance Board	
PREPARED: TG	DATED: 13-Jun-2017	DRAWING NO: 183-05-A	REV: A1
RESPONSIBLE: xxx	DATED: xx/xx/xxxx	SHEET NAME: CONNECTORS	PAGE: 3 OF 4




REV	DATE	ENGINEER	NOTES
1.0	14 February 2013	CPJ	Initial version.
A1	13 Juney 2017	TG	Aligned Label 'L2' to avoid confusion. Corrected C53 to 10uF

Default Jumper Placement:


LNK28

 RED
Fit to J14:1-2


LNK30

 RED
Fit to J16:2-3


LNK31

 RED
Fit to J17:2-3


LNK1

 RED
Fit to J23:2-3


LNK7

 RED
Fit to J28:1-2


LNK2

 BLUE
Fit to J27:1-2


LNK3

 BLUE
Fit to J27:3-4


LNK4

 BLUE
Fit to J27:5-6

LNK5

 BLUE
Fit to J27:7-8

LNK6

 BLUE
Fit to J27:9-10