

Customer Notification

QB-70F3534-PD

In-Circuit-Emulator

Operating Precautions

Target Device

μPD70F3522-26, 35-37, V850E2/DX4

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.

"Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.

10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority- owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

Table of Contents

A) Table of Operating Precautions	5
B) Description of Operating Precautions	6
C) Valid Specification	9
D) Revision History.....	10

A) Table of Operating Precautions

No.	Outline	QB-70F3534-PD				
		Rev.	A	B	C	D
		Date	10-Dec 2009	10-Mar 2010	15-Jun 2010	04-Oct 2011
		HW Version	V1.00	V2.20	V3.10	V4.00
		70F3534	DS1.0	DS2.0	DS2.2	n/a
70F3534A	n/a	n/a	n/a	ES1.0		
1	Tool status is DS	Y	N	N	N	
2	Trace not supported	Y	N	N	N	
3	PLL 0/1/2 not working correctly	Y	N	N	N	
4	POC not supported	Y	Y	N	N	
5	POC not supported when PWGDEN = 0 and PWRGOOD = L	Y	Y	Y	N	
6	LVI levels are higher than for device	Y	Y	Y	N	
7	VLVF not supported (Remaining limitation)	Y	Y	Y	Y	
8	Ports supplied by E0VDD fixed to 5.5V of internal power supply	Y	N	N	N	
9	WAKE pin is not Hi-Z during RESET	Y	Y	Y	Y	
10	LCD segment pin allocation differs between device revisions	Y	Y	Y	N	
11	RTC clock selector differs between device revisions	Y	Y	Y	N	
12	LVI level 3.1V is not available	N	N	N	Y	
13	REG1VDD must remain powered at all times when emulating devices	Y	Y	Y	Y	

N: Not applicable

Y: Applicable

Note: The control code is the second letter from the left of the 10 digit serial number or in case of update the latest control code is mentioned on the version up sticker.

B) Description of Operating Precautions

No. 1	Tool status is DS
<p><u>Details</u> Tool test coverage is below 60%.</p> <p><u>Workaround</u> None.</p>	
No. 2	POC not supported
<p><u>Details</u> When the supply voltage REG0VDD drops below the POC (power-on-clear) threshold voltage, the debugger will hang.</p> <p><u>Workaround</u> None.</p>	
No. 3	Trace not supported
<p><u>Details</u> None.</p> <p><u>Workaround</u> None.</p>	
No. 4	PLL 0/1/2 not working correctly
<p><u>Details</u> Maximum PLL frequency is up to 40 MHz.</p> <p><u>Workaround</u> None.</p>	
No. 5	POC not supported when PWGDEN = 0 and PWRGOOD = L
<p><u>Details</u> If the flash mask option PWGDEN is set to 0 and the pin PWRGOOD is at a low-level during release of the POC condition (i.e. when REG0VDD rises above the POC threshold voltage) the device will not start up.</p> <p><u>Workaround</u> Clamp the pin PWRGOOD to H. As this pin's function is disabled, the level should not be of importance.</p>	

No. 6	LVI levels are higher than for device
	<p><u>Details</u> The LVI levels (set in the SFR LVICNT) are higher in the tool than in the device. The difference is approx. 0.18V. E.g. if the LVI would trigger at 3.50V in the device, it will trigger at 3.68V on the tool.</p> <p><u>Workaround</u> None.</p>
No. 7	VLVF not supported
	<p><u>Details</u> The VLVF flag is not supported. Even if REG0VDD is below the threshold voltage, the flag's value is not affected.</p> <p><u>Workaround</u> None.</p>
No. 8	Ports supplied by E0VDD fixed to 5.5V of internal power supply
	<p><u>Details</u> Following ports are effected: P0, JP0, VCMPIN, WAKE, PWRGOOD, FLMD0</p> <p><u>Workaround</u> None.</p>
No. 9	WAKE pin is not Hi-Z during RESET
	<p><u>Details</u> The behavior of the WAKE pin during an external RESET was re-specified. Newer device versions do not drive the WAKE pin during RESET (i.e. Hi-Z). The tool drives it at all times, even during RESET. Also, the buffer characteristics and timings will differ from the device.</p> <p><u>Workaround</u> None.</p>

No. 10	LCD segment pin allocation differs between device revisions
	<p><u>Details</u> The mapping of the LCD segment functions differs between device revisions. The tool has this configuration: - JP0.4/SEG13 - JP0.5/SEG12 Newer device revisions have this configuration: - JP0.4/SEG12 - JP0.5/SEG13</p> <p><u>Workaround</u> a) The target hardware may be adapted to the swapped segment lines. b) The segments may be swapped in the layout of the LCD macro (software solution).</p>
No. 11	RTC clock selector differs between device revisions
	<p><u>Details</u> The mapping of the RTC clock selector (AWO_09) differs between device revisions. The tool has this configuration: ID=1 is used for the low speed ring oscillator. Newer device revisions have this configuration: ID=10 (non-standard) is used for the low speed ring oscillator.</p> <p><u>Workaround</u> Use the corresponding ID (software solution).</p>
No. 12	LVI level 3.1V is not available
	<p><u>Details</u> When setting the LVI to a level of 3.1V, it will not react, even if the voltage drops below this voltage.</p> <p><u>Workaround</u> None.</p>
No. 13	REG1VDD must remain powered at all times when emulating devices
	<p><u>Details</u> This item only applies when emulating one of the following devices: uPD70F3522/23/24/25/26 when using a version of firmware prior to E1.00s The device allows the supply pins REG1VDD0..2 to be turned off when the WAKE pin is not driving a High level (e.g. during sleep mode or reset). The tool does not allow this condition. Please keep these pins powered at all times to work with the tool.</p> <p><u>Workaround</u> 1) Update the firmware version to E1.00s (or later), or 2) Modify target hardware to supply REG1VDD0..2 at all times.</p>

C) Valid Specification

Item	Date published	Document No.	Document Title
1	September 2012	R20TU0018ED0300	This document
2	April 2010	EEDT-CD-0423-2.0	Preliminary User's Manual

D) Revision History

Item	Date published	Document No.	Comment
1	December 2009	EEDT-OP-0044-1.0	1 st release
2	February 2010	EEDT-OP-0044-2.0	Update
3	March 2010	EEDT-OP-0044-3.0	Tool reached ES-level
4	March 2010	EEDT-OP-0044-3.1	Update
5	April 2010	EEDT-OP-0044-3.2	New company name
6	June 2010	EEDT-OP-0044-4.0	Update
7	August 2010	R20TU0018ED0100	Update, items 5+6 separated, items 9-11 added
8	October 2011	R20TU0018ED0200	Update (new emulation chip), item 12 added
9	September 2012	R20TU0018ED0300	Minimum firmware version specification (item 13)

