

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

| | |
|-------------------|--|
| Masked ROM Number | |
|-------------------|--|

**RENESAS TECHNOLOGY SINGLE-CHIP 16/32-BIT
MICROCOMPUTER M30876MJ-XXXFP/GP
MASKED ROM CONFIRMATION FORM**

| |
|------------------|
| Renesas use only |
| Date*: |
| Received by* |
| Approved by* |

Note : Please fill out all items except ones marked with asterisks(*)

| | |
|--|--------------|
| Company : | Date issued: |
| Contact person name : | Prepared by |
| Phone number : - - | Approved by |

1. Checklist

Renesas Technology customizes masked ROM with your mask file generated by the mask file generation utilities. Renesas Technology makes no warranty, representation or guarantee regarding the suitability of its products unless the products contain the different ROM data from the mask file you provided. Submit your mask files in 3.5" 2HD floppy disks, IBM formatted. Each floppy disk must contain one mask file only.

Microcomputer type : M30876MJ-XXXFP M30876MJ-XXXGP

File code : (HEX)

Mask file name : .MSK (8-digit alphanumeric)

2. Marking Specification

The marking specification varies with package types. Complete separate marking specification sheets for each package and attach it to the associated masked ROM confirmation form.

For M30876MJ-XXXFP, use the 100P6S marking specification sheet of M32C only.

For M30876MJ-XXXGP, use the 100P6Q marking specification sheet of M32C only.

3. Operating Conditions

For reference when testing the products, please answer the following questions concerning the operating conditions of the products.

(1) Which type of resonator do you use with the XIN-XOUT oscillation circuit?

- Ceramic resonator Crystal oscillator
 External clock input Other ())

What frequency do you use?

f(XIN) = MHz

| | |
|-------------------|--|
| Masked ROM Number | |
|-------------------|--|

**RENESAS TECHNOLOGY SINGLE-CHIP 16/32-BIT
MICROCOMPUTER M30876MJ-XXXFP/GP
MASKED ROM CONFIRMATION FORM**

(2) Which type of resonator do you use with the XCIN-XCOUT oscillation circuit?

- Ceramic resonator Crystal oscillator
 External clock input Other ()

What frequency do you use?


f(XCIN) = kHz

(3) Which operation mode do you use with the microcomputer?

- Single-chip mode Memory expansion mode
 Microprocessor mode


(4) Which operating supply voltage do you apply to the microcomputer?

(Circle the operating voltage range)



(5) Under which operating ambient temperature do you operate the microcomputer?

(Circle the operating temperature range)



(6) Do you use the I²C (Inter IC) bus function?

- Not use Use

(7) Do you use the IE (Inter Equipment) bus function?

- Not use Use

(8) Do you use the CAN (Controller Area Network) function?

- Not use Use

Thank you for your cooperation.

4. Special notes (Indicate none if there is nothing to specify)