

RL78:EXPLANATION OF ORDERABLE PART NUMBERS

(For part numbers start with R5F1)

R5 F 1 00 6 E C A SP #Vx

Renesas MCU ROM Type F: Flash RL78 Family

Product group

00	G13 with DF	0M	I1B	1F	G1H
01	G13 no DF	0N	I1C with AES	1M	L1A
02	G12 with DF	0P	F14	1N	H1D with AFE
03	G12 no DF	0R	L12	1P	H1D with AFE
04	G14	0W	L13	1R	H1D no AFE
05	G11	0Y	G10	1T	I1C no AES
07	I1A	10	L1C with USB	1W	G1M
09	F12	11	L1C no USB	1Y	G1N
0A	F13 no CAN	13	F15	1Z	G1P
0B	F13 with CAN	17	I1D	20	G15
0E	G1A	1A	G1D	21	G16
0F	G1E	1B	G1F	40	G13A
0J	G1C USBHost	1C	I1E		
0K	G1C USB Peri	1E	G1G		

Pin count

0	8	D	38
1	10	E	40
4	16	F	44
6	20	G	48
7	24	J	52
8	25	L	64
9	28	M	80
A	30	P	100
B	32	S	128
C	36	T	144

ROM Size (KB)

4	1	D	48
6	2	E	64
7	4	F	96
8	8	G	128
9	12	H	192
A	16	J	256
B	24	K	384
C	32	L	512

Temperature & Quality Grade

A	-40°C to 85°C	Consumer
D	-40°C to 85°C	Industrial
G	-40°C to 105°C	Industrial
M	-40°C to 125°C	Industrial
J	-40°C to 85°C	Automotive
L	-40°C to 105°C	Automotive
K	-40°C to 125°C	Automotive
Y	-40°C to 150°C	Automotive

C Cu (Copper)

Packaging, Material (Pb-free)

#0	Full Carton (HWQFN,HVQFN,WFLGA)
#1	Full Carton (SSOP,LSSOP,LQFP,LFQFP,TSSOP,WDFN)
#U, #2	Tray (HWQFN,HVQFN,VFBGA,VFLGA,WFLGA,FLGA,TFBGA)
#V, #3	Tray, Tube*1 (SSOP,LSSOP,LQFP,LFQFP,TSSOP,WDFN)
#W, #4	Embossed Tape (HWQFN,HVQFN,VFBGA,VFLGA,WFLGA,FLGA,TFBGA)
#X, #5	Embossed Tape (SSOP,LSSOP,LQFP,LFQFP,TSSOP,WDFN)
#6	Full Tray (HWQFN,HVQFN,VFBGA,WFLGA)
#7	Full Tray (LFQFP,LQFP,SSOP,TSSOP,LSSOP,WDFN)

Package, Pin Pitch

SP	SSOP 0.65 mm	LA	WFLGA 0.5 mm
	LSSOP 0.65 mm		VFLGA 0.65 mm
SM	TSSOP 0.65 mm	BG	VFBGA 0.4 mm
NA	HWQFN 0.5 mm		TFBGA 0.5mm
	HVQFN 0.5 mm	FA	LQFP 0.65 mm
NB	HWQFN 0.65 mm	FB	LFQFP 0.5 mm
	HWQFN 0.4 mm		FP
NS	WDFN 0.65mm		

*1: For 20-pin RL78/G11, RL78/G12, RL78/G15, RL78/G16 RL78/I1A and RL78/I1D LSSOP products only the package specification is tube.

*2: Please contact Renesas sales or agent for details.

RL78:EXPLANATION OF ORDERABLE PART NUMBERS

(For part numbers start with R7F1)

