

M16C/62P Group, M16C/65 Group Differences between M16C/62P and M16C/65

R01AN0442EJ0103 Rev. 1.03 Jul 29, 2011

# Abstract

The following document describes differences between M16C/62P 100-pin version and M16C/65 100-pin version. Refer to each device's hardware manual for details.

# Products

MCUs: M16C/62P Group, M16C/65 Group

With its enhanced peripheral functions, the M16C/65 Group MCU has pin assignments and peripheral functions that are compatible with the M16C/62P Group, making it simple to replace the M16C/62P Group with the M16C/65 Group.



# Contents

1.	Differences	3
1.1	Differences in Functions	3
1.2	Pin Characteristics	6
2.	Detailed Comparison	7
2.1	Differences between Protections	7
2.2	Differences between Resets	7
2.3	Differences between Voltage Detectors	8
2.4	Differences between Clock Generators	9
2.5	Differences between Power Controls	. 10
2.6	Differences between Processor Modes	. 10
2.7	Differences in Bus	11
2.8	Differences between Programmable I/O Ports	. 12
2.9	Differences between Interrupts	. 13
2.10	Differences in Watchdog Timers	. 16
2.11	Differences between DMACs	. 17
2.12	Differences in Timers	. 19
2.13	Differences between Three-phase Motor Control Timer Functions	. 22
2.14	Differences between Serial Interfaces	. 23
2.15	Differences between A/D Converters	. 26
2.16	Differences between CRC Calculators	. 27
2.17	Differences between Flash Memories	. 27
2.18	Differences between Flash Memory Block Configurations	. 30
2.19	New Functions added in the M16C/65	. 31
2.20	Differences in Development Tool	. 31
3.	Reference Documents	. 32



# 1. Differences

### 1.1 Differences in Functions

Table 1.1 and Table 1.3 list Differences in Functions.

#### Table 1.1 Differences between Functions (1/3) <sup>(1)</sup>

Item		M16C/62P	M16C/65	
Minimum Instruction Execution Time		41.7 ns (f(BCLK) = 24 MHz, VCC1 = 3.0 to 5.5 V) 100 ns (f(BCLK) = 10 MHz, VCC1 = 2.7 to 5.5 V)	31.25 ns (f(BLCK) = 32 MHz, VCC1 = 2.7 to 5.5 V)	
Clock Gene	erator	PLL, XIN, XCIN, on-chip oscillator (approx.1 MHz)	PLL, XIN, XCIN, 125 kHz on-chip oscillator, 40 MHz on-chip oscillator	
Power	Slow read mode	No	Yes	
Control	Low current consumption read mode	No	Yes	
CPU Clock	After Reset	Main clock divided by 8	125 kHz on-chip oscillator clock divided by 8	
NMI Pin		MII interrupt input port	PM24 bit = 0 (when $\overline{\text{NMI}}$ is disabled): I/O port (N-channel <u>open</u> drain output) PM24 bit = 1 (when NMI is enabled): NMI interrupt input port	
Expanded area External Bus		04000h to 07FFFh (when PM13 = 0) 08000h to 0FFFFh (when PM10 = 0) 10000h to 26FFFh 28000h to 7FFFFh 80000h to CFFFFh (when PM13 = 0) D0000h to FFFFFh (in microprocessor mode)	04000h to 07FFFh (when PM13 = 0) 08000h to 0CFFFh (when PM10 = 0) 0D800h to 0DFFFh 0E000h to 0FFFFh (when PM10 = 0) 10000h to 13FFFh (when PRG2C0 = 1) 14000h to 26FFFh 28000h to 7FFFFh 80000h to CFFFFh (when PM13 = 0) D0000h to FFFFFh (in microprocessor mode)	
	Bus wait	0 to 3 wait(s) selectable	0 to 8 wait(s) selectable	
	Recovery cycle	No	0 to 3 cycle(s) selectable	
	HOLD input	Enabled	Disabled	
Interrupt		External interrupts: 8	External interrupts: 13	
Watchdog Timer	Reset start function	No	Selectable from start and stop	
	Count source	CPU clock, on-chip oscillator (approx. 1 MHz)	CPU clock, on-chip oscillator (125 kHz)	
DMA	DMAC	2 channels Trigger sources: 25	4 channels Trigger sources: 43	

PM24: Bit in the PM2 register PM13,PM10: Bits in the PM1 register PRG2C0: Bit in the PRG2C register

Note:

1. Refer to hardware manual for electrical characteristics and more details.



	Item	M16C/62P	M16C/65
	Timer A, timer B count source	Selectable from f1, f2, f8, f32, and fC32	Selectable from f1TIMAB, f2TIMAB, f8TIMAB, f32TIMAB, f64TIMAB, fOCO-S, fOCO-F, and fC32
Timer	Real-time clock	No	Count: second, minute, hour, day of week
Inner	PWM function	No	8 bits x 2
	Remote control signal receive function	No	2 circuits
	UART	Clock synchronous/asynchronous x 3 channels	Clock synchronous/asynchronous x 6 channels
Serial Interface	UART0 to UART2, UART5 to UART7 clock prior to division select function	f1 only	Selectable from f1 and fOCO-F
	CEC	No	Yes
	Multi-master I <sup>2</sup> C-bus interface	No	1 channel
	Resolution	8-bit/10-bit (selectable)	10-bit only
A/D Converter	Operation clock φAD	Selectable from fAD, fAD divided by 2, fAD divided by 3, fAD divided by 4, fAD divided by 6, and fAD divided by 12	Selectable from f1, f1 divided by 2, f1 divided by 3, f1 divided by 4, f1 divided by 6, f1 divided by 12, fOCO40M divided by 2, fOCO40M divided by 3, fOCO40M divided by 4, fOCO40M divided by 6, and fOCO40M divided by 12
	Sample and hold	Yes/No (selectable)	Yes
CRC Calculator	Generator polynomial	CRC-CCITT (X <sup>16</sup> + X <sup>12</sup> + X <sup>5</sup> + 1)	Selectable from CRC-CCITT ( $X^{16} + X^{12} + X^5 + 1$ ) and CRC-16 ( $X^{16} + X^{15} + X^2 + 1$ )
	MSB/LSB select function	No	Yes
	CRC snoop	No	Yes

Table 1.2	Differences between Functions (2/3) <sup>(1)</sup>
-----------	--

Note:

1. Refer to hardware manual for electrical characteristics and more details.



Item		M16C/62P	M16C/65	
	Address FFFFFh function setting ROM code protect select function		<ul> <li>Selectable Options</li> <li>Watchdog timer autostart function (after reset)</li> <li>Count source protection mode select function (after reset)</li> <li>ROM code protect function</li> <li>Vdet0 select function</li> <li>Voltage monitor 0 reset function (after hardware reset)</li> </ul>	
Flash Memory	Memory map Juser ROM Program ROM 080000h to 0FFFFh Data flash Block A 00F000h to 00FFFh		User ROM • Program ROM 1 080000h to 0FFFFh • Program ROM 2 010000h to 013FFFh Data flash • Block A 00E000h to 00EFFFh • Block B 00F000h to 00FFFFh	
	User ROM (512-Kbyte)	64 Kbytes x 7 32 Kbytes x 1 8 Kbytes x 3 4 Kbytes x 2	64 Kbytes x 8 16 Kbytes x 1 (program ROM 2)	
	Data flash	4 Kbytes x 1 (block A)	4 Kbytes x 2 (block A, block B)	
	Program method	In units of 1 word (16-bit)	In units of 2 words (32-bit)	
	Erase method	Erase all unlocked blocks, block erase	Block erase	
	User boot mode	No	Yes	

Table 1.3	Differences between Functions (3/3) <sup>(1)</sup>
-----------	--

Note:

1. Refer to hardware manual for electrical characteristics and more details.



#### 1.2 Pin Characteristics

Table 1.4 lists Differences between Pin Characteristics.

Table 1.4	Differences between Pin Characteristics
	Differences between i in onarabteristios

M16C/62P	M16C/65	Changes from M16C/62P
P9_4 / TB4IN / DA1	P9_4 / TB4IN / DA1 / PWM1	Added: PWM1
P9_3 / TB3IN / DA0	P9_3 / TB3IN / DA0 / PWM0	Added: PWM0
P9_2 / TB2IN / SOUT3	P9_2 / TB2IN / SOUT3 / PMC0	Added: PMC0
P9_1 / TB1IN / SIN3	P9_1 / TB1IN / SIN3 / PMC1	Added: PMC1
P8_5 / NMI	P8_5 / NMI / SD / CEC	Added: SD/CEC
P8_1 / TA4IN / U	P8_1 / TA4IN / U / CTS5 / RTS5	Added: CTS5 / RTS5
P8_0 / TA4OUT / U	P8_0 / TA4OUT / U / RXD5 / SCL5	Added: RXD5/SCL5
P7_7 / TA3IN	P7_7 / TA3IN / CLK5	Added: CLK5
P7_6 / TA3OUT	P7_6 / TA3OUT / TXD5 / SDA5	Added: TXD5/SDA5
P7_1 / TA0IN / TB5IN / RXD2 / SCL2	P7_1 / TA0IN / TB5IN / RXD2 / SCL2 / SCLMM	Added: SCLMM
P7_0 / TA0OUT / TXD2 / SDA2	P7_0 / TA0OUT / TXD2 / SDA2 / SDAMM	Added: SDAMM
P6_0 / CTS0 / RTS0	P6_0 / CTS0 / RTS0 / RTCOUT	Added: RTCOUT
P4_7 / CS3	P4_7 / CS3 / PWM1 / TXD7 / SDA7	Added: PWM1/TXD7/SDA7
P4_6 / CS2	P4_6 / CS2 / PWM0 / RXD7 / SCL7	Added: PWM0/RXD7/SCL7
P4_5 / CS1	P4_5 / CS1 / CLK7	Added: CLK7
P4_4 / CS0	P4_4 / CS0 / CTS7 / RTS7	Added: CTS7 / RTS7
P2_5 / AN2_5 / A5 (/ D5 / D4)	P2_5 / INT7 / AN2_5 / A5, [A5 / D5], [A5 / D4]	Added: INT7
P2_4 / AN2_4 / A4 (/ D4 / D3)	P2_4 / INT6 / AN2_4 / A4, [A4 / D4], [A4 / D3]	Added: INT6
P1_7 / INT5 / D15	P1_7 / INT5 / D15 / IDU	Added: IDU
P1_6 / INT4 / D14	P1_6 / INT4 / D14 / IDW	Added: IDW
P1_5 / INT3 / D13	P1_5 / INT3 / D13 / IDV	Added: IDV
P1_3 / D11	P1_3 / D11 / TXD6 / SDA6	Added: TXD6 / SDA6
P1_2 / D10	P1_2 / D10 / RXD6 / SCL6	Added: RXD6 / SCL6
P1_1 / D9	P1_1 / D9 / CLK6	Added: CLK6
P1_0 / D8	P1_0 / D8 / CTS6 / RTS6	Added: CTS6 / RTS6



# 2. Detailed Comparison

#### 2.1 Differences between Protections

Table 2.1 lists Differences in Registers Associated with Protect Functions.

#### Table 2.1 Differences in Registers Associated with Protect Functions

Symbol	Add	ress	Bit	Differences		
Symbol	M16C/62P	M16C/65	Dit	M16C/62P	M16C/65	
	000Ah 000Ah		0	Protect bit 0 Enable write access to registers CM0, CM1, CM2, PLC0, and PCLKR	Protect bit 0 Enable write access to registers CM0, CM1, CM2, PLC0, PCLKR, and FRA0	
PRCR		000Ah	3	Protect bit 3 Enable write access to registers VCR2, and D4INT	Protect bit 3 Enable write access to registers VCR2, VWCE, VD1LS, VW0C, VW1C, and VW2C	
		6		Protect bit 6 Enable write access to the PRG2C register		

#### 2.2 Differences between Resets

Table 2.2 lists Differences between Resets and Table 2.3 lists Difference between Registers Associated with Resets.

Table 2.2	Differences between Resets	
-----------	----------------------------	--

Item	M16C/62P	M16C/65
Types of resets	Hardware reset Brown-out detection reset Oscillation stop detection reset Watchdog timer reset Software reset	Hardware reset Voltage monitor 0 reset Voltage monitor 1 reset Voltage monitor 2 reset Power-on reset Oscillation stop detection reset Watchdog timer reset Software reset
Cold start, warm start discrimination method	WDC5 bit in the WDC register	CWR bit in the RSTFR register
Reset Source Determine Register	No	Yes

#### Table 2.3 Difference between Registers Associated with Resets

Symbol	Address		Bit	Differences	
Symbol	M16C/62P	M16C/65	DIL	M16C/62P	M16C/65
RSTFR	—	0018h	_	_	M16C/65 only



# 2.3 Differences between Voltage Detectors

Table 2.4 lists Differences between Voltage Detectors and Table 2.5 lists Differences between Registers Associated with Voltage Detectors.

Table 2.4	Differences between Voltage Detectors
-----------	---------------------------------------

Item	M16C/62P	M16C/65
Voltage detection interrupt monitor level	Vdet4	<ul> <li>Vdet1 (voltage detection circuit 1)</li> <li>Vdet2 (voltage detection circuit 2)</li> </ul>
Voltage detection reset monitor level	Vdet3	<ul> <li>Vdet0 (voltage detection circuit 0)</li> <li>Vdet1 (voltage detection circuit 1)</li> <li>Vdet2 (voltage detection circuit 2)</li> </ul>

Refer to the hardware manual and electric characteristics on detection voltage.

Table 2.5	Differences between Registers Associated with Voltage Detectors
-----------	---

Symbol	Add	Address		Address		Difference	Differences	
Symbol	M16C/62P	M16C/65	Bit	M16C/62P	M16C/65			
		001Ah	5	Reserved bit	Voltage detector 0 enable bit 0: Voltage detector 0 disabled 1: Voltage detector 0 enabled			
VCR2 001Ah	6		Reset Level Monitor Bit 0 : Disable reset level detection circuit 1 : Enable reset level detection circuit	Voltage detector 1 enable bit 0: Voltage detector 1 disabled 1: Voltage detector 1 enabled				
	7		Low Voltage Monitor Bit 0 : Disable low voltage detection circuit 1 : Enable low voltage detection circuit	Voltage detector 2 enable bit 0: Voltage detector 2 disabled 1: Voltage detector 2 enabled				
VWCE	—	0026h		—	M16C/65 only			
VD1LS	—	0028h	_	—	M16C/65 only			
VW0C	—	002Ah	_	—	M16C/65 only			
VW1C	—	002Bh	—	—	M16C/65 only			
VW2C	—	002Ch	_	—	M16C/65 only			
D4INT	001Fh	—		M16C/62P only	—			



### 2.4 Differences between Clock Generators

Table 2.6 lists Differences between Clock Generators, and Table 2.7 to Table 2.8 list Differences between Registers Associated with Clock Generators.

 Table 2.6
 Differences between Clock Generators

Item	M16C/62P	M16C/65
Clock output function	Selectable from fC, f8, and f32	Selectable from fC, f8, f32, and f1
CPU clock after reset	Main clock divided by 8 (default setting of the CM21 bit: 0)	125 kHz on-chip oscillator clock divided by 8 (default setting of CM21 bit: 1)
Peripheral clock (fC)	Supply constantly	Provided or not provided can be selected by the PM25 bit
40 MHz on-chip oscillator	No	Yes
125 kHz on-chip oscillator	No	Yes
On-chip oscillator frequency	Approx. 1 MHz	Approx. 125 kHz, approx. 40 MHz
Calculation formula for PLL clock frequency	f(XIN) x n	f(XIN)/m x n

n: Multiply ratio set by bits PLC02 to PLC00 in the PLC0 register

m: Division ratio set by bits  $\mathsf{PLC05}$  to  $\mathsf{PLC04}$  in the  $\mathsf{PLC0}$  register

Table 2.7 Differences between Registers Associated with Clock Gene	erators (1/2)
--	---------------

Symbol	Address		Bit	Differences		
Symbol	M16C/62P	M16C/65	DIL	M16C/62P	M16C/65	
			3	Reserved bits	<ul><li>XIN-XOUT feedback resistor select bit</li><li>0 : Internal feedback resistor connected</li><li>1 : Internal feedback resistor not connected</li></ul>	
CM1	11 0007h 0007h		4		125 kHz on-chip oscillator oscillation stop bit 0: 125 kHz on-chip oscillator on 1: 125 kHz on-chip oscillator off	
				Different address		
PCLKR	025Eh	0012h	5	Reserved bit	Clock output function extension bit (valid in single-chip mode) 0: Selected by bits CM01 to CM00 in the CM0 register 1: Output f1	
PLC0 001Ch		1Ch 001Ch	4	Reserved bit Set to 1.	Reference frequency counter set bit 00: No division	
			5	Reserved bit	01: Divide-by-2 10: Divide-by-4 11: Do not set	



	Symbol Address M16C/62P M16C/65		D'1	Differences		
Symbol			Bit	M16C/62P M16C/65		
			0	Specifying wait when accessing SFR at PLL operation 0 : 2 waits 1 : 1 wait	Reserved bit Set to 1.	
PM2	W2 001Eh 001Eh	001Eh	2 001Eh	<ul> <li>WDT count source protect bit</li> <li>CPU clock is used for the watchdog timer count source</li> <li>On-chip oscillator clock is used for the watchdog timer count source</li> </ul>	No register bit	
	4	4	Reserved bit	NMI interrupt enable bit           0: <u>NMI</u> interrupt disabled           1: NMI interrupt enabled		
		5	5	No register bit	Peripheral clock fC provide bit 0: Not provided 1: Provided	
FRA0	_	0022h	_		M16C/65 only	

Table 2.8	Differences between Registers Associated with Clock Generators (2	2/2)
-----------	---	------

# 2.5 Differences between Power Controls

Table 2.9 lists Differences between Power Controls and Table 2.10 lists Difference between Registers Associated with Power Controls.

Table 2.9	Differences between Power Controls
-----------	------------------------------------

Item	M16C/62P	M16C/65	
Slow read mode	No	Yes	
Low current consumption read mode	No	Yes	

#### Table 2.10 Difference between Registers Associated with Power Controls

Symbol	Address		Bit	Differences	
Symbol	M16C/62P	M16C/65	Dit	M16C/62P	M16C/65
FMR2	—	0222h	_	—	M16C/65 only

#### 2.6 Differences between Processor Modes

Table 2.11 lists Differences between Registers Associated with Processor Modes.

#### Table 2.11 Differences between Registers Associated with Processor Modes

Symbol	Address		Bit	Differences		
Symbol	M16C/62P	M16C/65	DIL	M16C/62P	M16C/65	
PM1	0005h	0005h		CS2 area switch bit 0: 08000h to 26FFFh (block A disabled) 1: 10000h to 26FFFh (block A enabled)	CS2 area switch bit 0: CS2 area (0E000h to 0FFFFh) 1: Data flash (0E000h to 0FFFFh)	
PRG2C	_	0010h			M16C/65 only	



### 2.7 Differences in Bus

Table 2.12 lists Differences between Buses and Table 2.13 lists Differences between Registers Associated with Buses.

Item	M16C/62P	M16C/65
External area wait	Selectable from 0 to 3 wait(s) CSiW bit in the CSR register, Selected by bits CSEi0W and CSEi1W in the CSE register (i = 0 to 3)	Selectable from 0 to 8 wait(s) Selected by CSiW bit in the CSR register, bits CSEi0W and CSEi1W in the CSE register, and bits EWCi0 to EWCi1 in the EWC register
Recovery cycle	No	Selectable from 0 to 3 cycle(s) Selectable by bits EWR0 to EWR1 in the EWR register

#### Table 2.12 Differences between Buses

#### Table 2.13 Differences between Registers Associated with Buses

Symbol	Address		Bit	Differences	
Symbol	M16C/62P	M16C/65	DIL	M16C/62P	M16C/65
		-	1 - 0	CS0 wait expansion bit <sup>b1 b0</sup> 1 1: Do not set	CS0 wait expansion bit b1 b0 1 1: Selected by bits EWC01 and EWC00 in the EWC register
CSE	001Bh		3 -2	CS1 wait expansion bit <sup>b3 b2</sup> 1 1: Do not set	CS1 wait expansion bit <sup>b3 b2</sup> 1 1: Selected by bits EWC11 and EWC10 in the EWC register
USE			5 - 4	CS2 wait expansion bit <sup>b5 b4</sup> 1 1: Do not set	CS2 wait expansion bit <sup>b5 b4</sup> 1 1: Selected by bits EWC21 and EWC20 in the EWC register
			7 - 6	CS3 wait expansion bit <sup>b7 b6</sup> 1 1: Do not set	CS3 wait expansion bit <sup>b7 b6</sup> 1 1: Selected by bits EWC31 and EWC30 in the EWC register
EWC	_	0011h			M16C/65 only
EWR	_	0009h		—	M16C/65 only



# 2.8 Differences between Programmable I/O Ports

Table 2.14 lists Difference between Programmable I/O Ports and Table 2.15 lists Differences between Registers Associated with Programmable I/O Ports.

Table 2.14	Difference between Programmable I/O Ports
------------	---

Item	M16C/62P	M16C/65
NMI / SD digital filter	INO	Use or non-use of digital filter can be selectable by the NMIDF register

#### Table 2.15 Differences between Registers Associated with Programmable I/O Ports

Sumbol	Address		Bit	Differences	
Symbol	M16C/62P	M16C/65	ы	M16C/62P	M16C/65
PD8	03F2h	03F2h	5	No register bit	Port P8_5 direction bit 0 : Input mode (Functions as an input port) 1 : Output mode (Functions as an output port)
PUR0	03FCh	0360h	—	Differen	t address
PUR1	03FDh	0361h	—	Different address	
PUR2	03FEh	0362h	—	Different address	
		03FFh 0366h	-	Differen	t address
			3	No register bit	Reserved bit
PCR	03FFh		4	No register bit	CEC output enable bit
FUR	03661	030011	5	No register bit	INT6 input enable bit
			6	No register bit	INT7 input enable bit
			7	No register bit	Key input enable bit
NMIDF	_	0369h	_	—	M16C/65 only



# 2.9 Differences between Interrupts

Table 2.16 lists Difference between Interrupts and Table 2.17 to Table 2.18 list Differences in Interrupt Vectors, and Table 2.19 lists Differences between Registers Associated with Interrupts.

Table 2.16	Difference	between	Interrupts
	Dilloronoo	8000000	micori apto

Item	M16C/62P	M16C/65
NMI enable function	I Enable only	Enable or disable is selectable by the PM24 bit in the PM2 register

Table 2.17 Diffe	rences between	Interrupt Vector	<sup>.</sup> s - (1/2)
------------------	----------------	------------------	------------------------

Software Interrupt Number	Vector Address	M16C/62P	M16C/65
0	+0 to +3 (0000h to 0003h)	BRK instruction	BRK instruction
1	+4 to +7 (0004h to 0007h)	— (Reserved)	INT instruction interrupt
2	+8 to +11 (0008h to 000Bh)		INT7
3	+12 to +15 (000Ch to 000Fh)		INT6
4	+16 to +19 (0010h to 0013h)	INT3	INT3
5	+20 to +23 (0014h to 0017h)	Timer B5	Timer B5
6	+24 to +27 (0018h to 001Bh)	Timer B4, UART1 start/stop condition detection, bus collision detection	Timer B4, UART1 start/stop condition detection, bus collision detection
7	+28 to +31 (001Ch to 001Fh)	Timer B3, UART0 start/stop condition detection, bus collision detection	Timer B3, UART0 start/stop condition detection, bus collision detection
8	+32 to +35 (0020h to 0023h)	SI/O4, INT5	SI/O4, INT5
9	+36 to +39 (0024h to 0027h)	SI/O3, INT4	SI/O3, INT4
10	+40 to +43 (0028h to 002Bh)	UART2 start/stop condition detection, bus collision detection	UART2 start/stop condition detection, bus collision detection
11	+44 to +47 (002Ch to 002Fh)	DMA0	DMA0
12	+48 to +51 (0030h to 0033h)	DMA1	DMA1
13	+52 to +55 (0034h to 0037h)	Key input interrupt	Key input interrupt
14	+56 to +59 (0038h to 003Bh)	A/D converter	A/D converter
15	+60 to +63 (003Ch to 003Fh)	UART2 transmit, NACK2	UART2 transmit, NACK2
16	+64 to +67 (0040h to 0043h)	UART2 receive, ACK2	UART2 receive, ACK2
17	+68 to +71 (0044h to 0047h)	UART0 transmit, NACK0	UART0 transmit, NACK0
18	+72 to +75 (0048h to 004Bh)	UART0 receive, ACK0	UART0 receive, ACK0
19	+76 to +79 (004Ch to 004Fh)	UART1 transmit, NACK1	UART1 transmit, NACK1
20	+80 to +83 (0050h to 0053h)	UART1 receive, ACK1	UART1 receive, ACK1
21	+84 to +87 (0054h to 0057h)	Timer A0	Timer A0
22	+88 to +91 (0058h to 005Bh)	Timer A1	Timer A1
23	+92 to +95 (005Ch to 005Fh)	Timer A2	Timer A2
24	+96 to +99 (0060h to 0063h)	Timer A3	Timer A3
25	+100 to +103 (0064h to 0067h)	Timer A4	Timer A4
26	+104 to +107 (0068h to 006Bh)	Timer B0	Timer B0
27	+108 to +111 (006Ch to 006Fh)	Timer B1	Timer B1
28	+112 to +115 (0070h to 0073h)	Timer B2	Timer B2



Software Interrupt Number	Vector Address	M16C/62P	M16C/65
29	+116 to +119 (0074h to 0077h)	INT0	INTO
30	+120 to +123 (0078h to 007Bh)	INT1	INT1
31	+124 to +127 (007Ch to 007Fh)	INT2	INT2
32 to 40	+128 to +131 (0080h to 0083h) to +160 to +163 (00A0h to 00A3h)		INT instruction interrupt
41	+164 to +167 (00A4h to 00A7h)		DMA2
42	+168 to +171 (00A8h to 00ABh)		DMA3
43	+172 to +175 (00ACh to 00AFh)		UART5 start/stop condition detection, bus collision detection, CEC1
44	+176 to +179 (00B0h to 00B3h)		UART5 transmit, NACK5, CEC2
45	+180 to +183 (00B4h to 00B7h)		UART5 receive, ACK5
46	+184 to +187 (00B8h to 00BBh)		UART6 start/stop condition detection, bus collision detection, real-time clock period
47	+188 to +191 (00BCh to 00BFh)		UART6 transmit, NACK6, real-time clock compare
48	+192 to +195 (00C0h to 00C3h)	INT instruction interrupt	UART6 receive, ACK6
49	+196 to +199 (00C4h to 00C7h)		UART7 start/stop condition detection, bus collision detection, remote control 0
50	+200 to +203 (00C8h to 00CBh)		UART7 transmit, NACK7, remote control 1
51	+204 to +207 (00CCh to 00CFh)	-	UART7 receive, ACK7
52 to 58	+208 to +211 (00D0h to 00D3h) to +232 to +235 (00E8h to 00EBh)		INT instruction interrupt
59	+236 to +239 (00ECh to 00EFh)	1	I <sup>2</sup> C-bus interface interrupt
60	+240 to +243 (00F0h to 00F3h)	1	SCL/SDA interrupt
61 to 63	+244 to +247 (00F4h to 00F7h) to +252 to +255 (00FCh to 00FFh)		INT instruction interrupt

 Table 2.18
 Differences between Interrupt Vectors - (2/2)



O week al	Addı	ress	Dit	Differences		
Symbol	M16C/62P	M16C/65	Bit	M16C/62P	M16C/65	
IFSR3A	—	0205h		—	M16C/65 only	
				Different address		
			2	No register bit	Interrupt request source select bit 0: Not used 1: I <sup>2</sup> C-bus interface	
			3	No register bit	Interrupt request source select bit 0: Not used 1: SCL/SDA	
	035Eh	035Eh 0206h	4	No register bit	Interrupt request source select bit 0: UART7 start/stop condition detection, bus collision detection 1: Remote control receiving function 0	
IFSR2A			5	No register bit	Interrupt request source select bit 0: UART7 transmission, NACK 1: Remote control receiving function 1	
			6	Interrupt request factor select bit 0: Timer B3 1: UART0 bus collision detection	Interrupt request source select bit 0: Timer B3 1: UART0 start/stop condition detection, bus collision detection	
			7	Interrupt request factor select bit 0: Timer B4 1: UART1 bus collision detection	Interrupt request source select bit 0: Timer B4 1: UART1 start/stop condition detection, bus collision detection	
IFSR	035Fh	0207h	_	Differen	t address	
AIER	0009h	020Eh		Differen	t address	
AIER2	01BBh	020Fh	—	Differen	t address	
RMAD0	0010h to 0012h	0210h to 0212h	—	Differen	t address	
RMAD1	0014h to 0016h	0214h to 0216h	_	Different address		
RMAD2	01B8h to 01BAh	0218h to 021Ah	_	Different address		
RMAD3	01BCh to 01BEh	021Ch to 021Eh	_	Different address		

### Table 2.19 Differences between Registers Associated with Interrupts

# 2.10 Differences in Watchdog Timers

Table 2.20 lists Differences between Watchdog Timers and Table 2.21 lists Differences in Registers Associated with Watchdog Timer.

Item	M16C/62P	M16C/65
Count source protect mode enable setting	Set the PM22 bit to 1.	Set the CSPRO bit to 1. <sup>(1)</sup>
Watchdog timer cycle in count source protection mode	Approx. 32.8 ms (32768 / approx. 1 MHz)	Approx. 32.8 ms (4096 / approx. 125 kHz)
Watchdog timer counter refresh	Watchdog timer counter is initialized and starts	Write 00h, and then FFh to the WDTR register
Count start conditions	Watchdog timer counter is initialized and starts counting by writing to the WDTS register.	Count automatically starts after reset by setting the WDTON bit in the OFS1 address to 0. Count starts by writing to the WDTS register.

#### Table 2.20 Differences between Watchdog Timers

Note:

1. When the CSPROINI bit in the OFS1 address is 0, the value after reset becomes 1.

Table 2.21	Differences in Registers Associated with Watchdog Timers
	Billoronood in Registoro Accoolatoa man Matemacy miloro

Sumbol	Address		Bit	Differences			
Symbol	M16C/62P M16C/65		DIL	M16C/62P	M16C/65		
WDTS	000Eh	037Eh		Different address			
			—			Different address	
WDC	000Fh	037Fh	5	Cold Start / Warm Start Discrimination Flag 0 : Cold Start 1 : Warm Start	No register bit		
VW2C	—	002Ch	_	—	M16C/65 only		
CSPR	_	037Ch	_	—	M16C/65 only		
WDTR	—	037Dh	—	—	M16C/65 only		



### 2.11 Differences between DMACs

Table 2.22 lists Difference between DMACs, Table 2.23 to 2.24 list Differences in DMA Request Sources, and Table 2.25 lists Differences between Registers Associated with DMACs.


Table 2.22 Difference between DMACs	Table 2.22	Difference between DMACs
-------------------------------------	------------	--------------------------

Item	M16C/62P	M16C/65
Number of channels	2 channels	4 channels

# Table 2.23Differences between DMAi Request Sources (i=0 and 1 in M16C/62P; i=0 to 3 in<br/>M16C/65)(1/2)

DSEL4 to	M16C/6	32P	M16C/	/65
DSEL0	DMS = 0	DMS = 1	DMS = 0	DMS = 1
00000b	Falling edge of INTi pin	—	Falling edge of INTi pin	—
00001b	Software trigger	_	Software trigger	_
00010b	Timer A0	—	Timer A0	—
00011b	Timer A1	—	Timer A1	—
00100b	Timer A2	—	Timer A2	—
00101b	Timer A3	SI/O3 (DMA1 only)	Timer A3	SI/O3 (DMA1, DMA3 only)
00110b	Timer A4	DMA0: Both edges of INTi pin DMA1: SI/O4	Timer A4	DMA0, DMA2: Both edges of INTi pin DMA1, DMA3: SI/O4
00111b	Timer B0	DMA0, DMA2: Timer B3 DMA1, DMA3: Both edges of INTi pin	Timer B0	DMA0, DMA2: Timer B3 DMA1,DMA3: Both edges of INTi pin
01000b	Timer B1	Timer B4 (DMA0 only)	Timer B1	Timer B4 (DMA0, DMA2 only)
01001b	Timer B2	Timer B5 (DMA0 only)	Timer B2	Timer B5 (DMA0, DMA2 only)
01010b	UART0 transmission	—	UART0 transmission	—
01011b	DMA0: UART0 reception DMA1: UART0 reception / ACK0	_	DMA0, DMA2: UART0 reception DMA1, DMA3: UART0 reception / ACK0	_
01100b	UART2 transmission	—	UART2 transmission	—
01101b	DMA0: UART2 reception DMA1: UART2 reception / ACK2	_	DMA0, DMA2: UART2 reception DMA1, DMA3: UART2 reception / ACK2	_
01110b	A/D converter	_	A/D converter	—
01111b	DMA0: UART1 transmission DMA1: UART1 reception / ACK1	_	DMA0, DMA2: UART1 transmission DMA1, DMA3: UART1 reception / ACK1	_





# Table 2.24Differences between DMAi Request Sources (i=0 and 1 in M16C/62P; i=0 to 3 in<br/>M16C/65)(2/2)

Table 2.25	Differences between Registers Associated with DMACs
------------	---

Symbol	Address		Bits	Differ	ences
Symbol	M16C/62P	M16C/65	DIIS	M16C/62P	M16C/65
DAR0	0024h to 0026h	0184h to 0186h		Different	address
DAR1	0034h to 0036h	0194h to 0196h		Different	address
DAR2	_	01A4h to 01A6h			M16C/65 only
DAR3	—	01B4h to 01B6h		—	M16C/65 only
DM0CON	002Ch	018Ch		Different	address
DM1CON	003Ch	019Ch	_	Different	address
DM2CON	—	01ACh	_	—	M16C/65 only
DM3CON	—	01BCh	_	—	M16C/65 only
SAR0	0020h to 0022h	0180h to 0182h	_	Different address	
SAR1	0030h to 0032h	0190h to 0192h	_	Different address	
SAR2	—	01A0h to 01A2h	_	—	M16C/65 only
SAR3	—	01B0h to 01B2h	_	—	M16C/65 only
TCR0	0028h to 0029h	0188h to 0189h		Different address	
TCR1	0038h to 0039h	0198h to 0199h	—	Different	address
TCR2	—	01A8h to 01A9h	_	—	M16C/65 only
TCR3	_	01B8h to 01B9h	_	—	M16C/65 only
DM0SL	03B8h	0398h	_	Different address	
DM1SL	03BAh	039Ah	_	Different address	
DM2SL		0390h		—	M16C/65 only
DM3SL		0392h	_		M16C/65 only



## 2.12 Differences in Timers

Table 2.26 lists Differences between Timers, and Table 2.27 to Table 2.28 list Differences in Registers Associated with Timers.

Item	M16C/62P	M16C/65
Count source	f1, f2, f8, f32, fC32	f1TIMAB, f2TIMAB, f8TIMAB, f32TIMAB, f64TIMAB, f0CO-S, f0CO-F, fC32
Output polarity inversion function	No	Yes
Clock select prior to timer AB division	No	Selectable from f1 and fOCO-F
Programmable output mode	No	Yes
Count direction (up/down) selected by the TAiOUT pin (i = 0 to 4)	Yes	No
Default value in pulse period/pulse width measurement modes	Undefined	Programmable
Read from timer register when in pulse period/pulse width measurement modes	Contents of the reload register (measurement result) can be read by reading the TBj register (j = 0 to 5).	<ul> <li>When bits PPWFSk2 to PPWFSk0 in the PPWFSk register (k = 1 and 2) are 0:</li> <li>Contents of the reload register (measurement result) can be read by reading the TBj register.</li> <li>When bits PPWFSk2 to PPWFSk0 in the PPWFSk register are 1:</li> <li>Contents of the counter (counter value) can be read by reading the TBj register</li> <li>Contents of the reload register (measurement result) can be read by reading the TBj1 register</li> </ul>
Write to timer register when in pulse period/pulse width measurement modes	The value written to the TBj register is not written to neither the reload register nor the counter.	When a value is written to the TBj register while the counter stops, the value is written to both the reload register and the counter.
Overflow flag clear method	Wait one or more count source cycles after the MR3 bit becomes 1 (overflow) while the TBjS bit is 1 (start counting), then write a value to the TBjMR register.	Write a value to the TBjMR register

 Table 2.26
 Differences between Timers



	bbA	Address		Differ	ences	
Symbol	M16C/62P	M16C/65	Bits	M16C/62P	M16C/65	
			2 - 0		TAi count source select bit ( $i = 0, 2,$ and 4) Select the TAi count source	
TACS0 to		01D0h to	01D0h to	3		<ul> <li>TAi count source option specified bit</li> <li>0: TCK0 to TCK1 enabled, TCS0 to TCS2 disabled</li> <li>1: TCK0 to TCK1 disabled, TCS0 to TCS2 enabled</li> </ul>
TACS2	_	01D2h	6 - 4	_	TAj count source select bit (j = 1 and 3) Select the TAj count source	
			7	_	TAj count source option specified bit 0: TCK0 to TCK1 enabled, TCS4 to TCS6 disabled 1: TCK0 to TCK1 disabled, TCS4 to TCS6 enabled	
TAOMR			—	Different	taddress	
to TA4MR	0396h to 039Ah	0336h to 033Ah	4	Up/Down switching factor select bit 0: UDF register 1: Input signal to TAiOUT pin	_	
TA0	0386h to 0387h	0326h to 0327h	_	Different address		
TA1	0388h to 0389h	0328h to 0329h	—	Different address		
TA2	038Ah to 038Bh	032Ah to 032Bh		Different address		
TA3	038Ch to 038Dh	032Ch to 032Dh	_	Different address		
TA4	038Eh to 038Fh	032Eh to 032Fh	—	Different address		
TABSR	0380h	0320h	—	Different	address	
UDF	0384h	0324h	_	Different	address	
ONSF	0382h	0322h	—	Different	address	
TRGSR	0383h	0323h	_	Different	address	
CPSRF	0381h	0015h	—	Different	address	
TCKDIVC0	_	01CBh	_	—	M16C/65 only	
PWMFS		01D4h		—	M16C/65 only	
TAPOFS	_	01D5h		—	M16C/65 only	
TAOW	_	01D8h	—		M16C/65 only	
TA11	0342h to	0302h to		Different	address	
	0343h	0303h	—	—	Used in programmable output mode	
TA21	0344h to	0304h to		Different	address	
.,	0345h	0305h	_	Used in programmable output m		
TA41	0346h to	0306h to		Different	address	
	0347h	0347h 0307h	—		Used in programmable output mode	

 Table 2.27
 Differences between Registers Associated with Timers (1/2)

Oursels at	Address		Bit		erences
Symbol	M16C/62P	M16C/65	BI	M16C/62P	M16C/65
			2 - 0	_	TBi count source select bit (i = 0, 2, 3, and 5) Select the TBi count source
TBCS0 TBCS1		01C8h 01C9h	3	_	TBi count source option specified bit 0: TCK0 to TCK1 enabled, TCS0 to TCS2 disabled 1: TCK0 to TCK1 disabled, TCS0 to TCS2 enabled
TBCS2 TBCS3		01E8h 01E9h	6 - 4	_	TBj count source select bit (j = 1 and 4) Select the TBj count source
		7	_	TBj count source option specified bit 0: TCK0 to TCK1 enabled, TCS4 to TCS6 disabled 1: TCK0 to TCK1 disabled, TCS4 to TCS6 enabled	
TB0MR to TB2MR	039Bh to 039Dh	033Bh to 033Dh		Different address	
TB3MR to TB5MR	035Bh to 035Dh	031Bh to 031Dh	—	Different address	
TB0	0390h to 0391h	0330h to 0331h	_	Differer	nt address
TB1	0392h to 0393h	0332h to 0333h		Differer	nt address
TB2	0394h to 0395h	0334h to 0335h		Differer	nt address
TB3	0350h to 0351h	0310h to 0311h		Differer	nt address
TB4	0352h to 0353h	0312h to 0313h		Differer	nt address
TB5	0354h to 0355h	0314h to 0315h		Differer	nt address
TBSR	0340h	0300h		Differer	nt address
TABSR	0380h	0320h		Differer	nt address
PPWFS1		01C6h		_	M16C/65 only
PPWFS2		01E6h	—	_	M16C/65 only
TB01	_	01C0h to 01C1h	_	_	M16C/65 only
TB11	_	01C2h to 01C3h	_	_	M16C/65 only
TB21	_	01C4h to 01C5h	_	_	M16C/65 only
TB31	—	01E0h to 01E1h	—	—	M16C/65 only
TB41	—	01E2h to 01E3h	—	—	M16C/65 only
TB51	—	01E4h to 01E5h	—	—	M16C/65 only

Table 2.28	Differences between Registers Associated with Timers (2/2)
------------	--

#### 2.13 Differences between Three-phase Motor Control Timer Functions

Table 2.29 lists Differences between Three-phase Motor Control Timer Functions and Table 2.30 lists Differences between Registers Associated with Three-phase Motor Control Timer Functions.

Item	M16C/62P	M16C/65		
Count source	f1, f2, f8, f32, fC32	f1TIMAB, f2TIMAB, f8TIMAB, f32TIMAB, f64TIMAB, f0CO-S, f0CO-F, fC32		
Position data retain function	No	Yes		
Three-phase PWM output pin select function	No	Yes		

#### Table 2.29 Differences between Three-phase Motor Control Timer Functions

# Table 2.30Differences between Registers Associated with Three-phase Motor Control Timer<br/>Functions

Symbol	Address		Bit	Differe	ences
Symbol	M16C/62P	M16C/65	DIL	M16C/62P	M16C/65
DTT	034Ch	030Ch	—	Different	address
ICTB2	034Dh	030Dh	_	Different	address
IDB0	034Ah	030Ah	—	Different	address
IDB1	034Bh	030Bh	_	Different	address
INVC0	0348h	0308h	_	Different	address
INVC1	0349h	0309h	—	Different	address
TA1	0388h to 0389h	0328h to 0329h	—	Different address	
TA2	038Ah to 038Bh	032Ah to 032Bh	_	Different address	
TA4	038Eh to 038Fh	032Eh to 032Fh	—	Different address	
TA11	0342h to 0343h	0302h to 0303h	—	Different address	
TA21	0344h to 0345h	0304h to 0305h	_	Different address	
TA41	0346h to 0347h	0306h to 0307h	—	Different	address
TB2SC	039Eh	033Eh	—	Different	address
TB2	0394h to 0395h	0334h to 0335h	_	Different	address
TRGSR	0383h	0323h	—	Different address	
TABSR	0380h	0320h	—	Different address	
PDRF	—	030Eh	_	—	M16C/65 only
PFCR		0318h		— M16C/65 only	
TPRC		01DAh	_	_	M16C/65 only



### 2.14 Differences between Serial Interfaces

Table 2.31 lists Differences between Serial Interfaces, and Table 2.32 to Table 2.33 list Differences in Registers Associated with Serial Interface.

Item		M16C/62P	M16C/65	
Clock sy	nchronous/asynchronous			
I <sup>2</sup> C mod	е	2 shappels (LIAPTO to LIAPT2)	6 observels (UAPTO to 2, UAPTE to 7)	
Special mode 2 IE mode		3 channels (UART0 to UART2)	6 channels (UART0 to 2, UART5 to 7)	
	o UART2, UART5 to UART7 or to division select function	f1 only	Selectable from f1 and fOCO-F	
SI/O3,4	Output control after transmission	The state of pins SOUT3 and SOUT4 after transmission is high-impedance.	The state after transmission can be selected whether to set high-impedance or retain the last bit level, by bits SM27 and SM26 in the S34C2 register.	
	SI/O prior to division clock	f1 only Selectable from f1 and fOCO-F		

#### Table 2.31 Differences between Serial Interfaces



Address		ress		Differences		
Symbol	M16C/62P	M16C/65	Bit	M16C/62P	M16C/65	
U0BRG	03A1h	0249h	_	Different	address	
U0C0	03A4h	024Ch		Different	address	
U0C1	03A5h	024Dh	_	Different	address	
U0MR	03A0h	0248h		Different	address	
U0RB	03A6h to 03A7h	024Eh to 024Fh		Different	address	
	00054	00.475		Different	address	
U0SMR	036Fh	0247h	3	LSYN <sup>(1)</sup>	Reserved bit	
U0SMR2	036Eh	0246h		Different	address	
U0SMR3	036Dh	0245h		Different	address	
U0SMR4	036Ch	0244h		Different	address	
U0TB	03A2h to 03A3h	024Ah to 024Bh		Different	address	
UCON	03B0h	0250h	_	Different	address	
UCLKSEL0	—	0252h		—	M16C/65 only	
U1BRG	03A9h	0259h		Different	address	
U1C0	03ACh	025Ch	_	Different address		
U1C1	03ADh	025Dh	_	Different address		
U1MR	03A8h	0258h		Different address		
U1RB	03AEh to 03AFh	025Eh to 025Fh		Different address		
	00705	0057h	_	Different address		
U1SMR	0373h	0257h	3	LSYN <sup>(1)</sup>	Reserved bit	
U1SMR2	0372h	0256h	_	Different	address	
U1SMR3	0371h	0255h	_	Different	address	
U1SMR4	0370h	0254h	_	Different	address	
U1TB	03AAh to 03ABh	025Ah to 025Bh		Different	address	
U2BRG	0379h	0269h	_	Different	address	
U2C0	037Ch	026Ch	_	Different	address	
U2C1	037Dh	026Dh	—	Different	address	
U2MR	0378h	0268h	_	Different	address	
U2RB	037Eh to 037Fh	026Eh to 026Fh	—	Different	address	
	00774	02075	_	Different	address	
U2SMR	0377h	0267h	3	LSYN <sup>(1)</sup>	Reserved bit	
U2SMR2	0376h	0266h	_	Different	address	
U2SMR3	0375h	0265h		Different	address	
U2SMR4	0374h	0264h		Different	address	
U2TB	037Ah to 037Bh	026Ah to 026Bh	_	Different	address	

#### Table 2.32 Differences between Registers Associated with Serial Interfaces (1/2)

Note:

1. Only enabled in M3062LFGPFP and M3062LFGPGP. This is a reserved bit in other products.

Question	Ade	dress	Dit	Differences		
Symbol	M16C/62P M16C/65		Bit	M16C/62P	M16C/65	
U5BRG		0289h		_	M16C/65 only	
U5C0		028Ch		—	M16C/65 only	
U5C1		028Dh		_	M16C/65 only	
U5MR		0288h			M16C/65 only	
U5RB		028Eh to 028Fh			M16C/65 only	
U5SMR		0287h			M16C/65 only	
U5SMR2		0286h			M16C/65 only	
U5SMR3		0285h		_	M16C/65 only	
U5SMR4		0284h		_	M16C/65 only	
U5TB		028Ah to 028Bh			M16C/65 only	
U6BRG		0299h			M16C/65 only	
U6C0		029Ch			M16C/65 only	
U6C1		029Dh			M16C/65 only	
U6MR		0298h		_	M16C/65 only	
U6RB		029Eh to 029Fh		_	M16C/65 only	
U6SMR		0297h			M16C/65 only	
U6SMR2		0296h		_	M16C/65 only	
U6SMR3		0295h		—	M16C/65 only	
U6SMR4		0294h		—	M16C/65 only	
U6TB		029Ah to 029Bh		_	M16C/65 only	
U7BRG		02A9h		—	M16C/65 only	
U7C0		02ACh	_	—	M16C/65 only	
U7C1	_	02ADh	_	_	M16C/65 only	
U7MR		02A8h	_	—	M16C/65 only	
U7RB	—	02AEh to 02AFh	_	—	M16C/65 only	
U7SMR	—	02A7h	_	—	M16C/65 only	
U7SMR2	—	02A6h		_	M16C/65 only	
U7SMR3	—	02A5h		—	M16C/65 only	
U7SMR4	—	02A4h		—	M16C/65 only	
U7TB	—	02AAh to 02ABh	_	—	M16C/65 only	
S3C	0362h	0272h		Different	address	
S4C	0366h	0276h	_	Different	address	
S3BRG	0363h	0273h	_	Different	address	
S4BRG	0367h	0277h	_	Different address		
S3TRR	0360h	0270h	_	Different	address	
S4TRR	0364h	0274h	_	Different	address	
S34C2		0278h	—	_	M16C/65 only	

 Table 2.33
 Differences in Registers Associated with Serial Interfaces (2/2)



#### 2.15 Differences between A/D Converters

Table 2.34 lists Differences between A/D Converters and Table 2.35 lists Differences in Registers Associated with A/D Converters.

Item	M16C/62P	M16C/65
Operation clock $\phi$ AD	fAD, fAD divided by 2, fAD divided by 3, fAD divided by 4, fAD divided by 6, and fAD divided by 12	f1, f1 divided by 2, f1 divided by 3, f1 divided by 4, f1 divided by 6, f1 divided by 12, fOCO40M divided by 2, fOCO40M divided by 3, fOCO40M divided by 4, fOCO40M divided by 6, and fOCO40M divided by 12
Conversion rate per pin	Without sample and hold 8-bit resolution: 49 \overline{AD} cycles 10-bit resolution: 59 \overline{AD} cycles With sample and hold 8-bit resolution: 28 \overline{AD} cycles 10-bit resolution: 33 \overline{AD} cycles	Minimum 43 ¢AD cycles
External op-amp connection mode	Yes	No
Resolution	8-bit/10-bit (selectable)	10-bit
Sample and hold	Yes/No (selectable)	Yes
fAD	f1 only	Selectable from f1 and fOCO40M
Open-circuit detection assist function	No	Yes

#### Table 2.34 Differences between A/D Converters

#### Table 2.35 Differences in Registers Associated with A/D Converters

Symbol	Add	ress	Bit	Differ	ences
Symbol	M16C/62P	M16C/65	ы	M16C/62P	M16C/65
			3	8/10-Bit Mode Select Bit 0: 8-bit mode 1: 10-bit mode	No register bit
			5	Vref Connect Bit 0: Vref not connected 1: Vref connected	A/D standby bit 0: A/D operation stopped (standby) 1: A/D operation enabled
ADCON1	03D7h	03D7h	7-6	External Op-Amp Connection Mode Bit 0 0: ANEX0 and ANEX1 are not used 0 1: ANEX0 input is A/D converted 1 0: ANEX1 input is A/D converted 1 1: External op-amp connection mode	Extended pin select bit 0 0: ANEX0 and ANEX1 are not used 0 1: ANEX0 input is A/D converted 1 0: ANEX1 input is A/D converted 1 1: Do not set
ADCON2	03D4h	03D4h	0	A/D Conversion Method Select Bit 0: Without sample and hold function 1: With sample and hold function	No register bit
	000411	000411	7	No register bit	fAD select bit 0: f1 1: fOCO40M
AINRST	_	03A2h	—	<u> </u>	M16C/65 only



#### 2.16 **Differences between CRC Calculators**

Table 2.36 lists Differences between CRC Calculators and Table 2.37 lists Differences between Registers Associated with CRC Calculators.

Item	M16C/62P	M16C/65						
CRC generator polynomial	CRC-CCITT (X <sup>16</sup> + X <sup>12</sup> + X <sup>5</sup> + 1)	CRC-CCITT (X <sup>16</sup> + X <sup>12</sup> + X <sup>5</sup> + 1) or CRC-16 (X <sup>16</sup> + X <sup>15</sup> + X <sup>2</sup> + 1)						
MSB/LSB selection	No	MSB/LSB (selectable)						
CRC snoop	No	Yes						

#### Table 2.36 **Differences between CRC Calculators**

Table 2.37	Differences between Registers Associated with CRC Calculators
------------	---

Symbol	Add	ress	Bit	Differences	
Symbol	M16C/62P	16C/62P M16C/65		M16C/62P	M16C/65
CRCMR	—	03B6h	_	—	M16C/65 only
CRCSAR		03B4h to 03B5h		—	M16C/65 only

#### 2.17 **Differences between Flash Memories**

Table 2.38 lists Differences between Flash Memories and Table 2.39 lists Differences between Software Commands, and 2.40 lists Differences between Registers Associated with Flash Memories.

Yes

20 years

Table 2.38 Differences	between Flash Memories	
Item	M16C/62P	M16C/65
Program method	1-word units (16-bit)	2-word units (32-bit)
Number of programs and erase cycles	100 times (all areas) or 1,000 times (all blocks other than block A and block 1 in user ROM area)/10,000 times (block A, block 1)	1,000 times (program ROM 1, program ROM 2)/10,000 times (data flash)
User boot function	No	Yes

No

10 years

Forced erase function

Data retention



Software	MOLL	First Bus	s Cycle	Second B	us Cycle	Third Bus Cycle	
Command	MCU	Address	Data	Address	Data	Address	Data
	M16C/62P	Х	XXFFh	_	—		—
Read array	M16C/65 <sup>(1)</sup>	Х	XXFFh	-	—	—	—
	M16C/65 <sup>(2)</sup>	B0-7	XXFFh	B8	XXFFh	_	_
	M16C/62P	Х	XX70h	Х	SRD	_	—
Read status register	M16C/65 <sup>(1)</sup>	Х	XX70h	Х	SRD	—	—
	M16C/65 <sup>(2)</sup>	BA	XX70h	Х	SRD	_	—
	M16C/62P	Х	XX50h	_	—	_	—
Clear status register	M16C/65 <sup>(1)</sup>	Х	XX50h	_	—	_	—
	M16C/65 <sup>(2)</sup>	B0-7	XX50h	B8	XX50h	_	—
	M16C/62P	WA	XX40h	WA	WD	_	_
Program	M16C/65 <sup>(1)</sup>	WA	XX41h	WA	WD0	WA	WD1
	M16C/65 <sup>(2)</sup>	WA	XX41h	WA	WD0	WA	WD1
	M16C/62P	Х	XX20h	BA	XXD0h	_	_
Block erase	M16C/65 <sup>(1)</sup>	Х	XX20h	BA	XXD0h	—	—
	M16C/65 <sup>(2)</sup>	BA	XX20h	BA	XXD0h	_	—
	M16C/62P	Х	XXA7h	Х	XXD0h	_	_
Erase all unlocked blocks	M16C/65 <sup>(1)</sup>	_	—	_	—	_	—
DIOCKS	M16C/65 <sup>(2)</sup>	_	—	_	—	_	—
	M16C/62P	Х	XX71h	BA	XXD0h	_	_
Read lock bit status	M16C/65 <sup>(1)</sup>	Х	XX71h	BA	XXD0h	—	—
	M16C/65 <sup>(2)</sup>	BA	XX71h	BA	XXD0h	_	_
	M16C/62P	—	—	—	—	—	—
Block blank check <sup>(3)</sup>	M16C/65 <sup>(1)</sup>	Х	XX25h	BA	XXD0h		_
	M16C/65 <sup>(2)</sup>	BA	XX25h	BA	XXD0h	_	—

 Table 2.39
 Differences between Software Commands

Notes:

1. Program ROM 1 is not over 512 KB

2. Program ROM 1 is over 512 KB

3. Block blank check command is designed for programmer manufacturer. Not for customers in general.

SRD: Data in the status register (D7 to D0)

WA: Even write address (but in M16C/65, set the end of the address to 0, 4, 8, or C (hexadecimal) only.) WD: 16-bit write data

WD0: 16-bit write data lower word

WD1: 16-bit write data upper word

BA: Highest-order block address (even address)

B0-7: Any even address in blocks 0 to 7, program ROM2, or data flash

B8: Any even address in blocks after 8.

X: Any even address in user ROM area

XX: Eight high-order bits of command code (ignored)



Symbol	Address		Bit	Differences	
	M16C/62P	M16C/65	Βιτ	M16C/62P	M16C/65
FIDR	01B4h	—		M16C/62P only	—
FMR0	01B7h	0220h	_	Different address	
FMR1 01B5h	00041	1	EW1 mode select bit 0: EW0 mode 1: EW1 mode	Write to FMR6 register enabled bit 0: Disabled 1: Enabled	
	01850	0221h	7	Reserved bit	Data flash wait bit 0: 1 wait 1: Follow the setting of the PM17 bit
FMR2	—	0222h		—	M16C/65 only
FMR6	—	0230h	—	—	M16C/65 only

Table 2.40	Differences between Registers Associated with Flash Memories
------------	--



# 2.18 Differences between Flash Memory Block Configurations

The flash ROM block configurations differ between the M16C/62P and the M16C/65. Figure 2.1 shows the Differences between Flash Memory Block Configurations. The differences are marked in yellow.

00F000h 00FFFFh	Block A: 4 Kbytes				00E000h 00EFFFh 00F000h 00FFFFh 010000h	Block A: 4 Kbytes Block B: 4 Kbytes
					013FFFh	Program ROM 2: 16 Kbytes
080000h 08FFFFh 090000h	Block 12: 64 Kbytes		0F0000h	Block 5: 32 Kbytes	080000h [	
09FFFFh 0A0000h 0AFFFFh 0B0000h	Block 11: 64 Kbytes Block 10: 64 Kbytes		0F7FFFh 0F8000h		08FFFFh 090000h 09FFFFh 0A0000h	Block 7: 64 Kbytes Block 6: 64 Kbytes
0BFFFFh 0C0000h 0CFFFFh	Block 9: 64 Kbytes Block 8: 64 Kbytes		0F9FFFh 0FA000h	Block 4: 8 Kbytes	0AFFFFh 0B0000h 0BFFFFh	Block 5: 64 Kbytes Block 4: 64 Kbytes
0D0000h 0DFFFFh 0E0000h	000h Block 7: 64 Kbytes 0F6 000h Block 6: 64 Kbytes	0FBFFh 0FC000h	Block 2: 8 Kbytes	0C0000h 0CFFFFh 0D0000h	Block 3: 64 Kbytes Block 2: 64 Kbytes	
0EFFFFh 0F0000h 0FFFFFh	Block 0 to 5 (32+8+8+8+4+4) Kbytes	Ý	OFDFFFh OFE000h OFEFFFh OFF000h OFFFFFh	Block 1: 4 Kbytes Block 0: 4 Kbytes	0DFFFFh 0E0000h 0EFFFFh 0F0000h 0FFFFFh	Block 1: 64 Kbytes Block 0: 64 Kbytes
		C/62P Gi				C/65 Group

Figure 2.1 Differences between Flash Memory Block Configurations



# 2.19 New Functions added in the M16C/65

The following functions have been added in the M16C/65 Group MCU:

- Multi-master I<sup>2</sup>C-bus interface
- CEC function
- Real-time clock
- PWM function
- Remote control signal receiver

# 2.20 Differences in Development Tool

Table 2.41 lists Differences in Development Tool.

Table 2.41Differences in Development Tool
---

Types of Tool	M16C/62P	M16C/65
C compiler	M3T-NC30WA	M3T-NC30WA
Real-time OS	M3T-MR30	M3T-MR30
Emulator debugger	PC7501	E100
Emulation probe	M3062PT2-EPB	—
MCU unit	—	R0E530650MCU00
Compact emulator	M3062PT3-CPE	—
On-chip debugging emulator	E8 E8a (7-wire system)	E8a (single-wire system)
Renesas starter kits	R0K33062PS001BE	R0K53650ES000BE



# 3. Reference Documents

M16C/62P Group Hardware Manual Rev.2.41 M16C/65 Group User's Manual: Hardware Rev.2.00 The latest version can be downloaded from the Renesas Electronics website.

Technical Update/Technical News

The latest information can be downloaded from the Renesas Electronics website.

# Website and Support

Renesas Electronics website http://www.renesas.com/

Inquiries http://www.renesas.com/inquiry



# **Revision History**

# M16C/62P Group, M16C/65 Group Differences between M16C/62P and M16C/65

Davi	Date	Description		
Rev.		Page	Summary	
1.00	May 21, 2008		First edition issued	
1.01	Feb 5, 2009	2	31.25 ns (f(BLCK) = 32 MHz, VCC1 = 3.0 to 5.5 V) 40 ns (f(BCLK) = 25 MHz, VCC1 = 2.7 to 5.5 V) >	
			31.25 ns (f(BLCK) = 32 MHz, VCC1 = 2.7 to 5.5 V)	
		3	Suspend function delete	
1.02	May 29, 2009	2	Table3.1 M16C/65: low-speed on-chip oscillator(125kHz)> 125 kHz on-chip	
			oscillator, high-speed on-chip oscillator(40MHz)> 40 MHz on-chip oscillator	
		2,9	Table 3.1, Table4.11 0 to 3 wait(s)>0 to 3 cycle(s)	
		4	Table3.3 Deleted: P3_0,P2_7,P2_6,P2_3,P2_2,P2_1,P2_0	
		5	Table4.1 Added: M16C/65 bit3 VWCE,VD1LS	
		6	Table4.5 Added: VCR2 register	
		7	Table4.7 Added: bit 3 in the CM1 register, bit 0 in the PM2 register	
			Bit5-4 in the PLC0 register added: M16/62P bit4 Set to1, M16C/65 11:Do not set	
		10	Table4.14 Added: PD8 register	
		11	Table4.16 Added: M16C/62P start/stop condition detection	
1		12	Table4.17 Modified: Vector Address 46 to 51,and 63	
			M16C/65 -(Reserved)> INT instruction interrupt	
		14	Table4.20 Added.	
		18	Table4.26 Added: TAOW register	
		24	Table4.34 Bit Symbol> Bit Name,	
			Bit 0 in the ADCON2: With> Without, Without> With	
		26	Table4.37 Deleted: Suspend function	
		27	Table4.38 revised.	
		28	Table4.39 FMR3> FMR2, 0223h> 0222h	
		29	Figure4.1 M16C/62P Block A 080000h> 00F000h	
1.03	Jul 30, 2011	Overall	Updated configuration of this document.	
		3	Table 1.1: Deleted the Power Consumption row, and added HOLD input to the External Bus row.	
		4	Table 1.2: Added sub items to the Serial Interface, A/D Converter, and CRC Calculator.	
		5	Table 1.3: Added last two options to the Address FFFFFh function setting for M16C/65.	
		7	<ul> <li>Table 2.2:</li> <li>Deleted "(operates at the same time as voltage monitor 0 reset)" from the M16C/65 column of the Cold start, warm start discrimination method row.</li> <li>Added Reset Source Determine Register row.</li> </ul>	
		9	<ul> <li>Table 2.6</li> <li>Added the 125 kHz on-chip oscillator row.</li> <li>Added "approx. 40 MHz" to the M16C/65 column of the On-chip oscillator frequency row.</li> </ul>	

Revision History	M16C/62P Group, M16C/65 Group
	Differences between M16C/62P and M16C/65

Rev.	Date	Description		
Nev. Dale		Page	Summary	
1.03	Jul 30, 2011	16	Table 2.20: Changed "Watchdog timer counter initialization" to "Watchdog timer counter refresh".	
		19	<ul> <li>Table 2.26:</li> <li>Changed the descriptions in the M16C/65 column of the Count source.</li> <li>"Added the Write to timer register in pulse period/pulse width measurement modes" row.</li> <li>Changed the Overflow flag clear method for M16C/62P.</li> </ul>	
		22	Table 2.29: Changed the M16C/65 column of the Count source.	
		26	Table 2.34: Added the Operation clock $\phi$ AD row.	
		27	Table 2.38: Added the Data retention row.	
		28	Table 2.39: Added note 3.	
		31	<ul> <li>Table 2.41:</li> <li>Changed the statuses of the Emulation probe and Renesas starter kits for M16C/65.</li> <li>Added the MCU unit row.</li> </ul>	

All trademarks and registered trademarks are the property of their respective owners.

## General Precautions in the Handling of MPU/MCU Products

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this manual, refer to the relevant sections of the manual. If the descriptions under General Precautions in the Handling of MPU/MCU Products and in the body of the manual differ from each other, the description in the body of the manual takes precedence.

1. Handling of Unused Pins

Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.

- The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.
- 2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.
  - In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

- The reserved addresses are provided for the possible future expansion of functions. Do not access these addresses; the correct operation of LSI is not guaranteed if they are accessed.
- 4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

- When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.
- 5. Differences between Products

Before changing from one product to another, i.e. to one with a different part number, confirm that the change will not lead to problems.

— The characteristics of MPU/MCU in the same group but having different part numbers may differ because of the differences in internal memory capacity and layout pattern. When changing to products of different part numbers, implement a system-evaluation test for each of the products.

#### Notice

- All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renease Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renease Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The recommended where you have failed to obtain the prior written consent of Renesas Electronics. The recommended where you have failed to obtain the prior written consent of Renesas Electronics. The recommended where you have failed to obtain the prior written consent of Renesas Electronics. The recommended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is or Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics.
- "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools
- personal electronic equipment; and industrial robots. "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
- "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations. or healthcare intervention (e.g. excision, etc.), and any other apolications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and mafunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and mafunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

Refer to "http://www.renesas.com/" for the latest and detailed information



#### SALES OFFICES

#### **Renesas Electronics Corporation**

http://www.renesas.com

Renease Electronics America Inc. 2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A. Tel: +1-408-588-000, Fax: +1-408-588-6130 Renease Electronics Canada Limited 1011 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada Tel: +1-905-898-5441, Fax: +1-905-898-3220 Renease Electronics Europe Limited Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-585-100, Fax: +44-1628-585-900 Renease Electronics Europe GmbH Arcadiastrasse 10, 40472 Disseldorf, Germany Tel: +49-211-65030, Fax: +44-1628-585-900 Renease Electronics (China) Co., Ltd. 7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China Tel: +48-10-2425-1155, Fax: +48-10-2825-7679 Renease Electronics (Changhai) Co., Ltd. 7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China Tel: +48-10-2425-1155, Fax: +480-10-2825-7679 Renease Electronics (Changhai) Co., Ltd. 7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China Tel: +48-21-5877-1818, Fax: +480-2817-7858 Renease Electronics (Shanghai) Co., Ltd. 1011 204, 205, AZIA Center, No.1233 Luijazui Ring Rd., Pudong District, Shanghai 200120, China Tel: +482-21-5877-1818, Fax: +480-2817-7858 Renease Electronics Hong Kong Limited Unit 1001-1813, 16F, Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +480-281759-9600, Fax: +4886 2-9175-9670 Renease Electronics Singapore Pte. Ltd. 1 harbourFront Avenue, #06-10, keppel Bay Tower, Singapore 098632 Tel: +656-27159-9600, Fax: +4886 2-9175-9670 Renease Electronics Malaysia Sch. Bhd. 1 harbourFont Avenue, #06-10, keppel Bay Tower, Singapore 098632 Tel: +656-9271900, Fax: +486-29017-9670 Renease Electronics Malaysia Sch. Bhd. 1 harbourFont Avenue, #06-10, keppel Bay Tower, Singapore 098632 Tel: +656-92790, Fax: +486-29017-956-9510 Renease Electronics Koree Co., Ltd. 11F, Samik Lavied' or Blok B, Menara Ramoor, Amorop Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Ja