



Winning Combinations04
Interface
Interface0!
Amplifiers
General Purpose Op-Amps & Comparators10
Precision Op Amps13
High-Speed Op-Amps14
Current Sensing10
Ontoelectronics


CONTENTS

Timing Real-Time Clocks
Data Converters
High Speed ADC/DACs
Precision Data Converters
Digital Potentiometers Portfolio23
Voltage References
Reset IC
Voltage Detecting, System Resetting IC25
Switches & Multiplexers
Analog Switches
AnalogPAK™ SLG47004V

Complete Signal Chain Solutions

Renesas' broad precision analog portfolio provides a wide range of next-gen precision instrumentation, medical, communication, and industrial process control applications where innovation, reliability, and dependability is central to the analog designs






WINNING COMBINATIONS

Renesas Industrial Signal Chain Solutions

Renesas offers dozens of Winning Combinations - expert designs showcasing Renesas' product portfolios of Embedded Processing, Analog, Power, and Connectivity. With these engineering-vetted designs, customers can take advantage of an elevated platform for their design ideas, accelerating their product development cycle and lowering their overall risk to bring their designs to market.



Featured Solution: 48V Position Control Solution

Solutions for BLDC motor applications have been increasing rapidly because of the demand for products that are smaller in size and provide high efficiency. The core of a BLDC motor design is a robust and reliable motor control circuit and a versatile MCU for a safe control algorithm. Key building blocks of a motor control circuit include a MOSFET driver, versatile MCU, voltage regulators, a cell balancer, and the battery charger. Analog Components highlighted in Blue.

Other Winning Combos featuring Analog products

Key Components	Key Features
ISL3156E	RS-485/RS-422 transceiver features high output drive and high ESD protection
ISL28023	High-side and Low-side digital current sense and voltage monitor with a serial interface
ISL8117	Synchronous Step-Down PWM Controller
HIP4086	3-Phase MOSFET Driver
ISL33002	I ² C Bus Buffer with Rise Time Accelerators and Hot Swap Capability
ISL88011	5 Ld Voltage Supervisor with Adjustable Power-On Reset, Dual Voltage Monitoring or Watchdog Timer Capability
RX24T	32-bit Microcontroller with On-chip FPU Enable to Drive Two Motors Simultaneously
ISL80505	High Performance Low Dropout Regulator
ISL85415	Synchronous Buck Regulator
ISL28005	Micropower, Rail-to-Rail Input Current Sense Amplifier


Bundle Code	Bundle Name	Segment
US041	Remote Monitoring System	Building Safety & Security
US043	48V Position Control	Factory Automation & Control
US017	Electronic Valve with Flow Meter	Appliances
US019	Remote Monitoring System (update from existing WC)	Building Safety & Security
CN039	Thermostat with Color Touchscreen and Cloud Connection	HVAC Systems
CN032	AC Servo Motor Control with Industrial Network Connections	Factory Automation & Control
CN032	AC Servo Motor Control with Industrial Network Connections	Factory Automation & Control
CN076	Edge Computing for Security Systems	Building Safety & Security
CN194	Over-The-Air Update Module for PLC Applications	Factory Automation & Control
CN104	Tankless Gas Water Heater with Remote User Control	Appliances
JP104	Robotics Solution with RZ/A2M	Robotics

Interface




High Noise Immunity

The RAA78815x transceiver have Industry's highest EFT Immunity and Output Drive.




Ultra Low Supply Current

ISL3260xE Idle current is 9 times lower than that of low power transceiver ISL3172E.




Space-Saving Small Package

Reduced package size enables smaller, more compact products.



Broad Portfolio to Fit Your Needs



RS-485/RS-422 Transceivers

RS-485 is a multi-point interface bus, meaning multiple drivers and receivers can be connected to one bus. RS-485 uses differential signaling to achieve high noise immunity. Its common-mode voltage range reaches from -7V up to +12V.

RS-422 is a multi-drop interface bus, meaning only one driver but multiple receivers can connect to one bus. RS-422 also uses differential signaling. Its common-mode voltage range however is smaller and ranges from -7V up to +7V.

Note that RS-485 transceiver can be used in RS-422 networks but not vice versa. RS-422 devices cannot be used in RS-485 systems.

Renesas has a 50-year history in interface transceivers and we are still a market leader today. We have a full portfolio of RS-485/RS-422 transceivers suited to most design needs.

Transceivers with High EFT Immunity per IEC61000-4-2

Transceiver Family	V _{CC} Range (V)	EFT (kV)	Data Rates (Mbps)	V _{OD} (typ) (V)	# Devices on bus	Half / Full Duplex	Bus ESD HD / FD (kV)	Quiescent I _{CC} (µA)(RX = on)	Temp Range (°C)
RAA78815x	4.5 – 5.5	5	0.115 / 1 / 20	3.1	256	HD / FD	16.5 / 10	550	-40 to +85
RAA78817x	3.0 - 3.6	3	0.25 / 0.5 / 20	2.0	256	HD / FD	16.5 / 10	480	-40 to +85

x = 0,2,3,5,6,8

High-Speed Transceivers (DR ≥ 40Mbps)

Part Number	V _{CC} Range (V)	Data Rate (Mbps)	Vod (typ)(V)	Half / Full Duplex	Devices allowed on bus	Hot Plug	IEC ESD (kV)	Icc (mA)	Ізном (µА)	Temp Range (°C)
ISL3179E	3.0 - 3.6	40	2.0	Half	160	Yes	±16.5	2.6	0.05	-40 to +125
ISL3180E	3.0 - 3.6	40	2.0	Full	160	Yes	±5	2.6	0.05	-40 to +85
ISL3159E	4.5 – 5.5	40	2.8	Half	160	Yes	±15	2.6	0.05	-40 to +125
ISL3160E	4.5 – 5.5	40	2.8	Full	160	Yes	±5	2.6	1.4	-40 to +125
ISL3259E	4.5 – 5.5	100	2.8	Half	160	Yes	±15	2.6	0.05	-40 to +85

Ultra-Low Power Transceivers

Part Number	# TX	# RX	V _{CC} Range (V)	Data Rates (kbps)	Duplex	# Devices allowed on bus	Bus ESD (kV)	Quiescent Icc (µA)	Ізном (µА)	Temp Range (°C)
ISL32600E	1	1	2.7 – 3.6	256	Full	256	±15	70	0.01	-40 to +125
ISL32601E	1	1	2.7 – 3.6	256	Half	256	±15	70	0.01	-40 to +125
ISL32603E	1	1	1.8 – 3.6	460	Half	256	±15	150	0.01	-40 to +125
ISL32612E	0	1	1.8 – 3.3	256 / 500	_	256	±16.5	85	_	-40 to +125
ISL32614E	1	0	1.8 – 3.3	128 / 256	_	256	±16.5	100	0.01	-40 to +125

Single RS-485/422 Drivers and Receivers

Part Number	# TX	# RX	V _{CC} Range (V)	Data Rate (Mbps)	V _{OD} (typ) (V)	V _L Pin (V)	TX / RX Enables	IEC ESD (kV)	Icc (µA)	Temp Range (°C)
ISL3295E	1	0	3.0 – 5.5	20	2.0 (Vcc = 3.0V) 3.4 (Vcc = 4.5V)	_	Active High	±16.5	120	-40 to +125
ISL3298E	1	0	3.0 – 5.5	20	2.0 (Vcc = 3.0V) 3.4 (Vcc = 4.5V)	1.6	Active High	±16.5	120	-40 to +125
ISL3280E	0	1	3.0 – 5.5	20	_	_	None	±16.5	400	-40 to +125
ISL3281E	0	1	3.0 – 5.5	20	_	_	Active High	±16.5	400	-40 to +125
ISL3282E	0	1	3.0 – 5.5	20	_	1.6	Active Low	±16.5	400	-40 to +125
ISL3283E	0	1	3.0 – 5.5	20	_	_	Active Low	±16.5	400	-40 to +125

Quad RS-422 Drivers and RS-485/422 Receivers

Part Number	# TX	# RX	V _{CC} Range (V)	Data Rate (Mbps)	V _{OD} (typ) (V)	V _L Pin (V)	TX / RX Enables	IEC ESD (kV)	Icc (µA)	Temp Range (°C)
RAA7884QT	4	0	3.0 – 5.5	50	2.6 (Vcc = 3.0V) 4.0 (Vcc = 4.5V)	_	Group	±16.5	0.8	-40 to +125
ISL32172E	4	0	3.0 – 5.5	32	2.6 (Vcc = 3.0V) 4.0 (Vcc = 4.5V)	_	Group	±16.5	0.6	-40 to +125
ISL32272E	4	0	3.0 – 5.5	10	2.6 (Vcc = 3.0V) 4.0 (Vcc = 4.5V)	_	Group	±16.5	0.6	-40 to +125
ISL32174E	4	0	3.0 – 5.5	32	2.6 (Vcc = 3.0V) 4.0 (Vcc = 4.5V)	_	Paired	±16.5	0.6	-40 to +125
ISL32179E	4	0	3.0 – 5.5	32	2.6 (Vcc = 3.0V) 4.0 (Vcc = 4.5V)	1.6	Individual & Group	±16.5	0.6	-40 to +125
ISL32173E	0	4	3.0 - 5.5	80	_	_	Group	±16.5	15	-40 to +125
ISL32177E	0	4	3.0 – 5.5	80	_	1.6	Individual & Group	±16.5	15	-40 to +125
ISL32273E	0	4	3.0 - 5.5	20	_	_	Group	±16.5	5.5	-40 to +125
ISL32275E	0	4	3.0 - 5.5	20	_	_	Paired	±16.5	5.5	-40 to +125
ISL32277E	0	4	3.0 – 5.5	20	_	1.6	Individual & Group	±16.5	5.5	-40 to +125
RAA7884QR	0	4	3.0 - 5.5	80	_	_	Group	±16.5	15	-40 to +125

Overvoltage Protected Transceivers

Part Number	V _{CC} Range (V)	OVP (V)	CMVR (V)	Half / Full Duplex	Data Rates (Mbps)	Devices allowed on bus	Hot Plug	IEC ESD (kV)	ICC /ISHDN (mA)	Temp Range (°C)
ISL3243xE	3.0 - 5.5	±40	±15	HD / FD	0.25 / 1.0	128	No	±15	2.1 / 0.01	-40 to +85
ISL3245xE	3.0 - 5.5	±60	±20	HD / FD	0.25 / 1 / 20	128	No	±15	2.1 / 0.01	-40 to +85
ISL3247xE	4.5 – 5.5	±60	±15	HD / FD	0.25 / 1 / 15	128	Yes	±16.5	2.3 / 0.01	-40 to +85
ISL3249xE	4.5 – 5.5	±60	±25	HD / FD	0.25 / 1 / 15	128	Yes	±16.5	2.3 / 0.01	-40 to +85

x = 0,2,3,5,6,8

RS-232 Transceivers


RS-232 is a point-to-point interface between two RS-232 transceivers. RS-232 using single-ended signaling but with positive and negative voltages, such as ± 5 V to ± 13 V.

RS-232 Transceivers with Single, Dual, and Triple Channels

Part Number	Data Rate(Mbps)	V _{CC} (V)	Shutdown* Man./Auto	High ESD (kV)	Temp Range (°C)	Package
			SINGLE TRANSC	CEIVER (1 Tx / 1 Rx)		
ICL3221E	0.5	3 – 5	A (B)	15	-40 to +85	SSOP16, TSSOP16
ICL3226E	0.5	3 – 5	A (E)	15	-40 to +85	SSOP16
			DUAL TRANSCE	IVERS (2 Tx / 2 Rx)		
ICL3222E	0.5	3 – 5	M	15	-40 to +85	SOIC18, SSOP20, TSSOP20
ICL3223E	0.5	3 – 5	A (B)	15	-40 to +85	SSOP20, TSSOP20
ICL3224E	0.5	3 – 5	A (E)	15	-40 to +85	SSOP20
ICL3225E	1	3 – 5	A (E)	15	-40 to +85	SSOP20
ICL3232E	0.5	3 – 5	M	15	-40 to +125	SOIC16, SSOP16, TSSOP16, TSSOP20
ISL4223E	0.5	3 – 5	A (B)	15	-40 to +85	QFN20
			TRIPLE TRANSCI	EIVERS (3 Tx / 3 Rx)		
ISL4270E	0.5	3.0 - 5.5	A (E)	15	-40 to +85	QFN32
ISL83387E	0.5	3.0 - 5.5	A (E)	15	-40 to +85	TSS0P24

Multi-Protocol Transceivers

Multi-Protocol transceivers support both RS-485 and RS-232 interface specifications. They can be used as compact interface solutions, or as interface bridges, converting signal from one standard to the other. Multi-Protocol transceivers are in single or dual port variants, where each port can be configured either as a full duplex RS-485 transceiver, or as a two-channel RS-232 transceiver.




Multi-Protocol Transceivers with Single and Dual Ports

Part Number # Ports	# Douts	Ports Config.	Data Rate (Mbps)		V _{CC} (V)	VL-Pin (1.8V)	RXEN Polarity	Laanbaak	ESD (kV)	Temp Range	Doolsons
Part Number	# PORTS		RS-485	RS-232	VCC (V)	VL-PIII (1.6V)	KAEN POINTILY	Loopback	ESD (KV)	(°C)	Package
ISL33337E	2	Fixed	20, 0.115	0.4	3	No	Low	No	15	-40 to +85	QFN40
ISL33354E	2	Fixed	20, 0.115	0.4	5	No	Low	No	15	-40 to +85	SSOP28
ISL81387	1	Prog.	20, 0.46, 0.115	0.65	5	No	High	Yes	15	-40 to +85	SOIC20, SSOP20
ISL3330	1	Prog.	20, 0.46	0.4	3	No	High	Yes	15	-40 to +85	SSOP20
ISL3331	1	Prog.	20, 0.46, 0.115	0.4	3	Yes	High and Low	Yes	15	-40 to +85	QFN40
ISL81334	2	Prog.	20 , 0.46 , 0.115	0.65	5	No	None	Yes	15	-40 to +85	SOIC28, SSOP28
ISL41334	2	Prog.	20, 0.46, 0.115	0.5	5	Yes	Low	Yes	15	-40 to +85	QFN40
ISL3332	2	Prog.	20	0.4	3	No	None	Yes	15	-40 to +85	SSOP28
ISL3333	2	Prog.	20, 0.46, 0.115	0.4	3	Yes	Low	Yes	15	-40 to +85	QFN40




General Purpose Op-Amps

The general purpose op-amp has low voltage amplifiers, high voltage amplifiers, low offset voltage amplifiers, high slew rate amplifiers, rail-to-rail amplifiers, and more. Adaptable and versatile to many applications such as audio, white goods and industrial equipment.




High Precision Op-Amps (Zero Drift)

Chopper-stabilized amplifiers (Zero Drift Amplifiers) offer one of the best solutions, for achieving the lowest offset voltage and drift. These amplifiers achieve high DC precision through a continuously running calibration mechanism that is implemented on-chip.




Comparators

We offers a diverse comparator portfolio that includes nano power comparators, high-speed CMOS comparators, and precision quad comparators. Our general-purpose comparators utilize CMOS processes suitable for low voltage, low power consumption and fast response. General-purpose comparators with expanded temperature operation suitable for high voltage applications are also available.



High-Speed Op-Amps

Our high-speed op-amps include amplifiers with low offset and rail-torail outputs for precision applications, high slew rate devices, and fully differential amplifiers with ultra-low distortion for driving high-speed ADCs.



GENERAL PURPOSE OP-AMPS & COMPARATORS

Op-Amps to Solve Your Design Challenges

Design Challenge #1

Energy Saving Product





- High demand for developing energy-saving products
- Adoption of energy-saving sensors such as current sensor, pressure sensor, gas sensor

Renesas Op-Amp Solution

Renesas provides a full range of input and output CMOS high precision amplifier products to meet the industry-demanding requirements of accurate sensing.

CMOS Operational Amplifiers

	Туре	V _{DD}	V _{IO} max.	SR typ.	Rail-to-Rail	Dual	Quad
		1.8 to 5.5V	±6mV	0.35V/µs	Input/output	READ2303G (General Purpose)	READ4303G (General Purpose)
L	Low power	1.8 to 5.5V	±6mV	0.35V/µs	Input/output	READ2353J (Automotive)	READ4353J (Automotive)
ŀ	liah slew	2.5 to 5.5V	±6mV	8V/µs	Input/output	READ2304G (General Purpose)	READ4304G (General Purpose)
	High slew rate	2.5 to 5.5V	±6mV	8V/µs	Input/output	READ2354J (Automotive)	READ4354J (Automotive)

Design Challenge #2

Short Development Time






Renesas Op-Amp Solution

Renesas provides total kit solutions for MCU and Op-Amps products. Simplify the design process and reduce development turnaround time by

utilizing the provided circuit diagrams and recommended parts.



Design Challenge #3

BOM Size



Complex ecosystem on battery-powered small applications

Renesas Op-Amp Solution

Renesas is expanding to include small MSOP package option to achieve mount area reduction.





CMOS Op-Amps

Туре	Rail-to-Rail	Part Number	Power Supply Voltage (V)	V _{IO} (max) (mV)	I _{DD} (typ) (µA/ch)	SR typ (V/µs)	Channels	Package
	Input/output	READ2351J (Automotive)	1.8 to 5.5	±6	40	0.35	2	8-pin TSSOP
	Input/output	READ2303G (General Purpose)	1.8 to 5.5	±6	40	0.35	2	8-pin TSSOP/MSOP
Low power	Input/output	READ2353J (Automotive)	1.8 to 5.5	±6	40	0.35	2	8-pin TSSOP
	Input/output	READ4303G (General Purpose)	1.8 to 5.5	±6	40	0.35	4	14-pin TSSOP
	Input/output	READ4353J (Automotive)	1.8 to 5.5	±6	40	0.35	4	14-pin TSSOP
	Input/output	READ2302G (General Purpose)	2.5 to 5.5	±6	750	8	2	8-pin TSSOP
	Input/output	READ2352J (Automotive)	2.5 to 5.5	±6	750	8	2	8-pin TSSOP
10.1.1	Input/output	READ2304G (General Purpose)	2.5 to 5.5	±6	750	8	2	8-pin TSSOP/MSOP
High slew rate	Input/output	READ2354J (Automotive)	2.5 to 5.5	±6	750	8	2	8-pin TSSOP
	Input/output	READ4304G (General Purpose)	2.5 to 5.5	±6	750	8	4	14-pin TSSOP
	Input/output	READ4354J (Automotive)	2.5 to 5.5	±6	750	8	4	14-pin TSSOP
	Output only	READ2606G (General Purpose)	4.5 to 32	±9	700	8	2	8-pin TSSOP
High voltage	Output only	READ2656J (Automotive)	4.5 to 32	±9	700	8	2	8-pin TSSOP
High slew rate	Input/output	READ4606G (General Purpose)	4.5 to 32	±9	700	8	4	14-pin TSSOP
	Input/output	READ4656J (Automotive)	4.5 to 32	±9	700	8	4	14-pin TSSOP

Bipolar Op-Amps

Most of Industrial's products are also compatible with automotive applications.

	Part Number								
Туре	Industrial	General Purpose	Power Supply Voltage (V)	V _{I0} (max) (mV)	I _{CC} (max) (mA)	SR (typ) (V/µs)	Channels	Package	
	μPC451	_	3 to 30	±7	2	0.3	4	14-pin SOP/TSSOP	
0	μPC452	μPC3403	3 to 32	±7	7	0.8	4	14-pin SOP	
Single power supply	μPC842/A	μPC4742	3 to 32	±5	4.5	7	2	8-pin SOP/TSSOP/MSOP*	
зирріу	μPC844	μΡC4744	3 to 32	±5	9	7	4	14-pin SOP/TSSOP	
	μPC1251	_	3 to 30	±7	1.2	0.3	2	8-pin SOP/TSSOP/MSOP	
	REAC1251G	_	3 to 30	±1	1.4	0.3	2	8-pin SOP/TSSOP/MSOP	
Law V/-a	REAC1251J (Automotive)	_	3 to 30	±1	1.4	0.3	2	8-pin SOP/TSSOP/MSOP	
Low V _{IO}	REAC842G	_	3 to 32	±1	6	7	2	8-pin SOP/MSOP	
	REAC842J (Automotive)	_	3 to 32	±1	6	7	2	8-pin SOP/MSOP	
	μPC258	μPC4558	±4 to ±16	±6	5.7	1	2	8-pin SOP	
	μPC259	μPC4560	±4 to ±16	±6	5.7	2.8	2	8-pin SOP	
Laurnaiaa	μPC458	μΡC4741	±4 to ±16	±5	7	1	4	14-pin SOP	
Low noise	_	μPC4570	±4 to ±16	±5	8	7	2	8-pin SOP/TSSOP	
	_	μPC4572	±2 to ±7	±5	7	6	2	8-pin SOP	
	_	μPC4574	±4 to ±16	±5	12	6	4	14-pin SOP/TSSOP	
	μPC811	_	±5 to ±16	±2.5	3.4	15	1	8-pin SOP	
	μPC812	μPC4092	±5 to ±16	±3	6.8	15	2	8-pin SOP	
	μPC813	_	±5 to ±16	±2.5	3.5	25	1	8-pin SOP	
	μPC814	μPC4094	±5 to ±16	±3	6.8	25	2	8-pin SOP	
J-FET	μPC822	μPC4072	±5 to ±16	±10	5	13	2	8-pin SOP	
	μPC824	μPC4074	±5 to ±16	±10	10	13	4	14-pin SOP	
	μPC832	μPC4062	±2 to ±16	±10	0.5	3	2	8-pin SOP	
	μPC834	μPC4064	±2 to ±16	±10	1	3	4	14-pin SOP	
	μPC835	_	±5 to ±16	±3	2.2	5.5	2	8-pin MSOP	
Low power	μΡC802	_	±1 to ±16	±6	≤0.1	≤1.0	1	8-pin SOP	
General	μPC251	μ P C1458	±7.5 to ±16	±6	5.6	0.5	1	8-pin SOP	

^{*} MSOP corresponds to uPC842A only

General Purpose Op-Amps

All general-purpose op-amps feature ground sensing capability. Most op-amps, however, possess rail-to-rail capability to enhance the dynamic input and output signal range and thus, signal integrity. Amongst these amplifiers, the ultra-low power op-amp, ISL28194, has a supply current of only 330nA, which makes it ideal for battery-powered applications.

Part Number	Channels (#)	Supply Range (V)	Vos (Max) (mV)	IBIAS (nA)	IS (per amp) (mA)	Bandwidth (MHz)	Slew Rate (V/µs)	Rail-to-Rail	Temperature Range (°C)
RRA786x0	x=1, 2, 4	1.8 – 5.5	1.9	0.006	0.52	10	7.5	In/Out	-40 to +125
RRA7900x	x=1, 2, 4	1.8 - 5.5	1.6	0.005	0.078	1	2.5	In/Out	-40 to +125
RRA7904x	x=1, 2, 4	1.2 – 5.5	2.25	0.012	0.013	0.35	0.2	In/Out	-40 to +125
CA3130	1	5 – 16	5	0.005	2	15	30	-Vs	-55 to +125
CA3140	1	4 – 36	5	0.01	4	4.5	9	-Vs	-55 to +125
ISL28x13	x = 1, 2, 4	1.8 – 5.5	5	0.003	0.13	2	1	In/Out	-40 to +125
ISL28x14	x = 1, 2, 4	1.8 – 5.5	5	0.003	0.039	5	2.5	In/Out	-40 to +125

Bipolar Comparators

	Part Number		Power						
Туре	Industrial	General Purpose	Supply Voltage (V)	V _{IO} (max) (mV)	Icc (max) (mA)	Tr/Tf (typ) (µs)	Channels	Package	
	μ PC177	_	2 to 32	±5	2	1.3	4	14-pin SOP/TSSOP	
0	μ PC271	_	5 to 32	±7.5	7.5	0.2	1	8-pin SOP	
General	μPC272	μ PC 319	5 to 16	±8	12.5	0.08	2	14-pin SOP	
	μ PC277	_	2 to 32	±5	1	1.3	2	8-pin SOP/TSSOP/MSOP	

[•] Industrial: Products with extended temperature tolerances (125°C).

PRECISION OP-AMPs: V_{0S} < 1mV

Unmatched Precision When Accuracy Matters

Zero Drift Amplifiers (Low Voltage Precision Op-Amps)

ISL28134, ISL28x33A, ISL28x30

Chopper-stabilized amplifiers (Zero Drift Amplifiers) offer one of the best solutions, for achieving the lowest offset voltage and drift. These amplifiers achieve high DC precision through a continuously running calibration mechanism that is implemented on-chip.

Key Features ISL28134

- Low offset voltage over supply range (typically < 0.2µV)
- Low offset voltage over temperature (typically < 0.5nV/°C)
- No 1/f noise
- Low wideband noise (typically 8nV/√Hz)
- Very high open loop gain (174dB)
- Wide Bandwidth (3.5MHz)
- Packages: Standard SOIC-8 and Tiny SOT-23-5 (2.9mm x 2.8mm)


Applications

High-Precision Signal Conditioners

- High-Gain Amplifiers
- Current Sensing
- Temperature Measurements
- Weight Scales
- Instrumentation
- Medical Equipment







Part Number	Channels (#)	Supply Range (V)	Vos (Max) (mV)	IBIAS (nA)	IS (per amp) (mA)	Bandwidth (MHz)	Slew Rate (V/µs)	Rail-to-Rail	Noise (nV/√Hz)
ISL28x30	x = 1, 2, 4	1.8 – 5.5	0.04	0.25	0.02	0.4	0.2	In/Out	65
ISL28x33A	x = 1, 2, 4	1.8 – 5.5	0.010	0.60	0.035	0.340	0.2	In/Out	75
ISL28134	1	2.25 – 6	0.0025	0.12	0.675	3.5	1.5	In/Out	8

High-Voltage Precision Op-Amps

Our high-voltage precision amplifiers feature low noise, high slew rate, and very low offset voltage, making them the ideal choice for applications where precision and low noise are important, such as precision medical and analytical instrumentation, sensor conditioning, precision power supply controls, industrial controls, and photodiode amplifiers. All devices operate over the extended temperature range from -40°C to +125°C.

Part Number	Channels (#)	Supply Range (V)	Vos (Max) (mV)	IBIAS (nA)	IS (per amp) (mA)	Bandwidth (MHz)	Slew Rate (V/µs)	Noise (nV/√Hz)	Temperature Range (°C)
ISL28207	2	4.5 – 40	0.075	0.015	0.21	1	0.32	13	-40 to 125
ISL28x08	x = 1, 2	3 – 40	0.15	-13	0.185	1.2	0.45	16	-40 to 125
ISL28x10	x = 1, 2	9 – 40	0.3	0.0003	2.55	12.5	23	6	-40 to 125
ISL28x17	x = 2, 4	4.5 – 40	0.05	1	0.44	1.5	0.5	8	-40 to 125
ISL28x18	x = 1, 2	3 – 40	0.15	-230	0.85	4	1.2	5.6	-40 to 125
ISL28227	2	4.5 – 40	0.07	10	2.8	10	3.6	2.5	-40 to 125
ISL28177	1	4.5 – 40	0.15	0.2	1.18	0.6	0.2	9.5	-40 to 125

High-Speed Op-Amps

High Speed Amplifiers

ISL55001, ISL28x91


Our high-speed op-amps include amplifiers with low offset and rail-torail outputs for precision applications, high slew rate devices, and fully differential amplifiers with ultra-low distortion for driving high-speed ADCs.


Key Features ISL55001


- 220MHz -3dB Bandwidth
- Unity-gain Stable
- Low Supply Current: 9mA @ VS = ±15V
- Wide Supply Range: ±2.5V to ±15V Dual-Supply and 5V to 30V Single-Supply
- High Slew Rate: 300V/µs
- Fast Settling: 75ns to 0.1% for a 10V Step
- Wide Output Voltage Swing: -12.75V/+13.6V with $VS = \pm 15V$, RL = 1k

Applications

- Video Amplifiers
- Single-supply Amplifiers
- Active Filters/Integrators
- High Speed Sample-and-Hold
- High Speed Signal Processing
- ADC/DAC Buffers
- Pulse/RF Amplifiers
- Pin Diode Receivers
- Log Amplifiers
- Photo Multiplier Amplifiers
- Difference Amplifier







High-Speed Op-Amps

Our high-speed op-amps include amplifiers with low offset and rail-to-rail outputs for precision applications, high slew rate devices, and fully differential amplifiers with ultra-low distortion for driving high-speed ADCs.

Part Number	Channels (#)	Topology	Supply Range (V)	Bandwidth (MHz)	Slew Rate (V/µs)	Noise (nV/√Hz)	2nd HD (dB)	3rd HD (dB)	IS per amp (mA)	V _{OS} (Max) (mV)
Voltage Feedba	ack Amplifiers wi	th Rail-to-Rail Ou	tputs							
ISL28191	1	VFA	3 – 5.5	61	17	1.7	-76	-70	2.6	0.63
ISL28291	2	VFA	3 – 5.5	61	17	1.7	-76	-70	2.6	0.63
Voltage Feedba	ack Amplifiers wi	th Enhanced Slev	v Rate							
ISL55001	1	VFA	5 – 30	220	300	12	-72	-80	9	3
Fully Differential Amplifiers										
ISL55210	1	FDA	3 – 4.2	2200	5600	0.85	-105	-120	35	1.4

CURRENT SENSING


Current sensing is a fundamental requirement in a wide range of electronic applications. Measuring current drop across a sense resistor is the most commonly used method due to being low cost, having high measurement accuracy, allowing a large measurable current range, and being capable to measure DC and AC currents.

Discrete Solution

Precision Op Amps for Current Sensing

A basic current sense amplifier is an op-amp configured as a difference amplifier. The diff-amp rejects the common mode voltage present at the points V1 and V2 and amplifies only the voltage difference across the sense resistor by the circuit gain. A separate reference voltage sets the midpoint of the output voltage around which the amplified input voltage swings. Substituting the voltage difference with the load current times the sense resistance and solving for the load current gives:

$$I_L = (V_O - V_{REF}) / (R_S \cdot G)$$



Most Common Discrete Solutions

Туре	Part Number	TCVos	V _{OS} Max @ 25°C	Notes
Low Noise	ISL28290	_	700µV	Low cost (low side)
Low Drift	ISL28x30	150nV/°C	40µV	Good – still low cost
Zero Drift	ISL28x33A	75nV/°C	10µV	Great
Zero Drift	ISL28134	15nV/°C	2.5µV	World Class
Standard CMOS	ISL28113 ISL28114	2μV/°C	5mV	
Standard CMOS	READ2302 READ2303 READ2304	_	6mV	
Standard Bipolar	REAC1251	1µV/°C	1mV	
Autotrim	SLG47004V	12.6µV/C (not trimmed) 5µV/C (trimmed)	243µV	Additional analog switches and digital macrocells

Generic versus High-Precision Solution

Using a low offset voltage op amp in the sensing circuit allows for a much lower sense resistor and less wasted power.

Example: 20mA Resolution, 5A Full Current

Solution	Vos	Rs	Rs Power Loss	Benefits
Generic	500µV	$25 m\Omega$	625mW	_
ISL28x30	40µV	2mΩ	50mW	92% Power Savings
ISL28134	2.5µV	125μΩ	3mW	99.5% Power Savings

Integrated Solution

The Simplest Type of Current Sense Amplifiers


The ISL28005 and ISL28006 are ground sensing current sense amplifiers that amplify milli-volt current signals developed across sub- 1Ω sense resistors. The simplest type of current sense amplifiers use single-stage op amp circuits that take their power from the same voltage source that generates the current to be measured.

Micropower, Current Sense Amplifier with Voltage Output



ISL28005/6

- High or low side unidirectional current sense
- Low power consumption, 50µA (typ)
- TIA Architecture:
- -Input Sense voltage converted to current
- -Current fed into 5V TIA for ADC drive
- -Constant 100kHz BW across gain
- Internal fixed gain for high accuracy and low TCVos



Current Sense Amplifiers

Part Number	Supply Range (V)	VICM Range (V)	Vos Max @ 25°C (µV)	Vos Max Temp (µV)	CMRR Min Temp (dB)	PSRR Min Temp (dB)	Gain Range (V/V)	Gain Accuracy @ 25°C (%)	Gain Accuracy Temp (%)	Is Max @ 25°C (µA)	Is Max Temp (µA)	Package
ISL28005	2.7 to 28	0 to 28	500	500	105	90	20, 50, 100	2	3	59	59	SOT-23-5
ISL28006	2.7 to 28	0 to 28	250	300	105	90	20, 50, 100 Adj (20–100)	0.7	1	62	62	SOT-23-5 SOT-23-6

Digital Power Monitors


High Voltage Precision Sensing for Current, Voltage, and Power

Integrated Analog Front End for High Voltage Monitoring and Bi-directional Current Sensing

ISL28022/23/25

The ISL28022/23/25 digital power monitors are high-side and low-side digital current sense and voltage monitors with serial interface. The "digital power monitor", or DPM, allows monitoring of power supplies, RF systems, and other high voltage applications.

- Input Common mode up to 60V
- High accuracy 0.05% error (ISL28023)
- User defined alerts OV, UV, OC
- Additional features (margin DAC, voltage regulator, internal temp sensor, auxiliary channel)




Current Sense Amplifiers

Part Number	Category	Primary Channel	LV AUX Channel	Accuracy	Current Measure LSB	Offset Voltage	Fast Alert Outputs	Package
ISL28022	Basic	0 to 60V	_	0.3%	10μV	75µV	_	MSOP10, QFN16
ISL28023	Full Featured	0 to 60V/12V	0 to V _{CC}	0.05%	2.5µV	30µV	2	QFN24
ISL28025	Tiny Package	0 to 60V/12V	0 to V _{CC}	0.1%	2.5µV	30µV	2	WLCSP-16

Optoelectronics

PHOTOCOUPLERS

Providing Highly Reliable, High Accuracy Small Footprint Solutions





Featured Products

Transistor output coupler for ultra-low input current

Input current IF=50 µA drive RV1S2x51A, RV1S2x55A


- Contribution
 The high CTR in the low input current region enables low power consumption of the application and control of multiple photocouplers by an MCU.
- Features
 - High CTR 300% or more
 - High temperature compatible 115°C
 - Creepage distance/Pin pitch 15/1.27mm (RV1S2451A)8.2/1.3mm (RV1S225xA)4/1.27mm (RV1S295xA)







LSSO5(5pin)/LSSOP(4pin)

- Downsizing while maintaining long creepage (35% reduction in mounting area compared to LSO5)
- Lineup: IGBT drive, IPM drive, 15 Mbps, Transistor output








Timing

REAL-TIME CLOCKS





ISL1208


I²C Real Time Clock/Calendar, Low Power RTC with Battery Backed SRAM

- Real Time Clock/Calendar
 - Tracks Time in Hours, Minutes, and Seconds
 - Day of the Week, Day, Month, and Year
 - Settable to the Second, Minute, Hour, Day of the Week, Day, or Month
- Automatic Backup to Battery or Super Capacitor 400nA Battery Supply Current
- 2 Bytes Battery-Backed User SRAM
- Single Alarm
- On-Chip Oscillator Compensation
- I²C Interface 400kHz Data Transfer Rate
- Small Package Options
 - 8 Ld MSOP and SOIC Packages
 - 8 Ld TDFN Package

Applications

- Utility Meters
- HVAC Equipment
- Audio/Video Components
- Set-Top Box/Television
- Modems
- Network Routers, Hubs, Switches, Bridges
- Cellular Infrastructure Equipment
- Fixed Broadband Wireless Equipment
- Pagers/PDA
- POS Equipment
- Test Meters/Fixtures
- Office Automation
- Home Appliances
- Computer Products
- Other Industrial/Medical/Automotive

Part Number	Alarms	#Fout frequencies	Battery Backup	Reseal	Memory (Bytes)	Event detection	Event time stamp	Bat timestamp	Auto DST adjust	Temp sensor	Power monitoring	Integrated Crystal
ISL12057	2	4										
ISL12058	2	4										
ISL12008	1	1	✓	✓								
ISL1208	1	15	✓		S2							
ISL1220	1	15	✓		S8							
ISL1209	1	15	✓		S2	✓						
ISL1219	1	15	✓		S2	✓	✓					
ISL1221	1	15	✓		S2	✓	✓					
ISL12022	1	15	✓	✓	S128			✓	✓	✓	✓	
ISL12026	2	3	✓		E512							
ISL12022M	1	15	✓	✓	S128			✓	✓	✓	✓	✓
ISL12020M	1	15	✓	✓	S128			✓	✓	✓	✓	✓



High Speed ADCs

Innovative FemtoCharge® CMOS technology yields ultra-high performance ADCs that consume a fraction of the power of the competition.

Competitive Advantages

- Between half and one fifth the power of the competition
- Superior wideband capabilities
- Compact footprint
 - The industry's first dual 12-bit 250MSPS ADC family
 - 500 MSPS option is 2 to 3.6x smaller than the competition

Applications

- Communications
- Networking
- Instrumentation
- Industrial
- Video and imaging

Speed	8-bit	10-bit	12-bit	14-bit	16-bit
500+	ISLA118P50	ISLA110P50 KAD5510P-50	ISLA112P50 ISLA212P50 KAD5512P-50	ISLA214P50	
250–350		KAD5510P-25 KAD5610P-25	ISLA212P25 ISLA222P25 ISLA222S25 KAD5512(H)P-25 KAD5612P-25	KAD5514P-25 ISLA224P25	ISLA216P25
130–210		KAD5510P-21 KAD5610P-21 KAD5510P-17 KAD5610P-17	KAD5512(H)P-21 KAD5612P-21 ISLA222S20 KAD5512(H)P-17 KAD5612P-17 ISLA222P13	KAD5514P-21 ISLA214P20 ISLA224P20 ISLA224S20 KAD5514P-17	ISLA216P20 ISLA216S20 ISLA216P13
Up to 125		KAD5510P-12 KAD5610P-12	KAD5512(H)P-12 KAD5512P-12	KAD5514P-12 ISLA224P12	





High Speed DACs

Key Features

- Excellent dynamic performance (ISL5957)
 - Nyquist SFDR at 10MHz = 75dBc
 - UMTS ACPR at 19.2MHz = 71dB
- GSM SFDR at 11MHz (20MHz window) = 94dBc
- +3.3V supply, low power: 103mW @ 130MSPS
- Adjustable full-scale output current: 2 to 20mA
- Pin compatible family of single and duals

Applications

- Wireless Comms
- Broadband Microwave Repeaters
- Military and SDR Radios

DACs	8-bit	10-bit	12-bit	14-bit
260 MSPS			ISL5857	
130–210 MSPS		ISL5761	ISL5861	ISL5961
60–125 MSPS	HI5660			




PRECISION DATA CONVERTERS

24-bit Delta-Sigma Converters

- High resolution (24-bit)
- Lower conversion rate

Applications

- Weigh scales
- Dynamic weighing
- Manufacturing systems
- Temperature and load sensors
- Load safety systems
- Scientific instrumentation



Successive Approximation (SAR) ADCs

- Medium to high-resolution ADCs (up to 12-bit)
- High conversion rate
- Low power

Applications

- Process controllers
- Human-machine interface devices
- Pressure and flow sensors
- Switchgear
- Safety monitors



- Robotic controls
- Automotive systems

24-bit Delta-Sigma Converters

Resolution	Max Conv Rate	Part Number	INL (%FS)	Noise	Power Consumption	Analog Supply Voltage Range	Digital Supply Voltage Range	Package	Technical Highlight
24-bit	4kSPS	ISL26102	0.0002	7nV/√Hz	33.75mW	4.75 – 5.25V	2.7 – 5.25V	24 and 28 Ld TSSOP	Programmable gain amplifier with gains of 1 to 128
	10SPS and 80SPS	ISL26132	0.0002	1.2µV/√Hz	50mW	5V	2.7V	24 and 28 Ld TSSOP	Up to 21.6 Noise-free bits

SAR ADC


Resolution	Max Conv Rate	Part Number	± INL (Integral Non-Linearity) (LSB)	SFDR	Power Consumption	Analog Supply Voltage (min)	Analog Supply Voltage (max)	Pkg Type	Temp Range (°C)
10-bit	1MSPS	ISL267440	0.5	-76dB	2mW	2.7V	5.25V	MSOP8, SOT8	-40 to +85
	TIVISPS	ISL26710	0.1	-82dB	3.75mW	2.7V	5.25V	DFN8, SOT8	-40 to +85
12-bit	125kSPS	ISL26313	0.7	96dB	11mW	2.7V	5.25V	SOIC8, TSSOP16	-40 to +125
	200kSPS	ISL267817	1	-85dB	2.15mW	4.75V	5.25V	MSOP8, SOIC8	-40 to +85
	250kSPS	ISL26321 , ISL26322	0.7	96dB	11mW, 15mW	2.7V	5.25V	SOIC8, TSSOP16	-40 to +125
	1MSPS	ISL26712	0.4	-87dB	3.75mW	2.7V	5.25V	DFN8, SOT8	-40 to +85

DIGITAL POTENTIOMETERS PORTFOLIO

Digital potentiometers replace mechanical potentiometers and trim resistors in applications where digital control allows microprocessor interfacing and extended functionality. Compared to mechanical potentiometers, electronic potentiometers are more accurate, easier to adjust, and they reduce manufacturing complexity. Renesas offers the widest selection of low-to-high resolution digital potentiometers (DCPs) in single, dual and quad configurations that are accurate, easy to adjust and reduce manufacturing complexity.

X9C102, X9C103, X9C104, X9C503 Digitally Controlled Potentiometer

- Three-Wire Serial Interface
- 1kΩ, 10kΩ, 50kΩ, 100kΩ
- 100 Wiper Tap Points
 - Wiper Position Stored in Non-volatile Memory and Recalled on Power-up
- 99 Resistive Elements
 - Temperature Compensated
 - End-to-End Resistance, ±20%
 - Terminal Voltages, ±5V
- Low Power CMOS
 - Vcc = 5V
 - Active Current, 3mA max.
 - Standby Current, 750µA max. High Reliability
- Reliability
 - Endurance, 100,000 Data Changes per Bit
 - Register Data Retention, 100 years
- 8 lead SOIC or PDIP



Тар	Part Number	Resistance kΩ	Channels	Interface
32	ISL23511	10	1	Pushbutton
128	ISL23318	10, 100	1	I ² C
	ISL23418	50	1	SPI
	ISL90727, 8	10, 50	1	I ² C
	ISL23315	10, 100	1	I ² C
	ISL23328	10	2	I ² C
256	ISL23415	10, 100	1	SPI
	ISL23325	10, 100	2	I ² C
	ISL23425	10, 100	2	I ² C
	ISL90842	10, 50	4	I ² C
1024	SLG47004V	100	2 (rheostat mode), 1 (potentiometer mode)	I ² C, internal custom logic circuit

Other Options with Vola	atile Memory
-------------------------	--------------

		Nonvolat	ile	
Тар	Part Number	Resistance kΩ	Channels	Interface
32	ISL22511	10	1	Pushbutton
	X9313	1, 10, 50	1	3-Wire (Up/Down)
	X9315	10, 50, 100	1	3-Wire (Up/Down)
	X9511	10	1	Pushbutton
64	X9241A	2, 10, 50	1	2-Wire
	X9401	10	4	SPI
100	X9317	10, 50	1	3-Wire (Up/Down)
	X9318	10	1	3-Wire (Up/Down)
	X9C102, 3, 4	1, 10, 100	1	3-Wire(Up/Down)
	X9C503	50	1	3-Wire (Up/Down)
128	ISL223x6	10	x = 1, 2, 4	I ² C
	ISL223x6WM	10	x = 1, 2, 4	I ² C
	ISL22317	10, 50, 100	1	I ² C
	ISL95311	10	1	I ² C
256	ISL958x0	2.5, 10, 50	x = 1, 2	I ² C
	X9252	2, 10	4	2-Wire, 3-Wire (Up/Down)
	ISL22424	10	2	SPI
	X9271, X9251, X9259	50	1, 4	SPI, 2-Wire
	X9250, X9258	50, 100	4	SPI, 2-Wire

Other Options with non-Volatile Memory


VOLTAGE REFERENCES

Renesas offers a wide range of precision voltage references in both FGA™ and Bandgap technology

Accurate and Stable Voltage Reference with Floating Gate Analog Technology (FGA™)

Renesas' revolutionary Floating Gate Analog (FGA TM) voltage reference circuits are not dependent on the voltage produced by a silicon junction. FGA technology produces extraordinarily accurate and stable reference voltages by storing a precise charge on a floating gate cell that is essentially unaffected by external influences such as variation in temperature, input voltage, and time.

The floating gate voltage is buffered with a high-quality CMOS amplifier as shown in the simplified diagram in Figure 1.




Ultra-Low Power, General Purpose Voltage Reference

ISL21080

The ISL21080 analog voltage references feature low supply voltage operation at ultra-low 310nA typical. Additionally, the ISL21080 family features ensured initial accuracy as low as $\pm 0.2\%$ and 50ppm/°C temperature coefficient.

These references are ideal for general purpose portable applications to extend battery life at lower cost. The ISL21080 is provided in the industry standard 3 Ld SOT-23 pinout.

- Supply current: 310nA typ
- Reference output voltage options:
 - 0.9V,1.024V, 1.25V, 1.5V, 2.048V, 2.5V, 3.0V, 3.3V, 4.096V
- Output voltage noise: 30µV_{P-P} typ
- Temperature Range: -45°C to +85°C
- Tempco: 50ppm/°C max
- Output current capability: ±7mA
- Package: 3 Ld SOT-23



Precision Voltage References

								Vo	UT													Output			
Туре	Part Number	0.9V	1.024V	1.2V	1.25V	1.5V	1.8V	2.048V	2.5V	2.6V	30	3.3V	4.096V	20	7.5V	Temp Coefficient (max)	Is (typ)	Is (max)	V _S (min)	V _S (max)	Initial Accuracy (% Vout @2.5V)	Noise (0.1Hz to 10Hz) (typ)	Hysteresis (ppm)	Pkg Type	Temp Range (°C)
Low Noise	ISL21090				•				•					•		7ppm/°C	750µA (1.25V Option)	1.28mA	3.7V	36V	±0.03% (1.25V Option)	1.0µV _{PP} (1.25V option)	_	SOIC8	-40 to 125
Low Cost	ISL21010		•			•		•	•		•	•	•			50ppm/°C	48µA	100μΑ	2.2V	5.5V	0.2%	58µV _{PP} (2.048V option)	100	SOT3	-40 to 125
	ISL21080	•	•		•	•		•	•		•	•	•			50ppm/°C	300nA	1.5µA	2.7V	5.5V	<0.7%	30µVpp	100	SOT3	-40 to 85
	ISL60002		•	•	•		•	•	•	•	•	•				20ppm/°C	350nA	900nA	2.7V	5.5V	<0.49%	30µVpp	100	SOT3	-40 to 85
NanoPower	X60003												•	•		10ppm/°C (B grade)	500nA	900nA	4.5V	9V	<0.1%	30µVpp	150/100	SOT3	-40 to 85
With Comparator	ISL21440	1.	.182V ±0.5% with Comparator							_	0.46µA	6.5µA	2V	11V	0.5%	_	Programmable	DFN8, MSOP8	-40 to 125						

Reset IC

VOLTAGE DETECTING, SYSTEM RESETTING IC

High Voltage Bipolar Reset IC detect power supply volyage & protect equipments.

Reset IC is useful for resetting various logic circuits such as MCU. With built in delay circuit, user can easily change its delay time with an external capacitor.


High Voltage Bipolar Supply Voltage: 18V MAX.

Detecting Voltage REAR56953A,B: 4.25V fix (No need ext. resistor)

REAR56957A,B: 2 to 15V (Change by ext. resistor R1, R2) REAR56958B: 2 to 15V (Change by ext. resistorR1, R2)

Delay Time
 Large delay time with a capacitor of small capacitance
 TYP:: 3.4 ms (Cd=0.01uF), changed by delay capacitor

Applications Industrial Consumer




Part Number	Detecting Voltage [Typ.] (V)	Reset Mode	Out-put Type	Package	Block Diagram	Operating Waveform
REAR56953AGSM	4.25	Low	Built-in load	SOP8	Power-supply A: Bullt-in Load B: Open Collector SipA 25pA 9 Typ Output	90 4.25V Add on 66V
REAR56953BGSM	4.25	Low	Open collector	SOP8	R2 1.25V GND Delay capacitor	Output undefined td ≈ 0.34 x Cd(pF) us
REAR56957AGSM	1.25 (Variable 2 to 15V)	Low	Built-in load	SOP8	Power-supply A: Built-in Load B: Open Collector SµA 25µA 7yp Input Output	egio, 1,25 V
REAR56957BGSM	1.25 (Variable 2 to 15V)	Low	Open collector	SOP8	GND Delay capacitor	td = 0.34 x Cd(pF) µs t
REAR56958BGSM	1.25 (Variable 2 to 15V)	High	Open collector	SOP8	Power-supply Input SjuA 6 Typ Typ Output 1.25V GND Delay capacitor	egg 1.25V egg 1.25V egg 1.25V td ≈ 0.34 x Cd(pF) µs t t t t t t t t t t t t t

Switches & Multiplexers





Renesas' broad portfolio of analog switches and multiplexers (MUX) provide excellent performance across a wide input voltage range. Products include 40V operation down to low voltage USB switching. The following figures and tables only show a fraction of the most commonly preferred analog switches and multiplexers. This portfolio includes single, dual and quad channels of single-pole single-throw and single-pole dual-throw switches, as well as single and dual dual-pole single-throw and dual-pole dual-throw switches, both available in normal-open (NO) and normal-closed (NC) configurations. For selective switching of multiple signal inputs, the input configurations of our multiplexers range from single and dual 4:1 and 8:1 and 16:1.



Data acquisition is the process of sampling signals that measure real-world physical conditions and converting the resulting samples into digital numeric values. Data acquisition circuitry includes sensors that convert physical parameters to electrical signals, signal conditioning circuitry, and analog to digital converters.

Data acquisition applications require analog switch and multiplexer products with low charge injection and parasitic capacitance to minimize switching errors and settling time in the input multiplexer and sample and hold circuits. Renesas offers high performance for these parameters, enabling high sampling rates and accuracy. In addition, Renesas also offers switches with low on-resistance that are suitable for mode switch, filtering, and programmable gain control applications.





Analog Switches

Part Number	Configuration	TON (ns)	TOFF (ns)	Charge Injection (pC)	Drain Cap (pF)	Leakage (nA)	RDS-on (Ω)	Source Cap (pf)	Supply Voltage (V)	IS (μA)
DG403	DPST x 2, NO, NC	100	60	60	39	0.04	20	12	5 to 34, ±5 to ±20	0.01
DG411	SPST x 4, NO	110	100	5	35	0.1	25	9	5 to 34, ±5 to ±20	0.0001
DG412	SPST x 4, NC	110	100	5	35	0.1	25	9	5 to 34, ±5 to ±20	0.0001
DG413	SPST x 4, NO, NC	110	100	5	35	0.1	25	9	5 to 34, ±5 to ±20	0.0001
DG441	SPST x 4, NO	150	90	1	16	0.08	50	4	5 to 34, ±5 to ±20	15
DG444	SPST x 4, NO	120	110	1	16	0.08	50	4	5 to 34, ±5 to ±20	0.001
HI-201	SPST x 4, NO	185	220	10	11	2	55	5.5	±15 (Typ)	500
ISL43120	SPST x 2, NO	25	17	5	21	0.01	11	8	2.7 to 12	0.0001
ISL43141	SPST x 4, NO	40	15	1	14	0.01	50	7	2 to 12, ±2 to ±6	0.05
ISL43144	SPST x 4, NO	52	40	5	34	0.2	18	10	2 to 12, ±2 to ±6	0.01
ISL43L110	SPST x 1, NO	8	5	89	160	30	0.24	68	1.1 to 4.5	0.05
ISL84714	SPDT x 1	7.5	2.9	20	100	2	0.44	40	1.65 to 3.6	0.018
ISL84715	SPST x 4, NO	9	5	70	160	3	0.26	68	1.65 to 3.6	0.018
ISL84053	SPDT x 3	50	40	2	14	0.002	60	3	2 to 12, ±2 to ±6	0.1
SLG47004V	SPST x 2, NO	200 (Pull Down), 625 (Pull Up)	200 (Pull Down), 625 (Pull Up)	N/A	3.6 to 10.2 (depending on the PIN selected)	17	53 (N-ch), 3 (P-ch)	10.2	2.5 (±4%) to 5 (±10%)	N/A

Analog Multiplexers

Part Number	Configuration	TON (ns)	TOFF (ns)	Charge Injection (pC)	Drain Cap (pF)	Leakage (nA)	RDS-on (Ω)	Source Cap (pf)	Supply Voltage (V)	IS (µA)
DG406	1 x 16:1	150	70	40	180	0.04	50	8	5 to 34, ±5 to ±20	0.08
DG408	1 x 8:1	115	105	20	37	1	40	3	5 to 34, ±5 to ±20	0.2
DG409	2 x 4:1	115	105	20	25	1	40	3	5 to 34, ±5 to ±20	0.2
HI-546	1 x 16:1	300	300	4	52	0.1	1200	10	±5 to ±18	0.5
ISL84051	1 x 8:1	50	40	2	26	0.002	60	3	2 to 12, ±2 to ±6	0.0001
ISL84052	2 x 4:1	50	40	2	18	0.002	60	3	2 to 12, ±2 to ±6	0.0001
ISL84781	1 x 8:1	16	14	39	485	15	0.41	65	1.6 to 3.6	0.00005


AnalogPAK™ SLG47004V

Programmable Mixed-Signal Matrix with In-System Programmability and Analog Features

Low energy consumption, miniaturization and functional integration are the main trends in modern consumer electronics. AnalogPAK products perfectly accomplish these requirements.

AnalogPAK embedded high-performance analog blocks, such as operational amplifiers, can be configured and controlled by customer-defined logic functions to implement various Wake/Sleep scenarios as well as improve accuracy. All macrocells are packed in one IC to achieve a high integration level of common analog and digital components.

The SLG47004 builds upon the flexibility of the GreenPAK™ | Renesas traditional mixed-signal solution by integrating a mix of advanced analog features including op amps with programmable bandwidth, 10-bit digital rheostats, analog switches, and a chopper analog comparator. The unique Auto-Trim feature highlights the ability of this GreenPAK device to periodically tune its rheostat value to either compensate for system error sources or



reconfigure circuit parameters. The SLG47004 provides dynamic Power Down control for all analog and digital blocks to optimize power consumption performance. Common applications include sensor interfaces, ADC analog front-ends, configurable amplifiers, tunable filters, and a variety of other analog circuits. This multi-time programmable solution is built into a tiny 3mm x 3mm package.

Product ID	Nominal VDD	GPIOs (#)	Special Features	ACMP Analog Comparator (#)	CNT/DLY (Max) (#)	LUTs (Max) (#)	DFF (Max) (#)	Pipe Delay	# of Programable Delays (#)	Oscillator Type	Temperature Sensor (ch) (#)	Interface	Pkg. Dimensions (mm)
SLG47004	2.4-5.5	8	2x Op Amp or 1x In-Amp, 2x Rheostat, 2x An Switch, 2-Ch Auto-Trim, EEPROM, Pattern Generator	3	7	20	18	16-stage	1	RC OSC, LF OSC, Ring OSC	1	Absolute Voltage, GPIO, I ² C, Switch Output	3.0 x 3.0, TQFN


Winning Combo: Drive Circuit for a Heating or Inductive Coil | Renesas

Software Tool (free and GUI-based): Go Configure™ Software Hub | Renesas

Tools: SLG47004 - Design & Development | Renesas

Application Notes: Documentation & Downloads Search | Renesas Electronics Corporation

How Does AnalogPAK Work in Practice?



MEMO		



Renesas Electronics Corporation TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan

Notice

- Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the
- design of your product or system. Renease Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.

 Renease Electronics hereby expressly disclaims any warranties against and liability for any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renease Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.

- No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.

 You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.

 You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copyring or reverse
- requirements.

 Reneasas Electronics products are classified according to the following two quality grades. "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. "Standard".

 Computers; office equipment; communications equipment, test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc. "High Quality". Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

 - Unless expressly designated as a high preliability product or a product for harsh environments in a Reneasa Electronics advantage leaves the environment of the Reneasa Electronics are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Reneasa Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.
- No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including The property of the property o ACCOMPANYING SOFTWARE OR HARDWARE. INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY. OR FITNESS FOR A PARTICULAR PURPOSE.
- When using Reneasa Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
- Authough Reneasa Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction of Renesas Electronics products, such as safety design for hardware and software, including but not limited to redundancy, fire control and malfunction prevention, appropriate
- retartment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impactical, you are responsible for evaluating the safety of the final protections or systems. Because the evaluation of microcomputer software alone is very difficult and impactical, you are responsible for evaluating the safety of the final protection or systems manufactured by you.

 Please contact a Renessa Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renessa Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renessa Electronics products in compliance with all these applicable laws and regulations. Renessa Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- Reneasa Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.

 It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
- This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics
- Please contact a Renessas Electronics sales office if you have any questions regarding the information contained in this document or Renessas Electronics products to 1) "Renessas Electronics" as used in this document means Renessas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 2020.10)

■Contact Us https://www.renesas.com/contact-us



Renesas Electronics Corporation

www.renesas.com