

RL78/G14

R01AN1505EJ0100

Rev. 1.00

Sep. 17, 2013

Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Abstract

This document describes how to forcibly cut off the pulse output using a combination of the RL78/G14 real-time clock (alarm interrupt function) and the event link controller (ELC).

Products

RL78/G14

When using this application note with other Renesas MCUs, careful evaluation is recommended after making modifications to comply with the alternate MCU.

Contents

1. Specifications	3
2. Operation Confirmation Conditions	3
3. Hardware	4
3.1 Hardware Configuration	4
3.2 Pin Used.....	4
4. Software	5
4.1 Operation Overview	5
4.2 Option Byte Settings	6
4.3 Functions.....	7
4.4 Function Specifications	7
4.5 Flowcharts.....	10
4.5.1 Overall Flowchart.....	10
4.5.2 Initialization	10
4.5.3 Peripheral Function Initialization.....	11
4.5.4 CPU Clock Initialization	12
4.5.5 RTC Initialization.....	13
4.5.6 RTC Start Setting.....	22
4.5.7 RTC Alarm Enable.....	23
4.5.8 ELC Initialization	26
4.5.9 Timer RD0 Initialization.....	27
4.5.10 Timer RD0 Start Setting	37
4.5.11 Main Processing	40
4.5.12 Main Initialization	40
5. Sample Code.....	41
6. Reference Documents.....	41

1. Specifications

In this application note, the PWM signal output from the TRDIOB0 pin is stopped using the pulse output forced cutoff function when an alarm interrupt of the real-time clock (RTC) is generated.

Table 1.1 lists the peripheral functions and their applications. Figure 1.1 shows the relationship among peripheral functions.

Table 1.1 Peripheral Functions and Their Applications

Peripheral Function	Application
RTC	Generates an event using the clock count and alarm interrupt function
ELC	Event source: RTC alarm match detection Event destination: Pulse output forced cutoff of timer RD0
Timer RD (timer RD0)	Outputs a pulse signal in PWM mode




Figure 1.1 Relationship Among Peripheral Functions

2. Operation Confirmation Conditions

The sample code accompanying this application note has been run and confirmed under the conditions below.

Table 2.1 Operation Confirmation Conditions

Item	Contents
MCU used	RL78/G14 (R5F104PJA)
Operating frequencies	<ul style="list-style-type: none"> High-speed on-chip oscillator clock (f_{HOCO}): 32 MHz (typ.) CPU/peripheral hardware clock (f_{CLK}): 32 MHz RTC operating clock (f_{SUB}): 32.768 kHz (typ.)
Operating voltage	5.0 V (operation enabled from 2.9 to 5.5 V) LVD operation (V_{LVI}): 2.81 V at the rising edge or 2.75 V at the falling edge in reset mode
Integrated development environment	Renesas Electronics Corporation CubeSuite+ V1.03.00
C compiler	Renesas Electronics Corporation CA78K0R V1.60
RL78/G14 code library	Renesas Electronics Corporation CodeGenerator for RL78/G14 V1.01.03.06

3. Hardware

3.1 Hardware Configuration

Figure 3.1 shows a connection example.




Figure 3.1 Connection Example

3.2 Pin Used

Table 3.1 lists the pin used and its function.

Table 3.1 Pin Used and Its Function

Pin Name	I/O	Function
P15/TRDIOB0	Output	Outputs PWM signal

4. Software

4.1 Operation Overview

After the RTC is started, an alarm interrupt is generated at the time specified by the alarm function. The ELC outputs a request of the pulse output forced cutoff to timer RD0 using the alarm interrupt as an event. Then, the PWM signal output from the TRDIOB0 pin is stopped.

Settings for the peripheral functions are listed below:

RTC


- Select the subsystem clock (f_{SUB}) as the RTC operating clock
- For 12-/24-hour mode setting, specify 24-hour mode
- Set the initial value as 0:00:00, Tuesday, January 1, 2013
- Set the alarm for 2:00 a.m. every day
- Enable an alarm interrupt (an alarm interrupt is used as a source to activate the ELC)
- Disable the fixed-cycle interrupt

ELC

- Set the alarm match detection as the event source
- Set the pulse output forced cutoff of timer RD0 as the event destination

Timer RD0

- Specify the PWM function as the operating mode
- Select the f_{CLK} (32 MHz) as the count source
- Specify the PWM period as 100 μ s
- Specify the duty cycle as 50%
- Use the TRDIOB0 pin, and set the initial output level as not active, and the output signal level as active high
- Enable the forced cutoff by an event input signal from the ELC
- Disable the INTTRD0 interrupt


Figure 4.1 Timing Diagram

(1) RTC and timer RD0 start, alarm function enabled

Start the RTC and timer RD0, and enable the alarm function.

(2) Alarm match

When the RTC time matches the appointed day of the week and time, an alarm match interrupt is generated.

The ELC outputs a forced cutoff signal to timer RD0 when it detects the alarm match.

PWM signaloutput from timer RD0 is stopped by the pulse forced cutoff function.

4.2 Option Byte Settings

Table 4.1 lists the option byte settings.

Table 4.1 Option Byte Settings

Address	Setting Value	Contents
000C0H/010C0H	11101111B	Stops the watchdog timer (counting is stopped when a reset is canceled)
000C1H/010C1H	01111111B	Sets the LVD in reset mode Detection voltage: 2.81 V at the rising edge, 2.75 V at the falling edge
000C2H/010C2H	11101000B	Sets the HOCO clock as 32 MHz in high-speed main (HS) mode
000C3H/010C3H	10000100B	Enables on-chip debugging

4.3 Functions

Table 4.2 lists the functions.

Table 4.2 Functions

Function Name	Outline
hdwinit	Initialization
R_Systeminit	Peripheral function initialization
R_CGC_Create	CPU clock initialization
R_RTC_Create	RTC initialization
R_RTC_Start	RTC start setting
R_RTC_Set_AlarmOn	RTC alarm enable
R_ELC_Create	ELC initialization
R_TMR_RD0_Create	Timer RD0 initialization
R_TMR_RD0_Start	Timer RD0 start setting
main	Main processing
R_MAIN_UserInit	Main initialization

4.4 Function Specifications

The following tables list the sample code function specifications.

hdwinit	
Outline	Initialization
Header	None
Declaration	void hdwinit(void)
Description	Initializes the peripheral functions.
Arguments	None
Return Value	None

R_Systeminit	
Outline	Peripheral function initialization
Header	None
Declaration	void R_Systeminit(void)
Description	Initializes the peripheral function used in this application note.
Arguments	None
Return Value	None

R_CGC_Create

Outline	CPU clock initialization
Header	r_cg_cgc.h
Declaration	void R_CGC_Create(void)
Description	Initializes the CPU clock.
Arguments	None
Return Value	None

R_RTC_Create

Outline	RTC initialization
Header	r_cg_rtc.h
Declaration	void R_RTC_Create(void)
Description	Initializes the RTC.
Arguments	None
Return Value	None

R_RTC_Start

Outline	RTC start setting
Header	r_cg_rtc.h
Declaration	void R_RTC_Start(void)
Description	Sets the RTC to operation-enabled status.
Arguments	None
Return Value	None

R_RTC_Set_AlarmOn

Outline	RTC alarm enable
Header	r_cg_rtc.h
Declaration	void R_RTC_Set_AlarmOn(void)
Description	Enables the alarm function in operation-enabled status.
Arguments	None
Return Value	None

R_RTC_Create

Outline	ELC initialization
Header	r_cg_elc.h
Declaration	void R_ELC_Create(void)
Description	Initializes the ELC.
Arguments	None
Return Value	None

R_TMR_RD0_Create	
Outline	Timer RD0 initialization
Header	r_cg_timer.h
Declaration	void R_TMR_RD0_Create(void)
Description	Initializes timer RD0 for use in the PWM function.
Arguments	None
Return Value	None
R_TMR_RD0_Start	
Outline	Timer RD0 start setting
Header	r_cg_timer.h
Declaration	void R_TMR_RD0_Start(void)
Description	Sets timer RD0 to operation-enabled status.
Arguments	None
Return Value	None
main	
Outline	Main processing
Header	None
Declaration	void main(void)
Description	Performs the main processing.
Arguments	None
Return Value	None
R_MAIN_UserInit	
Outline	Main initialization
Header	None
Declaration	void R_MAIN_UserInit(void)
Description	Performs processing required to initialize the main processing.
Arguments	None
Return Value	None

4.5 Flowcharts

4.5.1 Overall Flowchart

Figure 4.2 shows the overall flow.




Figure 4.2 Overall Flow

4.5.2 Initialization

Figure 4.3 shows the initialization.




Figure 4.3 Initialization

4.5.3 Peripheral Function Initialization

Figure 4.4 shows the peripheral function initialization.




Figure 4.4 Peripheral Function Initialization

4.5.4 CPU Clock Initialization

Figure 4.5 shows the CPU clock initialization.




Figure 4.5 CPU Clock Initialization

4.5.5 RTC Initialization

Figure 4.6 shows the RTC initialization.




Figure 4.6 RTC Initialization

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Enabling read and write operations for SFRs used by the RTC

- Peripheral enable register 0 (PER0)

Symbol	7	6	5	4	3	2	1	0
PER0	RTCEN	IICA1EN	ADCEN	IICA0EN	SAU1EN	SAU0EN	TAU1EN	TAU0EN
Value	1	x	x	x	x	x	x	x

Bit 7

RTCEN bit	Control of real-time clock (RTC) and 12-bit interval timer input clock supply
0	Stops input clock supply <ul style="list-style-type: none"> SFRs used by the real-time clock (RTC) and 12-bit interval timer cannot be written
1	Enables input clock supply <ul style="list-style-type: none"> SFRs used by the real-time clock (RTC) and 12-bit interval timer can be read and written

Stopping RTC counter operation

- Real-time clock control register 0 (RTCC0)

Symbol	7	6	5	4	3	2	1	0
RTCC0	RTCE	0	RCLOE1	0	AMPM	CT2	CT1	CT0
Value	0	—		—				

Bit 7

RTCE bit	Real-time clock operation control
0	Stops counter operation
1	Starts counter operation

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Disabling the RTC interrupt

- Interrupt mask flag register (MK1H)

Symbol	7	6	5	4	3	2	1	0
MK1H	TMMK10	TRJMK0	SRMK3 CSIMK31 IICMK31	STMK3 CSIMK30 IICMK30	KRMK	ITMK	RTCMK	ADMK
Value	x	x	x	x	x	x	1	x

Bit 1

RTCMK bit	Interrupt servicing control
0	Interrupt servicing enabled
1	Interrupt servicing disabled

- Interrupt request flag register (IF1H)

Symbol	7	6	5	4	3	2	1	0
IF1H	TMIF10	TRJIF0	SRIF3 CSIIF31 IICIF31	STIF3 CSIIF30 IICIF30	KRIF	ITIF	RTCIF	ADIF
Value	x	x	x	x	x	x	0	x

Bit 1

RTCIF bit	Interrupt request flag
0	No interrupt request signal is generated
1	Interrupt request signal is generated, interrupt request status

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Setting the RTC interrupt priority level

- Priority specification flag registers (PR11H, PR01H)

Symbol	7	6	5	4	3	2	1	0
PR11H	TMPR110	TRJPR10	SRPR13 CSIPR131 IICPR131	STPR13 CSIPR130 IICPR130	KRPR1	ITPR1	RTCPR1	ADPR1
Value	x	x	x	x	x	x	1	x

Symbol	7	6	5	4	3	2	1	0
PR01H	TMPR010	TRJPR00	SRPR03 CSIPR031 IICPR031	STPR03 CSIPR030 IICPR030	KRPR0	ITPR0	RTCPR0	ADPR0
Value	x	x	x	x	x	x	1	x

Bit 1

RTCPR1 bit	RTCPR0 bit	Priority level selection
0	0	Specifies level 0 (high priority level)
0	1	Specifies level 1
1	0	Specifies level 2
1	1	Specifies level 3 (low priority level)

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Setting the RTC operation

- Real-time clock control register 0 (RTCC0)
 - Output signals from the RTC1HZ pin: Disabled
 - 12-hour or 24-hour mode: 24-hour mode
 - Fixed-cycle interrupt function: Not used

Symbol	7	6	5	4	3	2	1	0
RTCC0	RTCE	0	RCLOE1	0	AMPM	CT2	CT1	CT0
Value		—	0	—	1	0	0	0

Bit 5

RCLOE1 bit	RTC1HZ pin output control
0	Disables output of the RTC1HZ pin (1 Hz)
1	Enables output of the RTC1HZ pin (1 Hz)

Bit 3

AMPM bit	Selection of 12-/24-hour system
0	12-hour system (a.m. and p.m. are displayed)
1	24-hour system

Bits 2 to 0

CT2 bit	CT1 bit	CT0 bit	Fixed-cycle interrupt (INTRTC) selection
0	0	0	Does not use fixed-cycle interrupt function
0	0	1	Once every 0.5 seconds (synchronized with counting up seconds)
0	1	0	Once per second (same time as counting up seconds)
0	1	1	Once per minute (second 00 every minute)
1	0	0	Once per hour (minute 00 and second 00 every hour)
1	0	1	Once per day (hour 00, minute 00, and second 00 every day)
1	1	×	Once per month (date 1, hour 00 a.m., minute 00, and second 00 every month)

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Configuring the RTC counter

- Second count register (SEC)
Sets the second to 0.

Symbol	7	6	5	4	3	2	1	0
SEC	0	SEC40	SEC20	SEC10	SEC8	SEC4	SEC2	SEC1
Value	–	0	0	0	0	0	0	0

	Function
Bits 6 to 0	Specify a decimal value of 00 to 59 in BCD code

- Minute count register (MIN)
Sets the minute to 0.

Symbol	7	6	5	4	3	2	1	0
MIN	0	MIN40	MIN20	MIN10	MIN8	MIN4	MIN2	MIN1
Value	–	0	0	0	0	0	0	0

	Function
Bits 6 to 0	Specify a decimal value of 00 to 59 in BCD code

- Hour count register (HOUR)
Sets the hour to 0.

Symbol	7	6	5	4	3	2	1	0
HOUR	0	0	HOUR20	HOUR10	HOUR8	HOUR4	HOUR2	HOUR1
Value	–	–	0	0	0	0	0	0

	Function
Bits 5 to 0	Specify a decimal value of 00 to 23, or 01 to 12 or 21 to 32 in BCD code

- Day count register (DAY)
Sets the date to 1.

Symbol	7	6	5	4	3	2	1	0
DAY	0	0	DAY20	DAY10	DAY8	DAY4	DAY2	DAY1
Value	–	–	0	0	0	0	0	1

	Function
Bits 5 to 0	Specify a decimal value of 01 to 31 in BCD code

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; –: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

- Week count register (WEEK)
Sets the day of the week to Tuesday.

Symbol	7	6	5	4	3	2	1	0
WEEK	0	0	0	0	0	WEEK4	WEEK2	WEEK1
Value	—	—	—	—	—	0	1	0

	Function
Bits 2 to 0	Specify a decimal value of 00 to 06 in BCD code

- Month count register (MONTH)
Sets the month to January.

Symbol	7	6	5	4	3	2	1	0
MONTH	0	0	0	MONTH10	MONTH8	MONTH4	MONTH2	MONTH1
Value	—	—	—	0	0	0	0	1

	Function
Bits 4 to 0	Specify a decimal value of 01 to 12 in BCD code

- Year count register (YEAR)
Sets the year to 2013.

Symbol	7	6	5	4	3	2	1	0
YEAR	YEAR80	YEAR40	YEAR20	YEAR10	YEAR8	YEAR4	YEAR2	YEAR1
Value	0	0	0	1	0	0	1	1

	Function
Bits 7 to 0	Specify a decimal value of 00 to 99 in BCD code

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Controlling the alarm

- Real-time clock control register 1 (RTCC1)
 - Alarm match operation: Invalid
 - An interrupt when an alarm matches: Generated

Symbol	7	6	5	4	3	2	1	0
RTCC1	WALE	WALIE	0	WAFG	RIFG	0	RWST	RWAIT
Value	0	1	—			—		

Bit 7

WALE bit	Alarm operation control
0	Match operation is invalid
1	Match operation is valid

Bit 6

WALIE bit	Alarm detection status flag
0	Does not generate interrupt on matching of alarm
1	Generates interrupt on matching of alarm

Setting an alarm

- Alarm minute register (ALARMWM)
 - Sets the minute value to 0.

Symbol	7	6	5	4	3	2	1	0
ALARMWM	0	WM40	WM20	WM10	WM8	WM4	WM2	WM1
Value	—	0	0	0	0	0	0	0

	Function
Bits 6 to 0	Specify a decimal value of 00 to 59 in BCD code

- Alarm hour register (ALARMWH)
 - Sets the hour value to 2.

Symbol	7	6	5	4	3	2	1	0
ALARMWH	0	0	WH20	WH10	WH8	WH4	WH2	WH1
Value	—	—	0	0	0	0	1	0

	Function
Bits 5 to 0	Specify a decimal value of 00 to 23, or 01 to 12 or 21 to 32 in BCD code

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

- Alarm week register (ALARMWW)
Sets the day of the week value to every day.

Symbol	7	6	5	4	3	2	1	0
ALARMWW	0	WW6	WW5	WW4	WM3	WW2	WW1	WW0
Value	–	1	1	1	1	1	1	1

Bits 6 to 0

	Day of the week alarm sounds	Function	
WW6	Saturday	0	Disables an alarm
		1	Enables an alarm
WW5	Friday	0	Disables an alarm
		1	Enables an alarm
WW4	Thursday	0	Disables an alarm
		1	Enables an alarm
WW3	Wednesday	0	Disables an alarm
		1	Enables an alarm
WW2	Tuesday	0	Disables an alarm
		1	Enables an alarm
WW1	Monday	0	Disables an alarm
		1	Enables an alarm
WW0	Sunday	0	Disables an alarm
		1	Enables an alarm

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; –: reserved bit or unallocated bit

4.5.6 RTC Start Setting

Figure 4.7 shows the setting to start RTC counter operation.




Figure 4.7 RTC Start Setting

Starting RTC counter operation

- Real-time clock control register 0 (RTCC0)

Symbol	7	6	5	4	3	2	1	0
RTCC0	RTCE	0	RCLOE1	0	AMPM	CT2	CT1	CT0
Value	1	—		—				

Bit 7

RTCE bit	Real-time clock operation control
0	Stops counter operation
1	Starts counter operation

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

4.5.7 RTC Alarm Enable

Figure 4.8 shows the setting to enable the RTC alarm function.




Figure 4.8 Enabling the RTC Alarm Function

Disabling the RTC interrupt

- Interrupt mask flag register (MK1H)

Symbol	7	6	5	4	3	2	1	0
MK1H	TMMK10	TRJMK0	SRMK3 CSIMK31 IICMK31	STMK3 CSIMK30 IICMK30	KRMK	ITMK	RTCMK	ADMK
Value	x	x	x	x	x	x	1	x

Bit 1

RTCMK bit	Interrupt servicing control
0	Interrupt servicing enabled
1	Interrupt servicing disabled

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Controlling the alarm

- Real-time clock control register 1 (RTCC1)

Symbol	7	6	5	4	3	2	1	0
RTCC1	WALE	WALIE	0	WAFG	RIFG	0	RWST	RWAIT
Value	1		—		x	—	x	x

Bit 7

WALE bit	Alarm operation control
0	Match operation is invalid
1	Match operation is valid

Clearing the alarm detection status flag

- Real-time clock control register (RTCC1)

Symbol	7	6	5	4	3	2	1	0
RTCC1	WALE	WALIE	0	WAFG	RIFG	0	RWST	RWAIT
Value			—	0	x	—	x	x

Bit 4

WAFG bit	Alarm detection status flag
0	Alarm mismatch
1	Detection of matching of alarm

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Enabling the RTC interrupt

- Interrupt request flag register (IF1H)

Symbol	7	6	5	4	3	2	1	0
IF1H	TMIF10	TRJIF0	SRIF3 CSIF31 IICIF31	STIF3 CSIF30 IICIF30	KRIF	ITIF	RTCIF	ADIF
Value	x	x	x	x	x	x	0	x

Bit 1

RTCIF bit	Interrupt request flag
0	No interrupt request signal is generated
1	Interrupt request signal is generated, interrupt request status

- Interrupt mask flag register (MK1H)

Symbol	7	6	5	4	3	2	1	0
MK1H	TMMK10	TRJMK0	SRMK3 CSIMK31 IICMK31	STMK3 CSIMK30 IICMK30	KRMK	ITMK	RTCMK	ADMK
Value	x	x	x	x	x	x	0	x

Bit 1

RTCMK bit	Interrupt servicing control
0	Interrupt servicing enabled
1	Interrupt servicing disabled

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

4.5.8 ELC Initialization

Figure 4.9 shows the ELC initialization.



Figure 4.9 ELC Initialization

Setting the event destination

- Event output destination select register 07 (ELSELR07)

Register Name	Event Generator (Output Origin of Event Input 7)	Event Description
ELSELR07	RTC fixed-cycle signal/alarm match detection	INTRTC

Symbol	7	6	5	4	3	2	1	0
ELSELR07	0	0	0	0	ELSEL3	ELSEL2	ELSEL1	ELSEL0
Value	–	–	–	–	0	1	1	0

Bits 3 to 0

ELSEL3 bit	ELSEL2 bit	ELSEL1 bit	ELSEL0 bit	Event link selection
0	0	0	0	Event link disabled
0	0	0	1	Selects operation of peripheral function to link
0	0	1	0	Selects operation of peripheral function to link
0	0	1	1	Selects operation of peripheral function to link
0	1	0	0	Selects operation of peripheral function to link
0	1	0	1	Selects operation of peripheral function to link
0	1	1	0	Link destination peripheral function: Timer RD0 Operation when an event is acknowledged: TRDIOD0 input capture, pulse output forced cutoff
0	1	1	1	Selects operation of peripheral function to link
1	0	0	0	Selects operation of peripheral function to link
1	0	0	1	Selects operation of peripheral function to link

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; –: reserved bit or unallocated bit

4.5.9 Timer RD0 Initialization

Figure 4.10 and Figure 4.11 show the timer RD0 initialization.





Figure 4.10 Timer RD0 Initialization (1/2)


Figure 4.11 Timer RD0 Initialization (2/2)
Enabling read and write operations for SFRs used by timer RD

- Peripheral enable register 1 (PER1)

Symbol	7	6	5	4	3	2	1	0
PER1	DACEN	TRGEN	CMPEN	TRD0EN	DTCEN	0	0	TRJ0EN
Value	x	x	x	1	x	—	—	x

Bit 4

TRD0EN bit	Control of timer RD input clock supply
0	Stops input clock supply <ul style="list-style-type: none"> SFR used by timer RD cannot be written. Timer RD is in the reset status.
1	Enables input clock supply <ul style="list-style-type: none"> SFR used by timer RD can be read and written.

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

Specifying timer RD0 count operation

- Timer RD start register (TRDSTR)

Symbol	7	6	5	4	3	2	1	0
TRDSTR	0	0	0	0	CSEL1	CSEL0	TSTART1	TSTART0
Value	—	—	—	—	x	1	x	

Bit 2

CSEL0 bit	TRD0 count operation select
0	Count stops at a compare match with TRDGRA0 register
1	Count continues after compare match with TRDGRA0 register

Setting timer RD0 to stop counting

- Timer RD start register (TRDSTR)

Symbol	7	6	5	4	3	2	1	0
TRDSTR	0	0	0	0	CSEL1	CSEL0	TSTART1	TSTART0
Value	—	—	—	—	x		x	0

Bit 0

TSTART0 bit	TRD0 count start flag
0	Count stops
1	Count starts

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Disabling the RD0 interrupt

- Interrupt mask flag register (MK2H)

Symbol	7	6	5	4	3	2	1	0
MK2H	FLMK	IICAMK1	1	SREMK3 TMMK13H	TRGMK	TRDMK1	TRDMK0	PMK11 CMPMK1
Value	x	x	—	x	x	x	1	x

Bit 1

TRDMK0 bit	Interrupt servicing control
0	Interrupt servicing enabled
1	Interrupt servicing disabled

- Interrupt request flag register (IF2H)

Symbol	7	6	5	4	3	2	1	0
IF2H	FLIF	IICAIF1	0	SREIF3 TMIF13H	TRGIF	TRDIF1	TRDIF0	PIF11 CMPIF1
Value	x	x	—	x	x	x	0	x

Bit 1

TRDIF0 bit	Interrupt request flag
0	No interrupt request signal is generated
1	Interrupt request signal is generated, interrupt request status

Enabling ELC event input 0 for timer RD pulse output forced cutoff

- Timer RD ELC register (TRDEL0)

Symbol	7	6	5	4	3	2	1	0
TRDEL0	0	0	ELCOBE1	ELCICE1	0	0	ELCOBE0	ELCICE0
Value	—	—	x	x	—	—	1	x

- Bit 1

ELCOBE0 bit	ELC event input 0 enable for timer RD pulse output forced cutoff
0	Forced cutoff is disabled
1	Forced cutoff is enabled

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Setting registers TRDGRD0 and TRDGRC0 as general registers

- Timer RD mode register (TRDMR)

Symbol	7	6	5	4	3	2	1	0
TRDMR	TRDBFD1	TRDBFC1	TRDBFD0	TRDBFC0	0	0	0	TRDSYNC
Value	x	x	0	0	–	–	–	

Bit 5

TRDBFD0 bit	TRDGRD0 register function select
0	General register
1	Buffer register for TRDGRB0 register

Bit 4

TRDBFC0 bit	TRDGRC0 register function select
0	General register
1	Buffer register for TRDGRA0 register

Specifying the PWM function for timer RD

- Timer RD PWM function select register (TRDPMR)

Symbol	7	6	5	4	3	2	1	0
TRDPMR	0	TRDPWMD1	TRDPWMC1	TRDPWMB1	0	TRDPWMD0	TRDPWMC0	TRDPWMB0
Value	–	x	x	x	–	x	x	1

Bit 0

TRDPWMB0 bit	PWM function of TRDIOB0 select
0	Input capture function or output compare function
1	PWM function

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; –: reserved bit or unallocated bit

Setting the pulse output forced cutoff

- Timer RD digital filter function select register 0 (TRDDF0)
 - TRDIOB0 pin pulse output forced cutoff: High-impedance output
 - TRDIOC0 pin pulse output forced cutoff: Disabled
 - TRDIOD0 pin pulse output forced cutoff: Disabled

Symbol	7	6	5	4	3	2	1	0
TRDDF0	DFCK1	DFCK0	PENB1	PENB0	DFD	DFC	DFB	DFA
Value			0	1	0	0	0	0

Bits 5 and 4

PENB1 bit	PENB0 bit	TRDIOB0 pin pulse forced cutoff control
0	0	Forced cutoff disabled
0	1	High-impedance output
1	0	Low output
1	1	High output

Bits 3 and 2

DFD bit	DFC bit	TRDIOC0 pin digital filter function select
0	0	Forced cutoff disabled
0	1	High-impedance output
1	0	Low output
1	1	High output

- Bits 1 and 0

DFB bit	DFA bit	TRDIOD0 pin digital filter function select
0	0	Forced cutoff disabled
0	1	High-impedance output
1	0	Low output
1	1	High output

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Setting an output from timer RD0

- Timer RD output master enable register 1 (TRDOER1)

Symbol	7	6	5	4	3	2	1	0
TRDOER1	ED1	EC1	EB1	EA1	ED0	EC0	EB0	EA0
Value	x	x	x	x	1	1	0	1

Bit 3

ED0 bit	TRDIOD0 output disable
0	Output enabled
1	Output disabled (TRDIOD0 pin functions as an I/O port)

Bit 2

EC0 bit	TRDIOC0 output disable
0	Output enabled
1	Output disabled (TRDIOC0 pin functions as an I/O port)

- Bit 1

EB0 bit	TRDIOB0 output disable
0	Output enabled
1	Output disabled (TRDIOB0 pin is functions as an I/O port)

- Bit 0

EA0 bit	TRDIOA0 output disable
0	Output enabled
1	Output disabled (TRDIOA0 pin functions as an I/O port)

Setting the initial output level from the TRDIOB0 pin

- Timer RD output control register (TRDOCR)

Symbol	7	6	5	4	3	2	1	0
TRDOCR	TOD1	TOC1	TOB1	TOA1	TOD0	TOC0	TOB0	TOA0
Value	x	x	x	x	x	x	0	x

Bit 1

TOB0 bit	TRDIOB0 initial output level select
0	Low initial output
1	High initial output

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; -: reserved bit or unallocated bit

Controlling timer RD0

- Timer RD control register 0 (TRDCR0)
 - TRD0 counter is cleared by: A compare match with the TRDGRA0 register
 - Count source: fCLK

Symbol	7	6	5	4	3	2	1	0
TRDCR0	CCLR2	CCLR1	CCLR0	CKEG1	CKEG0	TCK2	TCK1	TCK0
Value	0	0	1	×	×	0	0	0

Bits 7 to 5

CCLR2 bit	CCLR1 bit	CCLR0 bit	TRD0 counter clear select
0	0	0	Clear disabled (free-running operation)
0	0	1	Clear by input capture or compare match with TRDGRA0
0	1	0	Clear by input capture or compare match with TRDGRB0
0	1	1	Synchronous clear (clear simultaneously with other timer RD0 counter)
1	0	0	Do not set.
1	0	1	Clear by input capture or compare match with TRDGRC0
1	1	0	Clear by input capture or compare match with TRDGRD0
1	1	1	Do not set.

Bits 2 to 0

TCK2 bit	TCK1 bit	TCK0 bit	Count source select
0	0	0	fCLK, fHOCO
0	0	1	fCLK/2
0	1	0	fCLK/4
0	1	1	fCLK/8
1	0	0	fCLK/32
1	0	1	TRDCLK input
1	1	0	Do not set.
1	1	1	Do not set.

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Setting timer RD0 interrupt source

- Timer RD interrupt enable register 0 (TRDIER0)

Symbol	7	6	5	4	3	2	1	0
TRDIER0	0	0	0	OVIE	IMIED	IMIEC	IMIEB	IMIEA
Value	—	—	—	x	x	x	0	0

Bit 1

IMIEB bit	Input capture/compare match interrupt enable B
0	Interrupt (IMIB) by the IMFB bit (IMIB) is disabled
1	Interrupt (IMIB) by the IMFB bit (IMIB) is enabled

Bit 0

IMIEA bit	Input capture/compare match interrupt enable A
0	Interrupt (IMIA) by the IMFA bit (IMIA) is disabled
1	Interrupt (IMIA) by the IMFA bit (IMIA) is enabled

Setting the output signal level from the TRDIOB0 pin

- Timer RD PWM function output level control register 0 (TRDPOCR0)

Symbol	7	6	5	4	3	2	1	0
TRDPOCR0	0	0	0	0	0	POLD	POLC	POLB
Value	—	—	—	—	—	x	x	1

Bit 0

POLB bit	PWM function output level control B
0	TRDIOB0 output signal level is low active
1	TRDIOB0 output signal level is high active

Setting the PWM period

- Timer RD general register A0 (TRDGRA0)
Specifies the PWM period as 100 μ s

Symbol	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
TRDGRA0	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—
Value	3199															

	Function
Bits 15 to 0	General register. Set the PWM period.

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Setting the changing point of PWM output

- Timer RD general register B0 (TRDGRB0)
Specifies the changing point of the PWM output signal as 50 μ s.

Symbol	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
TRDGRB0	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–	–
Value	1599															

	Function
Bits 15 to 0	General register. Set the changing point of the PWM output signal.

Setting the TRDIOB0 pin

- Port register 1 (P1)

Symbol	7	6	5	4	3	2	1	0
P1	P17	P16	P15	P14	P13	P12	P11	P10
Value	x	x	0	x	x	x	x	x

Bit 5

P15 bit	Function
0	Outputs 0
1	Outputs 1

- Port mode register 1 (PM1)

Symbol	7	6	5	4	3	2	1	0
PM1	PM17	PM16	PM15	PM14	PM13	PM12	PM11	PM10
Value	x	x	0	x	x	x	x	x

Bit 5

PM15 bit	Function
0	Output mode (output buffer on)
1	Input mode (output buffer off)

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

x: Unused bit; blank cell: unchanged bit; –: reserved bit or unallocated bit

4.5.10 Timer RD0 Start Setting




Figure 4.12 Setting Timer RD0 to Start

Clearing the timer RD0 status flag

- Timer RD status register (TRDSR0)

Symbol	7	6	5	4	3	2	1	0
TRDSR0	0	0	0	OVF	IMFD	IMFC	IMFB	IMFA
Value	—	—	—	0	0	0	0	0

Bit 4

OVF bit	Overflow flag
Condition to be 0: Write 0 after reading the bit	
Condition to be 1: When the TRD0 register overflows	

- Bit 3

IMFD bit	Input capture/compare match flag D
Condition to be 0: Write 0 after reading the bit	
Condition to be 1: When the values in registers TRD0 and TRDGRD0 match	

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

Bit 2

IMFC bit	Input capture/compare match flag C
Condition to be 0: Write 0 after reading the bit	
Condition to be 1: When the values in registers TRD0 and TRDGRC0 match	

Bit 1

IMFB bit	Input capture/compare match flag B
Condition to be 0: Write 0 after reading the bit	
Condition to be 1: When the values in registers TRD0 and TRDGRB0 match	

Bit 0

IMFA bit	Input capture/compare match flag A
Condition to be 0: Write 0 after reading the bit	
Condition to be 1: When the values in registers TRD0 and TRDGRA0 match	

Specifying timer RD0 count operation

- Timer RD start register (TRDSTR)

Symbol	7	6	5	4	3	2	1	0
TRDSTR	0	0	0	0	CSEL1	CSEL0	TSTART1	TSTART0
Value	—	—	—	—	×	1	×	

Bit 2

CSEL0 bit	TRD0 count operation select
0	Count stops after compare match with TRDGRA0 register
1	Count continues after compare match with TRDGRA0 register

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC

Starting timer RD0 count operation

- Timer RD start register (TRDSTR)

Symbol	7	6	5	4	3	2	1	0
TRDSTR	0	0	0	0	CSEL1	CSEL0	TSTART1	TSTART0
Value	—	—	—	—	×		×	1

Bit 0

TSTART0 bit	TRD0 count start flag
0	Count stops
1	Count starts

For details on register setting, refer to the RL78/G14 User's Manual: Hardware.

Legend symbol:

×: Unused bit; blank cell: unchanged bit; —: reserved bit or unallocated bit

4.5.11 Main Processing

Figure 4.13 shows the main processing.




Figure 4.13 Main Processing

4.5.12 Main Initialization

Figure 4.14 shows the main initialization.




Figure 4.14 Main Initialization

5. Sample Code

Sample code can be downloaded from the Renesas Electronics website.

6. Reference Documents

User's Manual

RL78/G14 User's Manual: Hardware Rev.1.00

RL78 Family User's Manual: Software Rev.1.00

The latest versions can be downloaded from the Renesas Electronics website.

Technical Update/Technical News

The latest information can be downloaded from the Renesas Electronics website.

Website and Support

Renesas Electronics website

<http://www.renesas.com>

Inquiries

<http://www.renesas.com/contact/>

REVISION HISTORY	RL78/G14 Pulse Output Forced Cutoff Using the Clock Alarm Function and ELC
-------------------------	---

Rev.	Date	Description	
		Page	Summary
1.00	Sep. 17, 2013	—	First edition issued

All trademarks and registered trademarks are the property of their respective owners.

General Precautions in the Handling of MPU/MCU Products

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Handling of Unused Pins

Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.

- The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.

2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.

In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

- The reserved addresses are provided for the possible future expansion of functions. Do not access these addresses; the correct operation of LSI is not guaranteed if they are accessed.

4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable.

When switching the clock signal during program execution, wait until the target clock signal has stabilized.

- When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.

5. Differences between Products

Before changing from one product to another, i.e. to one with a different type number, confirm that the change will not lead to problems.

- The characteristics of an MPU or MCU in the same group but having a different part number may differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a system-evaluation test for the given product.

Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.
"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.
Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.
6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SALES OFFICES

Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

Renesas Electronics America Inc.

2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A.
Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited

1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada
Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K
Tel: +44-1628-651-700, Fax: +44-1628-651-804

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany
Tel: +49-211-65030, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd.

7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.

Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd., Pudong District, Shanghai 200120, China
Tel: +86-21-5877-1818, Fax: +86-21-6887-7858 / -7898

Renesas Electronics Hong Kong Limited

Unit 1601-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2886-9318, Fax: +852 2886-9022/9044

Renesas Electronics Taiwan Co., Ltd.

13F, No. 363, Fu Shing North Road, Taipei, Taiwan
Tel: +886-2-8175-9600, Fax: +886 2-8175-9670

Renesas Electronics Singapore Pte. Ltd.

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre Singapore 339949
Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.

Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd.

11F., Samik Lavied' or Bldg., 720-2 Yeoksam-Dong, Kangnam-Ku, Seoul 135-080, Korea
Tel: +82-2-558-3737, Fax: +82-2-558-5141