HA1630S07 Single CMOS High Drive Operational Amplifier

R03DS0083EJ0200 Rev.2.00 Jan 10, 2014

Description

HA1630S07 is a low power single CMOS operational amplifier featuring high output current with typical current supply of 60 μ A (2.7 V to 5.5 V). This IC designed to operate from a single power supply and have full swing outputs. Available in CMPAK-5 and MPAK-5 package, the miniature size of this IC not only allows compact integration in portable devices but also minimizes distance of signal sources (sensors), thus reducing external noise pick up prior to amplification. This IC exhibit excellent current drive-power ratio capable of 2 k Ω load driving and yet resistant to oscillation for capacitive loads up to 200 pF.

Features


- Low supply current $I_{DD} = 60 \ \mu A \ Typ \ (V_{DD} = 3 \ V, R_L = No \ load)$
- Low voltage operation $V_{DD} = 2.7 \text{ V to } 5.5 \text{ V}$
- Low input offset voltage $V_{IO} = 6 \text{ mV Max}$
- Low input bias current $I_{IB} = 1 \text{ pA Typ}$
- High output current $I_{OSOURCE} = 15 \text{ mA Typ} (V_{DD} = 3.0 \text{ V}, V_{OH} = 2.5 \text{ V})$
 - $I_{OSINK} = 15 \text{ mA Typ} (V_{DD} = 3.0 \text{ V}, V_{OL} = 0.5 \text{ V})$
- Input common voltage range includes ground

Ordering Information


Part No.	Package Name	Package Code
HA1630S07CM	CMPAK-5	PTSP0005ZC-A
HA1630S07LP	MPAK-5	PLSP0005ZB-A



Pin Arrangement



Equivalent Circuit





Absolute Maximum Ratings

(Ta =	25°C)
-------	-------

Item	Symbol	Ratings	Unit	Note
Supply voltage	V _{DD}	7.0	V	
Differential input voltage	V _{IN(diff)}	$-V_{DD}$ to $+V_{DD}$	V	1
Input voltage	V _{IN}	-0.1 to +V _{DD}	V	
Output current	lout	40	mA	
Power dissipation	PT	80 (CMPAK-5)	mW	2
		120 (MPAK-5)		
Operating temperature	Topr	-40 to +85	°C	
Storage temperature	Tstg	-55 to +125	°C	

Note: 1. Do not apply input voltage exceeding V_{DD} or 7 V.

2. If Ta > 25°C,

CMPAK-5: -0.8 mW/°C MPAK-5: -1.2 mW/°C

Electrical Characteristics

DC Characteristics

					(Ta = 25	$^{\circ}$ C, V _{DD} = 3.0 V, V _{SS} = 0 V)
Item	Symbol	Min	Тур	Max	Unit	Test Conditions
Input offset voltage	V _{IO}	—	_	6	mV	V_{IN} = 1.5 V, R_L = 1 M Ω
Input bias current	I _{IB}	—	(1)	—	pА	V _{IN} = 1.5 V
Input offset current	I _{IO}	—	(1)	—	pА	V _{IN} = 1.5 V
Common mode input voltage range	V _{CM}	-0.1	_	1.8	V	
Supply current	I _{DD}	_	60	170	μΑ	$V_{IN(+)} = 1.0 \text{ V}, \text{ R}_{L} = \infty$
Output source current	IOSOURCE	7.5	15	—	mA	V _{OUT} = 2.5 V
Output sink current	I _{OSINK}	7.5	15	—	mA	V _{OUT} = 0.5 V
Open loop voltage gain	Av	55	80	—	dB	R _L = 100 kΩ
Common mode rejection ratio	CMRR	50	80	—	dB	$V_{IN1} = 0 V, V_{IN2} = 1.8 V$
Power supply rejection ratio	PSRR	55	80	—	dB	$V_{DD1} = 2.7 \text{ V}, V_{DD2} = 5.5 \text{ V}$
Output high voltage	V _{OH}	2.9		—	V	$R_L = 2 k\Omega$ to V_{SS}
Output low voltage	V _{OL}	—	—	0.1	V	$R_L = 2 k\Omega$ to V_{DD}

Note: (): Design specification

AC Characteristics

 $(Ta = 25^{\circ}C, V_{DD} = 3.0 V, V_{SS} = 0 V)$

					(1a - 23)	$C, V_{DD} = 5.0 V, V_{SS} = 0 V$
Item	Symbol	Min	Тур	Max	Unit	Test Conditions
Slew rate	SRr	—	(1)		V/µs	$V_{IN} = 1.5 V, C_L = 15 pF$
	SRf	_	(1)			$(V_{INL} = 0.2 \text{ V}, V_{INH} = 1.7 \text{ V})$
Gain bandwidth product	GBW	—	(1.5)		MHz	$V_{IN} = 1.5 V, C_L = 15 pF$

Note: (): Design specification




Table of Graphs

Electrical Cl	naracteristics		Characteristic Curves	Test Circuit No.
Supply current	I _{DD}	vs. Supply voltage	1	1
		vs. Temperature	2	1
Output high voltage	V _{OH}	vs. Rload	3	2
Output low voltage	V _{OL}	vs. Rload	4	3
Output source current	IOSOURCE	vs. Output high voltage	5	4
		vs. Temperature	6	4
Output sink current	I _{OSINK}	vs. Output low voltage	7	5
		vs. Temperature	8	5
Input offset voltage	V _{IO}	vs. Supply voltage	9	6
		vs. Input voltage	10	6
		vs. Temperature	11	7
Common mode input voltage range	V _{CM}	vs. Supply voltage	12	8
		vs. Temperature	13	8
Common mode rejection ratio	CMRR	vs. Input voltage	14	9
Power supply rejection ratio	PSRR	vs. Supply voltage	15	10
Input bias current	I _{IB}	vs. Input voltage	16	11, 12
		vs. Temperature	17	11, 12
Slew rate (rising)	SRr	vs. Cload	18	13
		vs. Temperature	19	13
		Time waveform	20	13
Slew rate (falling)	SRf	vs. Cload	21	13
		vs. Temperature	22	13
		Time waveform	23	13
Open loop gain	Av	vs. Rload	24	14
		vs. Frequency	25, 26	14
Phase margin	PM	vs. Cload	27	14
Noise input voltage	VNI	vs. Frequency	28	15




Test Circuits






Test Circuits (cont.)

(Unless otherwise noted, $V_{DD} = 3 \text{ V}$, $V_{SS} = 0 \text{ V}$, $Ta = 25^{\circ}\text{C}$)




Test Circuits (cont.)


(Unless otherwise noted, $V_{DD} = 3 \text{ V}$, $V_{SS} = 0 \text{ V}$, $Ta = 25^{\circ}\text{C}$)








Characteristic Curves
















Package Dimensions

JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
SC-88A	PTSP0005ZC-A	CMPAK-5 / CMPAK-5V	0.006










A-A Section


Reference	Dimensions in millimeters			
Symbol	Min	Nom	Max	
Α	0.8		1.1	
A ₁	0		0.1	
A ₂	0.8	0.9	1.0	
A ₃		0.25		
b	0.15	0.22	0.3	
С	0.1	0.13	0.15	
D	1.8	2.0	2.2	
E	1.15	1.25	1.35	
е		0.65		
HE	1.8	2.1	2.4	
L	0.3		0.7	
L ₁	0.1		0.5	
Lp	0.2		0.6	
Х			0.05	
У			0.05	
Q		0.25		


© 2013 Renesas Electronics Corporation. All rights reserved.




JEITA Package Code	RENESAS Code	Previous Code	MASS (Typ) [g]
SC-74A	PLSP0005ZB-A	MPAK-5 / MPAK-5V	0.015










Reference	Dimensions in millimeters			
Symbol	Min	Nom	Max	
A	1.0		1.4	
A ₁	0		0.1	
A ₂	1.0	1.1	1.3	
A ₃		0.25		
b	0.35	0.4	0.5	
С	0.11	0.16	0.26	
D	2.8	2.95	3.1	
E	1.5	1.6	1.8	
е	—	0.95	—	
HE	2.5	2.8	3.0	
L	0.3		0.7	
L ₁	0.1		0.5	
LP	0.2		0.6	
Х			0.05	
у			0.05	
Q		0.3		


© 2013 Renesas Electronics Corporation. All rights reserved.



Taping & Reel Specification



Mark Indication





Notice

- Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or
- technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.

Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics may way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.

- 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
- 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations.
- 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



SALES OFFICES

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics Corporation

http://www.renesas.com

Renesas Electronics America Inc. 2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A. Tel: +1-40-588-8000, Fax: +1-408-588-6130 Renesas Electronics Canada Limited 1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada Tel: +1-905-989-5441, Fax: +1-905-898-3220 Renesas Electronics Europe Limited Dukes Meadow, Milboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-651-700, Fax: +44-1628-651-804 Renesas Electronics Europe GmbH Arcadiastrasse 10, 40472 Düsseldorf, Germany Tel: +49-211-65030, Fax: +44-1628-651-804 Renesas Electronics (Shanghai) Co., Ltd. 7th Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China Tel: +86-10-235-1155, Fax: +86-10-235-7679 Renesas Electronics (Shanghai) Co., Ltd. 7th Floor, Quantum Towers, 565 LanGao Rd., Putuo District, Shanghai, China Tel: +86-10-235-1155, Fax: +86-21-2226-0989 Renesas Electronics Hong Kong Limited Unit 1001-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +88-08-286-9318, Fax: +88-21-2226-0999 Renesas Electronics Indentry Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +88-08-08-090, Fax: +88-29-0229044 Renesas Electronics Hong Kong Limited Unit 1001-1613, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong Tel: +88-0-800, Fax: +886 2-8175-9670 Renesas Electronics Magayai Sdn.Bhd. 011 906, Blook, B., Menara : 4856-21000, Fax: +86-521-3000 Renesas Electronics Malaysia Sdn.Bhd. 011 906, Blook, B., Menara : 465-621-3000 Renesas Electronics Kong Anoop Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia Tel: +60-3-7955-9390, Fax: +60-3-7955-9510 Renesas Electronics Kong Co., Ltd. 17, 234 Tehteran-ro, Gangam-Gu, Seoul, 135-080, Korea Tel: +60-3-7955-9390, Fax: +60-3-7955-9510