

mPD166035GR

INTELLIGENT POWER DEVICE

R07DS1117EJ0200 Rev.2.00 Jul 31, 2014

Description

The mPD166035 is an N-channel high side driver with built-in charge pump and embedded protection function.

When device is overtemperature or overcurrent is generated in output MOS, the protection function operates to prevent destruction and degradation of the product, and also outputs self-diagnostic signal.

Features

- High temperature operation ($T_{ch} = 175^{\circ}C$ MAX.)
- · Built-in charge pump circuit
- · Low on-state resistance

 $R_{DS(ON)} = 80 \text{ mWMAX.}$ $(V_{IN} = V_{IH}, I_O = 1.5A, Tch = 25^{\circ}C)$

- · Built-in protection circuit
 - 3/4 Current limitation
 - 3/4 Overtemperature protection
- · Active clamp operation at inductive load switch off
- · Built-in diagnostic function
- · Package: Power SOP 8


Application

· Switching of all types of 14 V DC grounded loads, such as inductor, resistor and capacitor

Ordering Information


Part No.	Lead Plating	Packing	Package
mPD166035GR-E1-AY	Sn	Tape 2500 p/reel	Power SOP 8
mPD166035GR-E2-AY	Sn	Tape 2500 p/reel	Power SOP 8

Block Diagram



Pin Configuration

· Power SOP 8



Pin Functions

Pin No.	Pin Name	Function		
1	IN	Input pin		
2	DIAG	DIAG output pin		
3	GND	Ground pin		
4	OUT	High side output pin		
5	VCC	Power supply pin		
6	VCC	Power supply pin		
7	VCC	Power supply pin		
8	VCC	Power supply pin		

Absolute Maximum Ratings

 $(Ta = 25^{\circ}C, unless otherwise specified)$

Item	Symbol	Rating	Unit	Condition
Power supply voltage	V _{CC1}	-0.3 to +28	V	
	V _{CC2}	35	V	t = 300 ms
IN input voltage	V _{IN1}	-0.5 to +5.5	V	
	V _{IN2}	5	V	$V_{CC} = 0 \text{ V}, t = 0.5 \text{ s}$
IN input current	I _{IN}	±10	mA	
Output current	I _{OA}	2	А	
Output negative voltage	Voa	V _{CC} -30	V	Without dynamic clamp
Power dissipation	P _D	2.70	W	T _a = 25°C Note
Operation temperature	Topt	-40 to +125	°C	
Storage temperature	Tstg	-55 to +175	°C	
DIAG output voltage	V _{DIAG}	7.0	V	
DIAG output current	I _{DIAG}	10	mA	
Clamp susceptibility	E _{CLP}	100	mJ	

Note: When mounted on a epoxy PCB (where FR-4 is 10 cm ´ 10 cm, dimension of copper foil is 15% and thickness of copper foil is 35 mm), PW = 10 s

Electrical Characteristics


 $(V_{CC} = 8 \text{ to } 16 \text{ V}, \text{Tch} = -40 \text{ to } +175^{\circ}\text{C}, \text{ unless otherwise specified})$

Item	Symbol	MIN.	TYP.	MAX.	Unit	Condition	
Input voltage	V _{IH}	2.8		5.5	V	V _{CC} = 4.5 to 16 V	
	V _{IL}	0		1.5	V		
Input current	I _{IH}	_		350	mΑ	V _{IN} = 5.5 V	
	I _{IL}	-10		_	mΑ	V _{IN} = 0 V	
Standby current	Іссн	_	_	4.0	mA	V _{IN} = V _{IH} Note 1	
	I _{CCL}	_		900	mΑ	V _{IN} = V _{IL} Note 1	
Output leakage current	I _{OH1}	_	_	2	mA	$V_{IN} = V_{IL}, V_O = V_{CC}$	
	I _{OH2}	_		0.4	mA	$V_{IN} = V_{IL}, V_O = 4V$	
	I _{OL}	-0.24	_	_	mA	$V_{IN} = V_{IL}, V_O = 0V$	
DIAG output low level voltage	V _{DIAG}	_	_	0.5	V	$V_{CC} = 4.5$ to 16V, $I_{DIAG} = 0.6$ mA	
DIAG output leakage current	I _{DIAG}	_	_	10	mA	$V_{DIAG} = 7V$	
Open load detection voltage	Voih	4	_	_	V		
Load connection detection voltage	Voll	_	_	1.45	V		
Drain to source on-state	R _{DS(ON)}	_	_	80	mW	$V_{IN} = V_{IH}, I_O = 1.5A$ Tch = 25°C	
resistance		_	_	130	mW	Tch = 150°C	
Overcurrent detection	Is	2	_	10	Α		
Overtemperature detection	Tth	(175)	_	_	°C	Note 2	
Turn on delay time	t _{D(ON)}	_	4	200	ms	$R_L = 9.3W$, $V_{CC} = 14V$, $V_{IN} = 5.5V-0V$	
Turn off delay time	t _{D(OFF)}	_	30	200	ms		
Rise time	ton	_	24	100	ms		
Fall time	t _{OFF}	_	5	100	ms		
DIAG Output Delay	t _{Dpd}	_	_	300	ms	$R_L = 9.3\Omega$, $R_{DIAG} = 5.1k\Omega$, $V_{CC} = 14V$	
Time							
Negative Output Voltage	-V _O	V _{CC} -30	_	V _{CC} -40	V	Io=-60mA	
Output Oscillation Cycle at over current condition	ts	_	_	14	ms	Overcurrent condition	
Output On Duty at over current condition	Ds	_		30	%	Overcurrent condition	

Notes: 1. OUT, DIAG current is not included.

2. Not subject to production test, specified by design.

Definition of Switching Time



Truth Table

ltem	V _{IN}	V _{OUT}	V_{DIAG}
Normal operation	Н	Н	Н
	L	L	L
Overtemperature detection	Н	L	L
	L	L	L
Overcurrent detection	Н	Chopping	L
	L	L	L
Open load detection	Н	Н	Н
	L	Н	Н


Outline of Functions

Pre-Driver (Charge Pump Circuit) ON/OFF Control

When the input voltage of the input pin (IN) is high level (2.8 V or more), the output MOS (Nch) turns on.

When the output voltage of the input pin (IN) is low level (1.5 V or less), the output MOS (Nch) turns off.

Charge pump circuit is built-in to drive the output MOS (Nch) that is connected to the high side.



Overcurrent Detection Circuit

This circuit detects overcurrent to output pin (OUT) caused by short circuit etc., and feeds back detection signal to control circuit.

When the overcurrent is detected, the current limitation circuit and the control circuit start operation. The output current is restricted and chopping operation begins.


Current Limitation Circuit

This circuit limits the output current by using the detection signal from the overcurrent detection circuit, preventing destruction and degradation of the product.

Overtemperature Detection Circuit

This circuit detects overtemperature by output MOS (Nch) driving, and feeds back detection signal to control circuit.


When the circuit detects overtemperature, the protection function of the control circuit operates and output is shutdown. Output MOS (Nch) automatically restarts when channel temperature cools down after shutdown.



Open Load Detection Circuit

This circuit detects Open Load of output terminal. However, In case of using Open Load detection function, it is necessary to connect pull-up resistor $(5.1 \text{Kohm} \pm 10\%)$ with output terminal. (There are no electric characteristics influences in other circuit by presence of pull-up resistor.)


Open Load is detected by inputting low-level (1.5V or less) to input terminal (IN). DAIG terminal outputs Hi-Z (pull-up: high-level) when the output terminal is open.




Diagnostic Output Circuit

This circuit controls output of diagnostic signal form DIAG terminal when over current or over temperature or Open Load is detected.


Timing Chart





Example of Application Circuit





Typical Characteristics






















Ta - Ambient Temperature - °C




















































Transient Thermal Resistance Characteristics




Package Drawing




Taping Information

There are two types (-E1, -E2) of taping depending on the direction of the device.



Marking Information

This figure indicates the marking items and arrangement. However, details of the letterform, the size and the position aren't indicated.



Recommended Soldering Conditions

The mPD166035 should be soldered and mounted under the following recommended conditions.

For soldering methods and conditions other than those recommended below, contact a Renesas Electronics sales representative.

For technical information, see the following website.

Semiconductor Package Mount Manual (http://www.renesas.com/products/package/manual/index.jsp)

- mPD166035GR-E1-AY Note: Power SOP 8
- mPD166035GR-E2-AY Note: Power SOP 8

Process	Conditions	Symbol		
Infrared reflow	red reflow Maximum temperature (package's surface temperature): 260°C or below,			
	Time at maximum temperature: 10 seconds or less,			
	Time at temperature higher than 220°C: 60 seconds or less,			
	Preheating time at 160°C to 180°C: 60 to 120 seconds, Times: Three times,			
	Flux: Rosin flux with low chlorine (0.2 Wt% or below) recommended.			
Partial Heating	Pin temperature: 300°C or below,	_		
Method	Heat time: 3 seconds or less (Per each side of the device),			
	Flux: Rosin flux with low chlorine (0.2 Wt% or below) recommended.			

Note: Pb-free (This product does not contain Pb in the external electrode.)

Revision History

mPD166035GR Data Sheet

		Description			
Rev.	Date	Page	Page Summary		
1.00	Sep 20, 2013	_	First Edition Issued		
2.00	Jul 31, 2014	3	Absolute Maximum Ratings: IN input voltage(V _{IN1})		
			Change "-0.5V to +5.6V" to "-0.5V to +5.5V".		
		4	Negative Output Voltage: Change "mA" to "V".		
		5	Definition of Switching Time (tDpd): Change "90%" to "50%".		
		9	Output Leakage Current: Change "A" to "mA".		
		10	Output Leakage Current: Change "A" to "mA".		
		15	Semiconductor Package Mount Manual: Change URL.		

Notice

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 2. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein
- 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or
- 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.

Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application for which it is not intended. Renesas Electronics shall not be in any way liable for any damages or losse incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics

- 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the ise of Renesas Electronics products beyond such specified ranges.
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
- 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations
- 10. It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries. (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics



SALES OFFICES

Renesas Electronics Corporation

http://www.renesas.com

Refer to "http://www.renesas.com/" for the latest and detailed information

Renesas Electronics America Inc. 2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A. Tel: +1-408-588-6000, Fax: +1-408-588-6130

Renesas Electronics Canada Limited 1101 Nicholson Road, Newmarket, Ontario L3Y 9C3, Canada Tel: +1-905-898-5441, Fax: +1-905-898-3220

Renesas Electronics Europe Limited Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K Tel: +44-1628-585-100, Fax: +44-1628-585-900

Renesas Electronics Europe GmbH

Arcadiastrasse 10, 40472 Düsseldorf, Germany Tel: +49-211-6503-0, Fax: +49-211-6503-1327

Renesas Electronics (China) Co., Ltd. Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China Tei: +86-10-2035-1155, Fax: +86-10-8235-7679

Renesas Electronics (Shanghai) Co., Ltd.
Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

Renesas Electronics Hong Kong Limited
Unit 1601-1613, 161F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: +852-2856-5688, Fax: +852 2886-9022/9044

Renesas Electronics Taiwan Co., Ltd. 13F, No. 363, Fu Shing North Road, Taipei 105-Tel: +886-2-8175-9600, Fax: +886 2-8175-9670 . ipei 10543, Taiwan

Renesas Electronics Singapore Pte. Ltd. 80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949 Tel: +65-6213-0200, Fax: +65-6213-0300

Renesas Electronics Malaysia Sdn.Bhd.
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

Renesas Electronics Korea Co., Ltd. 12F., 234 Teheran-ro, Gangnam-Ku, Seoul, 135-920, Korea Tel: +82-2-558-3737, Fax: +82-2-558-5141