RENESAS

RL78/G12

RENESAS MCU

True low-power platform (63 μ A/MHz) for the general-purpose applications, with 1.8-V to 5.5-V operation, 2- to 16-Kbyte code flash memory, and 31 DMIPS at 24 MHz

1. OUTLINE

1.1 Features

Ultra-low power consumption technology

- V_{DD} = single power supply voltage of 1.8 to 5.5 V which can operate at a low voltage
- HALT mode
- STOP mode
- SNOOZE mode

RL78 CPU core

- CISC architecture with 3-stage pipeline
- Minimum instruction execution time: Can be changed from high speed (0.04167 μs: @ 24 MHz operation with high-speed on-chip oscillator) to ultra-low speed (1 μs: @ 1 MHz operation)
- Address space: 1 MB
- General-purpose registers: (8-bit register x 8) x 4 banks
- On-chip RAM: 256 B to 2 KB
- Code flash memory
- Code flash memory: 2 to 16 KB
- Block size: 1 KB
- Prohibition of block erase and rewriting (security function)
- On-chip debug function
- Self-programming (with flash shield window function)

Data flash memory Note2

- Data flash memory: 2 KB
- Back ground operation (BGO): Instructions are executed from the program memory while rewriting the data flash memory.
- Number of rewrites: 1,000,000 times (TYP.)
- Voltage of rewrites: V_{DD} = 1.8 to 5.5 V

High-speed on-chip oscillator

- Select from 24 MHz, 16 MHz, 12 MHz, 8 MHz, 6 MHz, 4 MHz, 3 MHz, 2 MHz, and 1 MHz
- High accuracy: +/- 1.0 % (V_{DD} = 1.8 to 5.5 V, T_A = -20 to +85 °C)

Operating ambient temperature

- T_A = -40 to +85 °C (A: Consumer applications, D: Industrial applications)
- T_A = -40 to +105 °C (G: Industrial applications) ^{Note2}

Power management and reset function

- On-chip power-on-reset (POR) circuit
- On-chip voltage detector (LVD) (Select interrupt and reset from 12 levels)

DMA (Direct Memory Access) controller Note2

- 2 channels
- Number of clocks during transfer between 8/16-bit SFR and internal RAM: 2 clocks

Multiplier and divider/multiply-accumulator

- 16 bits x 16 bits = 32 bits (Unsigned or signed)
- 32 bits x 32 bits = 32 bits (Unsigned)
- 16 bits x 16 bits + 32 bits = 32 bits (Unsigned or signed)

Serial interface

- Simplified SPI (CSI Note1):
- UART

- : 1 to 3 channels
 - : 1 to 3 channels : 0 to 3 channels
- Simplified I²C communication I²C communication
 - : 1 channel

Timer

- 16-bit timer : 4 to 8 channels
 - 12-bit interval timer : 1 channel
 - Watchdog timer : 1 channe
 - : 1 channel (operable with the dedicated low-speed on-chip oscillator)

A/D converter

- 8/10-bit resolution A/D converter (VDD = 1.8 to 5.5 V)
- 8 to 11 channels, internal reference voltage (1.45 V), and temperature sensor Note2

I/O port

- I/O port: 18 to 26
- (N-ch open drain I/O [withstand voltage of 6 V]: 2, N-ch open drain I/O [V_DD withstand voltage]: 4 to 9)
- Can be set to N-ch open drain, TTL input buffer, and on-chip pull-up resistor
- Different potential interface: Can connect to a 1.8/2.5/3
 V device
- On-chip key interrupt function
- On-chip clock output/buzzer output controller

Others

- On-chip BCD (binary-coded decimal) correction circuit
- **Note 1.** Although the CSI function is generally called SPI, it is also called CSI in this product, so it is referred to as such in this manual.
- Note 2. Can be selected only in HS (high-speed main) mode.
- Remark The functions mounted depend on the product. See 1.7 Outline of Functions.

Datasheet

R01DS0193EJ0240 Rev.2.40 Mar 29, 2024

Code flash	Data flash	RAM	20 pins	24 pins	30 pins
16 KB	2 KB	2 KB	_	_	R5F102AA
	_		_	_	R5F103AA
	2 KB	1.5 KB	R5F1026A Note 1	R5F1027A Note 1	_
	-		R5F1036A Note 1	R5F1037A Note 1	_
12 KB	2KB	1 KB	R5F10269 Note 1	R5F10279 Note 1	R5F102A9
	_		R5F10369 Note 1	R5F10379 Note 1	R5F103A9
8 KB	2 KB	768 B	R5F10268 Note 1	R5F10278 Note 1	R5F102A8
	-		R5F10368 Note 1	R5F10378 Note 1	R5F103A8
4 KB	2KB	512 B	R5F10267	R5F10277	R5F102A7
	-		R5F10367	R5F10377	R5F103A7
2 KB	2 KB	256 B	R5F10266 Note 2	_	_
	_		R5F10366 Note 2	_	_

O ROM, RAM capacities

Notes 1. This is 640 bytes when the self-programming function or data flash function is used. (For details, see CHAPTER 3 CPU ARCHITECTURE in the RL78/G12 User's Manual.)

2. The self-programming function cannot be used for R5F10266 and R5F10366.




Caution When the flash memory is rewritten via a user program, the code flash area and RAM area are used because each library is used. When using the library, refer to RL78 Family Flash Self Programming Library Type01 User's Manual and RL78 Family Data Flash Library Type04 User's Manual.

1.2 List of Part Numbers



Figure 1-1. Part Number, Memory Size, and Package of RL78/G12



- Notes 1. For details about the differences between the R5F102 products and the R5F103 products of RL78/G12, see 1.3 Differences between the R5F102 Products and the R5F103 Products.
 - 2. Products only for "A: Consumer applications (T_A = -40 to +85°C)" and "D: Industrial applications (T_A = -40 to +85°C)"

	Pin	Package	Data	Fields of	Ordering Part Number		RENESAS Code	
	count		flash	Application Note	Product Name	Packaging Specifications		
	20 pins		Mounted	A	R5F1026AASP, R5F10269ASP, R5F10268ASP, R5F10267ASP, R5F10266ASP	#V5, #35, #X5, #55	PLSP0020JB-A	
		LSSOP (4.4 × 6.5 mm. 0.65-		D	R5F1026ADSP, R5F10269DSP, R5F10268DSP, R5F10267DSP, R5F10266DSP			
		mm pitch)		G	R5F1026AGSP, R5F10269GSP, R5F10268GSP, R5F10267GSP, R5F10266GSP			
		Not mounted		A	R5F1036AASP, R5F10369ASP, R5F10368ASP, R5F10367ASP, R5F10366ASP	#V5, #35, #X5, #55	PLSP0020JB-A	
				D	R5F1036ADSP, R5F10369DSP, R5F10368DSP, R5F10367DSP, R5F10366DSP			
<r></r>		20-pin plastic	Mounted	A	R5F1026AASM, R5F10269ASM, R5F10268ASM, R5F10267ASM, R5F10266ASM	#15, #35, #55, #75	PTSP0020JI-A	
		TSSOP (4.4 x 6.5		G	R5F1026AGSM, R5F10269GSM, R5F10268GSM, R5F10267GSM, R5F10266GSM			
		mm, 0.65- mm pitch)	Not mounted	A	R5F1036AASM, R5F10369ASM, R5F10368ASM, R5F10367ASM, R5F10366ASM			
	24 pins	24-pin plastic	Mounted	A	R5F1027AANA, R5F10279ANA, R5F10278ANA, R5F10278ANA, R5F10277ANA	#U5, #W5	PWQN0024KE-A	
<r></r>		HWQFN (4 × 4 mm, 0.5-mm pitch)	\	(4 × 4 mm,		R5F1027AANA, R5F10279ANA, R5F10278ANA, R5F10277ANA	#05, #25, #45, #65	PWQN0024KF-A PWQN0024KH-A
				D	R5F1027ADNA, R5F10279DNA, R5F10278DNA, R5F10278DNA, R5F10277DNA	#U5, #W5	PWQN0024KE-A	
					R5F1027AGNA, R5F10279GNA, R5F10278GNA, R5F10277GNA			
<r></r>					R5F1027AGNA, R5F10279GNA, R5F10278GNA, R5F10278GNA, R5F10277GNA	#05, #25, #45, #65	PWQN0024KF-A PWQN0024KH-A	
			Not mounted	А	R5F1037AANA, R5F10379ANA, R5F10378ANA, R5F10378ANA, R5F10377ANA	#U5, #W5	PWQN0024KE-A	
<r></r>					R5F1037AANA, R5F10379ANA, R5F10378ANA, R5F10377ANA	#05, #25, #45, #65	PWQN0024KF-A PWQN0024KH-A	
				D	R5F1037ADNA, R5F10379DNA, R5F10378DNA, R5F10377DNA	#U5, #W5	PWQN0024KE-A	
<r></r>	30 pins	30-pin Mounted plastic LSSOP (7.62 mm		А	R5F102AAASP, R5F102A9ASP, R5F102A8ASP, R5F102A7ASP	#V0, #10, #30, #X0, #50, #70	PLSP0030JB-B	
51.02	pine			D	R5F102AADSP, R5F102A9DSP, R5F102A8DSP, R5F102A7DSP			
		(300), 0.65- mm pitch)		G	R5F102AAGSP, R5F102A9GSP, R5F102A8GSP, R5F102A7GSP	-		
<r></r>			Not mounted	A	R5F103AAASP, R5F103A9ASP, R5F103A8ASP, R5F103A7ASP	#V0, #10, #30, #X0, #50, #70	PLSP0030JB-B	
				D	R5F103AADSP, R5F103A9DSP, R5F103A8DSP, R5F103A7DSP			

Note For fields of application, see Figure 1-1 Part Number, Memory Size, and Package of RL78/G12.

Caution The ordering part numbers represent the numbers at the time of publication. For the latest ordering part numbers, refer to the target product page of the Renesas Electronics website.

1.3 Differences between the R5F102 Products and the R5F103 Products

The following are differences between the R5F102 products and the R5F103 products.

- O Whether the data flash memory is mounted or not
- O High-speed on-chip oscillator oscillation frequency accuracy
- O Number of channels in serial interface
- O Whether the DMA function is mounted or not
- O Whether a part of the safety functions are mounted or not

1.3.1 Data Flash

The data flash memory of 2 KB is mounted on the R5F102 products, but not on the R5F103 products.

Product	Data Flash
R5F102 products	2 KB
R5F1026A, R5F1027A, R5F102AA,	
R5F10269, R5F10279, R5F102A9,	
R5F10268, R5F10278, R5F102A8,	
R5F10267, R5F10277, R5F102A7,	
R5F10266 Note	
R5F103 products	Not mounted
R5F1036A, R5F1037A, R5F103AA,	
R5F10369, R5F10379, R5F103A9,	
R5F10368, R5F10378 R5F103A8,	
R5F10367, R5F10377, R5F103A7,	
R5F10366	

- **Note** The RAM in the R5F10266 has capacity as small as 256 bytes. Depending on the customer's program specification, the stack area to execute the data flash library may not be kept and data may not be written to or erased from the data flash memory.
- Caution When the flash memory is rewritten via a user program, the code flash area and RAM area are used because each library is used. When using the library, refer to RL78 Family Flash Self Programming Library Type01 User's Manual and RL78 Family Data Flash Library Type04 User's Manual.



1.3.2 On-chip oscillator characteristics

(1) High-speed on-chip oscillator oscillation frequency of the R5F102 products

Oscillator	Condition	MIN	MAX	Unit
High-speed on-chip	T _A = -20 to +85°C	-1.0	+1.0	%
oscillator oscillation	T _A = -40 to -20°C	-1.5	+1.5	
frequency accuracy	T _A = +85 to +105°C	-2.0	+2.0	

(2) High-speed on-chip oscillator oscillation frequency of the R5F103 products

Oscillator	Condition	MIN	MAX	Unit
High-speed on-chip	T _A = -40 to + 85°C	-5.0	+5.0	%
oscillator oscillation				
frequency accuracy				

1.3.3 Peripheral Functions

The following are differences in peripheral functions between the R5F102 products and the R5F103 products.


		R5F102	product	R5F103 product	
RL78/G12		20, 24 pin product	30 pin product	20, 24 pin product	30 pin product
Serial interface	erface UART		3 channels	1 channel	
	Simplified SPI (CSI)		3 channels	1 channel	
Simplified I ² C		2 channels	3 channels	None	
DMA function		2 channels		None	
Safety function	CRC operation	Yes		None	
RAM guard		Yes		None	
SFR guard		Yes		None	



1.4 Pin Configuration (Top View)

1.4.1 20-pin products

- 20-pin plastic LSSOP (4.4 × 6.5 mm, 0.65-mm pitch)
- 20-pin plastic TSSOP (4.4 × 6.5 mm, 0.65-mm pitch)




Note Provided only in the R5F102 products.

- Remarks 1. For pin identification, see 1.5 Pin Identification.
 - Functions in parentheses in the above figure can be assigned via settings in the peripheral I/O redirection register (PIOR). See Figure 4-8 Format of Peripheral I/O Redirection Register (PIOR) in the RL78/G12 User's Manual.



1.4.2 24-pin products

• 24-pin plastic HWQFN (4 × 4 mm, 0.5-mm pitch)



Note Provided only in the R5F102 products.


Remarks 1. For pin identification, see 1.5 Pin Identification.

- Functions in parentheses in the above figure can be assigned via settings in the peripheral I/O redirection register (PIOR). See Figure 4-8 Format of Peripheral I/O Redirection Register (PIOR) in the RL78/G12 User's Manual.
- 3. It is recommended to connect an exposed die pad to Vss.



1.4.3 30-pin products

• 30-pin plastic LSSOP (7.62 mm (300), 0.65-mm pitch)



Note Provided only in the R5F102 products.

Caution Connect the REGC pin to Vss via capacitor (0.47 to 1 μ F).

Remarks 1. For pin identification, see 1.5 Pin Identification.

 Functions in parentheses in the above figure can be assigned via settings in the peripheral I/O redirection register (PIOR). See Figure 4-8 Format of Peripheral I/O Redirection Register (PIOR) in the RL78/G12 User's Manual.




1.5 Pin Identification

ANI0 to ANI3,		REGC:	Regulator Capacitance
ANI16 to ANI22:	Analog input	RESET:	Reset
AVREFM:	Analog Reference Voltage Minus	RxD0 to RxD2:	Receive Data
AVREFP:	Analog reference voltage plus	SCK00, SCK01, SCK11,	
EXCLK:	External Clock Input	SCK20:	Serial Clock Input/Output
	(Main System Clock)	SCL00, SCL01,	
INTP0 to INTP5	Interrupt Request From Peripheral	SCL11, SCL20, SCLA0:	Serial Clock Input/Output
KR0 to KR9:	Key Return	SDA00, SDA01, SDA11,	
P00 to P03:	Port 0	SDA20, SDAA0:	Serial Data Input/Output
P10 to P17:	Port 1	SI00, SI01, SI11, SI20:	Serial Data Input
P20 to P23:	Port 2	SO00, SO01, SO11,	
P30 to P31:	Port 3	SO20:	Serial Data Output
P40 to P42:	Port 4	TI00 to TI07:	Timer Input
P50, P51:	Port 5	TO00 to TO07:	Timer Output
P60, P61:	Port 6	TOOL0:	Data Input/Output for Tool
P120 to P122, P125:	Port 12	TOOLRxD, TOOLTxD:	Data Input/Output for External
P137:	Port 13		Device
P147:	Port 14	TxD0 to TxD2:	Transmit Data
PCLBUZ0, PCLBUZ1:	Programmable Clock Output/	Vdd:	Power supply
	Buzzer Output	Vss:	Ground
		X1, X2:	Crystal Oscillator (Main System Clock)



1.6 Block Diagram


1.6.1 20-pin products



Note Provided only in the R5F102 products.




1.6.2 24-pin products



Note Provided only in the R5F102 products.



1.6.3 30-pin products



Note Provided only in the R5F102 products.

Remark Functions in parentheses in the above figure can be assigned via settings in the peripheral I/O redirection register (PIOR). See Figure 4-8 Format of Peripheral I/O Redirection Register (PIOR) in the RL78/G12 User's Manual.

RENESAS

1.7 Outline of Functions

This outline describes the function at the time when Peripheral I/O redirection register (PIOR) is set to 00H.

	Item	20-	pin	24-pin		30-pin		
		R5F1026x	R5F1036x	R5F1027x	R5F1037x	R5F102Ax	R5F103Ax	
Code flas	h memory	2 to 16 KB Note 1 4 to 1			16 KB			
Data flas	n memory	2 KB	_	2 KB	_	2 KB	_	
RAM		256 B to	o 1.5 KB	512 B to	o 1.5 KB	512 B	to 2KB	
Address space				1	MB			
Main system clock	High-speed system X1 (crystal/ceramic) oscillation, external main system clock input (EXCL HS (High-speed main) mode : 1 to 20 MHz (VDD = 2.7 to 5.5 V), HS (High-speed main) mode : 1 to 16 MHz (VDD = 2.4 to 5.5 V), LS (Low-speed main) mode : 1 to 8 MHz (VDD = 1.8 to 5.5 V)			,				
	High-speed on-chip oscillator clockHS (High-speed main) mode : 1 to 24 MHz (V_DD = 2.7 to 5.5 V), HS (High-speed main) mode : 1 to 16 MHz (V_DD = 2.4 to 5.5 V), LS (Low-speed main) mode : 1 to 8 MHz (V_DD = 1.8 to 5.5 V)							
Low-speed on-chip oscillator clock		15 kHz (TYP)						
General-purpose register		(8-bit register × 8) × 4 banks						
Minimum instruction execution time		0.04167 μ s (High-speed on-chip oscillator clock: f _{IH} = 24 MHz operation)						
		0.05 µs (High-speed system clock: f _{MX} = 20 MHz operation)						
Instructio	n set	Data transfer (8/16 bits)						
		Adder and subtractor/logical operation (8/16 bits)						
		Multiplication (8 bits × 8 bits)						
	T	Rotate, barrel shift, and bit manipulation (set, reset, test, and Boolean operation), etc.						
I/O port	Total	1	8	2	2	2	26	
	CMOS I/O	(N-ch C	2).D. I/O d voltage]: 4)	(N-ch C	6 D.D. I/O id voltage]: 5)	(N-ch (21 D.D. I/O nd voltage]: 9)	
	CMOS input	2	1		4		3	
	N-ch open-drain I/O (6 V tolerance)	2						
Timer	16-bit timer	4 channels		8 cha	annels			
	Watchdog timer	1 channel						
	12-bit Interval timer	1 channel						
Timer output		4 channels 8 channels (PWM outputs: 3 ^{Note 3}) (PWM outputs: 7 ^{Notes 3})						

Notes 1. The self-programming function cannot be used in the R5F10266 and R5F10366.

2. The maximum number of channels when PIOR0 is set to 1.

3. The number of PWM outputs varies depending on the setting of channels in use (the number of masters and slaves). (See **6.9.3 Operation as multiple PWM output function** in the RL78/G12 User's Manual.)

Caution When the flash memory is rewritten via a user program, the code flash area and RAM area are used because each library is used. When using the library, refer to RL78 Family Flash Self Programming Library Type01 User's Manual and RL78 Family Data Flash Library Type04 User's Manual.

Item		20-	pin	24-pin		30-pin			
		R5F1026x	R5F1036x	R5F1027x	R5F1037x	R5F102Ax	R5F103A		
Clock output/buzzer o	utput			1		2			
		2.44 kHz to 10	MHz: (Peripher	al hardware cloo	: fmain = 20 MH	z operation)			
8/10-bit resolution A/D	converter		11 ch	annels		8 char	nnels		
Serial interface		[R5F1026x (20	[R5F1026x (20-pin), R5F1027x (24-pin)]						
		Simplified SF	PI (CSI): 2 chan	nels/Simplified I ²	C: 2 channels/U	IART: 1 channel			
		[R5F102Ax (30)-pin)]						
		 Simplified SF 	PI (CSI): 1 chan	nel/Simplified I ² C	C: 1 channel/UAI	RT: 1 channel			
		 Simplified SF 	PI (CSI): 1 chan	nel/Simplified I ² C	C: 1 channel/UAI	RT: 1 channel			
		 Simplified SF 	PI (CSI): 1 chan	nel/Simplified I ² C	C: 1 channel/UAI	RT: 1 channel			
		[R5F1036x (20	-pin), R5F1037:	x (24-pin)]					
		 Simplified SF 	• Simplified SPI (CSI): 1 channel/Simplified I ² C: 0 channel/UART: 1 channel						
		[R5F103Ax (30-pin)]							
		• Simplified SPI (CSI): 1 channel/Simplified I ² C: 0 channel/UART: 1 channel							
	I ² C bus	1 channel							
Multiplier and divider/r	nultiply-	• 16 bits × 16 bits = 32 bits (unsigned or signed)							
accumulator		• 32 bits × 32 bits = 32 bits (unsigned)							
		• 16 bits × 16 bits + 32 bits = 32 bits (unsigned or signed)							
DMA controller		2 channels	-	2 channels	-	2 channels	-		
Vectored interrupt sources	Internal	18	16	18	16	26	19		
	External			5		6			
Key interrupt		6		1	0	_			
Reset		-	 Reset by RESET pin Internal reset by watchdog timer 						
			t by power-on-re						
		Internal reset by voltage detector							
		Internal reset by illegal instruction execution ^{Note}							
		Internal reset by RAM parity error							
		Internal reset by illegal-memory access							
Power-on-reset circuit		Power-on-reset: 1.51 V (TYP) Power-down-reset: 1.50 V (TYP)							
Voltage detector		• Rising edge : 1.88 to 4.06 V (12 stages)							
		• Falling edge : 1.84 to 3.98 V (12 stages)							
On-chip debug function		Provided							
Power supply voltage		V _{DD} = 1.8 to 5.5	5 V						
Operating ambient ter	nperature	T _A = –40 to +85 (G: Industrial a	•	er applications,	D: Industrial app	olications), T _A = –4	40 to +105°C		

Note The illegal instruction is generated when instruction code FFH is executed.

Reset by the illegal instruction execution not issued by emulation with the in-circuit emulator or on-chip debug emulator.

2. ELECTRICAL SPECIFICATIONS ($T_A = -40$ to +85°C)

This chapter describes the following electrical specifications.

- Target products A: Consumer applications T_A = -40 to +85°C
 - R5F102xxAxx, R5F103xxAxx
 - D: Industrial applications T_A = -40 to +85°C R5F102xxDxx, R5F103xxDxx
 - G: Industrial applications when $T_A = -40$ to $+105^{\circ}$ C products is used in the range of $T_A = -40$ to $+85^{\circ}$ C R5F102xxGxx
- Cautions 1. The RL78 microcontrollers have an on-chip debug function, which is provided for development and evaluation. Do not use the on-chip debug function in products designated for mass production, because the guaranteed number of rewritable times of the flash memory may be exceeded when this function is used, and product reliability therefore cannot be guaranteed. Renesas Electronics is not liable for problems occurring when the on-chip debug function is used.
 - 2. The pins mounted depend on the product. Refer to 2.1 Port Functions to 2.2.1 Functions for each product in the RL78/G12 User's Manual.



2.1 Absolute Maximum Ratings

Absolute Maximum Ratings (T_A = 25°C)

Parameter	Symbols		Conditions	Ratings	Unit
Supply Voltage	VDD			-0.5 to + 6.5	V
REGC terminal input voltage ^{Note1}	VIREGC	REGC		-0.3 to +2 and -0.3 to V _{DD} + 0.3	V
-				Note 2	
Input Voltage	VI1	Other than P60, F	261	-0.3 to V _{DD} + 0.3 ^{Note 3}	V
	VI2	P60, P61 (N-ch o	pen drain)	-0.3 to 6.5	V
Output Voltage	Vo			-0.3 to V_DD + $0.3^{Note 3}$	V
Analog input voltage	VAI	20-, 24-pin produc	cts: ANI0 to ANI3, ANI16 to ANI22	-0.3 to V _{DD} + 0.3	V
		30-pin products: A	ANI0 to ANI3, ANI16 to ANI19	and –0.3 to AV _{REF} (+)+0.3 ^{Notes 3, 4}	
Output current, high	Іон1	Per pin	Other than P20 to P23	-40	mA
		Total of all pins	All the terminals other than P20 to P23	-170	mA
			20-, 24-pin products: P40 to P42	-70	mA
			30-pin products: P00, P01, P40, P120		
			20-, 24-pin products: P00 to P03 ^{Note 5} , P10 to P14	-100	mA
			30-pin products: P10 to P17, P30, P31, P50, P51, P147		
	Іон2	Per pin	P20 to P23	-0.5	mA
		Total of all pins		-2	mA
Output current, low	Iol1	Per pin	Other than P20 to P23	40	mA
		Total of all pins	All the terminals other than P20 to P23	170	mA
			20-, 24-pin products: P40 to P42 30-pin products: P00, P01, P40, P120	70	mA
			20-, 24-pin products: P00 to P03 ^{Note 5} , P10 to P14, P60, P61 30-pin products: P10 to P17, P30, P31, P50, P51, P60, P61, P147	100	mA
	IOL2	Per pin	P20 to P23	1	mA
		Total of all pins		5	mA
Operating ambient temperature	TA			-40 to +85	°C
Storage temperature	Tstg			-65 to +150	°C

Notes 1. 30-pin product only.

- 2. Connect the REGC pin to Vss via a capacitor (0.47 to 1 μ F). This value determines the absolute maximum rating of the REGC pin. Do not use it with voltage applied.
- 3. Must be 6.5 V or lower.
- 4. Do not exceed AVREF(+) + 0.3 V in case of A/D conversion target pin.
- **5.** 24-pin products only.
- Caution Product quality may suffer if the absolute maximum rating is exceeded even momentarily for any parameter. That is, the absolute maximum ratings are rated values at which the product is on the verge of suffering physical damage, and therefore the product must be used under conditions that ensure that the absolute maximum ratings are not exceeded.
- **Remarks 1.** Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.
 - **2.** AVREF(+) : + side reference voltage of the A/D converter.
 - 3. Vss : Reference voltage

2.2 Oscillator Characteristics

2.2.1 X1 oscillator characteristics

$(T_A = -40 \text{ to } +85^{\circ}C, 1.8 \text{ V} \le \text{V}_{DD} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

Parameter	Resonator	Conditions	MIN.	TYP.	MAX.	Unit
X1 clock oscillation	Ceramic resonator /	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	1.0		20.0	MHz
frequency (fx) ^{Note}	crystal oscillator	1.8 V ≤ V _{DD} < 2.7 V	1.0		8.0	

Note Indicates only permissible oscillator frequency ranges. Refer to AC Characteristics for instruction execution time. Request evaluation by the manufacturer of the oscillator circuit mounted on a board to check the oscillator characteristics.

- Caution Since the CPU is started by the high-speed on-chip oscillator clock after a reset release, check the X1 clock oscillation stabilization time using the oscillation stabilization time counter status register (OSTC) by the user. Determine the oscillation stabilization time of the OSTC register and the oscillation stabilization time select register (OSTS) after sufficiently evaluating the oscillation stabilization time with the resonator to be used.
- Remark When using the X1 oscillator, refer to 5.4 System Clock Oscillator in the RL78/G12 User's Manual.

2.2.2 On-chip oscillator characteristics

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Oscillators	Parameters	Conditions		MIN.	TYP.	MAX.	Unit
High-speed on-chip oscillator clock frequency ^{Notes 1, 2}	fін			1		24	MHz
High-speed on-chip oscillator		R5F102 products	T _A = -20 to +85°C	-1.0		+1.0	%
clock frequency accuracy			$T_{A} = -40$ to $-20^{\circ}C$	-1.5		+1.5	%
		R5F103 products		-5.0		+5.0	%
Low-speed on-chip oscillator clock frequency	fı∟				15		kHz
Low-speed on-chip oscillator clock frequency accuracy				-15		+15	%

Notes 1. High-speed on-chip oscillator frequency is selected by bits 0 to 3 of option byte (000C2H) and bits 0 to 2 of HOCODIV register.

2. This only indicates the oscillator characteristics. Refer to AC Characteristics for instruction execution time.



2.3 DC Characteristics

2.3.1 Pin characteristics

|--|

$I_A = -40$ to +85°C, '	1.8 V ≦ V	$V_{DD} \le 5.5 \text{ V}, \text{ Vss} = 0 \text{ V}$			r		(1/4)
Parameter	Symbol	Conditions			TYP.	MAX.	Unit
Output current, high ^{Note 1}	Per P1 30- Per	20-, 24-pin products: Per pin for P00 to P03 ^{Note 4} , P10 to P14, P40 to P42 30-pin products: Per pin for P00, P01, P10 to P17, P30, P31, P40, P50, P51, P120, P147				-10.0 Note 2	mA
		20-, 24-pin products:	$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}$			-30.0	mA
		Total of P40 to P42	$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$			-6.0	mA
		30-pin products: Total of P00, P01, P40, P120 (When duty ≤ 70% ^{Note 3})	$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 2.7 \text{ V}$			-4.5	mA
		20-, 24-pin products:	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$			-80.0	mA
		Total of P00 to P03 ^{Note 4} , P10 to P14	$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$			-18.0	mA
		30-pin products: Total of P10 to P17, P30, P31, P50, P51, P147 (When duty ≤ 70% ^{Note 3})	1.8 V ≤ V _{DD} < 2.7 V			-10.0	mA
		Total of all pins (When duty $\leq 70\%^{\text{Note 3}}$)				-100	mA
	Іон2	Per pin for P20 to P23				-0.1	mA
		Total of all pins				-0.4	mA

Notes 1. value of current at which the device operation is guaranteed even if the current flows from the VDD pin to an output pin.

2. However, do not exceed the total current value.

3. The output current value under conditions where the duty factor \leq 70%. If duty factor > 70%: The output current value can be calculated with the following expression (where n

represents the duty factor as a percentage).

• Total output current of pins = $(I_{OH} \times 0.7)/(n \times 0.01)$

<Example> Where n = 80% and IoH = -10.0 mA

Total output current of pins = $(-10.0 \times 0.7)/(80 \times 0.01) \approx -8.7$ mA

However, the current that is allowed to flow into one pin does not vary depending on the duty factor. A current higher than the absolute maximum rating must not flow into one pin.

4. 24-pin products only.

Caution P10 to P12 and P41 for 20-pin products, P01, P10 to P12, and P41 for 24-pin products, and P00, P10 to P15, P17, and P50 for 30-pin products do not output high level in N-ch open-drain mode.

Remark Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.

....

T _A = -40 to +85°C,	<u>1.8 V ≤ V</u>	$\sqrt{DD \le 5.5 \text{ V}, \text{ Vss} = 0 \text{ V})}$			(2/4)		
Parameter	Symbol IoL1	Conditions		MIN.	TYP.	MAX.	Unit
Output current, low ^{Note 1}		20-, 24-pin products: Per pin for P00 to P03 ^{Note 4} , P10 to P14, P40 to P42				20.0 Note 2	mA
		30-pin products: Per pin for P00, P01, P10 to P17, P30, P31, P40, P50, P51, P120, P147					
		Per pin for P60, P61				15.0 Note 2	mA
		20-, 24-pin products:	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$			60.0	mA
		Total of P40 to P42	$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$			9.0	mA
		30-pin products: Total of P00, P01, P40, P120 (When duty ≤ 70% ^{Note 3})	$1.8 \text{ V} \le \text{V}_{\text{DD}} < 2.7 \text{ V}$			1.8	mA
		20-, 24-pin products:	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$			80.0	mA
		Total of P00 to P03 ^{Note 4} ,	$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$			27.0	mA
		P10 to P14, P60, P61 30-pin products: Total of P10 to P17, P30, P31, P50, P51, P60, P61, P147 (When duty ≤ 70% ^{Note 3})	1.8 V ≤ V _{DD} < 2.7 V			5.4	mA
		Total of all pins (When duty $\leq 70\%^{\text{Note 3}}$)				140	mA
	Iol2	Per pin for P20 to P23				0.4	mA
		Total of all pins				1.6	mA

.

Notes 1. Value of current at which the device operation is guaranteed even if the current flows from an output pin to the Vss pin.

- 2. However, do not exceed the total current value.
- 3. The output current value under conditions where the duty factor \leq 70%.

If duty factor > 70%: The output current value can be calculated with the following expression (where n represents the duty factor as a percentage).

- Total output current of pins = $(I_{OL} \times 0.7)/(n \times 0.01)$
- <Example> Where n = 80% and IoL = 10.0 mA

Total output current of pins = $(10.0 \times 0.7)/(80 \times 0.01) \approx 8.7$ mA

However, the current that is allowed to flow into one pin does not vary depending on the duty factor. A current higher than the absolute maximum rating must not flow into one pin.

- 4. 24-pin products only.
- Remark Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.



Parameter	Symbol	Condition	s	MIN.	TYP.	MAX.	Unit
Input voltage, high	VIH1	Normal input buffer		0.8Vdd		Vdd	V
		20-, 24-pin products: P00 to P0 P40 to P42)3 ^{Note 2} , P10 to P14,				
		30-pin products: P00, P01, P1 P40, P50, P51, P120, P147	0 to P17, P30, P31,				
	V _{IH2}	TTL input buffer	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.2		Vdd	V
		20-, 24-pin products: P10, P11	$3.3 V \le V_{DD} < 4.0 V$	2.0		Vdd	V
		30-pin products: P01, P10, P11, P13 to P17	$1.8 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}$	1.5		Vdd	V
	VIH3	P20 to P23		0.7Vdd		Vdd	V
	VIH4	P60, P61		0.7Vdd		6.0	V
	VIH5	P121, P122, P125 ^{Note 1} , P137,	EXCLK, RESET	0.8Vdd		Vdd	V
nput voltage, low	VIL1	Normal input buffer		0		0.2VDD	V
		20-, 24-pin products: P00 to P0 P40 to P42)3 ^{Note 2} , P10 to P14,				
		30-pin products: P00, P01, P10 P40, P50, P51, P120, P147) to P17, P30, P31,				
	VIL2	TTL input buffer	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	0		0.8	V
		20-, 24-pin products: P10, P11	$3.3 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$	0		0.5	V
		30-pin products: P01, P10, P11, P13 to P17	$1.8 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}$	0		0.32	V
	VIL3	P20 to P23		0		0.3Vdd	V
	VIL4	P60, P61		0		0.3Vdd	V
	VIL5	P121, P122, P125 ^{Note 1} , P137,	EXCLK, RESET	0		0.2VDD	V
Dutput voltage, high	Vон1	20-, 24-pin products: P00 to P03 ^{Note 2} , P10 to P14,	4.0 V ≤ V _{DD} ≤ 5.5 V, Іон1 = −10.0 mA	VDD-1.5			V
		P40 to P42 30-pin products:	4.0 V ≤ V _{DD} ≤ 5.5 V, Іон1 = −3.0 mA	V _{DD} -0.7			V
		P00, P01, P10 to P17, P30, P31, P40, P50, P51, P120,	2.7 V ≤ V _{DD} ≤ 5.5 V, Іон1 = −2.0 mA	Vdd-0.6			V
		P147	1.8 V ≤ V _{DD} ≤ 5.5 V, Іон1 = −1.5 mA	Vdd-0.5			V
	Vон2	P20 to P23	Іон2 = –100 µA	Vdd-0.5			V

. - - - -

Notes 1. 20, 24-pin products only. 2. 24-pin products only.

Caution The maximum value of V_I of pins P10 to P12 and P41 for 20-pin products, P01, P10 to P12, and P41 for 24-pin products, and P00, P10 to P15, P17, and P50 for 30-pin products is VDD even in N-ch opendrain mode.

High level is not output in the N-ch open-drain mode.

Remark Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.

Parameter	Symbol		Conditio	ins	MIN.	TYP.	MAX.	Unit
Output voltage, low	Vol1	20-, 24-pin product P00 to P03 ^{Note} , P1		$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 20.0 mA			1.3	V
				$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 8.5 mA			0.7	V
	P10 to P17, P30, P31, P40, P50, P51, P120, P147			$2.7 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 3.0 mA			0.6	V
				$2.7 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ lol1 = 1.5 mA			0.4	V
				$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ $I_{\text{OL1}} = 0.6 \text{ mA}$			0.4	V
	Vol2	P20 to P23	P20 to P23				0.4	V
	Vol3	P60, P61		$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 15.0 mA			2.0	V
				$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ IOL1 = 5.0 mA			0.4	V
				$2.7 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 3.0 mA			0.4	V
				$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 2.0 mA			0.4	V
Input leakage current, high	Ілні	Other than P121, P122	VI = VDD				1	μA
	Ішн2	P121, P122 (X1, X2/EXCLK)	VI = VDD	Input port or external clock input			1	μA
				When resonator connected			10	μA
Input leakage current, low	ILIL1	Other than P121, P122	VI = Vss				-1	μA
	ILIL2	P121, P122 (X1, X2/EXCLK)	VI = VSS	Input port or external clock input			-1	μA
				When resonator connected			-10	μA
On-chip pull-up resistance			Vı = Vss, input port	10	20	100	kΩ	
		30-pin products: P0 P10 to P17, P30, F P50, P51, P120, P	P31, P40,					

.... 0500 401441 < = = \/ \/ **~ `**^

Note 24-pin products only.

Remark Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.

(1/2)

2.3.2 Supply current characteristics

(1) 20-, 24-pin products

 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Parameter	Symbol			Conditions			MIN.	TYP.	MAX.	Unit
Supply	IDD1	Operating	HS(High-speed	fi⊢ = 24 MHz ^{Note 3}	Basic	V _{DD} = 5.0 V		1.5		mA
current ^{Note 1}		mode	main) mode ^{Note 4}		operation	V _{DD} = 3.0 V		1.5		
					Normal	V _{DD} = 5.0 V		3.3	5.0	mA
					operation	V _{DD} = 3.0 V		3.3	5.0	
				f⊮ = 16 MHz ^{Note 3}		V _{DD} = 5.0 V		2.5	3.7	mA
						V _{DD} = 3.0 V		2.5	3.7	
			LS(Low-speed	f⊮ = 8 MHz ^{Note 3}		V _{DD} = 3.0 V		1.2	1.8	mA
	main) mode ^{Note 4}			V _{DD} = 2.0 V		1.2	1.8			
			HS(High-speed	f _{MX} = 20 MHz ^{Note 2} ,		Square wave input		2.8	4.4	mA
	main) mode ^{№te4}	main) mode ^{Note4}	V _{DD} = 5.0 V		Resonator connection		3.0	4.6		
	f _{MX} = 20 MHz ^{Note 2} ,		Square wave input		2.8	4.4	mA			
				V _{DD} = 3.0 V		Resonator connection		3.0	4.6	
				f _{MX} = 10 MHz ^{Note 2} ,		Square wave input		1.8	2.6	mA
			V _{DD} = 5.0 V		Resonator connection		1.8	2.6		
				f _{MX} = 10 MHz ^{Note 2} ,		Square wave input		1.8	2.6	mA
				V _{DD} = 3.0 V	Resonator connection		1.8	2.6		
			LS(Low-speed	$f_{MX} = 8 \text{ MHz}^{\text{Note 2}},$		Square wave input		1.1	1.7	mA
	main) mode ^{Note 4}	V _{DD} = 3.0 V		Resonator connection		1.1	1.7			
				$f_{MX} = 8 \text{ MHz}^{\text{Note 2}},$		Square wave input		1.1	1.7	mA
				$V_{DD} = 2.0 V$		Resonator connection		1.1	1.7	

Notes 1. Total current flowing into V_{DD}, including the input leakage current flowing when the level of the input pin is fixed to V_{DD} or Vss. The values below the MAX. column include the peripheral operation current. However, not including the current flowing into the A/D converter, LVD circuit, I/O port, and on-chip pull-up/pull-down resistors and the current flowing during data flash rewrite.

- 2. When high-speed on-chip oscillator clock is stopped.
- 3. When high-speed system clock is stopped
- **4.** Relationship between operation voltage width, operation frequency of CPU and operation mode is as follows.

HS (High speed main) mode: VDD = 2.7 V to 5.5 V @1 MHz to 24 MHz

VDD = 2.4 V to 5.5 V @1 MHz to 16 MHz

LS (Low speed main) mode: VDD = 1.8 V to 5.5 V @1 MHz to 8 MHz

- Remarks 1. fmx: High-speed system clock frequency (X1 clock oscillation frequency or external main system clock frequency)
 - 2. fin: high-speed on-chip oscillator clock frequency
 - **3.** Temperature condition of the TYP. value is $T_A = 25^{\circ}C$.



(2/2)

(1) 20-, 24-pin products

$(T_{A} = -40 \text{ to } +85^{\circ}C)$	$1.8~V \leq V_{\text{DD}} \leq 5.5$	V, Vss = 0 V)
--	-------------------------------------	---------------

1 = -40 10	+05 C, I	.0 V <u>2</u> VD	$D \ge 5.5 V, VSS =$	0 V)		1	1		(2/2
Parameter	Symbol			Conditions		MIN.	TYP.	MAX.	Unit
Supply	DD2Note 2	HALT	HS (High-speed	f⊪ = 24 MHz ^{Note 4}	V _{DD} = 5.0 V		440	1210	μA
current Note 1		mode	main) mode ^{Note 6}		V _{DD} = 3.0 V		440	1210	
				f⊪ = 16 MHz ^{Note 4}	V _{DD} = 5.0 V		400	950	μA
					V _{DD} = 3.0 V		400	950	
			LS (Low-speed	f _{IH} = 8 MHz ^{Note 4}	V _{DD} = 3.0 V		270	542	μA
			main) mode ^{Note 6}		V _{DD} = 2.0 V		270	542	
			HS (High-speed	f _{MX} = 20 MHz ^{Note 3} ,	Square wave input		280	1000	μA
			main) mode ^{Note 6}	V _{DD} = 5.0 V	Resonator connection		450	1170	
				f _{MX} = 20 MHz ^{Note 3} ,	Square wave input		280	1000	μA
				V _{DD} = 3.0 V	Resonator connection		450	1170	
	$f_{MX} = 10 \text{ MHz}^{\text{Note}}$ $V_{\text{DD}} = 5.0 \text{ V}$	f _{MX} = 10 MHz ^{Note 3} ,	Square wave input		190	590	μA		
		V _{DD} = 5.0 V	Resonator connection		260	660			
				$f_{MX} = 10 \text{ MHz}^{\text{Note 3}},$ $V_{\text{DD}} = 3.0 \text{ V}$	Square wave input		190	590	μA
					Resonator connection		260	660	
			LS (Low-speed	f _{MX} = 8 MHz ^{Note 3} ,	Square wave input		110	360	μA
			main) mode ^{Note 6}	V _{DD} = 3.0 V	Resonator connection		150	416	
				f _{MX} = 8 MHz ^{Note 3} ,	Square wave input		110	360	μA
				V _{DD} = 2.0 V	Resonator connection		150	416	
	DD3 ^{Note 5}	STOP	T _A = -40°C				0.19	0.50	μA
1	mode $T_A = +25^{\circ}C$ $T_A = +50^{\circ}C$ $T_A = +70^{\circ}C$				0.24	0.50			
		T _A = +50°C				0.32	0.80		
		T _A = +70°C				0.48	1.20		
			T _A = +85°C				0.74	2.20	

Notes 1. Total current flowing into V_{DD}, including the input leakage current flowing when the level of the input pin is fixed to V_{DD} or V_{SS}. The values below the MAX. column include the peripheral operation current. However, not including the current flowing into the A/D converter, LVD circuit, I/O port, and on-chip pull-up/pull-down resistors and the current flowing during data flash rewrite.

- **2.** During HALT instruction execution by flash memory.
- **3.** When high-speed on-chip oscillator clock is stopped.
- 4. When high-speed system clock is stopped.
- 5. Not including the current flowing into the 12-bit interval timer and watchdog timer.
- **6.** Relationship between operation voltage width, operation frequency of CPU and operation mode is as follows.

HS (High speed main) mode: V_{DD} = 2.7 V to 5.5 V @1 MHz to 24 MHz V_{DD} = 2.4 V to 5.5 V @1 MHz to 16 MHz

- LS (Low speed main) mode: VDD = 1.8 V to 5.5 V @1 MHz to 8 MHz
- **Remarks 1.** f_{MX}: High-speed system clock frequency (X1 clock oscillation frequency or external main system clock frequency)
 - 2. fin: high-speed on-chip oscillator clock frequency
 - 3. Except temperature condition of the TYP. value is $T_A = 25^{\circ}C$, other than STOP mode

(1/2)

(2) 30-pin products

 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Parameter	Symbol			Conditions			MIN.	TYP.	MAX.	Unit
Supply	IDD1	Operating	HS (High-speed	f⊪ = 24 MHz ^{Note 3}	Basic	V _{DD} = 5.0 V		1.5		mA
current ^{Note 1}		mode	main) mode ^{Note 4}		operation	V _{DD} = 3.0 V		1.5		
					Normal	V _{DD} = 5.0 V		3.7	5.5	mA
					operation	V _{DD} = 3.0 V		3.7	5.5	
				f⊪ = 16 MHz ^{Note 3}		V _{DD} = 5.0 V		2.7	4.0	mA
						V _{DD} = 3.0 V		2.7	4.0	
			LS (Low-speed	f⊪ = 8 MHz ^{Note 3}		V _{DD} = 3.0 V		1.2	1.8	mA
		main) mode ^{Note 4}			V _{DD} = 2.0 V		1.2	1.8		
		HS (High-speed	$f_{MX} = 20 \text{ MHz}^{\text{Note 2}},$		Square wave input		3.0	4.6	mA	
		ma	main) mode ^{Note 4} V _{DD} = 5.0 V	V _{DD} = 5.0 V		Resonator connection		3.2	4.8	
	$f_{MX} = 20 \text{ MHz}^{\text{Note 2}},$		Square wave input		3.0	4.6	mA			
				V _{DD} = 3.0 V		Resonator connection		3.2	4.8	
				$f_{MX} = 10 \text{ MHz}^{\text{Note 2}},$		Square wave input		1.9	2.7	mA
				$V_{DD} = 5.0 \text{ V}$ $f_{MX} = 10 \text{ MHz}^{Note 2},$		Resonator connection		1.9	2.7	
						Square wave input		1.9	2.7	mA
				V _{DD} = 3.0 V		Resonator connection		1.9	2.7	
		LS (Low-spe	LS (Low-speed	$f_{MX} = 8 \text{ MHz}^{\text{Note 2}},$		Square wave input		1.1	1.7	mA
	main) mode ^{Note 4}	$V_{DD} = 3.0 V$ f _{MX} = 8 MHz ^{Note 2} ,		Resonator connection		1.1	1.7			
				Square wave input		1.1	1.7	mA		
				$V_{DD} = 2.0 V$		Resonator connection		1.1	1.7	

- **Notes 1.** Total current flowing into V_{DD}, including the input leakage current flowing when the level of the input pin is fixed to V_{DD} or V_{SS}. The values below the MAX. column include the peripheral operation current. However, not including the current flowing into the A/D converter, LVD circuit, I/O port, and on-chip pull-up/pull-down resistors and the current flowing during data flash rewrite.
 - 2. When high-speed on-chip oscillator clock is stopped.
 - 3. When high-speed system clock is stopped
 - 4. Relationship between operation voltage width, operation frequency of CPU and operation mode is as follows.

HS (High speed main) mode: V_{DD} = 2.7 V to 5.5 V @1 MHz to 24 MHz

- VDD = 2.4 V to 5.5 V @1 MHz to 16 MHz
- LS (Low speed main) mode: VDD = 1.8 V to 5.5 V @1 MHz to 8 MHz
- **Remarks 1.** f_{MX}: High-speed system clock frequency (X1 clock oscillation frequency or external main system clock frequency)
 - 2. fin: high-speed on-chip oscillator clock frequency
 - **3.** Temperature condition of the TYP. value is $T_A = 25^{\circ}C$.



(2/2)

(2) 30-pin products

(T _A = -40 to +85°C	$1.8 V \le V_{DD} \le 5.5$	V, Vss = 0 V)
--------------------------------	----------------------------	---------------

Parameter	Symbol			Conditions		MIN.	TYP.	MAX.	Unit
Supply	DD2 ^{Note 2}	HALT	HS (High-speed	f _{IH} = 24 MHz ^{Note 4}	V _{DD} = 5.0 V		440	1280	μA
current ^{Note 1}		mode	main) mode ^{Note 6}		V _{DD} = 3.0 V		440	1280	
				f⊪ = 16 MHz ^{Note 4}	V _{DD} = 5.0 V		400	1000	μA
					V _{DD} = 3.0 V		400	1000	
			LS (Low-speed	f⊪ = 8 MHz ^{Note 4}	V _{DD} = 3.0 V		260	530	μA
			main) mode ^{Note 6}		V _{DD} = 2.0 V		260	530	
				f _{MX} = 20 MHz ^{Note 3} ,	Square wave input		280	1000	μA
			main) mode ^{Note 6}	V _{DD} = 5.0 V	Resonator connection		450	1170	
				f _{MX} = 20 MHz ^{Note 3} ,	Square wave input		280	1000	μA
				V _{DD} = 3.0 V	Resonator connection		450	1170	
				f _{MX} = 10 MHz ^{Note 3} ,	Square wave input		190	600	μA
				V _{DD} = 5.0 V	Resonator connection		260	670	
				f _{MX} = 10 MHz ^{Note 3} ,	Square wave input		190	600	μA
				V _{DD} = 3.0 V	Resonator connection		260	670	
			LS (Low-speed	f _{MX} = 8 MHz ^{Note 3} ,	Square wave input		95	330	μA
			main) mode ^{Note 6}	V _{DD} = 3.0 V	Resonator connection		145	380	
				f _{MX} = 8 MHz ^{Note 3} ,	Square wave input		95	330	μA
				V _{DD} = 2.0 V	Resonator connection		145	380	
	DD3 ^{Note 5}	STOP	T _A = -40°C				0.18	0.50	μA
		mode	T _A = +25°C	T _A = +25°C			0.23	0.50	
			T _A = +50°C				0.30	1.10	
			T _A = +70°C				0.46	1.90	
			T _A = +85°C				0.75	3.30	

Notes 1. Total current flowing into V_{DD}, including the input leakage current flowing when the level of the input pin is fixed to V_{DD} or V_{SS}. The values below the MAX. column include the peripheral operation current. However, not including the current flowing into the A/D converter, LVD circuit, I/O port, and on-chip pull-up/pull-down resistors and the current flowing during data flash rewrite.

- **2.** During HALT instruction execution by flash memory.
- **3.** When high-speed on-chip oscillator clock is stopped.
- 4. When high-speed system clock is stopped.
- 5. Not including the current flowing into the 12-bit interval timer and watchdog timer.
- **6.** Relationship between operation voltage width, operation frequency of CPU and operation mode is as follows.

HS (High speed main) mode: V_{DD} = 2.7 V to 5.5 V @1 MHz to 24 MHz V_{DD} = 2.4 V to 5.5 V @1 MHz to 16 MHz

- LS (Low speed main) mode: V_{DD} = 1.8 V to 5.5 V @1 MHz to 8 MHz
- **Remarks 1.** f_{MX}: High-speed system clock frequency (X1 clock oscillation frequency or external main system clock frequency)
 - 2. fin: high-speed on-chip oscillator clock frequency
 - 3. Except STOP mode, temperature condition of the TYP. value is $T_A = 25^{\circ}C$.

(3) Peripheral functions (Common to all products)

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Parameter	Symbol		Conditions	MIN.	TYP.	MAX.	Unit
Low-speed onchip oscillator operating current	FiL Note 1				0.20		μA
12-bit interval timer operating current	ITMKA Notes 1, 2, 3				0.02		μA
Watchdog timer operating current	WDT Notes 1, 2, 4	f⊩ = 15 kHz			0.22		μA
A/D converter	ADC ^{Notes 1, 5}	When conversion at	Normal mode, AV _{REFP} = V _{DD} = 5.0 V		1.30	1.70	mA
operating current		maximum speed	Low voltage mode, $AV_{REFP} = V_{DD} = 3.0 V$		0.50	0.70	mA
A/D converter reference voltage operating current	ADREF Note 1				75.0		μA
Temperature sensor operating current	TMPS Note 1				75.0		μA
LVD operating current	ILVD Notes 1, 6				0.08		μA
Self- programming operating current	FSP Notes 1, 8				2.00	12.20	mA
BGO operating current	BGO Notes 1, 7				2.00	12.20	mA
SNOOZE	ISNOZ Note 1	ADC operation	The mode is performed Note 9		0.50	0.60	mA
operating current			The A/D conversion operations are performed, Low voltage mode, $AV_{REFP} = V_{DD} = 3.0 V$		1.20	1.44	mA
		Simplified SPI (CSI)/L	JART operation		0.70	0.84	mA

Notes 1. Current flowing to the VDD.

- 2. When high speed on-chip oscillator and high-speed system clock are stopped.
- 3. Current flowing only to the 12-bit interval timer (excluding the operating current of the low-speed on-chip oscillator). The current value of the RL78 microcontrollers is the sum of IDD1, IDD2 or IDD3, and IFIL and ITMKA when the 12-bit interval timer operates.
- 4. Current flowing only to the watchdog timer (including the operating current of the low-speed on-chip oscillator). The current value of the RL78 microcontrollers is the sum of IDD1, IDD2 or IDD3 and IWDT when the watchdog timer operates.
- **5.** Current flowing only to the A/D converter. The current value of the RL78 microcontrollers is the sum of IDD1 or IDD2 and IADC when the A/D converter operates in an operation mode or the HALT mode.
- **6.** Current flowing only to the LVD circuit. The current value of the RL78 microcontrollers is the sum of IDD1, IDD2 or IDD3 and ILVD when the LVD circuit operates.
- 7. Current flowing only during data flash rewrite.
- 8. Current flowing only during self programming.
- 9. For shift time to the SNOOZE mode, see 17.3.3 SNOOZE mode in the RL78/G12 User's Manual.

Remarks 1. fil: Low-speed on-chip oscillator clock frequency

2. Temperature condition of the TYP. value is $T_A = 25^{\circ}C$

2.4 AC Characteristics


$A = -40$ to +85°C, 1.8 V \leq VDD \leq 5.5 V, Vs	s = 0 V)
---	----------

Items	Symbol		Condition	S	MIN.	TYP.	MAX.	Unit
Instruction cycle (minimum	Тсү	Main system	HS (High-	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	0.04167		1	μs
instruction execution time)		clock (fMAIN) operation	speed main) mode	$2.4 \text{ V} \leq \text{V}_{\text{DD}} < 2.7 \text{ V}$	0.0625		1	μs
			LS (Low- speed main) mode	$1.8 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	0.125		1	μs
		During self	HS (High-	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	0.04167		1	μs
		programming	speed main) mode	$2.4 \text{ V} \le \text{V}_{\text{DD}} \le 2.7 \text{ V}$	0.0625		1	μs
			LS (Low- speed main) mode	$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}$	0.125		1	μs
External main system clock	fex	$2.7 V \le V_{DD} \le 5.5 V$ 2.4 V \le V_{DD} < 2.7 V 1.8 V \le V_{DD} < 2.4 V			1.0		20.0	MHz
frequency					1.0		16.0	MHz
					1.0		8.0	MHz
External main system clock	texн, texL	texh, texl $2.7 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}$						ns
input high-level width, low-		$2.4 \text{ V} \le \text{V}_{\text{DD}} \le 2.7 \text{ V}$			30			ns
level width		$1.8 V \le V_{DD} \le 2.4 V$						ns
TI00 to TI07 input high-level width, low-level width	t⊓∺, t⊓∟				1/fмск + 10			ns
TO00 to TO07 output	fто	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$					12	MHz
frequency		$2.7 V \le V_{DD} < 4.0 V$					8	MHz
		1.8 V ≤ V _{DD} < 2	.7 V				4	MHz
PCLBUZ0, or PCLBUZ1	f PCL	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5$.5 V				16	MHz
output frequency		$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4$.0 V				8	MHz
		1.8 V ≤ V _{DD} < 2	.7 V				4	MHz
INTP0 to INTP5 input high- level width, low-level width	tinth, tintl				1			μs
KR0 to KR9 input available width	tkr.				250			ns
RESET low-level width	t RSL				10			μs

Remark f_{MCK}: Timer array unit operation clock frequency (Operation clock to be set by the timer clock select register 0 (TPS0) and the CKS0n bit of timer mode register 0n (TMR0n). n: Channel number (n = 0 to 7))




Minimum Instruction Execution Time during Main System Clock Operation







AC Timing Test Point



External Main System Clock Timing



TI/TO Timing





2.5 Peripheral Functions Characteristics

AC Timing Test Point

Vін/Vон VIH/VOH Test points Vil/Vol VIL/VOL

2.5.1 Serial array unit

(1) During communication at same potential (UART mode)

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

Parameter	Symbol	Conditions		h-speed Mode	``	/-speed Mode	Unit
			MIN.	MAX.	MIN.	MAX.	
Transfer rate				fмск/6		fмск/6	bps
Note 1		Theoretical value of the maximum transfer rate $f_{CLK} = f_{MCK} ^{Note \; 2}$		4.0		1.3	Mbps

Notes 1. Transfer rate in the SNOOZE mode is 4800 bps only.

2. The maximum operating frequencies of the CPU/peripheral hardware clock (fcLK) are:


HS (high-speed main) mode: 24 MHz (2.7 V \leq V_{DD} \leq 5.5 V)

16 MHz (2.4 V \leq V_{DD} \leq 5.5 V)


LS (low-speed main) mode: 8 MHz ($1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}$)

Caution Select the normal input buffer for the RxDq pin and the normal output mode for the TxDq pin by using port input mode register g (PIMg) and port output mode register g (POMg).

UART mode connection diagram (during communication at same potential)



UART mode bit width (during communication at same potential) (reference)



Remarks 1. q: UART number (q = 0 to 2), g: PIM, POM number (g = 0, 1)

2. fMCK: Serial array unit operation clock frequency

(Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn).

m: Unit number, n: Channel number (mn = 00 to 03, 10, 11))

(2) During communication at same potential (simplified SPI (CSI) mode) (master mode, SCK00... internal clock output, corresponding CSI00 only)

Parameter	Symbol	Conditions	HS (high-speed main) Mode		LS (low-sp Mo	Unit	
			MIN.	MAX.	MIN.	MAX.	
SCK00 cycle time	tkcy1	tκcγ1 ≥ 2/fc∟κ	83.3		250		ns
SCK00 high-/low-	tкнı,	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	tксү1/2–7		tксү1/2–50		ns
level width	t ĸ∟1	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	tксү1/2–10		tксү1/2–50		ns
SI00 setup time	tsik1	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	23		110		ns
(to SCK00↑) ^{Note 1}		$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	33		110		ns
SI00 hold time (from SCK00↑) ^{Note 2}	tksi1		10		10		ns
Delay time from SCK00↓ to SO00 output ^{Note 3}	tkso1	C = 20 pF ^{Note 4}		10		10	ns

 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, 2.7 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

- Notes 1. When DAP00 = 0 and CKP00 = 0, or DAP00 = 1 and CKP00 = 1. The SI00 setup time becomes "to SCK00↓" when DAP00 = 0 and CKP00 = 1, or DAP00 = 1 and CKP00 = 0.
 - When DAP00 = 0 and CKP00 = 0, or DAP00 = 1 and CKP00 = 1. The SI00 hold time becomes "from SCK00↓" when DAP00 = 0 and CKP00 = 1, or DAP00 = 1 and CKP00 = 0.
 - 3. When DAP00 = 0 and CKP00 = 0, or DAP00 = 1 and CKP00 = 1. The delay time to SO00 output becomes "from SCK00↑" when DAP00 = 0 and CKP00 = 1, or DAP00 = 1 and CKP00 = 0.
 - 4. C is the load capacitance of the SCK00 and SO00 output lines.

Caution Select the normal input buffer for the SI00 pin and the normal output mode for the SO00 and SCK00 pins by using port input mode register 1 (PIM1) and port output mode register 1 (POM1).

- **Remarks 1.** This specification is valid only when CSI00's peripheral I/O redirect function is not used.
 - 2. fMCK: Serial array unit operation clock frequency
 - (Operation clock to be set by the serial clock select register 0 (SPS0) and the CKS00 bit of serial mode register 00 (SMR00).)



(3) During communication at same potential (simplified SPI (CSI) mode) (master mode, SCKp... internal clock output)

Parameter	Symbol	C	Conditions		speed ode	LS (low-s main) M		Unit
				MIN.	MAX.	MIN.	MAX.	
SCKp cycle time	tkcy1	tĸcy1 ≥ 4/fclĸ	tkcy1 ≥ 4/fclk 2.7 V ≤ VDD ≤ 5.5 V			500		ns
			$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	250		500		ns
			$1.8 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	-		500		ns
SCKp high-/low-level width	t кн1,			tксү1/2–12		tксү1/2–50		ns
	tĸ∟1			tксү1/2–18		tксү1/2–50		ns
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		tксү1/2-38		tксү1/2–50		ns
		$1.8 \text{ V} \leq \text{V}_{\text{DD}} \leq$	5.5 V	-		tксү1/2–50		ns
SIp setup time (to SCKp↑)	tsik1	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq$	5.5 V	44		110		ns
Note 1		$2.7 V \leq V_{DD} \leq 3$	5.5 V	44		110		ns
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq$	5.5 V	75		110		ns
		$1.8 \text{ V} \leq \text{V}_{\text{DD}} \leq$	5.5 V	_		110		ns
SIp hold time (from SCKp↑) ^{Note 2}	tksi1			19		19		ns
Delay time from SCKp↓ to SOp output ^{Note 3}	tĸso1	C = 30 pF ^{Note}	C = 30 pF Note 4		25		25	ns

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, \text{V}_{\text{SS}} = 0 \text{ V})$

- Notes 1. When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp setup time becomes "to SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - **2.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp hold time becomes "from SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - **3.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The delay time to SOp output becomes "from SCKp↑" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - 4. C is the load capacitance of the SCKp and SOp output lines.
- Caution Select the normal input buffer for the SIp pin and the normal output mode for the SOp and SCKp pins by using port input mode register 1 (PIM1) and port output mode registers 0, 1, 4 (POM0, POM1, POM4).
- **Remarks 1.** p: CSI number (p = 00, 01, 11, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0, 1, 3: "1, 3" is only for the R5F102 products)
 - 2. fMCK: Serial array unit operation clock frequency
 - (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn). m: Unit number (m = 0, 1), n: Channel number (n = 0, 1, 3: "1, 3" is only for the R5F102 products.))


(4) During communication at same potential (simplified SPI (CSI) mode) (slave mode, SCKp... external clock input)

Parameter	Symbol	Conc	litions	HS (high- main) M	•	LS (low-spe Moo	,	Unit
				MIN.	MAX.	MIN.	MAX.	
SCKp cycle time Note 5	tксү2	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	20 MHz < fмск	8/fмск		_		ns
			fмск ≤ 20 MHz	6/fмск		6/fмск		ns
		$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	16 MHz < fмск	8/fмск		_		ns
			fмск ≤ 16 MHz	6/fмск		6/fмск		ns
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		6/fмск		6/fмск		ns
				and 500		and 500		
		1.8 V ≤ V _{DD} ≤ 5.5 V		-		6/f мск		ns
						and 750		
SCKp high-/low-level	tкн2,	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		tксү2/2-7		tксү2/2–7		ns
width	tĸ∟2	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		tксү2/2-8		tксү2/2-8		ns
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		tксү2/2–18		tксү2/2–18		ns
		$1.8 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		-		tксү2/2–18		ns
SIp setup time	tsık2	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		1/fмск + 20		1/fмск + 30		ns
(to SCKp↑) ^{Note 1}		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		1/fмск + 30		1/fмск + 30		ns
		$1.8 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		_		1/fмск + 30		ns
SIp hold time (from SCKp↑) ^{Note 2}	tksi2			1/fмск + 31		1/fмск + 31		ns
Delay time from SCKp↓ to	tkso2	C = 30 pF ^{Note 4}	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		2/fмск + 44		2/fмск + 110	ns
SOp output Note 3			$2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}$		2/fмск + 75		2/fмск + 110	ns
			$1.8 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		_		2/fмск + 110	ns


 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

- Notes 1. When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp setup time becomes "to SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - **2.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp hold time becomes "from SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - **3.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The delay time to SOp output becomes "from SCKp↑" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - 4. C is the load capacitance of the SOp output lines.
 - **5.** Transfer rate in the SNOOZE mode: MAX. 1 Mbps.
- Caution Select the normal input buffer for the SIp and SCKp pins and the normal output mode for the SOp pin by using port input mode register 1 (PIM1) and port output mode registers 0, 1, 4 (POM0, POM1, POM4).


Simplified SPI (CSI) mode connection diagram (during communication at same potential)



Simplified SPI (CSI) mode serial transfer timing (during communication at same potential) (When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1.)



Simplified SPI (CSI) mode serial transfer timing (during communication at same potential) (When DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.)



(Remarks are listed on the next page.)



- Remarks 1. p: CSI number (p = 00, 01, 11, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0, 1, 3: "1, 3" is only for the R5F102 products.)
 - 2. fMCK: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn). m: Unit number (m = 0, 1), n: Channel number (n = 0, 1, 3: "1, 3" is only for the R5F102 products.))

(5)	During	communication	at same potential	(simplified I ² C mode)
-----	--------	---------------	-------------------	------------------------------------

Parameter	Symbol	Conditions	HS (high-speed	HS (high-speed main) Mode		
			LS (low-speed r	main) Mode		
			MIN.	MAX.		
SCLr clock frequency	fsc∟	$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$		400 Note 1	kHz	
		C_b = 100 pF, R_b = 3 k Ω				
		$1.8 \text{ V} \le \text{V}_{\text{DD}} < 2.7 \text{ V},$		300 Note 1	kHz	
		C_b = 100 pF, R_b = 5 k Ω				
Hold time when SCLr = "L"	t∟ow	$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$	1150		ns	
		C_b = 100 pF, R_b = 3 k Ω				
		$1.8 \text{ V} \le \text{V}_{\text{DD}} < 2.7 \text{ V},$	1550		ns	
		C_b = 100 pF, R_b = 5 k Ω				
Hold time when SCLr = "H"	tніgн	$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$	1150		ns	
		C_b = 100 pF, R_b = 3 k Ω				
		$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 2.7 \text{ V},$	1550		ns	
		C_b = 100 pF, R_b = 5 k Ω				
Data setup time (reception)	tsu:dat	$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$	1/fмск + 145 ^{Note 2}		ns	
		C_b = 100 pF, R_b = 3 k Ω				
		$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 2.7 \text{ V},$	1/fмск + 230 ^{Note 2}		ns	
		C_b = 100 pF, R_b = 5 k Ω				
Data hold time (transmission)	thd:dat	$1.8 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$	0	355	ns	
		C_b = 100 pF, R_b = 3 k Ω				
		$1.8 \text{ V} \le \text{V}_{\text{DD}} < 2.7 \text{ V},$	0	405	ns	
		C _b = 100 pF, R _b = 5 kΩ				

(ອ)	During communication at same potential (simplined r
/ T .	

Notes 1. The value must be equal to or less than fmck/4.


2. Set tsu:DAT so that it will not exceed the hold time when SCLr = "L" or SCLr = "H".

Caution Select the N-ch open drain output (Vob tolerance) mode for SDAr by using port output mode register h (POMh).


(Remarks are listed on the next page.)



Simplified I²C mode connection diagram (during communication at same potential)



Simplified I²C mode serial transfer timing (during communication at same potential)



Remarks 1. R_b [Ω]:Communication line (SDAr) pull-up resistance

- Cb [F]: Communication line (SCLr, SDAr) load capacitance
- **2.** r: IIC number (r = 00, 01, 11, 20), h: = POM number (h = 0, 1, 4, 5)
- fMCK: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn). m: Unit number (m = 0, 1), n: Channel number (0, 1, 3))
- **4.** Simplified I²C mode is supported only by the R5F102 products.



(6) Communication at different potential (1.8 V, 2.5 V, 3 V) (UART mode) $(T_A = -40 \text{ to } +85^\circ\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Parameter	Symbol			Conditions		igh-speed n) Mode		w-speed) Mode	Unit
						MAX.	MIN.	MAX.	
Transfer rate ^{Note4}		Reception	4.0 V ≤ V _D 2.7 V ≤ V _b	,		fмск/6 Note1		fмск/6 Note1	bps
				Theoretical value of the maximum transfer rate $f_{MCK} = f_{CLK}$ Note3		4.0		1.3	Mbps
			2.7 V ≤ V _D 2.3 V ≤ V _b			fмск/6 Note1		fмск/6 Note1	bps
				Theoretical value of the maximum transfer rate $f_{MCK} = f_{CLK}$ Note3		4.0		1.3	Mbps
		$1.8 V \le V_{DD} < 3.3 V,$ $1.6 V \le V_b \le 2.0 V$			fмск/6 Notes1, 2		fмск/6 Notes1, 2	bps	
				Theoretical value of the maximum transfer rate $f_{MCK} = f_{CLK}^{Note3}$		4.0		1.3	Mbps
		Transmission	4.0 V ≤ V _D 2.7 V ≤ V _b			Note4		Note4	bps
				Theoretical value of the maximum transfer rate $C_b = 50 \text{ pF}, R_b = 1.4 \text{ k}\Omega, V_b = 2.7 \text{ V}$		2.8 Note5		2.8 Note5	Mbps
			2.7 V ≤ V _D 2.3 V ≤ V _b			Note6		Note6	bps
				Theoretical value of the maximum transfer rate C_b = 50 pF, R_b = 2.7 k Ω , V_b = 2.3 V		1.2 Note7		1.2 Note7	Mbps
			1.8 V ≤ V _D 1.6 V ≤ V _b			Notes 2, 8		Notes 2, 8	bps
				Theoretical value of the maximum transfer rate $C_b = 50 \text{ pF}, R_b = 5.5 \text{ k}\Omega, V_b = 1.6 \text{ V}$		0.43 Note9		0.43 Note9	Mbps

Notes 1. Transfer rate in the SNOOZE mode is 4800 bps only.

- **2.** Use it with $V_{DD} \ge V_b$.
- The maximum operating frequencies of the CPU/peripheral hardware clock (fcLk) are: HS (high-speed main) mode: 24 MHz (2.7 V ≤ V_{DD} ≤ 5.5 V)

16 MHz (2.4 V ≤ Vod ≤ 5.5 V)

- LS (low-speed main) mode: 8 MHz (1.8 V \leq V_{DD} \leq 5.5 V)
- **4.** The smaller maximum transfer rate derived by using f_{MCK}/6 or the following expression is the valid maximum transfer rate.

Expression for calculating the transfer rate when 4.0 V \leq V_{DD} \leq 5.5 V and 2.7 V \leq V_b \leq 4.0 V

$$\frac{1}{\{-C_b \times R_b \times \ln (1 - \frac{2.2}{V_b})\} \times 3}$$
 [bps]

Baud rate error (theoretical value) = $\frac{\frac{1}{\text{Transfer rate} \times 2} - \{-C_b \times R_b \times \ln(1 - \frac{2.2}{V_b})\}}{(\frac{1}{\text{Transfer rate}}) \times \text{Number of transferred bits}} \times 100 \,[\%]$

* This value is the theoretical value of the relative difference between the transmission and reception sides.

- × 100 [%]

- This value as an example is calculated when the conditions described in the "Conditions" column are met. Refer to Note 4 above to calculate the maximum transfer rate under conditions of the customer.
- **6.** The smaller maximum transfer rate derived by using f_{MCK}/6 or the following expression is the valid maximum transfer rate.

Expression for calculating the transfer rate when 2.7 V \leq V_{DD} < 4.0 V and 2.3 V \leq V_b \leq 2.7 V

Maximum transfer rate =

$$\frac{1}{\{-C_b \times R_b \times \ln (1 - \frac{2.0}{V_b})\} \times 3}$$
 [bps]

Baud rate error (theoretical value) =

 $(\frac{1}{\text{Transfer rate}})$ × Number of transferred bits

 $\frac{1}{\text{Transfer rate } \times 2} - \{-C_b \times R_b \times \ln (1 - \frac{2.0}{V_b})\}$

- * This value is the theoretical value of the relative difference between the transmission and reception sides.
- This value as an example is calculated when the conditions described in the "Conditions" column are met. Refer to Note 6 above to calculate the maximum transfer rate under conditions of the customer.
- 8. The smaller maximum transfer rate derived by using fmck/6 or the following expression is the valid maximum transfer rate.

Expression for calculating the transfer rate when 1.8 V \leq V_{DD} < 3.3 V, 1.6 V \leq V_b \leq 2.0 V

Maximum transfer rate =

Baud r

$$\frac{1}{\{-C_b \times R_b \times \ln (1 - \frac{1.5}{V_b})\} \times 3}$$
 [bps]


ate error (theoretical value) =
$$\frac{\frac{1}{\text{Transfer rate } \times 2} - \{-C_b \times R_b \times \ln(1 - \frac{1.5}{V_b})\}}{(\frac{1}{(\text{Transfer rate})} \times \text{Number of transferred bits}} \times 100 [\%]$$

* This value is the theoretical value of the relative difference between the transmission and reception sides.


- **9.** This value as an example is calculated when the conditions described in the "Conditions" column are met. Refer to **Note 8** above to calculate the maximum transfer rate under conditions of the customer.
- Caution Select the TTL input buffer for the RxDq pin and the N-ch open drain output (V_{DD} tolerance) mode for the TxDq pin by using port input mode register g (PIMg) and port output mode register g (POMg). For V_{IH} and V_{IL}, see the DC characteristics with TTL input buffer selected.




UART mode connection diagram (during communication at different potential)



UART mode bit width (during communication at different potential) (reference)





- **Remarks 1.** R_b[Ω]: Communication line (TxDq) pull-up resistance, C_b[F]: Communication line (TxDq) load capacitance, V_b[V]: Communication line voltage
 - **2.** q: UART number (q = 0 to 2), g: PIM and POM number (g = 0, 1)
 - **3.** fMCK: Serial array unit operation clock frequency

(Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn).

m: Unit number, n: Channel number (mn = 00 to 03, 10, 11))

4. UART0 of the 20- and 24-pin products supports communication at different potential only when the peripheral I/O redirection function is not used.



(7) Communication at different potential (2.5 V, 3 V) (simplified SPI (CSI) mode) (master mode, SCK00... internal clock output, corresponding CSI00 only)

Parameter	Symbol		Conditions	HS (higl main)		LS (low main)		Unit
				MIN.	MAX.	MIN.	MAX.	
SCK00 cycle time	t ксү1	tĸcy1≥2/fcLK		200		1150		ns
			$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \\ 2.3 \; V \leq V_b \leq 2.7 \; V, \\ C_b = 20 \; pF, \; R_b = 2.7 \; k\Omega \end{array}$	300		1150		ns
SCK00 high-level width	tкнı	$4.0 V \le V_{DD} \le 5$ $C_b = 20 \text{ pF}, R_b \le 5$.5 V, 2.7 V ≤ V₅ ≤ 4.0 V, = 1.4 kΩ	tксү1/2 – 50		tксү1/2 – 50		ns
		2.7 V ≤ V _{DD} < 4 C _b = 20 pF, R _b =	.0 V, 2.3 V ≤ V♭ ≤ 2.7 V, = 2.7 kΩ	tксү1/2 – 120		tксү1/2 – 120		ns
SCK00 low-level width	tĸ∟ı	$4.0 V \le V_{DD} \le 5$ $C_b = 20 \text{ pF}, R_b \le 5$.5 V, 2.7 V ≤ V₅ ≤ 4.0 V, = 1.4 kΩ	tксү1/2 – 7		tксү1/2 – 50		ns
		2.7 V ≤ V _{DD} < 4 C _b = 20 pF, R _b :	.0 V, 2.3 V ≤ V₅ ≤ 2.7 V, = 2.7 kΩ	tксү1/2 – 10		tксү1/2 – 50		ns
SI00 setup time (to SCK00↑) ^{Note 1}	tsik1	$4.0 V \le V_{DD} \le 5$ $C_b = 20 \text{ pF}, R_b \le 5$.5 V, 2.7 V ≤ V _b ≤ 4.0 V, = 1.4 kΩ	58		479		ns
		2.7 V ≤ V _{DD} < 4 C _b = 20 pF, R _b :	.0 V, 2.3 V ≤ V₅ ≤ 2.7 V, = 2.7 kΩ	121		479		ns
SI00 hold time (from SCK00↑) ^{Note 1}	tksi1	$4.0 V \le V_{DD} \le 5.0 C_{b} = 20 \text{ pF}, R_{b} \le 100 \text{ cm}$.5 V, 2.7 V ≤ V _b ≤ 4.0 V, = 1.4 kΩ	10		10		ns
		2.7 V ≤ V _{DD} < 4 C _b = 20 pF, R _b :	.0 V, 2.3 V ≤ V₅ ≤ 2.7 V, = 2.7 kΩ	10		10		ns
Delay time from SCK00↓ to SO00 output ^{Note 1}	tkso1	$4.0 V \le V_{DD} \le 5$ $C_b = 20 \text{ pF}, R_b \le 5$.5 V, 2.7 V ≤ V _b ≤ 4.0 V, = 1.4 kΩ		60		60	ns
		2.7 V ≤ V _{DD} < 4 C _b = 20 pF, R _b :	.0 V, 2.3 V ≤ V₅ ≤ 2.7 V, = 2.7 kΩ		130		130	ns
SI00 setup time (to SCK00↓) ^{Note 2}	tsik1	$4.0 V \le V_{DD} \le 5$ $C_b = 20 \text{ pF}, R_b \le 5$.5 V, 2.7 V ≤ V _b ≤ 4.0 V, = 1.4 kΩ	23		110		ns
		2.7 V ≤ V _{DD} < 4 C _b = 20 pF, R _b :	.0 V, 2.3 V ≤ V₅ ≤ 2.7 V, = 2.7 kΩ	33		110		ns
SI00 hold time (from SCK00↓) ^{Note 2}	tksi1	$4.0 V \le V_{DD} \le 5$ $C_b = 20 \text{ pF}, R_b \le 5$.5 V, 2.7 V ≤ V _b ≤ 4.0 V, = 1.4 kΩ	10		10		ns
		2.7 V ≤ V _{DD} < 4 C _b = 20 pF, R _b :	.0 V, 2.3 V ≤ V _b ≤ 2.7 V, = 2.7 kΩ	10		10		ns
Delay time from SCK00↑ to SO00 output ^{Note 2}	tkso1	$4.0 V \le V_{DD} \le 5$ $C_b = 20 \text{ pF}, R_b \le 5$.5 V, 2.7 V ≤ V _b ≤ 4.0 V, = 1.4 kΩ		10		10	ns
		2.7 V ≤ V _{DD} < 4 C _b = 20 pF, R _b :	.0 V, 2.3 V ≤ V₅ ≤ 2.7 V, = 2.7 kΩ		10		10	ns

 $⁽T_A = -40 \text{ to } +85^{\circ}\text{C}, 2.7 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

(Notes, Caution, and Remarks are listed on the next page.)



Notes 1. When DAP00 = 0 and CKP00 = 0, or DAP00 = 1 and CKP00 = 1

- **2.** When DAP00 = 0 and CKP00 = 1, or DAP00 = 1 and CKP00 = 0.
- Caution Select the TTL input buffer for the SI00 pin and the N-ch open drain output (VDD tolerance) mode for the SO00 pin and SCK00 pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For VIH and VIL, see the DC characteristics with TTL input buffer selected.
- **Remarks 1.** R_b [Ω]:Communication line (SCK00, SO00) pull-up resistance, C_b [F]: Communication line (SCK00, SO00) load capacitance, V_b [V]: Communication line voltage
 - fMCK: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register 0 (SPS0) and the CKS00 bit of serial mode register 00 (SMR00).)



(8) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified SPI (CSI) mode) (master mode, SCKp... internal clock output) (1/3)

Parameter	Symbol		Conditions	HS (high-spe Mode	,	LS (low-spee Mode	'	Unit
				MIN.	MAX.	MIN.	MAX.	
SCKp cycle time	tkcy1	tксү1 ≥ 4/fclк	$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$	300		1150		ns
			$2.7 \text{ V} \le \text{V}_{b} \le 4.0 \text{ V},$					
			C_b = 30 pF, R_b = 1.4 k Ω					
			$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V},$	500		1150		ns
			$2.3 \text{ V} \leq \text{V}_{\text{b}} \leq 2.7 \text{ V},$					
			C_b = 30 pF, R_b = 2.7 k Ω					
			$1.8 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V},$	1150		1150		ns
			1.6 V \leq V _b \leq 2.0 V ^{Note} ,					
			C_b = 30 pF, R_b = 5.5 k Ω					
SCKp high-level width	t ĸнı			tксү1/2—75		tксү1/2-75		ns
				tксү1/2-170		tксү1/2–170		ns
		$1.8 V \leq V_{DD} <$	3.3 V, 1.6 V \leq V_b \leq 2.0 V ^{Note} ,	tксү1/2 –458		tксү1/2-458		ns
		C _b = 30 pF, R	_b = 5.5 kΩ					
SCKp low-level width	t ĸ∟1	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq$	5.5 V, 2.7 V \leq V _b \leq 4.0 V,	tксү1/2-12		tксү1/2–50		ns
		C _b = 30 pF, R	_b = 1.4 kΩ					
		$2.7 V \leq V_{DD} <$	4.0 V, 2.3 V \leq V _b \leq 2.7 V,	tксү1/2-18		tксү1/2–50		ns
		C _b = 30 pF, R	_b = 2.7 kΩ					
		$1.8 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, \ 1.6 \text{ V} \le \text{V}_{\text{b}} \le 2.0 \text{ V}^{\text{Note}},$		tксү1/2—50		tксү1/2–50		ns
		C _b = 30 pF, R	_b = 5.5 kΩ					

 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Note Use it with $V_{DD} \ge V_b$.

- Cautions 1. Select the TTL input buffer for the SIp pin and the N-ch open drain output (V_{DD} tolerance) mode for the SOp pin and SCKp pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For V_{IH} and V_{IL}, see the DC characteristics with TTL input buffer selected.
 CSI01 and CSI11 cannot communicate at different potential.
- **Remarks 1.** R_b [Ω]: Communication line (SCKp, SOp) pull-up resistance, C_b [F]: Communication line (SCKp, SOp) load capacitance, V_b [V]: Communication line voltage
 - **2.** p: CSI number (p = 00, 20)



(8) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified SPI (CSI) mode) (master mode, SCKp... internal clock output) (2/3)

Parameter	Symbol	Conditions		h-speed Mode		v-speed Mode	Unit
			MIN.	MAX.	MIN.	MAX.	
SIp setup time (to SCKp↑) ^{Note 1}	tsik1	$\begin{array}{l} 4.0 \; V \leq V_{DD} \leq 5.5 \; V, 2.7 \; V \leq V_{b} \leq 4.0 \; V, \\ \\ \mathbf{C}_{b} = 30 \; pF, \; R_{b} = 1.4 \; k\Omega \end{array}$	81		479		ns
		$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_b \leq 2.7 \; V, \\ C_b = 30 \; pF, \; R_b = 2.7 \; k\Omega \end{array}$	177		479		ns
		$\label{eq:VDD} \begin{split} 1.8 \ V \leq V_{DD} < 3.3 \ V, \ 1.6 \ V \leq V_b \leq 2.0 \ V^{\text{Note 2}}, \\ C_b = 30 \ pF, \ R_b = 5.5 \ k\Omega \end{split}$	479		479		ns
SIp hold time (from SCKp↑) ^{Note 1}	tksi1		19		19		ns
		$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_b \leq 2.7 \; V, \\ C_b = 30 \; pF, \; R_b = 2.7 \; k\Omega \end{array}$	19		19		ns
		$\label{eq:VDD} \begin{split} 1.8 \ V \leq V_{DD} < 3.3 \ V, \ 1.6 \ V \leq V_b \leq 2.0 \ V \ ^{\text{Note 2}}, \\ C_b = 30 \ pF, \ R_b = 5.5 \ k\Omega \end{split}$	19		19		ns
Delay time from SCKp↓ to	tkso1			100		100	ns
SOp output ^{Note 1}		$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_b \leq 2.7 \; V, \\ C_b = 30 \; pF, \; R_b = 2.7 \; k\Omega \end{array}$		195		195	ns
		$\label{eq:VDD} \begin{array}{l} 1.8 \mbox{ V} \leq \mbox{ V}_{\rm DD} < 3.3 \mbox{ V}, \ 1.6 \mbox{ V} \leq \mbox{ V}_{\rm b} \leq 2.0 \mbox{ V}^{\mbox{ Note 2}}, \\ C_{\rm b} = 30 \mbox{ pF}, \ R_{\rm b} = 5.5 \mbox{ k}\Omega \end{array}$		483		483	ns

$(T_A = -40 \text{ to } +85^{\circ}C, 1.8 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

Notes 1. When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1.

2. Use it with $V_{DD} \ge V_b$.

(Cautions and Remarks are listed on the next page.)




(8) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified SPI (CSI) mode) (master mode, SCKp... internal clock output) (3/3)

Parameter	Symbol	Conditions		h-speed Mode	``	/-speed Mode	Unit
			MIN.	MAX.	MIN.	MAX.	
SIp setup time (to SCKp↓) ^{Note 1}	tsik1	$\begin{array}{l} 4.0 \; V \leq V_{DD} \leq 5.5 \; V, 2.7 \; V \leq V_{b} \leq 4.0 \; V, \\ C_{b} = 30 \; pF, \; R_{b} = 1.4 \; k\Omega \end{array}$	44		110		ns
		$ \begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 30 \ pF, \ R_b = 2.7 \ k\Omega \end{array} $	44		110		ns
			110		110		ns
SIp hold time (from SCKp↓) ^{Note 1}	tksi1		19		19		ns
		$\begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 30 \ pF, \ R_b = 2.7 \ k\Omega \end{array}$	19		19		ns
			19		19		ns
Delay time from SCKp↑ to	tkso1			25		25	ns
SOp output ^{Note 1}				25		25	ns
				25		25	ns


 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

- **Notes 1.** When DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - **2.** Use it with $V_{DD} \ge V_b$.
- Cautions 1. Select the TTL input buffer for the SIp pin and the N-ch open drain output (V_{DD} tolerance) mode for the SOp pin and SCKp pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For V_{IH} and V_{IL}, see the DC characteristics with TTL input buffer selected.
 2. CSI01 and CSI11 cannot communicate at different potential.
- **Remarks 1.** R_b [Ω]: Communication line (SCKp, SOp) pull-up resistance, C_b [F]: Communication line (SCKp, SOp) load capacitance, V_b [V]: Communication line voltage
 - **2.** p: CSI number (p = 00, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0)

Simplified SPI (CSI) mode connection diagram (during communication at different potential)








Simplified SPI (CSI) mode serial transfer timing (master mode) (during communication at different potential) (When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1)

Simplified SPI (CSI) mode serial transfer timing (master mode) (during communication at different potential) (When DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.)



(9) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified SPI (CSI) mode) (slave mode, SCKp... external clock input)

Parameter	Symbol	C	onditions	HS (high-sp Mod	,	LS (low-spe Mod	,	Unit
				MIN.	MAX.	MIN.	MAX.	
SCKp cycle time Note 1	t ксү2	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V},$	20 MHz < fмск ≤ 24 MHz	12/fмск		_		ns
		$2.7~V \leq V_b \leq 4.0~V$	8 MHz < fмск ≤ 20 MHz	10/fмск		_		ns
			4 MHz < fмск ≤ 8 MHz	8/f мск		16/fмск		ns
			fмск ≤ 4 MHz	6/fмск		10/fмск		ns
		$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V},$	20 MHz < fмск ≤ 24 MHz	16/f мск		_		ns
		$2.3~V \leq V_b \leq 2.7~V$	16 MHz < fмск ≤ 20 MHz	14/f мск		_		ns
			8 MHz < fмск ≤ 16 MHz	12/fмск		_		ns
			4 MHz < fмск ≤ 8 MHz	8/f мск		16/ f мск		ns
			fмск ≤ 4 MHz	6/fмск		10/ f мск		ns
		$1.8 V \le V_{DD} < 3.3 V$,	20 MHz < fмск ≤ 24 MHz	36/f мск		-		ns
		$1.6~V \leq V_b \leq 2.0~V$	16 MHz < fмск ≤ 20 MHz	32/f мск		-		ns
		Note 2	8 MHz < fмск ≤ 16 MHz	26/f мск		-		ns
			4 MHz < fмск ≤ 8 MHz	16/f мск		16/fмск		ns
			fмск ≤ 4 MHz	10/f мск		10/fмск		ns
SCKp high-/low-level	tкн2,	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V},$	$2.7 \text{ V} \leq \text{V}_{b} \leq 4.0 \text{ V}$	tkcy2/2 – 12		tксү2/2 – 50		ns
width	t _{KL2}	$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V},$	$2.3 \text{ V} \leq \text{V}_{b} \leq 2.7 \text{ V}$	tkcy2/2 – 18		tксү2/2 – 50		ns
		$1.8 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V},$	1.6 V \leq V _b \leq 2.0 V ^{Note 2}	tkcy2/2 - 50		tксү2/2 – 50		ns
SIp setup time	tsik2	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V},$	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 4.0 \text{ V}$	1/fмск + 20		1/fмск + 30		ns
(to SCKp↑) ^{Note 3}		$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V},$	$2.3 \text{ V} \leq \text{V}_{b} \leq 2.7 \text{ V}$	1/fмск + 20		1/fмск + 30		ns
		$1.8 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V},$	1.6 V \leq V _{DD} \leq 2.0 V ^{Note 2}	1/fмск + 30		1/fмск + 30		ns
SIp hold time (from SCKp↑) ^{Note 4}	tksi2			1/fмск + 31		1/fмск + 31		ns
Delay time from	tĸso2	$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$	$2.7 \text{ V} \le \text{V}_{b} \le 4.0 \text{ V},$		2/fмск +		2/fмск +	ns
SCKp↓ to SOp		$C_b = 30 \text{ pF}, R_b = 1.4$	kΩ		120		573	
output ^{Note 5}		$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V},$	$2.3 \text{ V} \le \text{V}_{b} \le 2.7 \text{ V},$		2/fмск +		2/fмск +	ns
		C _b = 30 pF, R _b = 2.7	kΩ		214		573	
		$1.8 V \le V_{DD} < 3.3 V$,	$1.6 \text{ V} \le \text{V}_{b} \le 2.0 \text{ V}^{\text{Note 2}},$		2/fмск +		2/fмск +	ns
		C _b = 30 pF, R _b = 5.5	kΩ		573		573	

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$


Notes 1. Transfer rate in the SNOOZE mode: MAX. 1 Mbps

- **2.** Use it with $V_{DD} \ge V_b$.
- **3.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp setup time becomes "to SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
- **4.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp hold time becomes "from SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
- 5. When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The delay time to SOp output becomes "from SCKp↑" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.

Cautions 1. Select the TTL input buffer for the SIp and SCKp pins and the N-ch open drain output (VDD tolerance) mode for the SOp pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For VH and VL, see the DC characteristics with TTL input buffer selected.


2. CSI01 and CSI11 cannot communicate at different potential.

Simplified SPI (CSI) mode connection diagram (during communication at different potential)




- **Remarks 1.** R_b [Ω]: Communication line (SOp) pull-up resistance, C_b [F]: Communication line (SOp) load capacitance, V_b [V]: Communication line voltage
 - **2.** p: CSI number (p = 00, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0)
 - f_{MCK}: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn). m: Unit number, n: Channel number (mn = 00, 10))

Simplified SPI (CSI) mode serial transfer timing (slave mode) (during communication at different potential) (When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1.)



Simplified SPI (CSI) mode serial transfer timing (slave mode) (during communication at different potential) (When DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.)



Remark p: CSI number (p = 00, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0)



(10) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified l²C mode) (T_A = -40 to +85°C, 1.8 V \leq V_{DD} \leq 5.5 V, V_{SS} = 0 V)


Parameter	Symbol	Conditions		h-speed Mode	-	v-speed Mode	Unit
			MIN.	MAX.	MIN.	MAX.	
SCLr clock frequency	fscL	$\begin{array}{l} 4.0 \; V \leq V_{DD} \leq 5.5 \; V, 2.7 \; V \leq V_{b} \leq 4.0 \; V, \\ \\ \mathbf{C}_{b} = 100 \; pF, \; R_{b} = 2.8 \; k\Omega \end{array}$		400 ^{Note1}		300 ^{Note1}	kHz
		$\begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 100 \ pF, \ R_b = 2.7 \ k\Omega \end{array}$		400 ^{Note1}		300 ^{Note1}	kHz
		$\begin{array}{l} 1.8 \ V \leq V_{\text{DD}} < 3.3 \ V, \ 1.6 \ V \leq V_{b} \leq 2.0 \ V, \\ \text{Note2} \\ C_{b} = 100 \ \text{pF}, \ R_{b} = 5.5 \ \text{k}\Omega \end{array}$		300 ^{Note1}		300 ^{Note1}	kHz
Hold time when SCLr = "L"	tLOW	4.0 V \leq V _{DD} \leq 5.5 V, 2.7 V \leq V _b \leq 4.0 V, C _b = 100 pF, R _b = 2.8 kΩ	1150		1550		ns
		$\begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 100 \ pF, \ R_b = 2.7 \ k\Omega \end{array}$	1150		1550		ns
		$1.8 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, 1.6 \text{ V} \le \text{V}_{b} \le 2.0 \text{ V}, \text{^{Note2}}$ $C_{b} = 100 \text{ pF}, \text{ R}_{b} = 5.5 \text{ k}\Omega$	1550		1550		ns
Hold time when SCLr = "H"	tніgн	4.0 V \leq V _{DD} \leq 5.5 V, 2.7 V \leq V _b \leq 4.0 V, C _b = 100 pF, R _b = 2.8 k Ω	675		610		ns
		$\begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 100 \ pF, \ R_b = 2.7 \ k\Omega \end{array}$	600		610		ns
		1.8 V ≤ V _{DD} < 3.3 V, 1.6 V ≤ V _b ≤ 2.0 V, ^{Note2} C _b = 100 pF, R _b = 5.5 kΩ	610		610		ns
Data setup time (reception)	tsu:dat	4.0 V \leq V _{DD} \leq 5.5 V, 2.7 V \leq V _b \leq 4.0 V, C _b = 100 pF, R _b = 2.8 kΩ	1/fмск + 190 Note3		1/fмск + 190 Note3		ns
		$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V}, 2.3 \text{ V} \le \text{V}_{b} \le 2.7 \text{ V},$ $C_{b} = 100 \text{ pF}, \text{ R}_{b} = 2.7 \text{ k}\Omega$	1/fмск + 190 Note3		1/fмск + 190 Note3		ns
		$\label{eq:VDD} \begin{array}{l} 1.8 \ V \leq V_{\text{DD}} < 3.3 \ V, \ 1.6 \ V \leq V_{b} \leq 2.0 \ V, \\ Note2 \\ C_{b} = 100 \ p\text{F}, \ R_{b} = 5.5 \ k\Omega \end{array}$	1/fмск + 190 Note3		1/fмск + 190 Note3		ns
Data hold time (transmission)	thd:dat	$\begin{array}{l} 4.0 \; V \leq V_{DD} \leq 5.5 \; V, 2.7 \; V \leq V_b \leq 4.0 \; V, \\ C_b = 100 \; pF, \; R_b = 2.8 \; k\Omega \end{array}$	0	355	0	355	ns
		$\begin{array}{l} 2.7 \ V \leq V_{\text{DD}} < 4.0 \ V, \ 2.3 \ V \leq V_{b} \leq 2.7 \ V, \\ C_{b} = 100 \ p\text{F}, \ R_{b} = 2.7 \ k\Omega \end{array}$	0	355	0	355	ns
		$\begin{array}{l} 1.8 \ V \leq V_{\text{DD}} < 3.3 \ V, \ 1.6 \ V \leq V_{b} \leq 2.0 \ V, \\ \text{Note2} \\ C_{b} = 100 \ \text{pF}, \ R_{b} = 5.5 \ \text{k}\Omega \end{array}$	0	405	0	405	ns

Notes 1. The value must be equal to or less than fmck/4.


- **2.** Use it with $V_{DD} \ge V_b$.
- 3. Set tsu:DAT so that it will not exceed the hold time when SCLr = "L" or SCLr = "H".
- Cautions 1. Select the TTL input buffer and the N-ch open drain output (V_{DD} tolerance) mode for the SDAr pin and the N-ch open drain output (V_{DD} tolerance) mode for the SCLr pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For V_{IH} and V_{IL}, see the DC characteristics with TTL input buffer selected.
 - 2. IIC01 and IIC11 cannot communicate at different potential.

(**Remarks** are listed on the next page.)

Simplified I²C mode connection diagram (during communication at different potential)



Simplified I²C mode serial transfer timing (during communication at different potential)



- **Remarks 1.** R_b [Ω]: Communication line (SDAr, SCLr) pull-up resistance, C_b [F]: Communication line (SDAr, SCLr) load capacitance, V_b [V]: Communication line voltage
 - **2.** r: IIC Number (r = 00, 20)
 - fMCK: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn).
 m: Unit number (m = 0,1), n: Channel number (n = 0))
 - 4. Simplified I²C mode is supported only by the R5F102 products.




2.5.2 Serial interface IICA

Parameter	Symbol	Conditions	HS	(high-spee	ed main) m	node	Unit
			LS	(low-spee	d main) m	ode	
			Standa	rd Mode	Fast	Mode	
			MIN.	MAX.	MIN.	MAX.	
SCLA0 clock frequency	fsc∟	Fast mode: fc∟к≥ 3.5 MHz			0	400	kHz
		Normal mode: fcLκ≥ 1 MHz	0	100			kHz
Setup time of restart condition	tsu:sta		4.7		0.6		μs
Hold time ^{Note 1}	thd:sta		4.0		0.6		μs
Hold time when SCLA0 = "L"	t LOW		4.7		1.3		μs
Hold time when SCLA0 = "H"	tнigн		4.0		0.6		μs
Data setup time (reception)	tsu:dat		250		100		ns
Data hold time (transmission)Note 2	thd:dat		0	3.45	0	0.9	μs
Setup time of stop condition	tsu:sto		4.0		0.6		μs
Bus-free time	t BUF		4.7		1.3		μs

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Notes 1. The first clock pulse is generated after this period when the start/restart condition is detected.

- Caution Only in the 30-pin products, the values in the above table are applied even when bit 2 (PIOR2) in the peripheral I/O redirection register (PIOR) is 1. At this time, the pin characteristics (IOH1, IOL1, VOH1, VOL1) must satisfy the values in the redirect destination.
- **Remark** The maximum value of Cb (communication line capacitance) and the value of Rb (communication line pull-up resistor) at that time in each mode are as follows.



IICA serial transfer timing



^{2.} The maximum value (MAX.) of the during normal transfer and a clock stretch state is inserted in the ACK (acknowledge) timing.

2.6 Analog Characteristics

2.6.1 A/D converter characteristics

Classification of A/D converter characteristics

Input channel		Reference Voltage	
	Reference voltage (+) = AVREFP Reference voltage (–) = AVREFM	Reference voltage (+) = VDD Reference voltage (-) = Vss	Reference voltage (+) = V _{BGR} Reference voltage (–) = AV _{REFM}
ANI0 to ANI3	Refer to 2.6.1 (1) .	Refer to 2.6.1 (3) .	Refer to 2.6.1 (4) .
ANI16 to ANI22	Refer to 2.6.1 (2) .		
Internal reference voltage	Refer to 2.6.1 (1) .		-
Temperature sensor output voltage			

(1) When reference voltage (+) = AV_{REFP}/ANI0 (ADREFP1 = 0, ADREFP0 = 1), reference voltage (–) = AV_{REFM}/ANI1 (ADREFM = 1), target pin: ANI2, ANI3, internal reference voltage, and temperature sensor output voltage

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{AV}_{\text{REFP}} \le \text{VDD} \le 5.5 \text{ V}, \text{ V}_{\text{SS}} = 0 \text{ V}, \text{ Reference voltage (+)} = \text{AV}_{\text{REFP}}, \text{ Reference voltage (-)} = \text{AV}_{\text{REFM}} = 0 \text{ V}$

Parameter	Symbol	Cor	nditions	MIN.	TYP.	MAX.	Unit
Resolution	RES			8		10	bit
Overall error ^{Note 1}	AINL	10-bit resolution			1.2	±3.5	LSB
		AV _{REFP} = V _{DD} ^{Note 3}			1.2	±7.0 Note 4	LSB
Conversion time	t CONV	10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.125		39	μs
		Target pin: ANI2, ANI3	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	3.1875		39	μs
			$1.8 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	17		39	μs
				57		95	μs
		10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.375		39	μs
		Target pin: Internal	$2.7 \text{ V} \leq \text{V}_{DD} \leq 5.5 \text{ V}$	3.5625		39	μs
	temperature output volta (HS (high-sj mode)	reference voltage, and temperature sensor output voltage (HS (high-speed main) mode)	2.4 V ≤ V _{DD} ≤ 5.5 V	17		39	μs
Zero-scale error ^{Notes 1, 2}	EZS	10-bit resolution				±0.25	%FSR
		AV _{REFP} = V _{DD} Note 3				±0.50 ^{Note 4}	%FSR
Full-scale error ^{Notes 1, 2}	EFS	10-bit resolution				±0.25	%FSR
		AV _{REFP} = V _{DD} ^{Note 3}				±0.50 ^{Note 4}	%FSR
Integral linearity error ^{Note 1}	ILE	10-bit resolution				±2.5	LSB
		AV _{REFP} = V _{DD} ^{Note 3}				±5.0 Note 4	LSB
Differential linearity error	DLE	10-bit resolution				±1.5	LSB
Note 1		AV _{REFP} = V _{DD} ^{Note 3}				±2.0 Note 4	LSB
Analog input voltage	VAIN	ANI2, ANI3		0		AVREFP	V
		Internal reference voltage (2.4 V ≤ V _{DD} ≤ 5.5 V, HS	e (high-speed main) mode)		V _{BGR} Note 5		V
		Temperature sensor outp (2.4 V \leq VDD \leq 5.5 V, HS	out voltage (high-speed main) mode)	N	VTMPS25 Note	5	V

(Notes are listed on the next page.)



- **Notes 1.** Excludes quantization error (±1/2 LSB).
 - 2. This value is indicated as a ratio (%FSR) to the full-scale value.
 - 3. When AV_{REFP} < V_{DD}, the MAX. values are as follows. Overall error: Add ±1.0 LSB to the MAX. value when AV_{REFP} = V_{DD}. Zero-scale error/Full-scale error: Add ±0.05%FSR to the MAX. value when AV_{REFP} = V_{DD}. Integral linearity error/ Differential linearity error: Add ±0.5 LSB to the MAX. value when AV_{REFP} = V_{DD}.
 - 4. Values when the conversion time is set to 57 μs (min.) and 95 μs (max.).
 - 5. Refer to 2.6.2 Temperature sensor/internal reference voltage characteristics.
- (2) When reference voltage (+) = AVREFP/ANI0 (ADREFP1 = 0, ADREFP0 = 1), reference voltage (-) = AVREFM/ANI1 (ADREFM = 1), target pin: ANI16 to ANI22

 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{AV}_{REFP} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V}, \text{ Reference voltage (+)} = \text{AV}_{REFP}, \text{ Reference voltage (-)} = \text{AV}_{REFM} = 0 \text{ V}$

Parameter	Symbol	Conditio	ns	MIN.	TYP.	MAX.	Unit
Resolution	Res			8		10	bit
Overall error Note 1	AINL	10-bit resolution	/ _{REFP} = V _{DD} Note 3		1.2	±5.0	LSB
		AV _{REFP} = V _{DD} ^{Note 3}			1.2	±8.5 Note 4	LSB
Conversion time	t _{CONV}	10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.125		39	μs
		Target ANI pin: ANI16 to ANI22	2.7 V ≤ VDD ≤ 5.5 V	3.1875		39	μs
			1.8 V ≤ VDD ≤ 5.5 V	17		39	μs
				57		95	μs
Zero-scale error Notes 1, 2	EZS	10-bit resolution				±0.35	%FSR
		AV _{REFP} = V _{DD} ^{Note 3}				±0.60 Note 4	%FSR
Full-scale error Notes 1, 2	EFS	10-bit resolution				±0.35	%FSR
		AV _{REFP} = V _{DD} ^{Note 3}				±0.60 Note 4	%FSR
Integral linearity error Note 1	ILE	10-bit resolution				±3.5	LSB
		AV _{REFP} = V _{DD} ^{Note 3}				±6.0 Note 4	LSB
Differential linearity	DLE	10-bit resolution				±2.0	LSB
error Note 1		AV _{REFP} = V _{DD} ^{Note 3}				±2.5 Note 4	LSB
Analog input voltage	VAIN	ANI16 to ANI22		0		AV _{REFP} and V _{DD}	V

Notes 1. Excludes quantization error (±1/2 LSB).

- 2. This value is indicated as a ratio (%FSR) to the full-scale value.
- 3. When AV_{REFP} ≤ V_{DD}, the MAX. values are as follows. Overall error: Add ±4.0 LSB to the MAX. value when AV_{REFP} = V_{DD}. Zero-scale error/Full-scale error: Add ±0.20%FSR to the MAX. value when AV_{REFP} = V_{DD}. Integral linearity error/ Differential linearity error: Add ±2.0 LSB to the MAX. value when AV_{REFP} = V_{DD}.
- 4. When the conversion time is set to 57 μs (min.) and 95 μs (max.).

(3) When reference voltage (+) = V_{DD} (ADREFP1 = 0, ADREFP0 = 0), reference voltage (-) = V_{ss} (ADREFM = 0), target pin: ANI0 to ANI3, ANI16 to ANI22, internal reference voltage, and temperature sensor output voltage

Parameter	Symbol	Condition	าร	MIN.	TYP.	MAX.	Unit
Resolution	Res			8		10	bit
Overall error ^{Note 1}	AINL	10-bit resolution			1.2	±7.0	LSB
					1.2	±10.5 ^{Note 3}	LSB
Conversion time	t CONV	10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.125		39	μs
		Target pin: ANI0 to ANI3,	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	3.1875		39	μs
		ANI16 to ANI22	1.8 V ≤ V _{DD} ≤ 5.5 V	17		39	μs
				57		95	μs
Conversion time	t CONV	10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.375		39	μs
		Target pin: internal reference	2.7 V ≤ VDD ≤ 5.5 V	3.5625		39	μs
		voltage, and temperature ensor output voltage (HS high-speed main) mode) $2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		17		39	μs
Zero-scale error ^{Notes 1, 2}	EZS	10-bit resolution				±0.60	%FSR
						±0.85 Note 3	%FSR
Full-scale error ^{Notes 1, 2}	EFS	10-bit resolution				±0.60	%FSR
						±0.85 Note 3	%FSR
Integral linearity error ^{Note 1}	ILE	10-bit resolution				±4.0	LSB
						±6.5 Note 3	LSB
Differential linearity error Note 1	DLE	10-bit resolution				±2.0	LSB
						±2.5 Note 3	LSB
Analog input voltage	VAIN	ANI0 to ANI3, ANI16 to ANI2	2	0		Vdd	V
		Internal reference voltage (2.4 V ≤ Vɒɒ ≤ 5.5 V, HS (higł	n-speed main) mode)	V _{BGR} Note 4			V
		Temperature sensor output v (2.4 V \leq VDD \leq 5.5 V, HS (high	•	Ň	VTMPS25 Note 4		

Notes 1. Excludes quantization error (±1/2 LSB).

2. This value is indicated as a ratio (%FSR) to the full-scale value.

3. When the conversion time is set to 57 μs (min.) and 95 μs (max.).

4. Refer to 2.6.2 Temperature sensor/internal reference voltage characteristics.

(4) When reference voltage (+) = Internal reference voltage (ADREFP1 = 1, ADREFP0 = 0), reference voltage (-) = AV_{REFM} (ADREFM = 1), target pin: ANI0, ANI2, ANI3, and ANI16 to ANI22

 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, \text{ V}_{\text{SS}} = 0 \text{ V}, \text{ Reference voltage (+)} = \text{V}_{\text{BGR}}^{\text{Note 3}}, \text{ Reference voltage (-)} = \text{AV}_{\text{REFM}}^{\text{Note 4}}$ Note ⁴= 0 V, HS (high-speed main) mode)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Resolution	Res			8		bit
Conversion time	t CONV	8-bit resolution	17		39	μs
Zero-scale error ^{Notes 1, 2}	EZS	8-bit resolution			±0.60	%FSR
Integral linearity error ^{Note 1}	ILE	8-bit resolution			±2.0	LSB
Differential linearity error Note 1	DLE	8-bit resolution			±1.0	LSB
Analog input voltage	VAIN		0		$V_{\text{BGR}}{}^{\text{Note 3}}$	V

Notes 1. Excludes quantization error (±1/2 LSB).

2. This value is indicated as a ratio (%FSR) to the full-scale value.

3. Refer to 2.6.2 Temperature sensor/internal reference voltage characteristics.

4. When reference voltage (–) = Vss, the MAX. values are as follows.

Zero-scale error: Add $\pm 0.35\%$ FSR to the MAX. value when reference voltage (–) = AV_{REFM}. Integral linearity error: Add ± 0.5 LSB to the MAX. value when reference voltage (–) = AV_{REFM}. Differential linearity error: Add ± 0.2 LSB to the MAX. value when reference voltage (–) = AV_{REFM}.



2.6.2 Temperature sensor/internal reference voltage characteristics

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Temperature sensor output voltage	VTMPS25	Setting ADS register = 80H, T _A = +25°C		1.05		V
Internal reference voltage	VBGR	Setting ADS register = 81H	1.38	1.45	1.50	V
Temperature coefficient	Fvtmps	Temperature sensor output voltage that depends on the temperature		-3.6		mV/°C
Operation stabilization wait time	tamp		5			μs


(T_A = -40 to +85°C, 2.4 V \leq V_{DD} \leq 5.5 V, V_{SS} = 0 V, HS (high-speed main) mode

2.6.3 POR circuit characteristics

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, V_{\text{SS}} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Detection voltage	Vpor	The power supply voltage is rising.	1.47	1.51	1.55	V
	Vpdr	The power supply voltage is falling.	1.46	1.50	1.54	V
Minimum pulse width Note	T _{PW}		300			μs

Note Minimum time required for a POR reset when V_{DD} exceeds below V_{PDR}. This is also the minimum time required for a POR reset from when V_{DD} exceeds below 0.7 V to when V_{DD} exceeds V_{POR} while STOP mode is entered or the main system clock is stopped through setting bit 0 (HIOSTOP) and bit 7 (MSTOP) in the clock operation status control register (CSC).





2.6.4 LVD circuit characteristics

LVD Detection Voltage of Reset Mode and Interrupt Mode

 $(T_A = -40 \text{ to } +85^{\circ}\text{C}, V_{PDR} \le V_{DD} \le 5.5 \text{ V}, \text{ Vss} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Detection supply voltage	VLVD0	The power supply voltage is rising.	3.98	4.06	4.14	V
		The power supply voltage is falling.	3.90	3.98	4.06	V
	VLVD1	The power supply voltage is rising.	3.68	3.75	3.82	V
		The power supply voltage is falling.	3.60	3.67	3.74	V
	VLVD2	The power supply voltage is rising.	3.07	3.13	3.19	V
		The power supply voltage is falling.	3.00	3.06	3.12	V
	VLVD3	The power supply voltage is rising.	2.96	3.02	3.08	V
		The power supply voltage is falling.	2.90	2.96	3.02	V
	VLVD4	The power supply voltage is rising.	2.86	2.92	2.97	V
		The power supply voltage is falling.	2.80	2.86	2.91	V
	VLVD5	The power supply voltage is rising.	2.76	2.81	2.87	V
		The power supply voltage is falling.	2.70	2.75	2.81	V
	VLVD6	The power supply voltage is rising.	2.66	2.71	2.76	V
		The power supply voltage is falling.	2.60	2.65	2.70	V
	VLVD7	The power supply voltage is rising.	2.56	2.61	2.66	V
		The power supply voltage is falling.	2.50	2.55	2.60	V
	VLVD8	The power supply voltage is rising.	2.45	2.50	2.55	V
		The power supply voltage is falling.	2.40	2.45	2.50	V
	VLVD9	The power supply voltage is rising.	2.05	2.09	2.13	V
		The power supply voltage is falling.	2.00	2.04	2.08	V
	VLVD10	The power supply voltage is rising.	1.94	1.98	2.02	V
		The power supply voltage is falling.	1.90	1.94	1.98	V
	VLVD11	The power supply voltage is rising.	1.84	1.88	1.91	V
		The power supply voltage is falling.	1.80	1.84	1.87	V
Minimum pulse width	t∟w		300			μs
Detection delay time					300	μs



LVD detection voltage of interrupt & reset mode $(T_A = -40 \text{ to } +85^\circ\text{C}, V_{PDR} \le V_{DD} \le 5.5 \text{ V}, V_{SS} = 0 \text{ V})$

Parameter	Symbol		Con	ditions	MIN.	TYP.	MAX.	Unit
Interrupt and reset	VLVDB0	VPOC2,	VPOC1, VPOC0 = 0, 0, 1, fal	ling reset voltage	1.80	1.84	1.87	V
mode	VLVDB1		LVIS1, LVIS0 = 1, 0	Rising reset release voltage	1.94	1.98	2.02	V
				Falling interrupt voltage	1.90	1.94	1.98	V
	VLVDB2		LVIS1, LVIS0 = 0, 1	Rising reset release voltage	2.05	2.09	2.13	V
				Falling interrupt voltage	2.00	2.04	2.08	V
	VLVDB3		LVIS1, LVIS0 = 0, 0	Rising reset release voltage	3.07	3.13	3.19	V
				Falling interrupt voltage	3.00	3.06	3.12	V
	VLVDC0	Vpoc2,	VPOC1, VPOC0 = 0, 1, 0, fal	ling reset voltage	2.40	2.45	2.50	V
	VLVDC1		LVIS1, LVIS0 = 1, 0	Rising reset release voltage	2.56	2.61	2.66	V
				Falling interrupt voltage	2.50	2.55	2.60	V
	VLVDC2		LVIS1, LVIS0 = 0, 1	Rising reset release voltage	2.66	2.71	2.76	V
				Falling interrupt voltage	2.60	2.65	2.70	V
	VLVDC3		LVIS1, LVIS0 = 0, 0	Rising reset release voltage	3.68	3.75	3.82	V
				Falling interrupt voltage	3.60	3.67	3.74	V
	VLVDD0	Vpoc2,	VPOC1, VPOC1 = 0, 1, 1, fal	ling reset voltage	2.70	2.75	2.81	V
	VLVDD1		LVIS1, LVIS0 = 1, 0	Rising reset release voltage	2.86	2.92	2.97	V
				Falling interrupt voltage	2.80	2.86	2.91	V
	VLVDD2		LVIS1, LVIS0 = 0, 1	Rising reset release voltage	2.96	3.02	3.08	V
				Falling interrupt voltage	2.90	2.96	3.02	V
	VLVDD3		LVIS1, LVIS0 = 0, 0	Rising reset release voltage	3.98	4.06	4.14	V
				Falling interrupt voltage	3.90	3.98	4.06	V

2.6.5 Power supply voltage rising slope characteristics

$(T_A = -40 \text{ to } +85^{\circ}C, V_{SS} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Power supply voltage rising slope	SVDD				54	V/ms


Caution Make sure to keep the internal reset state by the LVD circuit or an external reset until V_{DD} reaches the operating voltage range shown in 2.4 AC Characteristics.

2.7 RAM Data Retention Characteristics

$(T_A = -40 \text{ to } +85^\circ \text{C}, \text{V}_{\text{SS}} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Data retention supply voltage	VDDDR		1.46 Note		5.5	V

Note This depends on the POR detection voltage. For a falling voltage, data in RAM are retained until the voltage reaches the level that triggers a POR reset but not once it reaches the level at which a POR reset is generated.



2.8 Flash Memory Programming Characteristics

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
System clock frequency	fськ		1		24	MHz
Code flash memory rewritable times Notes 1, 2, 3	Cerwr	Retained for 20 years T _A = 85°C	1,000			Times
Data flash memory rewritable times Notes 1, 2, 3		Retained for 1 year T _A = 25°C		1,000,000		
		Retained for 5 years T _A = 85°C	100,000			
		Retained for 20 years T _A = 85°C	10,000			

Notes 1. 1 erase + 1 write after the erase is regarded as 1 rewrite. The retaining years are until next rewrite after the rewrite.

- 2. When using flash memory programmer and Renesas Electronics self programming library
- **3.** These are the characteristics of the flash memory and the results obtained from reliability testing by Renesas Electronics Corporation.

2.9 Dedicated Flash Memory Programmer Communication (UART)


($(1_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$									
	Parameter	Parameter Symbol Conditions		MIN.	TYP.	MAX.	Unit			
•	Transfer rate	During serial programming		115,200		1,000,000	bps			

.

2.10 Timing of Entry to Flash Memory Programming Modes

$(T_A = -40 \text{ to } +85^{\circ}\text{C}, 1.8 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Time to complete the communication for the initial setting after the external reset is released	tsuinit	POR and LVD reset are released before external reset release			100	ms
Time to release the external reset after the TOOL0 pin is set to the low level	ts∪	POR and LVD reset are released before external reset release	10			μs
Time to hold the TOOL0 pin at the low level after the external reset is released (excluding the processing time of the firmware to control the flash memory)	tно	POR and LVD reset are released before external reset release	1			ms



- <1> The low level is input to the TOOL0 pin.
- <2> The external reset is released (POR and LVD reset must be released before the external reset is released.).
- <3> The TOOL0 pin is set to the high level.
- <4> Setting of the flash memory programming mode by UART reception and complete the baud rate setting.
- Remark tsuinit: Communication for the initial setting must be completed within 100 ms after the external reset is released during this period.
 - Time to release the external reset after the TOOL0 pin is set to the low level tsu:
 - Time to hold the TOOL0 pin at the low level after the external reset is released (excluding the processing thd: time of the firmware to control the flash memory)



3. ELECTRICAL SPECIFICATIONS (G: INDUSTRIAL APPLICATIONS $T_A = -40$ to +105°C)

This chapter describes the following electrical specifications.

Target products G: Industrial applications $T_A = -40$ to $+105^{\circ}C$

R5F102xxGxx

- Cautions 1. The RL78 microcontrollers have an on-chip debug function, which is provided for development and evaluation. Do not use the on-chip debug function in products designated for mass production, because the guaranteed number of rewritable times of the flash memory may be exceeded when this function is used, and product reliability therefore cannot be guaranteed. Renesas Electronics is not liable for problems occurring when the on-chip debug function is used.
 - 2. The pins mounted depend on the product. Refer to 2.1 Port Functions to 2.2.1 Functions for each product in the RL78/G12 User's Manual.
 - 3. Please contact Renesas Electronics sales office for derating of operation under $T_A = +85^{\circ}C$ to $+105^{\circ}C$. Derating is the systematic reduction of load for the sake of improved reliability.

Remark When the RL78 microcontroller is used in the range of $T_A = -40$ to $+85^{\circ}$ C, see 2. ELECTRICAL SPECIFICATIONS ($T_A = -40$ to $+85^{\circ}$ C).

There are following differences between the products "G: Industrial applications ($T_A = -40$ to +105°C)" and the products "A: Consumer applications, and D: Industrial applications".

Parameter	Applic	ation
	A: Consumer applications, D: Industrial applications	G: Industrial applications
Operating ambient temperature	T _A = -40 to +85°C	T _A = -40 to +105°C
Operating mode	HS (high-speed main) mode:	HS (high-speed main) mode only:
Operating voltage range	2.7 V ≤ V _{DD} ≤ 5.5 V@1 MHz to 24 MHz	2.7 V ≤ V _{DD} ≤ 5.5 V@1 MHz to 24 MHz
	2.4 V ≤ V _{DD} ≤ 5.5 V@1 MHz to 16 MHz	2.4 V ≤ V _{DD} ≤ 5.5 V@1 MHz to 16 MHz
	LS (low-speed main) mode:	
	1.8 V ≤ V _{DD} ≤ 5.5 V@1 MHz to 8 MHz	
High-speed on-chip oscillator	R5F102 products, 1.8 V \leq V _{DD} \leq 5.5 V:	R5F102 products, 2.4 V \leq V _{DD} \leq 5.5 V:
clock accuracy	±1.0%@ T _A = -20 to +85°C	±2.0%@ T _A = +85 to +105°C
	±1.5%@ T _A = -40 to -20°C	±1.0%@ T _A = -20 to +85°C
	R5F103 products, 1.8 V \leq V _{DD} \leq 5.5 V:	±1.5%@ T _A = -40 to -20°C
	±5.0%@ T _A = -40 to +85°C	
Serial array unit	UART	UART
	Simplified SPI (CSI): fcLk/2 (supporting 12 Mbps),	Simplified SPI (CSI): fcLK/4
	fclk/4	Simplified I ² C communication
	Simplified I ² C communication	
Voltage detector	Rise detection voltage: 1.88 V to 4.06 V (12 levels)	Rise detection voltage: 2.61 V to 4.06 V
	Fall detection voltage: 1.84 V to 3.98 V (12 levels)	(8 levels)
		Fall detection voltage: 2.55 V to 3.98 V (8 levels)

Remark The electrical characteristics of the products G: Industrial applications (T_A = -40 to +105°C) are different from those of the products "A: Consumer applications, and D: Industrial applications". For details, refer to **3.1** to

3.10.

3.1 Absolute Maximum Ratings

Absolute Maximum Ratings (T_A = 25°C)

Parameter	Symbols		Conditions	Ratings	Unit
Supply Voltage	VDD			-0.5 to + 6.5	V
REGC terminal input voltage ^{Note1}	VIREGC	REGC		-0.3 to +2.8 and -0.3 to V _{DD} + 0.3 _{Note 2}	V
Input Voltage	VI1	Other than P60, F	261	-0.3 to V _{DD} + 0.3 ^{Note 3}	V
	V ₁₂	P60, P61 (N-ch o	pen drain)	-0.3 to 6.5	V
Output Voltage	Vo			-0.3 to V _{DD} + 0.3 ^{Note 3}	V
Analog input voltage	Vai	20, 24-pin produc	ts: ANI0 to ANI3, ANI16 to ANI22	-0.3 to V _{DD} + 0.3	V
		30-pin products: A	ANI0 to ANI3, ANI16 to ANI19	and –0.3 to AV _{REF} (+)+0.3 ^{Notes 3, 4}	
Output current, high	Іон1	Per pin	Other than P20 to P23	-40	mA
		Total of all pins	All the terminals other than P20 to P23	-170	mA
			20-, 24-pin products: P40 to P42 30-pin products: P00, P01, P40, P120	-70	mA
			20-, 24-pin products: P00 to P03 ^{Note 5} , P10 to P14 30-pin products: P10 to P17, P30, P31, P50, P51, P147	-100	mA
	Іон2	Per pin P20 to P23		-0.5	mA
		Total of all pins		-2	mA
Output current, low	IOL1	Per pin	Other than P20 to P23	40	mA
		Total of all pins	All the terminals other than P20 to P23	170	mA
			20-, 24-pin products: P40 to P42 30-pin products: P00, P01, P40, P120	70	mA
			20-, 24-pin products: P00 to P03 ^{Note 5} , P10 to P14, P60, P61 30-pin products: P10 to P17, P30, P31, P50, P51, P60, P61, P147	100	mA
	IOL2	Per pin	P20 to P23	1	mA
		Total of all pins		5	mA
Operating ambient temperature	TA		·	-40 to +105	°C
Storage temperature	Tstg			-65 to +150	°C

Notes 1. 30-pin product only.

- 2. Connect the REGC pin to Vss via a capacitor (0.47 to 1 μ F). This value determines the absolute maximum rating of the REGC pin. Do not use it with voltage applied.
- 3. Must be 6.5 V or lower.
- 4. Do not exceed AVREF(+) + 0.3 V in case of A/D conversion target pin.
- **5.** 24-pin products only.
- Caution Product quality may suffer if the absolute maximum rating is exceeded even momentarily for any parameter. That is, the absolute maximum ratings are rated values at which the product is on the verge of suffering physical damage, and therefore the product must be used under conditions that ensure that the absolute maximum ratings are not exceeded.
- **Remarks 1.** Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.
 - **2.** AVREF(+): + side reference voltage of the A/D converter.
 - 3. Vss : Reference voltage

3.2 Oscillator Characteristics

3.2.1 X1 oscillator characteristics

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Parameter	Resonator	Conditions	MIN.	TYP.	MAX.	Unit
X1 clock oscillation	Ceramic resonator /	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	1.0		20.0	MHz
frequency (fx) ^{Note}	crystal oscillator	$2.4 \text{ V} \le \text{V}_{\text{DD}} \le 2.7 \text{ V}$	1.0		8.0	

Note Indicates only permissible oscillator frequency ranges. Refer to AC Characteristics for instruction execution time. Request evaluation by the manufacturer of the oscillator circuit mounted on a board to check the oscillator characteristics.

- Caution Since the CPU is started by the high-speed on-chip oscillator clock after a reset release, check the X1 clock oscillation stabilization time using the oscillation stabilization time counter status register (OSTC) by the user. Determine the oscillation stabilization time of the OSTC register and the oscillation stabilization time select register (OSTS) after sufficiently evaluating the oscillation stabilization time with the resonator to be used.
- Remark When using the X1 oscillator, refer to 5.4 System Clock Oscillator in the RL78/G12 User's Manual.

3.2.2 On-chip oscillator characteristics

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Oscillators	Parameters	Cond	litions	MIN.	TYP.	MAX.	Unit
High-speed on-chip oscillator clock frequency ^{Notes 1, 2}	fін			1		24	MHz
High-speed on-chip oscillator		R5F102 products	T _A = -20 to +85°C	-1.0		+1.0	%
clock frequency accuracy			T _A = -40 to -20°C	-1.5		+1.5	%
			T _A = +85 to +105°C	-2.0		+2.0	%
Low-speed on-chip oscillator clock frequency	fı∟				15		kHz
Low-speed on-chip oscillator clock frequency accuracy				-15		+15	%

Notes 1. High-speed on-chip oscillator frequency is selected by bits 0 to 3 of option byte (000C2H) and bits 0 to 2 of HOCODIV register.

2. This only indicates the oscillator characteristics. Refer to AC Characteristics for instruction execution time.



3.3 DC Characteristics

3.3.1 Pin characteristics

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

$(1A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{VDD} \le 5.5 \text{ V}, \text{VSS} = 0 \text{ V}) $ (1)								
Parameter	Symbol	Conditions		MIN.	TYP.	MAX.	Unit	
Output current, high ^{Note 1}	Іон1	20-, 24-pin products: Per pin for P00 to P03 ^{Note 4} , P10 to P14, P40 to P42				-3.0 Note 2	mA	
		30-pin products: Per pin for P00, P01, P10 to P17, P30, P31, P40, P50, P51, P120, P147						
		20-, 24-pin products:	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$			-9.0	mA	
		Total of P40 to P42	$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$			-6.0	mA	
		30-pin products: Total of P00, P01, P40, P120 (When duty ≤ 70% ^{Note 3})	$2.4 \text{ V} \le \text{V}_{\text{DD}} < 2.7 \text{ V}$			-4.5	mA	
		20-, 24-pin products:	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$			-27.0	mA	
		Total of P00 to P03 ^{Note 4} , P10 to P14	$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$			-18.0	mA	
		30-pin products: Total of P10 to P17, P30, P31, P50, P51, P147 (When duty ≤ 70% ^{Note 3})	$2.4 \text{ V} \le \text{V}_{\text{DD}} \le 2.7 \text{ V}$			-10.0	mA	
		Total of all pins (When duty $\leq 70\%^{\text{Note 3}}$)				-36.0	mA	
	Іон2	Per pin for P20 to P23				-0.1	mA	
		Total of all pins				-0.4	mA	

Notes 1. value of current at which the device operation is guaranteed even if the current flows from the V_{DD} pin to an output pin.

2. However, do not exceed the total current value.

3. The output current value under conditions where the duty factor ≤ 70%. If duty factor > 70%: The output current value can be calculated with the following expression (where n represents the duty factor as a percentage).

• Total output current of pins = (I_{OH} × 0.7)/(n × 0.01) <Example> Where n = 80% and I_{OH} = -10.0 mA

Total output current of pins = $(-10.0 \times 0.7)/(80 \times 0.01) \approx -8.7$ mA

However, the current that is allowed to flow into one pin does not vary depending on the duty factor. A current higher than the absolute maximum rating must not flow into one pin.

- 4. 24-pin products only.
- Caution P10 to P12 and P41 for 20-pin products, P01, P10 to P12, and P41 for 24-pin products, and P00, P10 to P15, P17, and P50 for 30-pin products do not output high level in N-ch open-drain mode.
- **Remark** Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.

(1/1)

$T_A = -40$ to $+105^{\circ}C_{,}$, 2.4 V ≤	V DD \leq 5.5 V, Vss = 0 V)				(2/4)	
Parameter	Symbol	Conditions		MIN.	TYP.	MAX.	Unit
Output current, low ^{Note 1}	IOL1	20-, 24-pin products: Per pin for P00 to P03 ^{Note 4} , P10 to P14, P40 to P42 30-pin products: Per pin for P00, P01, P10 to P17, P30, P31, P40, P50, P51, P120, P147				8.5 Note 2	mA
		Per pin for P60, P61				15.0 Note 2	mA
		20-, 24-pin products:	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$			25.5	mA
		Total of P40 to P42	$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$			9.0	mA
		30-pin products: Total of P00, P01, P40, P120 (When duty ≤ 70% ^{Note 3})	$2.4 \text{ V} \leq \text{V}_{\text{DD}} < 2.7 \text{ V}$			1.8	mA
		20-, 24-pin products:	$4.0~V \leq V_{\text{DD}} \leq 5.5~V$			40.0	mA
		Total of P00 to P03 ^{Note 4} ,	$2.7~V \leq V_{\text{DD}} < 4.0~V$			27.0	mA
		P10 to P14, P60, P61 30-pin products: Total of P10 to P17, P30, P31, P50, P51, P60, P61, P147 (When duty ≤ 70% ^{Note 3})	2.4 V ≤ V _{DD} < 2.7 V			5.4	mA
		Total of all pins (When duty $\leq 70\%^{\text{Note 3}}$)				65.5	mA
	IOL2	Per pin for P20 to P23				0.4	mA
		Total of all pins				1.6	mA

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

(2/4)

Notes 1. Value of current at which the device operation is guaranteed even if the current flows from an output pin to the Vss pin.

2. However, do not exceed the total current value.

3. The output current value under conditions where the duty factor ≤ 70%. If duty factor > 70%: The output current value can be calculated with the following expression (where n

represents the duty factor as a percentage).

• Total output current of pins = $(I_{OL} \times 0.7)/(n \times 0.01)$

<Example> Where n = 80% and IoL = 10.0 mA

Total output current of pins = $(10.0 \times 0.7)/(80 \times 0.01) \cong 8.7 \text{ mA}$

However, the current that is allowed to flow into one pin does not vary depending on the duty factor. A current higher than the absolute maximum rating must not flow into one pin.

- **4.** 24-pin products only.
- **Remark** Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.

Parameter	Symbol	Condition	s	MIN.	TYP.	MAX.	Unit
Input voltage, high	VIH1	Normal input buffer 20-, 24-pin products: P00 to P0	2Note 2 D10 to D14	0.8Vdd		Vdd	V
		P40 to P42	, FIU LU F14,				
		30-pin products: P00, P01, P1 P40, P50, P51, P120, P147	0 to P17, P30, P31,				
	VIH2	TTL input buffer	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.2		Vdd	V
		20-, 24-pin products: P10, P11	$3.3 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$	2.0		Vdd	V
		30-pin products: P01, P10, P11, P13 to P17	$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}$	1.5		Vdd	V
	Vінз	Normal input buffer		0.7Vdd		Vdd	V
		P20 to P23					
	VIH4	P60, P61		0.7Vdd		6.0	V
	VIH5	P121, P122, P125 ^{Note 1} , P137,	EXCLK, RESET	0.8VDD		Vdd	V
Input voltage, low	VIL1	Normal input buffer		0		0.2V _{DD}	V
		20-, 24-pin products: P00 to P0 P40 to P42)3 ^{Note 2} , P10 to P14,				
		30-pin products: P00, P01, P10 P40, P50, P51, P120, P147) to P17, P30, P31,				
	VIL2	TTL input buffer	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	0		0.8	V
		20-, 24-pin products: P10, P11	$3.3 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V}$	0		0.5	V
		30-pin products: P01, P10, P11, P13 to P17	$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}$	0		0.32	V
	VIL3	P20 to P23		0		0.3Vdd	V
	VIL4	P60, P61		0		0.3Vdd	V
	VIL5	P121, P122, P125 ^{Note 1} , P137,	EXCLK, RESET	0		0.2VDD	V
Output voltage, high	Vон1	20-, 24-pin products: P00 to P03 ^{Note 2} , P10 to P14,	4.0 V ≤ V _{DD} ≤ 5.5 V, Іон1 = −3.0 mA	Vdd-0.7			V
		P40 to P42 30-pin products:	2.7 V ≤ V _{DD} ≤ 5.5 V, Іон1 = −2.0 mA	VDD-0.6			V
		P00, P01, P10 to P17, P30, P31, P40, P50, P51, P120, P147	2.4 V ≤ V _{DD} ≤ 5.5 V, Іон1 = −1.5 mA	Vdd-0.5			V
	Vон2	P20 to P23	Iон2 = -100 µА	Vdd-0.5			V

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

(3/4)

Notes 1. 20, 24-pin products only.

2. 24-pin products only.

Caution The maximum value of V_{IH} of pins P10 to P12 and P41 for 20-pin products, P01, P10 to P12, and P41 for 24-pin products, and P00, P10 to P15, P17, and P50 for 30-pin products is V_{DD} even in N-ch opendrain mode.

High level is not output in the N-ch open-drain mode.

Remark Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

(4/4)

Parameter	Symbol		Conditio	ns	MIN.	TYP.	MAX.	Unit
Output voltage, low	Vol1	20-, 24-pin product P00 to P03 ^{Note} , P1		$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 8.5 mA			0.7	V
	30-pin products: P00, P01, Ic P10 to P17, P30, P31, P40, 2		2.7 V ≤ V _{DD} ≤ 5.5 V, Io∟1 = 3.0 mA			0.6	V	
			$2.7 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 1.5 mA			0.4	V	
				$2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 0.6 mA			0.4	V
	Vol2	P20 to P23		Ιοι2 = 400 μΑ			0.4	V
	Vol3	 		$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 15.0 mA			2.0	V
				$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 5.0 mA			0.4	V
				$2.7 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 3.0 mA			0.4	V
				$2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$ Iol1 = 2.0 mA			0.4	V
Input leakage current, high	Ішні	Other than P121, P122	-				1	μA
	Ілна	P121, P122 (X1, X2/EXCLK)	VI = VDD	Input port or external clock input			1	μA
				When resonator connected			10	μA
Input leakage current, low	Ilil1	Other than P121, P122	VI = Vss				-1	μA
	Ilil2	P121, P122 (X1, X2/EXCLK)	VI = Vss	Input port or external clock input			-1	μA
				When resonator connected			-10	μA
On-chip pull-up resistance	Ru	20-, 24-pin products: P00 to P03 ^{Note} , P10 to P14, P40 to P42, P125, RESET		VI = Vss, input port	10	20	100	kΩ
		30-pin products: P0 P10 to P17, P30, F P50, P51, P120, P	P31, P40,					

Note 24-pin products only.

Remark Unless specified otherwise, the characteristics of alternate-function pins are the same as those of the port pins.



3.3.2 Supply current characteristics

(1) 20-, 24-pin products

<u>(Ta = -40</u>	to +105°C,	$2.4 V \leq V_{DD}$	≤ 5.5 V, Vss = 0 V)

Parameter	Symbol			Conditions			MIN.	TYP.	MAX.	Unit
Supply	IDD1	Operating	HS (High-speed	f⊪ = 24 MHz ^{Note 3}	Basic	V _{DD} = 5.0 V		1.5		mA
current ^{Note 1}		mode	main) mode ^{Note 4}		operation	V _{DD} = 3.0 V		1.5		
					Normal	V _{DD} = 5.0 V		3.3	5.3	mA
					operation	V _{DD} = 3.0 V		3.3	5.3	
				f⊮ = 16 MHz ^{Note 3}		V _{DD} = 5.0 V		2.5	3.9	mA
						V _{DD} = 3.0 V		2.5	3.9	
				$f_{MX} = 20 \text{ MHz}^{\text{Note 2}},$		Square wave input		2.8	4.7	mA
				V _{DD} = 5.0 V		Resonator connection		3.0	4.8	
				$f_{MX} = 20 \text{ MHz}^{\text{Note 2}},$		Square wave input		2.8	4.7	mA
				V _{DD} = 3.0 V		Resonator connection		3.0	4.8	
				$f_{MX} = 10 \text{ MHz}^{\text{Note 2}},$		Square wave input		1.8	2.8	mA
				V _{DD} = 5.0 V		Resonator connection		1.8	2.8	
				$f_{MX} = 10 \text{ MHz}^{\text{Note 2}},$		Square wave input		1.8	2.8	mA
				V _{DD} = 3.0 V		Resonator connection		1.8	2.8	

Notes 1. Total current flowing into V_{DD}, including the input leakage current flowing when the level of the input pin is fixed to V_{DD} or V_{SS}. The values below the MAX. column include the peripheral operation current. However, not including the current flowing into the A/D converter, LVD circuit, I/O port, and on-chip pull-up/pull-down resistors and the current flowing during data flash rewrite.

- 2. When high-speed on-chip oscillator clock is stopped.
- 3. When high-speed system clock is stopped
- **4.** Relationship between operation voltage width, operation frequency of CPU and operation mode is as follows.

HS (High speed main) mode: $V_{DD} = 2.7$ V to 5.5 V @1 MHz to 24 MHz $V_{DD} = 2.4$ V to 5.5 V @1 MHz to 16 MHz

- **Remarks 1.** f_{MX}: High-speed system clock frequency (X1 clock oscillation frequency or external main system clock frequency)
 - 2. fin: high-speed on-chip oscillator clock frequency
 - **3.** Temperature condition of the TYP. value is $T_A = 25^{\circ}C$.



(1/2)

(1)	20-,	24-pin	products
-----	------	--------	----------

Parameter	Symbol			Conditions		MIN.	TYP.	MAX.	Unit
Supply	DD2 Note 2	HALT	HS (High-speed	f⊪ = 24 MHz ^{Note 4}	V _{DD} = 5.0 V		440	2230	μA
current ^{Note 1}		mode	main) mode ^{Note 6}		V _{DD} = 3.0 V		440	2230	
				f⊪ = 16 MHz ^{Note 4}	V _{DD} = 5.0 V		400	1650	μA
					V _{DD} = 3.0 V		400	1650	
				f _{MX} = 20 MHz ^{Note 3} ,	Square wave input		280	1900	μA
				V _{DD} = 5.0 V	Resonator connection		450	2000	
				f _{MX} = 20 MHz ^{Note 3} ,	Square wave input		280	1900	μA
				V _{DD} = 3.0 V	Resonator connection		450	2000	
				f _{MX} = 10 MHz ^{Note 3} ,	Square wave input		190	1010	μA
				V _{DD} = 5.0 V	Resonator connection		260	1090	
				f _{MX} = 10 MHz ^{Note 3} ,	Square wave input		190	1010	μA
				V _{DD} = 3.0 V	Resonator connection		260	1090	
	IDD3 Note 5	STOP	T _A = -40°C				0.19	0.50	μA
		mode	T _A = +25°C				0.24	0.50	
			T _A = +50°C				0.32	0.80	
	T _A = +70°C				0.48	1.20			
	T _A = +85°C					0.74	2.20		
			T _A = +105°C				1.50	10.20	

 Notes 1.
 Total current flowing into VDD, including the input leakage current flowing when the level of the input pin is fixed to VDD or Vss. The values below the MAX. column include the peripheral operation current. However, not including the current flowing into the A/D converter, LVD circuit, I/O port, and on-chip pull-up/pull-down

- resistors and the current flowing during data flash rewrite.
- **2.** During HALT instruction execution by flash memory.
- 3. When high-speed on-chip oscillator clock is stopped.
- 4. When high-speed system clock is stopped.
- **5.** Not including the current flowing into the 12-bit interval timer and watchdog timer.
- **6.** Relationship between operation voltage width, operation frequency of CPU and operation mode is as follows.

HS (High speed main) mode: V_{DD} = 2.7 V to 5.5 V @1 MHz to 24 MHz V_{DD} = 2.4 V to 5.5 V @1 MHz to 16 MHz

- Remarks 1. fmx: High-speed system clock frequency (X1 clock oscillation frequency or external main system clock frequency)
 - 2. fin: high-speed on-chip oscillator clock frequency
 - 3. Except temperature condition of the TYP. value is T_A = 25°C, other than STOP mode



(2) 30-pin products

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD})$	≤ 5.5 V, Vss = 0 V)
---	---------------------

(T _A = −40 to +105°C, 2.4 V ≤ V _{DD} ≤ 5.5 V, V _{SS} = 0 V)								(1/2)		
Parameter	Symbol	Conditions				MIN.	TYP.	MAX.	Unit	
Supply	IDD1	Operating	HS (High-speed	f⊮ = 24 MHz ^{Note 3}	Basic	V _{DD} = 5.0 V		1.5		mA
current ^{Note 1}		mode	main) mode ^{Note 4}		operation	V _{DD} = 3.0 V		1.5		
					Normal	V _{DD} = 5.0 V		3.7	5.8	mA
					operation	V _{DD} = 3.0 V		3.7	5.8	
				f⊪ = 16 MHz ^{Note 3}		V _{DD} = 5.0 V		2.7	4.2	mA
						V _{DD} = 3.0 V		2.7	4.2	
				$f_{MX} = 20 \text{ MHz}^{\text{Note 2}},$		Square wave input		3.0	4.9	mA
				V _{DD} = 5.0 V	-	Resonator connection		3.2	5.0	
				$f_{MX} = 20 \text{ MHz}^{\text{Note 2}},$ $V_{DD} = 3.0 \text{ V}$		Square wave input		3.0	4.9	mA
						Resonator connection		3.2	5.0	
				$f_{MX} = 10 \text{ MHz}^{\text{Note 2}},$ $V_{DD} = 5.0 \text{ V}$		Square wave input		1.9	2.9	mA
						Resonator connection		1.9	2.9	
				$f_{MX} = 10 \text{ MHz}^{\text{Note 2}},$ $V_{\text{DD}} = 3.0 \text{ V}$		Square wave input		1.9	2.9	mA
						Resonator connection		1.9	2.9	

Notes 1. Total current flowing into VDD, including the input leakage current flowing when the level of the input pin is fixed to VDD or Vss. The values below the MAX. column include the peripheral operation current. However, not including the current flowing into the A/D converter, LVD circuit, I/O port, and on-chip pull-up/pull-down resistors and the current flowing during data flash rewrite.

- 2. When high-speed on-chip oscillator clock is stopped.
- 3. When high-speed system clock is stopped
- 4. Relationship between operation voltage width, operation frequency of CPU and operation mode is as follows.

HS (High speed main) mode: VDD = 2.7 V to 5.5 V @1 MHz to 24 MHz VDD = 2.4 V to 5.5 V @1 MHz to 16 MHz

- Remarks 1. fmx: High-speed system clock frequency (X1 clock oscillation frequency or external main system clock frequency)
 - 2. fin: high-speed on-chip oscillator clock frequency
 - **3.** Temperature condition of the TYP. value is $T_A = 25^{\circ}C$.



(2) 30-pin products

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$
--

$T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{ Vss} = 0 \text{ V})$								1	(2/2)
Parameter	Symbol	Conditions				MIN.	TYP.	MAX.	Unit
Supply current ^{Note 1}	IDD2 Note 2	HALT mode	HS (High-speed main) mode ^{Note 6}	$f_{IH} = 24 \text{ MHz}^{Note 4}$	V _{DD} = 5.0 V		440	2300	μA
					V _{DD} = 3.0 V		440	2300	
				f⊪ = 16 MHz ^{Note 4}	V _{DD} = 5.0 V		400	1700	μΑ
					V _{DD} = 3.0 V		400	1700	
				$f_{MX} = 20 \text{ MHz}^{\text{Note 3}},$ $V_{\text{DD}} = 5.0 \text{ V}$	Square wave input		280	1900	μA
					Resonator connection		450	2000	
				f _{MX} = 20 MHz ^{Note 3} , V _{DD} = 3.0 V	Square wave input		280	1900	μA
					Resonator connection		450	2000	
				f _{MX} = 10 MHz ^{Note 3} , V _{DD} = 5.0 V	Square wave input		190	1020	μA
					Resonator connection		260	1100	
				f _{MX} = 10 MHz ^{Note 3} , V _{DD} = 3.0 V	Square wave input		190	1020	μA
					Resonator connection		260	1100	
	I _{DD3} Note 5	STOP mode	$T_A = -40^{\circ}C$				0.18	0.50	μA
			T _A = +25°C				0.23	.3 0.50	
			$T_A = +50^{\circ}C$ $T_A = +70^{\circ}C$ $T_A = +85^{\circ}C$				0.30	1.10	
							0.46	1.90	
							0.75	3.30	
			T _A = +105°C	T _A = +105°C			2.94	15.30	

Notes 1. Total current flowing into VDD, including the input leakage current flowing when the level of the input pin is fixed to VDD or Vss. The values below the MAX. column include the peripheral operation current. However, not including the current flowing into the A/D converter, LVD circuit, I/O port, and on-chip pull-up/pull-down resistors and the current flowing during data flash rewrite.

- 2. During HALT instruction execution by flash memory.
- 3. When high-speed on-chip oscillator clock is stopped.
- 4. When high-speed system clock is stopped.
- 5. Not including the current flowing into the 12-bit interval timer and watchdog timer.
- 6. Relationship between operation voltage width, operation frequency of CPU and operation mode is as follows.

HS (High speed main) mode: VDD = 2.7 V to 5.5 V @1 MHz to 24 MHz VDD = 2.4 V to 5.5 V @1 MHz to 16 MHz

- Remarks 1. fmx: High-speed system clock frequency (X1 clock oscillation frequency or external main system clock frequency)
 - 2. fin: high-speed on-chip oscillator clock frequency
 - 3. Except STOP mode, temperature condition of the TYP. value is $T_A = 25^{\circ}C$.



(3) Peripheral functions (Common to all products)

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Parameter	Symbol		Conditions	MIN.	TYP.	MAX.	Unit
Low-speed onchip oscillator operating current	_{FIL} Note 1				0.20		μA
12-bit interval timer operating current	ITMKA Notes 1, 2, 3				0.02		μA
Watchdog timer operating current	IWDT Notes 1, 2, 4	fı∟ = 15 kHz			0.22		μA
A/D converter	IADC	When conversion	Normal mode, AV _{REFP} = V _{DD} = 5.0 V		1.30	1.70	mA
operating current		at maximum speed	Low voltage mode, AV _{REFP} = V _{DD} = 3.0 V		0.50	0.70	mA
A/D converter reference voltage operating current	ladref Note 1				75.0		μA
Temperature sensor operating current	ITMPS Note 1				75.0		μA
LVD operating current	ILVD Notes 1, 6				0.08		μA
Self-programming operating current	IFSP Notes 1, 8				2.00	12.20	mA
BGO operating current	IBGO Notes 1, 7				2.00	12.20	mA
SNOOZE operating	Isnoz	ADC operation	The mode is performed Note 9		0.50	1.10	mA
current Note	Note 1		The A/D conversion operations are performed, Low voltage mode, AV_{REFP} = V_{DD} = 3.0 V		1.20	2.04	mA
		Simplified SPI (CSI)	/UART operation		0.70	1.54	mA

Notes 1. Current flowing to the VDD.

- 2. When high speed on-chip oscillator and high-speed system clock are stopped.
- 3. Current flowing only to the 12-bit interval timer (excluding the operating current of the low-speed on-chip oscillator). The current value of the RL78 microcontrollers is the sum of IDD1, IDD2 or IDD3, and IFIL and ITMKA when the 12-bit interval timer operates.
- 4. Current flowing only to the watchdog timer (including the operating current of the low-speed on-chip oscillator). The current value of the RL78 microcontrollers is the sum of IDD1, IDD2 or IDD3 and IWDT when the watchdog timer operates.
- **5.** Current flowing only to the A/D converter. The current value of the RL78 microcontrollers is the sum of IDD1 or IDD2 and IADC when the A/D converter operates in an operation mode or the HALT mode.
- 6. Current flowing only to the LVD circuit. The current value of the RL78 microcontrollers is the sum of IDD1, IDD2 or IDD3 and ILVD when the LVD circuit operates.
- 7. Current flowing only during data flash rewrite.
- **8.** Current flowing only during self programming.
- 9. For shift time to the SNOOZE mode, see 17.3.3 SNOOZE mode in the RL78/G12 User's Manual.

Remarks 1. fil: Low-speed on-chip oscillator clock frequency

2. Temperature condition of the TYP. value is $T_A = 25^{\circ}C$



3.4 AC Characteristics

 $(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$


Items	Symbol		Condition	s	MIN.	TYP.	MAX.	Unit
Instruction cycle (minimum	Тсч	Main system	HS (High-	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	0.04167		1	μs
instruction execution time)		clock (fMAIN) operation	speed main) mode	$2.4 \text{ V} \leq \text{V}_{\text{DD}} < 2.7 \text{ V}$	0.0625		1	μs
		During self programming	HS (High-	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	0.04167		1	μs
			speed main) mode	$2.4 \text{ V} \leq \text{V}_{\text{DD}} < 2.7 \text{ V}$	0.0625		1	μs
External main system clock	fex	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.$.5 V		1.0		20.0	MHz
frequency		$2.4 \text{ V} \leq \text{V}_{\text{DD}} < 2$.7 V		1.0		16.0	MHz
External main system clock	texh, texl	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$			24			ns
input high-level width, low- level width		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 2.4$.7 V		30			ns
TI00 to TI07 input high-level width, low-level width	tr⊪, tr⊾				1/fмск + 10			ns
TO00 to TO07 output	fто	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5$.5 V				12	MHz
frequency		$2.7 V \le V_{DD} < 4$.0 V				8	MHz
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} < 2$.7 V				4	MHz
PCLBUZ0, or PCLBUZ1	f PCL	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5$.5 V				16	MHz
output frequency		$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4$.0 V				8	MHz
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} < 2$.7 V				4	MHz MHz ns ns ns MHz MHz MHz MHz
INTP0 to INTP5 input high- level width, low-level width	tinth, tintl				1			μs
KR0 to KR9 input available width	tkr				250			ns
RESET low-level width	t RSL				10			μs

Remark fmck: Timer array unit operation clock frequency


(Operation clock to be set by the timer clock select register 0 (TPS0) and the CKS0n bit of timer mode register 0n (TMR0n). n: Channel number (n = 0 to 7))




Minimum Instruction Execution Time during Main System Clock Operation



AC Timing Test Point




External Main System Clock Timing







TI/TO Timing




Interrupt Request Input Timing



Key Interrupt Input Timing




RESET Input Timing





3.5 Peripheral Functions Characteristics

AC Timing Test Point



3.5.1 Serial array unit

(1) During communication at same potential (UART mode) ($T_A = -40$ to +105°C, 2.4 V $\leq V_{DD} \leq 5.5$ V, Vss = 0 V)

<u>(1A 40 to :</u>		- • • •				
Parameter	Symbol		Conditions HS (high-speed main) Mode		ed main) Mode	Unit
				MIN.	MAX.	
Transfer rate					fмск/12	bps
Note 1			Theoretical value of the maximum transfer rate $f_{CLK} = f_{MCK}^{Note 2}$		2.0	Mbps


Notes 1. Transfer rate in the SNOOZE mode is 4800 bps only.

2. The maximum operating frequencies of the CPU/peripheral hardware clock (fclk) are:


HS (high-speed main) mode: 24 MHz (2.7 V ≤ V_{DD} ≤ 5.5 V) 16 MHz (2.4 V ≤ V_{DD} ≤ 5.5 V)

Caution Select the normal input buffer for the RxDq pin and the normal output mode for the TxDq pin by using port input mode register g (PIMg) and port output mode register g (POMg).

UART mode connection diagram (during communication at same potential)



UART mode bit width (during communication at same potential) (reference)



Remarks 1. q: UART number (q = 0 to 2), g: PIM, POM number (g = 0, 1)

2. fMCK: Serial array unit operation clock frequency

(Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn).

m: Unit number, n: Channel number (mn = 00 to 03, 10, 11))

(2) During communication at same potential (simplified SPI (CSI) mode) (master mode, SCKp... internal clock output)

Parameter	Symbol	C	Conditions HS (high-speed mai		d main) Mode	Unit	
				MIN.	MAX.		
SCKp cycle time	tkCY1	tĸcy1 ≥ 4/fcLĸ	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	334		ns	
			$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	500		ns	
SCKp high-/low-level width	t кн1,	$4.0 V \le V_{DD} \le 5.5 V$ $2.7 V \le V_{DD} \le 5.5 V$		tксү1/2–24		ns	
	tĸL1			tксү1/2–36		ns	
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		tксү1/2–76		ns	
SIp setup time (to SCKp↑) ^{Note 1}	tsiĸ1	$4.0 \vee \leq V_{DD} \leq 5.5 \vee$		66		ns	
		$2.7 V \leq V_{DD} \leq 5.$	5 V	66		ns ns ns ns	
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.4 \text{ V}_{\text{DD}}$	5 V	113			
SIp hold time (from SCKp↑) ^{Note 2}	tĸsı1			38		ns	
Delay time from SCKp↓ to SOp output ^{Note 3}	tkso1	C = 30 pF Note 4			50	ns	

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

- Notes 1. When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp setup time becomes "to SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - **2.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp hold time becomes "from SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - **3.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The delay time to SOp output becomes "from SCKp↑" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - 4. C is the load capacitance of the SCKp and SOp output lines.
- Caution Select the normal input buffer for the SIp pin and the normal output mode for the SOp and SCKp pins by using port input mode register 1 (PIM1) and port output mode registers 0, 1, 4 (POM0, POM1, POM4).

Remarks 1. p: CSI number (p = 00, 01, 11, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0, 1, 3)

 fmck: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn). m: Unit number (m = 0, 1), n: Channel number (n = 0, 1, 3))




(3) During communication at same potential (simplified SPI (CSI) mode) (slave mode, SCKp... external clock input)

Parameter	Symbol	Con	ditions	HS (high-speed	main) Mode	Unit
				MIN.	MAX.	
SCKp cycle time Note 5	tксү2	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	20 MHz < fмск	16/fмск		ns
			fмск ≤ 20 MHz	12/fмск		ns
		$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	16 MHz < fмск	16/ f мск		ns
			fмск ≤ 16 MHz	12/fмск		ns
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		12/fмск		ns
				and 1000		
SCKp high-/low-level width	t кн2,	$4.0 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		tксү2/2–14		ns
	tĸl2	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		tксү2/2–16		ns
		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		tксү2/2–36		ns
SIp setup time (to SCKp↑)	tsık2	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		1/fмск + 40		ns
Note 1		$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		1/fмск + 60		ns
SIp hold time (from SCKp↑) ^{Note 2}	tksi2			1/fмск + 62		ns
Delay time from SCKp↓ to	tĸso2	C = 30 pF Note 4	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		2/fмск + 66	ns
SOp output Note 3			$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$		2/fмск + 113	ns


$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, \text{V}_{\text{SS}} = 0 \text{ V})$

- Notes 1. When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp setup time becomes "to SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp hold time becomes "from SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - **3.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The delay time to SOp output becomes "from SCKp↑" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
 - 4. C is the load capacitance of the SOp output lines.
 - 5. Transfer rate in the SNOOZE mode: MAX. 1 Mbps.
- Caution Select the normal input buffer for the SIp and SCKp pins and the normal output mode for the SOp pin by using port input mode register 1 (PIM1) and port output mode registers 0, 1, 4 (POM0, POM1, POM4).


Simplified SPI (CSI) mode connection diagram (during communication at same potential)








Simplified SPI (CSI) mode serial transfer timing (during communication at same potential) (When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1.)





- Remarks 1. p: CSI number (p = 00, 01, 11, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0, 1, 3)
 2. fMCK: Serial array unit operation clock frequency
 - (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn). m: Unit number (m = 0,1), n: Channel number (n = 0, 1, 3))

1A 40 to 100 0; 2.4 V	<u> </u>	33 V V			
Parameter	Symbol	Conditions	HS (high-speed main) Mode		Unit
			MIN.	MAX.	
SCLr clock frequency	fsc∟	C_b = 100 pF, R_b = 3 k Ω		100 ^{Note 1}	kHz
Hold time when SCLr = "L"	tLOW	C_b = 100 pF, R_b = 3 k Ω	4600		ns
Hold time when SCLr = "H"	tніgн	C_b = 100 pF, R_b = 3 k Ω	4600		ns
Data setup time (reception)	tsu:dat	C_b = 100 pF, R_b = 3 k Ω	1/f _{MCK} + 580 ^{Note 2}		ns
Data hold time (transmission)	thd:dat	C_b = 100 pF, R_b = 3 k Ω	0	1420	ns


(4) During communication at same potential (simplified I²C mode)

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$


Notes 1. The value must be equal to or less than fmck/4.

- Set tsu:DAT so that it will not exceed the hold time when SCLr = "L" or SCLr = "H". 2.
- Caution Select the N-ch open drain output (Vbb tolerance) mode for SDAr by using port output mode register h (POMh).

Simplified I²C mode connection diagram (during communication at same potential)



Simplified I²C mode serial transfer timing (during communication at same potential)



Remarks 1. R_b [Ω]:Communication line (SDAr) pull-up resistance

Cb [F]: Communication line (SCLr, SDAr) load capacitance


2. r: IIC number (r = 00, 01, 11, 20), h: = POM number (h = 0, 1, 4, 5)

3. fMCK: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn).

m: Unit number (m = 0, 1), n: Channel number (0, 1, 3))

Parameter	Symbol		Conditions		speed main) ode	Unit
				MIN.	MAX.	
Transfer		Reception	$4.0 V \le V_{DD} \le 5.5 V$,		fмск/12	bps
rate Note4	rate		$2.7 V \le V_b \le 4.0 V$		Note 1	
			Theoretical value of the maximum transfer rate $f_{MCK} = f_{CLK}$ Note 2		2.0	Mbps
			$2.7 V \le V_{DD} < 4.0 V,$		fмск/12 Note 1	bps
			$2.3 \text{ V} \leq \text{V}_{b} \leq 2.7 \text{ V}$		Note I	
			Theoretical value of the maximum transfer rate		2.0	Mbps
			f _{MCK} = f _{CLK} Note 2			
			$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V},$		fмск/12	bps
			$1.6 V \le V_b \le 2.0 V$		Note 1	
			Theoretical value of the maximum transfer rate		2.0	Mbps
			f _{MCK} = f _{CLK} Note 2			
		Transmission	$4.0 \ \forall \leq \forall_{DD} \leq 5.5 \ \forall,$		Note 3	bps
			$2.7 \text{ V} \leq \text{V}_{\text{b}} \leq 4.0 \text{ V}$			
			Theoretical value of the maximum		2.0	Mbps
			transfer rate		Note 4	
			C _b = 50 pF, R _b = 1.4 kΩ, V _b = 2.7 V			
			$2.7 \text{ V} \leq \text{V}_{\text{DD}} < 4.0 \text{ V},$		Note 5	bps
			$2.3 V \le V_b \le 2.7 V$,			
			Theoretical value of the maximum		1.2	Mbps
			transfer rate		Note 6	
			$C_b = 50 \text{ pF}, R_b = 2.7 \text{ k}\Omega, V_b = 2.3 \text{ V}$			
			$2.4 V \le V_{DD} < 3.3 V,$		Notes	bps
			$1.6 V \le V_b \le 2.0 V$		2, 7	
			Theoretical value of the maximum transfer rate		0.43 Note 8	Mbps
			$C_{\rm b}$ = 50 pF, $R_{\rm b}$ = 5.5 kΩ, $V_{\rm b}$ = 1.6 V			

(5) Communication at different potential (1.8 V, 2.5 V, 3 V) (UART mode)



Notes 1. Transfer rate in the SNOOZE mode is 4800 bps only.

2. The maximum operating frequencies of the CPU/peripheral hardware clock (fcLK) are: HS (high-speed main) mode: 24 MHz (2.7 V \leq VDD \leq 5.5 V)

$$16 \text{ MHz} (2.4 \text{ V} \le \text{Vpp} \le 5.5 \text{ V})$$

3. The smaller maximum transfer rate derived by using fmck/12 or the following expression is the valid maximum transfer rate.

Expression for calculating the transfer rate when $4.0 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}$ and $2.7 \text{ V} \le \text{V}_{b} \le 4.0 \text{ V}$

Maximum transfer rate =

 $\frac{1}{\{-C_b \times R_b \times \ln (1 - \frac{2.2}{V_b})\} \times 3}$ [bps]

Baud rate error (theoretical value) =

$$\frac{\frac{1}{\text{Transfer rate} \times 2} - \{-C_b \times R_b \times \ln (1 - \frac{2.2}{V_b})\}}{(\frac{1}{(\text{Transfer rate})} \times \text{Number of transferred bits}} \times 100 [\%]$$

* This value is the theoretical value of the relative difference between the transmission and reception sides.

- 4. This value as an example is calculated when the conditions described in the "Conditions" column are met. Refer to Note 3 above to calculate the maximum transfer rate under conditions of the customer.
- 5. The smaller maximum transfer rate derived by using fMCK/12 or the following expression is the valid maximum transfer rate.

Expression for calculating the transfer rate when 2.7 V \leq V_DD < 4.0 V and 2.3 V \leq V_b \leq 2.7 V

Maximum transfer rate =
$$\frac{1}{\{-C_b \times R_b \times \ln (1 - \frac{2.0}{V_b})\} \times 3}$$
 [bps]

Baud rate error (theoretical value) =

 $\frac{1}{\text{Transfer rate } \times 2} - \{-C_b \times R_b \times \ln (1 - \frac{2.0}{V_b})\}$ $(\frac{1}{(\text{Transfer rate})} \times \text{Number of transferred bits}$

- * This value is the theoretical value of the relative difference between the transmission and reception sides.
- This value as an example is calculated when the conditions described in the "Conditions" column are met. Refer to Note 5 above to calculate the maximum transfer rate under conditions of the customer.
- 7. The smaller maximum transfer rate derived by using fMCK/12 or the following expression is the valid maximum transfer rate.

Expression for calculating the transfer rate when 2.4 V \leq V_{DD} < 3.3 V, 1.6 V \leq V_b \leq 2.0 V

Maximum transfer rate =

$$\frac{1}{b \times R_b \times \ln (1 - \frac{1.5}{V_b})} \times 3$$
 [bps]

Baud rate error (theoretical value) =


{--C

 $\frac{\frac{1}{\text{Transfer rate} \times 2} - \{-C_b \times R_b \times \ln (1 - \frac{1.5}{V_b})\}}{(\frac{1}{(\text{Transfer rate})} \times \text{Number of transferred bits}} \times 100 [\%]$


- * This value is the theoretical value of the relative difference between the transmission and reception sides.
- This value as an example is calculated when the conditions described in the "Conditions" column are met. Refer to Note 7 above to calculate the maximum transfer rate under conditions of the customer.
- Caution Select the TTL input buffer for the RxDq pin and the N-ch open drain output (V_{DD} tolerance) mode for the TxDq pin by using port input mode register g (PIMg) and port output mode register g (POMg). For V_{IH} and V_{IL}, see the DC characteristics with TTL input buffer selected.




UART mode connection diagram (during communication at different potential)



UART mode bit width (during communication at different potential) (reference)





- **Remarks 1.** R_b[Ω]: Communication line (TxDq) pull-up resistance, C_b[F]: Communication line (TxDq) load capacitance, V_b[V]: Communication line voltage
 - **2.** q: UART number (q = 0 to 2), g: PIM and POM number (g = 0, 1)
 - fMCK: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn).

m: Unit number, n: Channel number (mn = 00 to 03, 10, 11))

4. UART0 of the 20- and 24-pin products supports communication at different potential only when the peripheral I/O redirection function is not used.



(6) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified SPI (CSI) mode) (master mode, SCKp... internal clock output) (1/3)

Parameter	Symbol		Conditions	HS (high-speed	d main) Mode	Unit
				MIN.	MAX.	
SCKp cycle time	tkcy1	tксү1 ≥ 4/fcLк	$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$	600		ns
			$2.7 \text{ V} \le \text{V}_{b} \le 4.0 \text{ V},$			
			C_b = 30 pF, R_b = 1.4 k Ω			
			$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V},$	1000		ns
			$2.3 V \le V_b \le 2.7 V$,			
			C_b = 30 pF, R_b = 2.7 k Ω			
			$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V},$	2300		ns
			$1.6 V \le V_b \le 2.0 V$,			
			C_b = 30 pF, R_b = 5.5 k Ω			
SCKp high-level width	tкнı	$4.0 V \leq V_{DD} \leq 3$	5.5 V, 2.7 V \leq V _b \leq 4.0 V,	tkcy1/2 –150		ns
		C _b = 30 pF, Rt	₀ = 1.4 kΩ			
		$2.7 V \leq V_{DD} < d$	4.0 V, 2.3 V ≤ Vb ≤ 2.7 V,	tkcy1/2 –340		ns
		C _b = 30 pF, Rt	₀ = 2.7 kΩ			
		2.4 V ≤ V _{DD} < 3	3.3 V, 1.6 V ≤ V _b ≤ 2.0 V,	tkcy1/2 –916		ns
		C _b = 30 pF, Rt	₀ = 5.5 kΩ			
SCKp low-level width	tĸ∟1	$4.0 V \leq V_{DD} \leq 3$	5.5 V, 2.7 V ≤ V₅ ≤ 4.0 V,	tксү1/2—24		ns
		C₀ = 30 pF, Rt	₀ = 1.4 kΩ			
		2.7 V ≤ V _{DD} < 4	4.0 V, 2.3 V ≤ V _b ≤ 2.7 V,	tксү1/2 —36		ns
		C₀ = 30 pF, Rt	₀ = 2.7 kΩ			
		-	3.3 V, 1.6 V ≤ V _b ≤ 2.0 V,	tkcy1/2 –100		ns
		C₀ = 30 pF, Rt				

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

- Cautions 1. Select the TTL input buffer for the SIp pin and the N-ch open drain output (V_{DD} tolerance) mode for the SOp pin and SCKp pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For V_H and V_{IL}, see the DC characteristics with TTL input buffer selected.
 - 2. CSI01 and CSI11 cannot communicate at different potential.
- **Remarks 1.** R_b [Ω]: Communication line (SCKp, SOp) pull-up resistance, C_b [F]: Communication line (SCKp, SOp) load capacitance, V_b [V]: Communication line voltage
 - **2.** p: CSI number (p = 00, 20)



(6) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified SPI (CSI) mode) (master mode, SCKp... internal clock output) (2/3)

Parameter	Symbol	Conditions	HS (high-spee	ed main) Mode	Unit
			MIN.	MAX.	
SIp setup time (to SCKp↑) _{Note}	tsik1	$\begin{array}{l} 4.0 \; V \leq V_{DD} \leq 5.5 \; V, \; 2.7 \; V \leq V_b \leq 4.0 \; V, \\ C_b = 30 \; pF, \; R_b = 1.4 \; k\Omega \end{array}$	162		ns
		$\label{eq:VD} \begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 30 \ pF, \ R_b = 2.7 \ k\Omega \end{array}$	354		ns
		$\begin{array}{l} 2.4 \ V \leq V_{DD} < 3.3 \ V, \ 1.6 \ V \leq V_b \leq 2.0 \ V, \\ C_b = 30 \ pF, \ R_b = 5.5 \ k\Omega \end{array}$	958		ns
SIp hold time (from SCKp↑) ^{Note}	tksi1		38		ns
		$\begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 30 \ pF, \ R_b = 2.7 \ k\Omega \end{array}$	38		ns
		$\begin{array}{l} 2.4 \ V \leq V_{DD} < 3.3 \ V, \ 1.6 \ V \leq V_b \leq 2.0 \ V, \\ C_b = 30 \ pF, \ R_b = 5.5 \ k\Omega \end{array}$	38		ns
Delay time from SCKp↓ to SOp output ^{Note}	tkso1			200	ns
		$\label{eq:VDD} \begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 30 \ pF, \ R_b = 2.7 \ k\Omega \end{array}$		390	ns
		$\begin{array}{l} 2.4 \ V \leq V_{DD} < 3.3 \ V, \ 1.6 \ V \leq V_b \leq 2.0 \ V, \\ C_b = 30 \ pF, \ R_b = 5.5 \ k\Omega \end{array}$		966	ns

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, \text{V}_{\text{SS}} = 0 \text{ V})$

Note When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1.

(Cautions and Remarks are listed on the next page.)



(6) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified SPI (CSI) mode) (master mode, SCKp... internal clock output) (3/3)


Parameter	Symbol	Conditions	HS (high-speed main) Mode	Unit
			MIN. MAX.	
SIp setup time (to SCKp↓) _{Note}	tsiki		88	ns
		$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_b \leq 2.7 \; V, \\ C_b = 30 \; pF, \; R_b = 2.7 \; k\Omega \end{array}$	88	ns
		$\begin{array}{l} 2.4 \ V \leq V_{DD} < 3.3 \ V, \ 1.6 \ V \leq V_b \leq 2.0 \ V, \\ C_b = 30 \ pF, \ R_b = 5.5 \ k\Omega \end{array}$	220	ns
SIp hold time (from SCKp↓) ^{Note}	tksi1		38	ns
		$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_b \leq 2.7 \; V, \\ C_b = 30 \; pF, \; R_b = 2.7 \; k\Omega \end{array}$	38	ns
		$\begin{array}{l} 2.4 \; V \leq V_{DD} < 3.3 \; V, \; 1.6 \; V \leq V_b \leq 2.0 \; V, \\ C_b = 30 \; pF, \; R_b = 5.5 \; k\Omega \end{array}$	38	ns
Delay time from SCKp↑ to SOp output ^{Note}	tkso1		50	ns
		$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_b \leq 2.7 \; V, \\ C_b = 30 \; pF, \; R_b = 2.7 \; k\Omega \end{array}$	50	ns
		$\begin{array}{l} 2.4 \; V \leq V_{DD} < 3.3 \; V, \; 1.6 \; V \leq V_b \leq 2.0 \; V, \\ C_b = 30 \; pF, \; R_b = 5.5 \; k\Omega \end{array}$	50	ns

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$


Note When DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.

- Cautions 1. Select the TTL input buffer for the SIp pin and the N-ch open drain output (VDD tolerance) mode for the SOp pin and SCKp pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For VIH and VIL, see the DC characteristics with TTL input buffer selected.
 - 2. CSI01 and CSI11 cannot communicate at different potential.
- **Remarks 1.** R_b [Ω]: Communication line (SCKp, SOp) pull-up resistance, C_b [F]: Communication line (SCKp, SOp) load capacitance, V_b [V]: Communication line voltage
 - **2.** p: CSI number (p = 00, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0)

Simplified SPI (CSI) mode connection diagram (during communication at different potential)









Simplified SPI (CSI) mode serial transfer timing (master mode) (during communication at different potential) (When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1)

Simplified SPI (CSI) mode serial transfer timing (master mode) (during communication at different potential) (When DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.)





(7) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified SPI (CSI) mode) (slave mode, SCKp... external clock input)


Parameter	Symbol		Conditions	HS (high-spe Mod		Unit
				MIN.	MAX.	
SCKp cycle time Note 1	t ксү2	$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V},$	20 MHz < fмск ≤ 24 MHz	24/f мск		ns
		$2.7~V \leq V_b \leq 4.0~V$	8 MHz < fмск ≤ 20 MHz	20/f мск		ns
			4 MHz < fмск ≤ 8 MHz	16/f мск		ns
			fмск ≤ 4 MHz	12/f мск		ns
		$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V},$	20 MHz < fмск ≤ 24 MHz	32/fмск		ns
		$2.3 \text{ V} \leq \text{V}_{b} \leq 2.7 \text{ V}$	16 MHz < fмск ≤ 20 MHz	28/f мск		ns
			8 MHz < fмск ≤ 16 MHz	24/f мск		ns
			4 MHz < fмск ≤ 8 MHz	16/f мск		ns
			fмск ≤ 4 MHz	12/f мск		ns
		$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V},$	20 MHz < fмск ≤ 24 MHz	72/f мск		ns
		$1.6 \text{ V} \le \text{V}_{b} \le 2.0 \text{ V}$	16 MHz < fмск ≤ 20 MHz	64/f мск		ns
			8 MHz < fмск ≤ 16 MHz	52/f мск		ns
			4 MHz < fмск ≤ 8 MHz	32/f мск		ns
			fмск ≤ 4 MHz	20/f мск		ns
SCKp high-/low-level	tкн2,	$4.0 V \le V_{DD} \le 5.5 V, 2.$	$7 \text{ V} \leq \text{V}_{b} \leq 4.0 \text{ V}$	tkcy2/2 – 24		ns
width	tĸL2	$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V}, 2.$	$3 \text{ V} \leq \text{V}_{b} \leq 2.7 \text{ V}$	tkcy2/2 - 36		ns
		$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, 1.$	$6 \text{ V} \leq \text{V}_{\text{b}} \leq 2.0 \text{ V}$	tkcy2/2 – 100		ns
SIp setup time	tsik2	$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, 2.$	$7 \text{ V} \leq \text{V}_{\text{DD}} \leq 4.0 \text{ V}$	1/fмск + 40		ns
(to SCKp↑) ^{Note 2}		$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V}, 2.$	$3 \text{ V} \leq \text{V}_{b} \leq 2.7 \text{ V}$	1/fмск + 40		ns
		$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, 1.$	$6 \text{ V} \leq \text{V}_{\text{DD}} \leq 2.0 \text{ V}$	1/fмск + 60		ns
SIp hold time (from SCKp↑) ^{Note 3}	tksi2			1/fмск + 62		ns
Delay time from SCKp↓ to	tĸso2	$4.0 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, 2.$	$7 \text{ V} \leq \text{V}_{b} \leq 4.0 \text{ V},$		2/fмск +	ns
SOp output Note 4		C _b = 30 pF, R _b = 1.4 k	D		240	
		$2.7 \text{ V} \le \text{V}_{\text{DD}} < 4.0 \text{ V}, 2.$	$3 \text{ V} \leq \text{V}_{b} \leq 2.7 \text{ V},$		2/fмск +	ns
		C _b = 30 pF, R _b = 2.7 k	D		428	
		$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, 1.$	$6 \text{ V} \leq \text{V}_{\text{b}} \leq 2.0 \text{ V},$		2/fмск +	ns
		$C_b = 30 \text{ pF}, R_b = 5.5 \text{ km}$	Ω		1146	

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, \text{V}_{\text{SS}} = 0 \text{ V})$


Notes 1. Transfer rate in the SNOOZE mode: MAX. 1 Mbps

- **2.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp setup time becomes "to SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
- **3.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The SIp hold time becomes "from SCKp↓" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
- **4.** When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1. The delay time to SOp output becomes "from SCKp↑" when DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.
- Cautions 1. Select the TTL input buffer for the SIp and SCKp pins and the N-ch open drain output (V_{DD} tolerance) mode for the SOp pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For V_{IH} and V_{IL}, see the DC characteristics with TTL input buffer selected.
 - 2. CSI01 and CSI11 cannot communicate at different potential.

Simplified SPI (CSI) mode connection diagram (during communication at different potential)




Simplified SPI (CSI) mode serial transfer timing (slave mode) (during communication at different potential) (When DAPmn = 0 and CKPmn = 0, or DAPmn = 1 and CKPmn = 1.)



- Remarks 1.
 R_b [Ω]: Communication line (SOp) pull-up resistance, C_b [F]: Communication line (SOp) load capacitance,

 V_b [V]: Communication line voltage
 - **2.** p: CSI number (p = 00, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0)

 fMCK: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn))



Simplified SPI (CSI) mode serial transfer timing (slave mode) (during communication at different potential) (When DAPmn = 0 and CKPmn = 1, or DAPmn = 1 and CKPmn = 0.)

Remark p: CSI number (p = 00, 20), m: Unit number (m = 0, 1), n: Channel number (n = 0)



Parameter	Symbol	Conditions	HS (high-sp Mo	,	Unit
			MIN.	MAX.	Unit kHz kHz kHz ns ns ns ns ns ns ns ns ns ns ns
SCLr clock frequency	fsc∟	$\begin{array}{l} 4.0 \; V \leq V_{DD} \leq 5.5 \; V, 2.7 \; V \leq V_{b} \leq 4.0 \; V, \\ \\ C_{b} = 100 \; pF, \; R_{b} = 2.8 \; k\Omega \end{array}$		100 ^{Note1}	kHz
		$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_b \leq 2.7 \; V, \\ C_b = 100 \; pF, \; R_b = 2.7 \; k\Omega \end{array}$		100 ^{Note1}	kHz
		$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, 1.6 \text{ V} \le \text{V}_{\text{b}} \le 2.0 \text{ V},$ $C_{\text{b}} = 100 \text{ pF}, R_{\text{b}} = 5.5 \text{ k}\Omega$		100 ^{Note1}	kHz
Hold time when SCLr = "L"	t∟ow	$\begin{array}{l} 4.0 \ V \leq V_{DD} \leq 5.5 \ V, \ 2.7 \ V \leq V_{b} \leq 4.0 \ V, \\ C_{b} = 100 \ pF, \ R_{b} = 2.8 \ k\Omega \end{array}$	4600		ns
		$ \begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_{b} \leq 2.7 \; V, \\ \mathbf{C}_{b} = 100 \; pF, \; R_{b} = 2.7 \; k\Omega \end{array} $	4600		ns
		$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, 1.6 \text{ V} \le \text{V}_{\text{b}} \le 2.0 \text{ V},$ $C_{\text{b}} = 100 \text{ pF}, R_{\text{b}} = 5.5 \text{ k}\Omega$	4650		ns
Hold time when SCLr = "H"	tніgн	$\begin{array}{l} 4.0 \; V \leq V_{\text{DD}} \leq 5.5 \; V, \; 2.7 \; V \leq V_{\text{b}} \leq 4.0 \; V, \\ \\ C_{\text{b}} = 100 \; pF, \; R_{\text{b}} = 2.8 \; k\Omega \end{array}$	2700		ns
		$\begin{array}{l} 2.7 \; V \leq V_{DD} < 4.0 \; V, \; 2.3 \; V \leq V_{b} \leq 2.7 \; V, \\ \mathbf{C}_{b} = 100 \; pF, \; R_{b} = 2.7 \; k\Omega \end{array}$	2400		ns
		$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, 1.6 \text{ V} \le \text{V}_{\text{b}} \le 2.0 \text{ V},$ $C_{\text{b}} = 100 \text{ pF}, R_{\text{b}} = 5.5 \text{ k}\Omega$	1830		ns
Data setup time (reception)	tsu:dat	$\begin{array}{l} 4.0 \ V \leq V_{DD} \leq 5.5 \ V, \ 2.7 \ V \leq V_{b} \leq 4.0 \ V, \\ C_{b} = 100 \ pF, \ R_{b} = 2.8 \ k\Omega \end{array}$	1/fмск + 760 ^{Note2}		ns
		$ \begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 100 \ pF, \ R_b = 2.7 \ k\Omega \end{array} $	1/f _{мск} + 760 ^{Note2}		ns
		$\label{eq:VD} \begin{array}{l} 2.4 \ V \leq V_{DD} < 3.3 \ V, \ 1.6 \ V \leq V_b \leq 2.0 \ V, \\ \\ C_b = 100 \ pF, \ R_b = 5.5 \ k\Omega \end{array}$	1/fмск + 570 ^{Note2}		ns
Data hold time (transmission)	thd:dat		0	1420	ns
		$\begin{array}{l} 2.7 \ V \leq V_{DD} < 4.0 \ V, \ 2.3 \ V \leq V_b \leq 2.7 \ V, \\ C_b = 100 \ pF, \ R_b = 2.7 \ k\Omega \end{array}$	0	1420	ns
		$2.4 \text{ V} \le \text{V}_{\text{DD}} < 3.3 \text{ V}, 1.6 \text{ V} \le \text{V}_{b} \le 2.0 \text{ V},$ $C_{b} = 100 \text{ pF}, R_{b} = 5.5 \text{ k}\Omega$	0	1215	ns

(8) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified I^2C mode)

 $(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$


Notes 1. The value must be equal to or less than $f_{MCK}/4$.

2. Set tsu:DAT so that it will not exceed the hold time when SCLr = "L" or SCLr = "H".


- Cautions 1. Select the TTL input buffer and the N-ch open drain output (V_{DD} tolerance) mode for the SDAr pin and the N-ch open drain output (V_{DD} tolerance) mode for the SCLr pin by using port input mode register 1 (PIM1) and port output mode register 1 (POM1). For V_{IH} and V_{IL}, see the DC characteristics with TTL input buffer selected.
 - 2. IIC01 and IIC11 cannot communicate at different potential.

(**Remarks** are listed on the next page.)

Simplified I²C mode connection diagram (during communication at different potential)



Simplified I²C mode serial transfer timing (during communication at different potential)



- Remarks 1. R_b [Ω]: Communication line (SDAr, SCLr) pull-up resistance, C_b [F]: Communication line (SDAr, SCLr) load capacitance, Vb [V]: Communication line voltage
 - **2.** r: IIC Number (r = 00, 20)
 - 3. fMCK: Serial array unit operation clock frequency (Operation clock to be set by the serial clock select register m (SPSm) and the CKSmn bit of serial mode register mn (SMRmn).

m: Unit number (m = 0,1), n: Channel number (n = 0))



3.5.2 Serial interface IICA

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, \text{V}_{\text{DD}} \le 5.5 \text{ V})$	′ss = 0 V)
--	------------


Parameter	Symbol	Conditions	HS	HS (high-speed main) mode			Unit
			Standar	rd Mode	d Mode Fast Mode		
			MIN.	MAX.	MIN.	MAX.	
SCLA0 clock frequency	fscl	Fast mode: fc∟к≥ 3.5 MHz			0	400	kHz
		Normal mode: fcLK≥ 1 MHz	0	100			kHz
Setup time of restart condition	tsu:sta		4.7		0.6		μs
Hold time ^{Note 1}	thd:sta		4.0		0.6		μs
Hold time when SCLA0 = "L"	t LOW		4.7		1.3		μs
Hold time when SCLA0 = "H"	tніgн		4.0		0.6		μs
Data setup time (reception)	tsu:dat		250		100		ns
Data hold time (transmission) ^{Note 2}	thd:dat		0	3.45	0	0.9	μs
Setup time of stop condition	tsu:sto		4.0		0.6		μs
Bus-free time	t BUF		4.7		1.3		μs

Notes 1. The first clock pulse is generated after this period when the start/restart condition is detected.

2. The maximum value (MAX.) of the:DAT is during normal transfer and a clock stretch state is inserted in the ACK (acknowledge) timing.

- Caution Only in the 30-pin products, the values in the above table are applied even when bit 2 (PIOR2) in the peripheral I/O redirection register (PIOR) is 1. At this time, the pin characteristics (IOH1, IOL1, VOH1, VOL1) must satisfy the values in the redirect destination.
- **Remark** The maximum value of Cb (communication line capacitance) and the value of Rb (communication line pull-up resistor) at that time in each mode are as follows.

IICA serial transfer timing





3.6 Analog Characteristics

3.6.1 A/D converter characteristics

Classification of A/D converter characteristics

Input channel	Reference Voltage								
	Reference voltage (+) = AVREFP Reference voltage (–) = AVREFM	Reference voltage (+) = VDD Reference voltage (-) = Vss	Reference voltage (+) = VBGR Reference voltage (–) = AVREFM						
ANI0 to ANI3	Refer to 3.6.1 (1) .	Refer to 3.6.1 (3) .	Refer to 3.6.1 (4) .						
ANI16 to ANI22	Refer to 3.6.1 (2) .								
Internal reference voltage Temperature sensor output voltage	Refer to 3.6.1 (1) .		_						

(1) When reference voltage (+) = AV_{REFP}/ANI0 (ADREFP1 = 0, ADREFP0 = 1), reference voltage (–) = AV_{REFM}/ANI1 (ADREFM = 1), target pin: ANI2, ANI3, internal reference voltage, and temperature sensor output voltage

 $(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{AV}_{REFP} \le \text{VDD} \le 5.5 \text{ V}, \text{Vss} = 0 \text{ V}, \text{Reference voltage (+)} = \text{AV}_{REFP}, \text{Reference voltage (-)} = \text{AV}_{REFM} = 0 \text{ V})$

Parameter	Symbol	Cor	Conditions			MAX.	Unit
Resolution	RES			8		10	bit
Overall error ^{Note 1}	AINL	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}			1.2	±3.5	LSB
Conversion time	t CONV	10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.125		39	μs
		Target pin: ANI2, ANI3	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	3.1875		39	μs
			$2.4 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	17		39	μs
		10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.375		39	μs
		Target pin: Internal	$2.7 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	3.5625		39	μs
reference voltage, and temperature sensor output voltage (HS (high-speed main) mode)	2.4 V ≤ V _{DD} ≤ 5.5 V	17		39	μs		
Zero-scale error ^{Notes 1, 2}	EZS	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}				±0.25	%FSR
Full-scale error ^{Notes 1, 2}	EFS	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}				±0.25	%FSR
Integral linearity error ^{Note 1}	ILE	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}				±2.5	LSB
Differential linearity error	DLE	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}				±1.5	LSB
Analog input voltage	VAIN	ANI2, ANI3		0		AVREFP	V
		Ŭ	Internal reference voltage (HS (high-speed main) mode)		VBGR Note 4		V
			Temperature sensor output voltage (HS (high-speed main) mode)			4	V

(**Notes** are listed on the next page.)



- **Notes 1.** Excludes quantization error (±1/2 LSB).
 - **2.** This value is indicated as a ratio (%FSR) to the full-scale value.
 - 3. When AV_{REFP} < V_{DD}, the MAX. values are as follows. Overall error: Add ±1.0 LSB to the MAX. value when AV_{REFP} = V_{DD}. Zero-scale error/Full-scale error: Add ±0.05%FSR to the MAX. value when AV_{REFP} = V_{DD}. Integral linearity error/ Differential linearity error: Add ±0.5 LSB to the MAX. value when AV_{REFP} = V_{DD}.
 - 4. Refer to 3.6.2 Temperature sensor/internal reference voltage characteristics.
- (2) When reference voltage (+) = AVREFP/ANI0 (ADREFP1 = 0, ADREFP0 = 1), reference voltage (-) = AVREFM/ANI1 (ADREFM = 1), target pin: ANI16 to ANI22

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{AV}_{\text{REFP}} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, \text{V}_{\text{SS}} = 0 \text{ V}, \text{Reference voltage (+)} = \text{AV}_{\text{REFP}}, \text{Reference voltage (-)} = 100^{\circ}\text{C}, 1$	
AVREFM = 0 V)	

Parameter	Symbol	Conditio	ns	MIN.	TYP.	MAX.	Unit
Resolution	Res			8		10	bit
Overall error Note 1	AINL	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}				±5.0	LSB
Conversion time	tconv	10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.125		39	μs
		Target ANI pin: ANI16 to ANI22	2.7 V ≤ VDD ≤ 5.5 V	3.1875		39	μs
			2.4 V ≤ VDD ≤ 5.5 V	17		39	μs
Zero-scale error Notes 1, 2	EZS	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}			±0.35	%FSR	
Full-scale error Notes 1, 2	EFS	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}				±0.35	%FSR
Integral linearity error Note 1	ILE	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}				±3.5	LSB
Differential linearity error ^{Note 1}	DLE	10-bit resolution AV _{REFP} = V _{DD} ^{Note 3}				±2.0	LSB
Analog input voltage	VAIN	ANI16 to ANI22		0		AVREFP and VDD	V

Notes 1. Excludes quantization error (±1/2 LSB).

- **2.** This value is indicated as a ratio (%FSR) to the full-scale value.
- **3.** When $AV_{REFP} \leq V_{DD}$, the MAX. values are as follows.

Overall error: Add ± 4.0 LSB to the MAX. value when AV_{REFP} = V_{DD}.

Zero-scale error/Full-scale error: Add $\pm 0.20\%$ FSR to the MAX. value when AV_{REFP} = V_{DD}.

Integral linearity error/ Differential linearity error: Add ±2.0 LSB to the MAX. value when AVREFP = VDD.



(3) When reference voltage (+) = V_{DD} (ADREFP1 = 0, ADREFP0 = 0), reference voltage (−) = V_{SS} (ADREFM = 0), target pin: ANI0 to ANI3, ANI16 to ANI22, internal reference voltage, and temperature sensor output voltage

Parameter	Symbol	Condition	ns	MIN.	TYP.	MAX.	Unit
Resolution	Res			8		10	bit
Overall error ^{Note 1}	AINL	10-bit resolution			1.2	±7.0	LSB
Conversion time	t CONV	10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.125		39	μs
		Target pin: ANI0 to ANI3,	2.7 V ≤ V _{DD} ≤ 5.5 V	3.1875		39	μs
		ANI16 to ANI22	2.4 V ≤ VDD ≤ 5.5 V	17		39	μs
Conversion time	t CONV	10-bit resolution	$3.6 \text{ V} \leq \text{V}_{\text{DD}} \leq 5.5 \text{ V}$	2.375		39	μs
			2.7 V ≤ VDD ≤ 5.5 V	3.5625		39	μs
	voltage, and temperature sensor output voltage (HS (high-speed main) mode)	2.4 V ≤ V _{DD} ≤ 5.5 V	17		39	μs	
Zero-scale error ^{Notes 1, 2}	EZS	10-bit resolution				±0.60	%FSR
Full-scale error ^{Notes 1, 2}	EFS	10-bit resolution				±0.60	%FSR
Integral linearity error ^{Note 1}	ILE	10-bit resolution				±4.0	LSB
Differential linearity error Note 1	DLE	10-bit resolution				±2.0	LSB
Analog input voltage	VAIN	ANI0 to ANI3, ANI16 to ANI2	2	0		VDD	V
		Internal reference voltage (HS (high-speed main) mode)			VBGR Note 3		V
		Temperature sensor output v (HS (high-speed main) mode)	0	V _{TMPS25} Note 3			V

- ((TA = –40 to +105°C, 2.4 V ≤ VDD ≤ 5.5 V, Vs	ss = 0 V. Reference voltage (+) = Vpp.	Reference voltage (–) = Vss)

Notes 1. Excludes quantization error (±1/2 LSB).

2. This value is indicated as a ratio (%FSR) to the full-scale value.

3. Refer to 3.6.2 Temperature sensor/internal reference voltage characteristics.



(4) When reference voltage (+) = Internal reference voltage (ADREFP1 = 1, ADREFP0 = 0), reference voltage (-) = AV_{REFM} (ADREFM = 1), target pin: ANI0, ANI2, ANI3, and ANI16 to ANI22

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{ Vss} = 0 \text{ V}, \text{ Reference voltage (+)} = \text{V}_{BGR} \text{ Note 3}, \text{ Reference voltage (-)} = 0 \text{ V}_{BGR} \text{ Note 3}$
AV _{REFM} Note 4 = 0 V, HS (high-speed main) mode)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Resolution	Res			8		bit
Conversion time	t CONV	8-bit resolution	17		39	μs
Zero-scale error ^{Notes 1, 2}	EZS	8-bit resolution			±0.60	%FSR
Integral linearity error ^{Note 1}	ILE	8-bit resolution			±2.0	LSB
Differential linearity error Note 1	DLE	8-bit resolution			±1.0	LSB
Analog input voltage	VAIN		0		VBGR Note 3	V

Notes 1. Excludes quantization error (±1/2 LSB).

2. This value is indicated as a ratio (%FSR) to the full-scale value.

3. Refer to 3.6.2 Temperature sensor/internal reference voltage characteristics.

4. When reference voltage (–) = Vss, the MAX. values are as follows.

Zero-scale error: Add $\pm 0.35\%$ FSR to the MAX. value when reference voltage (–) = AV_{REFM}. Integral linearity error: Add ± 0.5 LSB to the MAX. value when reference voltage (–) = AV_{REFM}. Differential linearity error: Add ± 0.2 LSB to the MAX. value when reference voltage (–) = AV_{REFM}.



3.6.2 Temperature sensor/internal reference voltage characteristics

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Temperature sensor output voltage	VTMPS25	Setting ADS register = 80H, TA = +25°C		1.05		V
Internal reference voltage	VBGR	Setting ADS register = 81H	1.38	1.45	1.50	V
Temperature coefficient	Fvtmps	Temperature sensor output voltage that depends on the temperature		-3.6		mV/°C
Operation stabilization wait time	tamp		5			μs


$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V}, \text{HS (high-speed main) mode}$

3.6.3 POR circuit characteristics

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, V_{\text{SS}} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Detection voltage	Vpor	The power supply voltage is rising.	1.45	1.51	1.57	V
	Vpdr	The power supply voltage is falling.	1.44	1.50	1.56	V
Minimum pulse width Note	Tpw		300			μs

Note Minimum time required for a POR reset when V_{DD} exceeds below V_{PDR}. This is also the minimum time required for a POR reset from when V_{DD} exceeds below 0.7 V to when V_{DD} exceeds V_{POR} while STOP mode is entered or the main system clock is stopped through setting bit 0 (HIOSTOP) and bit 7 (MSTOP) in the clock operation status control register (CSC).





3.6.4 LVD circuit characteristics

LVD Detection Voltage of Reset Mode and Interrupt Mode

 $(T_A = -40 \text{ to } +105^{\circ}\text{C}, \text{ VPDR} \le \text{VDD} \le 5.5 \text{ V}, \text{ Vss} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Detection supply voltage	VLVD0	The power supply voltage is rising.	3.90	4.06	4.22	V
		The power supply voltage is falling.	3.83	3.98	4.13	V
	VLVD1	The power supply voltage is rising.	3.60	3.75	3.90	V
		The power supply voltage is falling.	3.53	3.67	3.81	V
	VLVD2	The power supply voltage is rising.	3.01	3.13	3.25	V
		The power supply voltage is falling.	2.94	3.06	3.18	V
	VLVD3	The power supply voltage is rising.	2.90	3.02	3.14	V
		The power supply voltage is falling.	2.85	2.96	3.07	V
	VLVD4	The power supply voltage is rising.	2.81	2.92	3.03	V
		The power supply voltage is falling.	2.75	2.86	2.97	V
	VLVD5	The power supply voltage is rising.	2.70	2.81	2.92	V
		The power supply voltage is falling.	2.64	2.75	2.86	V
	VLVD6	The power supply voltage is rising.	2.61	2.71	2.81	V
		The power supply voltage is falling.	2.55	2.65	2.75	V
	VLVD7	The power supply voltage is rising.	2.51	2.61	2.71	V
		The power supply voltage is falling.	2.45	2.55	2.65	V
Minimum pulse width	tLw		300			μs
Detection delay time					300	μs



LVD detection voltage of interrupt & reset mode $(T_{A} = -40 \text{ to } +105^{\circ}\text{C} \text{ V}_{PDP} \le \text{V}_{PP} \le 5.5 \text{ V} \text{ V}_{ee} = 0.17$

$(1_A = -40 \text{ to } +105^{\circ}\text{C}, \text{ Vpdr} \le \text{Vdd} \le 5.5 \text{ V}, \text{ Vss} = 0 \text{ V})$								
Parameter	Symbol		Conditions			TYP.	MAX.	Unit
Interrupt and reset	VLVDD0	VPOC2,	VPOC1, VPOC1 = 0, 1, 1, falli	ng reset voltage	2.64	2.75	2.86	V
mode	VLVDD1		LVIS1, LVIS0 = 1, 0	Rising reset release voltage	2.81	2.92	3.03	V
				Falling interrupt voltage	2.75	2.86	2.97	V
	VLVDD2		LVIS1, LVIS0 = 0, 1	Rising reset release voltage	2.90	3.02	3.14	V
				Falling interrupt voltage	2.85	2.96	3.07	V
	VLVDD3		LVIS1, LVIS0 = 0, 0	Rising reset release voltage	3.90	4.06	4.22	V
				Falling interrupt voltage	3.83	3.98	4.13	V

3.6.5 Power supply voltage rising slope characteristics

(T_A = -40 to +105°C, Vss = 0 V)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Power supply voltage rising slope	SVDD				54	V/ms

Caution Make sure to keep the internal reset state by the LVD circuit or an external reset until VDD reaches the operating voltage range shown in 3.4 AC Characteristics.




3.7 RAM Data Retention Characteristics

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, V_{SS} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Data retention supply voltage	VDDDR		1.44 ^{Note}		5.5	V

Note This depends on the POR detection voltage. For a falling voltage, data in RAM are retained until the voltage reaches the level that triggers a POR reset but not once it reaches the level at which a POR reset is generated.



3.8 Flash Memory Programming Characteristics

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{DD} \le 5.5 \text{ V}, \text{V}_{SS} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
System clock frequency	fськ		1		24	MHz
Code flash memory rewritable times Notes 1, 2, 3	Cerwr	Retained for 20 years $T_A = 85^{\circ}C^{Note 4}$	1,000			Times
Data flash memory rewritable times Notes 1, 2, 3		Retained for 1 year T _A = 25°C		1,000,000		
		Retained for 5 years T _A = 85°C Note 4	100,000			
		Retained for 20 years T _A = 85°C ^{Note 4}	10,000			

Notes 1. 1 erase + 1 write after the erase is regarded as 1 rewrite. The retaining years are until next rewrite after the rewrite.

- 2. When using flash memory programmer and Renesas Electronics self programming library
- **3.** These are the characteristics of the flash memory and the results obtained from reliability testing by Renesas Electronics Corporation.
- 4. This temperature is the average value at which data are retained.



3.9 Dedicated Flash Memory Programmer Communication (UART)


$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le \text{V}_{\text{DD}} \le 5.5 \text{ V}, \text{V}_{\text{SS}} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Transfer rate		During serial programming	115,200		1,000,000	bps

3.10 Timing of Entry to Flash Memory Programming Modes

$(T_A = -40 \text{ to } +105^{\circ}\text{C}, 2.4 \text{ V} \le V_{DD} \le 5.5 \text{ V}, \text{ V}_{SS} = 0 \text{ V})$

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Time to complete the communication for the initial setting after the external reset is released	tsuinit	POR and LVD reset are released before external release			100	ms
Time to release the external reset after the TOOL0 pin is set to the low level	tsu	POR and LVD reset are released before external release	10			μs
Time to hold the TOOL0 pin at the low level after the external reset is released (excluding the processing time of the firmware to	tнo	POR and LVD reset are released before external release	1			ms
control the flash memory)						




- <1> The low level is input to the TOOL0 pin.
- <2> The external reset is released (POR and LVD reset must be released before the external reset is released.).
- <3> The TOOL0 pin is set to the high level.
- <4> Setting of the flash memory programming mode by UART reception and complete the baud rate setting.
- **Remark** tsuinit: Communication for the initial setting must be completed within 100 ms after the external reset is released during this period.
 - $t_{\text{SU:}}$ Time to release the external reset after the TOOL0 pin is set to the low level
 - the: Time to hold the TOOL0 pin at the low level after the external reset is released (excluding the processing time of the firmware to control the flash memory)




4. PACKAGE DRAWINGS


4.1 20-pin package

JEITA Package Code	RENESAS Code	Previous Code	MASS (TYP.) [g]
P-LSSOP20-4.4x6.5-0.65	PLSP0020JB-A	P20MA-65-NAA-1	0.1



detail of lead end





NOTE

1.Dimensions "%1" and "%2" do not include mold flash.

2.Dimension "%3" does not include trim offset.


◄ ──── H	E
St	


	(UNIT:mm)
ITEM	DIMENSIONS
D	6.50±0.10
Е	4.40±0.10
HE	6.40±0.20
А	1.45 MAX.
A1	0.10±0.10
A2	1.15
е	0.65±0.12
bp	0.22 + 0.10 - 0.05
С	0.15 + 0.05 - 0.02
L	0.50±0.20
У	0.10
θ	0° to 10°

O 2012 Renesas Electronics Corporation. All rights reserved.




JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-TSSOP20-4.40x6.50-0.65	PTSP0020JI-A	0.08










NOTES: 1. DIMENSION 'D' AND 'E1' DOES NOT INCLUDE MOLD FLASH. 2. DIMENSION 'b' DOES NOT INCLUDE TRIM OFFSET. 3. DIMENSION 'D' AND 'E1' TO BE DETERMINED AT DATUM PLANE .

Reference	Dimension in Millimeters				
Symbol	Min.	Nom.	Max.		
Α	-	-	1.20		
A1	0.05	-	0.15		
A2	0.80	1.00	1.05		
b	0.19	-	0.30		
С	0.09	0.127	0.20		
D	6.40	6.50	6.60		
E1	4.30	4.40	4.50		
E		6.40 BSC			
e		0.65 BSC			
L1		1.00 REF			
L	0.50	0.60	0.75		
S	0.20	-	-		
θ	0°	-	8°		
aaa		0.10			
bbb	0.10				
ccc	0.05				
ddd		0.20			

С

4.2 24-pin package

JEITA Package Code	RENESAS Code	Previous Code	MASS (TYP.) [g]
P-HWQFN24-4x4-0.50	PWQN0024KE-A	P24K8-50-CAB-1	0.04



C


13 e

b 🕀 x 🕅 S A B

E2

12

DETAIL OF	(A)	PART
-----------	-----	------



(UNIT:mm)
DIMENSIONS
4.00±0.05
$4.00\pm\!0.05$
0.75±0.05
$0.25 \substack{+0.05 \\ -0.07}$
0.50
$0.40\pm\!0.10$
0.05
0.05

ITEM		D2		E2			
		MIN	NOM	MAX	MIN	NOM	MAX
EXPOSED DIE PAD VARIATIONS	А	2.45	2.50	2.55	2.45	2.50	2.55

©2012 Renesas Electronics Corporation. All rights reserved.

24

19


Lp


<u>|</u> 18

В




JEITA Package code	RENESAS code	MASS(TYP.)[g]
P-HWQFN024-4x4-0.50	PWQN0024KF-A	0.04








JEITA Package Code	RENESAS Code	MASS(Typ.)[g]
P-HWQFN24-4×4-0.50	PWQN0024KH-A	0.04







Reference	Dimens	Dimension in Millimeters		
Symbol	Min.	Nom.	Max.	
А	-	_	0.80	
A ₁	0.00	_	0.05	
A ₃	0	.20 REF	Ξ.	
b	0.20	0.25	0.30	
D	_	4.00	_	
E		4.00	_	
е		0.50	-	
N		24		
L	0.30	0.40	0.50	
К	0.20	—	-	
D ₂	2.50	2.60	2.70	
E ₂	2.50	2.60	2.70	
aaa	—	—	0.15	
bbb	-	—	0.10	
ссс	_	_	0.10	
ddd	_	—	0.05	
eee	_	—	0.08	




4.3 30-pin package

Γ	JEITA Package Code	RENESAS Code	Previous Code	MASS (TYP.) [g]
	P-LSSOP30-0300-0.65	PLSP0030JB-B	S30MC-65-5A4-3	0.18







NOTE

Each lead centerline is located within 0.13 mm of its true position (T.P.) at maximum material condition.

H-	
 -	► J
Î	
	ITEM MILLIMETERS

Lκ

11 - 101	
A	9.85±0.15
В	0.45 MAX.
С	0.65 (T.P.)
D	$0.24^{+0.08}_{-0.07}$
E	0.1±0.05
F	1.3±0.1
G	1.2
Н	8.1±0.2
I	6.1±0.2
J	1.0±0.2
K	0.17±0.03
L	0.5
М	0.13
N	0.10
Р	3° ^{+5°} -3°
Т	0.25
U	0.6±0.15

© 2012 Renesas Electronics Corporation. All rights reserved.



Revision History

RL78/G12 Datasheet

		Description		
Rev.	Date	Page	Summary	
1.00	Dec 10, 2012	-	First Edition issued	
2.00	Sep 06, 2013	1	Modification of 1.1 Features	
		3	Modification of 1.2 List of Part Numbers	
		4	Modification of Table 1-1. List of Ordering Part Numbers, Note, and Caution	
		7 to 9	Modification of package name in 1.4.1 to 1.4.3	
		14	Modification of tables in 1.7 Outline of Functions	
		17	Modification of description of table in 2.1 Absolute Maximum Ratings (T _A = 25°C)	
		18	Modification of table, Note, and Caution in 2.2.1 X1 oscillator characteristics	
		18	Modification of table in 2.2.2 On-chip oscillator characteristics	
		19	Modification of Note 3 in 2.3.1 Pin characteristics (1/4)	
		20	Modification of Note 3 in 2.3.1 Pin characteristics (2/4)	
		23	Modification of Notes 1 and 2 in (1) 20-, 24-pin products (1/2)	
		24	Modification of Notes 1 and 3 in (1) 20-, 24-pin products (2/2)	
		25	Modification of Notes 1 and 2 in (2) 30-pin products (1/2)	
		26	Modification of Notes 1 and 3 in (2) 30-pin products (2/2)	
		27	Modification of (3) Peripheral functions (Common to all products)	
		28	Modification of table in 2.4 AC Characteristics	
		29	Addition of Minimum Instruction Execution Time during Main System Clock Operation	
		30	Modification of figures of AC Timing Test Point and External Main System Clock Timing	
		31	Modification of figure of AC Timing Test Point	
		31	Modification of description and Note 2 in (1) During communication at same potential (UART mode)	
		32	Modification of description in (2) During communication at same potential (CSI mode)	
		33	Modification of description in (3) During communication at same potential (CSI mode)	
		34	Modification of description in (4) During communication at same potential (CSI mode)	
		36	Modification of table and Note 2 in (5) During communication at same potential (simplified I ² C mode)	
		38, 39	Modification of table and Notes 1 to 9 in (6) Communication at different potential	
			(1.8 V, 2.5 V, 3 V) (UART mode)	
		40	Modification of Remarks 1 to 3 in (6) Communication at different potential (1.8 V, 2.5 V, 3 V) (UART mode)	
		41	Modification of table in (7) Communication at different potential (2.5 V, 3 V) (CSI mode)	
		42	Modification of Caution in (7) Communication at different potential (2.5 V, 3 V) (CSI mode)	
		43	Modification of table in (8) Communication at different potential (1.8 V, 2.5 V, 3 V) (CSI mode) (1/3)	
		44	Modification of table and Notes 1 and 2 in (8) Communication at different potential (1.8 V, 2.5 V, 3 V) (CSI mode) (2/3)	
		45	Modification of table, Note 1, and Caution 1 in (8) Communication at different potential (1.8 V, 2.5 V, 3 V) (CSI mode) (3/3)	
		47	Modification of table in (9) Communication at different potential (1.8 V, 2.5 V, 3 V) (CSI mode)	
		50	Modification of table, Note 1, and Caution 1 in (10) Communication at different potential (1.8 V, 2.5 V, 3 V) (simplified I ² C mode)	

			Description
Rev.	Date	Page	Summary
2.00	Sep 06, 2013	52	Modification of Remark in 2.5.2 Serial interface IICA
		53	Addition of table to 2.6.1 A/D converter characteristics
		53	Modification of description in 2.6.1 (1)
		54	Modification of Notes 3 to 5 in 2.6.1 (1)
		54	Modification of description and Notes 2 to 4 in 2.6.1 (2)
		55	Modification of description and Notes 3 and 4 in 2.6.1 (3)
		56	Modification of description and Notes 3 and 4 in 2.6.1 (4)
		57	Modification of table in 2.6.2 Temperature sensor/internal reference voltage characteristics
		57	Modification of table and Note in 2.6.3 POR circuit characteristics
		58	Modification of table in 2.6.4 LVD circuit characteristics
		59	Modification of table of LVD detection voltage of interrupt & reset mode
		59	Modification of number and title to 2.6.5 Power supply voltage rising slope characteristics
		61	Modification of table, figure, and Remark in 2.10 Timing of Entry to Flash Memory Programming Modes
		62 to 103	Addition of products of industrial applications (G: T _A = -40 to +105°C)
		104 to 106	Addition of products of industrial applications (G: $T_A = -40$ to $+105^{\circ}C$)
2.10	Mar 25, 2016	6	Modification of Figure 1-1 Part Number, Memory Size, and Package of RL78/G12
		7	Modification of Table 1-1 List of Ordering Part Numbers
		8	Addition of product name (RL78/G12) and description (Top View) in 1.4.1 20- pin products
		9	Addition of product name (RL78/G12) and description (Top View) in 1.4.2 24- pin products
		10	Addition of product name (RL78/G12) and description (Top View) in 1.4.3 30- pin products
		15	Modification of description in 1.7 Outline of Functions
		16	Modification of description, and addition of target products
		52	Modification of note 2 in 2.5.2 Serial interface IICA
		60	Modification of title and note, and addition of caution in 2.7 RAM Data Retention Characteristics
		60	Modification of conditions in 2.8 Flash Memory Programming Characteristics
		62	Modification of description, and addition of target products and remark
		94	Modification of note 2 in 3.5.2 Serial interface IICA
		102	Modification of title and note in 3.7 RAM Data Retention Characteristics
		102	Modification of conditions in 3.8 Flash Memory Programming Characteristics
		104 to 106	Addition of package name
2.20	Oct 31, 2018	4	Modification of Table 1-1 List of Ordering Part Numbers
		7	Modification of pin configuration diagram in 1.4.1 20-pin products
2.21	Jan 31, 2020	3	Addition of packaging specifications in Figure 1-1 Part Number, Memory Size, and Package of RL78/G12
		4, 5	Addition of part numbers and RENESAS codes in Table 1-1 List of Ordering Part Numbers
		105, 106, 108	Modification of the titles of the subchapters and deletion of product names in Chapter 4
		108	Addition of figure in 4.2 24-pin package
2.22	Apr 28, 2020	3	Addition of packaging specifications and package type in Figure 1-1 Part
			Number, Memory Size, and Package of RL78/G12
		4	Addition of packaging specifications in Table 1-1 List of Ordering Part Numbers
		9	Addition of packaging specifications in 1.4.1 20-pin products
		107	Addition of figure in 4.1 20-pin package

		Description	
Rev.	Date	Page	Summary
2.30	Jun 19, 2020	3	Modification of Figure 1-1 Part Number, Memory Size, and Package of RL78/G12
		4	Modification of Table 1-1 List of Ordering Part Numbers
2.31	Mar 20, 2023	All	The module name for CSI was changed to Simplified SPI (CSI)
		All	"wait" for IIC was modified to "clock stretch"
		1	Addition of Note 1 in 1 Features
		4	Modification of description in Table 1-1 List of Ordering Part Numbers
		108	Addition of package drawing in 4.4 24-pin Package
2.40	Mar 29, 2024	3	Modification of Figure 1-1. Part Number, Memory Size, and Package of RL78/G12
		4	Modification of Table 1-1. List of Ordering Part Numbers

All trademarks and registered trademarks are the property of their respective owners.

SuperFlash is a registered trademark of Silicon Storage Technology, Inc. in several countries including the United States and Japan.

Caution: This product uses SuperFlash[®] technology licensed from Silicon Storage Technology, Inc.

General Precautions in the Handling of Microprocessing Unit and Microcontroller Unit Products

The following usage notes are applicable to all Microprocessing unit and Microcontroller unit products from Renesas. For detailed usage notes on the products covered by this document, refer to the relevant sections of the document as well as any technical updates that have been issued for the products.

1. Precaution against Electrostatic Discharge (ESD)

A strong electrical field, when exposed to a CMOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop the generation of static electricity as much as possible, and quickly dissipate it when it occurs. Environmental control must be adequate. When it is dry, a humidifier should be used. This is recommended to avoid using insulators that can easily build up static electricity. Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors must be grounded. The operator must also be grounded using a wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions must be taken for printed circuit boards with mounted semiconductor devices.

2. Processing at power-on

The state of the product is undefined at the time when power is supplied. The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the time when power is supplied. In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the time when power is supplied until the reset process is completed. In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the time when power is supplied until the power is supplied until the power is supplied until the power reaches the level at which resetting is specified.

3. Input of signal during power-off state

Do not input signals or an I/O pull-up power supply while the device is powered off. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Follow the guideline for input signal during power-off state as described in your product documentation.

4. Handling of unused pins

Handle unused pins in accordance with the directions given under handling of unused pins in the manual. The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of the LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible.

5. Clock signals

After applying a reset, only release the reset line after the operating clock signal becomes stable. When switching the clock signal during program execution, wait until the target clock signal is stabilized. When the clock signal is generated with an external resonator or from an external oscillator during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Additionally, when switching to a clock signal produced with an external resonator or by an external oscillator while program execution is in progress, wait until the target clock signal is stable.

6. Voltage application waveform at input pin

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (Max.) and V_{IH} (Min.) due to noise, for example, the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (Max.) and V_{IH} (Min.).

7. Prohibition of access to reserved addresses

Access to reserved addresses is prohibited. The reserved addresses are provided for possible future expansion of functions. Do not access these addresses as the correct operation of the LSI is not guaranteed.

8. Differences between products

Before changing from one product to another, for example to a product with a different part number, confirm that the change will not lead to problems. The characteristics of a microprocessing unit or microcontroller unit products in the same group but having a different part number might differ in terms of internal memory capacity, layout pattern, and other factors, which can affect the ranges of electrical characteristics, such as characteristic values, operating margins, immunity to noise, and amount of radiated noise. When changing to a product with a different part number, implement a systemevaluation test for the given product.

Notice

- 1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
- Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other claims involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawings, charts, programs, algorithms, and application examples.
- 3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 4. You shall be responsible for determining what licenses are required from any third parties, and obtaining such licenses for the lawful import, export, manufacture, sales, utilization, distribution or other disposal of any products incorporating Renesas Electronics products, if required.
- 5. You shall not alter, modify, copy, or reverse engineer any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copying or reverse engineering.
- 6. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; industrial robots; etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Unless expressly designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not intended or authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems; surgical implantations; etc.), or may cause serious property damage (space system; undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or any third parties arising from the use of any Renesas Electronics product that is inconsistent with any Renesas Electronics data sheet, user's manual or other Renesas Electronics document.

- 7. No semiconductor product is absolutely secure. Notwithstanding any security measures or features that may be implemented in Renesas Electronics hardware or software products, Renesas Electronics shall have absolutely no liability arising out of any vulnerability or security breach, including but not limited to any unauthorized access to or use of a Renesas Electronics product or a system that uses a Renesas Electronics product. RENESAS ELECTRONICS DOES NOT WARRANT OR GUARANTEE THAT RENESAS ELECTRONICS PRODUCTS, OR ANY SYSTEMS CREATED USING RENESAS ELECTRONICS PRODUCTS WILL BE INVULNERABLE OR FREE FROM CORRUPTION, ATTACK, VIRUSES, INTERFERENCE, HACKING, DATA LOSS OR THEFT, OR OTHER SECURITY INTRUSION ("Vulnerability Issues"). RENESAS ELECTRONICS DISCLAIMS ANY AND ALL RESPONSIBILITY OR LIABILITY ARISING FROM OR RELATED TO ANY VULNERABILITY ISSUES. FURTHERMORE, TO THE EXTENT PERMITTED BY APPLICABLE LAW, RENESAS ELECTRONICS DISCLAIMS ANY AND ALL WARRANTIES, EXPRESS OR IMPLIED, WITH RESPECT TO THIS DOCUMENT AND ANY RELATED OR ACCOMPANYING SOFTWARE OR HARDWARE, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY, OR FITNESS FOR A PARTICULAR PURPOSE.
- 8. When using Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat dissipation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions, failure or accident arising out of the use of Renesas Electronics products outside of such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics, such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Unless designated as a high reliability product or a product for harsh environments in a Renesas Electronics data sheet or other Renesas Electronics document, Renesas Electronics products are not subject to radiation resistance design. You are responsible for implementing safety measures to guard against the possibility of bodily injury, injury or damage caused by fire, and/or danger to the public in the event of a failure or malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult and impractical, you are responsible for evaluating the safety of the final products or systems manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. You are responsible for carefully and sufficiently investigating applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive, and using Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall comply with any applicable export control laws and regulations promulgated and administered by the governments of any countries asserting jurisdiction over the parties or transactions.
- 12. It is the responsibility of the buyer or distributor of Renesas Electronics products, or any other party who distributes, disposes of, or otherwise sells or transfers the product to a third party, to notify such third party in advance of the contents and conditions set forth in this document.
- 13. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 14. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its directly or indirectly controlled subsidiaries.
- (Note2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.5.0-1 October 2020)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu, Koto-ku, Tokyo 135-0061, Japan

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit: www.renesas.com/contact/

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.