

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Not recommended
for new design

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

M52790SP/FP

AV Switch with I²C Bus Control

REJ03F0187-0201
Rev.2.01
Mar 31, 2008

Description

The M52790 is AV switch semiconductor integrated circuit with I²C bus control.

This IC contains 2-channels of 4-input audio switches and 2-channels of 4-input video switches. Each channel can be controlled independently.

The video switches contain amplifiers can be controlled a gain of output 0 dB or 6 dB.

Features

- Video and stereo sound switches in one package
- Wide frequency range (video switch): DC to 20 MHz
- High separation (video switch): Crosstalk -60 dB (Typ) at 1 MHz
- Two types of packages are provided: SDIP with a lead pitch of 1.778 mm (M52790SP); and SSOP with a lead pitch of 0.8 mm (M52790FP).

Application

Video equipment

Recommended Operating Condition


Supply voltage: 4.7 V to 9.3 V

Rated supply voltage: 5 V, 9 V


Maximum output current: 63 mA (at 9 V)

Not recommended
for new design







Block Diagram



Pin Arrangement




Pin Description

Pin No.	Name	Peripheral Circuit Pins	DC Voltage (V)	Remarks
1	V _{CC}	—	9 V	5 to 9 V
2 6 7 11 12 16 32 36	VIDEO 2 IN Y 2 IN VIDEO 3 IN Y 3 IN VIDEO 4 IN Y 4 IN Y IN TUNER IN		3.6 V	Clamp in
3 5 8 10 13 15 33 35	Lch 2 IN Rch 2 IN Lch 3 IN Rch 3 IN Lch 4 IN Rch 4 IN Rch T IN Lch T IN		4.7 V	
4 9 14 34	C 2 IN C 3 IN C 4 IN C IN		4.7 V	
17	SCL		V _{IL} max = 1.5 V V _{IH} min = 3.0 V	
18	SDA		V _{IL} max = 1.5 V V _{IH} min = 3.0 V V _{OL} max = 0.4 V	At I _{lin} = 3 mA
19	GND	—	—	
20	CHIP SELECT		SLAVE ADDRESS 0 to 1.5 V: 90H 2.5 to V _{CC} : 92H OPEN: 90H	

Pin No.	Name	Peripheral Circuit Pins	DC Voltage (V)	Remarks
21	BIAS		4.2 V	
22 26 27 31	Y 2 OUT V 2 OUT Y 1 OUT V 1 OUT		SYNC CHIP DC = 2.9 V	
24 29	C 2 OUT C 1 OUT		4.0 V	
23 25 28 30	Rch 2 OUT Lch 2 OUT Rch 1 OUT Lch 1 OUT		4.0 V	

I²C Bus


I²C Bus (Inter IC Bus) is multi master bus system developed by PHILIPS. Two wires (SDA-serial data, SCL-serial clock) realize functions of start, stop, transferring data, synchronization and arbitration. The output stages of device connected to the bus must have an open drain or open collector in order to perform the wired-AND function.



Every byte put on the SDA line must be 8-bits long. Each byte has to be followed by an acknowledge bit. Data is transferred with the most significant bit (MSB) first. The data on the SDA line must be stable during the HIGH period of the clock. The HIGH or LOW state of the data line can only change when the clock signal on the SCL line is LOW.

Control

This IC controls 2-channel switches with 2-byte data (DATA1 and DATA2). SW1 is controlled by DATA1. SW2 is controlled by DATA2.



Data Byte Format

M52790 FUNCTION TABLE

S	SLAVE ADDRESS	A	DATA (D7 to D0)	A	DATA (DF to D8)	A	P
---	---------------	---	-----------------	---	-----------------	---	---

SLAVE ADDRESS

SLAVE ADDRESS	A6	A5	A4	A3	A2	A1	A0	R/W
	1	0	0	1	0	0	0/1	0

DATA1 (D7 to D0) CONT

DATA CONT	D7	D6	D5	D4	D3	D2	D1	D0
	AUDIO MODE1		—	Y/C AMP1	V AMP1	S/N	SW1 CONT	

VIDEO SW1 CONT

DATA			OUT		
S/N (S:1)	V-SW1		V OUT1	Y OUT1	C OUT1
D2	D1	D0			
0	0	0	T IN	Y IN	C IN
0	0	1	V 2 IN	Y IN	C IN
0	1	0	V 3 IN	Y IN	C IN
0	1	1	V 4 IN	Y IN	C IN
1	0	0	Y/C MIX T	Y IN	C IN
1	0	1	Y/C MIX 2	Y 2 IN	C 2 IN
1	1	0	Y/C MIX 3	Y 3 IN	C 3 IN
1	1	1	Y/C MIX 4	Y 4 IN	C 4 IN

AMP1 GAIN CONT

DATA	AMP	DATA	AMP
D4	YC AMP1	D3	V AMP1
0	0 dB	0	0 dB
1	6 dB	1	6 dB

AUDIO MODE1 CONT

DATA		MODE
D7	D6	
0	0	MUTE
0	1	R/R
1	0	L/L
1	1	NORMAL

AUDIO SW1 CONT

MODE		MUTE		R/R		L/L		NORMAL	
DATA		OUT		OUT		OUT		OUT	
D1	D0	Lch OUT 1	Rch OUT 1	Lch OUT 1	Rch OUT 1	Lch OUT 1	Rch OUT 1	Lch OUT 1	Rch OUT 1
0	0	MUTE	MUTE	Rch T IN	Rch T IN	Lch T IN	Lch T IN	Lch T IN	Rch T IN
0	1	MUTE	MUTE	Rch 2 IN	Rch 2 IN	Lch 2 IN	Lch 2 IN	Lch 2 IN	Rch 2 IN
1	0	MUTE	MUTE	Rch 3 IN	Rch 3 IN	Lch 3 IN	Lch 3 IN	Lch 3 IN	Rch 3 IN
1	1	MUTE	MUTE	Rch 4 IN	Rch 4 IN	Lch 4 IN	Lch 4 IN	Lch 4 IN	Rch 4 IN

DATA2 (DF to D8) CONT

DATA CONT	DF	DE	DD	DC	DB	DA	D9	D8
	AUDIO MODE2		—	Y/C AMP2	V AMP2	S/N	SW2 CONT	

VIDEO SW2 CONT

DATA			OUT		
S/N (S:1)	V-SW2		V OUT2	Y OUT2	C OUT2
DA	D9	D8			
0	0	0	T IN	Y IN	C IN
0	0	1	V 2 IN	Y 2 IN	C 2 IN
0	1	0	V 3 IN	Y 3 IN	C 3 IN
0	1	1	V 4 IN	Y 4 IN	C 4 IN
1	0	0	Y/C MIX T	Y IN	C IN
1	0	1	Y/C MIX 2	Y 2 IN	C 2 IN
1	1	0	Y/C MIX 3	Y 3 IN	C 3 IN
1	1	1	Y/C MIX 4	Y 4 IN	C 4 IN

AMP2 GAIN CONT

DATA	AMP	DATA	AMP
DC	Y/C AMP2	DB	V AMP2
0	0 dB	0	0 dB
1	6 dB	1	6 dB

AUDIO MODE2 CONT

DATA		MODE
DF	DE	
0	0	MUTE
0	1	R/R
1	0	L/L
1	1	NORMAL

AUDIO SW2 CONT

MODE		MUTE		R/R		L/L		NORMAL	
DATA		OUT		OUT		OUT		OUT	
D9	D8	Lch OUT 2	Rch OUT 2	Lch OUT 2	Rch OUT 2	Lch OUT 2	Rch OUT 2	Lch OUT 2	Rch OUT 2
0	0	MUTE	MUTE	Rch T IN	Rch T IN	Lch T IN	Lch T IN	Lch T IN	Rch T IN
0	1	MUTE	MUTE	Rch 2 IN	Rch 2 IN	Lch 2 IN	Lch 2 IN	Lch 2 IN	Rch 2 IN
1	0	MUTE	MUTE	Rch 3 IN	Rch 3 IN	Lch 3 IN	Lch 3 IN	Lch 3 IN	Rch 3 IN
1	1	MUTE	MUTE	Rch 4 IN	Rch 4 IN	Lch 4 IN	Lch 4 IN	Lch 4 IN	Rch 4 IN

Electrical Characteristics

(Ta = 25°C, V_{CC} = 9 V, unless otherwise noted)


Item	Symbol	Min	Typ	Max	Unit	Test Condition
Supply voltage	V _{CC}	4.7	—	9.3	V	
Circuit current	I _{CC}	—	63	83	mA	V _{CC} = 9 V, V _{in} = 0 Vp-p, R _I = ∞Ω
		—	54	71		V _{CC} = 5 V, V _{in} = 0 Vp-p, R _I = ∞Ω
Video						
Voltage gain	G	-0.5	0	0.5	dB	f = 100 kHz, 1 Vp-p (0 dB) (T→V _{1OUT})
		5.5	6	6.5		f = 100 kHz, 1 Vp-p (6 dB) (T→V _{1OUT})
		-0.5	0	0.5		f = 100 kHz, 1 Vp-p (0 dB) (Y→V _{1OUT})
		5.5	6	6.5		f = 100 kHz, 1 Vp-p (6 dB) (Y→V _{1OUT})
Frequency characteristics	F	-2.0	0	2.0	dB	f = 10 MHz/100 kHz, 1 Vp-p (0 dB) (T→V _{1OUT})
		-2.0	0	2.0		f = 10 MHz/100 kHz, 1 Vp-p (6 dB) (T→V _{1OUT})
		-2.0	0	2.0		f = 10 MHz/100 kHz, 1 Vp-p (0 dB) (Y→V _{1OUT})
		-2.0	0	2.0		f = 10 MHz/100 kHz, 1 Vp-p (6 dB) (Y→V _{1OUT})
Dynamic Range	D	4	—	—	Vp-p	V _{CC} = 9 V (0 dB) (T→V _{1OUT})
		2	—	—		V _{CC} = 5 V (0 dB) (T→V _{1OUT})
		4	—	—		V _{CC} = 9 V (0 dB) (Y→V _{1OUT})
		2	—	—		V _{CC} = 5 V (0 dB) (Y→V _{1OUT})
Input impedance	Z _{IC}	14	20	26	kΩ	(C ₁ , C ₂ , C ₃ , C ₄)
	Z _{IV}	—	—	—		Clamp in (T, V ₂ , V ₃ , V ₄)
	Z _{IY}	—	—	—		Clamp in (Y, Y ₂ , Y ₃ , Y ₄)
Crosstalk	CT	—	-60	-54	dB	f = 1 MHz, 1 Vp-p T→V _{1OUT} (at V ₂ mode)
Audio						
Voltage gain	G	-0.5	0	0.5	dB	f = 1 kHz, 1 Vp-p (V _{CC} 9 V) (R _T →R _{1OUT})
		-0.5	0	0.5		f = 1 kHz, 1 Vp-p (V _{CC} 5 V) (R _T →R _{1OUT})
Frequency characteristics	F	-2.0	0	1	dB	f = 100 kHz/1 kHz, 1 Vp-p (R _T →R _{1OUT})
Total harmonic distortion	THD	—	0.01	0.05	%	f = 1 kHz, 2 Vp-p, at 400 Hz HPE + 30 kHz LPF (R _T →R _{1OUT})
Dynamic Range	D	5.5	6.0	—	Vp-p	f = 1 kHz, Maximum with distortion < 0.5% (R _T →R _{1OUT})
Output DC offset voltage	V _{OFF}	-20	0	20	mV	(MODE: R _T , R ₂ , R ₃ , R ₄ →R _{1OUT})
Input impedance	Z _I	22	30	38	kΩ	(R _T , R ₂ , R ₃ , R ₄ , L _T , L ₂ , L ₃ , L ₄)
Crosstalk	CT	—	-90	-84	dB	1 kHz, 1 Vp-p R _T →R _{1OUT} (at R ₂ mode)
I ² C Bus control signal						
Max. input high voltage	V _{IH}	3.0	—	5.0	V	SDA = 3 mA
Min. input low voltage	V _{IL}	0.0	—	1.5		
Low level output voltage (SDA)	V _{OL}	0.0	—	0.4		
High level input current	I _{IH}	-10	—	10	μA	SDA, SCL = 4.5 V
Low level input current	I _{IL}	-10	—	10		SDA, SCL = 0.4 V
SCL clock frequency	f _{SCL}	0.0	—	100	kHz	
Time of bus must be free before a new transmission can start	t _{BUF}	4.7	—	—	μs	
Hold time at start condition	t _{HD;STA}	4.0	—	—		
The low period of the clock	t _{LOW}	4.7	—	—		
The high period of the clock	t _{HIGH}	4.0	—	—		
Step-up time for start condition	t _{SU;STA}	4.7	—	—		

Electrical Characteristics (cont.)

(Ta = 25°C, VCC = 9 V, unless otherwise noted)


Item	Symbol	Min	Typ	Max	Unit	Test Condition
Hold time DATA	t _{HD;DAT}	5.0	—	—	ns	
Setup time DATA	t _{SU;DAT}	250	—	—		
Rise time of both SDA and SCL line	t _R	—	—	1000		
Fall time of both SDA and SCL line	t _F	—	—	300		
Setup time for stop condition	t _{SU;STO}	4.0	—	—	μs	

I²C Bus Control Signal



Not recommended for new design

Application Circuit Example



Note How To Use This IC

- Input signal with sufficient low impedance to input terminal.
- The capacitance of output terminal as small as possible.
- Set the capacitance between V_{CC} and GND near the pins if possible.
- Assign an area as large as possible for grounding.

Power-on Reset



- The M52790 has an internal power-on reset function that sets each control register to "0" during IC power ON.
- The power-on reset VTH has 2.5 V.

Not recommend
for new design

Package Dimensions

36P4E

Plastic 36pin 500mil SDIP



Notes:

1. This document is provided for reference purposes only so that Renesas customers may select the appropriate Renesas products for their use. Renesas neither makes warranties or representations with respect to the accuracy or completeness of the information contained in this document nor grants any license to any intellectual property rights or any other rights of Renesas or any third party with respect to the information in this document.
2. Renesas shall have no liability for damages or infringement of any intellectual property or other rights arising out of the use of any information in this document, including, but not limited to, product data, diagrams, charts, programs, algorithms, and application circuit examples.
3. You should not use the products or the technology described in this document for the purpose of military applications such as the development of weapons of mass destruction or for the purpose of any other military use. When exporting the products or technology described herein, you should follow the applicable export control laws and regulations, and procedures required by such laws and regulations.
4. All information included in this document such as product data, diagrams, charts, programs, algorithms, and application circuit examples, is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas products listed in this document, please confirm the latest product information with a Renesas sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas such as that disclosed through our website. (<http://www.renesas.com>)
5. Renesas has used reasonable care in compiling the information included in this document, but Renesas assumes no liability whatsoever for any damages incurred as a result of errors or omissions in the information included in this document.
6. When using or otherwise relying on the information in this document, you should evaluate the information in light of the total system before deciding about the applicability of such information to the intended application. Renesas makes no representations, warranties or guarantees regarding the suitability of its products for any particular application and specifically disclaims any liability arising out of the application and use of the information in this document or Renesas products.
7. With the exception of products specified by Renesas as suitable for automobile applications, Renesas products are not designed, manufactured or tested for applications or otherwise in systems the failure or malfunction of which may cause a direct threat to human life or create a risk of human injury or which require especially high quality and reliability such as safety systems, or equipment or systems for transportation and traffic, healthcare, combustion control, aerospace and aeronautics, nuclear power, or undersea communication transmission. If you are considering the use of our products for such purposes, please contact a Renesas sales office beforehand. Renesas shall have no liability for damages arising out of the uses set forth above.
8. Notwithstanding the preceding paragraph, you should not use Renesas products for the purposes listed below:
 - (1) artificial life support devices or systems
 - (2) surgical implantations
 - (3) healthcare intervention (e.g., excision, administration of medication, etc.)
 - (4) any other purposes that pose a direct threat to human lifeRenesas shall have no liability for damages arising out of the uses set forth in the above and purchasers who elect to use Renesas products in any of the foregoing applications shall indemnify and hold harmless Renesas Technology Corp., its affiliated companies and their officers, directors, and employees against any and all damages arising out of such applications.
9. You should use the products described herein within the range specified by Renesas, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas shall have no liability for malfunctions or damages arising out of the use of Renesas products beyond such specified ranges.
10. Although Renesas endeavors to improve the quality and reliability of its products, IC products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Please be sure to implement safety measures to guard against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other applicable measures. Among others, since the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
11. In case Renesas products listed in this document are detached from the products to which the Renesas products are attached or affixed, the risk of accident such as swallowing by infants and small children is very high. You should implement safety measures so that Renesas products may not be easily detached from your products. Renesas shall have no liability for damages arising out of such detachment.
12. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written approval from Renesas.
13. Please contact a Renesas sales office if you have any questions regarding the information contained in this document, Renesas semiconductor products, or if you have any other inquiries.



RENEASAS SALES OFFICES

<http://www.renesas.com>

Refer to "<http://www.renesas.com/en/network>" for the latest and detailed information.

Renesas Technology America, Inc.
450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500, Fax: <1> (408) 382-7501

Renesas Technology Europe Limited
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.
Tel: <44> (1628) 585-100, Fax: <44> (1628) 585-900

Renesas Technology (Shanghai) Co., Ltd.
Unit 204, 205, AZIACenter, No.1233 Lujiazui Ring Rd, Pudong District, Shanghai, China 200120
Tel: <86> (21) 5877-1818, Fax: <86> (21) 6887-7858/7898

Renesas Technology Hong Kong Ltd.
7th Floor, North Tower, World Finance Centre, Harbour City, Canton Road, Tsimshatsui, Kowloon, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2377-3473

Renesas Technology Taiwan Co., Ltd.
10th Floor, No.99, Fushing North Road, Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 3518-3399

Renesas Technology Singapore Pte. Ltd.
1 Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001

Renesas Technology Korea Co., Ltd.
Kukje Center Bldg. 18th Fl., 191, 2-ka, Hangang-ro, Yongsan-ku, Seoul 140-702, Korea
Tel: <82> (2) 796-3115, Fax: <82> (2) 796-2145

Renesas Technology Malaysia Sdn. Bhd
Unit 906, Block B, Menara Amcorp, Amcorp Trade Centre, No.18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia
Tel: <603> 7955-9390, Fax: <603> 7955-9510