

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

## C to X BAND AMPLIFIER

## C to X BAND OSC

## N-CHANNEL GaAs MES FET

### FEATURES

- High Power Gain:  $G_s = 5.5$  dB TYP. @  $f = 12$  GHz
- Gate Length:  $L_g = 0.8 \mu\text{m}$  (recessed gate)
- Gate Width:  $W_g = 330 \mu\text{m}$
- 4 pins super mini mold
- Tape & reel packaging only available


### ORDERING INFORMATION

PART NUMBER	QUANTITY	PACKING STYLE
NE72118-T1	3 Kpcs/Reel.	Embossed tape 8 mm wide. Pin 3 (Source), Pin 4 (Drain) face to perforation side of the tape.
NE72118-T2	3 Kpcs/Reel.	Embossed tape 8 mm wide. Pin 1 (Source), Pin 2 (Gate) face to perforation side of the tape.

\* Please contact with responsible NEC person, if you require evaluation sample. Unit sample quantity shall be 50 pcs. (Part No.: NE72118)

### ABSOLUTE MAXIMUM RATINGS ( $T_A = 25^\circ\text{C}$ )

Drain to Source Voltage	$V_{DS}$	5.0	V
Gate to Source Voltage	$V_{GS}$	-6.0	V
Gate to Drain Voltage	$V_{GD}$	-6.0	V
Drain Current	$I_D$	$I_{DSS}$	mA
Total Power Dissipation	$P_{tot}$	250	mW
Channel Temperature	$T_{ch}$	125	$^\circ\text{C}$
Storage Temperature	$T_{stg}$	-65 to +125	$^\circ\text{C}$



The information in this document is subject to change without notice.




**ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25 °C)**

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITIONS
Gate to Source Leak Current	I <sub>gso</sub>		1.0	10	μA	V <sub>GS</sub> = -5 V
Saturated Drain Current	I <sub>DSS</sub>	30	60	100	mA	V <sub>DS</sub> = 3 V, V <sub>GS</sub> = 0 V
Gate to Source Cut off Voltage	V <sub>GS (off)</sub>	-0.5	-2.0	-4.0	V	V <sub>DS</sub> = 3 V, I <sub>D</sub> = 100 μA
Transconductance	g <sub>m</sub>	20	40		mS	V <sub>DS</sub> = 3 V, I <sub>D</sub> = 30 mA
Phase Noise	PN		-110		dBc/Hz	V <sub>DS</sub> = 3 V, I <sub>D</sub> = 30 mA f = 11 GHz 100 kHz offset
			-85		dBc/Hz	V <sub>DS</sub> = 3 V, I <sub>D</sub> = 30 mA f = 11 GHz 10 kHz offset
Power Gain	G <sub>s</sub>		5.5		dB	V <sub>DS</sub> = 3 V, I <sub>D</sub> = 30 mA f = 12 GHz
Output Power at 1 dB Gain Compression point	P <sub>o</sub> (1 dB)		13.5		dBm	V <sub>DS</sub> = 3 V, I <sub>D</sub> = 30 mA f = 12 GHz

**I<sub>DSS</sub> CLASSIFICATION**

Rank	I <sub>DSS</sub> (mA)	MARKING
53	30 to 100	V53
54	55 to 100	V54
55	30 to 65	V55

TYPICAL CHARACTERISTICS (T<sub>A</sub> = 25 °C)



**S-PARAMETER**

MAG. AND ANG.

 $V_{DS} = 3\text{ V}$ ,  $I_D = 10\text{ mA}$ 

FREQUENCY MHz	S <sub>11</sub>		S <sub>21</sub>		S <sub>12</sub>		S <sub>22</sub>	
	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)
2000	.922	-46.8	2.257	134.5	.067	58.5	.667	-27.5
3000	.864	-66.8	2.171	116.4	.089	47.7	.627	-39.0
4000	.784	-89.8	2.125	97.4	.104	37.0	.591	-49.5
5000	.709	-116.1	2.049	77.5	.110	25.3	.545	-58.9
6000	.658	-140.5	1.927	58.5	.107	17.8	.481	-68.0
7000	.623	-164.0	1.780	40.2	.101	13.2	.416	-80.0
8000	.597	171.4	1.639	23.3	.095	12.7	.358	-92.8
9000	.613	146.3	1.545	6.5	.100	16.8	.323	-109.6
10000	.677	125.6	1.450	-12.0	.117	16.3	.284	-137.3
11000	.749	107.4	1.297	-31.1	.136	10.0	.251	-178.5
12000	.797	90.8	1.117	-48.8	.147	1.6	.295	138.4
13000	.839	78.4	.959	-65.1	.159	-8.4	.395	107.9
14000	.877	65.7	.811	-82.3	.164	-20.8	.499	85.8
15000	.909	51.9	.636	-99.1	.157	-33.1	.577	68.3
16000	.934	43.9	.483	-111.1	.145	-42.7	.643	54.4
17000	.928	40.2	.376	-118.6	.136	-49.3	.733	44.4
18000	.920	31.7	.306	-125.6	.126	-55.8	.795	39.5

## AMP. PARAMETER

 $V_{DS} = 3\text{ V}$ ,  $I_D = 10\text{ mA}$ 

FREQUENCY MHz	GUmax dB	GAmax dB	$ S_{21} ^2$ dB	$ S_{12} ^2$ dB	K	Delay ns	Mason's U dB	G1 dB	G2 dB
2000	17.86		7.07	-23.49	.38	.064	20.787	8.24	2.55
3000	14.86		6.73	-21.05	.50	.050	19.443	5.96	2.17
4000	12.57		6.55	-19.62	.65	.053	18.058	4.15	1.87
5000	10.79		6.23	-19.14	.83	.055	15.937	3.03	1.53
6000	9.31	10.84	5.70	-19.42	1.08	.053	14.113	2.47	1.14
7000	7.97	8.79	5.01	-19.89	1.38	.051	12.135	2.13	.82
8000	6.80	7.42	4.29	-20.44	1.72	.047	10.166	1.91	.59
9000	6.30	7.03	3.78	-20.03	1.70	.047	9.776	2.05	.48
10000	6.25	7.31	3.23	-18.62	1.37	.051	10.424	2.66	.36
11000	6.11	7.58	2.26	-17.30	1.13	.053	10.310	3.57	.28
12000	5.73	7.19	.96	-16.63	1.07	.049	8.722	4.37	.40
13000	5.67		-.36	-15.96	.95	.045	8.001	5.29	.74
14000	5.79		-1.81	-15.68	.83	.048	7.689	6.36	1.25
15000	5.42		-3.93	-16.07	.79	.047	6.575	7.60	1.76
16000	4.97		-6.32	-16.75	.75	.033	5.777	8.97	2.32
17000	3.43		-8.49	-17.35	.86	.021	3.808	8.58	3.35
18000	2.18		-10.29	-18.02	.97	.019	2.340	8.12	4.35

**S-PARAMETER**

MAG. AND ANG.

 $V_{DS} = 3\text{ V}$ ,  $I_D = 20\text{ mA}$ 

FREQUENCY MHz	S <sub>11</sub>		S <sub>21</sub>		S <sub>12</sub>		S <sub>22</sub>	
	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)
2000	.907	-49.0	2.672	133.0	.061	58.3	.637	-27.5
3000	.838	-69.9	2.534	114.7	.081	48.6	.594	-38.8
4000	.752	-93.4	2.437	95.8	.093	38.1	.561	-48.8
5000	.675	-120.3	2.318	76.0	.098	29.5	.521	-57.4
6000	.627	-144.7	2.155	57.5	.096	24.3	.459	-65.3
7000	.591	-168.0	1.972	39.6	.095	21.6	.394	-76.3
8000	.570	167.6	1.803	23.2	.093	22.7	.337	-88.8
9000	.592	143.3	1.695	7.0	.104	24.6	.307	-104.8
10000	.666	123.6	1.594	-11.0	.125	22.4	.269	-132.2
11000	.742	105.8	1.429	-29.9	.144	13.7	.226	-173.8
12000	.794	89.6	1.239	-47.1	.157	4.7	.260	139.7
13000	.838	77.7	1.073	-63.6	.168	-5.6	.365	107.7
14000	.880	65.3	.913	-81.1	.173	-18.0	.476	85.9
15000	.914	51.1	.723	-98.1	.166	-31.7	.552	69.2
16000	.939	43.3	.552	-110.5	.153	-40.2	.617	55.1
17000	.935	39.5	.431	-118.9	.141	-48.1	.707	44.5
18000	.920	30.8	.350	-124.9	.134	-57.2	.788	39.6

**AMP. PARAMETER** $V_{DS} = 3\text{ V}$ ,  $I_D = 20\text{ mA}$ 

FREQUENCY MHz	GUmax dB	GAmax dB	$ S_{21} ^2$ dB	$ S_{12} ^2$ dB	K	Delay ns	Mason's U dB	G1 dB	G2 dB
2000	18.30		8.54	-24.33	.43	.066	21.197	7.50	2.26
3000	15.23		8.08	-21.88	.56	.051	20.047	5.26	1.89
4000	13.00		7.74	-20.59	.72	.053	18.259	3.62	1.64
5000	11.31		7.30	-20.15	.91	.055	17.087	2.64	1.37
6000	9.86	11.13	6.67	-20.33	1.15	.052	15.173	2.16	1.03
7000	8.50	9.29	5.90	-20.45	1.43	.050	12.982	1.87	.73
8000	7.35	7.97	5.12	-20.68	1.72	.046	10.881	1.71	.52
9000	6.89	7.66	4.58	-19.67	1.58	.045	10.644	1.88	.43
10000	6.93	8.19	4.05	-18.06	1.23	.050	11.553	2.55	.33
11000	6.80	8.85	3.10	-16.81	1.03	.052	11.430	3.48	.23
12000	6.49		1.86	-16.10	.98	.048	9.746	4.32	.30
13000	6.50		.61	-15.51	.89	.046	8.869	5.27	.62
14000	6.78		-.79	-15.25	.77	.049	8.507	6.45	1.12
15000	6.60		-2.82	-15.57	.71	.047	7.889	7.84	1.58
16000	6.17		-5.16	-16.30	.68	.034	6.643	9.25	2.08
17000	4.73		-7.30	-17.01	.76	.023	4.987	9.02	3.01
18000	3.20		-9.13	-17.44	.86	.017	3.626	8.12	4.21

**S-PARAMETER**

MAG. AND ANG.

 $V_{DS} = 3\text{ V}$ ,  $I_D = 30\text{ mA}$ 

FREQUENCY MHz	S <sub>11</sub>		S <sub>21</sub>		S <sub>12</sub>		S <sub>22</sub>	
	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)
2000	.900	-50.1	2.906	132.3	.058	58.4	.640	-27.1
3000	.826	-71.2	2.733	114.0	.074	49.0	.596	-38.2
4000	.734	-94.9	2.611	95.2	.086	39.8	.563	-47.6
5000	.657	-121.9	2.466	75.7	.088	32.6	.524	-55.7
6000	.609	-146.2	2.286	57.4	.089	28.1	.468	-63.2
7000	.577	-169.5	2.084	39.8	.089	27.6	.407	-74.0
8000	.558	166.5	1.899	23.7	.091	30.1	.354	-85.7
9000	.581	142.6	1.789	7.8	.104	31.9	.323	-101.4
10000	.659	123.3	1.688	-10.0	.130	27.7	.285	-127.2
11000	.739	105.9	1.522	-28.8	.152	18.4	.238	-167.1
12000	.794	89.9	1.324	-46.2	.164	8.5	.260	145.9
13000	.840	77.8	1.150	-62.6	.177	-2.9	.359	112.2
14000	.888	65.3	.983	-80.4	.183	-16.4	.469	89.2
15000	.923	51.2	.781	-97.6	.175	-29.8	.549	71.6
16000	.944	43.3	.596	-110.4	.157	-39.7	.621	56.4
17000	.941	39.4	.465	-119.0	.147	-47.1	.712	45.5
18000	.922	30.8	.374	-125.9	.136	-54.5	.787	40.0

## AMP. PARAMETER

 $V_{DS} = 3\text{ V}$ ,  $I_D = 30\text{ mA}$ 

FREQUENCY MHz	GUmax dB	GAmax dB	$ S_{21} ^2$ dB	$ S_{12} ^2$ dB	K	Delay ns	Mason's U dB	G1 dB	G2 dB
2000	18.76		9.27	-24.80	.44	.066	21.824	7.21	2.29
3000	15.62		8.73	-22.58	.59	.051	20.429	4.98	1.91
4000	13.35		8.33	-21.27	.76	.052	18.846	3.36	1.66
5000	11.69		7.84	-21.06	.96	.054	17.616	2.46	1.39
6000	10.27	11.46	7.18	-21.00	1.19	.051	15.786	2.01	1.07
7000	8.92	9.76	6.38	-20.98	1.44	.049	13.691	1.76	.79
8000	7.77	8.46	5.57	-20.83	1.66	.045	11.556	1.62	.58
9000	7.32	8.17	5.05	-19.67	1.50	.044	11.175	1.79	.48
10000	7.39	9.05	4.55	-17.71	1.12	.050	12.450	2.47	.37
11000	7.33		3.65	-16.34	.93	.052	12.431	3.43	.25
12000	7.06		2.43	-15.69	.89	.048	10.536	4.32	.30
13000	7.14		1.22	-15.03	.80	.046	9.718	5.32	.60
14000	7.67		-.15	-14.76	.68	.049	9.802	6.74	1.08
15000	7.68		-2.14	-15.14	.62	.048	9.075	8.27	1.56
16000	7.28		-4.49	-16.06	.60	.036	7.935	9.66	2.11
17000	5.80		-6.66	-16.65	.67	.024	6.011	9.39	3.07
18000	3.89		-8.55	-17.34	.82	.019	3.912	8.25	4.19

**S-PARAMETER**

MAG. AND ANG.

 $V_{DS} = 3\text{ V}$ ,  $I_D = 40\text{ mA}$ 

FREQUENCY MHz	S <sub>11</sub>		S <sub>21</sub>		S <sub>12</sub>		S <sub>22</sub>	
	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)	MAG.	ANG. (deg.)
2000	.894	-50.6	3.050	132.1	.053	59.6	.660	-26.6
3000	.817	-72.0	2.858	113.7	.068	49.2	.615	-37.0
4000	.725	-95.7	2.716	95.0	.078	41.5	.582	-46.0
5000	.647	-122.6	2.556	75.8	.080	33.7	.546	-53.7
6000	.600	-146.6	2.368	57.7	.079	34.1	.495	-61.2
7000	.569	-170.0	2.156	40.2	.082	34.0	.440	-71.7
8000	.550	166.1	1.968	24.2	.086	37.9	.394	-82.9
9000	.571	142.5	1.855	8.7	.104	40.5	.366	-97.4
10000	.653	123.9	1.760	-9.0	.134	35.6	.329	-121.7
11000	.737	106.6	1.602	-27.9	.159	24.5	.279	-158.0
12000	.799	90.5	1.398	-45.5	.176	13.2	.282	157.2
13000	.846	78.3	1.215	-62.3	.188	1.8	.368	120.6
14000	.895	65.9	1.045	-80.3	.195	-12.7	.477	95.3
15000	.931	51.6	.827	-98.1	.186	-26.9	.562	75.6
16000	.956	43.6	.630	-111.4	.169	-38.4	.635	59.3
17000	.949	39.4	.487	-120.5	.158	-47.0	.724	47.5
18000	.932	30.6	.386	-127.2	.144	-53.2	.792	41.7

**AMP. PARAMETER** $V_{DS} = 3\text{ V}$ ,  $I_D = 40\text{ mA}$ 

FREQUENCY MHz	GUmax dB	GAmax dB	$ S_{21} ^2$ dB	$ S_{12} ^2$ dB	K	Delay ns	Mason's U dB	G1 dB	G2 dB
2000	19.16		9.69	-25.51	.44	.067	23.057	6.99	2.48
3000	15.97		9.12	-23.33	.61	.051	20.581	4.78	2.07
4000	13.72		8.68	-22.19	.79	.052	19.425	3.24	1.80
5000	12.04	14.83	8.15	-21.92	1.00	.053	17.691	2.36	1.54
6000	10.65	11.83	7.49	-22.06	1.24	.050	16.421	1.94	1.22
7000	9.30	10.21	6.67	-21.73	1.45	.048	14.244	1.70	.93
8000	8.18	8.96	5.88	-21.34	1.63	.044	12.045	1.56	.73
9000	7.70	8.73	5.37	-19.70	1.41	.043	11.643	1.72	.62
10000	7.83	10.81	4.91	-17.44	1.00	.049	13.058	2.42	.50
11000	7.85		4.09	-15.98	.82	.053	13.349	3.41	.35
12000	7.69		2.91	-15.08	.76	.049	11.658	4.42	.36
13000	7.79		1.69	-14.50	.71	.047	10.225	5.46	.63
14000	8.52		.38	-14.19	.59	.050	10.481	7.01	1.12
15000	8.73		-1.65	-14.59	.53	.049	9.765	8.73	1.65
16000	8.84		-4.02	-15.44	.48	.037	9.669	10.61	2.24
17000	6.97		-6.25	-16.05	.53	.025	7.553	10.00	3.22
18000	4.84		-8.27	-16.84	.69	.019	4.828	8.83	4.28

**RECOMMENDED SOLDERING CONDITIONS**

The following conditions (see table below) must be met when soldering this product.

Please consult with our sales offices in case other soldering process is used, or in case soldering is done under different conditions.

**<TYPES OF SURFACE MOUNT DEVICE>**

For more details, refer to our document "SEMICONDUCTOR DEVICE MOUNTING TECHNOLOGY MANUAL" (C10535E).

Soldering process	Soldering conditions	Symbol
VPS	Package peak temperature: 215 °C, Time: 40 seconds MAX. (200 °C MIN.), Number of times: 2, Number of days: not limited*	VP15-00-2
Wave soldering	Soldering bath temperature: 260 °C MAX., Time: 10 seconds MAX., Number of times: 1, Number of days: not limited*	WS60-00-1
Infrared ray reflow	Peak package's surface temperature: 230 °C or below, Reflow time: 30 seconds or below (210 °C or higher), Number of reflow process: 2, Exposure limit*: None	IR30-00-2
Partial heating method	Terminal temperature: 230 °C or below, Flow time: 10 seconds or below, Exposure limit*: None	

\* Exposure limit before soldering after dry-pack package is opened.

Storage conditions: 25 °C and relative humidity at 65 % or less.

**Note** Do not apply more than a single process at once, except for "Partial heating method".

**PRECAUTION** Avoid high static voltage and electric fields, because this device is MES FET with GaAs shottky barrier gate.

[MEMO]

Discontinued Product

[MEMO]

Discontinued Product

[MEMO]

Discontinued Product

## Caution

**The Great Care must be taken in dealing with the devices in this guide.**

**The reason is that the material of the devices is GaAs (Gallium Arsenide), which is designated as harmful substance according to the law concerned.**

**Keep the law concerned and so on, especially in case of removal.**

No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Corporation. NEC Corporation assumes no responsibility for any errors which may appear in this document.

NEC Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Corporation or others.

While NEC Corporation has been making continuous effort to enhance the reliability of its semiconductor devices, the possibility of defects cannot be eliminated entirely. To minimize risks of damage or injury to persons or property arising from a defect in an NEC semiconductor device, customers must incorporate sufficient safety measures in its design, such as redundancy, fire-containment, and anti-failure features.

NEC devices are classified into the following three quality grades:

"Standard", "Special", and "Specific". The Specific quality grade applies only to devices developed based on a customer designated "quality assurance program" for a specific application. The recommended applications of a device depend on its quality grade, as indicated below. Customers must check the quality grade of each device before using it in a particular application.

Standard: Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots

Special: Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)

Specific: Aircrafts, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems or medical equipment for life support, etc.

The quality grade of NEC devices is "Standard" unless otherwise specified in NEC's Data Sheets or Data Books. If customers intend to use NEC devices for applications other than those specified for Standard quality grade, they should contact an NEC sales representative in advance.

Anti-radioactive design is not implemented in this product.