

To our customers,

---

## Old Company Name in Catalogs and Other Documents

---

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1<sup>st</sup>, 2010  
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

## Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

## IPOLAR ANALOG + DIGITAL INTEGRATED CIRCUIT

**Phase-out/Discontinued**

# μPB1007K

### REFERENCE FREQUENCY 16.368 MHz, 2nd IF FREQUENCY 4.092 MHz RF/IF FREQUENCY DOWN-CONVERTER + PLL FREQUENCY SYNTHESIZER IC FOR GPS RECEIVER

#### DESCRIPTION

The μPB1007K is a silicon monolithic integrated circuit for GPS receiver. This IC is designed as double conversion RF block integrated Pre-Amplifier + RF/IF down-converter + PLL frequency synthesizer on 1 chip.

This IC is lower current than the μPB1005K and packaged in a 36-pin QFN package.

This IC is manufactured using our 30 GHz  $f_{max}$  UHS0 (Ultra High Speed Process) silicon bipolar process.

#### FEATURES

- Double conversion :  $f_{REFin} = 16.368$  MHz,  $f_{1stIFin} = 61.380$  MHz,  $f_{2ndIFin} = 4.092$  MHz
- Integrated RF block : Pre-Amplifier + RF/IF frequency down-converter + PLL frequency synthesizer
- Needless to input counter data : fixed division internal prescaler
  - VCO side division :  $\div 200$  ( $\div 25$ ,  $\div 8$  serial prescaler)
  - Reference division :  $\div 2$
- Supply voltage :  $V_{CC} = 2.7$  to  $3.3$  V
- Low current consumption :  $I_{CC} = 25.0$  mA TYP. @  $V_{CC} = 3.0$  V
- Gain adjustable externally : Gain control voltage pin (control voltage up vs. gain down)
- On-chip pre-amplifier :  $G_P = 15.5$  dB TYP. @  $f = 1.57542$  GHz  
 $NF = 3.2$  dB TYP. @  $f = 1.57542$  GHz
- Power-save function : Power-save dark current  $I_{CC}(PD) = 5$  μA MAX.
- High-density surface mountable : 36-pin plastic QFN

#### APPLICATIONS

- Consumer use GPS receiver of reference frequency 16.368 MHz, 2nd IF frequency 4.092 MHz (for general use)

#### ORDERING INFORMATION

Part Number	Package	Supplying Form
μPB1007K-E1	36-pin plastic QFN	<ul style="list-style-type: none"> <li>• 12 mm wide embossed taping</li> <li>• Pin 1 indicates pull-out direction of tape</li> <li>• Qty 2.5 kpcs/reel</li> </ul>

**Remark** To order evaluation samples, contact your nearby sales office.

Part number for sample order: μPB1007K

**Caution Electro-static sensitive devices**

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.  
 Not all devices/types available in every country. Please check with local NEC Compound Semiconductor Devices representative for availability and additional information.

### PRODUCT LINE-UP ( $T_A = +25^{\circ}\text{C}$ , $V_{CC} = 3.0\text{ V}$ )


Type	Part Number	Functions (Frequency unit: MHz)	V <sub>CC</sub> (V)	I <sub>CC</sub> (mA)	CG (dB)	Package	Status
Clock Frequency Specific 1 chip IC	μPB1007K	Pre-amplifier + RF/IF down-converter + PLL synthesizer REF = 16.368 1stIF = 61.380/2ndIF = 4.092	2.7 to 3.3	25.0	100 to 120	36-pin plastic QFN	New Device
	μPB1005GS	RF/IF down-converter + PLL synthesizer	2.7 to 3.3	45.0	76 to 96	30-pin plastic SSOP	Available
	μPB1005K	REF = 16.368 1stIF = 61.380/2ndIF = 4.092				36-pin plastic QFN	

**Remark** Typical performance. Please refer to ELECTRICAL CHARACTERISTICS in detail.

To know the associated products, please refer to their latest data sheets.

## SYSTEM APPLICATION EXAMPLE


### GPS receiver RF block diagram



**Caution** This diagram schematically shows only the  $\mu$ PB1007K's internal functions on the system. This diagram does not present the actual application circuits.



PIN CONNECTION AND INTERNAL BLOCK DIAGRAM



Top View



PIN EXPLANATION

Pin No.	Pin Name	Applied Voltage (V)	Pin Voltage (V)	Function and Application	Internal Equivalent Circuit
1	Pre-AMP <sub>out</sub>	—	voltage as same as V <sub>CC</sub>	Output pin of Pre-amplifier. Output biasing and matching required as it is a open collector output.	
2	V <sub>CC</sub> (V <sub>reg</sub> )	2.7 to 3.3	—	Supply voltage pin of voltage regulator. This pin should be externally equipped with bypass capacitor to minimize ground impedance.	
3	GND(V <sub>reg</sub> )	0	—	Ground pin of voltage regulator.	
35	Pre-AMP <sub>in</sub>	—	0.79	Input pin of Pre-amplifier. LC matching circuit must be connected to this pin.	
36	GND(Pre-AMP)	0	—	Ground pin of Pre-amplifier.	
4	RF-MIX <sub>in</sub>	—	1.00	Input pin of RF mixer. 1 575.42 MHz band pass filter can be inserted between pin 1 and 4.	
5	GND(RF-MIX)	0	—	Ground pin of RF mixer.	
33	RF-MIX <sub>out</sub>	—	1.30	Output pin of RF mixer. 1st IF filter must be inserted between pin 31 and 33.	
34	V <sub>CC</sub> (RF-MIX)	2.7 to 3.3	—	Supply voltage pin of RF mixer. This pin should be externally equipped with bypass capacitor to minimize ground impedance.	
6	1stLO-OSC1	—	1.80	Pin 6 and 7 are each base pin of differential amplifier for 1st LO oscillator. These pins should be equipped with LC and varactor to oscillate on 1 636.80 MHz as VCO.	
7	1stLO-OSC2	—	1.80		
8	V <sub>CC</sub> (1stLO-OSC)	2.7 to 3.3	—	Supply voltage pin of differential amplifier for 1st LO oscillator circuit.	

Pin No.	Pin Name	Applied Voltage (V)	Pin Voltage (V)	Function and Application	Internal Equivalent Circuit			
9	V <sub>cc</sub> (PLL Block)	2.7 to 3.3	–	Supply voltage pin of PLL block. This pin should be externally equipped with bypass capacitor to minimize ground impedance.				
10	CP <sub>out</sub>	–	Output in accordance with phase difference.	Output pin of charge-pump. This pin should be equipped with external RC in order to adjust dumping factor and cut-off frequency. This tuning voltage output must be connected to varactor diode of 1stLO-OSC.				
11	GND(PLL Block)	0	–	Ground pin of PLL block.				
12	V <sub>cc</sub> (PLL Block)	2.7 to 3.3	–	Supply voltage pin of PLL block. This pin should be externally equipped with bypass capacitor to minimize ground impedance.				
13	LO <sub>out</sub>	–	1.85	Monitor pin of 1/200 prescaler output.				
14	REF <sub>out</sub> 2	–	1.68	Monitor pin of 1/2 prescaler output.				
15	Power Down1	0 or V <sub>cc</sub>	–	Stand-by mode control pin of Pre-amplifier block, 1stLO-OSC block, charge pump prescaler block, LO output amplifier, RF mixer, IF mixer, 2ndIF amplifier. <div><table><tr><td>Low</td><td>OFF</td></tr><tr><td>High</td><td>ON</td></tr></table></div>		Low	OFF	High
Low	OFF							
High	ON							

Pin No.	Pin Name	Applied Voltage (V)	Pin Voltage (V)	Function and Application	Internal Equivalent Circuit				
16	Power Down2	0 or V <sub>cc</sub>	—	Stand-by mode control pin of reference block. <table border="1"><tr><td>Low</td><td>OFF</td></tr><tr><td>High</td><td>ON</td></tr></table>	Low	OFF	High	ON	
Low	OFF								
High	ON								
17	REF <sub>out</sub> 1	—	—	Output pin of reference frequency. The frequency from pin 19 can be taken out as 3 V <sub>P-P</sub> swing.					
18	REF <sub>in</sub> 2	—	2.45	Input pin of reference frequency. This pin should be grounded through capacitor.					
19	REF <sub>in</sub> 1	—	2.45	Input pin of reference frequency. This pin can use as an input pin of reference frequency buffer. This pin should be equipped with external 16.368 MHz oscillator (example: TCXO).					
20	V <sub>cc</sub> (REF Block)	2.7 to 3.3	—	Supply voltage pin of reference block. This pin should be externally equipped with bypass capacitor to minimize ground impedance.					
21	GND(REF Block)	0	—	Ground pin of reference block.					
22	2ndIF <sub>out</sub>	—	1.80	Output pin of 2nd IF amplifier. This pin output 4.092 MHz. This pin should be equipped with external buffer amplifier to adjust level to next stage on user's system.					
23	V <sub>cc</sub> (2nd IF-AMP)	2.7 to 3.3	—	Supply voltage pin of 2nd IF amplifier. This pin should be externally equipped with bypass capacitor to minimize ground impedance.					
24	2ndIF <sub>bypass</sub>	—	2.10	Bypass pin of 2nd IF amplifier. This pin should be grounded through capacitor.					
25	2ndIF <sub>in</sub> 2	—	2.10	Pin of 2nd IF amplifier input 2. This pin should be grounded through capacitor.					
26	2ndIF <sub>in</sub> 1	—	2.10	Pin of 2nd IF amplifier input 1. 2nd IF filter can be inserted between 26 and 28.					
27	GND(2nd IF-AMP)	0	—	Ground pin of 2nd IF amplifier.					



Pin No.	Pin Name	Applied Voltage (V)	Pin Voltage (V)	Function and Application	Internal Equivalent Circuit
28	IF-MIX <sub>out</sub>	—	1.0	Output pin of IF mixer. IF mixer output signal goes through gain control amplifier before this emitter follower output port.	
29	V <sub>cc</sub> (IF-MIX)	2.7 to 3.3	—	Supply voltage pin of IF mixer. This pin should be externally equipped with bypass capacitor to minimize ground impedance.	
30	V <sub>gc</sub> (IF-MIX)	0 to 3.3	—	Gain control voltage pin of IF mixer output amplifier. This voltage performs forward control (V <sub>gc</sub> up → Gain down).	
31	IF-MIX <sub>in</sub>	—	1.97	Input pin of IF mixer.	
32	GND(IF-MIX)	0	—	Ground pin of IF mixer.	

**Caution** Ground pattern on the board must be formed as wide as possible to minimize ground impedance.

# ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Test Conditions	Ratings	Unit
Supply Voltage	V <sub>CC</sub>	T <sub>A</sub> = +25°C	3.6	V
Total Circuit Current	I <sub>CCTotal</sub>	T <sub>A</sub> = +25°C	100	mA
Power Dissipation	P <sub>D</sub>	T <sub>A</sub> = +85°C <b>Note</b>	360	mW
Operating Ambient Temperature	T <sub>A</sub>		−40 to +85	°C
Storage Temperature	T <sub>stg</sub>		−55 to +150	°C

**Note** Mounted on double-sided copper-clad 50 × 50 × 1.6 mm epoxy glass PWB

# RECOMMENDED OPERATING RANGE

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Supply Voltage	V <sub>CC</sub>	2.7	3.0	3.3	V
Operating Ambient Temperature	T <sub>A</sub>	−40	+25	+85	°C
RF Input Frequency	f <sub>RFin</sub>	—	1 575.42	—	MHz
1st LO Oscillating Frequency	f <sub>1stLOin</sub>	—	1 636.80	—	MHz
1st IF Input Frequency	f <sub>1stIFin</sub>	—	61.380	—	MHz
2nd LO Input Frequency	f <sub>2ndLOin</sub>	—	65.472	—	MHz
2nd IF Input Frequency	f <sub>2ndIFin</sub>	—	4.092	—	MHz
Reference Input/Output Frequency	f <sub>REFin</sub> f <sub>REFout</sub>	—	16.368	—	MHz
LO Output Frequency	f <sub>LOout</sub>	—	8.184	—	MHz

ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = +25°C, V<sub>CC</sub> = 3.0 V)

Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
Total Circuit Current	I <sub>CCTotal</sub>	All block operating @ PLL lock	19.0	25.0	35.0	mA
Power-save Dark Current	I <sub>CC(PD)</sub>	Pin 15 = Pin 16 = 0 V	–	–	5	μA
Reference Block Circuit Current	I <sub>CCREF</sub>	Pin 15 = 0 V, Pin 16 = 3 V	–	3	4	mA
Pre-amplifier Block (f <sub>RFIn</sub> = 1 575.42 MHz, Z <sub>S</sub> = Z <sub>L</sub> = 50 Ω)						
Circuit Current 1	I <sub>CC1</sub>	No Signals	1.65	2.50	3.50	mA
Power Gain	G <sub>P</sub>	Input/Output matching, P <sub>RFIn</sub> = –40 dBm	12.5	15.5	18.5	dB
Noise Figure	NF	Input/Output matching	–	3.2	4.0	dB
RF Down-converter Block (f <sub>RFIn</sub> = 1 575.42 MHz, f <sub>1stLOin</sub> = 1 636.80 MHz, P <sub>LOin</sub> = –10 dBm, Z <sub>S</sub> = Z <sub>L</sub> = 50 Ω)						
Circuit Current 2	I <sub>CC2</sub>	No Signals	5.2	7.0	9.9	mA
RF Conversion Gain	CG <sub>RF</sub>	P <sub>RFIn</sub> = –40 dBm	15.5	18.5	21.5	dB
RF-SSB Noise Figure	NF <sub>RF</sub>		–	10.5	13.5	dB
RF Saturated Output Power	P <sub>O(sat)RF</sub>	P <sub>RFIn</sub> = –10 dBm	–4	–1	–	dBm
IF Down-converter Block (f <sub>1stIFin</sub> = 61.38 MHz, f <sub>2ndLOin</sub> = 65.472 MHz, Z <sub>S</sub> = 50 Ω, Z <sub>L</sub> = 2 kΩ)						
Circuit Current 3	I <sub>CC3</sub>	No Signals	2.7	3.5	5.0	mA
IF Conversion Voltage Gain	CG <sub>(GV)IF</sub>	at Maximum Gain, P <sub>1stIFin</sub> = –50 dBm	40	43	46	dB
IF-SSB Noise Figure	NF <sub>IF</sub>	at Maximum Gain	–	11.5	14.5	dB
2nd IF Saturated Output Power	P <sub>O(sat)2ndIF</sub>	at Maximum Gain, P <sub>1stIFin</sub> = –20 dBm	–9.0	–6.0	–	dBm
Gain Control Voltage	V <sub>GC</sub>	Voltage at Maximum Gain CG <sub>IF</sub>	–	–	1.0	V
Gain Control Range	D <sub>GC</sub>	P <sub>1stIFin</sub> = –50 dBm	20	–	–	dB
2nd IF Amplifier (f <sub>2ndIFin</sub> = 4.092 MHz, Z <sub>S</sub> = 50 Ω, Z <sub>L</sub> = 2 kΩ)						
Circuit Current 4	I <sub>CC4</sub>	No Signals	0.8	1.0	1.6	mA
Voltage Gain	G <sub>V</sub>	P <sub>2ndIFin</sub> = –60 dBm	40	43	46	dB
2nd IF Saturated Output Power	P <sub>O(sat)2ndIF</sub>	P <sub>2ndIFin</sub> = –30 dBm	–14.0	–11.0	–	dBm
PLL Synthesizer Block						
Circuit Current 5	I <sub>CC5</sub>	PLL All Block Operating	8.7	11.0	14.4	mA
Loop Filter Output (High)	V <sub>oH</sub>		2.8	–	–	V
Loop Filter Output (Low)	V <sub>oL</sub>		–	–	0.4	V
Reference Minimum Input Level	V <sub>REFin</sub>	Z <sub>L</sub> = 100 kΩ/0.6 pF Impedance of measurement equipment	200	–	–	mV <sub>P-P</sub>
Reference Output Swing	V <sub>REFout</sub>	Z <sub>L</sub> = 100 kΩ/0.6 pF Impedance of measurement equipment	2.9	3.0	–	V <sub>P-P</sub>


STANDARD CHARACTERISTICS (T<sub>A</sub> = +25°C, V<sub>CC</sub> = 3.0 V)

Parameter	Symbol	Test Conditions	Reference	Unit
Pre-amplifier Block (f <sub>RFin</sub> = 1 575.42 MHz, Z <sub>S</sub> = Z <sub>L</sub> = 50 Ω)				
Input 1dB Compression Level	P <sub>in(1dB)</sub>	Input/Output matching	−20	dBm
RF Down-converter Block (P <sub>1stLOin</sub> = −10 dBm, Z <sub>S</sub> = Z <sub>L</sub> = 50 Ω)				
LO Leakage to IF Pin	LO <sub>if</sub>	f <sub>1stLOin</sub> = 1 636.80 MHz	−37	dBm
LO Leakage to RF Pin	LO <sub>rf</sub>	f <sub>1stLOin</sub> = 1 636.80 MHz	−36	dBm
Input 3rd Order Intercept Point	IIP <sub>3(RF)</sub>	f <sub>RFin1</sub> = 1 600 MHz, f <sub>RFin2</sub> = 1 605 MHz, f <sub>1stLOin</sub> = 1 660 MHz	−15	dBm
IF Down-converter Block (1st LO oscillating, Z <sub>S</sub> = 50 Ω, Z <sub>L</sub> = 2 kΩ)				
LO Leakage to 1st IF Pin	LO <sub>1stif</sub>	f <sub>2ndLOin</sub> = 65.472 MHz	−90	dBm
LO Leakage to 2nd IF Pin	LO <sub>2ndif</sub>	f <sub>2ndLOin</sub> = 65.472 MHz	−63	dBm
Input 3rd Order Intercept Point	IIP <sub>3(IF)</sub>	f <sub>1stIFin1</sub> = 61.38 MHz, f <sub>1stIFin2</sub> = 61.48 MHz, f <sub>2ndLOin</sub> = 65.472 MHz	−27.5	dBm
PLL Synthesizer Block				
Phase Comparing Frequency	f <sub>PD</sub>	PLL loop	8.184	MHz
VCO Block				
Phase Noise	C/N	PLL Loop, Δ1 kHz of VCO wave	83	dBc/Hz

★ TYPICAL CHARACTERISTICS (Unless otherwise specified,  $T_A = +25^\circ\text{C}$ ,  $V_{CC} = 3.0\text{ V}$ )


— IC TOTAL —

TOTAL CIRCUIT CURRENT  
vs. SUPPLY VOLTAGE




— PRE-AMPLIFIER BLOCK —


CIRCUIT CURRENT vs. SUPPLY VOLTAGE



OUTPUT POWER vs. INPUT POWER




OUTPUT POWER vs. INPUT POWER




— RF DOWN-CONVERTER BLOCK —


CIRCUIT CURRENT vs. SUPPLY VOLTAGE




1stIF OUTPUT POWER vs. RF INPUT POWER




1stIF OUTPUT POWER vs. RF INPUT POWER




1stIF OUTPUT POWER vs. 1stLO INPUT POWER




RF CONVERSION GAIN vs. RF INPUT FREQUENCY



RF CONVERSION GAIN vs.  
1stIF OUTPUT FREQUENCY




1stIF OUTPUT POWER OF EACH TONE  
vs. RF INPUT POWER OF EACH TONE




— IF DOWN-CONVERTER BLOCK —


CIRCUIT CURRENT vs. SUPPLY VOLTAGE




2ndIF OUTPUT POWER  
vs. 1stIF INPUT POWER




2ndIF OUTPUT POWER  
vs. 1stIF INPUT POWER




IF CONVERSION VOLTAGE GAIN  
vs. 1stIF INPUT FREQUENCY




IF CONVERSION VOLTAGE GAIN  
vs. 1stIF INPUT FREQUENCY




IF CONVERSION VOLTAGE GAIN  
vs. 2ndIF OUTPUT FREQUENCY




IF CONVERSION VOLTAGE GAIN  
vs. 2ndIF OUTPUT FREQUENCY



IF CONVERSION VOLTAGE GAIN  
vs. GAIN CONTROL VOLTAGE




IF CONVERSION VOLTAGE GAIN  
vs. GAIN CONTROL VOLTAGE






2ndIF OUTPUT POWER OF EACH TONE  
vs. 1stIF INPUT POWER OF EACH TONE




— IF AMPLIFIER BLOCK —


CIRCUIT CURRENT vs. SUPPLY VOLTAGE




2ndIF OUTPUT POWER  
vs. 2ndIF INPUT POWER




2ndIF OUTPUT POWER  
vs. 2ndIF INPUT POWER



VOLTAGE GAIN vs.  
2ndIF INPUT FREQUENCY




VOLTAGE GAIN vs.  
2ndIF INPUT FREQUENCY




### — PLL SYNTHESIZER BLOCK —

CIRCUIT CURRENT vs. SUPPLY VOLTAGE




### — REFERENCE BLOCK —


REFERENCE OUTPUT SWING vs.  
REFERENCE INPUT FREQUENCY




REFERENCE OUTPUT SWING vs.  
REFERENCE INPUT FREQUENCY



REFERENCE OUTPUT SWING vs.  
REFERENCE INPUT POWER




REFERENCE OUTPUT SWING vs.  
REFERENCE INPUT POWER




**Remark** The graphs indicate nominal characteristics.

★ MEASUREMENT CIRCUIT


MEASUREMENT CIRCUIT 1 (Pre-Amplifier Block)




MEASUREMENT CIRCUIT 2 (Pre-Amplifier Block: NF)




### MEASUREMENT CIRCUIT 3 (RF-MIX Block)




### MEASUREMENT CIRCUIT 4 (RF-MIX Block: NF)




### MEASUREMENT CIRCUIT 5 (IF Down-Converter Block)




### MEASUREMENT CIRCUIT 6 (IF Down-Converter Block: NF)




MEASUREMENT CIRCUIT 7 (IF Amplifier Block)




MEASUREMENT CIRCUIT 8 (IF Amplifier Block: NF)



### MEASUREMENT CIRCUIT 9 (IF Amplifier Block: Output Swing)




### MEASUREMENT CIRCUIT 10 (1/2 Prescaler)






MEASUREMENT CIRCUIT 11 (1/200 Prescaler)




MEASUREMENT CIRCUIT 12 (REF Output)



★ PACKAGE DIMENSIONS

36-PIN PLASTIC QFN (UNIT: mm)



## NOTES ON CORRECT USE

- (1) Observe precautions for handling because of electro-static sensitive devices.
- (2) Form a ground pattern as widely as possible to minimize ground impedance (to prevent abnormal oscillation).
- (3) Keep the wiring length of the ground pins as short as possible.
- (4) Connect a bypass capacitor (example: 1 000 pF) to the V<sub>cc</sub> pin.
- (5) High-frequency signal I/O pins must be coupled with the external circuit using a coupling capacitor.

## ★ RECOMMENDED SOLDERING CONDITIONS

This product should be soldered and mounted under the following recommended conditions. For soldering methods and conditions other than those recommended below, contact your nearby sales office.

Soldering Method	Soldering Conditions	Condition Symbol
Infrared Reflow	Peak temperature (package surface temperature) : 260°C or below Time at peak temperature : 10 seconds or less Time at temperature of 220°C or higher : 60 seconds or less Preheating time at 120 to 180°C : 120±30 seconds Maximum number of reflow processes : 3 times Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	IR260
VPS	Peak temperature (package surface temperature) : 215°C or below Time at temperature of 200°C or higher : 25 to 40 seconds Preheating time at 120 to 150°C : 30 to 60 seconds Maximum number of reflow processes : 3 times Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	VP215
Wave Soldering	Peak temperature (molten solder temperature) : 260°C or below Time at peak temperature : 10 seconds or less Preheating temperature (package surface temperature) : 120°C or below Maximum number of flow processes : 1 time Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	WS260
Partial Heating	Peak temperature (pin temperature) : 350°C or below Soldering time (per side of device) : 3 seconds or less Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	HS350

**Caution** Do not use different soldering methods together (except for partial heating).

- **The information in this document is current as of February, 2002. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC's data sheets or data books, etc., for the most up-to-date specifications of NEC semiconductor products. Not all products and/or types are available in every country. Please check with an NEC sales representative for availability and additional information.**
- No part of this document may be copied or reproduced in any form or by any means without prior written consent of NEC. NEC assumes no responsibility for any errors that may appear in this document.
- NEC does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC semiconductor products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of customer's equipment shall be done under the full responsibility of customer. NEC assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC endeavours to enhance the quality, reliability and safety of NEC semiconductor products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC semiconductor products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment, and anti-failure features.
- NEC semiconductor products are classified into the following three quality grades:  
 "Standard", "Special" and "Specific". The "Specific" quality grade applies only to semiconductor products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of a semiconductor product depend on its quality grade, as indicated below. Customers must check the quality grade of each semiconductor product before using it in a particular application.  
 "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots  
 "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)  
 "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.  
 The quality grade of NEC semiconductor products is "Standard" unless otherwise expressly specified in NEC's data sheets or data books, etc. If customers wish to use NEC semiconductor products in applications not intended by NEC, they must contact an NEC sales representative in advance to determine NEC's willingness to support a given application.  
 (Note)  
 (1) "NEC" as used in this statement means NEC Corporation, NEC Compound Semiconductor Devices, Ltd. and also includes its majority-owned subsidiaries.  
 (2) "NEC semiconductor products" means any semiconductor product developed or manufactured by or for NEC (as defined above).

M8E 00.4-0110

---

► **Business issue**

**NEC Compound Semiconductor Devices, Ltd.**

5th Sales Group, Sales Division TEL: +81-3-3798-6372 FAX: +81-3-3798-6783 E-mail: salesinfo@csd-nec.com

**NEC Compound Semiconductor Devices Hong Kong Limited**

Hong Kong Head Office TEL: +852-3107-7303 FAX: +852-3107-7309

Taipei Branch Office TEL: +886-2-8712-0478 FAX: +886-2-2545-3859

Korea Branch Office TEL: +82-2-528-0301 FAX: +82-2-528-0302

**NEC Electron Devices European Operations** <http://www.nec.de/>

TEL: +49-211-6503-101 FAX: +49-211-6503-487

**California Eastern Laboratories, Inc.** <http://www.cel.com/>

TEL: +1-408-988-3500 FAX: +1-408-988-0279

► **Technical issue**

**NEC Compound Semiconductor Devices, Ltd.** <http://www.csd-nec.com/>

Sales Engineering Group, Sales Division

E-mail: techinfo@csd-nec.com FAX: +81-44-435-1918