Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.

Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anticrime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majorityowned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



MOS INTEGRATED CIRCUIT 44165082A-A, 44165092A-A, 44165182A-A, 44165362A-A

18M-BIT QDR[™]II SRAM 2-WORD BURST OPERATION

Description

The μ PD44165082A-A is a 2,097,152-word by 8-bit, the μ PD44165092A-A is a 2,097,152-word by 9-bit, the μ PD44165182A-A is a 1,048,576-word by 18-bit and the μ PD44165362A-A is a 524,288-word by 36-bit synchronous quad data rate static RAM fabricated with advanced CMOS technology using full CMOS six-transistor memory cell.

The *µ*PD44165082A-A, *µ*PD44165092A-A, *µ*PD44165182A-A and *µ*PD44165362A-A integrate unique synchronous peripheral circuitry and a burst counter. All input registers controlled by an input clock pair (K and K#) are latched on the positive edge of K and K#.

These products are suitable for application which require synchronous operation, high speed, low voltage, high density and wide bit configuration.

These products are packaged in 165-pin PLASTIC BGA.

Features

- 1.8 ± 0.1 V power supply
- 165-pin PLASTIC BGA (13 x 15)
- HSTL interface
- PLL circuitry for wide output data valid window and future frequency scaling
- · Separate independent read and write data ports with concurrent transactions
- 100% bus utilization DDR READ and WRITE operation
- Two-tick burst for low DDR transaction size
- Two input clocks (K and K#) for precise DDR timing at clock rising edges only
- Two output clocks (C and C#) for precise flight time and clock skew matching-clock and data delivered together to receiving device
- Internally self-timed write control
- Clock-stop capability. Normal operation is restored in 1,024 cycles after clock is resumed.
- User programmable impedance output
- Fast clock cycle time : 4.0 ns (250 MHz), 5.0 ns (200 MHz)
- Simple control logic for easy depth expansion
- JTAG boundary scan
- Operating ambient temperature : Commercial T_A = 0 to +70°C (-E40, -E50)

Industrial $T_A = -40$ to +85°C (-E40Y, -E50Y)

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version. Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.

Document No. M19869EJ1V0DS00 (1st edition) Date Published July 2009 Printed in Japan

Ordering Information

(1) Operating Ambient Temperature $T_A = 0$ to +70°C

Part number	Cycle	Clock	Organization	Package	Operating
	Time	Frequency	(word x bit)		Ambient
	ns	MHz			Temperature
μPD44165082AF5-E40-EQ2-A	4.0	250	2M x 8-bit	165-pin PLASTIC	Commercial
μPD44165082AF5-E50-EQ2-A	5.0	200		BGA (13 x 15)	(T _A = 0 to +70°C)
μPD44165092AF5-E40-EQ2-A	4.0	250	2M x 9-bit		
μPD44165092AF5-E50-EQ2-A	5.0	200		Lead-free	
μPD44165182AF5-E40-EQ2-A	4.0	250	1M x 18-bit		
μPD44165182AF5-E50-EQ2-A	5.0	200			
μPD44165362AF5-E40-EQ2-A	4.0	250	512K x 36-bit		
μPD44165362AF5-E50-EQ2-A	5.0	200			

Remarks 1. QDR Consortium standard package size is 13 x 15 and 15 x 17.

The footprint is commonly used.

2. Products with -A at the end of the part number are lead-free products.

(2) Operating Ambient Temperature $T_A = -40$ to $+85^{\circ}C$

Part number	Cycle	Clock	Organization	Package	Operating
	Time	Frequency	(word x bit)		Ambient
	ns	MHz			Temperature
μPD44165082AF5-E40Y-EQ2-A	4.0	250	2M x 8-bit	165-pin PLASTIC	Industrial
μPD44165082AF5-E50Y-EQ2-A	5.0	200		BGA (13 x 15)	(T _A = -40 to +85°C)
μPD44165092AF5-E40Y-EQ2-A	4.0	250	2M x 9-bit		
μPD44165092AF5-E50Y-EQ2-A	5.0	200		Lead-free	
μPD44165182AF5-E40Y-EQ2-A	4.0	250	1M x 18-bit		
μPD44165182AF5-E50Y-EQ2-A	5.0	200			

Remarks 1. QDR Consortium standard package size is 13 x 15 and 15 x 17.

The footprint is commonly used.

2. Products with -A at the end of the part number are lead-free products.

NEC

Pin Configurations

165-pin PLASTIC BGA (13 x 15) (Top View) [μPD44165082A-A] 2M x 8-bit

_	1	2	3	4	5	6	7	8	9	10	11
Α	CQ#	Vss	Α	W#	NW1#	K#	NC	R#	Α	Vss	CQ
в	NC	NC	NC	Α	NC	к	NW0#	Α	NC	NC	Q3
с	NC	NC	NC	Vss	Α	Α	Α	Vss	NC	NC	D3
D	NC	D4	NC	Vss	Vss	Vss	Vss	Vss	NC	NC	NC
Е	NC	NC	Q4	VDDQ	Vss	Vss	Vss	VDDQ	NC	D2	Q2
F	NC	NC	NC	VDDQ	VDD	Vss	VDD	VDDQ	NC	NC	NC
G	NC	D5	Q5	VDDQ	VDD	Vss	VDD	VDDQ	NC	NC	NC
н	DLL#	VREF	VDDQ	VDDQ	VDD	Vss	VDD	VDDQ	VDDQ	VREF	ZQ
J	NC	NC	NC	VDDQ	VDD	Vss	VDD	VDDQ	NC	Q1	D1
к	NC	NC	NC	VDDQ	VDD	Vss	VDD	VDDQ	NC	NC	NC
L	NC	Q6	D6	VDDQ	Vss	Vss	Vss	VDDQ	NC	NC	Q0
м	NC	NC	NC	Vss	Vss	Vss	Vss	Vss	NC	NC	D0
Ν	NC	D7	NC	Vss	Α	Α	Α	Vss	NC	NC	NC
Ρ	NC	NC	Q7	Α	Α	С	Α	Α	NC	NC	NC
R	TDO	тск	Α	A	Α	C#	Α	A	Α	TMS	TDI

А	: Address inputs	DLL#	: DLL/PLL disable
D0 to D7	: Data inputs	TMS	: IEEE 1149.1 Test input
Q0 to Q7	: Data outputs	TDI	: IEEE 1149.1 Test input
R#	: Read input	TCK	: IEEE 1149.1 Clock input
W#	: Write input	TDO	: IEEE 1149.1 Test output
NW0#, NW1#	: Nibble Write data select	VREF	: HSTL input reference input
K, K#	: Input clock	Vdd	: Power Supply
C, C#	: Output clock	VddQ	: Power Supply
CQ, CQ#	: Echo clock	Vss	: Ground
ZQ	: Output impedance matching	NC	: No connection

- 2. Refer to Package Drawing for the index mark.
- **3**. 2A, 7A and 10A are expansion addresses: 10A for 36Mb, 2A for 72Mb and 7A for 144Mb. 2A and 10A of this product can also be used as NC.

165-pin PLASTIC BGA (13 x 15) (Top View) [μPD44165092A-A] 2M x 9-bit

_	1	2	3	4	5	6	7	8	9	10	11
Α	CQ#	Vss	A	W#	NC	K#	NC	R#	A	Vss	CQ
в	NC	NC	NC	Α	NC	к	BW0#	А	NC	NC	Q4
с	NC	NC	NC	Vss	Α	Α	Α	Vss	NC	NC	D4
D	NC	D5	NC	Vss	Vss	Vss	Vss	Vss	NC	NC	NC
Е	NC	NC	Q5	VDDQ	Vss	Vss	Vss	VDDQ	NC	D3	Q3
F	NC	NC	NC	VDDQ	VDD	Vss	VDD	VDDQ	NC	NC	NC
G	NC	D6	Q6	VDDQ	VDD	Vss	VDD	VDDQ	NC	NC	NC
н	DLL#	VREF	VDDQ	VDDQ	VDD	Vss	VDD	VDDQ	VDDQ	VREF	ZQ
J	NC	NC	NC	VDDQ	VDD	Vss	VDD	VDDQ	NC	Q2	D2
к	NC	NC	NC	VDDQ	VDD	Vss	VDD	VDDQ	NC	NC	NC
L	NC	Q7	D7	VDDQ	Vss	Vss	Vss	VDDQ	NC	NC	Q1
м	NC	NC	NC	Vss	Vss	Vss	Vss	Vss	NC	NC	D1
Ν	NC	D8	NC	Vss	Α	Α	Α	Vss	NC	NC	NC
Ρ	NC	NC	Q8	Α	Α	С	Α	A	NC	D0	Q0
R	TDO	тск	Α	Α	Α	C#	Α	Α	Α	TMS	TDI

А	: Address inputs	DLL#	: DLL/PLL disable
D0 to D8	: Data inputs	TMS	: IEEE 1149.1 Test input
Q0 to Q8	: Data outputs	TDI	: IEEE 1149.1 Test input
R#	: Read input	TCK	: IEEE 1149.1 Clock input
W#	: Write input	TDO	: IEEE 1149.1 Test output
BW0#	: Byte Write data select	VREF	: HSTL input reference input
K, K#	: Input clock	Vdd	: Power Supply
C, C#	: Output clock	VddQ	: Power Supply
CQ, CQ#	: Echo clock	Vss	: Ground
ZQ	: Output impedance matching	NC	: No connection

- 2. Refer to Package Drawing for the index mark.
- **3.** 2A, 7A and 10A are expansion addresses: 10A for 36Mb, 2A for 72Mb and 7A for 144Mb. 2A and 10A of this product can also be used as NC.

165-pin PLASTIC BGA (13 x 15) (Top View) [μΡD44165182A-A] 1M x 18-bit

_	1	2	3	4	5	6	7	8	9	10	11
Α	CQ#	Vss	NC	W#	BW1#	K#	NC	R#	A	Vss	CQ
в	NC	Q9	D9	Α	NC	к	BW0#	Α	NC	NC	Q8
с	NC	NC	D10	Vss	Α	Α	Α	Vss	NC	Q7	D8
D	NC	D11	Q10	Vss	Vss	Vss	Vss	Vss	NC	NC	D7
Е	NC	NC	Q11	VDDQ	Vss	Vss	Vss	VDDQ	NC	D6	Q6
F	NC	Q12	D12	VDDQ	VDD	Vss	VDD	VDDQ	NC	NC	Q5
G	NC	D13	Q13	VDDQ	VDD	Vss	VDD	VDDQ	NC	NC	D5
н	DLL#	VREF	VDDQ	VDDQ	VDD	Vss	VDD	VDDQ	VDDQ	VREF	ZQ
J	NC	NC	D14	VDDQ	VDD	Vss	VDD	VDDQ	NC	Q4	D4
к	NC	NC	Q14	VDDQ	VDD	Vss	VDD	VDDQ	NC	D3	Q3
L	NC	Q15	D15	VDDQ	Vss	Vss	Vss	VDDQ	NC	NC	Q2
М	NC	NC	D16	Vss	Vss	Vss	Vss	Vss	NC	Q1	D2
N	NC	D17	Q16	Vss	Α	Α	Α	Vss	NC	NC	D1
Ρ	NC	NC	Q17	Α	Α	С	Α	Α	NC	D0	Q0
R	TDO	тск	Α	Α	Α	C#	Α	Α	Α	TMS	TDI

А	: Address inputs	DLL#	: DLL/PLL disable
D0 to D17	: Data inputs	TMS	: IEEE 1149.1 Test input
Q0 to Q17	: Data outputs	TDI	: IEEE 1149.1 Test input
R#	: Read input	TCK	: IEEE 1149.1 Clock input
W#	: Write input	TDO	: IEEE 1149.1 Test output
BW0#, BW1#	: Byte Write data select	VREF	: HSTL input reference input
K, K#	: Input clock	Vdd	: Power Supply
C, C#	: Output clock	VddQ	: Power Supply
CQ, CQ#	: Echo clock	Vss	: Ground
ZQ	: Output impedance matching	NC	: No connection

- 2. Refer to Package Drawing for the index mark.
- **3.** 2A, 3A and 10A are expansion addresses: 3A for 36Mb, 10A for 72Mb and 2A for 144Mb. 2A and 10A of this product can also be used as NC.

165-pin PLASTIC BGA (13 x 15) (Top View) [μΡD44165362A-A] 512K x 36-bit

_	1	2	3	4	5	6	7	8	9	10	11
Α	CQ#	Vss	NC	W#	BW2#	K#	BW1#	R#	NC	Vss	CQ
в	Q27	Q18	D18	Α	BW3#	к	BW0#	Α	D17	Q17	Q8
с	D27	Q28	D19	Vss	Α	Α	Α	Vss	D16	Q7	D8
D	D28	D20	Q19	Vss	Vss	Vss	Vss	Vss	Q16	D15	D7
Е	Q29	D29	Q20	VDDQ	Vss	Vss	Vss	VDDQ	Q15	D6	Q6
F	Q30	Q21	D21	VDDQ	VDD	Vss	VDD	VDDQ	D14	Q14	Q5
G	D30	D22	Q22	VDDQ	VDD	Vss	VDD	VDDQ	Q13	D13	D5
н	DLL#	VREF	VDDQ	VDDQ	VDD	Vss	VDD	VDDQ	VDDQ	VREF	ZQ
J	D31	Q31	D23	VDDQ	VDD	Vss	VDD	VDDQ	D12	Q4	D4
к	Q32	D32	Q23	VDDQ	VDD	Vss	VDD	VDDQ	Q12	D3	Q3
L	Q33	Q24	D24	VDDQ	Vss	Vss	Vss	VDDQ	D11	Q11	Q2
м	D33	Q34	D25	Vss	Vss	Vss	Vss	Vss	D10	Q1	D2
Ν	D34	D26	Q25	Vss	Α	Α	Α	Vss	Q10	D9	D1
Ρ	Q35	D35	Q26	Α	Α	С	Α	Α	Q9	D0	Q0
R	TDO	тск	Α	Α	Α	C#	Α	Α	Α	TMS	TDI

А	: Address inputs	DLL#	: DLL/PLL disable
D0 to D35	: Data inputs	TMS	: IEEE 1149.1 Test input
Q0 to Q35	: Data outputs	TDI	: IEEE 1149.1 Test input
R#	: Read input	TCK	: IEEE 1149.1 Clock input
W#	: Write input	TDO	: IEEE 1149.1 Test output
BW0# to BW3#	: Byte Write data select	VREF	: HSTL input reference input
K, K#	: Input clock	Vdd	: Power Supply
C, C#	: Output clock	VddQ	: Power Supply
CQ, CQ#	: Echo clock	Vss	: Ground
ZQ	: Output impedance matching	NC	: No connection

- 2. Refer to Package Drawing for the index mark.
- 3. 3A, 9A and 10A are expansion addresses: 9A for 36Mb, 3A for 72Mb and 10A for 144Mb.2A and 10A of this product can also be used as NC.

(1/2)

Pin Identification

Symbol	Description
A	Synchronous Address Inputs: These inputs are registered and must meet the setup and hold times around the rising edge of K for READ cycles and must meet the setup and hold times around the rising edge of K# for WRITE cycles. All transactions operate on a burst of two words (one clock period of bus activity). These inputs are ignored when device is deselected, i.e., NOP (R# = W# = HIGH).
D0 to Dxx	Synchronous Data Inputs: Input data must meet setup and hold times around the rising edges of K and K# during WRITE operations. See Pin Configurations for ball site location of individual signals. x8 device uses D0 to D7. x9 device uses D0 to D8. x18 device uses D0 to D17. x36 device uses D0 to D35.
Q0 to Qxx	Synchronous Data Outputs: Output data is synchronized to the respective C and C# or to K and K# rising edges if C and C# are tied HIGH. Data is output in synchronization with C and C# (or K and K#), depending on the R# command. See Pin Configurations for ball site location of individual signals. x8 device uses Q0 to Q7. x9 device uses Q0 to Q8. x18 device uses Q0 to Q17. x36 device uses Q0 to Q35.
R#	Synchronous Read: When LOW this input causes the address inputs to be registered and a READ cycle to be initiated. This input must meet setup and hold times around the rising edge of K.
W#	Synchronous Write: When LOW this input causes the address inputs to be registered and a WRITE cycle to be initiated. This input must meet setup and hold times around the rising edge of K.
BWx# NWx#	Synchronous Byte Writes (Nibble Writes on x8): When LOW these inputs cause their respective byte or nibble to be registered and written during WRITE cycles. These signals must meet setup and hold times around the rising edges of K and K# for each of the two rising edges comprising the WRITE cycle. See Pin Configurations for signal to data relationships. x8 device uses NW0#, NW1#. x9 device uses BW0#. x18 device uses BW0#, BW1#. x36 device uses BW0# to BW3#. See Byte Write Operation for relation between BWx#, NWx# and Dxx.
К, К#	Input Clock: A READ address and control input signal are input in synchronization with the rising edge of K and a WRITE address is input in synchronization with the rising edge of K#. Input data is input in synchronization with the rising edge of K and K#. K# is ideally 180 degrees out of phase with K. All synchronous inputs must meet setup and hold times around the clock rising edges.
C, C#	Output Clock: This clock pair provides a user controlled means of tuning device output data. The rising edge of C# is used as the output timing reference for first output data. The rising edge of C is used as the output reference for second output data. Ideally, C# is 180 degrees out of phase with C. When use of K and K# as the reference instead of C and C#, then fixed C and C# to HIGH. Operation cannot be guaranteed unless C and C# are fixed to HIGH (i.e. toggle of C and C#).

(2/2)

Symbol	Description
CQ, CQ#	Synchronous Echo Clock Outputs. The rising edges of these outputs are tightly matched to the synchronous data outputs and can be used as a data valid indication. These signals run freely and do not stop when Q tristates. If C and C# are stopped (if K and K# are stopped in the single clock mode), CQ and CQ# will also stop.
ZQ	Output Impedance Matching Input: This input is used to tune the device outputs to the system data bus impedance. Q, CQ and CQ# output impedance are set to $0.2 \times RQ$, where RQ is a resistor from this bump to ground. The output impedance can be minimized by directly connect ZQ to V _{DD} Q. This pin cannot be connected directly to GND or left unconnected. The output impedance is adjusted every 1,024 cycles upon power-up to account for drifts in supply voltage and temperature. After replacement for a resistor, the new output impedance is reset by implementing power-on sequence.
DLL#	DLL/PLL Disable: When debugging the system or board, the operation can be performed at a clock frequency slower than TKHKH (MAX.) without the DLL/PLL circuit being used, if DLL# = LOW. The AC/DC characteristics cannot be guaranteed. For normal operation, DLL# must be HIGH and it can be connected to VDDQ through a 10 k Ω or less resistor.
TMS TDI	IEEE 1149.1 Test Inputs: 1.8 V I/O level. These balls may be left Not Connected if the JTAG function is not used in the circuit.
ТСК	IEEE 1149.1 Clock Input: 1.8 V I/O level. This pin must be tied to Vss if the JTAG function is not used in the circuit.
TDO	IEEE 1149.1 Test Output: 1.8 V I/O level.
VREF	HSTL Input Reference Voltage: Nominally VDDQ/2. Provides a reference voltage for the input buffers.
Vdd	Power Supply: 1.8 V nominal. See Recommended DC Operating Conditions and DC Characteristics for range.
VddQ	Power Supply: Isolated Output Buffer Supply. Nominally 1.5 V. 1.8 V is also permissible. See Recommended DC Operating Conditions and DC Characteristics for range.
Vss	Power Supply: Ground
NC	No Connect: These signals are not connected internally.

Block Diagram









Data Sheet M19869EJ1V0DS

Power-on Sequence

The following timing charts show the recommended power-on sequence, i.e., when starting the clock after $V_{DD}/V_{DD}Q$ stable and when starting the clock before $V_{DD}/V_{DD}Q$ stable.

1. Clock starts after VDD/VDDQ stable

The clock is supplied from a controller.

(a)



Note Input a stable clock from the start.



2. Clock starts before VDD/VDDQ stable

The clock is supplied from a clock generator.



Truth Table

Operation	CLK	R#	W#	D or Q
WRITE cycle	$L\toH$	х	L	Data in
Load address, input write data on				Input data DA (A+0) DA (A+1)
consecutive K and K# rising edge				Input clock $K(t) \uparrow K\#(t) \uparrow$
READ cycle	$L\toH$	L	х	Data out
Load address, output data on				Output data QA (A+0) QA (A+1)
consecutive C and #C rising edge				Output clock $C#(t+1) \uparrow C(t+2) \uparrow$
NOP (No operation)	$L\toH$	Н	Н	D = X, Q = High-Z
Clock stop	Stopped	х	х	Previous state

Remarks 1. H : HIGH, L : LOW, \times : don't care, \uparrow : rising edge.

- 2. Data inputs are registered at K and K# rising edges. Data outputs are delivered at C and C# rising edges except if C and C# are HIGH then Data outputs are delivered at K and K# rising edges.
- All control inputs in the truth table must meet setup/hold times around the rising edge (LOW to HIGH) of K. All control inputs are registered during the rising edge of K.
- 4. This device contains circuitry that ensure the outputs to be in high impedance during power-up.
- 5. Refer to state diagram and timing diagrams for clarification.
- **6.** It is recommended that K = K# = C = C# when clock is stopped. This is not essential but permits most rapid restart by overcoming transmission line charging symmetrically.

Byte Write Operation

[*µ*PD44165082A-A]

Operation	К	K#	NW0#	NW1#
Write D0 to D7	$L\toH$	-	0	0
	_	$L\toH$	0	0
Write D0 to D3	$L\toH$	Ι	0	1
	_	$L\toH$	0	1
Write D4 to D7	$L\toH$	Ι	1	0
	_	$L\toH$	1	0
Write nothing	$L\toH$	Ι	1	1
	_	$L\toH$	1	1

Remarks 1. H : HIGH, L : LOW, \rightarrow : rising edge.

 Assumes a WRITE cycle was initiated. NW0# and NW1# can be altered for any portion of the BURST WRITE operation provided that the setup and hold requirements are satisfied.

[µPD44165092A-A]

Operation	К	K#	BW0#
Write D0 to D8	$L\toH$	-	0
	Ι	$L\toH$	0
Write nothing	$L\toH$	_	1
	_	$L\toH$	1

Remarks 1. H : HIGH, L : LOW, \rightarrow : rising edge.

2. Assumes a WRITE cycle was initiated. BW0# can be altered for any portion of the BURST WRITE operation provided that the setup and hold requirements are satisfied.

[*µ*PD44165182A-A]

Operation	К	K#	BW0#	BW1#
Write D0 to D17	$L\toH$	_	0	0
	_	$L\toH$	0	0
Write D0 to D8	$L\toH$	_	0	1
	_	$L\toH$	0	1
Write D9 to D17	$L\toH$	_	1	0
	_	$L\toH$	1	0
Write nothing	$L\toH$	_	1	1
	-	$L\toH$	1	1

Remarks 1. H : HIGH, L : LOW, \rightarrow : rising edge.

2. Assumes a WRITE cycle was initiated. BW0# and BW1# can be altered for any portion of the BURST WRITE operation provided that the setup and hold requirements are satisfied.

[µPD44165362A-A]

Operation	к	K#	BW0#	BW1#	BW2#	BW3#
Write D0 to D35	$L\toH$	-	0	0	0	0
	_	$L\toH$	0	0	0	0
Write D0 to D8	$L\toH$	-	0	1	1	1
	_	$L\toH$	0	1	1	1
Write D9 to D17	$L\toH$	Ι	1	0	1	1
	_	$L\toH$	1	0	1	1
Write D18 to D26	$L\toH$	-	1	1	0	1
	_	$L\toH$	1	1	0	1
Write D27 to D35	$L\toH$	-	1	1	1	0
	_	$L\toH$	1	1	1	0
Write nothing	$L\toH$	_	1	1	1	1
	_	$L\toH$	1	1	1	1

Remarks 1. H : HIGH, L : LOW, \rightarrow : rising edge.

2. Assumes a WRITE cycle was initiated. BW0# to BW3# can be altered for any portion of the BURST WRITE operation provided that the setup and hold requirements are satisfied.

Bus Cycle State Diagram



Remarks 1. The address is concatenated with 1 additional internal LSB to facilitate burst operation. The address order is always fixed as: xxx...xxx+0, xxx...xxx+1. Bus cycle is terminated at the end of this sequence (burst count = 2).

- **2.** Read and write state machines can be active simultaneously.
- 3. State machine control timing sequence is controlled by K.

Electrical Specifications

Absolute Maximum Ratings

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Supply voltage	Vdd		-0.5		+2.5	V
Output supply voltage	VddQ		-0.5		Vdd	V
Input voltage	Vin		-0.5		VDD + 0.5 (2.5 V MAX.)	V
Input / Output voltage	Vi/o		-0.5		VDDQ + 0.5 (2.5 V MAX.)	V
Operating ambient temperature	Та	Commercial	0		+70	°C
		Industrial	-40		+85	
Storage temperature	Tstg		-55		+125	°C

Caution Exposing the device to stress above those listed in Absolute Maximum Ratings could cause permanent damage. The device is not meant to be operated under conditions outside the limits described in the operational section of this specification. Exposure to Absolute Maximum Rating conditions for extended periods may affect device reliability.

Recommended DC Operating Conditions

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit	Note
Supply voltage	Vdd		1.7		1.9	V	
Output supply voltage	VddQ		1.4		Vdd	V	1
Input HIGH voltage	VIH (DC)		Vref + 0.1		VDDQ + 0.3	V	1, 2
Input LOW voltage	VIL (DC)		-0.3		Vref – 0.1	V	1, 2
Clock input voltage	VIN		-0.3		VDDQ + 0.3	V	1, 2
Reference voltage	Vref		0.68		0.95	V	

Notes 1. During normal operation, VDDQ must not exceed VDD.

2. Power-up: VIH \leq VDDQ + 0.3 V and VDD \leq 1.7 V and VDDQ \leq 1.4 V for $t \leq$ 200 ms

Recommended AC Operating Conditions

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit	Note
Input HIGH voltage	VIH (AC)		Vref + 0.2		_	V	1
Input LOW voltage	VIL (AC)		_		Vref – 0.2	V	1

Note 1. Overshoot: VIH (AC) \leq VDD + 0.7 V (2.5 V MAX.) for t \leq TKHKH/2

Undershoot: VIL $_{(AC)} \geq -$ 0.5 V for $t \leq TKHKH/2$

Control input signals may not have pulse widths less than TKHKL (MIN.) or operate at cycle rates less than TKHKH (MIN.).

Parameter	Symbol		Test condition		MIN.	TYP.		MAX.		Unit	Note
							x8, x9	x18	x36		
Input leakage current	Iц				-2	_		+2		μA	
I/O leakage current	Ilo				-2	١		+2		μA	
Operating supply	IDD	Note1	Commercial	-E40			530	640	850	mA	
current			(T _A = 0 to +70°C)	-E50			460	550	710		
(Read cycle/			Industrial	-E40Y			570	660	-		
Write cycle)			(T _A = -40 to +85°C)	-E50Y			490	570	-		
Standby supply	ISB1	Note1	Commercial	-E40			290	290	290	mA	
current			(T _A = 0 to +70°C)	-E50			270	270	270		
(NOP)			Industrial	-E40Y			310	310	-		
			(T _A = -40 to +85°C)	-E50Y			290	290	-		
Output HIGH voltage	VOH(Low)	Іон ≤ 0.1 m	A		VDDQ - 0.2	_		VddQ		V	4, 5
	Vон	Note2			VDDQ/2-0.12	-	VD	DQ/2+0	.12		4, 5
Output LOW voltage	VOL(Low)	$IOL \le 0.1 \text{ mA}$			Vss	-		0.2		V	4, 5
	Vol	Note3			VDDQ/2-0.12	-	VD	DQ/2+0	.12		4, 5

DC Characteristics (VDD = 1.8 ± 0.1 V)

Notes 1. $V_{IN} \leq V_{IL} \text{ or } V_{IN} \geq V_{IH}$, $I_{I/O}$ = 0 mA, Cycle = MAX.

- 2. Outputs are impedance-controlled. | IoH | = (V_{DD}Q/2)/(RQ/5) ±15% for values of 175 $\Omega \le RQ \le 350 \Omega$.
- 3. Outputs are impedance-controlled. IoL = (VDDQ/2)/(RQ/5) ±15% for values of 175 $\Omega \le RQ \le 350 \Omega$.
- 4. AC load current is higher than the shown DC values.
- 5. HSTL outputs meet JEDEC HSTL Class I standards.

Capacitance (TA = 25°C, f = 1 MHz)

Parameter	Symbol	Test conditions	MIN.	TYP.	MAX.	Unit
Input capacitance (Address, Control)	Cin	VIN = 0 V		4	5	pF
Input / Output capacitance	Ci/o	VI/O = 0 V		6	7	pF
(D, Q, CQ, CQ#)						
Clock Input capacitance	Cclk	Vclk = 0 V		5	6	pF

Remark These parameters are periodically sampled and not 100% tested.

Thermal Resistance

Parameter	Symbol	Test conditions	MIN.	TYP.	MAX.	Unit
Thermal resistance	heta j-a			25.1		°C/W
(junction – ambient)						
Thermal resistance	heta j-c			2.8		°C/W
(junction – case)						

Remark These parameters are simulated under the condition of air flow velocity = 1 m/s.

NEC

AC Characteristics (VDD = 1.8 ± 0.1 V)

AC Test Conditions (VDD = $1.8 \pm 0.1 \text{ V}$, VDDQ = 1.4 V to VDD)

Input waveform (Rise / Fall time \leq 0.3 ns)



Output waveform



Output load condition

Figure 1. External load at test



Read and Write Cycle

Para	ameter	Symbol		-E40Y	-E50,		Unit	Note
				MHz)	,	MHz)	_	
			MIN.	MAX.	MIN.	MAX.		
Clock					1			
Average Clock cycle	e time (K, K#, C, C#)	TKHKH	4.0	8.4	5.0	8.4	ns	1
Clock phase jitter (K	Clock phase jitter (K, K#, C, C#)		-	0.2	-	0.2	ns	2
Clock HIGH time (K	, K#, C, C#)	TKHKL	1.6	-	2.0	-	ns	
Clock LOW time (K,	K#, C, C#)	TKLKH	1.6	-	2.0	-	ns	
Clock HIGH to Clock	k# HIGH	TKHK#H	1.8	-	2.2	-	ns	
$(K \rightarrow K\#, C \rightarrow C\#)$		T 17#11711	1.0		0.0			
Clock# HIGH to Clock# (K# \rightarrow K, C# \rightarrow C)	CK HIGH	TK#HKH	1.8	-	2.2	-	ns	
Clock to data clock	200 to 250 MHz	ТКНСН	0	1.8	_	_	ns	
$(K \rightarrow C, K \# \rightarrow C \#)$	167 to 200 MHz		0	2.3	0	2.3	-	
	133 to 167 MHz		0	2.8	0	2.8	1	
	< 133 MHz		0	3.55	0	3.55	1	
DLL/PLL lock time (DLL/PLL lock time (K, C)		1,024	-	1,024	-	Cycle	3
	K static to DLL/PLL reset		30	_	30	_	ns	4
		TKC reset		l		I		
Output Times								
C, C# HIGH to output valid		TCHQV	-	0.45	-	0.45	ns	
C, C# HIGH to output hold		TCHQX	- 0.45	-	- 0.45	-	ns	
C, C# HIGH to echo clock valid		TCHCQV	-	0.45	-	0.45	ns	
C, C# HIGH to echo	clock hold	TCHCQX	- 0.45	-	- 0.45	-	ns	
CQ, CQ# HIGH to o	utput valid	TCQHQV	-	0.3	-	0.35	ns	5
CQ, CQ# HIGH to o	utput hold	TCQHQX	- 0.3	-	- 0.35	-	ns	5
C HIGH to output Hi	igh-Z	TCHQZ	-	0.45	-	0.45	ns	
C HIGH to output Lo	ow-Z	TCHQX1	- 0.45	-	- 0.45	-	ns	
Setup Times								
Address valid to K ri	ising edge	TAVKH	0.35	_	0.4	_	ns	6
Control inputs (R#, V		TIVKH	0.35	-	0.4	-	ns	6
edge								
Data inputs and writ		TDVKH	0.35	-	0.4	-	ns	6
inputs (BWx#, NWx	#) valid to K, K#							
rising edge								
Hold Times								
K rising edge to add	ress hold	TKHAX	0.35	_	0.4	_	ns	6
K rising edge to con hold		ТКНІХ	0.35	_	0.4	_	ns	6
K, K# rising edge to write data select inp hold		TKHDX	0.35	_	0.4	_	ns	6

- Notes 1. When debugging the system or board, these products can operate at a clock frequency slower than TKHKH (MAX.) without the DLL/PLL circuit being used, if DLL# = LOW. Read latency (RL) is changed to 1.5 clock in this operation. The AC/DC characteristics cannot be guaranteed, however.
 - Clock phase jitter is the variance from clock rising edge to the next expected clock rising edge. TKC var (MAX.) indicates a peak-to-peak value.
 - 3. VDD slew rate must be less than 0.1 V DC per 50 ns for DLL/PLL lock retention.
 DLL/PLL lock time begins once VDD and input clock are stable.
 It is recommended that the device is kept NOP (R# = W# = HIGH) during these cycles.
 - **4.** K input is monitored for this operation. See below for the timing.



- 5. Echo clock is very tightly controlled to data valid / data hold. By design, there is a \pm 0.1 ns variation from echo clock to data. The data sheet parameters reflect tester guardbands and test setup variations.
- **6.** This is a synchronous device. All addresses, data and control lines must meet the specified setup and hold times for all latching clock edges.

Remarks 1. This parameter is sampled.

- **2.** Test conditions as specified with the output loading as shown in AC Test Conditions unless otherwise noted.
- 3. Control input signals may not be operated with pulse widths less than TKHKL (MIN.).
- 4. If C, C# are tied HIGH, K, K# become the references for C, C# timing parameters.
- **5.** VDDQ is 1.5 V DC.

Read and Write Timing



Remarks 1. Q00 refers to output from address A0+0.

Q01 refers to output from the next internal burst address following A0,i.e.,A0+1.

- Outputs are disabled (high impedance) 2.5 clocks after the last READ (R# = LOW) is input in the sequences of [READ/WRITE]-[NOP/WRITE], [READ/WRITE]-[NOP/NOP], [READ/NOP]-[NOP/WRITE] and [READ/NOP] -[NOP/NOP].
- In this example, if address A0 = A1, data Q00 = D10, Q01 = D11.
 Write data is forwarded immediately as read results.

Application Example



Remark AC specifications are defined at the condition of SRAM outputs, CQ, CQ# and Q with termination.

JTAG Specification

These products support a limited set of JTAG functions as in IEEE standard 1149.1.

Test Access Port (TAP) Pins

Pin name	Pin assignments	Description
тск	2R	Test Clock Input. All input are captured on the rising edge of TCK and all outputs propagate from the falling edge of TCK.
TMS	10R	Test Mode Select. This is the command input for the TAP controller state machine.
TDI	11R	Test Data Input. This is the input side of the serial registers placed between TDI and TDO. The register placed between TDI and TDO is determined by the state of the TAP controller state machine and the instruction that is currently loaded in the TAP instruction.
TDO	1R	Test Data Output. This is the output side of the serial registers placed between TDI and TDO. Output changes in response to the falling edge of TCK.

Remark The device does not have TRST (TAP reset). The Test-Logic Reset state is entered while TMS is held HIGH for five rising edges of TCK. The TAP controller state is also reset on the SRAM POWER-UP.

JTAG DC Characteristics (VDD = 1.8 ± 0.1 V, unless otherwise noted)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
JTAG Input leakage current	Iц	$0~V \leq V_{\text{IN}} \leq V_{\text{DD}}$	-5.0	_	+5.0	μA
JTAG I/O leakage current	Ilo	$0 \ V \leq V_{\text{IN}} \leq V_{\text{DD}} Q \ ,$	-5.0	-	+5.0	μA
		Outputs disabled				
JTAG input HIGH voltage	Vін		1.3	-	VDD+0.3	V
JTAG input LOW voltage	VIL		-0.3	-	+0.5	V
JTAG output HIGH voltage	Voh1	Іонс = 100 μА	1.6	-	-	V
	Vон2	Іонт = 2 mA	1.4	-	-	V
JTAG output LOW voltage	Vol1	lolc = 100 μA	-	-	0.2	V
	Vol2	IOLT = 2 mA	_	_	0.4	V

JTAG AC Test Conditions

Input waveform (Rise / Fall time ≤ 1 ns)



Output waveform



Output load





JTAG AC Characteristics

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Clock						
Clock cycle time	tтнтн		50	_	_	ns
Clock frequency	ftf		_	_	20	MHz
Clock HIGH time	tтнт∟		20	_	_	ns
Clock LOW time	tт∟тн		20	_	-	ns
Output time						-
TCK LOW to TDO unknown	t tlox		0	-	-	ns
TCK LOW to TDO valid	t τιον		-	_	10	ns
Setup time						
TMS setup time	tмvтн		5	_	_	ns
TDI valid to TCK HIGH	tdvth		5	_	_	ns
Capture setup time	tcs		5	_	_	ns
	_					
Hold time						
TMS hold time	tтнмх		5	_	-	ns
TCK HIGH to TDI invalid	t thdx		5	_	_	ns
Capture hold time	tсн		5	_	_	ns

JTAG Timing Diagram



Scan Register Definition (1)

Register name	Description
Instruction register	The instruction register holds the instructions that are executed by the TAP controller when it is moved into the run-test/idle or the various data register state. The register can be loaded when it is placed between the TDI and TDO pins. The instruction register is automatically preloaded with the IDCODE instruction at power-up whenever the controller is placed in test-logic-reset state.
Bypass register	The bypass register is a single bit register that can be placed between TDI and TDO. It allows serial test data to be passed through the RAMs TAP to another device in the scan chain with as little delay as possible.
ID register	The ID Register is a 32 bit register that is loaded with a device and vendor specific 32 bit code when the controller is put in capture-DR state with the IDCODE command loaded in the instruction register. The register is then placed between the TDI and TDO pins when the controller is moved into shift-DR state.
Boundary register	The boundary register, under the control of the TAP controller, is loaded with the contents of the RAMs I/O ring when the controller is in capture-DR state and then is placed between the TDI and TDO pins when the controller is moved to shift-DR state. Several TAP instructions can be used to activate the boundary register. The Scan Exit Order tables describe which device bump connects to each boundary register location. The first column defines the bit's position in the boundary register. The second column is the name of the input or I/O at the bump and the third column is the bump number.

Scan Register Definition (2)

Register name	Bit size	Unit
Instruction register	3	bit
Bypass register	1	bit
ID register	32	bit
Boundary register	107	bit

ID Register Definition

Part number	Organization	ID [31:28] vendor revision no.	ID [27:12] part no.	ID [11:1] vendor ID no.	ID [0] fix bit
μPD44165082A-A	2M x 8	XXXX	0000 0000 0000 1100	00000010000	1
μPD44165092A-A	2M x 9	XXXX	0000 0000 0101 0001	00000010000	1
μPD44165182A-A	1M x 18	XXXX	0000 0000 0000 1101	00000010000	1
μPD44165362A-A	512K x 36	XXXX	0000 0000 0000 1110	00000010000	1

SCAN Exit Order

Bit		Signal	name		Bump
no.	x8	x9	x18	x36	ID
1		С	;#		6R
2		C	C		6P
3		ļ	A		6N
4		ŀ	4		7P
5		ļ	4		7N
6		ŀ	4		7R
7		ŀ	4		8R
8		ŀ	4		8P
9		1	4	i	9R
10	NC	Q0	Q0	Q0	11P
11	NC	D0	D0	D0	10P
12	NC	NC	NC	D9	10N
13	NC	NC	NC	Q9	9P
14	NC	NC	Q1	Q1	10M
15	NC	NC	D1	D1	11N
16	NC	NC	NC	D10	9M
17	NC	NC	NC	Q10	9N
18	Q0	Q1	Q2	Q2	11L
19	D0	D1	D2	D2	11M
20	NC	NC	NC	D11	9L
21	NC	NC	NC	Q11	10L
22	NC	NC	Q3	Q3	11K
23	NC	NC	D3	D3	10K
24	NC	NC	NC	D12	9J
25	NC	NC	NC	Q12	9K
26	Q1	Q2	Q4	Q4	10J
27	D1	D2	D4	D4	11J
28		Z	Q	i	11H
29	NC	NC	NC	D13	10G
30	NC	NC	NC	Q13	9G
31	NC	NC	Q5	Q5	11F
32	NC	NC	D5	D5	11G
33	NC	NC	NC	D14	9F
34	NC	NC	NC	Q14	10F
35	Q2	Q3	Q6	Q6	11E
36	D2	D3	D6	D6	10E

Bit		Signal	name	i	Bump
no.	x8	x9	x18	x36	ID
37	NC	NC	NC	D15	10D
38	NC	NC	NC	Q15	9E
39	NC	NC	Q7	Q7	10C
40	NC	NC	D7	D7	11D
41	NC	NC	NC	D16	9C
42	NC	NC	NC	Q16	9D
43	Q3	Q4	Q8	Q8	11B
44	D3	D4	D8	D8	11C
45	NC	NC	NC	D17	9B
46	NC	NC	NC	Q17	10B
47		С	Q		11A
48		-	-		Internal
49	А	А	А	NC	9A
50		8B			
51		7C			
52		6C			
53		R	#		8A
54	NC	NC	NC	BW1#	7A
55	NW0#	BW0#	BW0#	BW0#	7B
56		ł	<		6B
57		ĸ	#	i	6A
58	NC	NC	NC	BW3#	5B
59	NW1#	NC	BW1#	BW2#	5A
60		N	/#		4A
61		ŀ	A		5C
62		ŀ	4	1	4B
63	А	А	NC	NC	3A
64		DL	.L#		1H
65		1A			
66	NC	NC	Q9	Q18	2B
67	NC	NC	D9	D18	3B
68	NC	NC	NC	D27	1C
69	NC	NC	NC	Q27	1B
70	NC	NC	Q10	Q19	3D
71	NC	NC	D10	D19	3C
72	NC	NC	NC	D28	1D

Bit		Bump			
no.	x8	X9	name x18	x36	ID
73	NC	NC	NC	Q28	2C
74	Q4	Q5	Q11	Q20	20 3E
75	D4	D5	D11	D20	2D
76	NC	NC	NC	D29	2E
77	NC	NC	NC	Q29	1E
78	NC	NC	Q12	Q21	2F
79	NC	NC	D12	D21	3F
80	NC	NC	NC	D30	1G
81	NC	NC	NC	Q30	1F
82	Q5	Q6	Q13	Q22	3G
83	D5	D6	D13	D22	2G
84	NC	NC	NC	D31	 1J
85	NC	NC	NC	Q31	2J
86	NC	NC	Q14	Q23	3K
87	NC	NC	D14	D23	3J
88	NC	NC	NC	D32	2K
89	NC	NC	NC	Q32	1K
90	Q6	Q7	Q15	Q24	2L
91	D6	D7	D15	D24	3L
92	NC	NC	NC	D33	1M
93	NC	NC	NC	Q33	1L
94	NC	NC	Q16	Q25	3N
95	NC	NC	D16	D25	3M
96	NC	NC	NC	D34	1N
97	NC	NC	NC	Q34	2M
98	Q7	Q8	Q17	Q26	3P
99	D7	D8	D17	D26	2N
100	NC	NC	NC	D35	2P
101	NC	NC	NC	Q35	1P
102			4		3R
103		4R			
104	A				4P
105		5P			
106			٩		5N
107		1	4		5R

JTAG Instructions

Instructions	Description
EXTEST	The EXTEST instruction allows circuitry external to the component package to be tested. Boundary- scan register cells at output pins are used to apply test vectors, while those at input pins capture test results. Typically, the first test vector to be applied using the EXTEST instruction will be shifted into the boundary scan register using the PRELOAD instruction. Thus, during the update-IR state of EXTEST, the output drive is turned on and the PRELOAD data is driven onto the output pins.
IDCODE	The IDCODE instruction causes the ID ROM to be loaded into the ID register when the controller is in capture-DR mode and places the ID register between the TDI and TDO pins in shift-DR mode. The IDCODE instruction is the default instruction loaded in at power up and any time the controller is placed in the test-logic-reset state.
BYPASS	When the BYPASS instruction is loaded in the instruction register, the bypass register is placed between TDI and TDO. This occurs when the TAP controller is moved to the shift-DR state. This allows the board level scan path to be shortened to facilitate testing of other devices in the scan path.
SAMPLE / PRELOAD	SAMPLE / PRELOAD is a Standard 1149.1 mandatory public instruction. When the SAMPLE / PRELOAD instruction is loaded in the instruction register, moving the TAP controller into the capture-DR state loads the data in the RAMs input and Q pins into the boundary scan register. Because the RAM clock(s) are independent from the TAP clock (TCK) it is possible for the TAP to attempt to capture the I/O ring contents while the input buffers are in transition (i.e., in a metastable state). Although allowing the TAP to sample metastable input will not harm the device, repeatable results cannot be expected. RAM input signals must be stabilized for long enough to meet the TAPs input data capture setup plus hold time (tcs plus tch). The RAMs clock inputs need not be paused for any other TAP operation except capturing the I/O ring contents into the boundary scan register. Moving the controller to shift-DR state then places the boundary scan register between the TDI and TDO pins.
SAMPLE-Z	If the SAMPLE-Z instruction is loaded in the instruction register, all RAM Q pins are forced to an inactive drive state (high impedance) and the boundary register is connected between TDI and TDO when the TAP controller is moved to the shift-DR state.

JTAG Instruction Coding

IR2	IR1	IR0	Instruction	Note
0	0	0	EXTEST	
0	0	1	IDCODE	
0	1	0	SAMPLE-Z	1
0	1	1	RESERVED	2
1	0	0	SAMPLE / PRELOAD	
1	0	1	RESERVED	2
1	1	0	RESERVED	2
1	1	1	BYPASS	

Notes 1. TRISTATE all Q pins and CAPTURE the pad values into a SERIAL SCAN LATCH.

2. Do not use this instruction code because the vendor uses it to evaluate this product.

Output Pin States of CQ, CQ# and Q

Instructions	Control-Register Status	Output Pin Status	
		CQ, CQ#	Q
EXTEST	0	Update	High-Z
	1	Update	Update
IDCODE	0	SRAM	SRAM
	1	SRAM	SRAM
SAMPLE-Z	0	High-Z	High-Z
	1	High-Z	High-Z
SAMPLE	0	SRAM	SRAM
	1	SRAM	SRAM
BYPASS	0	SRAM	SRAM
	1	SRAM	SRAM

Remark The output pin statuses during each instruction vary according to the Control-Register status (value of Boundary Scan Register, bit no. 48).

There are three statuses:

- Update : Contents of the "Update Register" are output to the output pin (QDR Pad).
- SRAM : Contents of the SRAM internal output "SRAM Output" are output to the output pin (QDR Pad).
- High-Z : The output pin (QDR Pad) becomes high impedance by controlling of the "High-Z JTAG ctrl".

The Control-Register status is set during Update-DR at the EXTEST or SAMPLE instruction.



Boundary Scan Register Status of Output Pins CQ, CQ# and Q

Instructions	SRAM Status	Boundary Scan Register Status		Note
		CQ, CQ#	Q	
EXTEST	READ (Low-Z)	Pad	Pad	
	NOP (High-Z)	Pad	Pad	
IDCODE	READ (Low-Z)	_	_	No definition
	NOP (High-Z)	_	_	
SAMPLE-Z	READ (Low-Z)	Pad	Pad	
	NOP (High-Z)	Pad	Pad	
SAMPLE	READ (Low-Z)	Internal	Internal	
	NOP (High-Z)	Internal	Pad	
BYPASS	READ (Low-Z)	_	_	No definition
	NOP (High-Z)	_	_	

Remark The Boundary Scan Register statuses during execution each instruction vary according to the instruction code and SRAM operation mode.

There are two statuses:

- Pad : Contents of the output pin (QDR Pad) are captured in the "CAPTURE Register" in the Boundary Scan Register.
- Internal : Contents of the SRAM internal output "SRAM Output" are captured in the "CAPTURE Register" in the Boundary Scan Register.



NEC

TAP Controller State Diagram



Disabling the Test Access Port

It is possible to use this device without utilizing the TAP. To disable the TAP Controller without interfering with normal operation of the device, TCK must be tied to Vss to preclude mid level inputs. TDI and TMS may be left open but fix them to V_{DD} via a resistor of about 1 k Ω when the TAP controller is not used. TDO should be left unconnected also when the TAP controller is not used.



Test Logic Operation (Instruction Scan)





Test Logic (Data Scan)

Package Drawing

165-PIN PLASTIC BGA (13x15)



TIEM	DIMENSIONS
D	13.00±0.10
E	15.00±0.10
w	0.15
е	1.00
А	1.40±0.11
A1	0.40±0.05
A2	1.00
b	0.50±0.05
x	0.08
У	0.10
y1	0.20
ZD	1.50
ZE	0.50
	P165F5-100-EQ2

Recommended Soldering Condition

Please consult with our sales offices for soldering conditions of these products.

Types of Surface Mount Devices

μPD44165082AF5-EQ2-A:165-pin PLASTIC BGA (13 x 15)
μPD44165092AF5-EQ2-A:165-pin PLASTIC BGA (13 x 15)
μPD44165182AF5-EQ2-A:165-pin PLASTIC BGA (13 x 15)
μPD44165362AF5-EQ2-A : 165-pin PLASTIC BGA (13 x 15)

Quality Grade

- A quality grade of the products is "Standard".
- Anti-radioactive design is not implemented in the products.
- Semiconductor devices have the possibility of unexpected defects by affection of cosmic ray that reach to the ground and so forth.

[MEMO]

NOTES FOR CMOS DEVICES -----

1 VOLTAGE APPLICATION WAVEFORM AT INPUT PIN

Waveform distortion due to input noise or a reflected wave may cause malfunction. If the input of the CMOS device stays in the area between V_{IL} (MAX) and V_{IH} (MIN) due to noise, etc., the device may malfunction. Take care to prevent chattering noise from entering the device when the input level is fixed, and also in the transition period when the input level passes through the area between V_{IL} (MAX) and V_{IH} (MIN).

(2) HANDLING OF UNUSED INPUT PINS

Unconnected CMOS device inputs can be cause of malfunction. If an input pin is unconnected, it is possible that an internal input level may be generated due to noise, etc., causing malfunction. CMOS devices behave differently than Bipolar or NMOS devices. Input levels of CMOS devices must be fixed high or low by using pull-up or pull-down circuitry. Each unused pin should be connected to V_{DD} or GND via a resistor if there is a possibility that it will be an output pin. All handling related to unused pins must be judged separately for each device and according to related specifications governing the device.

③ PRECAUTION AGAINST ESD

A strong electric field, when exposed to a MOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop generation of static electricity as much as possible, and quickly dissipate it when it has occurred. Environmental control must be adequate. When it is dry, a humidifier should be used. It is recommended to avoid using insulators that easily build up static electricity. Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work benches and floors should be grounded. The operator should be grounded using a wrist strap. Semiconductor devices must have hands. Similar precautions need to be taken for PW boards with mounted semiconductor devices.

④ STATUS BEFORE INITIALIZATION

Power-on does not necessarily define the initial status of a MOS device. Immediately after the power source is turned ON, devices with reset functions have not yet been initialized. Hence, power-on does not guarantee output pin levels, I/O settings or contents of registers. A device is not initialized until the reset signal is received. A reset operation must be executed immediately after power-on for devices with reset functions.

5 POWER ON/OFF SEQUENCE

In the case of a device that uses different power supplies for the internal operation and external interface, as a rule, switch on the external power supply after switching on the internal power supply. When switching the power supply off, as a rule, switch off the external power supply and then the internal power supply. Use of the reverse power on/off sequences may result in the application of an overvoltage to the internal elements of the device, causing malfunction and degradation of internal elements due to the passage of an abnormal current.

The correct power on/off sequence must be judged separately for each device and according to related specifications governing the device.

(6) INPUT OF SIGNAL DURING POWER OFF STATE

Do not input signals or an I/O pull-up power supply while the device is not powered. The current injection that results from input of such a signal or I/O pull-up power supply may cause malfunction and the abnormal current that passes in the device at this time may cause degradation of internal elements. Input of signals during the power off state must be judged separately for each device and according to related specifications governing the device.

NEC

QDR RAMs and Quad Data Rate RAMs comprise a new series of products developed by Cypress Semiconductor, Renesas, IDT, NEC Electronics, and Samsung.

- The information in this document is current as of July, 2009. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC Electronics data sheets, etc., for the most up-to-date specifications of NEC Electronics products. Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Electronics. NEC Electronics assumes no responsibility for any errors that may appear in this document.
- NEC Electronics does not assume any liability for infringement of patents, copyrights or other intellectual
 property rights of third parties by or arising from the use of NEC Electronics products listed in this document
 or any other liability arising from the use of such products. No license, express, implied or otherwise, is
 granted under any patents, copyrights or other intellectual property rights of NEC Electronics or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of a customer's equipment shall be done under the full responsibility of the customer. NEC Electronics assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC Electronics endeavors to enhance the quality and safety of NEC Electronics products, customers
 agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. In addition, NEC
 Electronics products are not taken measures to prevent radioactive rays in the product design. When customers
 use NEC Electronics products with their products, customers shall, on their own responsibility, incorporate
 sufficient safety measures such as redundancy, fire-containment and anti-failure features to their products in
 order to avoid risks of the damages to property (including public or social property) or injury (including death) to
 persons, as the result of defects of NEC Electronics products.
- NEC Electronics products are classified into the following three quality grades: "Standard", "Special" and "Specific".

The "Specific" quality grade applies only to NEC Electronics products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of an NEC Electronics product depend on its quality grade, as indicated below. Customers must check the quality grade of each NEC Electronics product before using it in a particular application.

- "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots.
- "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support).
- "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC Electronics products is "Standard" unless otherwise expressly specified in NEC Electronics data sheets or data books, etc. If customers wish to use NEC Electronics products in applications not intended by NEC Electronics, they must contact an NEC Electronics sales representative in advance to determine NEC Electronics' willingness to support a given application.

(Note)

- (1) "NEC Electronics" as used in this statement means NEC Electronics Corporation and also includes its majority-owned subsidiaries.
- (2) "NEC Electronics products" means any product developed or manufactured by or for NEC Electronics (as defined above).

M8E0904E