

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

**4-BIT SINGLE-CHIP MICROCONTROLLER
FOR INFRARED REMOTE CONTROL TRANSMISSION**

The μ PD6P5 is a microcontroller for infrared remote control transmitters which is provided with a one-time PROM as the program memory.

Because users can write programs for the μ PD6P5, it is ideal for program evaluation and small-scale production of the application systems using the μ PD64A or 65.

When reading this document, also refer to the μ PD64A, 65 Data Sheet (U14380E).

FEATURES

- Program memory (one-time PROM) : $2,026 \times 10$ bits
- Data memory (RAM) : 32×4 bits
- Built-in carrier generation circuit for infrared remote control
- 9-bit programmable timer : 1 channel
- Command execution time : $16 \mu\text{s}$ (when operating at $f_x = 4 \text{ MHz}$: ceramic oscillation)
- Stack level : 1 level (Stack RAM is for data memory RF as well.)
- I/O pins ($K_{I/O}$) : 8 units
- Input pins (K_i) : 4 units
- Sense input pin (S_0, S_2) : 2 units
- $S_1/\overline{\text{LED}}$ pin (I/O) : 1 unit (In output mode, this is the remote control transmission display pin.)
- Power supply voltage : $V_{DD} = 2.2$ to 3.6 V
- Operating ambient temperature : $T_A = -40$ to $+85 \text{ }^\circ\text{C}$
- Oscillator frequency : $f_x = 2.4$ to 4.8 MHz
- POC circuit

APPLICATION

Infrared remote control transmitter (for AV and household electric appliances)

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.
Not all devices/types available in every country. Please check with local NEC representative for availability and additional information.

ORDERING INFORMATION


Part Number	Package
μPD6P5MC-5A4	20-pin plastic SSOP (7.62 mm (300))

PIN CONFIGURATION (TOP VIEW)


20-pin Plastic SSOP (7.62 mm (300))

- μPD6P5MC-5A4

(1) Normal operation mode




(2) PROM programming mode



Caution Round brackets () indicate the pins not used in the PROM programming mode.

L: Connect each of these pins to GND via a pull-down resistor.

BLOCK DIAGRAM



LIST OF FUNCTIONS

Item	μ PD6P5
ROM capacity	2,026 \times 10 bits One-time PROM
RAM capacity	32 \times 4 bits
Stack	1 level (shared with RF of RAM)
I/O pin	<ul style="list-style-type: none"> • Key input (K_i) : 4 pins • Key I/O ($K_{i/o}$) : 8 pins • Key expansion input (S_0, S_1, S_2) : 3 pins • Remote control transmitter display output (\overline{LED}) : 1 pin (shared with S_1 pin)
Number of keys	<ul style="list-style-type: none"> • 32 keys • 56 keys (when expanded by key expansion input)
Clock frequency	Ceramic oscillation <ul style="list-style-type: none"> • $f_x = 2.4$ to 4.8 MHz
Instruction execution time	16 μ s (at $f_x = 4$ MHz)
Carrier frequency	$f_x/8, f_x/16, f_x/64, f_x/96, f_x/128, f_x/192$, no carrier (high level)
Timer	9-bit programmable timer : 1 channel
POC circuit	Provided
Supply voltage	$V_{DD} = 2.2$ to 3.6 V
Operating ambient temperature	<ul style="list-style-type: none"> • $T_A = -40$ to $+85$ °C
Package	<ul style="list-style-type: none"> • 20-pin plastic SSOP (7.62 mm (300))

TABLE OF CONTENTS

1. PIN FUNCTIONS	6
1.1 Normal Operation Mode.....	6
1.2 PROM Programming Mode	7
1.3 INPUT/OUTPUT Circuits of Pins	8
1.4 Dealing with Unused Pins	9
1.5 Notes on Using K ₁ Pin at Reset	9
2. DIFFERENCES AMONG μPD64A, 65, AND μPD6P5	10
2.1 Program Memory (One-time PROM)	11
3. WRITING AND VERIFYING ONE-TIME PROM (PROGRAM MEMORY)	12
3.1 Operation Mode When Writing/Verifying Program Memory	12
3.2 Program Memory Writing Procedure	13
3.3 Program Memory Reading Procedure	14
4. ELECTRICAL SPECIFICATIONS	15
5. CHARACTERISTIC CURVE (REFERENCE VALUES)	21
6. APPLIED CIRCUIT EXAMPLE	22
7. PACKAGE DRAWINGS	23
8. RECOMMENDED SOLDERING CONDITIONS	24
APPENDIX A. DEVELOPMENT TOOLS	25
APPENDIX B. EXAMPLE OF REMOTE-CONTROL TRANSMISSION FORMAT	26

1. PIN FUNCTIONS

1.1 Normal Operation Mode

Pin No.	Symbol	Function	Output Format	When Reset
1 2 15-20	$K_{I/O0}-K_{I/O7}$	These pins refer to the 8-bit I/O ports. I/O switching can be made in 8-bit units. In INPUT mode, a pull-down resistor is added. In OUTPUT mode, they can be used as a key scan output from key matrix.	CMOS push-pull ^{Note 1}	High-level output
3	S_0	Refers to the input port. Can also be used as a key return input from key matrix. In INPUT mode, the availability of the pull-down resistor of the S_0 and S_1 ports can be specified by software in terms in 2-bit units. If INPUT mode is canceled by software, this pin is placed in OFF mode and enters the high-impedance state.	—	High-impedance (OFF mode)
4	S_1/\overline{LED}	Refers to the I/O port. In INPUT mode (S_1), this pin can also be used as a key return input from key matrix. The availability of the pull-down resistor of the S_0 and S_1 ports can be specified by software in 2-bit units. In OUTPUT mode (\overline{LED}), this pin becomes the remote control transmission display output (active low). When the remote control carrier is output from the \overline{REM} output, this pin outputs the low level from the \overline{LED} output synchronously with the \overline{REM} signal.	CMOS push-pull	High-level output (\overline{LED})
5	\overline{REM}	Refers to the infrared remote control transmission output. The output is active high. Carrier frequency: $f_x/8$, $f_x/64$, $f_x/96$, high-level, $f_x/16$, $f_x/128$, $f_x/192$ (usable on software)	CMOS push-pull	Low-level output
6	V_{DD}	Refers to the power supply.	—	—
7 8	X_{OUT} X_{IN}	These pins are connected to system clock ceramic resonators.	—	Low level (oscillation stopped)
9	GND	Refers to the ground.	—	—
10	S_2	Refers to the input port. The use of the STOP mode release of the S_2 port can be specified by software. When using this pin as a key input from a key matrix, enable the use of the STOP mode release (at this time, a pull-down resistor is connected internally.) When the STOP mode release is disabled, this pin can be used as the input port which does not release the STOP mode even if the release condition is established (at this time, a pull-down resistor is not connected internally.)	—	Input (high-impedance, STOP mode release cannot be used)
11-14	$K_{I0}-K_{I3}$ ^{Note 2}	These pins refer to the 4-bit input ports. They can be used as a key return input from key matrix. The use of the pull-down resistor can be specified by software in 4-bit units.	—	Input (low-level)

Notes 1. Note that the drive capability of the low-level output side is held low.

2. In order to prevent malfunction, be sure to input a low level to more than one of pins K_{I0} to K_{I3} when POC is released due to supply voltage startup.


1.2 PROM Programming Mode

Pin No.	Symbol	Function	I/O
1, 2 15-20	D ₀ -D ₇	8-bit data input/output when writing/verifying program memory	I/O
3	CLK	Clock input for updating address when writing/verifying program memory	Input
6	V _{DD}	Power Supply. Supply +6 V to this pin when writing/verifying program memory.	—
7	X _{OUT}	Clock necessary for writing program memory. Connect 4 MHz ceramic resonator to these pins.	—
8	X _{IN}		Input
9	GND	GND	—
10	V _{PP}	Supplies voltage for writing/verifying program memory. Apply +12.5 V to this pin.	—
11-14	MD ₀ -MD ₃	Input for selecting operation mode when writing/verifying program memory.	Input

1.3 INPUT/OUTPUT Circuits of Pins


The input/output circuits of the μ PD6P5 pins are shown in partially simplified forms below.

(1) $K_{I/O0}$ - $K_{I/O7}$




Note The drive capability is held low.


(2) K_{I0} - K_{I3}




(3) REM




(4) S_0



(5) S_1/\overline{LED}



(6) S_2



1.4 Dealing with Unused Pins

The following connections are recommended for unused pins in the normal operation mode.

Table 1-1. Connections for Unused Pins

Pin		Connection	
		Inside the Microcontroller	Outside the Microcontroller
K _{I/O}	INPUT mode	—	Leave open
	OUTPUT mode	High-level output	
REM		—	
S ₁ /LED		OUTPUT mode (LED) setting	Directly connect these pins to GND
S ₀		OFF mode setting	
S ₂		—	
K _I		—	

Caution The I/O mode and the terminal output level are recommended to be fixed by setting them repeatedly in each loop of the program.

1.5 Notes on Using K_I Pin at Reset

In order to prevent malfunction, be sure to input a low level to more than one of pins K_{I0} to K_{I3} when POC is released due to supply voltage startup.

2. DIFFERENCES AMONG μ PD64A, 65, AND μ PD6P5

Table 2-1 shows the differences among the μ PD64A, 65, and μ PD6P5.

The only differences among these models are the program memory, supply voltage, system clock frequency, and oscillation stabilization wait time, and the CPU function and internal peripheral hardware are the same.

The electrical characteristics also differ slightly. For the electrical characteristics, refer to the Data Sheet of each model.

Table 2-1. Differences among μ PD64A, 65, and μ PD6P5

Item	μPD6P5	μPD64A	μPD65
ROM	One-time PROM	Mask ROM	
	2,026 × 10 bits	1,002 × 10 bits	2,026 × 10 bits
Clock frequency	Ceramic oscillation 2.4 to 4.8 MHz	Ceramic oscillation 2.4 to 8 MHz	
Oscillation stabilization wait time			
• On releasing STOP mode by release condition	286/f _x	52/f _x	
• At reset	478/f _x to 926/f _x	246/f _x to 694/f _x	
Supply voltage	V _{DD} = 2.2 to 3.6 V	V _{DD} = 2.0 to 3.6 V	
Electrical specifications	Some electrical specifications, such as data retention voltage and current consumption, differ. For details, refer to Data Sheet of each model.		


2.1 Program Memory (One-time PROM) ... 2,026 steps \times 10 bits

This one-time PROM is configured with 10 bits per step and is addressed by the program counter.

The program memory stores programs and table data.

The 22 steps from addresses 7EAH through 7FFH constitute a test program area and must not be used.

Figure 2-1. Program Memory Map



Note Even if execution jumps to the test program area by mistake, it returns to address 000H.

3. WRITING AND VERIFYING ONE-TIME PROM (PROGRAM MEMORY)

The program memory of the μ PD6P5 is a one-time PROM of $2,026 \times 10$ bits.

To write or verify this program memory, the pins shown in Table 3-1 are used. Note that no address input pin is used. Instead, the address is updated by using the clock input from the CLK pin.

Table 3-1. Pins Used to Write/Verify Program Memory

Pin Name	Function
V _{PP}	Supplies voltage when writing/verifying program memory. Apply +12.5 V to this pin.
V _{DD}	Power supply. Supply +6 V to this pin when writing/verifying program memory.
CLK	Inputs clock to update address when writing/verifying program memory. By inputting pulse four times to CLK pin, address of program memory is updated.
MD ₀ -MD ₃	Input to select operation mode when writing/verifying program memory.
D ₀ -D ₇	Inputs/outputs 8-bit data when writing/verifying program memory.
X _{IN} , X _{OUT}	Clock necessary for writing program memory. Connect 4-MHz ceramic resonator to this pin.

3.1 Operation Mode When Writing/Verifying Program Memory

The μ PD6P5 is set in the program memory write/verify mode when +6 V is applied to the V_{DD} pin and +12.5 V is applied to the V_{PP} pin after the μ PD6P5 has been in the reset status (V_{DD} = 5 V, V_{PP} = 0 V) for a specific time. In this mode, the operation modes shown in Table 3-2 can be set by setting the MD₀ through MD₃ pins. Connect all the pins other than those shown in Table 3-1 to GND via pull-down resistor.

Table 3-2. Setting Operation Mode

Setting of Operation Mode						Operation Mode
V _{PP}	V _{DD}	MD ₀	MD ₁	MD ₂	MD ₃	
+12.5 V	+6 V	H	L	H	L	Clear program address to 0
		L	H	H	H	Write mode
		L	L	H	H	Verify mode
		H	×	H	H	Program inhibit mode


×: don't care (L or H)

3.2 Program Memory Writing Procedure

The program memory is written at high speed in the following procedure.

- (1) Pull down the pins not used to GND via resistor. Keep the CLK pin low.
- (2) Supply 5 V to the V_{DD} pin. Keep the V_{PP} pin low.
- (3) Supply 5 V to the V_{PP} pin after waiting for 10 μ s.
- (4) Wait for 2 ms until oscillation of the ceramic resonator connected across the X_{IN} and X_{OUT} pins stabilizes.
- (5) Set the program memory address 0 clear mode by using the mode setting pins.
- (6) Supply 6 V to V_{DD} and 12.5 V to V_{PP} .
- (7) Set the program inhibit mode.
- (8) Write data to the program memory in the 1-ms write mode.
- (9) Set the program inhibit mode.
- (10) Set the verify mode. If the data have been written to the program memory, proceed to (11). If not, repeat steps (8) through (10).
- (11) Additional writing of (number of times of writing in (8) through (10): X) \times 1 ms.
- (12) Set the program inhibit mode.
- (13) Input a pulse to the CLK pin four times to update the program memory address (+1).
- (14) Repeat steps (8) through (13) up to the last address.
- (15) Set the 0 clear mode of the program memory address.
- (16) Change the voltages on the V_{DD} and V_{PP} pins to 5 V.
- (17) Turn off power.


The following figure illustrates steps (2) through (13) above.



3.3 Program Memory Reading Procedure

- (1) Pull down the pins not used to GND via resistor. Keep the CLK pin low.
- (2) Supply 5 V to the V_{DD} pin. Keep the V_{PP} pin low.
- (3) Supply 5 V to the V_{PP} pin after waiting for 10 μ s.
- (4) Wait for 2 ms until oscillation of the ceramic resonator connected across the X_{IN} and X_{OUT} pins stabilizes.
- (5) Set the program memory address 0 clear mode by using the mode setting pins.
- (6) Supply 6 V to V_{DD} and 12.5 V to V_{PP} .
- (7) Set the program inhibit mode.
- (8) Set the verify mode. Data of each address is output sequentially each time the clock pulse is input to the CLK pin four times.
- (9) Set the program inhibit mode.
- (10) Set the program memory address 0 clear mode.
- (11) Change the voltage on the V_{DD} and V_{PP} pins to 5 V.
- (12) Turn off power.

The following figure illustrates steps (2) through (10) above.



4. ELECTRICAL SPECIFICATIONS

Absolute Maximum Ratings (T_A = +25°C)

Parameter	Symbol	Conditions		Rating	Unit
Power supply voltage	V _{DD}			−0.3 to +7.0	V
	V _{PP}			−0.3 to +13.5	V
Input voltage	V _I	K _{I/O} , K _I , S ₀ , S ₁ , S ₂		−0.3 to V _{DD} + 0.3	V
Output voltage	V _O			−0.3 to V _{DD} + 0.3	V
High-level output current	I _{OH} ^{Note}	REM	Peak value	−30	mA
			rms	−20	mA
		$\overline{\text{LED}}$	Peak value	−7.5	mA
			rms	−5	mA
		One K _{I/O} pin	Peak value	−13.5	mA
			rms	−9	mA
		Total of $\overline{\text{LED}}$ and K _{I/O} pins	Peak value	−18	mA
			rms	−12	mA
Low-level output current	I _{OL} ^{Note}	REM	Peak value	7.5	mA
			rms	5	mA
		$\overline{\text{LED}}$	Peak value	7.5	mA
			rms	5	mA
Operating ambient temperature	T _A			−40 to +85	°C
Storage temperature	T _{stg}			−65 to +150	°C

Note The rms value should be calculated as follows: [rms value] = [Peak value] × $\sqrt{\text{Duty}}$

Caution Product quality may suffer if the absolute maximum rating is exceeded even momentarily for any parameter. That is, the absolute maximum ratings are rated values at which the product is on the verge of suffering physical damage, and therefore the product must be used under conditions that ensure that the absolute maximum ratings are not exceeded.

Recommended Power Supply Voltage Range (T_A = −40 to +85 °C)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Power supply voltage	V _{DD}	f _x = 2.4 to 4.8 MHz	2.2	3.0	3.6	V

DC Characteristics ($T_A = -40$ to $+85$ °C, $V_{DD} = 2.2$ to 3.6 V)

Parameter	Symbol	Conditions		MIN.	TYP.	MAX.	Unit
High-level input voltage	V_{IH1}	S_2		$0.8 V_{DD}$		V_{DD}	V
	V_{IH2}	$K_{I/O}$		$0.65 V_{DD}$		V_{DD}	V
	V_{IH3}	K_I, S_0, S_1		$0.65 V_{DD}$		V_{DD}	V
Low-level input voltage	V_{IL1}	S_2		0		$0.2 V_{DD}$	V
	V_{IL2}	$K_{I/O}$		0		$0.3 V_{DD}$	V
	V_{IL3}	K_I, S_0, S_1		0		$0.15 V_{DD}$	V
High-level input leakage current	I_{LIH1}	K_I $V_I = V_{DD}$, pull-down resistor not incorporated				3	μA
	I_{LIH2}	S_0, S_1, S_2 $V_I = V_{DD}$, pull-down resistor not incorporated				3	μA
Low-level input leakage current	I_{LIL1}	K_I	$V_I = 0$ V			-3	μA
	I_{LIL2}	$K_{I/O}$	$V_I = 0$ V			-3	μA
	I_{LIL3}	S_0, S_1, S_2	$V_I = 0$ V			-3	μA
High-level output voltage	V_{OH1}	REM, \overline{LED} , $K_{I/O}$	$I_{OH} = -0.3$ mA	$0.8 V_{DD}$			V
Low-level output voltage	V_{OL1}	REM, \overline{LED}	$I_{OL} = 0.3$ mA			0.3	V
	V_{OL2}	$K_{I/O}$	$I_{OL} = 15$ μA			0.4	V
High-level output current	I_{OH1}	REM	$V_{DD} = 3.0$ V, $V_{OH} = 1.0$ V	-5	-9		mA
	I_{OH2}	$K_{I/O}$	$V_{DD} = 3.0$ V, $V_{OH} = 2.2$ V	-2.5	-5		mA
Low-level output current	I_{OL1}	$K_{I/O}$	$V_{DD} = 3.0$ V, $V_{OL} = 0.4$ V	30	70		μA
			$V_{DD} = 3.0$ V, $V_{OL} = 2.2$ V	100	220		μA
Built-in pull-down resistor	R_1	K_I, S_0, S_1, S_2		75	150	300	k Ω
	R_2	$K_{I/O}$		130	250	500	k Ω
Data hold power supply voltage	V_{DDDR}	In STOP mode		1.2		3.6	V
Supply current ^{Note}	I_{DD1}	Operating mode	$f_x = 4$ MHz, $V_{DD} = 3$ V ± 10 %		1.1	2.2	mA
	I_{DD2}	HALT mode	$f_x = 4$ MHz, $V_{DD} = 3$ V ± 10 %		1.0	2.0	mA
	I_{DD3}	STOP mode	$V_{DD} = 3$ V ± 10 %		2.2	9.5	μA
			$V_{DD} = 3$ V ± 10 %, $T_A = 25^\circ C$		2.2	3.5	μA

AC Characteristics ($T_A = -40$ to $+85$ °C, $V_{DD} = 2.2$ to 3.6 V)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Instruction execution time	t_{CY}		13.3		27	μs
K1, S0, S1, S2 high-level width	t_H		10			μs
		When canceling standby mode				
		HALT mode	10			μs
		STOP mode	Note			μs

Note $10 + 286/f_x$ + oscillation growth time

Remark $t_{CY} = 64/f_x$ (f_x : System clock oscillator frequency)

POC Circuit ($T_A = -40$ to $+85$ °C)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
POC-detected voltage ^{Note}	V_{POC}			2.0	2.2	V


Note Refers to the voltage with which the POC circuit cancels an internal reset. If $V_{POC} < V_{DD}$, the internal reset is canceled.

From the time of $V_{POC} \geq V_{DD}$ until the internal reset takes effect, lag of up to 1 ms occurs. When the period of $V_{POC} \geq V_{DD}$ lasts less than 1 ms, the internal reset may not take effect.

System Clock Oscillator Characteristics ($T_A = -40$ to $+85$ °C, $V_{DD} = 2.2$ to 3.6 V)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Oscillator frequency (ceramic resonator)	f_x		2.4	3.64	4.8	MHz

An external circuit example



Remark For the resonator selection and oscillator constant, customers are required to either evaluate the oscillation themselves or apply to the resonator manufacturer for evaluation.

PROM Programming Mode**DC Programming Characteristics ($T_A = 25^\circ\text{C}$, $V_{DD} = 6.0 \pm 0.25 \text{ V}$, $V_{PP} = 12.5 \pm 0.3 \text{ V}$)**

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
High-level input voltage	V_{IH1}	Other than CLK	$0.7 V_{DD}$		V_{DD}	V
	V_{IH2}	CLK	$V_{DD} - 0.5$		V_{DD}	V
Low-level input voltage	V_{IL1}	Other than CLK	0		$0.3 V_{DD}$	V
	V_{IL2}	CLK	0		0.4	V
Input leakage current	I_{LI}	$V_{IN} = V_{IL} \text{ or } V_{IH}$			10	μA
High-level output voltage	V_{OH}	$I_{OH} = -1 \text{ mA}$	$V_{DD} - 1.0$			V
Low-level output voltage	V_{OL}	$I_{OL} = 1.6 \text{ mA}$			0.4	V
V_{DD} supply current	I_{DD}				30	mA
V_{PP} supply current	I_{PP}	$MD_0 = V_{IL}, MD_1 = V_{IH}$			30	mA


- Cautions**
1. Keep V_{PP} to within +13.5 V including overshoot.
 2. Apply V_{DD} before V_{PP} and turn it off after V_{PP} .

AC Programming Characteristics ($T_A = 25^\circ\text{C}$, $V_{DD} = 6.0 \pm 0.25\text{ V}$, $V_{PP} = 12.5 \pm 0.3\text{ V}$)


Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Address setup time ^{Note 1} (vs. $MD_0\downarrow$)	t_{AS}		2			μs
MD_1 setup time (vs. $MD_0\downarrow$)	t_{M1S}		2			μs
Data setup time (vs. $MD_0\downarrow$)	t_{DS}		2			μs
Address hold time ^{Note 1} (vs. $MD_0\uparrow$)	t_{AH}		2			μs
Data hold time (vs. $MD_0\uparrow$)	t_{DH}		2			μs
$MD_0\uparrow \rightarrow$ data output float delay time	t_{DF}		0		130	ns
V_{PP} setup time (vs. $MD_3\uparrow$)	t_{VPS}		2			μs
V_{DD} setup time (vs. $MD_3\uparrow$)	t_{VDS}		2			μs
Initial program pulse width	t_{PW}		0.95	1.0	1.05	ms
Additional program pulse width	t_{OPW}		0.95		21.0	ms
MD_0 setup time (vs. $MD_1\uparrow$)	t_{MOS}		2			μs
$MD_0\downarrow \rightarrow$ data output delay time	t_{DV}	$MD_0 = MD_1 = V_{IL}$			1	μs
MD_1 hold time (vs. $MD_0\uparrow$)	t_{M1H}	$t_{M1H} + t_{M1R} \geq 50\text{ }\mu\text{s}$	2			μs
MD_1 recovery time (vs. $MD_0\downarrow$)	t_{M1R}		2			μs
Program counter reset time	t_{PCR}		10			μs
CLK input high-, low-level width	t_{XH}, t_{XL}		0.125			μs
CLK input frequency	f_X				4.19	MHz
Initial mode set time	t_i		2			μs
MD_3 setup time (vs. $MD_1\uparrow$)	t_{M3S}		2			μs
MD_3 hold time (vs. $MD_1\downarrow$)	t_{M3H}		2			μs
MD_3 setup time (vs. $MD_0\downarrow$)	t_{M3SR}	When program memory is read	2			μs
Address ^{Note 1} \rightarrow data output delay time	t_{DAD}	When program memory is read			2	μs
Address ^{Note 1} \rightarrow data output hold time	t_{HAD}	When program memory is read	0		130	ns
MD_3 hold time (vs. $MD_0\uparrow$)	t_{M3HR}	When program memory is read	2			μs
$MD_3\downarrow \rightarrow$ data output float delay time	t_{DFR}	When program memory is read			2	μs
Reset setup time	t_{RES}		10			μs
Oscillation stabilization wait time ^{Note 2}	t_{WAIT}		2			ms

- Notes**
1. The internal address signal is incremented at the falling edge of the third clock of CLK.
 2. Connect a 4 MHz ceramic resonator between the X_{IN} and X_{OUT} pins.







Program Memory Write Timing



Program Memory Read Timing




5. CHARACTERISTIC CURVE (REFERENCE VALUES)



6. APPLIED CIRCUIT EXAMPLE


Example of Application to System

- Remote-control transmitter (48 keys; mode selection switch accommodated)




Note S₂: Set this pin to disable when releasing STOP mode.

- Remote-control transmitter (56 keys accommodated)



7. PACKAGE DRAWINGS

20-PIN PLASTIC SSOP (7.62 mm (300))



NOTE

Each lead centerline is located within 0.13 mm of its true position (T.P.) at maximum material condition.

ITEM	MILLIMETERS
A	6.65±0.15
B	0.475 MAX.
C	0.65 (T.P.)
D	0.24 ^{+0.08} _{-0.07}
E	0.1±0.05
F	1.3±0.1
G	1.2
H	8.1±0.2
I	6.1±0.2
J	1.0±0.2
K	0.17±0.03
L	0.5
M	0.13
N	0.10
P	3° ^{+5°} _{-3°}
T	0.25
U	0.6±0.15

S20MC-65-5A4-2

8. RECOMMENDED SOLDERING CONDITIONS

Carry out the soldered packaging of this product under the following recommended conditions.

For details of the soldering conditions, refer to information material **Semiconductor Device Mounting Technology Manual (C10535E)**.

For soldering methods and conditions other than the recommended conditions, please consult one of our NEC sales representatives.

Table 8-1. Soldering Conditions for Surface-Mount Type

μ PD6P5MC-5A4: 20-pin plastic SSOP (7.62 mm (300))

Soldering Method	Soldering Condition	Recommended Condition Symbol
Infrared reflow	Package peak temperature: 235 °C, Time: 30 sec. Max. (at 210 °C or higher), Count: three times or less	IR35-00-3
VPS	Package peak temperature: 215 °C, Time: 40 sec. Max. (at 200 °C or higher), Count: three times or less	VP15-00-3
Wave soldering	Solder bath temperature: 260 °C Max., Time: 10 sec. Max., Count: once, Preheating temperature: 120 °C Max. (package surface temperature)	WS60-00-1
Partial heating	Pin temperature: 300 °C Max., Time: 3 sec. Max. (per pin row)	—

Caution Do not use different soldering methods together (except for partial heating).

APPENDIX A. DEVELOPMENT TOOLS

A PROM programmer, program adapter, and emulator are provided for the μPD6P5.

Hardware

- **PROM programmer (AF-9706^{Note}, AF-9708^{Note}, AF-9709^{Note})**

This PROM programmer supports the μPD6P5.

By connecting a program adapter to this PROM programmer, the μPD6P5 can be programmed.

Note These are products of Ando Electric Co., Ltd. For details, consult Ando Electric Co., Ltd. (03-3733-1166).

- **Program adapter (PA-61P34BMC)**

It is used to program the μPD6P5 in combination with AF-9706, AF-9708, or AF-9709.

- **Emulator (EB-65^{Note})**

It is used to emulate the μPD6P5.

Note This is a product of Naito Densai Machida Mfg. Co., Ltd. For details, consult Naito Densai Machida Mfg. Co., Ltd. (044-822-3813).

Software

- **Assembler (AS6133)**

- This is a development tool for remote control transmitter software.

Part Number List of AS6133

Host Machine	OS	Supply Medium	Part Number
PC-9800 series (CPU: 80386 or more)	MS-DOS™ (Ver. 5.0 to Ver. 6.2)	3.5-inch 2HD	μS5A13AS6133
IBM PC/AT™ compatible	MS-DOS (Ver. 6.0 to Ver. 6.22)	3.5-inch 2HC	μS7B13AS6133
	PC DOS™ (Ver. 6.1 to Ver. 6.3)		


Caution Although Ver.5.0 or later has a task swap function, this function cannot be used with this software.

APPENDIX B. EXAMPLE OF REMOTE-CONTROL TRANSMISSION FORMAT

(in the case of NEC transmission format in command one-shot transmission mode)


Caution When using the NEC transmission format, please apply for a custom code at NEC.

(1) REM output waveform (From <2> on, the output is made only when the key is kept pressed.)




Remark If the key is repeatedly pressed, the power consumption of the infrared light-emitting diode (LED) can be reduced by sending the reader code and the stop bit from the second time.


(2) Enlarged waveform of <1>




(3) Enlarged waveform of <3>




(4) Enlarged waveform of <2>



(5) Carrier waveform (Enlarged waveform of each code's high period)



(6) Bit array of each code



Caution To prevent malfunction with other systems when receiving data in the NEC transmission format, not only fully decode (make sure to check Data code as well) the total 32 bits of the 16-bit custom codes (Custom code, Custom code') and the 16-bit data codes (Data code, Data code) but also check to make sure that no signals are present.

[MEMO]

[MEMO]

NOTES FOR CMOS DEVICES**① PRECAUTION AGAINST ESD FOR SEMICONDUCTORS**

Note:

Strong electric field, when exposed to a MOS device, can cause destruction of the gate oxide and ultimately degrade the device operation. Steps must be taken to stop generation of static electricity as much as possible, and quickly dissipate it once, when it has occurred. Environmental control must be adequate. When it is dry, humidifier should be used. It is recommended to avoid using insulators that easily build static electricity. Semiconductor devices must be stored and transported in an anti-static container, static shielding bag or conductive material. All test and measurement tools including work bench and floor should be grounded. The operator should be grounded using wrist strap. Semiconductor devices must not be touched with bare hands. Similar precautions need to be taken for PW boards with semiconductor devices on it.

② HANDLING OF UNUSED INPUT PINS FOR CMOS

Note:

No connection for CMOS device inputs can be cause of malfunction. If no connection is provided to the input pins, it is possible that an internal input level may be generated due to noise, etc., hence causing malfunction. CMOS devices behave differently than Bipolar or NMOS devices. Input levels of CMOS devices must be fixed high or low by using a pull-up or pull-down circuitry. Each unused pin should be connected to V_{DD} or GND with a resistor, if it is considered to have a possibility of being an output pin. All handling related to the unused pins must be judged device by device and related specifications governing the devices.

③ STATUS BEFORE INITIALIZATION OF MOS DEVICES

Note:

Power-on does not necessarily define initial status of MOS device. Production process of MOS does not define the initial operation status of the device. Immediately after the power source is turned ON, the devices with reset function have not yet been initialized. Hence, power-on does not guarantee out-pin levels, I/O settings or contents of registers. Device is not initialized until the reset signal is received. Reset operation must be executed immediately after power-on for devices having reset function.

Regional Information

Some information contained in this document may vary from country to country. Before using any NEC product in your application, please contact the NEC office in your country to obtain a list of authorized representatives and distributors. They will verify:

- Device availability
- Ordering information
- Product release schedule
- Availability of related technical literature
- Development environment specifications (for example, specifications for third-party tools and components, host computers, power plugs, AC supply voltages, and so forth)
- Network requirements

In addition, trademarks, registered trademarks, export restrictions, and other legal issues may also vary from country to country.

NEC Electronics Inc. (U.S.)

Santa Clara, California
Tel: 408-588-6000
800-366-9782
Fax: 408-588-6130
800-729-9288

NEC Electronics (Germany) GmbH

Duesseldorf, Germany
Tel: 0211-65 03 02
Fax: 0211-65 03 490

NEC Electronics (UK) Ltd.

Milton Keynes, UK
Tel: 01908-691-133
Fax: 01908-670-290

NEC Electronics Italiana s.r.l.

Milano, Italy
Tel: 02-66 75 41
Fax: 02-66 75 42 99

NEC Electronics (Germany) GmbH

Benelux Office
Eindhoven, The Netherlands
Tel: 040-2445845
Fax: 040-2444580

NEC Electronics (France) S.A.

Velizy-Villacoublay, France
Tel: 01-30-67 58 00
Fax: 01-30-67 58 99

NEC Electronics (France) S.A.

Spain Office
Madrid, Spain
Tel: 91-504-2787
Fax: 91-504-2860

NEC Electronics (Germany) GmbH

Scandinavia Office
Taeby, Sweden
Tel: 08-63 80 820
Fax: 08-63 80 388

NEC Electronics Hong Kong Ltd.

Hong Kong
Tel: 2886-9318
Fax: 2886-9022/9044

NEC Electronics Hong Kong Ltd.

Seoul Branch
Seoul, Korea
Tel: 02-528-0303
Fax: 02-528-4411

NEC Electronics Singapore Pte. Ltd.

United Square, Singapore 1130
Tel: 65-253-8311
Fax: 65-250-3583

NEC Electronics Taiwan Ltd.

Taipei, Taiwan
Tel: 02-2719-2377
Fax: 02-2719-5951

NEC do Brasil S.A.

Electron Devices Division
Rodovia Presidente Dutra, Km 214
07210-902-Guarulhos-SP Brasil
Tel: 55-11-6465-6810
Fax: 55-11-6465-6829

MS-DOS is either a registered trademark or a trademark of Microsoft Corporation in the United States and/or other countries.

PC/AT and PC DOS are trademarks of IBM Corporation.

The export of this product from Japan is regulated by the Japanese government. To export this product may be prohibited without governmental license, the need for which must be judged by the customer. The export or re-export of this product from a country other than Japan may also be prohibited without a license from that country. Please call an NEC sales representative.

- **The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version.**
 - No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Corporation. NEC Corporation assumes no responsibility for any errors which may appear in this document.
 - NEC Corporation does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from use of a device described herein or any other liability arising from use of such device. No license, either express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Corporation or others.
 - Descriptions of circuits, software, and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software, and information in the design of the customer's equipment shall be done under the full responsibility of the customer. NEC Corporation assumes no responsibility for any losses incurred by the customer or third parties arising from the use of these circuits, software, and information.
 - While NEC Corporation has been making continuous effort to enhance the reliability of its semiconductor devices, the possibility of defects cannot be eliminated entirely. To minimize risks of damage or injury to persons or property arising from a defect in an NEC semiconductor device, customers must incorporate sufficient safety measures in its design, such as redundancy, fire-containment, and anti-failure features.
 - NEC devices are classified into the following three quality grades:
 "Standard", "Special", and "Specific". The Specific quality grade applies only to devices developed based on a customer designated "quality assurance program" for a specific application. The recommended applications of a device depend on its quality grade, as indicated below. Customers must check the quality grade of each device before using it in a particular application.
 - Standard: Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots
 - Special: Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support)
 - Specific: Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems or medical equipment for life support, etc.
- The quality grade of NEC devices is "Standard" unless otherwise specified in NEC's Data Sheets or Data Books. If customers intend to use NEC devices for applications other than those specified for Standard quality grade, they should contact an NEC sales representative in advance.