

EVB-RTP100E2P6G1FL

Low-Voltage GaN RTP100E2P6G1FL

Description

The EVB-RTP100E2P6G1FL evaluation board is a synchronous buck converter, which contains two Renesas low-voltage GaNs (RTP100E2P6G1FL) in a half-bridge configuration driven by Renesas gate driver. The low-voltage GaNs are 2.6m Ω 100V enhancement-mode Gallium Nitride (GaN) FET in a 5x6 FCLGA package. Its footprint is compatible with standard silicon counterparts. The RRP68150 gate driver is a high-frequency, half-bridge driver designed specifically for enhancement mode GaN FETs.

The buck converter has a DC48V input, a DC12V output, a maximum output power of 330W, and operates between 250kHz and 500kHz switching frequencies. The dimension of the evaluation board is 53x53mm.

The evaluation board allows users to evaluate the electrical performance of the Renesas low-voltage GaN, including how to optimize the circuit board to enable a high-efficiency and high-power density board capable of operating at high frequencies. The board has some test points for easy measurement of the low-voltage GaN switching waveforms and energy efficiency.

Features

- Highly flexible and user-friendly buck converter evaluation board
- Performance testing of the Renesas low-voltage GaN over a wide range of V_{in} , V_{out} , F_{sw} , and P_{out}
- Experience system performance using Renesas gate driver, RRP68150



Figure 1. EVB-RTP100E2P6G1FL Evaluation Board

Contents

1. Functional Description	3
1.1 Overview	3
1.2 Renesas GaN FET (RTP100E2P6G1FL)	4
1.3 Renesas Gate Driver (RRP68150)	4
2. Board Features	6
2.1 Input PWM Signal	6
2.2 Duty Cycle	6
2.3 Dead Time	7
2.4 Split-Gate Output	8
3. Test Setup	9
3.1 Setup Procedure	9
3.2 Power-On Procedure	10
4. Test Results	12
4.1 Energy Efficiency and Power Loss	12
4.2 Thermal Performance	13
4.3 Switching Node Voltage Waveforms	14
5. Board Design	15
5.1 Board Schematic	15
5.2 Bill of Materials	17
6. Ordering Information	18
7. Revision History	18

1. Functional Description

1.1 Overview

The evaluation board's circuitry is divided into four parts as shown in Figure 3. The first part is a DC5V regulator, which provides a stable and accurate DC5V voltage to the PWM and gate drive circuits. The second part is the PWM and dead-time control circuits. It converts the single square wave signal provided by the signal generator into two independent signals to drive the high-side and low-side GaNs, while adding an appropriate dead time to prevent shoot-through. The third part is the gate driver, which provides 2A sourcing and 5.3A sinking peak current for the GaN devices switching. The last part is the power stage (two GaN devices RTP100E2P6G1FL, an inductor, and some input/output capacitors), which is the core part of the entire board, and is responsible for converting DC48V to DC12V.



Figure 2. EVB-RTP100E2P6G1FL




Figure 3. Block Diagram of the Buck Converter




Figure 4. Top (Left) and Bottom (Right) Views

Table 1. EVB Product Specification

Input (V)	DC48V typ. ~ DC80V (80% GaN-FET rated voltage)
Output (V)	DC12V typ. ~ DC16V (Maximum output capacitor rated voltage)
Output (A)	28A maximum
Switching Frequency	250KHz ~ 500KHz
Auxiliary Power Supply	DC9 ~ 12V
Renesas GaN FET	RTP100E2P6G1FL
Renesas Gate Driver	RRP68150

1.2 Renesas GaN FET (RTP100E2P6G1FL)

The RTP100E2P6G1FL 100V, 2.6m Ω is an enhancement mode Gallium Nitride (GaN) FET in 5x6 FCLGA package using Renesas' Gen I REXGaN® platform. Using advanced packaging technology, these devices deliver high-speed switching and enhanced thermal performance. Designed with footprint compatibility to standard silicon counterparts, the devices simplify the transition to GaN technology.

Features:

- Ultra-fast switching E-mode GaN HEMT
- JEDEC-qualified GaN technology
- Package footprint compatible to Si counterpart
- Low static losses
- Simplified thermal design
- Zero reverse recovery charge
- Low gate charge and output charge




Figure 5. RTP100E2P6G1FL and Schematic Symbol

V_{DS} (V)	100
$R_{DS(ON)}$ (m Ω) Typical	2.6
Q_{OSS} (nC)	46
Q_G (nC)	9.4
Q_{rr} (nC)	0

1.3 Renesas Gate Driver (RRP68150)

The RRP68150 gate driver is a 5V-powered, high-frequency half-bridge driver for enhancement mode GaN FETs and low-threshold N-channel MOSFETs. It features 2A source and 5.3A sink current capability with its switching node supporting up to 100V DC. The driver's PWM inputs are 3.3/5V CMOS logic-compatible and can tolerate input voltages up to 14V, independent of the VDD supply voltage. The high-side bias voltage is generated using a bootstrap technique and is internally clamped at 5.4V. This clamping action prevents the gate voltage from

exceeding the maximum gate-source voltage rating of the GaN FET. Its 5V operational supply enables convenient supply sharing with the controller.




Figure 6. Pin Assignments WLCSP12-2x2 – Top View




Figure 7. Typical Application

2. Board Features

2.1 Input PWM Signal

The evaluation board requires an input PWM signal to set the switching frequency and adjust the duty cycle to obtain the desired output voltage value. The PWM signal must be a square waveform, 0V for low-level signal and 5V (maximum 6.5V) for high-level signal. The input signal is connected to connector CN5. Figure 8 shows the connector (Type SMA-KE) and Figure 9 is an example of the PWM signal.




Figure 8. SMA-KE Connector




Figure 9. Input PWM Signal

2.2 Duty Cycle

The evaluation board is a buck converter, so the duty cycle can be calculated using the following formula. As the input voltage is DC48V, output voltage is DC12V. The calculated duty cycle is 0.25. In real applications, the actual duty cycle is higher than the calculated value due to power loss. To adjust the duty cycle, set the other output voltages within 0 to 16V (16V is the maximum output capacitor rated voltage).

$$D = \frac{V_{out}}{V_{in}}$$

2.3 Dead Time

Synchronous buck converters consist of high-side and low-side GaNs. If the dead time is not set correctly, it may lead to a shoot-through. To prevent this, set a reasonable time according to the GaN FET's switching behavior and PCB layout optimization. If the design is correct, it is recommended to set the dead time between 5ns and 15ns. It can effectively reduce the power loss without shoot-through.

Resistor R3 sets the dead time of the high-side GaN FET, and resistor R4 sets the dead time of the low-side GaN FET (see Figure 10 and Figure 11). The required resistance value can be calculated using the formula in the figure.




Figure 10. Resistors R3 and R4




Figure 11. Resistor R3 and R4 Dead Time

2.4 Split-Gate Output

The gate driver on the evaluation board features split-gate outputs with strong sink capability, enabling independent control of turn-on and turn-off drive strength for optimized switching performance. In the schematic diagram in Figure 12, resistors R11 and R12 control the on/off state of the high-side GaN Q1, while R13 and R14 control the on/off state of the low-side GaN Q2.

Users can adjust these four resistor values according to the buck converter's design parameters, such as switching frequency, input/output voltage values, and output power level, to control the drain-source voltage and gate-source voltage overshoot issues of the GaN FET.




Figure 12. Gate Drive Resistors

3. Test Setup

3.1 Setup Procedure

1. Turn off the power before connecting any device.
2. Connect a signal generator to SMA-KE connector CN5 as shown in item 1 of [Figure 13](#).
3. Connect a DC9~12V power supply with a current limit of 0.5A to terminal J2 as shown in item 2.
4. Connect a DC48V power supply with a current limit of 9A to connectors CN1(+) and CN2(-) as shown in item 3.
5. Connect a DC voltage meter to TP1(+) and TP2(-) to measure input voltage as shown in item 4.
6. Connect an electronic load to connectors CN3(+) and CN4(-) for output load current measurement and TP3(+) and TP4(-) for output voltage measurement as shown in item 5.




Figure 13. Setup Key

7. Place an axial fan (NMB: 4710PS-22T-B30) 13cm from the evaluation board and provide an air flow of 63.5 CFM as shown in item 6 of [Figure 14](#).




Figure 14. Axial Fan Airflow

3.2 Power-On Procedure

1. Complete the [Setup Procedure](#).
2. Set up the PWM signal on the signal generator as shown in [Figure 15](#), then turn on the PWM signal to the board.
 - Square wave
 - Vlow: 0V
 - Vhigh: 5V(typ), 6.5V(max)
 - Duty cycle: 0.25
 - Switching frequency: 250KHz




Figure 15. PWM Signal

3. Turn on the auxiliary power supply and adjust the output voltage to DC9V or DC12V. The Vgs voltage waveform of the low-side GaN FET Q2 is shown in [Figure 16](#).




Figure 16. Vgs Voltage Waveform

There are two methods for measuring the Vgs switching waveform. The first method is to directly measure the component traces using a passive probe as shown in [Figure 17](#). Use a spring clip to get a small ground loop. The second method is to measure the switching waveform using the MMCX jack at CN7 as shown in [Figure 18](#) (the jack at CN7 is not provided).




Figure 17. Passive Probe




Figure 18. MMCX Jack

4. Making sure the initial main power supply voltage is 0V, turn on the power and slowly increase the voltage to DC48V. The Vds voltage waveform of the low-side GaN FET Q2 is shown in the Figure 19. The same methods can be used to measure the Vds voltage at Q2 as shown in Figure 20 and Figure 21.




Figure 19. Vds Voltage Waveform




Figure 20. Passive Probe




Figure 21. MMCX Jack

5. When the output voltage of the buck converter reaches DC12V, the output load current can be increased gradually to check the switching behavior, energy efficiency, and other parameters.
6. For the shut-down procedure, follow the steps in reverse.

4. Test Results

4.1 Energy Efficiency and Power Loss

Test conditions:

- Input voltage was measured at TP1(+) and TP2(-).
- Output voltage was measured at TP3(+) and TP4(-).
- The energy efficiency was tested at an airflow of 63.5 CFM.
- The distance between evaluation board and axial fan is 13cm.




Figure 22. Axial Fan Layout

Figure 23 and Figure 24 show the energy efficiency and power loss results of the circuit board at three different switching frequencies (250KHz, 350KHz, 500KHz). Input voltage is DC48V. Output voltage is DC12V. Output current is 28A maximum. Inductor is 2.2uH Wurth 74436410220.




Figure 23. Energy Efficiency at Different Output Currents and Switching Frequencies




Figure 24. Power Loss at Different Output Currents and Switching Frequencies

4.2 Thermal Performance

Table 2 shows the maximum output current that the GaNs can achieve at around 100°C, with and without airflow, and at different switching frequencies. Thermistors were used to test the temperature of the components.

Table 2. Component Temperature

Switching Frequency	No Axial Fan				Axial Fan NMB: 4710PS-22T-B30, CFM 63.5			
	Max. OP Current	Component Temp. at 25 °C			Max. OP Current	Component Temp. at 25 °C		
		HS GaN	LS GaN	L1		HS GaN	LS GaN	L1
250KHz	19.0A	99.0 °C	99.5 °C	84.4 °C	29.5A	98.9 °C	98.6 °C	59.0 °C
500KHz	14.8A	103.0 °C	90.3 °C	70.4 °C	23.0A	101.2 °C	84.7 °C	49.7 °C

Figure 25 shows the measurement location. An axial fan was used in the thermal test the same test setup as measuring the energy efficiency.




Figure 25. Measurement Location

4.3 Switching Node Voltage Waveforms

Figure 26 shows the switching node waveforms (low-side GaN Q2 Vds voltage) at an input of DC48V, an output of DC12V 28A, and a switching frequency of 250KHz. The Vds voltage was measured 55.8Vpeak, which is far away from the maximum rating of 100V Vdss voltage. Another important value is slew rate. It must be optimized so that you can balance between the efficiency and the EMI compliance.




Figure 26. Switching Node Waveforms

5. Board Design

5.1 Board Schematic




Figure 27. Board Schematic




Figure 28. PCB Layout

PCB specification:

- PCB file name: AD29R4
- Size: 53x53mm.
- Thickness: 1.6mm
- Material: FR4, 2oz for all layers

5.2 Bill of Materials

Table 3. Bill of Materials

Item	Qty	Reference	Part Description	Manufacturer	Part Number
1	2	C1, C2	47pF, 50V, NPO, 0402		
2	4	C3, C4, C7, C8	0.1uF, 25V, X7R, 0402		
3	4	C5, C6, C12, C13	100pF, 50V, NPO, 0402		
4	1	C9	1uF, 25V, X7R, 0603		
5	1	C10	2.2uF, 16V, X7R, 0603		
6	1	C14	4.7uF, 10V, X5R, 0402		
7	1	C15	2.2uF, 16V, X7R, 0603		
8	5	C11, C16, C17, C18, C19	10uF, 100V, X7S, 1210		
9	10	C20, C21, C22, C23, C24, C25, C26, C27, C28, C29	22uF, 16V, X7R, 1206		
10	10	C30, C31, C32, C33, C34, C35, C36, C37, C38, C39	220nF, 100V, X7R, 0603		
11	4	CN1, CN2, CN3, CN4	Connector	Keystone	7701
12	1	CN5	Connector	Kinghelm	KH-SMA-KE-Z
13	0	CN6, CN7	MMCX Jack	Molex	734152063
14	2	D2, D3	40 V 30 mA	ST	BAT54KFILM
15	1	L1	2.2uH	Würth	74436410220
16	2	Q1, Q2	100V, 2.6mΩ, LV-GaN	Renesas	RTP100E2P6G1FL
17	6	R1, R2, R6, R7, R9, R10	10K, 1%, 0402		
18	1	R3	130Ω, 1%, 0603		
19	1	R4	180Ω, 1%, 0603		
20	2	R5, R8	2.2Ω, 5%, 0402		
21	1	R11	3.6Ω, 1%, 0402		
22	2	R12, R14	1Ω, 0402		
23	1	R13	4.7Ω, 1%, 0402		
24	2	U1, U2	SN74LVC1G86DCKR	TI	SN74LVC1G86DCKR
25	2	U3, U4	SN74LVC1G57DCKR	TI	SN74LVC1G57DCKR
26	1	U6	100V, 2A Source, 5.3A Sink, 5V-Powered High-Frequency GaN/MOSFET Half-Bridge Drivers with Anti-Shoot-Through Protection	Renesas	RRP68150
27	1	U7	5.0 V 250 mA DFN	Microchip	MCP1703T-5002E/MC
28	1	PCB	Size: 53x53mmx1.6mm, 4 layers, 2oz	JDB	AD29R4
29	4	M1, M2, M3, M4	M3*10+6, Nylon, Hex Standoff, White		
30	0	D1, J1, J2,	No components		
31	0	TP1, TP2, TP3, TP4	No components		

6. Ordering Information

Part Number	Description
EVB-RTP100E2P6G1FL	Low-voltage GaN RTP100E2P6G1FL Evaluation Board

7. Revision History

Revision	Date	Description
1.00	Sep 2, 2026	Initial release

IMPORTANT NOTICE AND DISCLAIMER

RENESAS ELECTRONICS CORPORATION AND ITS SUBSIDIARIES ("RENESAS") PROVIDES TECHNICAL SPECIFICATIONS AND RELIABILITY DATA (INCLUDING DATASHEETS), DESIGN RESOURCES (INCLUDING REFERENCE DESIGNS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, SAFETY INFORMATION, AND OTHER RESOURCES "AS IS" AND WITH ALL FAULTS, AND DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT OF THIRD-PARTY INTELLECTUAL PROPERTY RIGHTS.

These resources are intended for developers who are designing with Renesas products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards, and any other safety, security, or other requirements. These resources are subject to change without notice. Renesas grants you permission to use these resources only to develop an application that uses Renesas products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Renesas intellectual property or to any third-party intellectual property. Renesas disclaims responsibility for, and you will fully indemnify Renesas and its representatives against, any claims, damages, costs, losses, or liabilities arising from your use of these resources. Renesas' products are provided only subject to Renesas' Terms and Conditions of Sale or other applicable terms agreed to in writing. No use of any Renesas resources expands or otherwise alters any applicable warranties or warranty disclaimers for these products.

(Disclaimer Rev.1.01)

Corporate Headquarters

TOYOSU FORESIA, 3-2-24 Toyosu,
Koto-ku, Tokyo 135-0061, Japan
www.renesas.com

Contact Information

For further information on a product, technology, the most up-to-date version of a document, or your nearest sales office, please visit www.renesas.com/contact-us/.

Trademarks

Renesas and the Renesas logo are trademarks of Renesas Electronics Corporation. All trademarks and registered trademarks are the property of their respective owners.