Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1st, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.

Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anticrime systems; safety equipment; and medical equipment not specifically designed for life support.
 - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majorityowned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



User's Manual

IE-703204-G1-EM1

Emulation Board

Target Devices V850ES/SA2 V850ES/SA3

Document No. U16622EJ1V0UM00 (1st edition) Date Published September 2003 N CP(K)

© NEC Electronics Corporation 2003 Printed in Japan [MEMO]

Windows is either a trademark or a registered trademark of Microsoft Corporation in the United States and/or other countries.

PC/AT is a trademark of International Business Machines Corporation.

- The information in this document is current as of March, 2003. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC Electronics data sheets or data books, etc., for the most up-to-date specifications of NEC Electronics products. Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without the prior written consent of NEC Electronics. NEC Electronics assumes no responsibility for any errors that may appear in this document.
- NEC Electronics does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC Electronics products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Electronics or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of a customer's equipment shall be done under the full responsibility of the customer. NEC Electronics assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC Electronics endeavors to enhance the quality, reliability and safety of NEC Electronics products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC Electronics products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment and anti-failure features.
- NEC Electronics products are classified into the following three quality grades: "Standard", "Special" and "Specific".

The "Specific" quality grade applies only to NEC Electronics products developed based on a customerdesignated "quality assurance program" for a specific application. The recommended applications of an NEC Electronics product depend on its quality grade, as indicated below. Customers must check the quality grade of each NEC Electronics product before using it in a particular application.

- "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots.
- "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support).
- "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC Electronics products is "Standard" unless otherwise expressly specified in NEC Electronics data sheets or data books, etc. If customers wish to use NEC Electronics products in applications not intended by NEC Electronics, they must contact an NEC Electronics sales representative in advance to determine NEC Electronics' willingness to support a given application.

(Note)

- (1) "NEC Electronics" as used in this statement means NEC Electronics Corporation and also includes its majority-owned subsidiaries.
- (2) "NEC Electronics products" means any product developed or manufactured by or for NEC Electronics (as defined above).

Regional Information

Some information contained in this document may vary from country to country. Before using any NEC Electronics product in your application, please contact the NEC Electronics office in your country to obtain a list of authorized representatives and distributors. They will verify:

- · Device availability
- Ordering information
- Product release schedule
- · Availability of related technical literature
- Development environment specifications (for example, specifications for third-party tools and components, host computers, power plugs, AC supply voltages, and so forth)
- Network requirements

In addition, trademarks, registered trademarks, export restrictions, and other legal issues may also vary from country to country.

[GLOBAL SUPPORT] http://www.necel.com/en/support/support.html

NEC Electronics America, Inc. (U.S.)NEC Electronics (Europe) GmbHNEC Electronics Hong Kong Ltd.Santa Clara, CaliforniaDuesseldorf, GermanyHong KongTel: 408-588-6000
800-366-9782Tel: 0211-65 03 01Tel: 2886-9318• Sucursal en España

- Madrid, Spain Tel: 091-504 27 87
- Succursale Française Vélizy-Villacoublay, France Tel: 01-30-675800
- Filiale Italiana Milano, Italy Tel: 02-66 75 41
- Branch The Netherlands Eindhoven, The Netherlands Tel: 040-244 58 45
- Tyskland Filial Taeby, Sweden Tel: 08-63 80 820
- United Kingdom Branch Milton Keynes, UK Tel: 01908-691-133

NEC Electronics Hong Kong Ltd. Seoul Branch Seoul, Korea Tel: 02-558-3737

NEC Electronics Shanghai, Ltd. Shanghai, P.R. China Tel: 021-6841-1138

NEC Electronics Taiwan Ltd. Taipei, Taiwan Tel: 02-2719-2377

NEC Electronics Singapore Pte. Ltd. Novena Square, Singapore Tel: 6253-8311

INTRODUCTION

Target Readers		for users who design and develop application systems nd V850ES/SA3 microcontrollers.
Purpose	The purpose of this man 703204-G1-EM1 and its p	nual is to describe the basic specifications of the IE- proper operation.
Organization	This manual is broadly divOutlinePart names and functionSetup procedure	vided into the following parts. • Cautions • Restrictions
How to Read This Manual	 It is assumed that the reader of this manual has general knowledge in the fields of electrical engineering, logic circuits, and microcontrollers. Use the IE-703204-G1-EM1 connected to the in-circuit emulator (IE-V850ES-G1). This manual describes the basic setup procedures and switch settings of the IE-703204-G1-EM1 and IE-V850ES-G1. For the part names, functions, and configuration parts of the IE-V850ES-G1, refer to the IE-V850ES-G1 User's Manual (U16313E) provided separately. To learn about the basic specifications and operation →Read this manual in the order listed in CONTENTS. To learn software settings such as the operation methods, command functions, etc., of the IE-V850ES-G1 or IE-703204-G1-EM1 →Read the user's manual of the debugger (sold separately) that is used. 	
Conventions	Note: Caution: Remark: Numeral representation: Prefix representing a pow	Footnote for item marked with Note in the text Information requiring particular attention Supplementary information Binary $\cdots \times \times \times \times$ or $\times \times \times B$ Decimal $\cdots \times \times \times \times$ Hexadecimal $\cdots \times \times \times \times H$ rer of 2 (address space, memory capacity): K (kilo): $2^{10} = 1024$ M (mega): $2^{20} = 1024^2$
Terminology	The meanings of terms us	sed in this manual are listed below.

Target device	This is the device to be emulated.
Target system	The system (user-built system) to be debugged. This includes the target program and hardware configured by the user.
Emulation CPU	The CPU that executes the program created by the user in the emulator.

Related DocumentsWhen using this manual, refer to the following manuals.The related documents (user's manuals) indicated in this publication may include
preliminary versions. However, preliminary versions are not marked as such.

Documents Related to Development Tools (User's Manuals)

Document Name		Document Number
IE-V850ES-G1 (In-Circuit Emulator for V850ES)		U16313E
IE-703204-G1-EM1 (Emulation Board for V850ES/S	SA2, V850ES/SA3)	This manual
V850ES/SA2, V850ES/SA3 Hardware		U15905E
CA850 Ver.2.50 C Compiler Package	Operation	U16053E
	C Language	U16054E
	Assembly Language	U16042E
PM Plus Ver. 5.10		U16559E
ID850 Ver.2.50 Integrated Debugger	Operation Windows [™] based	U16217E
SM850 Ver.2.50 System Simulator	Operation Windows based	U16218E
SM850 Ver.2.00 or Later System Simulator	External Part User Open Interface Specifications	U14873E
RX850 Ver.3.13 or Later (Real-Time OS)	Basics	U13430E
	Installation	U13410E
Technical		U13431E
RX850 Pro Ver.3.13 (Real-Time OS)	Basics	U13773E
	Installation	U13774E
	Technical	U13772E
RD850 Ver.3.01 Task Debugger		U13737E
RD850 Pro Ver.3.01 Task Debugger		U13916E
AZ850 Ver.3.10 System Performance Analyzer		U14410E
PG-FP4 Flash Memory Programmer		U15260E

Caution The related documents listed above are subject to change without notice.

Be sure to use the latest version of each document when designing.

CONTENTS

CHAPTER 1 OUTLINE	10
1.1 Product Configuration	11
1.2 Features (When Connected to IE-V850ES-G1)	12
1.3 Function Specifications (When Connected to IE-V850ES-G1)	13
1.4 System Configuration	14
1.5 Contents in Carton	16
CHAPTER 2 PART NAMES AND FUNCTIONS	17
2.1 Part Names and Functions of IE-703204-G1-EM1	17
2.2 LEDs Controlled by IE-703204-G1-EM1	19
CHAPTER 3 SETUP PROCEDURE	20
3.1 Connecting IE-V850ES-G1 and IE-703204-G1-EM1 with Probe	20
3.2 Replacing Resonator	23
CHAPTER 4 CAUTIONS	24
4.1 Connection with Target System	24
4.2 Characteristics of Target Interface	24
CHAPTER 5 RESTRICTIONS	34
5.1 Clock Generator	34
5.2 Timing of Setting/Releasing Standby Mode	34
5.3 DMA	34
5.4 Operation During Break	34
APPENDIX A PACKAGE DRAWINGS	35

LIST OF FIGURES

Figure N	0.	Title	Page
1-1	System Configuration		14
1-2	Contents in Carton		16
2-1	Part Names of IE-703204-G1-EM1		17
2-2	LEDs Controlled by IE-703204-G1-EM1		19
4-1	Equivalent Circuit A		24
4-2	Equivalent Circuit B		24
4-3	Equivalent Circuit C		25
4-4	Equivalent Circuit D		25
4-5	Equivalent Circuit E		25
4-6	Equivalent Circuit F		
4-7	Equivalent Circuit G		
4-8	Equivalent Circuit H		
4-9	Equivalent Circuit I		
4-10	Equivalent Circuit J		
4-11	Equivalent Circuit K		27
4-12	Equivalent Circuit L		

LIST OF TABLES

Figure No	. Title	Page
4-1	Pin Correspondence List (V850ES/SA2 Pin Names)	28
4-2	Pin Correspondence List (V850ES/SA3 Pin Names)	31


CHAPTER 1 OUTLINE

The IE-703204-G1-EM1 is an emulation board for the IE-V850ES-G1 in-circuit emulator.

Connected to the IE-V850ES-G1, the IE-703204-G1-EM1 can be used for efficient hardware and software debugging during system development using the V850ES/SA2 and V850ES/SA3.

This manual describes the basic setup procedure and the switch settings of the IE-V850ES-G1 when connected to the IE-703204-G1-EM1. For the part names and functions of the IE-V850ES-G1, refer to the separate **IE-V850ES-G1 User's Manual (U16313E)**.

1.1 Product Configuration



1.2 Features (When Connected to IE-V850ES-G1)

- Maximum operating frequency: 20 MHz (2.2 V to 2.7 V)
- The following pins can be masked. NMI, WAIT, RESET, HLDRQ
- The external dimensions of the IE-703204-G1-EM1 are listed below

Item		Value
External dimensions	Height	35 mm
	Width	205 mm
	Depth	140 mm

Item		Specification
Emulation memory capacity	Internal ROM	1 MB
	For user memory	4 MB
Execution/pass detection coverage memory capacity	Internal ROM	256 KB
	External memory	1 MB
Memory access detection coverage memory capacity	External memory	1 MB
Branch destination entry count calculation coverage	Internal ROM	256 KB
memory capacity	External memory	1 MB
Trace memory capacity		168 bits × 32 K frames
Time measurement function		Internal timers × 3
External logic probe		8-bit external trace possible
		Trace/break event setting possible
Break function		Event break
		Step execution break
		Forced break
		Fail-safe break • Illegal access to peripheral I/O • Access to guard area • Write to ROM area


1.3 Function Specifications (When Connected to IE-V850ES-G1)

Caution Some functions may not be supported depending on the debugger that is used.

1.4 System Configuration

The system configuration when using the IE-703204-G1-EM1 connected to the IE-V850ES-G1, which itself is connected to a PC (PC-9800 series or PC/AT[™] compatible) is shown below.





Remarks <1>: PC (PC-9800 series or PC/AT compatible)

- <2>: Debugger (sold separately), device file (obtained separately)^{Note 1}
- <3>: PC interface board (IE-70000-PCI-IF(-A), IE-70000-CD-IF-A: Sold separately)
- <4>: PC interface cable (supplied with IE-V850ES-G1: Sold separately)
- <5>: IE-V850ES-G1 (sold separately)
- <6>: Emulation board (this product)
- <7>: Probe^{Note 2} (SWEX-120SE-1: Sold separately)
- <8>: Probe^{Note 2} (SWEX-100SD-1: Sold separately)
- <9>: CSICE121A1312N03^{Note 2} (sold separately)
- <10>: LSPACK121A1312N01^{Note 2} (sold separately)
- <11>: CSSOCKET121A1312N01^{Note 2} (sold separately) or CSSOCKET121A1312N01N^{Note 2} (sold separately) (CSSOCKET121A1312N01S1^{Note 2} (sold separately) can be used for stacking.) CSSOCKET121A1312N01N is a type with no guide pins.
- <12>: YQPACK100SD^{Note 2} (supplied with this product)


- <13>: NQPACK100SD^{Note 2} (supplied with this product)
- <14>: YQGUIDE^{Note 2} (supplied with this product)
- <15>: Power supply cable (supplied with IE-V850-G1: Sold separately)
- Notes 1. The device file can be downloaded from the NEC Electronics website. (URL: http://www.necel.com/micro)
 - **2.** These are products of TOKYO ELETECH CORPORATION.


For further information, contact Daimaru Kogyo Co., Ltd.

Tokyo Electronics Department (TEL: +81-3-3820-7112) Osaka Electronics Department (TEL: +81-6-6244-6672)

1.5 Contents in Carton

The IE-703204-G1-EM1 package contains the IE-703204-G1-EM1 emulation board, a guarantee card, a packing list, this manual, and an accessory bag. Check whether the accessory bag contains the items listed below. If you find any missing or damaged items, contact an NEC Electronics sales representative or distributor.





Check whether the accessory bag contains the following items in addition to this manual and the packing list (× 1).


(a)	7-pin header (for resonator replacement)	:: × 1
(b)	NQPACK100SD (for mounting board):	× 1
	YQPACK100SD (for mounting probe):	× 1
	HQPACK100SD (for mounting IC):	× 1
	YQ-GUIDE (guide pin):	× 4
(c)	Screws/washers:	6 sets (6 screws + 6 washers are included)

CHAPTER 2 PART NAMES AND FUNCTIONS

This chapter describes the part names and functions of the IE-703204-G1-EM1.

For the part names and functions of the IE-V850ES-G1, refer to the IE-V850ES-G1 User's Manual (U16313E).

2.1 Part Names and Functions of IE-703204-G1-EM1





(1) Socket for connecting SWEX-100SD-1

Connect the SWEX-100SD-1 when using the IE-703204-G1-EM1 as the emulator of the V850ES/SA2.

(2) Socket for connecting SWEX-120SE-1

Connect the SWEX-120SE-1 when using the IE-703204-G1-EM1 as the emulator of the V850ES/SA3.

(3) OSC1 (main clock)

This is the socket in which the resonator that generates the main clock is mounted. Use this socket when replacing the resonator for the main clock. For details, refer to **3.2 Resonator Replacement**.


(4) OSC2 (subclock)

This is the socket in which the resonator that generates the subclock is mounted. The frequency of the subclock is fixed to 32.768 kHz, so the resonator for subclock cannot be replaced.

2.2 LEDs Controlled by IE-703204-G1-EM1

Some of the LEDs mounted in the IE-V850ES-G1 are controlled by the IE-703204-G1-EM1. For the LEDs that are controlled by the IE-V850ES-G1, refer to the **IE-V850ES-G1 User's Manual (U16313E)**.





(1) Reset LED

The status of the $\overrightarrow{\text{RESET}}$ signal connected to the target system is indicated as follows.

Lit (ON): The target system is connected and the RESET signal is active (GND level).

Unlit (OFF): Either the target system is not connected, or the RESET signal is inactive (VDD level).

(2) Target VDD supply voltage <1>

The status of the V_{DD} signal connected to the target system is indicated as follows. (This LED indicates the status of pin 11 during V850ES/SA2 emulation, and the status of the F3 pin during V850ES/SA3 emulation.)

Lit (ON): The target system is connected, and voltage is being applied to the VDD pin.

Unlit (OFF): Either the target system is not connected, or voltage is not being applied to the VDD pin.

(3) Target VDD supply voltage <2>

The status of the V_{DD} signal connected to the target system is indicated as follows.

(This LED indicates the status of pin 19 during V850ES/SA2 emulation, and the status of the H2 pin during V850ES/SA3 emulation.)

Lit (ON): The target system is connected and voltage is being applied to the VDD pin.

Unlit (OFF): Either the target system is not connected, or voltage is not being applied to the VDD pin.


CHAPTER 3 SETUP PROCEDURE

This chapter describes how to connect the IE-703204-G1-EM1 to related products and how to replace the resonator.


3.1 Connecting IE-V850ES-G1 and IE-703204-G1-EM1 with Probe

The following shows the procedure to connect the IE-V850ES-G1 and IE-703204-G1-EM1 with the probe.

<1> Pull off the front cover of the IE-V850ES-G1.




<2> Raise the frame of the IE-V850ES-G1 as shown.




<3> With the main board and the IE-703204-G1-EM1 aligned as shown, insert three connectors on each side. At this time align the board so that the socket (YQSOCKET) to connect the prove faces towards the probe exit side.


Insert the probe (SWEX-100SD-1 or SWEX-120SE-1) in the socket corresponding to the target device (refer to the following figure).



<4> Slowly lower the frame of the IE-V850ES-G1.



<5> Replace the front cover of the IE-V850ES-G1.




3.2 Replacing Resonator

<u>The IE-703204-G1-EM1 does not support clock oscillation by the resonator on the target system</u>. Therefore, to change the main clock frequency, replace the resonator mounted in OSC1 (main clock) on the IE-703204-G1-EM1 with a resonator with the desired frequency. After shipment, the following oscillators are mounted as oscillators for generating each clock.

Item	Setting	
OSC1 (main clock)	20 MHz oscillator	
OSC2 (subclock)	32.768 kHz oscillator	

To change the main clock frequency, mount the resonator and capacitor on the included 7-pin header as shown and substitute it for the 7-pin header already mounted on OSC1 (main clock).



The frequency of the subclock is fixed to 32.768 kHz, so the resonator for the subclock cannot be replaced. The IE-703204-G1-EM1 does not support clock oscillation by the resonator on the target system. Therefore, operation between the resonator on the target system and the oscillator in the target device cannot be emulated using the IE-703204-G1-EM1.

CHAPTER 4 CAUTIONS

The following must be observed when using the IE-703204-G1-EM1.

4.1 Connection with Target System

Turn off power to the IE-V850ES-G1 before connecting the IE-703204-G1-EM1 to the target system.

4.2 Characteristics of Target Interface

The target interface (signals connecting the in-circuit emulator and the target system) functionally operates as if an actual device is connected, however, the characteristics may be different than those of the actual device. The target interface of the IE-703204-G1-EM1 is one of those shown in Figures 4-1 to 4-12. The target interface processing of each target device is shown in Tables 4-1 and 4-2.

Figure 4-1. Equivalent Circuit A

Target system side	IE system side
0	Port μPD70F3204Y pin Emulation CPU

Figure 4-2. Equivalent Circuit B





Figure 4-3. Equivalent Circuit C









Figure 4-5. Equivalent Circuit E



Note Conducts only when the target system is connected.

Figure 4-6. Equivalent Circuit F





Figure 4-7. Equivalent Circuit G











Figure 4-9. Equivalent Circuit I










Figure 4-11. Equivalent Circuit K







V850ES/SA2 Pin No.	Target Interface Name (V850ES/SA2 Pin Names)	Processing in In-Circuit Emulator
1	AV _{REF0}	Emulation circuit E
2	AV _{DD}	Emulation circuit I
3	AVss	Emulation circuit K
4	P80/ANO0	Emulation circuit A
5	P81/ANO1	Emulation circuit A
6	AV _{REF1}	Emulation circuit E
7	P00/NMI	Emulation circuit A
8	P30/SI1/RXD0	Emulation circuit A
9	P31/SO1/TXD0	Emulation circuit A
10	P32/SCK1	Emulation circuit A
11	V _{DD}	Emulation circuit A
12	Vss	Emulation circuit K
13	X1	Emulation circuit L
14	X2	Emulation circuit L
15	RESET	Emulation circuit D
16	XT1	Emulation circuit L
17	XT2	Emulation circuit L
18	V _{DD}	Emulation circuit G
19	Vss	Emulation circuit K
20	P90/A0	Emulation circuit C
21	P91/A1	Emulation circuit C
22	P92/A2/INTP5	Emulation circuit C
23	P93/A3/INTP6	Emulation circuit C
24	P94/A4/TO2	Emulation circuit C
25	P95/A5/TO3	Emulation circuit C
26	P96/A6/TO4	Emulation circuit C
27	P97/A7/TO5	Emulation circuit C
28	P98/A8/RXD1	Emulation circuit C
29	P99/A9/TXD1	Emulation circuit C
30	P910/A10/SI2	Emulation circuit C
31	P911/A11/SO2	Emulation circuit C
32	P912/A12/SCK2	Emulation circuit C
33	P913/A13/SI3	Emulation circuit C
34	P914/A14/SO3	Emulation circuit C
35	P915/A15/SCK3	Emulation circuit C
36	EVss	Emulation circuit K
37	EVDD	Emulation circuit I
38	PCS0/CS0	Emulation circuit B
39	PCS1/CS1	Emulation circuit B
40	PCS2/CS2	Emulation circuit B

Table 4-1. Pin Correspondence List (V850ES/SA2 Pin Names) (1/3)

V850ES/SA2 Pin No.	Target Interface Name (V850ES/SA2 Pin Names)	Processing in In-Circuit Emulator
41	PCS3/CS3	Emulation circuit B
42	PCM0/WAIT	Emulation circuit B
43	PCM1/CLKOUT	Emulation circuit B
44	PCM2/HLDAK	Emulation circuit B
45	PCM3/HLDRQ	Emulation circuit B
46	PCT0/WR0	Emulation circuit B
47	PCT1/WR1	Emulation circuit B
48	PCT4/RD	Emulation circuit B
49	PCT5	Emulation circuit B
50	PCT6/ASTB	Emulation circuit B
51	PCT7	Emulation circuit B
52	PDL0/AD0	Emulation circuit B
53	PDL1/AD1	Emulation circuit B
54	PDL2/AD2	Emulation circuit B
55	PDL3/AD3	Emulation circuit B
56	PDL4/AD4	Emulation circuit B
57	PDL5/AD5/FLMD1	Emulation circuit B
58	PDL6/AD6	Emulation circuit B
59	PDL7/AD7	Emulation circuit B
60	PDL8/AD8	Emulation circuit B
61	PDL9/AD9	Emulation circuit B
62	IC/FLMD0	Emulation circuit B
63	EVss	Emulation circuit K
64	EVDD	Emulation circuit I
65	PDL10/AD10	Emulation circuit B
66	PDL11/AD11	Emulation circuit B
67	PDL12/AD12	Emulation circuit B
68	PDL13/AD13	Emulation circuit B
69	PDL14/AD14	Emulation circuit B
70	PDL15/AD15	Emulation circuit B
71	PDH0/A16	Emulation circuit B
72	PDH1/A17	Emulation circuit B
73	PDH2/A18	Emulation circuit B
74	PDH3/A19	Emulation circuit B
75	PDH4/A20	Emulation circuit B
76	PDH5/A21	Emulation circuit B
77	P40/SI0	Emulation circuit A
78	P41/SO0/SDA	Emulation circuit A
79	P42/SCK0/SCL	Emulation circuit A
80	P43/INTP00/TI0/TCLR0	Emulation circuit A

Table 4-1. Pin Correspondence List (V850ES/SA2 Pin Names) (2/3)

V850ES/SA2 Pin No.	Target Interface Name (V850ES/SA2 Pin Names)	Processing in In-Circuit Emulator
81	P44/INTP01/TO0	Emulation circuit A
82	P45/INTP10/TI1/TCLR1	Emulation circuit A
83	P46/INTP11/TO1	Emulation circuit A
84	P01/INTP0/TI2	Emulation circuit A
85	P02/INTP1/TI3	Emulation circuit A
86	P03/INTP2/TI4	Emulation circuit A
87	P04/INTP3/TI5	Emulation circuit A
88	P05/INTP4	Emulation circuit A
89	P711/ANI11	Emulation circuit A
90	P710/ANI10	Emulation circuit A
91	P79/ANI9	Emulation circuit A
92	P78/ANI8	Emulation circuit A
93	P77/ANI7	Emulation circuit A
94	P76/ANI6	Emulation circuit A
95	P75/ANI5	Emulation circuit A
96	P74/ANI4	Emulation circuit A
97	P73/ANI3	Emulation circuit A
98	P72/ANI2	Emulation circuit A
99	P71/ANI1	Emulation circuit A
100	P70/ANI0	Emulation circuit A

Table 4-1. Pin Correspondence List (V850ES/SA2 Pin Names) (3/3)

V850ES/SA3 Pin No.	Target Interface Name (V850ES/SA3 Pin Names)	Processing in In-Circuit Emulator
A1	P70/ANI0	Emulation circuit A
A2	P71/ANI1	Emulation circuit A
A3	P73/ANI3	Emulation circuit A
A4	P713/ANI13	Emulation circuit A
A5	P76/ANI6	Emulation circuit A
A6	P78/ANI8	Emulation circuit A
A7	P711/ANI11	Emulation circuit A
A8	P04/INTP3/TI5	Emulation circuit A
A9	PCD2	Emulation circuit B
A10	P45/INTP10/TI1/TCLR1	Emulation circuit A
A11	P43/INTP00/TI0/TCLR0	Emulation circuit A
A12	P41/SO0/SDA	Emulation circuit A
A13	PDH5/A21	Emulation circuit B
B1	AV _{DD}	Emulation circuit I
B2	AVREFO	Emulation circuit E
B3	P72/ANI2	Emulation circuit A
B4	P712/ANI12	Emulation circuit A
B5	P75/ANI5	Emulation circuit A
B6	P77/ANI7	Emulation circuit A
B7	P710/ANI10	Emulation circuit A
B8	PCD3	Emulation circuit B
B9	P02/INTP1/TI3	Emulation circuit A
B10	P46/INTP11/TO1	Emulation circuit A
B11	P42/SCK0/SCL	Emulation circuit A
B12	P40/SI0	Emulation circuit A
B13	PDH4/A20	Emulation circuit B
C1	P80/ANO0	Emulation circuit A
C2	AVss	Emulation circuit K
C3	P74/ANI4	Emulation circuit A
C4	P714/ANI14	Emulation circuit A
C5	P715/ANI15	Emulation circuit A
C6	P79/ANI9	Emulation circuit A
C7	P05/INTP4[/ADTRG]	Emulation circuit A
C8	P03/INTP2/TI4	Emulation circuit A
C9	PCD1	Emulation circuit B
C10	P01/INTP0/TI2	Emulation circuit A
C11	P44/INTP01/TO0	Emulation circuit A
C12	PDH3/A19	Emulation circuit B
C13	PDH7/A23	Emulation circuit H
D1	P81/ANO1	Emulation circuit A
D2	AV _{REF1}	Emulation circuit E

Table 4-2. Pin Correspondence List (V850ES/SA3 Pin Names) (1/3)

V850ES/SA3	Target Interface Name	Processing in In-Circuit
Pin No. D3	(V850ES/SA3 Pin Names) P00/NMI	Emulator Emulation circuit A
		Emulation circuit A
D4	N.C.	
D11	PDH0/A16	Emulation circuit B
D12	PDH2/A18	Emulation circuit B
D13	PDH1/A17	Emulation circuit B
E1	P30/SI1/RXD0	Emulation circuit A
E2	P31/SO1/TXD0	Emulation circuit A
E3	P32/SCK1	Emulation circuit A
E11	PDL14/AD14	Emulation circuit B
E12	PDH6/A22	Emulation circuit H
E13	PDL15/AD15	Emulation circuit B
F1	Vss	Emulation circuit K
F2	X1	Emulation circuit L
F3	V _{DD}	Emulation circuit F
F11	PDL11/AD11	Emulation circuit B
F12	PDL13/AD13	Emulation circuit B
F13	PDL12/AD12	Emulation circuit B
G1	RESET	Emulation circuit D
G2	XT1	Emulation circuit L
G3	X2	Emulation circuit L
G11	EVss	Emulation circuit K
G12	PDL10/AD10	Emulation circuit B
G13	EVDD	Emulation circuit I
H1	Vss	Emulation circuit K
H2	V _{DD}	Emulation circuit G
H3	XT2	Emulation circuit L
H11	PDL8/AD8	Emulation circuit B
H12	MODE/FLMD0	Emulation circuit B
H13	PDL9/AD9	Emulation circuit B
J1	P20/SI4	Emulation circuit A
J2	P91/A1	Emulation circuit C
J3	P90/A0	Emulation circuit C
J11	PDL5/AD5/FLMD1	Emulation circuit B
J12	PDL7/AD7	Emulation circuit B
J13	PDL6/AD6	Emulation circuit B
K1	P22/SCK4	Emulation circuit A
K2	P92/A2/INTP5	Emulation circuit C
K3	P21/SO4	Emulation circuit A
K11	PCM1/CLKOUT	Emulation circuit A
K12	PDL4/AD4	Emulation circuit B

Table 4-2. Pin Correspondence List (V850ES/SA3 Pin Names) (2/3)

V850ES/SA3 Pin No.	Target Interface Name (V850ES/SA3 Pin Names)	Processing in In-Circuit Emulator
K13	PDL3/AD3	Emulation circuit B
L1	P93/A3/INTP6	Emulation circuit C
L2	P94/A4/TO2	Emulation circuit C
L3	P911/A11/SO2	Emulation circuit C
L4	P914/A14/SO3	Emulation circuit C
L5	P915/A15/SCK3	Emulation circuit C
L6	EVDD	Emulation circuit I
L7	PCS0/CS0	Emulation circuit B
L8	PCS2/CS2	Emulation circuit B
L9	PCM4	Emulation circuit H
L10	PCT2	Emulation circuit H
L11	PCT0/WR0	Emulation circuit B
L12	PDL1/AD1	Emulation circuit B
L13	PDL2/AD2	Emulation circuit B
M1	P95/A5/TO3	Emulation circuit C
M2	P97/A7/TO5	Emulation circuit C
МЗ	P99/A9/TXD1	Emulation circuit C
M4	P913/A13/SI3	Emulation circuit C
M5	EVss	Emulation circuit K
M6	PCS5	Emulation circuit H
M7	PCS4	Emulation circuit H
M8	PCM0/WAIT	Emulation circuit B
M9	PCM2/HLDAK	Emulation circuit B
M10	PCT3	Emulation circuit H
M11	PCT4/RD	Emulation circuit B
M12	PCT7	Emulation circuit B
M13	PDL0/AD0	Emulation circuit B
N1	P96/A6/TO4	Emulation circuit C
N2	P98/A8/RXD1	Emulation circuit C
N3	P910/A10/SI2	Emulation circuit C
N4	P912/A12/SCK2	Emulation circuit C
N5	PCS7	Emulation circuit H
N6	PCS6	Emulation circuit H
N7	PCS1/CS1	Emulation circuit B
N8	PCS3/CS3	Emulation circuit B
N9	PCM5	Emulation circuit H
N10	PCM3/HLDRQ	Emulation circuit B
N11	PCT1/WR1	Emulation circuit B
N12	PCT5	Emulation circuit B
N13	PCT6/ASTB	Emulation circuit B

Table 4-2. Pin Correspondence List (V850ES/SA3 Pin Names) (3/3)

CHAPTER 5 RESTRICTIONS

The IE-703204-G1-EM1 has the following restrictions.

5.1 Clock Generator

(1) Resonator to be connected

Oscillation by the resonator on the target system is not supported. Therefore, clock oscillation operation on the target system cannot be emulated with the in-circuit emulator.

- (2) Emulation of oscillation stabilization time after reset has been released In the target device for emulation, oscillation stabilization time is inserted after reset has been released; however, it is not inserted in the in-circuit emulator.
- (3) Operation clock after reset

In the target device for emulation, the operation clock after reset is fxx/8; however, there may be a period in which the clock is not initialized to fxx/8 with the in-circuit emulator (depending on the timing of reset release).

5.2 Timing of Setting/Releasing Standby Mode

The timing of setting/releasing the standby mode is different between the target device and the in-circuit emulator. The difference is within 1 clock when standby mode is set, and 2 or 3 clocks when it is released.

5.3 DMA


The status of the DCHC0 to DCHC3 registers of the DMA function vary when read; however, these registers cannot be displayed by the I/O register browser of the debugger.

5.4 Operation During Break


In the in-circuit emulator, peripheral functions operate during a break, so there may be a difference between the operations of the in-circuit emulator and target device.


(However, while the in-circuit emulator is in the break status, the counter of the watchdog timer stops.)

- TOP VIEW □21.0 0.5 X 24 = 12.0 R2.2 C 1.5 5.8 0.5 0.3 ი Slit width \oplus \oplus □16.6 □13.0 □20.2 5.8 $\frac{1}{\sqrt{3-\phi_{1.0}}}$ <u>□14</u>.0^{+ 0.1} 2.5 2.5 SIDE VIEW 3.9 5.5 5.1 9.45 ŝ 1.85 0.18 3 0.50 0.5 15.0 BOTTOM VIEW □17.0 □9.0 \oplus_\oplus Œ \oplus □ 16.0 □ 15.0 0.14.0 Slit width \oplus \oplus \oplus 0.2 $/4 - \phi 2.0$ Projection height 1.8
- (1) NQPACK100SD (unit: mm)





(2) YQPACK100SD (unit: mm)






(3) HQPACK100SD (unit: mm)






(4) CSICE121A1312N03 (unit: mm)






(5) LSPACK121A1312N01 (unit: mm)




Remark LSPACK121A1312N01 is a product of TOKYO ELETECH CORPORATION.

(6) CSSOCKET121A1312N01 (unit: mm)




Remark CSSOCKET121A1312N01 is a product of TOKYO ELETECH CORPORATION.

(7) CSSOCKET121A1312N01N (unit: mm)




Remark CSSOCKET121A1312N01N is a product of TOKYO ELETECH CORPORATION.

(8) CSSOCKET121A1312N01S1 (unit: mm)




Remark CSSOCKET121A1312N01S1 is a product of TOKYO ELETECH CORPORATION.


(9) CSSOCKET121A1312N01 (foot pattern) (unit: mm)




Remark CSSOCKET121A1312N01 is a product of TOKYO ELETECH CORPORATION.

(10) SWEX-100SD-1 (unit: mm)





(11) SWEX-120SE-1 (unit: mm)



Remark SWEX-120SE-1 is a product of TOKYO ELETECH CORPORATION.