



## TEST REPORT

Test report no.: 1-8868/19-01-03



### Testing laboratory

#### CTC advanced GmbH

Untertuerkheimer Strasse 6 – 10

66117 Saarbruecken / Germany

Phone: + 49 681 5 98 - 0

Fax: + 49 681 5 98 - 9075

Internet: <http://www.ctcadvanced.com>

e-mail: [mail@ctcadvanced.com](mailto:mail@ctcadvanced.com)

#### Accredited Testing Laboratory:

The testing laboratory (area of testing) is accredited according to DIN EN ISO/IEC 17025 (2005) by the Deutsche Akkreditierungsstelle GmbH (DAkkS)

The accreditation is valid for the scope of testing procedures as stated in the accreditation certificate with the registration number: D-PL-12076-01-03

### Applicant

#### Dialog Semiconductor BV

Het Zuiderkruis 53

5215 MV's Hertogenbosch / NETHERLANDS

Phone: -/-

Contact: Laura Dimitropoulou

e-mail: [Laura.Dimitropoulou@diasemi.com](mailto:Laura.Dimitropoulou@diasemi.com)

Phone: +30 2610 462406

### Manufacturer

#### Dialog Semiconductor BV

Het Zuiderkruis 53

5215 MV's Hertogenbosch / NETHERLANDS

### Test standard/s

ETSI EN 300 328  
V2.2.2

Wideband transmission systems; Data transmission equipment operating in the  
2,4 GHz band; Harmonised Standard for access to radio spectrum

For further applied test standards please refer to section 3 of this test report.

### Test Item

**Kind of test item:** Bluetooth LE SoC  
**Model name:** DA14531 (QFN)  
**Frequency:** ISM band 2400 MHz to 2483.5 MHz  
**Technology tested:** Bluetooth® LE  
**Antenna:** Integrated Printed Inverted F antenna  
**Power supply:** 3.0 V DC by external power supply  
**Temperature range:** -40°C to +85°C



This test report is electronically signed and valid without handwritten signature. For verification of the electronic signatures, the public keys can be requested at the testing laboratory.

### Test report authorized:

Andreas Luckenbill  
Lab Manager  
Radio Communications & EMC

### Test performed:

p.o.

Mihail Dorongovskij  
Lab Manager  
Radio Communications & EMC

## 1 Table of contents

1	Table of contents .....	2
2	General information .....	3
2.1	Notes and disclaimer .....	3
2.2	Application details .....	3
2.3	Test laboratories sub-contracted .....	3
3	Test standard/s .....	4
4	Test environment .....	4
5	Test item .....	5
5.1	General description .....	5
5.2	Additional information .....	5
6	Description of the test setup.....	6
6.1	Shielded fully anechoic chamber.....	7
6.2	Conducted measurements Bluetooth system .....	8
7	Summary of measurement results .....	9
8	Additional comments .....	10
9	EUT classification .....	11
10	Measurement results .....	12
10.1	Antenna gain.....	12
10.2	RF output power .....	13
10.3	Power spectral density .....	14
10.4	Occupied channel bandwidth .....	15
10.5	Transmitter unwanted emissions in the out-of-band domain .....	16
10.6	Transmitter unwanted emissions in the spurious domain.....	18
10.7	Receiver spurious emissions .....	22
10.8	Receiver blocking .....	25
11	Measurement uncertainty.....	27
Annex A	Glossary.....	28
Annex B	Document history .....	29
Annex C	Accreditation Certificate – D-PL-12076-01-03.....	29

## 2 General information

### 2.1 Notes and disclaimer

The test results of this test report relate exclusively to the test item specified in this test report. CTC advanced GmbH does not assume responsibility for any conclusions and generalizations drawn from the test results with regard to other specimens or samples of the type of the equipment represented by the test item.

The test report may only be reproduced or published in full. Reproduction or publication of extracts from the report requires the prior written approval of CTC advanced GmbH.

The testing service provided by CTC advanced GmbH has been rendered under the current "General Terms and Conditions for CTC advanced GmbH".

CTC advanced GmbH will not be liable for any loss or damage resulting from false, inaccurate, inappropriate or incomplete product information provided by the customer.

Under no circumstances does the CTC advanced GmbH test report include any endorsement or warranty regarding the functionality, quality or performance of any other product or service provided.

Under no circumstances does the CTC advanced GmbH test report include or imply any product or service warranties from CTC advanced GmbH, including, without limitation, any implied warranties of merchantability, fitness for purpose, or non-infringement, all of which are expressly disclaimed by CTC advanced GmbH.

All rights and remedies regarding vendor's products and services for which CTC advanced GmbH has prepared this test report shall be provided by the party offering such products or services and not by CTC advanced GmbH. In no case this test report can be considered as a Letter of Approval.

This test report is electronically signed and valid without handwritten signature. For verification of the electronic signatures, the public keys can be requested at the testing laboratory.

### 2.2 Application details

Date of receipt of order:	2019-07-26
Date of receipt of test item:	2019-08-06
Start of test:	2019-08-06
End of test:	2019-08-07
Person(s) present during the test:	Mr. Kai Lewandowski

### 2.3 Test laboratories sub-contracted

None

### 3 Test standard/s

Test standard	Date	Description
ETSI EN 300 328 V2.2.2	2019-07	Wideband transmission systems; Data transmission equipment operating in the 2,4 GHz band; Harmonised Standard for access to radio spectrum

### 4 Test environment

Temperature	:	$T_{nom}$ $T_{max}$ $T_{min}$	+22 °C during room temperature tests +85 °C during high temperature tests -40 °C during low temperature tests
Relative humidity content	:		55 %
Barometric pressure	:		not relevant for this kind of testing
Power supply	:	$V_{nom}$ $V_{max}$ $V_{min}$	3.0 V DC by external power supply / USB No tests under extreme voltage conditions required. No tests under extreme voltage conditions required.

## 5 Test item

### 5.1 General description

<b>Kind of test item</b>	:	Bluetooth LE SoC
<b>Type identification</b>	:	DA14531 (QFN)
<b>S/N serial number</b>	:	Rad. 00003 Cond. 00009
<b>Hardware status</b>	:	DA14531-AC/AD/AE/AF
<b>Software status</b>	:	6.0.12
<b>Firmware status</b>	:	6.0.12
<b>Frequency band</b>	:	ISM band 2400 MHz to 2483.5 MHz
<b>Type of radio transmission</b>	:	DSSS
<b>Use of frequency spectrum</b>	:	
<b>Type of modulation</b>	:	GFSK
<b>Number of channels</b>	:	40
<b>Channel bandwidth (B)</b>	:	1 MHz
<b>Channel spacing</b>	:	2 MHz
<b>Receiver category</b>	:	2
<b>Antenna</b>	:	Integrated Printed Inverted F antenna
<b>Power supply</b>	:	3.0 V DC by external power supply
<b>Temperature range</b>	:	-40°C to +85°C

### 5.2 Additional information

The content of the following annexes is defined in the QA. It may be that not all of the listed annexes are necessary for this report, thus some values in between may be missing.

Test setup and EUT photos are included in test report:      1-8868/19-01-01\_AnnexB  
    1-8868/19-01-01\_AnnexC

## 6 Description of the test setup


Typically, the calibrations of the test apparatus are commissioned to and performed by an accredited calibration laboratory. The calibration intervals are determined in accordance with the DIN EN ISO/IEC 17025. In addition to the external calibrations, the laboratory executes comparison measurements with other calibrated test systems or effective verifications. Weekly chamber inspections and range calibrations are performed. Where possible, RF generating and signaling equipment as well as measuring receivers and analyzers are connected to an external high-precision 10 MHz reference (GPS-based or rubidium frequency standard).

In order to simplify the identification of the equipment used at some special tests, some items of test equipment and ancillaries can be provided with an identifier or number in the equipment list below (Lab/Item).

### **Agenda:** Kind of Calibration

k	calibration / calibrated	EK	limited calibration
ne	not required (k, ev, izw, zw not required)	zw	cyclical maintenance (external cyclical maintenance)
ev	periodic self verification	izw	internal cyclical maintenance
Ve	long-term stability recognized	g	blocked for accredited testing
vlk!	Attention: extended calibration interval		
NK!	Attention: not calibrated	*)	next calibration ordered / currently in progress

## 6.1 Shielded fully anechoic chamber



Measurement distance: tri-log antenna and horn antenna 3 meter  
BAT-EMC software version: 3.16.0.49

OP = AV + D - G + CA

(OP-radiated output power; AV-analyzer value; D-free field attenuation of measurement distance;  
G-antenna gain+amplifier gain; CA-loss signal path)


Example calculation:

OP [dBm] = -65.0 [dBm] + 50 [dB] - 20 [dBi] + 5 [dB] = -30 [dBm] (1 µW)

**Equipment table:**

No.	Lab / Item	Equipment	Type	Manufacturer	Serial No.	INV. No.	Kind of Calibration	Last Calibration	Next Calibration
1	A, B	Anechoic chamber	-/-	TDK	-/-	300003726	ne	-/-	-/-
2	A, B	Double-Ridged Waveguide Horn Antenna 1-18.0GHz	3115	EMCO	9107-3697	300001605	vIKI!	27.02.2019	26.02.2021
3	A, B	Switch / Control Unit	3488A	HP	*	300000199	ne	-/-	-/-
4	A	Band Reject Filter	WRCG2400/2483-2375/2505-50/10SS	Wainwright	26	300003792	ne	-/-	-/-
5	A, B	EMI Test Receiver 9kHz-26,5GHz	ESR26	R&S	101376	300005063	k	19.12.2018	18.12.2019
6	A	Highpass Filter	WHKX2.6/18G-10SS	Wainwright	12	300004651	ne	-/-	-/-
7	A	Highpass Filter	WHKX7.0/18G-8SS	Wainwright	18	300003789	ne	-/-	-/-
8	A, B	Broadband Amplifier 0.5-18 GHz	CBLU5184540	CERNEX	22051	300004483	ev	-/-	-/-
9	A, B	4U RF Switch Platform	L4491A	Agilent Technologies	MY50000032	300004510	ne	-/-	-/-
10	A, B	NEXIO EMV-Software	BAT EMC V3.16.0.49	EMCO	-/-	300004682	ne	-/-	-/-
11	A, B	DC power supply, 60Vdc, 50A, 1200 W	6032A	HP	2818A03450	300001040	vIKI!	12.12.2017	11.12.2020

## 6.2 Conducted measurements Bluetooth system



OP = AV + CA  
(OP-output power; AV-analyzer value; CA-loss signal path)

Example calculation:

OP [dBm] = 6.0 [dBm] + 11.7 [dB] = 17.7 [dBm] (58.88 mW)

**Equipment table:**

No.	Lab / Item	Equipment	Type	Manufacturer	Serial No.	INV. No.	Kind of Calibration	Last Calibration	Next Calibration
1	B	Temperature Test Chamber	T-40/50	CTS GmbH	053031	300003592	ev	07.05.2018	06.05.2020
2	A, C	USB/GPIB interface	82357B	Agilent Technologies	MY52103346	300004390	ne	-/-	-/-
3	A, B, C	PC	Exone	F+W	-/-	300004179	ne	-/-	-/-
4	C	Wireless Connectivity Tester	CMW270	Rohde & Schwarz	100683	300005133	k	03.01.2018	02.01.2020
5	A	Spectrum Analyzer	FSV30	Rohde & Schwarz	103809	300005359	vIKI!	17.12.2018	16.12.2020
6	C	Signal Generator	SMB100A	Rohde & Schwarz	180587	300005462	vIKI!	20.11.2017	19.11.2020
7	A, B, C	Relay Switch Matrix	RSM-1	CTC	1	400001355	ev	07.02.2019	06.02.2020
8	B	Peak And Average Power Sensor	U2042XA	Keysight	MY58020014	300005547	k	19.12.2018	18.12.2019



## 7 Summary of measurement results

<input checked="" type="checkbox"/>	No deviations from the technical specifications were ascertained
<input type="checkbox"/>	There were deviations from the technical specifications ascertained
<input type="checkbox"/>	This test report is only a partial test report. The content and verdict of the performed test cases are listed below.

TC identifier	Description	verdict	date	Remark
RF-Testing	ETSI EN 300 328 V2.2.2 (2019-07)	See table!	2019-09-04	-/-

Test specification clause	Test case	temperature conditions	power source voltages	Mode	C	NC	NA	NP	Remark
5.4.2	RF output power	Nominal	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	-/-
		Low	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	
		High	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	
5.4.2	Duty cycle, Tx-sequence, Tx-gap, medium utilization	Nominal	Nominal	-/-	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.3	Power spectral density	Nominal	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.4	Accumulated transmit time, freq. occupation and hopping sequence	Nominal	Nominal	-/-	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.5	Hopping frequency separation	Nominal	Nominal	-/-	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.6	Adaptivity	Nominal	Nominal	-/-	<input type="checkbox"/>	<input type="checkbox"/>	<input checked="" type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.7	Occupied channel bandwidth	Nominal	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.8	Transmitter unwanted emissions in the out-of-band domain	Nominal	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.9	Transmitter unwanted emissions in the spurious domain (cond. + rad.)	Nominal	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.10	Receiver spurious emissions (cond. + rad.)	Nominal	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	-/-
5.4.11	Receiver blocking	Nominal	Nominal	1 Msps	<input checked="" type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	<input type="checkbox"/>	-/-

**Note:** C = Compliant; NC = Not compliant; NA = Not applicable; NP = Not performed

## 8 Additional comments

The Bluetooth® word mark and logos are owned by the Bluetooth SIG Inc. and any use of such marks by CTC advanced GmbH is under license.

Reference documents: Bluetooth® Core Specification 5.0  
 1-8868\_19-01-03\_log1\_conducted.pdf (based on 0 dBi antenna gain, relevant calculations for measured antenna gain within this document)

Special test descriptions: For all tests the Smart Snippets Software was used. The firmware power setting was set to 3 dBm.

Configuration descriptions:

Bluetooth Low Energy	
Longest Supported payload (37 – 255 Byte)	Tx: 255, RX: 251
LE 1M PHY supported	Yes
LE 2M PHY supported	No
Stable Modulation Index supported (SMI)	No
LE Coded PHY supported (S=2)	No
LE Coded PHY supported (S=8)	No

Test mode:

- Bluetooth direct test mode enabled (EUT is controlled via CBT/CMW)
- Special software is used. EUT is transmitting pseudo random data by itself

## 9 EUT classification

- Type of equipment:
- stand alone equipment
  - plug in radio equipment
  - combined equipment
- Modulation types:
- Wide band modulation (none hopping – e.g. DSSS, OFDM)
  - Frequency hopping spread spectrum (FHSS)
- Adaptive equipment:
- Yes, LBT-based
  - Yes, non-LBT-based
  - Yes (but can be disabled)
  - No
- Antennas and transmission operating modes:
- Operating mode 1 (single antenna)**
    - Equipment with 1 antenna,
    - Equipment with 2 diversity antennas operating in switched diversity mode by which at any moment in time only 1 antenna is used,
    - Smart antenna system with 2 or more transmit/receive chains, but operating in a mode where only 1 transmit/receive chain is used)
  - Operating mode 2 (multiple antennas, no beamforming)**
    - Equipment operating in this mode contains a smart antenna system using two or more transmit/receive chains simultaneously but without beamforming.
  - Operating mode 3 (multiple antennas, with beamforming)**
    - Equipment operating in this mode contains a smart antenna system using two or more transmit/receive chains simultaneously with beamforming.  
In addition to the antenna assembly gain (G), the beamforming gain (Y) may have to be taken into account when performing the measurements.

## 10 Measurement results

### 10.1 Antenna gain

#### Measurement:

The antenna gain of the system is calculated by the difference of radiated power in EIRP and the conducted power of the module.

Measurement parameters (radiated)	
Detector	Peak
Sweep time	Auto
Resolution bandwidth	2 MHz
Video bandwidth	5 MHz
Trace mode	Max hold
Additional EUT parameters:	Longest supported packet Pattern: PRBS 9
Test setup	See sub clause 6.1 - B
Measurement uncertainty	See sub clause 11

Measurement parameters (conducted)	
External result file	1-8868_19-01-03_log1_conducted.pdf FCC Part 15.247 Maximum Peak Conducted Output Power DTS
Test setup	See sub clause 6.2 - A
Measurement uncertainty	See sub clause 11

#### Limits:

No restriction!

#### Results:

	Low channel (2402 MHz)	Mid channel (2440 MHz)	High channel (2480 MHz)
Conducted power [dBm] Measured with GFSK modulation (1 Msps)	1.8	1.5	1.8
Radiated power [dBm] Measured with GFSK modulation (1 Msps)	4.6	3.8	2.6
Gain [dBi] Calculated	2.8	2.3	0.8

## 10.2 RF output power

Measurement parameters	
External result file	1-8868_19-01-03_log1_conducted.pdf Chapter EN300328 RF Output Power etc
Test setup	See sub clause 6.2 - B
Measurement uncertainty	See sub clause 11

Performed:  Conducted  
 Radiated (only if no conducted sample is provided)

### Limits:

For adaptive equipment	20 dBm
For non-adaptive equipment	Declared by the supplier and shall not exceed 20 dBm

### Results: 1 Msps

Test conditions		Maximum conducted burst power in 10 measured bursts [dBm]		
		low channel	mid channel	high channel
$T_{nom}$	$V_{nom}$	1.9	1.4	1.7
$T_{min}$	$V_{nom}$	2.7	2.3	2.6
$T_{max}$	$V_{nom}$	1.0	0.4	0.7

Test conditions		Maximum burst power in 10 measured bursts [dBm] E.I.R.P.		
		low channel	mid channel	high channel
$T_{nom}$	$V_{nom}$	4.7	3.7	2.5
$T_{min}$	$V_{nom}$	5.5	4.6	3.4
$T_{max}$	$V_{nom}$	3.8	2.7	1.5

**P = max cond. burst power (A) + antenna gain (G) + beamforming gain (Y)**

With:

Beamforming gain (Y) = 0 (SISO)

### 10.3 Power spectral density

#### Description:

The power spectral density is the mean equivalent isotropically radiated power (E.I.R.P.) density during a transmission burst.

Measurement parameters	
External result file	1-8868_19-01-03_log1_conducted.pdf Chapter EN300328 Power Spectral Density
Test setup	See sub clause 6.2 - A
Measurement uncertainty	See sub clause 11

Performed:  Conducted  
 Radiated (only if no conducted sample is provided)

#### Limits:

Under normal test conditions only (including antenna gain)	-20 dBW / 1 MHz 10 dBm / 1 MHz
---	-----------------------------------

#### Results: 1 Msps

ID	Measurement	Unit	Low channel	Mid channel	High channel
1	P (Tnom E.I.R.P.) (from chapter RF Output power)	dBm E.I.R.P.	4.7	3.7	2.5
2	Psum of all raw points	dBm	1.9	1.6	2.0
3	PSD max uncorrected	dBm/1MHz	1.9	1.5	1.9
4	C-corr = Psum-Peirp (1-2)	dB	2.8	2.1	0.5
	PSD max corrected (3+4)	dBm/1MHz E.I.R.P.	4.7	3.6	2.4

## 10.4 Occupied channel bandwidth

### Measurement:

The occupied channel bandwidth is the bandwidth that contains 99 % of the power of the signal.

Measurement parameters	
External result file	1-8868_19-01-03_log1_conducted.pdf Chapter EN300328 Occupied Channel Bandwidth
Test setup	See sub clause 6.2 - A
Measurement uncertainty	See sub clause 11

Performed:  Conducted  
 Radiated (only if no conducted sample is provided)

### Limits:

The occupied channel bandwidth shall fall completely within the band.

For non-adaptive systems using wide band modulations other than FHSS and with e.i.r.p greater than 10 dBm, the occupied channel bandwidth shall be less than 20 MHz.

### Results:

99% bandwidth [kHz]		
	Low channel	High channel
1 Msps	1033	1037

## 10.5 Transmitter unwanted emissions in the out-of-band domain

### Description:

Transmitter unwanted emissions in the out-of-band domain are emissions when the equipment is in transmit mode, on frequencies immediately outside the necessary bandwidth which results from the modulation process, but excluding spurious.


Measurement parameters	
External result file	1-8868_19-01-03_log1_conducted.pdf Chapter EN300328 TX Unwanted Emissions In The OOB Domain
Test setup	See sub clause 6.2 - A
Measurement uncertainty	See sub clause 11

Performed:  Conducted  
 Radiated (only if no conducted sample is provided)

### Limits:

The transmitter unwanted emissions in the out-of-band domain but outside the allocated band, shall not exceed the values provided by the mask.

NOTE: Within the 2400 MHz to 2483.5 MHz band, the Out-of-band emissions are fulfilled by compliance with the Occupied Channel Bandwidth requirement in clause 4.3.2.6.





**Results**

Unwanted emissions [dBm] (including antenna gain)	
<b>1 Msps, channel BW see plots</b>	
2400 MHz - 2BW to 2400 MHz – BW Limit:< -20dBm/MHz	compliant
2400 MHz - BW to 2400 MHz Limit:< -10dBm/MHz	compliant
2483.5 MHz to 2483.5 MHz + BW Limit:< -10dBm/MHz	compliant
2483.5 MHz + BW to 2483.5 MHz + 2BW Limit:< -20dBm/MHz	compliant

## 10.6 Transmitter unwanted emissions in the spurious domain

### Description:

Transmitter unwanted emissions in the spurious domain are emissions outside the allocated band and outside the out-of-band domain when the equipment is in transmit mode.

### Pre-scan:

Measurement parameters (radiated)	
Detector	Peak
Sweep time	5ms/MHz
Resolution bandwidth	Below 1 GHz: 100 kHz / above 1MHz
Video bandwidth	Below 1 GHz: 300 kHz / above 3MHz
Detector	Peak
Test setup	See sub clause 6.1 - A
Measurement uncertainty	See sub clause 11

Measurement parameters (conducted)	
External result file	1-8868_19-01-03_log1_conducted.pdf EN300328 Unwanted Emissions in spurious domain
Test setup	See sub clause 6.2 - A
Measurement uncertainty	See sub clause 11

Any emissions identified during the sweeps in the pre-scan and that fall within the 6 dB range below the applicable limit, shall be individually measured using the procedure "retest".

### Retest:

Measurement parameters (radiated)	
Detector	RMS
Measurement mode	Time domain power
Sweep time	30 ms
Resolution bandwidth	Below 1 GHz: 100 kHz / above 1MHz
Video bandwidth	Below 1 GHz: 300 kHz / above 3MHz
Span	Zero span
Trace mode	Single sweep
Test setup	See sub clause 6.1 - A
Measurement uncertainty	See sub clause 11

Measurement parameters (conducted)	
External result file	1-8868_19-01-03_log1_conducted.pdf EN300328 Unwanted Emissions in spurious domain
Test setup	See sub clause 6.2 - A
Measurement uncertainty	See sub clause 11

Performed:  Conducted  
 Radiated

**Limits:**

State	Max. spurious level		
	47 MHz to 74 MHz 87.5 MHz to 118 MHz 174 MHz to 230 MHz 470 MHz to 862 MHz	Other frequencies ≤ 1000 MHz	All frequencies > 1000 MHz
Operating	4.0 nW (-54 dBm)	250 nW (-36 dBm)	1.00 µW (-30 dBm)
Receiver / Idle	2.0 nW (-57 dBm)	2.0 nW (-57 dBm)	20.0 nW (-47 dBm)

**Results:** conducted, 1 Msp


Low channel			High channel		
f [MHz]	Detector Peak/RMS	Level [dBm]	f [MHz]	Detector Peak/RMS	Level [dBm]
All detected peaks are more than 6 dB below the limit			All detected peaks are more than 6 dB below the limit		

**Results:** radiated, 1 Msps

Low channel			High channel		
f [MHz]	Detector Peak/RMS	Level [dBm]	f [MHz]	Detector Peak/RMS	Level [dBm]
512	Peak	-58.6	512	Peak	-56.7
512	RMS	-63.6	512	RMS	-59.8


**Plots:** Radiated

**Plot 1:** 30 MHz to 12.75 GHz, Low channel, 1 Msps



The carrier signal is notched with a 2.4 GHz band rejection filter.

**Plot 2:** 30 MHz to 12.75 GHz, High channel, 1 Msps



The carrier signal is notched with a 2.4 GHz band rejection filter.

## 10.7 Receiver spurious emissions

### Description:

Receiver/idle unwanted emissions in the spurious domain are emissions outside the allocated band and outside the out-of-band domain when the equipment is in receiver/idle mode.

### Pre-scan:

Measurement parameters (radiated)	
Detector	Peak
Sweep time	5ms/MHz
Resolution bandwidth	Below 1 GHz: 100 kHz / above 1MHz
Video bandwidth	Below 1 GHz: 300 kHz / above 3MHz
Detector	Peak
Test setup	See sub clause 6.1 - A
Measurement uncertainty	See sub clause 11
Measurement parameters (conducted)	
External result file	1-8868_19-01-03_log1_conducted.pdf EN300328 Unwanted Emissions in spurious domain RX
Test setup	See sub clause 6.2 - A
Measurement uncertainty	See sub clause 11

Any emissions identified during the sweeps in the pre-scan and that fall within the 6 dB range below the applicable limit, shall be individually measured using the procedure "retest".

### Retest:

Measurement parameters (radiated)	
Detector	RMS
Measurement mode	Time domain power
Sweep time	30 ms
Resolution bandwidth	Below 1 GHz: 100 kHz / above 1MHz
Video bandwidth	Below 1 GHz: 300 kHz / above 3MHz
Span	Zero span
Trace mode	Single sweep
Test setup	See sub clause 6.1 - A
Measurement uncertainty	See sub clause 11
Measurement parameters (conducted)	
External result file	1-8868_19-01-03_log1_conducted.pdf EN300328 Unwanted Emissions in spurious domain RX
Test setup	See sub clause 6.2 - A
Measurement uncertainty	See sub clause 11

Performed:  Conducted  
 Radiated

**Limits:**

State	Max. spurious level		
	47 MHz to 74 MHz 87,5 MHz to 118 MHz 174 MHz to 230 MHz 470 MHz to 862 MHz	Other frequencies ≤ 1000 MHz	All frequencies > 1000 MHz
Operating	4.0 nW (-54 dBm)	250 nW (-36 dBm)	1.00 µW (-30 dBm)
Receiver/idle	2.0 nW (-57 dBm)	2.0 nW (-57 dBm)	20.0 nW (-47 dBm)

**Results:** conducted, 1 Msps


Low channel			High channel		
f [MHz]	Detector Peak/RMS	Level [dBm]	f [MHz]	Detector Peak/RMS	Level [dBm]
All detected peaks are more than 6 dB below the limit			All detected peaks are more than 6 dB below the limit		

**Results:** radiated, 1 Msps


Low channel			High channel		
f [MHz]	Detector Peak/RMS	Level [dBm]	f [MHz]	Detector Peak/RMS	Level [dBm]
4806	Peak	-46.2	4962	Peak	-46.3
4806	RMS	-52.3	4962	RMS	-52.5

**Plots:** Radiated

**Plot 1:** Receiver, 30 MHz to 12.75 GHz, Low channel, 1 Msps



**Plot 2:** Receiver, 30 MHz to 12.75 GHz, High channel, 1 Msps





## 10.8 Receiver blocking

### Description:

Receiver blocking is a measure of the ability of the equipment to receive a wanted signal on its operating channel without exceeding a given degradation in the presence of an unwanted signal (blocking signal) on frequencies other than those of the operating band.

Measurement parameters	
External result file	1-8868_19-01-03_log1_conducted.pdf Chapter EN300328 RX Receiver Blocking
Test setup	See sub clause 6.2 – C
Measurement uncertainty	See sub clause 11

Performed:  Conducted

Radiated

**Table 2:** Receiver blocking parameters for receiver category 2 equipment:

Wanted signal mean power from companion device (dBm) (see notes 1 and 3)	Blocking signal frequency (MHz)	Blocking signal power (dBm) (see note 3)	Type of blocking signal
(-139 dBm + 10 × log <sub>10</sub> (OCBW) + 10 dB) or (-74 dBm + 10 dB) whichever is less (see note 2)	2380 2504 2300 2584	-34	CW
NOTE 1:	OCBW is in Hz.		
NOTE 2:	In case of radiated measurements using a companion device and the level of the wanted signal from the companion device cannot be determined, a relative test may be performed using a wanted signal up to P <sub>min</sub> + 26 dB where P <sub>min</sub> is the minimum level of wanted signal required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal.		
NOTE 3:	The level specified is the level at the UUT receiver input assuming a 0 dBi antenna assembly gain. In case of conducted measurements, this level has to be corrected for the (in-band) antenna assembly gain (G). In case of radiated measurements, this level is equivalent to a power flux density (PFD) in front of the UUT antenna with the UUT being configured/positioned as recorded in clause 5.4.3.2.2.		

OCBW is 1037 kHz, therefore the signal mean power from the companion device is -69 dBm or -64 dBm, whichever is less. This results in a wanted signal mean power of -69 dBm.

**Limits:**

	Channel	
	Low channel	High channel
Packet error rate limit	10% PER*	

\*The manufacturer may declare alternative performance criteria as long as that is appropriate for the intended use of the equipment

**Result:** Compliant (See log file for details)

**11 Measurement uncertainty**

<b>Measurement uncertainty</b>	
Occupied channel bandwidth	±5 %
RF output power, conducted	±1.5 dB
Power spectral density, conducted	±3 dB
Unwanted emissions, conducted	±3 dB
All emissions, radiated	±3 dB
Temperature	±1 °C
Humidity	±5 %
DC and low frequency voltages	±3 %
Time	±5 %
Duty cycle	±5 %

## Annex A Glossary

<b>EUT</b>	Equipment under test
<b>DUT</b>	Device under test
<b>UUT</b>	Unit under test
<b>GUE</b>	GNSS User Equipment
<b>ETSI</b>	European Telecommunications Standards Institute
<b>EN</b>	European Standard
<b>FCC</b>	Federal Communications Commission
<b>FCC ID</b>	Company Identifier at FCC
<b>IC</b>	Industry Canada
<b>PMN</b>	Product marketing name
<b>HMN</b>	Host marketing name
<b>HVIN</b>	Hardware version identification number
<b>FVIN</b>	Firmware version identification number
<b>EMC</b>	Electromagnetic Compatibility
<b>HW</b>	Hardware
<b>SW</b>	Software
<b>Inv. No.</b>	Inventory number
<b>S/N or SN</b>	Serial number
<b>C</b>	Compliant
<b>NC</b>	Not compliant
<b>NA</b>	Not applicable
<b>NP</b>	Not performed
<b>PP</b>	Positive peak
<b>QP</b>	Quasi peak
<b>AVG</b>	Average
<b>OC</b>	Operating channel
<b>OCW</b>	Operating channel bandwidth
<b>OBW</b>	Occupied bandwidth
<b>OOB</b>	Out of band
<b>DFS</b>	Dynamic frequency selection
<b>CAC</b>	Channel availability check
<b>OP</b>	Occupancy period
<b>NOP</b>	Non occupancy period
<b>DC</b>	Duty cycle
<b>PER</b>	Packet error rate
<b>CW</b>	Clean wave
<b>MC</b>	Modulated carrier
<b>WLAN</b>	Wireless local area network
<b>RLAN</b>	Radio local area network
<b>DSSS</b>	Dynamic sequence spread spectrum
<b>OFDM</b>	Orthogonal frequency division multiplexing
<b>FHSS</b>	Frequency hopping spread spectrum
<b>GNSS</b>	Global Navigation Satellite System
<b>C/N<sub>0</sub></b>	Carrier to noise-density ratio, expressed in dB-Hz

**Annex B Document history**

Version	Applied changes	Date of release
-/-	Initial release	2019-09-04

**Annex C Accreditation Certificate – D-PL-12076-01-03**

first page	last page
 <p>Deutsche Akkreditierungsstelle GmbH</p> <p>Befähigte gemäß § 8 Absatz 1 AkkStelleG i.V.m. § 1 Absatz 1 AkkStelleGBV Unterzeichnerin der Multilateralen Abkommen von EA, ILAC und IAF zur gegenseitigen Anerkennung</p> <p><b>Akkreditierung</b> </p> <p>Die Deutsche Akkreditierungsstelle GmbH bestätigt hiermit, dass das Prüflaboratorium <b>CTC advanced GmbH</b> Untertürkheimer Straße 6-10, 66117 Saarbrücken</p> <p>die Kompetenz nach DIN EN ISO/IEC 17025:2005 besitzt, Prüfungen in folgenden Bereichen durchzuführen: <b>Telekommunikation</b></p> <p>Die Akkreditierungsurkunde gilt nur in Verbindung mit dem Bescheid vom 11.01.2019 mit der Akkreditierungsnummer D-PL-12076-01 und ist gültig bis 21.04.2021. Sie besteht aus diesem Deckblatt, der Rückseite des Deckblatts und der folgenden Anlage mit insgesamt 33 Seiten.</p> <p>Registrierungsnummer der Urkunde: <b>D-PL-12076-01-03</b></p> <p>Frankfurt am Main, 11.01.2019  Im Auftrag Dipl.-Biol. Uwe Zimmermann Abteilungsleiter</p> <p><small>Seite 1 von 1 auf der Rückseite</small></p>	<p>Deutsche Akkreditierungsstelle GmbH</p> <p>Standort Berlin Spittelmarkt 10 10117 Berlin</p> <p>Standort Frankfurt am Main Europa-Allee 52 60327 Frankfurt am Main</p> <p>Standort Braunschweig Bundesallee 100 38116 Braunschweig</p> <p>Die auszugsweise Veröffentlichung der Akkreditierungsurkunde bedarf der vorherigen schriftlichen Zustimmung der Deutsche Akkreditierungsstelle GmbH (DAkKS). Ausgenommen davon ist die separate Weiterverbreitung des Deckblattes durch die umseitig genannte Konformitätsbewertungsstelle in unveränderter Form.</p> <p>Es darf nicht der Anschein erweckt werden, dass sich die Akkreditierung auch auf Bereiche erstreckt, die über den durch die DAkKS bestätigten Akkreditierungsbereich hinausgehen.</p> <p>Die Akkreditierung erfolgte gemäß des Gesetzes über die Akkreditierungsstelle (AkkStelleG) vom 31. Juli 2009 (BGBl. I S. 2625) sowie der Verordnung (EG) Nr. 765/2008 des Europäischen Parlaments und des Rates vom 9. Juli 2008 über die Vorschriften für die Akkreditierung und Marktüberwachung im Zusammenhang mit der Vermarktung von Produkten (Abt. L 218 vom 9. Juli 2008, S. 30).</p> <p>Die DAkKS ist Unterzeichnerin der Multilateralen Abkommen zur gegenseitigen Anerkennung der European co-operation for Accreditation (EA), des International Accreditation Forum (IAF) und der International Laboratory Accreditation Cooperation (ILAC). Die Unterzeichner dieser Abkommen erkennen ihre Akkreditierungen gegenseitig an.</p> <p>Der aktuelle Stand der Mitgliedschaft kann folgenden Webseiten entnommen werden: EA: <a href="http://www.european-accreditation.org">www.european-accreditation.org</a> ILAC: <a href="http://www.ilac.org">www.ilac.org</a> IAF: <a href="http://www.iaf.eu">www.iaf.eu</a></p>

**Note: The current certificate annex is published on the website (link see below) of the Accreditation Body DAkKS or may be received by CTC advanced GmbH on request**

<https://www.dakks.de/as/ast/d/D-PL-12076-01-03.pdf>

##### END OF TEST REPORT #####