

# APPLICATION NOTE

# R8C/27 Group Timer RC in Input Capture Function

R01AN1277EJ0110 Rev. 1.10 June 1, 2012

#### 1. Abstract

This document describes how to set up and use timer RC in the input capture function in the R8C/27 Group.

#### 2. Introduction

The application example described in this document is applied to the following MCU and parameter(s):

#### • MCU: R8C/27 Group

This program can be used with other R8C/Tiny Series which have the same special function registers (SFRs) as the R8C/27 Group. Check the manual for any additions and modifications to functions. Careful evaluation is recommended before using this application note.

Note on oscillation stabilization wait time

In chapter 4.2.1, select the high-speed on-chip oscillator after starting the high-speed on-chip oscillator and waiting until oscillation stabilizes.



# 3. Applications

# 3.1 Timer RC

Timer RC is a 16-bit timer with four I/O pins. Timer RC uses either f1 or fOCO40M as its operation clock. Table 3.1 lists the Timer RC Operation Clock.

#### Table 3.1 Timer RC Operation Clock

Condition	Timer RC Operation Clock
Count source is f1, f2, f4, f8, f32, or TRCCLK input (bits TCK2 to TCK0 in	f1
TRCCR1 register are set to a value from 000b to 101b)	
Count source is fOCO40M (bits TCK2 to TCK0 in TRCCR1 register are set	fOCO40M
to 110b)	

Table 3.2 lists the Timer RC I/O Pins, and Figure 3.1 shows a Timer RC Block Diagram.

Timer RC has three modes:

• Timer mode

- Input capture function	The counter value is captured to a register, using an external signal as the trigger.		
- Output compare function	Matches between the counter and register values are detected. (Pin output state		
	changes when a match is detected.)		
The following two modes use the output compare function:			


PWM mode
 Pulses of a given width are output continuously.

- PWM2 mode A one-shot waveform or PWM waveform is output following the trigger after
- the wait time has elapsed.

Input capture function, output compare function, and PWM mode settings may be specified independently for each pin.

In PWM2 mode, waveforms are output based on a combination of the counter and the register. Pin function is decided by the mode.





#### Figure 3.1 Timer RC Block Diagram

#### Table 3.2 Timer RC I/O Pins

Pin Name	I/O	Function
TRCIOA(P1_1)	I/O	Function differs according to the mode. Refer to descriptions
TRCIOB(P1_2)		of individual modes for details.
TRCIOC(P5_3 or P3_4) <sup>(1)</sup>		
TRCIOD(P5_4 or P3_5) <sup>(1)</sup>		
TRCCLK(P3_3)	Input	External clock input
TRCTRG(P1_1)	Input	PWM2 mode external trigger input

NOTE:

1. The pins used for TRCIOC and TRCIOD can be selected. Refer to the description of bits TRCIOCSEL and TRCIODSEL in the PINSR3 register in the **R8C/27 Group Hardware Manual** for details.



# 3.2 Registers Associated with Timer RC

Table 3.3 lists the Registers Associated with Timer RC. Figures 3.2 to 3.11 show details of the registers associated with timer RC.

			Мо	de		
Address	Symbol	Tir Input Capture Function	ner Output Compare Function	PWM	PWM2	Related Information
0120h	TRCMR	Valid	Valid	Valid	Valid	Timer RC mode register Figure 3.2 TRCMR Register
0121h	TRCCR1	Valid	Valid	Valid	Valid	Timer RC control register 1 Figure 3.3 TRCCR1 Register
0122h	TRCIER	Valid	Valid	Valid	Valid	Timer RC interrupt enable register Figure 3.4 TRCIER Register
0123h	TRCSR	Valid	Valid	Valid	Valid	Timer RC status register Figure 3.5 TRCSR Register
0124h	TRCIOR0	Valid	Valid	-	_	Timer RC I/O control register 0, timer RC I/O control register 1 Figure 3.11 Registers TRCIOR0 and TRCIOR1 Figure 3.16 TRCIOR0 Register for Input Capture Function
0125h	TRCIOR1					Figure 3.17 TRCIOR1 Register for Input Capture Function
0126h 0127h	TRC	Valid	Valid	Valid	Valid	Timer RC counter Figure 3.6 TRC Register
0128h 0129h	TRCGRA	Valid	Valid	Valid	Valid	Timer RC general registers A, B, C, and D Figure 3.7 Registers TRCGRA, TRCGRB,
012Ah 012Bh	TRCGRB					TRCGRC, and TRCGRD
012Ch 012Dh	TRCGRC					
012Eh 012Fh	TRCGRD					
0130h	TRCCR2	-	-	_	Valid	Timer RC control register 2 Figure 3.8 TRCCR2 Register
0131h	TRCDF	Valid	-	_	Valid	Timer RC digital filter function select register Figure 3.9 TRCDF Register
0132h	TRCOER	-	Valid	Valid	Valid	Timer RC output mask enable register Figure 3.10 TRCOER Register

Table 3.3 Registers Associated with Timer RC

– : Invalid

b7 b6 b5	b4 b3 b2 b1 b0				
X		Symbol	Address	After Reset	
TTT	╷╷╷╷╷	TRCMR	0120h	01001000b	
		Bit Symbol	Bit Name	Function	RW
		PWMB	PWM mode of TRCIOB select bit <sup>(2)</sup>	0: Timer mode 1: PWM mode	RW
		PWMC	PWM mode of TRCIOC select bit <sup>(2)</sup>	0: Timer mode 1: PWM mode	RW
		PWMD	PWM mode of TRCIOD select bit <sup>(2)</sup>	0: Timer mode 1: PWM mode	RW
		PWM2	PWM2 mode select bit	0: PWM 2 mode 1: Timer mode or PWM mode	RW
		BFC	TRCGRC register function select bit <sup>(3)</sup>	0: General register 1: Buffer register of TRCGRA register	RW
		BFD	TRCGRD register function select bit	0: General register 1: Buffer register of TRCGRB register	RW
		(b6)	Nothing is assigned. If necessary, When read, the content is 1.	set to 0.	1-
		TSTART	TRC count start bit	0: Count stops 1: Count starts	RW

1. For notes on PWM2 mode, refer to the **R8C/27 Group Hardware Manual**.

2. These bits are enabled when the  $\ensuremath{\mathsf{PWM2}}$  bit is set to 1 (timer mode or  $\ensuremath{\mathsf{PWM}}$  mode).

3. Set the BFC bit to 0 (general register) in PWM2 mode.

Figure 3.2 TRCMR Register



b7 b6 l	b5 b4 b3 b2 b1 b0	Symbol TRCCR1	Address 0121h	After Reset 00h	
		Bit Symbol	Bit Name	Function	RW
		TOA	TRCIOA output level select bit <sup>(1)</sup>	Function varies according to the operating mode (function). <sup>(2)</sup>	RW
		ТОВ	TRCIOB output level select bit <sup>(1)</sup>		RW
		ТОС	TRCIOC output level select bit <sup>(1)</sup>		RW
		TOD	TRCIOD output level select bit <sup>(1)</sup>		RW
		тско	Count source select bits <sup>(1)</sup>	b6 b5 b4 0 0 0: f1 0 0 1: f2	RW
		TCK1		0 1 0: f4 0 1 1: f8 1 0 0: f32	RW
		тск2		<ol> <li>1 0 1: TRCCLK input rising edge</li> <li>1 0: fOCO40M</li> <li>1 1: Do not set.</li> </ol>	RW
		CCLR	TRC counter clear select bit <sup>(2, 3)</sup>	<ul> <li>0: Disable clear (free-running operation)</li> <li>1: Clear by compare match in the TRCGRA register</li> </ul>	RW

1. Set to these bits when the TSTART bit in the TRCMR register is set to 0 (count stops).

2. Bits CCLR, TOA, TOB, TOC and TOD are disabled for the input capture function of the timer mode.

3. The TRC counter performs free-running operation for the input capture function of the timer mode independent of the CCLR bit setting.

Figure 3.3 TRCCR1 Register






Figure 3.4 **TRCIER Register** 



b3 b2 b1 b0	Symbol TRCSR	Address 0123h	After Reset 01110000b	
	Bit Symbol	Bit Name	Function	RW
	IMFA	Input capture/compare match flag A	Write 0 after read <sup>(1)</sup> .	RW
	IMFB	Input capture/compare match flag B	[Source for setting this bit to 1] Refer to the table below .	RW
	IMFC	Input capture/compare match flag C		RW
	IMFD	Input capture/compare match flag D		RW
		Nothing is assigned. If necessary, se	et to 0.	
	(b6 - b4)	When read, the content is 1.		
	OVF	Overflow flag	[Source for setting this bit to 0] Write 0 after read <sup>(1)</sup> . [Source for setting this bit to 1] Refer to the table below.	RW

NOTE:

1. The writing results are as follow s:

• This bit is set to 0 when the read result is 1 and 0 is written to the same bit.

• This bit remains unchanged even if the read result is 0 and 0 is written to the same bit.

(This bit remains 1 even if it is set to 1 from 0 after reading, and writing 0.)

• This bit remains unchanged if 1 is written to it.

	Timer Mo	ode		
Bit Symbol	Input capture Function	Output Compare Function	PWM Mode	PWM2 Mode
IMFA	TRCIOA pin input edge <sup>(1)</sup>	When the values of the registers TRC and TRCGRA match.		
IMFB	TRCIOB pin input edge <sup>(1)</sup>	When the values of the	e registers TRC and	d TRCGRB match.
IMFC	TRCIOC pin input edge <sup>(1)</sup> When the values of the registers TRC and TRCGRC match. <sup>(2)</sup>		d TRCGRC	
IMFD	TRCIOD pin input edge <sup>(1)</sup>	When the values of the match. <sup>(2)</sup>	e registers TRC and	d TRCGRD
OVF	When the TRC register overfl	ows.		


NOTES:


1. Edge selected by bits IOj1 to IOj0 (j = A, B, C, or D).

2. Includes the condition that bits BFC and BFD are set to 1 (buffer registers of registers TRCGRA and TRCGRB).














Figure 3.7 Registers TRCGRA, TRCGRB, TRCGRC, and TRCGRD





3. In timer mode and PWM mode, these bits are disabled.


Figure 3.8 TRCCR2 Register



- 1. These bits are enabled for the input capture function.
- These bits are enabled when in PWM2 mode and bits TCEG1 to TCEG0 in the TRCCR2 register are set to 01b, 10b, or 11b (TRCTRG trigger input enabled).

Figure 3.9 TRCDF Register









b7 b6 b5	C I/O Contr	0			
X	1	Symbol	Address	After Reset	
		TRCIOR0	0124h	10001000b	
		Bit Symbol	Bit Name	Function	RW
		IOA0	TRCGRA control bits	Function varies according to the operating mode	RW
		IOA1		(function).	RW
		IOA2	TRCGRA mode select bit <sup>(2)</sup>	0: Output compare function 1: Input capture function	RW
		(b3)	Reserved bit	Set to 1.	RW
		IOB0	TRCGRB control bits	Function varies according to the operating mode	RW
		IOB1		(function).	RW
		IOB2	TRCGRB mode select bit <sup>(3)</sup>	0: Output compare function 1: Input capture function	RW
		(b7)	Nothing is assigned. If necess When read, the content is 1.	sary, set to 0.	_

NOTES:

- 1. The TRCIOR0 register is enabled in timer mode. It is disabled in modes PWM and PWM2.
- 2. When the BFC bit in the TRCMR register is set to 1 (buffer register of TRCGRA register), set the IOC2 bit in the TRCIOR1 register to the same value as the IOA2 bit in the TRCIOR0 register.
- 3. When the BFD bit in the TRCMR register is set to 1 (buffer register of TRCGRB register), set the IOD2 bit in the TRCIOR1 register to the same value as the IOB2 bit in the TRCIOR0 register.

Timer RC I/O Control Register 1<sup>(1)</sup>

b7 b6 b	5 b4 b3 b2 b1	1 b0				
		Symbol TRCIOR1	Address 0125h	After Reset 10001000b		
			Bit Symbol	Bit Name	Function	RW
			IOC0	TRCGRC control bits	Function varies according to the operating mode	RW
			IOC1		(function).	RW
			IOC2	TRCGRC mode select bit <sup>(2)</sup>	0: Output compare function 1: Input capture function	RW
			(b3)	Nothing is assigned. If neces: When read, the content is 1.	sary, set to 0.	—
			IOD0	TRCGRD control bits	Function varies according to the operating mode	RW
			IOD1		(function).	RW
			IOD2	TRCGRD mode select bit <sup>(3)</sup>	0: Output compare function 1: Input capture function	RW
			—	Nothing is assigned. If neces	sary, set to 0.	_
			(b7)	When read, the content is 1.		

NOTES:

- 1. The TRCIOR1 register is enabled in timer mode. It is disabled in modes PWM and PWM2.
- 2. When the BFC bit in the TRCMR register is set to 1 (buffer register of TRCGRA register), set the IOC2 bit in the TRCIOR1 register to the same value as the IOA2 bit in the TRCIOR0 register.
- 3. When the BFD bit in the TRCMR register is set to 1 (buffer register of TRCGRB register), set the IOD2 bit in the TRCIOR1 register to the same value as the IOB2 bit in the TRCIOR0 register.

Figure 3.11 Registers TRCIOR0 and TRCIOR1



# 3.3 Common Items for Multiple Modes

#### 3.3.1 Count Source

The method of selecting the count source is common to all modes. Table 3.4 lists the Count Source Selection, and Figure 3.12 shows a Count Source Block Diagram.

Table 3.4	Count Source Selection
-----------	------------------------

Count Source	Selection Method
f1, f2, f4, f8, f32	Count source selected using bits TCK2 to TCK0 in TRCCR1 register
fOCO40M	FRA00 bit in FRA0 register set to 1 (high-speed on-chip oscillator on) and bits TCK2 to TCK0 in TRCCR1 register are set to 110b (fOCO40M)
External signal input to TRCCLK pin	Bits TCK2 to TCK0 in TRCCR1 register are set to 101b (count source is rising edge of external clock) and PD3_3 bit in PD3 register is set to 0 (input mode)




Figure 3.12 Count Source Block Diagram

The pulse width of the external clock input to the TRCCLK pin should be three cycles or more of the timer RC operation clock (see **Table 3.1 Timer RC Operation Clock**).

To select fOCO40M as the count source, set the FRA00 bit in the FRA0 register to 1 (high-speed on-chip oscillator on), and then set bits TCK2 to TCK0 in the TRCCR1 register to 110b (fOCO40M).



# 3.3.2 Buffer Operation

Bits BFC and BFD in the TRCMR register are used to select the TRCGRC or TRCGRD register as the buffer register for the TRCGRA or TRCGRB register.

• Buffer register for TRCGRA register: TRCGRC register

• Buffer register for TRCGRB register: TRCGRD register

Buffer operation differs depending on the mode.

Table 3.5 lists the Buffer Operation in Each Mode, and Figure 3.13 shows the Buffer Operation for Input Capture Function.

Table 3.5	Buffer Operation in Each Mode
-----------	-------------------------------

Function, Mode	Transfer Timing	Transfer Destination Register
Input capture function	Input capture signal input	Contents of TRCGRA (TRCGRB)
		register are transferred to buffer
		register
Output compare function	Compare match between TRC register	Contents of buffer register are
PWM mode	and TRCGRA (TRCGRB) register	transferred to TRCGRA (TRCGRB) register
PWM2 mode	<ul> <li>Compare match between TRC register and TRCGRA register</li> <li>TRCTRG pin trigger input</li> </ul>	Contents of buffer register (TRCGRD) are transferred to TRCGRB register




Figure 3.13 Buffer Operation for Input Capture Function



Set the following in timer mode:

- To use the TRCGRC register as the buffer register for the TRCGRA register: Set the IOC2 bit in the TRCIOR1 register to the same value as the IOA2 bit in the TRCIOR0 register.
- To use the TRCGRD register as the buffer register for the TRCGRB register: Set the IOD2 bit in the TRCIOR1 register to the same value as the IOB2 bit in the TRCIOR0 register.

When the input capture function and the TRCGRC register or TRCGRD register is also functioning as a buffer register, the IMFC bit or IMFD bit in the TRCSR register is set to 1 at the input edge of a signal input to the TRCIOC pin or TRCIOD pin.



# 3.3.3 Digital Filter

The input to TRCTRG or TRCIOj (j = A, B, C, or D) is sampled, and the level is considered to be determined when three matches occur. The digital filter function and sampling clock are selected using the TRCDF register. Figure 3.14 shows a Block Diagram of Digital Filter.




Figure 3.14 Block Diagram of Digital Filter



# 3.4 Timer Mode (Input Capture Mode Function)

This function measures the width or period of an external signal. An external signal input to the TRCIOj (j = A, B, C, or D) pin acts as a trigger for transferring the contents of the TRC register (counter) to the TRCGRj register (input capture). The input capture function, or any other mode or function, can be selected for each individual pin.

Table 3.6 lists the Specifications of Input Capture Function, Figure 3.15 shows a Block Diagram of Input Capture Function, Figure 3.16 and Figure 3.17 show registers associated with the input capture function, Table 3.7 lists the Functions of TRCGRj Register when Using Input Capture Function, and Figure 3.18 shows an Operating Example of Input Capture Function.

Item	Specification
Count source	f1, f2, f4, f8, f32, fOCO40M, or external signal (rising edge) input to TRCCLK
	pin
Count operation	Increment
Count period	1/fk × 65,536 fk: Count source frequency
Count start condition	1 (count starts) is written to the TSTART bit in the TRCMR register.
Count stop condition	0 (count stops) is written to the TSTART bit in the TRCMR register.
	The TRC register retains a value before count stops.
Interrupt request generation	Input capture (valid edge of TRCIOj input signal)
timing	The TRC register overflows.
TRCIOA, TRCIOB, TRCIOC,	Programmable I/O port or input capture input (selectable individually by pin)
and TRCIOD pin functions	
INT0 pin function	Programmable I/O port or INT0 interrupt input
Read from timer	The count value can be read by the reading TRC register.
Write to timer	The TRC register can be written to.
Select functions	Input capture input pin select
	One or more of pins TRCIOA, TRCIOB, TRCIOC, and TRCIOD
	Input capture input valid edge selected
	Rising edge, falling edge, or both rising and falling edges
	Buffer operation (refer to 3.3.2 Buffer Operation)
	Digital filter (refer to 3.3.3 Digital Filter)

Table 3.6 Specifications of Input Capture Function

j = A, B, C, or D







Figure 3.15 Block Diagram of Input Capture Function






1. When the BFC bit in the TRCMR register is set to 1 (buffer register of TRCGRA register), set the IOC2 bit in the TRCIOR1 register to the same value as the IOA2 bit in the TRCIOR0 register.

2. When the BFD bit in the TRCMR register is set to 1 (buffer register of TRCGRB register), set the IOD2 bit in the TRCIOR1 register to the same value as the IOB2 bit in the TRCIOR0 register.

Figure 3.16 TRCIOR0 Register for Input Capture Function





1. When the BFC bit in the TRCMR register is set to 1 (buffer register of TRCGRA register), set the IOC2 bit in the TRCIOR1 register to the same value as the IOA2 bit in the TRCIOR0 register.

2. When the BFD bit in the TRCMR register is set to 1 (buffer register of TRCGRB register), set the IOD2 bit in the TRCIOR1 register to the same value as the IOB2 bit in the TRCIOR0 register.

TRCIOR1 Register for Input Capture Function Figure 3.17

#### Table 3.7 Functions of TRCGRj Register when Using Input Capture Function

Register	Setting	Register Function	Input Capture Input Pin
TRCGRA	-	General register. Can be used to read the TRC register value	TRCIOA
TRCGRB		at input capture.	TRCIOB
TRCGRC	BFC = 0	General register. Can be used to read the TRC register value	TRCIOC
TRCGRD	BFD = 0	at input capture.	TRCIOD
TRCGRC	BFC = 1	Buffer registers. Can be used to hold transferred value from	TRCIOA
TRCGRD	BFD = 1	the general register (refer to <b>3.3.2 Buffer Operation</b> ).	TRCIOB

j = A, B, C, or D

BFC, BFD: Bits in TRCMR register






Figure 3.18 Operating Example of Input Capture Function




#### 3.5 Timer RC Interrupt

Timer RC generates a timer RC interrupt request from five sources. The timer RC interrupt uses a single TRCIC register (bits IR and ILVL0 to ILVL2) and a single vector.

Table 3.8 lists the Registers Associated with Timer RC Interrupt, and Figure 3.19 is a Timer RC Interrupt Block Diagram.

Table 3.8	Registers Associated with Timer RC Interrupt
-----------	--

Timer RC Status Register	Timer RC Interrupt Enable Register	Timer RC Interrupt Control Register
TRCSR0	TRCIER	TRCIC



#### Figure 3.19 Timer RC Interrupt Block Diagram

Like other maskable interrupts, the timer RC interrupt is controlled by the combination of the I flag, IR bit, bits ILVL0 to ILVL2, and IPL. However, it differs from other maskable interrupts in the following respects because a single interrupt source (timer RC interrupt) is generated from multiple interrupt request sources.

- The IR bit in the TRCIC register is set to 1 (interrupt requested) when a bit in the TRCSR register is set to 1 and the corresponding bit in the TRCIER register is also set to 1 (interrupt enabled).
- The IR bit is set to 0 (no interrupt request) when the bit in the TRCSR register or the corresponding bit in the TRCIER register is set to 0, or both are set to 0. In other words, the interrupt request is not maintained if the IR bit is once set to 1, but the interrupt is not acknowledged.
- If after the IR bit is set to 1, another interrupt source is triggered, the IR bit remains set to 1 and does not change.
- If multiple bits in the TRCIER register are set to 1, use the TRCSR register to determine the source of the interrupt request.
- The bits in the TRCSR register are not automatically set to 0 when an interrupt is acknowledged. Set them to 0 within the interrupt routine. Refer to **Figure 3.5 TRCSR Register** for the procedure for setting these bits to 0.

#### Refer to Figure 3.4 TRCIER Register for details on the TRCIER register.

Refer to the **R8C/27 Group Hardware Manual** for details on the TRCIC register and for information on interrupt vectors.



#### 3.6 Notes on Timer RC

# 3.6.1 TRC Register

• The following note applies when the CCLR bit in the TRCCR1 register is set to 1 (clear TRC register at compare match with TRCGRA register).

When using a program to write a value to the TRC register while the TSTART bit in the TRCMR register is set to 1 (count starts), ensure that the write does not overlap with the timing with which the TRC register is set to 0000h.

If the timing of the write to the TRC register and the setting of the TRC register to 0000h coincide, the write value will not be written to the TRC register and the TRC register will be set to 0000h.

Reading from the TRC register immediately after writing to it can result in the value previous to the write being read out. To prevent this, execute the JMP.B instruction between the read and the write instructions.
 Program Example MOV.W #XXXXh, TRC ;Write

ample	MOV.W	#XXXXh, TRC	;Write
	JMP.B	L1	;JMP.B instruction
L1:	MOV.W	TRC,DATA	;Read

# 3.6.2 TRCSR Register

Reading from the TRCSR register immediately after writing to it can result in the value previous to the write being read out. To prevent this, execute the JMP.B instruction between the read and the write instructions.

Program Example	MOV.B	#XXh, TRCSR	;Write
	JMP.B	L1	;JMP.B instruction
L1:	MOV.B	TRCSR,DATA	;Read

# 3.6.3 Count Source Switching

• Stop the count before switching the count source.

Switching procedure:

- (1) Set the TSTART bit in the TRCMR register to 0 (count stops).
- (2) Change the settings of bits TCK2 to TCK0 in the TRCCR1 register.
- After switching the count source from fOCO40M to another clock, allow a minimum of two cycles of f1 to elapse after changing the clock setting before stopping fOCO40M.

Switching procedure:

- (1) Set the TSTART bit in the TRCMR register to 0 (count stops).
- (2) Change the settings of bits TCK2 to TCK0 in the TRCCR1 register.
- (3) Wait for a minimum of two cycles of f1.
- (4) Set the FRA00 bit in the FRA0 register to 0 (high-speed on-chip oscillator off).

#### 3.6.4 Input Capture Function

- The pulse width of the input capture signal should be three cycles or more of the timer RC operation clock (refer to Table 3.1 Timer RC Operation Clock).
- The value of the TRC register is transferred to the TRCGRj register one or two cycles of the timer RC operation clock after the input capture signal is input to the TRCIOj (j = A, B, C, or D) pin (when the digital filter function is not used).



#### R8C/27 Group


#### 4. Program Overview

When an active edge is detected on the external signal input to the TRCIOA pin (IMFA bit = 1), the contents of both the general (TRCGRA) and buffer (TRCGRC) registers will be read during main handling.

The setting conditions of this program are as follows:

- Select the high-speed on-chip oscillator (fOCOM40M) as count source.
- Detect an input capture to the TRCIOA pin at both edges.
- Retain the count value of timer RC counter (TRC) when an active edge is detected.

Figure 4.1 shows the Pin Used.







# 4.1 Function Table


#### Table 4.1

Declaration	void timer_rc_ir	void timer_rc_init(void)		
Overview	SFR initial setti	SFR initial setting associated with timer RC		
Argument	Argument name	9	Meaning	
	None	None		
Variable used	Variable name		Usage	
(global)	None	None		
Return value	Туре	Value	Meaning	
	None			
Function	Initialize the SF	Initialize the SFR registers associated with timer RC		




# 4.2 Flow chart

# 4.2.1 Main Function





# 4.2.2 Timer RC SER Initial Setting





# 5. Sample Programming Code

A sample program can be downloaded from the Renesas Electronics website.

#### 6. Reference Documents

User's Manual: Hardware R8C/27 Group Hardware Manual The latest version can be downloaded from the Renesas Electronics website.

Technical Update/Technical News The latest information can be downloaded from the Renesas Electronics website.

# Website and Support

Renesas Electronics website http://www.renesas.com

Inquiries http://www.renesas.com/contact/



REVISION HISTORY	R8C/27 Group	
REVISION HISTORY	Timer RC in Input Capture Function	

Rev.	Date	Description	
		Page	Summary
1.00	Dec 01, 2006	-	First Edition issued
1.10	June 1, 2012	1	Note on oscillation stabilization wait time added
		<ul> <li>Previous document number: REJ05B0837</li> </ul>	

All trademarks and registered trademarks are the property of their respective owners.



# General Precautions in the Handling of MPU/MCU Products

The following usage notes are applicable to all MPU/MCU products from Renesas. For detailed usage notes on the products covered by this manual, refer to the relevant sections of the manual. If the descriptions under General Precautions in the Handling of MPU/MCU Products and in the body of the manual differ from each other, the description in the body of the manual takes precedence.

1. Handling of Unused Pins

Handle unused pins in accord with the directions given under Handling of Unused Pins in the manual.

- The input pins of CMOS products are generally in the high-impedance state. In operation with an unused pin in the open-circuit state, extra electromagnetic noise is induced in the vicinity of LSI, an associated shoot-through current flows internally, and malfunctions occur due to the false recognition of the pin state as an input signal become possible. Unused pins should be handled as described under Handling of Unused Pins in the manual.
- 2. Processing at Power-on

The state of the product is undefined at the moment when power is supplied.

- The states of internal circuits in the LSI are indeterminate and the states of register settings and pins are undefined at the moment when power is supplied.
  - In a finished product where the reset signal is applied to the external reset pin, the states of pins are not guaranteed from the moment when power is supplied until the reset process is completed.

In a similar way, the states of pins in a product that is reset by an on-chip power-on reset function are not guaranteed from the moment when power is supplied until the power reaches the level at which resetting has been specified.

3. Prohibition of Access to Reserved Addresses

Access to reserved addresses is prohibited.

- The reserved addresses are provided for the possible future expansion of functions. Do
  not access these addresses; the correct operation of LSI is not guaranteed if they are
  accessed.
- 4. Clock Signals

After applying a reset, only release the reset line after the operating clock signal has become stable. When switching the clock signal during program execution, wait until the target clock signal has stabilized.

- When the clock signal is generated with an external resonator (or from an external oscillator) during a reset, ensure that the reset line is only released after full stabilization of the clock signal. Moreover, when switching to a clock signal produced with an external resonator (or by an external oscillator) while program execution is in progress, wait until the target clock signal is stable.
- 5. Differences between Products

Before changing from one product to another, i.e. to one with a different part number, confirm that the change will not lead to problems.

— The characteristics of MPU/MCU in the same group but having different part numbers may differ because of the differences in internal memory capacity and layout pattern. When changing to products of different part numbers, implement a system-evaluation test for each of the products.

#### Notice

- Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 3. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or
- technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
- 4. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics product.
- 5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

\*Standard\*: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; and safety equipment etc.

Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (nuclear reactor control systems, military equipment etc.). You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for which it is not intended. Renesas Electronics shall not be in any way liable for any application for which the product is not intended by Nenesas Electronics.

- 6. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 7. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or systems manufactured by you.
- 8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 9. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You should not use Renesas Electronics products or technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. When exporting the Renesas Electronics products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations.
- It is the responsibility of the buyer or distributor of Renesas Electronics products, who distributes, disposes of, or otherwise places the product with a third party, to notify such third party in advance of the contents and conditions set forth in this document, Renesas Electronics assumes no responsibility for any losses incurred by you or third parties as a result of unauthorized use of Renesas Electronics products.
- 11. This document may not be reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



#### SALES OFFICES

Refer to "http://www.renesas.com/" for the latest and detailed information

#### **Renesas Electronics Corporation**

http://www.renesas.com

 Renesas Electronics America Inc.

 2880 Scott Boulevard Santa Clara, CA 95050-2554, U.S.A.

 Tel: +1-408-588-6000, Fax: +1-408-588-6130

 Renesas Electronics Canada Limited

 101 Nicholson Road, Newmarkst, Ontario L3Y 9C3, Canada

 Tel: +1-905-989-5441, Fax: +1-905-988-3220

 Renesas Electronics Europe Limited

 Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K

 Tel: +492-11-65030, Fax: +44-1628-585-900

 Renesas Electronics Europe GmbH

 Arcadiastrase 10, 40472 Dusseldorf, Germany

 Tel: +92-11-65030, Fax: +44-1628-585-900

 Renesas Electronics Chingo Co., Ltd.

 The Floor, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100083, P.R.China

 Tel: +92-11-65030, Fax: +48-21-0523 Lujiazui Ring Rd, Pudong District, Shanghai 200120, China

 Tel: +962-757-1818, Fax: +862-108235-7679

 Renesas Electronics (Shanghai) Co., Ltd.

 Unit 204, 205, AZIA Center, No.1233 Lujiazui Ring Rd, Pudong District, Shanghai 200120, China

 Tel: +862-78587-7858 / -7898

 Renesas Electronics Taivan Co., Ltd.

 Nuit 1601-1613, 16/F., Towre 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong

 Tel: +852-2886-9318, Fax: +852 2886-9022/9044

 Renesas Electronics Taiwan Co., Ltd.

 TaFN, No. 383, Fu Shing Month Road, Taipei, Taiwa