

TEST REPORT

Test report no.: 1-6565/18-01-02



Testing laboratory

CTC advanced GmbH

Untertuerkheimer Strasse 6 – 10

66117 Saarbruecken / Germany

Phone: + 49 681 5 98 - 0

Fax: + 49 681 5 98 - 9075

Internet: <http://www.ctcadvanced.com>

e-mail: mail@ctcadvanced.com

Accredited Testing Laboratory:

The testing laboratory (area of testing) is accredited according to DIN EN ISO/IEC 17025 (2005) by the Deutsche Akkreditierungsstelle GmbH (DAkkS)

The accreditation is valid for the scope of testing procedures as stated in the accreditation certificate with the registration number: D-PL-12076-01-03

Applicant

Dialog Semiconductor BV

Het Zuiderkruis 53

5215 MV's Hertogenbosch / NETHERLANDS

Phone: -/-

Contact: Steven Leussink

e-mail: steven.leussink@diasemi.com

Phone: +31 73 680 22 10

Manufacturer

Dialog Semiconductor BV

Het Zuiderkruis 53

5215 MV's Hertogenbosch / NETHERLANDS

Test standard/s

ETSI EN 300 328
V2.1.1

Wideband transmission systems; Data transmission equipment operating in the 2.4 GHz ISM band and using wide band modulation techniques; Harmonised Standard covering the essential requirements of article 3.2 of Directive 2014/53/EU

For further applied test standards please refer to section 3 of this test report.

Test Item

Kind of test item: Single chip Bluetooth solution for wearables

Model name: DA14683

Frequency: ISM band 2400 MHz to 2483.5 MHz

Technology tested: Bluetooth® LE

Antenna: Integrated antenna

Power supply: 5.0 V DC by USB

Temperature range: -40°C to +85°C



This test report is electronically signed and valid without handwritten signature. For verification of the electronic signatures, the public keys can be requested at the testing laboratory.

Test report authorized:

Joerg Warken
Lab Manager
Radio Communications & EMC

Test performed:

Mihail Dorongovskij
Lab Manager
Radio Communications & EMC

1 Table of contents

| | | |
|---------|--|----|
| 1 | Table of contents | 2 |
| 2 | General information | 3 |
| 2.1 | Notes and disclaimer | 3 |
| 2.2 | Application details..... | 3 |
| 2.3 | Test laboratories sub-contracted | 3 |
| 3 | Test standard/s | 4 |
| 4 | Test environment..... | 4 |
| 5 | Test item..... | 5 |
| 5.1 | General description..... | 5 |
| 5.2 | Additional information | 5 |
| 6 | Description of the test setup..... | 6 |
| 6.1 | Shielded fully anechoic chamber | 7 |
| 6.2 | Conducted measurements | 8 |
| 7 | Summary of measurement results | 9 |
| 8 | Additional comments..... | 10 |
| 9 | EUT classification: | 11 |
| 10 | Measurement results | 12 |
| 10.1 | Antenna gain | 12 |
| 10.2 | RF output power | 13 |
| 10.3 | Power spectral density..... | 14 |
| 10.4 | Occupied channel bandwidth | 17 |
| 10.5 | Transmitter unwanted emissions in the out-of-band domain | 19 |
| 10.6 | Transmitter unwanted emissions in the spurious domain..... | 21 |
| 10.7 | Receiver spurious emissions | 26 |
| 10.8 | Receiver blocking | 31 |
| 11 | Measurement uncertainty..... | 34 |
| Annex A | Glossary..... | 35 |
| Annex B | Document history | 36 |
| Annex C | Accreditation Certificate | 36 |

2 General information

2.1 Notes and disclaimer

The test results of this test report relate exclusively to the test item specified in this test report. CTC advanced GmbH does not assume responsibility for any conclusions and generalizations drawn from the test results with regard to other specimens or samples of the type of the equipment represented by the test item.

The test report may only be reproduced or published in full. Reproduction or publication of extracts from the report requires the prior written approval of CTC advanced GmbH.

The testing service provided by CTC advanced GmbH has been rendered under the current "General Terms and Conditions for CTC advanced GmbH".

CTC advanced GmbH will not be liable for any loss or damage resulting from false, inaccurate, inappropriate or incomplete product information provided by the customer.

Under no circumstances does the CTC advanced GmbH test report include any endorsement or warranty regarding the functionality, quality or performance of any other product or service provided.

Under no circumstances does the CTC advanced GmbH test report include or imply any product or service warranties from CTC advanced GmbH, including, without limitation, any implied warranties of merchantability, fitness for purpose, or non-infringement, all of which are expressly disclaimed by CTC advanced GmbH.

All rights and remedies regarding vendor's products and services for which CTC advanced GmbH has prepared this test report shall be provided by the party offering such products or services and not by CTC advanced GmbH. In no case this test report can be considered as a Letter of Approval.

This test report is electronically signed and valid without handwritten signature. For verification of the electronic signatures, the public keys can be requested at the testing laboratory.

2.2 Application details

| | |
|------------------------------------|------------|
| Date of receipt of order: | 2018-05-15 |
| Date of receipt of test item: | 2018-05-28 |
| Start of test: | 2018-05-28 |
| End of test: | 2018-05-28 |
| Person(s) present during the test: | -/- |

2.3 Test laboratories sub-contracted

None

3 Test standard/s

| Test standard | Date | Description |
|---------------------------|---------|--|
| ETSI EN 300 328 V2.1.1 | 2016-11 | Wideband transmission systems; Data transmission equipment operating in the 2.4 GHz ISM band and using wide band modulation techniques; Harmonised Standard covering the essential requirements of article 3.2 of Directive 2014/53/EU |

4 Test environment

| | | | |
|---------------------------|---|-------------------------------------|---|
| Temperature | : | T_{nom} T_{max} T_{min} | +22 °C during room temperature tests +85 °C during high temperature tests -40 °C during low temperature tests |
| Relative humidity content | : | | 55 % |
| Barometric pressure | : | | not relevant for this kind of testing |
| Power supply | : | V_{nom} V_{max} V_{min} | 5.0 V DC by USB No tests under extreme voltage conditions required. No tests under extreme voltage conditions required. |

5 Test item

5.1 General description

| | | |
|---|---|--|
| Kind of test item | : | Single chip Bluetooth solution for wearables |
| Type identification | : | DA14683 |
| S/N serial number | : | 1815_00025 |
| HW hardware status | : | BB |
| SW software status | : | SDK V1.0.10 and later |
| Frequency band | : | ISM band 2400 MHz to 2483.5 MHz |
| Type of radio transmission : Use of frequency spectrum : | : | Other than FHSS |
| Type of modulation | : | GFSK |
| Number of channels | : | 40 |
| Channel bandwidth (B) | : | 1 MHz |
| Channel spacing | : | 2 MHz |
| Receiver category | : | 2 |
| Antenna | : | Integrated antenna |
| Power supply | : | 5.0 V DC by USB |
| Temperature range | : | -40°C to +85°C |

5.2 Additional information

The content of the following annexes is defined in the QA. It may be that not all of the listed annexes are necessary for this report, thus some values in between may be missing.

Test setup and EUT photos are included in test report: 1-6565/18-01-01_AnnexA
 1-6565/18-01-01_AnnexC

6 Description of the test setup


Typically, the calibrations of the test apparatus are commissioned to and performed by an accredited calibration laboratory. The calibration intervals are determined in accordance with the DIN EN ISO/IEC 17025. In addition to the external calibrations, the laboratory executes comparison measurements with other calibrated test systems or effective verifications. Weekly chamber inspections and range calibrations are performed. Where possible, RF generating and signaling equipment as well as measuring receivers and analyzers are connected to an external high-precision 10 MHz reference (GPS-based or rubidium frequency standard).

In order to simplify the identification of the equipment used at some special tests, some items of test equipment and ancillaries can be provided with an identifier or number in the equipment list below (Lab/Item).

Agenda: Kind of Calibration

| | | | |
|------|--|-----|--|
| k | calibration / calibrated | EK | limited calibration |
| ne | not required (k, ev, izw, zw not required) | zw | cyclical maintenance (external cyclical maintenance) |
| ev | periodic self verification | izw | internal cyclical maintenance |
| Ve | long-term stability recognized | g | blocked for accredited testing |
| vlk! | Attention: extended calibration interval | | |
| NK! | Attention: not calibrated | *) | next calibration ordered / currently in progress |

6.1 Shielded fully anechoic chamber



Measurement distance: tri-log antenna and horn antenna 3 meter

$$OP = AV + D - G + CA$$

(OP-radiated output power; AV-analyzer value; D-free field attenuation of measurement distance; G-antenna gain+amplifier gain; CA-loss signal path)


Example calculation:

$$OP \text{ [dBm]} = -65.0 \text{ [dBm]} + 50 \text{ [dB]} - 20 \text{ [dBi]} + 5 \text{ [dB]} = -30 \text{ [dBm]} \text{ (1 } \mu\text{W)}$$

Equipment table:

| No. | Lab / Item | Equipment | Type | Manufacturer | Serial No. | INV. No. | Kind of Calibration | Last Calibration | Next Calibration |
|-----|------------|--|---------------------------------|-----------------------------|------------|-----------|---------------------|------------------|------------------|
| 1 | A, B | Anechoic chamber | FAC 3/5m | MWB / TDK | 87400/02 | 300000996 | ev | -/- | -/- |
| 2 | A, B | Double-Ridged Waveguide Horn Antenna 1-18.0GHz | 3115 | EMCO | 9107-3697 | 300001605 | vKII! | 14.02.2017 | 13.02.2019 |
| 3 | A, B | Switch / Control Unit | 3488A | HP | * | 300000199 | ne | -/- | -/- |
| 4 | B | Band Reject filter | WRCG2400/2483-2375/2505-50/10SS | Wainwright | 11 | 300003351 | ev | -/- | -/- |
| 5 | A, B | EMI Test Receiver 20Hz- 26,5GHz | ESU26 | R&S | 100037 | 300003555 | k | 20.12.2017 | 19.12.2018 |
| 6 | B | Highpass Filter | WHK1.1/15G-10SS | Wainwright | 3 | 300003255 | ev | -/- | -/- |
| 7 | B | Highpass Filter | WHKX7.0/18G-8SS | Wainwright | 19 | 300003790 | ne | -/- | -/- |
| 8 | A, B | Broadband Amplifier 0.5-18 GHz | CBLU5184540 | CERNEX | 22049 | 300004481 | ev | -/- | -/- |
| 9 | B | Broadband Amplifier 5-13 GHz | CBLU5135235 | CERNEX | 22010 | 300004491 | ev | -/- | -/- |
| 10 | A, B | 4U RF Switch Platform | L4491A | Agilent Technologies | MY50000037 | 300004509 | ne | -/- | -/- |
| 11 | A, B | NEXIO EMV-Software | BAT EMC V3.16.0.49 | EMCO | | 300004682 | ne | -/- | -/- |
| 12 | A, B | PC | ExOne | F+W | | 300004703 | ne | -/- | -/- |
| 13 | B | TRILOG Broadband Test-Antenna | VULB9163 | Schwarzbeck Mess Elektronik | 01029 | 300005379 | k | 07.04.2017 | 06.04.2020 |

6.2 Conducted measurements



OP = AV + CA
(OP-output power; AV-analyzer value; CA-loss signal path)

Example calculation:

OP [dBm] = 6.0 [dBm] + 11.7 [dB] = 17.7 [dBm] (58.88 mW)

Equipment table:

| No. | Lab / Item | Equipment | Type | Manufacturer | Serial No. | INV. No. | Kind of Calibration | Last Calibration | Next Calibration |
|-----|------------|--|-------------------|--------------------------|------------------|-----------|---------------------|------------------|------------------|
| 1 | B | Climatic Box | VT 4011 | Voetsch Industrietechnik | 58566230600010 | 300005363 | ev | 01.06.2017 | 31.05.2019 |
| 2 | A, B, C | Switch / Control Unit | 3488A | HP | | 300000929 | ne | -/- | -/- |
| 3 | A, B, C | Directional Coupler | 101020010 | Krytar | 70215 | 300002840 | ev | -/- | -/- |
| 4 | A, B, C | DC-Blocker | 8143 | Inmet Corp. | none | 300002842 | ne | -/- | -/- |
| 5 | A, B, C | Powersplitter | 6005-3 | Inmet Corp. | | 300002841 | ev | -/- | -/- |
| 6 | C | RF and Microwave Signal Generator up to 20 GHz | SMB100A | R&S | 176183 | 300004853 | k | 09.10.2017 | 08.10.2020 |
| 7 | A | Signal Analyzer 30GHz | FSV30 | R&S | 103170 | 300004855 | k | 30.01.2017 | 29.01.2019 |
| 8 | B | Open Switch and Control Unit and Power Sensors | OSP120 incl. B157 | R&S | 101274, 100877 | 300004825 | ne | -/- | -/- |
| 9 | A, B, C | RF-Cable | ST18/SMAm/SMAm/48 | Huber & Suhner | Batch no. 699866 | 400001189 | ev | -/- | -/- |
| 10 | A, B, C | RF-Cable | ST18/SMAm/SMAm/48 | Huber & Suhner | Batch no. 14844 | 400001190 | ev | -/- | -/- |

7 Summary of measurement results

| | |
|-------------------------------------|--|
| <input checked="" type="checkbox"/> | No deviations from the technical specifications were ascertained |
| <input type="checkbox"/> | There were deviations from the technical specifications ascertained |
| <input type="checkbox"/> | This test report is only a partial test report. The content and verdict of the performed test cases are listed below. |

| TC identifier | Description | verdict | date | Remark |
|---------------|----------------------------------|------------|------------|--------|
| RF-Testing | ETSI EN 300 328 V2.1.1 (2016-11) | See table! | 2018-05-30 | -/- |

| Test specification clause | Test case | temperature conditions | power source voltages | Mode | C | NC | NA | NP | Remark |
|---------------------------|--|------------------------|-----------------------|------|-------------------------------------|--------------------------|-------------------------------------|--------------------------|--------|
| 4.3.2.2 5.4.2 | RF output power | Nominal | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | -/- |
| | | Low | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | |
| | | High | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | |
| 4.3.2.4 5.4.2 | Duty cycle, Tx-sequence, Tx-gap, medium utilization | Nominal | Nominal | -/- | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.2.3 5.4.3 | Power spectral density | Nominal | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.1.4 5.4.4 | Accumulated transmit time, freq. occupation and hopping sequence | Nominal | Nominal | -/- | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.1.5 5.4.5 | Hopping frequency separation | Nominal | Nominal | -/- | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.2.6 5.4.6 | Adaptivity | Nominal | Nominal | -/- | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.2.7 5.4.7 | Occupied channel bandwidth | Nominal | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.2.8 5.4.8 | Transmitter unwanted emissions in the out-of-band domain | Nominal | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.2.9 5.4.9 | Transmitter unwanted emissions in the spurious domain | Nominal | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.2.10 5.4.10 | Receiver spurious emissions | Nominal | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.2.11 5.4.11 | Receiver blocking | Nominal | Nominal | GFSK | <input checked="" type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | <input type="checkbox"/> | -/- |
| 4.3.2.12 | Geo-location | Nominal | Nominal | -/- | <input type="checkbox"/> | <input type="checkbox"/> | <input checked="" type="checkbox"/> | <input type="checkbox"/> | -/- |

| | | | |
|----|----------------|----|---------------|
| C | Compliant | NC | Not compliant |
| NA | Not applicable | NP | Not performed |

8 Additional comments

The Bluetooth® word mark and logos are owned by the Bluetooth SIG Inc. and any use of such marks by CTC advanced GmbH is under license.

- Reference documents: Bluetooth® Core Specification (up to 5.0)
Customer Questionnaire_1-6565_18-01 _SL v1.docx
- Special test descriptions: The tests have been performed with the EUT mounted on an evaluation board.
The evaluation board is powered by a notebook via USB.
During the radiated tests, the emission at 100 MHz is caused by the notebook and its power supply.
- Configuration descriptions: TX tests were performed with 255 bytes payload packets and static PRBS pattern payload.
RX tests were performed with 255 bytes payload packets.
- Test mode:
- Bluetooth direct test mode enabled
(EUT is controlled via CBT/CMW)
 - Special software is used.
EUT is transmitting pseudo random data by itself

9 EUT classification:

- Type of equipment:
- stand alone equipment
 - plug in radio equipment
 - combined equipment
- Modulation types:
- Wide band modulation (none hopping – e.g. DSSS, OFDM)
 - Frequency hopping spread spectrum (FHSS)
- Adaptive equipment:
- Yes, LBT-based
 - Yes, non-LBT-based
 - Yes (but can be disabled)
 - No
- Antennas and transmission operating modes:
- Operating mode 1 (single antenna)**
 - Equipment with 1 antenna,
 - Equipment with 2 diversity antennas operating in switched diversity mode by which at any moment in time only 1 antenna is used,
 - Smart antenna system with 2 or more transmit/receive chains, but operating in a mode where only 1 transmit/receive chain is used)
 - Operating mode 2 (multiple antennas, no beamforming)**
 - Equipment operating in this mode contains a smart antenna system using two or more transmit/receive chains simultaneously but without beamforming.
 - Operating mode 3 (multiple antennas, with beamforming)**
 - Equipment operating in this mode contains a smart antenna system using two or more transmit/receive chains simultaneously with beamforming.
In addition to the antenna assembly gain (G), the beamforming gain (Y) may have to be taken into account when performing the measurements.

10 Measurement results

10.1 Antenna gain

Measurement:

The antenna gain of the system is calculated by the difference of radiated power in EIRP and the conducted power of the module.

| Measurement parameters | |
|-------------------------|---|
| Detector | Peak |
| Sweep time | Auto |
| Resolution bandwidth | 3 MHz |
| Video bandwidth | 3 MHz |
| Trace mode | Max hold |
| Test setup | See sub clause 6.2 – A (conducted) See sub clause 6.1 – A (radiated) |
| Measurement uncertainty | See sub clause 11 |

Limits:

No restriction!

Results:

| T _{nom} | V _{nom} | lowest channel | middle channel | highest channel |
|---|------------------|----------------|----------------|-----------------|
| Conducted peak power [dBm] Measured with GFSK modulation | | -0.3 | -0.9 | -0.6 |
| Radiated peak power [dBm] Measured with GFSK modulation | | 2.1 | 1.6 | 0.7 |
| Gain [dBi] Calculated | | 2.4 | 2.5 | 1.3 |

10.2 RF output power

Measurement:

The Output power measurement is used to detect the maximum power of a device under test. The measurement is performed according to the EN specification 5.4.2.

Measurement parameters:

Instrument: Power Meter measuring average burst Power of a least 10 packets

| | |
|-------------------------|------------------------|
| Test setup | See sub clause 6.2 – B |
| Measurement uncertainty | See sub clause 11 |

Performed: Conducted
 Radiated (only if no conducted sample is provided)

Limits:

| | |
|----------------------------|--|
| For adaptive equipment | 20 dBm |
| For non-adaptive equipment | Declared by the supplier and shall not exceed 20 dBm |

Results:

| Test conditions | | Maximum conducted burst power in 10 measured bursts [dBm] | | |
|------------------|------------------|---|----------------|-----------------|
| | | lowest channel | middle channel | highest channel |
| T _{nom} | V _{nom} | -0.3 | -0.9 | -0.6 |
| T _{min} | V _{nom} | 0.5 | -0.1 | 0.3 |
| T _{max} | V _{nom} | -1.0 | -1.5 | -1.3 |

P = max cond. burst power (A) + antenna gain (G) + beamforming gain (Y)

With:

Beamforming gain (Y) = 0 (SISO)

| | |
|--|------------------------------|
| Result P [dBm] E.I.R.P (lowest channel): | 0.5 dBm + 2.4 dBi = 2.9 dBm |
| Result P [dBm] E.I.R.P (middle channel): | -0.1 dBm + 2.5 dBi = 2.4 dBm |
| Result P [dBm] E.I.R.P (highest channel): | 0.3 dBm + 1.3 dBi = 1.6 dBm |

10.3 Power spectral density

Description:

The power spectral density is the mean equivalent isotropically radiated power (E.I.R.P.) density during a transmission burst.

| Measurement parameters | |
|-------------------------|---|
| Detector | RMS |
| Sweep time | ≥ 10s |
| Resolution bandwidth | 10 kHz |
| Video bandwidth | 30 kHz |
| Span | Start: 2400.00 MHz Stop: 2483.50 MHz |
| Trace mode | Max hold |
| Test setup | See sub clause 6.2 - A |
| Measurement uncertainty | See sub clause 11 |

Performed: Conducted
 Radiated (only if no conducted sample is provided)

Limits:


| | |
|---|-----------------------------------|
| Under normal test conditions only (including antenna gain) | -20 dBW / 1 MHz 10 dBm / 1 MHz |
|---|-----------------------------------|

Results:


| | Measured power density | | |
|--|------------------------|----------------|-----------------|
| | lowest channel | middle channel | highest channel |
| 1) Power density (max peak) conducted [dBm/1MHz] | -1.9 | -2.3 | -2.0 |
| 2) Sum of all raw points [dBm] | -1.9 | -2.3 | -2.0 |
| 3) Max EIRP [dBm] | 2.1 | 1.6 | 1.9 |
| 4) Correction factor (3-2) | 4.0 | 3.9 | 3.9 |
| Power density (max peak) radiated (1+4) [dBm/1MHz] | 2.1 | 1.6 | 1.9 |

Plots:


Plot 1: lowest channel



Plot 2: middle channel



Plot 3: highest channel



10.4 Occupied channel bandwidth

Measurement:

The occupied channel bandwidth is the bandwidth that contains 99 % of the power of the signal.

| Measurement parameters | |
|-------------------------|------------------------|
| Detector | RMS |
| Sweep time | 1s |
| Resolution bandwidth | 30 kHz |
| Video bandwidth | 100 kHz |
| Span | 3 MHz |
| Trace mode | Max hold |
| Test setup | See sub clause 6.2 - A |
| Measurement uncertainty | See sub clause 11 |

Performed: Conducted
 Radiated (only if no conducted sample is provided)

Limits:

The occupied channel bandwidth shall fall completely within the band.


For non-adaptive systems using wide band modulations other than FHSS and with e.i.r.p greater than 10 dBm, the occupied channel bandwidth shall be less than 20 MHz.

Results:

| 99% bandwidth [kHz] | |
|---------------------|-----------------|
| Lowest channel | Highest channel |
| 1053 | 1047 |

Plots:

Plot 1: GFSK modulation, lowest channel



Plot 2: GFSK modulation, highest channel



10.5 Transmitter unwanted emissions in the out-of-band domain

Description:

Transmitter unwanted emissions in the out-of-band domain are emissions when the equipment is in transmit mode, on frequencies immediately outside the necessary bandwidth which results from the modulation process, but excluding spurious.


| Measurement parameters | |
|-------------------------|--|
| Detector | RMS |
| Sweep time | depending on packet length (min 120% of packet length) |
| Resolution bandwidth | 1 MHz |
| Video bandwidth | 3 MHz |
| Span | Zero span |
| Trace mode | Video trigger |
| Test setup | See sub clause 6.2 - A |
| Measurement uncertainty | See sub clause 11 |

Performed: Conducted
 Radiated (only if no conducted sample is provided)

Limits:

The transmitter unwanted emissions in the out-of-band domain but outside the allocated band, shall not exceed the values provided by the mask.

NOTE: Within the 2400 MHz to 2483.5 MHz band, the Out-of-band emissions are fulfilled by compliance with the Occupied Channel Bandwidth requirement in clause 4.3.2.6.




Results

| Unwanted emissions [dBm] (including antenna gain) | |
|--|-----------|
| GFSK, channel BW see plots | |
| 2400 MHz - 2BW to 2400 MHz – BW Limit: < -20dBm/MHz | compliant |
| 2400 MHz - BW to 2400 MHz Limit: < -10dBm/MHz | compliant |
| 2483.5 MHz to 2483.5 MHz + BW Limit: < -10dBm/MHz | compliant |
| 2483.5 MHz + BW to 2483.5 MHz + 2BW Limit: < -20dBm/MHz | compliant |

Plots:

Plot 1:



10.6 Transmitter unwanted emissions in the spurious domain

Description:

Transmitter unwanted emissions in the spurious domain are emissions outside the allocated band and outside the out-of-band domain when the equipment is in transmit mode.

Pre-scan:

| Measurement parameters | |
|-------------------------|---|
| Detector | Peak |
| Sweep time | 1s |
| Resolution bandwidth | Below 1 GHz: 100 kHz / above 1MHz |
| Video bandwidth | Below 1 GHz: 300 kHz / above 3MHz |
| Trace mode | Max hold |
| Test setup | See sub clause 6.2 – A (conducted) See sub clause 6.1 – B (radiated) |
| Measurement uncertainty | See sub clause 11 |

Any emissions identified during the sweeps in the pre-scan and that fall within the 6 dB range below the applicable limit, shall be individually measured using the procedure “retest”.

Retest:

| Measurement parameters | |
|-------------------------|---|
| Detector | RMS |
| Measurement mode | Time domain power |
| Sweep time | 500ms |
| Resolution bandwidth | Below 1 GHz: 100 kHz / above 1MHz |
| Video bandwidth | Below 1 GHz: 300 kHz / above 3MHz |
| Span | Zero span |
| Trace mode | Single sweep |
| Test setup | See sub clause 6.2 – A (conducted) See sub clause 6.1 – B (radiated) |
| Measurement uncertainty | See sub clause 11 |

Performed: Conducted
 Radiated

Limits:


| State | Max. spurious level | | |
|-----------------|---|---------------------------------|-------------------------------|
| | 47 MHz to 74 MHz 87.5 MHz to 118 MHz 174 MHz to 230 MHz 470 MHz to 862 MHz | Other frequencies ≤ 1000 MHz | All frequencies > 1000 MHz |
| Operating | 4.0 nW (-54 dBm) | 250 nW (-36 dBm) | 1.00 µW (-30 dBm) |
| Receiver / Idle | 2.0 nW (-57 dBm) | 2.0 nW (-57 dBm) | 20.0 nW (-47 dBm) |

Results: conducted


| lowest channel | | | highest channel | | |
|----------------|-------------------|-------------|---|-------------------|-------------|
| f [MHz] | Detector Peak/RMS | Level [dBm] | f [MHz] | Detector Peak/RMS | Level [dBm] |
| 4804 | Peak | -35.8 | All detected peaks are more than 6 dB below the limit | | |
| 4804 | TDP burst | -38.7 | | | |
| | | | | | |
| | | | | | |

Plots:

Plot 1: GFSK, lowest channel, positive peak



Plot 2: GFSK, highest channel, positive peak




Results: radiated

| lowest channel | | | highest channel | | |
|---|-------------------|-------------|---|-------------------|-------------|
| f [MHz] | Detector Peak/RMS | Level [dBm] | f [MHz] | Detector Peak/RMS | Level [dBm] |
| All detected peaks are more than 6 dB below the limit | | | All detected peaks are more than 6 dB below the limit | | |
| | | | | | |
| | | | | | |
| | | | | | |

NOTE: The emission at 100 MHz is caused by the notebook and its power supply


Plots:

Plot 1: 30 MHz to 12.75 GHz, lowest channel



The carrier signal is notched with a 2.4 GHz band rejection filter.

Plot 2: 30 MHz to 12.75 GHz, highest channel



The carrier signal is notched with a 2.4 GHz band rejection filter.

10.7 Receiver spurious emissions

Description:

Receiver/idle unwanted emissions in the spurious domain are emissions outside the allocated band and outside the out-of-band domain when the equipment is in receiver/idle mode.

Pre-scan:

| Measurement parameters | |
|-------------------------|---|
| Detector | Peak |
| Sweep time | 1s |
| Resolution bandwidth | Below 1 GHz: 100 kHz / above 1MHz |
| Video bandwidth | Below 1 GHz: 300 kHz / above 3MHz |
| Trace mode | Max hold |
| Test setup | See sub clause 6.2 – A (conducted) See sub clause 6.1 – A (radiated) |
| Measurement uncertainty | See sub clause 11 |

Any emissions identified during the sweeps in the pre-scan and that fall within the 6 dB range below the applicable limit, shall be individually measured using the procedure “retest”.

Retest:

| Measurement parameters | |
|-------------------------|---|
| Detector | RMS |
| Measurement mode | Time domain power |
| Sweep time | 30ms |
| Resolution bandwidth | Below 1 GHz: 100 kHz / above 1MHz |
| Video bandwidth | Below 1 GHz: 300 kHz / above 3MHz |
| Span | Zero span |
| Trace mode | Single sweep |
| Test setup | See sub clause 6.2 – A (conducted) See sub clause 6.1 – A (radiated) |
| Measurement uncertainty | See sub clause 11 |

Performed: Conducted
 Radiated

Limits:


| State | Max. spurious level | | |
|---------------|---|---------------------------------|-------------------------------|
| | 47 MHz to 74 MHz 87,5 MHz to 118 MHz 174 MHz to 230 MHz 470 MHz to 862 MHz | Other frequencies ≤ 1000 MHz | All frequencies > 1000 MHz |
| Operating | 4.0 nW (-54 dBm) | 250 nW (-36 dBm) | 1.00 μW (-30 dBm) |
| Receiver/idle | 2.0 nW (-57 dBm) | 2.0 nW (-57 dBm) | 20.0 nW (-47 dBm) |

Results: conducted


| lowest channel | | | highest channel | | |
|---|-------------------|-------------|---|-------------------|-------------|
| f [MHz] | Detector Peak/RMS | Level [dBm] | f [MHz] | Detector Peak/RMS | Level [dBm] |
| All detected peaks are more than 6 dB below the limit | | | All detected peaks are more than 6 dB below the limit | | |
| | | | | | |
| | | | | | |
| | | | | | |

Plots:

Plot 1: Receiver, 30 MHz to 12.75 GHz, lowest channel



Plot 2: Receiver, 30 MHz to 12.75 GHz, highest channel




Results: radiated

| lowest channel | | | highest channel | | |
|----------------|-----------------------|-------------|-----------------|-----------------------|-------------|
| f [MHz] | Detector Peak/RMS | Level [dBm] | f [MHz] | Detector Peak/RMS | Level [dBm] |
| 266 | Peak | -62.1 | 4962 | Peak | -43.9 |
| 266 | RMS time domain power | -70.3 | 4962 | RMS time domain power | -50.4 |
| 4806 | Peak | -45.2 | | | |
| 4806 | RMS time domain power | -51.7 | | | |


NOTE: The emission at 100 MHz is caused by the notebook and its power supply

Plots:

Plot 1: Receiver, 30 MHz to 12.75 GHz, lowest channel



Plot 2: Receiver, 30 MHz to 12.75 GHz, highest channel



10.8 Receiver blocking

Description:

Receiver blocking is a measure of the ability of the equipment to receive a wanted signal on its operating channel without exceeding a given degradation in the presence of an unwanted signal (blocking signal) on frequencies other than those of the operating band.

The CBT is used as the signalling unit. Starting at a typical high signalling level (e.g. -70.0 dBm) the CBT is sending packets to the EUT. The PER is logged and the signalling level gets reduced in 1 dB steps until the PER is higher than 10%. This is the P_{min} value which is used as described in tables 1-3 depending on the receiver category of the EUT.

| Measurement parameters | |
|-------------------------|------------------------|
| Test setup | See sub clause 6.2 – C |
| Measurement uncertainty | See sub clause 11 |

Performed: Conducted

Radiated

Table 1: Receiver blocking parameters for receiver category 1 equipment:

| Wanted signal mean power from companion device (dBm) | Blocking signal frequency (MHz) | Blocking signal power (dBm) (see note 2) | Type of blocking signal |
|--|---|--|-------------------------|
| $P_{min} + 6$ dB | 2 380.0 2 503.5 | -53 | CW |
| $P_{min} + 6$ dB | 2 300.0 2 330.0 2 360.0 | -47 | CW |
| $P_{min} + 6$ dB | 2 523.5 2 553.5 2 583.5 2 613.5 2 643.5 2 673.5 | -47 | CW |
| NOTE 1: | P_{min} is the minimum level of wanted signal (in dBm) required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal. | | |
| NOTE 2: | The levels specified are levels in front of the UUT antenna. In case of conducted measurements, the levels have to be corrected by the actual antenna assembly gain. | | |

Table 2: Receiver blocking parameters for receiver category 2 equipment:

| Wanted signal mean power from companion device (dBm) | Blocking signal frequency (MHz) | Blocking signal power (dBm) (see note 2) | Type of blocking signal |
|--|--|--|-------------------------|
| $P_{\min} + 6$ dB | 2 380.0 2 503.5 | -57 | CW |
| $P_{\min} + 6$ dB | 2 300.0 2 583.5 | -47 | CW |
| NOTE 1: | P_{\min} is the minimum level of wanted signal (in dBm) required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal. | | |
| NOTE 2: | The levels specified are levels in front of the UUT antenna. In case of conducted measurements, the levels have to be corrected by the actual antenna assembly gain. | | |

Table 3: Receiver blocking parameters for receiver category 3 equipment:

| Wanted signal mean power from companion device (dBm) | Blocking signal frequency (MHz) | Blocking signal power (dBm) (see note 2) | Type of blocking signal |
|--|--|--|-------------------------|
| $P_{\min} + 12$ dB | 2 380.0 2 503.5 | -57 | CW |
| $P_{\min} + 12$ dB | 2 300.0 2 583.5 | -47 | CW |
| NOTE 1: | P_{\min} is the minimum level of wanted signal (in dBm) required to meet the minimum performance criteria as defined in clause 4.3.1.12.3 in the absence of any blocking signal. | | |
| NOTE 2: | The levels specified are levels in front of the UUT antenna. In case of conducted measurements, the levels have to be corrected by the actual antenna assembly gain. | | |

Limits:

| | Channel | |
|-------------------------|----------------|-----------------|
| | Lowest channel | Highest channel |
| Packet error rate limit | 10% PER* | |

*The manufacturer may declare alternative performance criteria as long as that is appropriate for the intended use of the equipment

Results: Tests according requirements for category 2 receiver equipment

| RX chan..... | PER..... | Psent... | Prec.... | RXL[dBm].. | Limit... | IntFr. [MHz].. | IntL [dBm].. | verdict |
|--------------|----------|----------|----------|------------|----------|----------------|--------------|-------------|
| 2402000000 | 1.000% | 1500 | 1485 | -75 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -76 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -77 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -78 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -79 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -80 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -81 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 0.066% | 1500 | 1499 | -82 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 0.400% | 1500 | 1494 | -83 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 0.266% | 1500 | 1496 | -84 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 3.066% | 1500 | 1454 | -85 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 1.599% | 1500 | 1476 | -86 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 2.466% | 1500 | 1463 | -87 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 2.600% | 1500 | 1461 | -88 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 5.000% | 1500 | 1425 | -89 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 9.666% | 1500 | 1355 | -90 | <= 10% | OFF | OFF | PASS |
| 2402000000 | 23.79% | 1500 | 1143 | -91 | <= 10% | OFF | OFF | Ref. |
| | | | | | | | | Sensitivity |
| 2402000000 | 1E-00% | 1500 | 1500 | -85 | <= 10% | 2380.0 | -57 | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -85 | <= 10% | 2503.5 | -57 | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -85 | <= 10% | 2300.5 | -47 | PASS |
| 2402000000 | 1E-00% | 1500 | 1500 | -85 | <= 10% | 2583.5 | -47 | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -75 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -76 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -77 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -78 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -79 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -80 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -81 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -82 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -83 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -84 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 0.599% | 1500 | 1491 | -85 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 1.066% | 1500 | 1484 | -86 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 0.466% | 1500 | 1493 | -87 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 2.933% | 1500 | 1456 | -88 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 5.000% | 1500 | 1425 | -89 | <= 10% | OFF | OFF | PASS |
| 2480000000 | 13.00% | 1500 | 1305 | -90 | <= 10% | OFF | OFF | Ref. |
| | | | | | | | | Sensitivity |
| 2480000000 | 1E-00% | 1500 | 1500 | -84 | <= 10% | 2380.0 | -57 | PASS |
| 2480000000 | 1E-00% | 1500 | 1500 | -84 | <= 10% | 2503.5 | -57 | PASS |
| 2480000000 | 0.066% | 1500 | 1499 | -84 | <= 10% | 2300.5 | -47 | PASS |
| 2480000000 | 0.066% | 1500 | 1499 | -84 | <= 10% | 2583.5 | -47 | PASS |

11 Measurement uncertainty

| Measurement uncertainty | |
|-----------------------------------|---------|
| Occupied channel bandwidth | ±5 % |
| RF output power, conducted | ±1.5 dB |
| Power spectral density, conducted | ±3 dB |
| Unwanted emissions, conducted | ±3 dB |
| All emissions, radiated | ±3 dB |
| Temperature | ±1 °C |
| Humidity | ±5 % |
| DC and low frequency voltages | ±3 % |
| Time | ±5 % |
| Duty cycle | ±5 % |

Annex A Glossary

| | |
|------------------------|--|
| EUT | Equipment under test |
| DUT | Device under test |
| UUT | Unit under test |
| GUE | GNSS User Equipment |
| ETSI | European Telecommunications Standards Institute |
| EN | European Standard |
| FCC | Federal Communications Commission |
| FCC ID | Company Identifier at FCC |
| IC | Industry Canada |
| PMN | Product marketing name |
| HMN | Host marketing name |
| HVIN | Hardware version identification number |
| FVIN | Firmware version identification number |
| EMC | Electromagnetic Compatibility |
| HW | Hardware |
| SW | Software |
| Inv. No. | Inventory number |
| S/N or SN | Serial number |
| C | Compliant |
| NC | Not compliant |
| NA | Not applicable |
| NP | Not performed |
| PP | Positive peak |
| QP | Quasi peak |
| AVG | Average |
| OC | Operating channel |
| OCW | Operating channel bandwidth |
| OBW | Occupied bandwidth |
| OOB | Out of band |
| DFS | Dynamic frequency selection |
| CAC | Channel availability check |
| OP | Occupancy period |
| NOP | Non occupancy period |
| DC | Duty cycle |
| PER | Packet error rate |
| CW | Clean wave |
| MC | Modulated carrier |
| WLAN | Wireless local area network |
| RLAN | Radio local area network |
| DSSS | Dynamic sequence spread spectrum |
| OFDM | Orthogonal frequency division multiplexing |
| FHSS | Frequency hopping spread spectrum |
| GNSS | Global Navigation Satellite System |
| C/N₀ | Carrier to noise-density ratio, expressed in dB-Hz |

Annex B Document history

| Version | Applied changes | Date of release |
|---------|-----------------|-----------------|
| -/- | Initial release | 2018-05-30 |

Annex C Accreditation Certificate

| first page | last page |
|---|--|
|  <p>  Deutsche Akkreditierungsstelle GmbH Entrusted according to Section 8 subsection 1 AkkStelleG in connection with Section 1 subsection 1 AkkStelleGBV Signatory to the Multilateral Agreements of EA, ILAC and IAF for Mutual Recognition  Accreditation The Deutsche Akkreditierungsstelle GmbH attests that the testing laboratory CTC advanced GmbH Untertürkheimer Straße 6-10, 66117 Saarbrücken is competent under the terms of DIN EN ISO/IEC 17025:2005 to carry out tests in the following fields: Telecommunication The accreditation certificate shall only apply in connection with the notice of accreditation of 02.06.2017 with the accreditation number D-PL-12076-01 and is valid until 21.04.2021. It comprises the cover sheet, the reverse side of the cover sheet and the following annex with a total of 43 pages. Registration number of the certificate: D-PL-12076-01-03 Frankfurt, 02.06.2017  Dipl.-Ing. (FH) Ralf Böber Head of Division See notes enclosed. </p> |  <p> Deutsche Akkreditierungsstelle GmbH Office Berlin Spittelmarkt 10 10117 Berlin Office Frankfurt am Main Europa-Allee 52 60327 Frankfurt am Main Office Braunschweig Bundesallee 100 38116 Braunschweig The publication of extracts of the accreditation certificate is subject to the prior written approval by Deutsche Akkreditierungsstelle GmbH (DAKKS). Exempted is the unchanged form of separate disseminations of the cover sheet by the conformity assessment body mentioned overleaf. No impression shall be made that the accreditation also extends to fields beyond the scope of accreditation attested by DAKKS. The accreditation was granted pursuant to the Act on the Accreditation Body (AkkStelleG) of 31 July 2009 (Federal Law Gazette I p. 2625) and the Regulation (EC) No 765/2008 of the European Parliament and of the Council of 9 July 2008 setting out the requirements for accreditation and market surveillance relating to the marketing of products (Official Journal of the European Union L 218 of 9 July 2008, p. 30). DAKKS is a signatory to the Multilateral Agreements for Mutual Recognition of the European co-operation for Accreditation (EA), International Accreditation Forum (IAF) and International Laboratory Accreditation Cooperation (ILAC). The signatories to these agreements recognise each other's accreditations. The up-to-date state of membership can be retrieved from the following websites: EA: www.european-accreditation.org ILAC: www.ilac.org IAF: www.iaf.nu </p> |

Note: The current certificate annex is published on the website (link see below) of the Accreditation Body DAKKS or may be received by CTC advanced GmbH on request

<http://www.dakks.de/as/ast/d/D-PL-12076-01-03.pdf>