

Thank you for using the AP4 for RL78.

This document describes the restrictions and points for caution. Read this document before using the product.

## Contents

Chapter 1. Introduction .....	2
Chapter 2. Target Devices .....	3
Chapter 3. Operating Environment.....	9
Chapter 4. Changes .....	10
4.1 Details of Changes .....	10
4.1.1 The latest device user's manual is supported.....	10
4.1.2 Addition of supported devices .....	10
Chapter 5. Points for Caution .....	11
5.1 List of Cautions.....	11
5.2 Cautions Details .....	12
5.2.1 Online Help.....	12
5.2.2 Restrictions of the coding rule of MISRA-C .....	12
5.2.3 Restrictions of High-speed on-chip oscillator frequency select register(HOCODIV) .....	12
5.2.4 Restrictions of internal low-speed or internal high-speed oscillator trimming register .....	12
5.2.5 Restrictions of Flash memory CRC operation function (high-speed CRC).....	12
5.2.6 Restrictions of Port mode select register (PMS) .....	12
5.2.7 Cautions of the LIN-bus function of UART .....	12
5.2.8 Cautions of extension code, wakeup function and multimaster of serial interface IICA or IIC0 .....	12
5.2.9 Cautions of Safety Functions .....	12
5.2.10 Restriction of USB .....	13
5.2.11 Fast Mode Plus setting in IICA slave .....	13
5.2.12 24-pin device TAU0 channel 1 setting restriction.....	13
Chapter 6. Correction History .....	14
6.1 List of RENESAS TOOL NEWS .....	14
6.2 Details of RENESAS TOOL NEWS .....	15
6.2.1 RENESAS TOOL NEWS Document No.150716/tn2 .....	15
6.2.2 RENESAS TOOL NEWS Document No. R20TS0045EJ0100.....	15

## Chapter 1. Introduction

The AP4 for RL78 is a software tool to generate control programs (device driver programs) for peripheral modules (timers, UART, A/D, etc.). It generates device driver codes using user settings through GUI. Initialize code and API (Application Programming Interface) functions are provided.

## Chapter 2. Target Devices

Below is a list of devices supported by the AP4 for RL78/L13 V1.04.01.02	
PIN	Device name
64pin	R5F10WLA, R5F10WLC, R5F10WLD, R5F10WLE, R5F10WLF, R5F10WLG
80pin	R5F10WMA, R5F10WMC, R5F10WMD, R5F10WME, R5F10WMF, R5F10WMG
Following documents.	
Manual Name	Document Number
RL78/L13 User's Manual: Hardware	R01UH0382JJ0100 Rev.1.00
	R01UH0382EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/G1E V1.04.01.03	
PIN	Device name
64pin	R5F10FLC, R5F10FLD, R5F10FLE
80pin	R5F10FMC, R5F10FMD, R5F10FME
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/G1E User's Manual: Hardware	R01UH0353JJ0200 Rev.2.00

Below is a list of devices supported by the AP4 for RL78/G10 V1.05.01.01	
PIN	Device name
10pin	R5F10Y14, R5F10Y16, R5F10Y17
16pin	R5F10Y44, R5F10Y46, R5F10Y47
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/G10 User's Manual: Hardware	R01UH0384JJ0311 Rev.3.11
	R01UH0384EJ0311 Rev.3.11

Below is a list of devices supported by the AP4 for RL78/G1C V1.03.01.02	
PIN	Device name
32pin	R5F10JBC, R5F10KBC
48pin	R5F10JGC, R5F10KGC
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/G1C User's Manual: Hardware	R01UH0348JJ0100 Rev.1.00
	R01UH0348EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/H1D V1.00.00.05	
PIN	Device name
48pin	R5F11NGG, R5F11NGF
64pin	R5F11NLG, R5F11PLG, R5F11NLF, R5F11PLF
80pin	R5F11RMG, R5F11NMG, R5F11NMF, R5F11NME
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/H1D User's Manual: Hardware	R01UH0756JJ0080 Rev.0.80
	R01UH0756EJ0080 Rev.0.80

Below is a list of devices supported by the AP4 for RL78/L1C V1.03.00.01	
PIN	Device name
80pin	R5F110MJ, R5F110MH, R5F110MG, R5F110MF, R5F110ME, R5F111MJ, R5F111MH, R5F111MG, R5F111MF, R5F111ME
100pin	R5F110PJ, R5F110PH, R5F110PG, R5F110PF, R5F110PE, R5F111PJ, R5F111PH, R5F111PG, R5F111PF, R5F111PE
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/L1C User's Manual: Hardware	R01UH0409JJ0100 Rev.1.00
	R01UH0409EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/I1B V1.03.01.01	
PIN	Device name
80pin	R5F10MME, R5F10MPG
100pin	R5F10MPE, R5F10MPG
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/I1B User's Manual: Hardware	R01UH0407JJ0100 Rev.1.00
	R01UH0407EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/I1D V1.01.01.01	
PIN	Device name
20pin	R5F11768, R5F1176A
24pin	R5F11778, R5F1177A
30pin	R5F117A8, R5F117AA, R5F117AC
32pin	R5F117BA, R5F117BC
48pin	R5F117GA, R5F117GC
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/I1D User's Manual: Hardware	R01UH0474JJ0100 Rev.1.00
	R01UH0474EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/G1G V1.01.00.01	
PIN	Device name
30pin	R5F11EA8, R5F11EAA
32pin	R5F11EB8, R5F11EBA
44pin	R5F11EF8, R5F11EFA
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/G1G User's Manual: Hardware	R01UH0499JJ0100 Rev.1.00
	R01UH0499EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/G1F V1.01.01.01	
PIN	Device name
24pin	R5F11B7C, R5F11B7E
32pin	R5F11BBC, R5F11BBE
36pin	R5F11BCC, R5F11BCE
48pin	R5F11BGC, R5F11BGE
64pin	R5F11BLC, R5F11BLE
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/G1F User's Manual: Hardware	R01UH0516JJ0100 Rev.1.00
	R01UH0516EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/G1D V1.01.01.03	
PIN	Device name
48pin	R5F11AGG, R5F11AGH, R5F11AGJ
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/G1D User's Manual: Hardware	R01UH0515JJ0100 Rev.1.00
	R01UH0515EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/I1E V1.03.01.01	
PIN	Device name
32pin	R5F11CBC
36pin	R5F11CCC
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/I1E User's Manual: Hardware	R01UH0524JJ0100 Rev.1.00
	R01UH0524EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/I1C V1.01.01.01	
PIN	Device name
64pin	R5F11NLE, R5F11NLG
80pin	R5F11NME, R5F11NMG, R5F11NMJ
100pin	R5F11NPJ
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/I1C User's Manual: Hardware	R01UH0587JJ0051 Rev.0.51
	R01UH0587EJ0051 Rev.0.51

Below is a list of devices supported by the AP4 for RL78/G1H V1.01.01.02	
PIN	Device name
64pin	R5F11FLJ, R5F11FLK, R5F11FLL
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/G1H User's Manual: Hardware	R01UH0575JJ0100 Rev.1.00
	R01UH0575EJ0100 Rev.1.00

Below is a list of devices supported by the AP4 for RL78/G11 V1.02.01.01	
PIN	Device name
10pin	R5F1051A
16pin	R5F1054A
20pin	R5F1056A
24pin	R5F1057A
25pin	R5F1058A
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/G11 User's Manual: Hardware	R01UH0637JJ0110 Rev.1.10
	R01UH0637EJ0110 Rev.1.10

Below is a list of devices supported by the AP4 for RL78/L1A V1.01.01.01	
PIN	Device name
80pin	R5F11MMD, R5F11MME, R5F11MMF
100pin	R5F11MPE, R5F11MPF, R5F11MPG
The Code Generator is based on the following documents	
Manual Name	Document Number
RL78/L1A User's Manual: Hardware	R01UH0636JJ0100 Rev.1.00
	R01UH0636EJ0100 Rev.1.00



## Chapter 3. Operating Environment

### ▪ Host machine

- IBM PC/AT compatibles (Windows® 10, Windows® 8.1, Windows® 7)
- Processor: 1 GHz or higher (must support hyper-threading, multi-core CPUs)
- Memory capacity: 2 GB or more recommended. Minimum requirement is 1 GB or more (64-bit Windows requires 2 G or more)
- Hard disk capacity: 200 MB or more spare capacity
- Display: 1024 x 768 or higher resolution, 65,536 or more colors
- All other necessary software environments in addition to WindowsOS
  - .NET Framework version4.5

### ▪ Development Environments

Product Name	Version
IAR Embedded Workbench for Renesas RL78	V2.21 or later
GNURL78	V15.02 or later
Renesas electronics Compiler for 78K0R [CA78K0R]	V1.72 or later
Renesas electronics Compiler for RL78 [CC-RL]	V1.05 or later

## Chapter 4. Changes

This chapter describes change to the AP4 for RL78 V1.14.00.

No	Description	Version *1															
		RL78/L1A	RL78/G11	RL78/I1C	RL78/G1H	RL78/I1E	RL78/G1D	RL78/G1F	RL78/G1G	RL78/I1D	RL78/I1B	RL78/L1C	RL78/G1C	RL78/G10	RL78/G1E	RL78/L13	RL78/H1D
		V1.01.00.01	V1.01.00.03	V1.01.00.02	V1.01.00.01	V1.03.00.01	V1.01.00.02	V1.01.00.02	V1.01.00.01	V1.01.00.02	V1.03.00.01	V1.03.00.01	V1.03.00.02	V1.05.00.02	V1.04.00.01	V1.04.01.02	V1.00.00.05
1	The latest device user's manual is supported	/	○	/	/	/	/	/	/	/	/	/	/	○	/	/	/
2	Addition of supported devices	/	○	/	/	/	/	/	/	/	/	/	/	/	/	/	○

○ : Applicable, -: Not Applicable(finish of correction), /: Outside of function

Note 1: Version is described in the generated code.

### 4.1 Details of Changes

#### 4.1.1 The latest device user's manual is supported.

The contents of the currently-issued Device User's Manual has been reflected in the tool as the design materials of the code generator.

#### 4.1.2 Addition of supported devices

Added the device support. The following devices are supported

- RL78/H1D group
- RL78/G11 group ( 10pin, 16pin )

## Chapter 5. Points for Caution

This section describes the cautions on the AP4 for RL78 V1.13.00.

### 5.1 List of Cautions

No	Description	version *1															
		RL78/L1A	RL78/G11	RL78/I1C	RL78/G1H	RL78/I1E	RL78/G1D	RL78/G1F	RL78/G1G	RL78/I1D	RL78/I1B	RL78/L1C	RL78/G1C	RL78/G10	RL78/G1E	RL78/L13	RL78/H1D
		V1.01.01.01	V1.02.01.01	V1.01.01.01	V1.01.01.02	V1.03.01.01	V1.01.01.03	V1.01.01.01	V1.01.00.01	V1.01.01.01	V1.03.01.01	V1.03.00.01	V1.03.01.02	V1.05.01.01	V1.04.01.03	V1.04.01.02	V1.00.00.05
1	Online Help	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○
2	Restrictions of the coding rule of MISRA-C.	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○
3	Restrictions of High-speed on-chip oscillator frequency select register	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○
4	Restrictions of internal low-speed or internal high-speed oscillator trimming	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○
5	Restrictions of Flash memory CRC operation function (high-speed CRC)	○	○	○	○	○	○	○	○	○	○	○	○	/	○	○	○
6	Restrictions of Port mode select register (PMS)	○	○	○	○	○	○	○	○	○	○	○	○	/	○	○	○
7	Cautions of the LIN-bus function of UART	○	○	○	○	○	○	○	○	○	○	○	○	/	○	○	○
8	Cautions of extension code, wakeup function and multimaster of serial interface IICA or IIC0	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○
9	Cautions of Safety Functions	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○
10	Restriction of USB	/	/	/	/	/	/	/	/	/	/	○	○	/	/	/	/
11	Fast Mode Plus setting in IICA slave	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○	○
12	24-pin device TAU0 channel 1 setting restriction	/	/	/	/	/	/	○	/	/	/	/	/	/	/	/	/

○: Applicable, /: Not Applicable

Note 1: Version is described in the generated code.

## 5.2 Cautions Details

### 5.2.1 Online Help

AP4 is not supporting online help.

### 5.2.2 Restrictions of the coding rule of MISRA-C

Compliance with the MISRA-C (Guidelines for the Use of the C Language in Vehicle Based Software) coding convention is not supported for source code output by AP4.

### 5.2.3 Restrictions of High-speed on-chip oscillator frequency select register(HOCODIV)

AP4 is not equivalent to a setup of high-speed on-chip oscillator frequency select register

### 5.2.4 Restrictions of internal low-speed or internal high-speed oscillator trimming register

AP4 is not equivalent to a setup of internal low-speed or internal high-speed oscillator trimming register.

### 5.2.5 Restrictions of Flash memory CRC operation function (high-speed CRC)

AP4 is not correspond to a flash memory CRC operation function (high-speed CRC). Please refer to application note r01an0736ej.

<https://www.renesas.com/search/keyword-search.html#genre=document&q=r01an0736ej>

### 5.2.6 Restrictions of Port mode select register (PMS)

AP4 is not supporting a port mode select register (PMS).

### 5.2.7 Cautions of the LIN-bus function of UART

AP4 is not supporting the LIN-bus functions of serial interface UART0, UART2, UART3, UART6 or UARTF.

### 5.2.8 Cautions of extension code, wakeup function and multimaster of serial interface IICA or IIC0

AP4 is not supporting the extension code, multimaster, and wakeup function of serial interface IICA or IC0.

### 5.2.9 Cautions of Safety Functions

AP4 is not supporting RAM parity error detection function of Safety Functions.

### 5.2.10 Restriction of USB

AP4 is not supporting USB host/function.

### 5.2.11 Fast Mode Plus setting in IICA slave

If the Fast Mode Plus is set when using the IICA slave, IICA Low level range setting register (IICWLn, n= channel number), and IICA High level range setting register (IICWHLn) are not set correctly.

[Workaround]      There is no workaround.

After doing code generator, please rewrite the numerical value of the register setting of IICWLn, IICWHn in the R\_IICAn\_Create function. I depend on a system for the numerical value. Please change device UM to reference.

### 5.2.12 24-pin device TAU0 channel 1 setting restriction

In the 24-pin device, interval timer is only selectable for the TAU0 channel 1 setting.

[Workaround]      There is no workaround.

In the 32-pin device, other timer functions besides "Interval timer" are selectable for the TAU0 channel 1 setting. Refer to the setting to make a correction.

## Chapter 6. Correction History

This section describes correction history of RENESAS TOOL NEWS.

### 6.1 List of RENESAS TOOL NEWS

Issue Date	Document No.	Description	Device Concerned	Fixed version
Jul. 16, 2015	150716/tn2	1. Clock Generation Circuit (PLL Circuit Operation)	RL78/G1C, RL78/L1C	V1.10.00
		2. Setting P40 of Port 4	RL78/G10, RL78/G1C, RL78/G1E, RL78/G1F, RL78/G1G, RL78/I1D, RL78/L1C, RL78/L13	V1.10.00
Aug. 01, 2016	R20TS0045EJ 0100	Peripheral I/O redirection register 0 (PIOR0)	RL78/G1F	V1.11.00

## 6.2 Details of RENESAS TOOL NEWS

### 6.2.1 RENESAS TOOL NEWS Document No.150716/tn2

This issue has been corrected in AP4 for RL78 V1.10.00.

1. Clock Generation Circuit (PLL Circuit Operation)  
(Applicable MCUs: RL78/G1C, and RL78/L1C groups)

Generated code includes an error when the PLL circuit is operating as the clock generation circuit. A wait is required immediately after setting the PLL control register (PLLCTL).

2. Setting P40 of Port 4  
(Applicable MCUs: RL78/G10, RL78/G1C, RL78/G1E, RL78/G1F, RL78/G1G, RL78/I1D, RL78/L1C, and RL78/L13 groups)

Generated code has an error when P40 is set such that the on-chip pull-up resistor for P40 is not connected even though this is included in the settings of the on-chip pull-up resistors for port 4. The code to set the pull-up resistor option register (PU4) of P40 is not generated.

For details of the problem, refer to the URL below.

[https://www.renesas.com/doc/toolnews/eng/2015/150716tn2\\_e.pdf](https://www.renesas.com/doc/toolnews/eng/2015/150716tn2_e.pdf)

### 6.2.2 RENESAS TOOL NEWS Document No. R20TS0045EJ0100

This issue has been corrected in AP4 for RL78 V1.11.00.

1. Peripheral I/O redirection register 0 (PIOR0)  
(Applicable MCUs: RL78/G1F group (32- and 36-pin products))

Regarding the common and clock generation circuit pin assignments, code generated by the tools listed above will have an error when the pin assignment setting of bit PIOR02 in the PIOR register should assign the SCLA0 and SDAA0 functions to pins P14 and P15. Thus, the serial interface IICA cannot be used.

For details of the problem, refer to the URL below.

<https://www.renesas.com/doc/toolnews/eng/2016/r20ts0045ej0100-cstnno.pdf>

## Notice

1. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation or any other use of the circuits, software, and information in the design of your product or system. Renesas Electronics disclaims any and all liability for any losses and damages incurred by you or third parties arising from the use of these circuits, software, or information.
  2. Renesas Electronics hereby expressly disclaims any warranties against and liability for infringement or any other disputes involving patents, copyrights, or other intellectual property rights of third parties, by or arising from the use of Renesas Electronics products or technical information described in this document, including but not limited to, the product data, drawing, chart, program, algorithm, application examples.
  3. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
  4. You shall not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part. Renesas Electronics disclaims any and all liability for any losses or damages incurred by you or third parties arising from such alteration, modification, copy or otherwise misappropriation of Renesas Electronics products.
  5. Renesas Electronics products are classified according to the following two quality grades: "Standard" and "High Quality". The intended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below.

"Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots etc.

"High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control (traffic lights); large-scale communication equipment; key financial terminal systems; safety control equipment; etc.

Renesas Electronics products are neither intended nor authorized for use in products or systems that may pose a direct threat to human life or bodily injury (artificial life support devices or systems, surgical implantations etc.), or may cause serious property damages (space and undersea repeaters; nuclear power control systems; aircraft control systems; key plant systems; military equipment; etc.). Renesas Electronics disclaims any and all liability for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for which the product is not intended by Renesas Electronics.
  6. When using the Renesas Electronics products, refer to the latest product information (data sheets, user's manuals, application notes, "General Notes for Handling and Using Semiconductor Devices" in the reliability handbook, etc.), and ensure that usage conditions are within the ranges specified by Renesas Electronics with respect to maximum ratings, operating power supply voltage range, heat radiation characteristics, installation, etc. Renesas Electronics disclaims any and all liability for any malfunctions or failure or accident arising out of the use of Renesas Electronics products beyond such specified ranges.
  7. Although Renesas Electronics endeavors to improve the quality and reliability of Renesas Electronics products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please ensure to implement safety measures to guard them against the possibility of bodily injury, injury or damage caused by fire, and social damage in the event of failure or malfunction of Renesas Electronics products, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures by your own responsibility as warranty for your products/system. Because the evaluation of microcomputer software alone is very difficult and not practical, please evaluate the safety of the final products or systems manufactured by you.
  8. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please investigate applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive carefully and sufficiently and use Renesas Electronics products in compliance with all these applicable laws and regulations. Renesas Electronics disclaims any and all liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
  9. Renesas Electronics products and technologies shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations. You shall not use Renesas Electronics products or technologies for (1) any purpose relating to the development, design, manufacture, use, stockpiling, etc., of weapons of mass destruction, such as nuclear weapons, chemical weapons, or biological weapons, or missiles (including unmanned aerial vehicles (UAVs)) for delivering such weapons, (2) any purpose relating to the development, design, manufacture, or use of conventional weapons, or (3) any other purpose of disturbing international peace and security, and you shall not sell, export, lease, transfer, or release Renesas Electronics products or technologies to any third party whether directly or indirectly with knowledge or reason to know that the third party or any other party will engage in the activities described above. When exporting, selling, transferring, etc., Renesas Electronics products or technologies, you shall comply with any applicable export control laws and regulations promulgated and administered by the governments of the countries asserting jurisdiction over the parties or transactions.
  10. Please acknowledge and agree that you shall bear all the losses and damages which are incurred from the misuse or violation of the terms and conditions described in this document, including this notice, and hold Renesas Electronics harmless, if such misuse or violation results from your resale or making Renesas Electronics products available any third party.
  11. This document shall not be reprinted, reproduced or duplicated in any form, in whole or in part, without prior written consent of Renesas Electronics.
  12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.

(Rev.3.0-1 November 2016)



### SALES OFFICES

### Renesas Electronics Corporation

<http://www.renesas.com>

Refer to "<http://www.renesas.com/>" for the latest and detailed information.

#### **Renesas Electronics America Inc.**

2801 Scott Boulevard Santa Clara, CA 95050-2549, U.S.A.  
Tel: +1-408-588-6000, Fax: +1-408-588-6130

#### **Renesas Electronics Canada Limited**

9251 Yonge Street, Suite 8309 Richmond Hill, Ontario Canada L4C 9T3  
Tel: +1-905-237-2004

#### **Renesas Electronics Europe Limited**

Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, U.K.  
Tel: +44-1628-585-100, Fax: +44-1628-585-900

#### **Renesas Electronics Europe GmbH**

Arcadiastrasse 10, 40472 Düsseldorf, Germany  
Tel: +49-211-6503-0, Fax: +49-211-6503-1327

#### **Renesas Electronics (China) Co., Ltd.**

Room 1709, Quantum Plaza, No.27 ZhiChunLu Haidian District, Beijing 100191, P.R.China  
Tel: +86-10-8235-1155, Fax: +86-10-8235-7679

#### **Renesas Electronics (Shanghai) Co., Ltd.**

Unit 301, Tower A, Central Towers, 555 Langao Road, Putuo District, Shanghai, P. R. China 200333  
Tel: +86-21-2226-0888, Fax: +86-21-2226-0999

#### **Renesas Electronics Hong Kong Limited**

Unit 1601-1611, 16/F., Tower 2, Grand Century Place, 193 Prince Edward Road West, Mongkok, Kowloon, Hong Kong  
Tel: +852-2265-6688, Fax: +852-2886-9022

#### **Renesas Electronics Taiwan Co., Ltd.**

13F, No. 363, Fu Shing North Road, Taipei 10543, Taiwan  
Tel: +886-2-8175-9600, Fax: +886-2-8175-9670

#### **Renesas Electronics Singapore Pte. Ltd.**

80 Bendemeer Road, Unit #06-02 Hyflux Innovation Centre, Singapore 339949  
Tel: +65-6213-0200, Fax: +65-6213-0300

#### **Renesas Electronics Malaysia Sdn.Bhd.**

Unit 1207, Block B, Menara Amcorp, Amcorp Trade Centre, No. 18, Jln Persiaran Barat, 46050 Petaling Jaya, Selangor Darul Ehsan, Malaysia  
Tel: +60-3-7955-9390, Fax: +60-3-7955-9510

#### **Renesas Electronics India Pvt. Ltd.**

No.777C, 100 Feet Road, HAL II Stage, Indiranagar, Bangalore, India  
Tel: +91-80-67208700, Fax: +91-80-67208777

#### **Renesas Electronics Korea Co., Ltd.**

12F., 234 Teheran-ro, Gangnam-Gu, Seoul, 135-080, Korea  
Tel: +82-2-558-3737, Fax: +82-2-558-5141