

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

32192/32195/32196 Group

Application of the TOU (3 Phase motor control)

1. Overview

This documentation presents examples of sample program, which use the Timer TOU incorporated in the 32192/32195/32196 Group Microcomputer.

2. Introduction

The sample task described in this documentation applies to the use of the following microcomputers, under the respective conditions.

- Microcomputer: 32192 Group (M32192F8VFP, M32192F8UFP, and M32192F8TFP)
32195 Group (M32195F4VFP, M32195F4UFP, and M32195F4TFP)
32196 Group (M32196F8VFP, M32196F8UFP, and M32196F8TFP)
- Operating Frequency: 128 to 160 MHz (The sample programs are compiled assuming a frequency of 160 MHz.)
- Operation Board: Starter kit for 32192

3. Explanation of the Technology Applied

3.1 Outline of the Multijunction Timer

The Multijunction Timer (MJT following MJT for abbreviation) have Input event bus and Output event bus, it can be single used and internal connection is possible mutually.

This function allows constructing Timer flexibly and corresponding to various applications. Multijunction is named because timers have many connection points with internal event bus.

Please refer to the hardware manual for details of the Multijunction Timer.

4. Phase-compensated PWM waveform output Sample Program

4.1 Outline of the Sample Program

In this sample program, TOU0_0 to TOU0_5 (PWM waveform output), TOU0_6 (calculates for next cycle and set that value), TOU0_7 (for generating carrier cycle) and outputted phase-compensated PWM waveform for 3 phase. The waveform is outputted to external pins TO21 to TO26 (using pin group A). In addition, PWM Output prohibits function that cuts output during detecting simultaneous "L" level at positive and negative phase of phase-compensated PWM waveform is used.

In this sample program Sine table divided by 256 is used, increment every 20kHz and triangle of 78.125 Hz outputs PWM waveform by control.

Figure 4.1.1 shows phase-compensated PWM waveform for 3 phase used in 3 phase motor control.




Figure 4.1.1 Output waveform

4.2 Timer construction

Because count source of timer TOU is maximum of PWM resolution, select BCLK (40MHz) and use with prescaler3 divided by 1. TOU0_7 set to continuous output mode, generate 20kHz of carrier cycle. TOU0_0, TOU0_2, TOU0_4 are set to single-shot PWM output mode, TOU0_6 is set to single-shot output mode and TOU0_0, TOU0_2, TOU0_4, TOU0_6 are started by the underflow of TOU0_7.

TOU0_1, TOU0_3, TOU0_5 are set to single-shot output mode, use for shorting prevention function is used.

PWM output waveform generated in TOU0_0 to TOU0_5 is outputted from TO21 to TO26.

Set the value underflow in the point 3/4 of carrier cycle for TOU0_6.

In addition, use input from external pin and PWM output disable function by port pin level.

Figure 4.2.1 shows Timer construction, and Figure 4.2.2 shows Operation timing.




Figure 4.2.1 Timer construction




Figure 4.2.2 Operation timing

4.3 Timer operation

4.3.1 Calculation way of output waveform duty

Duty calculation of PWM waveform and setting register of TOU0_0, TOU0_2 and TOU0_4 is operated by TOU0_6 interrupt processing.

Shorting prevention time operates setting reload register of TOU0_1, TOU0_3 and TOU0_5.




Figure 4.3.1 Calculation way of output waveform duty

When outputs waveform like figure 4.3.1, reload register setting value of each timer can be calculated by following equations.

TOU0_1 (3, 5):

$$\text{Reload register} = Td - 3$$

TOU0_0 (2, 4):

$$\text{Reload 1 register} = H\text{time} + Td - 1$$

$$\text{Reload 0 register} = ((\text{Carrier cycle} - H\text{time}) / 2) - Td - 2$$

4.3.2 Operation of short prevention function

When short prevention function is valid, TOU0 enable factor select bit of TOU0_1 (3, 5) is invalid, those are started by underflow of TOU0_0 (2, 4).

TOU0_0 (2, 4) is started by underflow of TOU0_7 and “reload 0 register setting value -1” is loaded to counter with synchrony count clock, start down counting. “Reload 1 register setting value -1” is loaded and start down counting at first underflow. Then stop count at second underflow. After 3 count clock of first and second counter underflow, TOU0_1 (3, 5) is started.

Figure 4.3.2 shows Timer operation when short prevention function is valid and diagram of output waveform.

When short prevention function is valid, it is necessary to set value in F/F data register and F/F data register for short prevention function.

When reversing of F/F output, the value of the F/F data register and the F/F data register for short prevention function is replaced, and the value of the F/F data register after the change becomes the output of F/F.

Furthermore, if sets same value to F/F data register and F/F data register for short prevention function, it is going to be fixed output.

- **High level is outputted at first**
Set F/F data register to “1”, F/F data register for short prevention function to “0”.
- **Low level is outputted at first**
Set F/F data register to “0”, F/F data register for short prevention function to “1”.
- **Output of fixed**
The same value to the F/F data register and the F/F data register for short prevention function is set.
When "0" is set to each register, "L" level is outputted, "1" it sets when, "H" level is outputted.

Note. When short prevention function invalid/valid bit is set, counter of all TOU timers should be count stopped.




Figure 4.3.2 Timer operation when short prevention function is valid

4.3.3 Setting F/F data register, F/F data register for short prevention function and pin output

Setting value of F/F data register, F/F data register for short prevention function and pin output are shown below.

In this sample program, the setting that output "H" to positive phase side, "L" to negative phase side is used.




Figure 4.3.3 Relation between F/F data registers and pin output

4.3.4 Setting Duty 0%, Duty 100%

With this sample program, Duty 0%, or as for Duty 100% output, data setting timing of the next period (TOU0_6 interrupting processing) the time, the F/F data register for short prevention function (SHFF2126D) it actualizes by the fact that value is operated.

As the F/F data register by the fact that the same value is set, "L" level, or "H" level is outputted in the F/F data register for short prevention function.

To secure the SHFF rewriting time, at carrier period at the time of Duty 0% setting, the PWM waveform that is close to 0% is outputted, at carrier period at the time of Duty 100% setting, the PWM waveform that is close to 100% is outputted.

In Duty 0% the value which outputs the PWM waveform of the smallest width, the inside of Duty 100% has set the value which outputs the PWM waveform of breadth maximum to each reload registers.

With this sample program, because it is necessary to do in "SHFF rewriting range" in figure 4.3.4, as generated the interruption of the TOU0_6 at 3/4 positions of carrier period, it sets the modification of F/F data register for short prevention function value.

TOU0_6 interruption occurrence timing has the necessity to consider the fact that the delay other interruption processing and the like with influence occurs.

Figure 4.3.4 shows the timing diagram of setting Duty 0%, Duty 100%.




Figure 4.3.4 The timing diagram of setting Duty 0%, Duty 100%

4.3.5 PWM output prohibit function

32192/32195/32196 group has function which can prohibit output from P87 (P00)/TO21 to P82 (P05)/TO26 and P110(P10)/TO29 to P115(P15)/TO34 (those are external pin of TOU0_0 to TOU0_5 timer and TOU1_0 to TOU1_5 timer) compulsorily.

To prohibit outputting is following three ways.

- PWM output is prohibited by signal inputted from external pin (TIN16/PWMOFF0, TIN17/PWMOFF1)
- PWM output is prohibited by PWM output prohibit control register
- PWM output is prohibited by pin level of port P87 (P00)/ TO21 to P82 (P05)/ TO26, P110 (P10)/ TO29 to P115 (P15)/ TO34

Figure 4.3.5 shows circuit construction diagram of PWM output prohibit function.




Figure 4.3.5 Circuit construction diagram of PWM output prohibit function (using pin group A)

In this sample program is following two kinds of PWM output prohibition function are used.

(1) PWM output prohibit by input signal from external pin

While detecting falling edge of external signal (PWMOFF0), output to external pin TO21 to TO26 are prohibited.




Figure 4.3.6 Operation diagram when PWM output prohibit by input signal from external pin

(2) PWM output prohibit by port pin level

While detecting simultaneous Low level in positive and negative phase of PWM waveform, PWM output to external pin TO21 to TO26 are prohibited.




Figure 4.3.7 Operation diagram when PWM output prohibit by port pin level

4.4 Processing Procedure

Figure 4.4.1 shows the processing flow for setting the timer.




Figure 4.4.1 Timer Initialization Flow

4.5 Interpretation of the Sample Program

Note. The registers used are indicated as (register name: bit name).

4.5.1 Port initializing function (port_init())

- (1) Set output flip flop control register
 - Set initial output data from FF21 to FF26 (FF2128P, FF2128D)
 - Set initial output data from FF21 to FF26 for short prevention function (SHFF2126P, SHFF2126D)
- (2) Setting port
 - Set input enable bit of port input special function control register to enable input. (PICNT: PIEN0)
 - Set P11 to output mode as multipurpose port. (P11DATA, P11DIR, P11MOD)
 - Set P8 to TO21 to TO26 (P8DATA, P8DIR, P8MOD, P8SMOD)
 - Set P13 to TIN16 (P13DIR, P13MOD, P13SMOD)
 - Set TIN16 to falling edge. (TINCR3)

4.5.2 Various initializing function (init_func())

- (1) Call port initializing function

4.5.3 TOU0 initializing function (TOU0_init())

- (1) Set TOU0 control register 0 as following (TOU0CR0)
 - Set TOU0_0, TOU0_2, TOU0_4 to single-shot PWM output mode
 - Set TOU0_1, TOU0_3, TOU0_5 to single-shot output mode
 - Set TOU0_6 to single-shot output mode
 - Set TOU0_7 to continuous output mode
- (2) Set TOU0 control register 1 as following (TOU0CR1)
 - Use prescaler 3
 - Prescaler 3 supply clock is BCLK
 - Set short prevention function as valid.
 - Set TOU0_0, TOU0_2, TOU0_4 to single-shot PWM output mode
- (3) Set operation period of TOU0_7 to counter and reload register (TOU07CTW, TOU07RLW)
- (4) Set reload register as the value underflow in the point 3/4 of carrier cycle for TOU0_6 (TOU06RLW)
- (5) Set prescaler divided by value
 - Set "prescaler divided by value-1" to prescaler 3 (PRS3)
- (6) Set TID control & prescaler enable register (TID0PRS3EN)
 - Set prescaler 3 to "start".
 - Set enable factor of TOU0 to TOU0_7 underflow
- (7) TOU0 PWM0FF input processing control register to falling edge (PWM0FF0CR)
- (8) TOU0 PWM output 0 prohibit level control register GA (PO0LVGACR)
 - Set disable output level as "L", disable output level select as valid
- (9) TOU0 PWM0FF0 function enable register to PWM0FF0 function valid (PWM0FF0EN)
- (10) Set TIN interrupt control register to TIN16 enable interrupt (TINIR4, TINIR5)
- (11) Set TOU0 interrupt request mask register to TOU0_6 enable interrupt request (TOU0IST, TOU0IMA)
- (12) Set interrupts enable and prior level
 - TOU0 output interrupt control register to interrupt level "2" (ITOU0CR)
 - MJT input interrupt control register to interrupt level "0" (the highest priority) (IMJTICR2)
- (13) Set shorting prevention time
 - "shorting prevention time-3" is set to the reload register of the TOU0_1, TOU0_3 and TOU0_5 (TOU01RLW, TOU03RLW, TOU05RLW)

4.5.4 Duty calculation of PWM waveform and setting function of TOU0 reload register (SetDuty())

- (1) Calculate "L" time positive phase side for next cycle
 - Get data for 3 phase (U, V, W) from sine wave table (calculate approximately 120 degrees for phase difference).
- (2) Set value for Duty 0% to FF data register for short prevention function when next Duty is 0%. (SHFF2126P, SHFF2126D)
 - In order to output the PWM waveform of the smallest width, the smallest value is set to the positive phase side "L" time data
- (3) Set value for Duty 100% to FF data register for short prevention function when next Duty is 100%. (SHFF2126P, SHFF2126D)
 - In order to output the PWM waveform of the maximum width, the maximum value is set to the positive phase side "L" time data
- (4) Set value for normal operation to FF data register for short prevention function when both next Duty is not 0% nor 100% and pervious Duty is 0% or 100%. (SHFF2126P, SHFF2126D)
- (5) Set calculation result to each reload registers of TOU0 (TOU00RL1, TOU00RL0, TOU02RL1, TOU02RL0, TOU04RL1, TOU04RL0).

4.5.5 Setting function of table pointer of sine wave (SetPointer())

- (1) Increment pointer to sine wave table

4.5.6 Main function (main())

- (1) Initial pointer "gSinPtr" to sine wave table
- (2) Initialize a coefficient of sine waveform width "gAmp" and calculate "L" time maximum value "gLLevel100Percent".
- (3) Initialize flags of Duty 0% and Duty 100% during operation
- (4) Call interrupt prohibit function
- (5) Call various initializing function
- (6) Call TOU0 initializing function
- (7) Call enable interrupt function
- (8) Duty calculation of PWM waveform and call setting function of TOU0 reload register
- (9) Start TOU0_7 counting (TOU0PRO, TOU0CEN)
- (10) Wait interrupt infinite loop

4.5.7 TOU0 interrupt processing function (Int_TOU0_7())

- (1) If interrupt request of TOU0_6 occurs, go to next processing
 - Clear interrupt request of TOU0_6
 - Call pointer setting function of sine wave table
 - Duty calculation of PWM waveform and call setting function of TOU0 reload register

4.5.8 TIN interrupt processing function (Int_TIN1619())

- (1) If interrupt request of TIN16 occurs, go to next processing
 - Clear TIN16 interrupt request (TINIR4)
 - All TOU0 timers are stopped. (TOU0PRO, TOU0CEN)
 - Set TOU0 interrupt request mask register to TOU0_6 disable interrupt request (TOU0IST, TOU0IMA)
 - TOU0 output interrupt control register to interrupt disabled (ITOU0CR)
 - Set infinite loop output H'03 and H'00 alternately in P11 data register.

4.6 Sample Program

Sample program for Phase-compensated PWM waveform output is shown below. In this program, TOU_7 is used in continuous output mode, 20 kHz for carrier cycle.

The amplitude rate of the sine wave can be changed depending on the value of global variable “gAmp”.

When a set value of global variable “gAmp” is 100 or less, the sine wave not to include the duty 0% and the duty 100% in the PWM output is controlled.

The duty 100% is contained, and a square wave (trapezoid wave) is controlled from 100 a set value of global variable “gAmp” to the PWM output when it is large by the duty 0%.

Note that the sample programs below require the SFR definition file.

The latest SFR definition file can be downloaded from Renesas Technology website.

When using the SFR definitions file, adjust the path setting to match the operating computer environment.

4.6.1 TOU_pwm.c

```

1  /*"FILE COMMENT"*****
2  *      M32R C Programming          Rev. 1.00
3  *      < Sample Program for 32192 >
4  *      < TOU0 3-phase PWM output >
5  *
6  *      Copyright (c) 2005 Renesas Technology Corporation
7  *      All Rights Reserved
8  *****/
9
10 *****/
11 /*      Include file          */
12 *****/
13 #include          "..\inc\sfr32192_pragma.h"
14
15 *****/
16 /*      Function prototype declaration          */
17 *****/
18 void          port_init(void);          /* Initialize port */
19 void          init_func(void);          /* Initial setup function */
20 void          TOU0_init( void );          /* TOU0 initialize function */
21 void          SetDuty( void );          /* Calculation of duty and register setting fu
nction */
22 void          SetPointer( void );          /* Sine wave table pointer Update function */
23 void          main(void);          /* Main function */
24 void          Int_TOU0_7( void );          /* TOU0 interrupt handler */
25 void          Int_TIN1619( void );          /* TIN16 interrupt handler */
26
27 *****/
28 /*      Definition of external reference          */
29 *****/
30 extern void          DisInt( void );          /* Interrupt disable function */
31 extern void          EnInt( void );          /* Interrupt enable function */
32
33 *****/
34 /*      Define macro          */
35 *****/
36 #define DEAD_TIME          120          /* shorting prevention time (3us@40MHz(BCLK)
*/
37 #define CARRIER_COUNT          2000          /* Carrier cycle (50us=20KHz@40MHz(BCLK) */
38 #define AMP_MAX          40          /* Amplitude coefficient maximum value */
39
40 #define H_MAX          (CARRIER_COUNT-(DEAD_TIME<<1)-4) /* H level max time(count clock) */
41 #define H_MID          ((H_MAX + H_MIN)>>1)          /* H level mid time(count clock) */
42 #define H_MIN          (2L)          /* H level min time(count clock) */
43
44
45 #define TID0_PRS          0x07u          /* 0000 0111B */
46          /* |||| |||+----- start prescaler 3 count          */
47          /* |||| +++----- TOU0 enable source is TOU0_7 underflow
*/
48          /* +++----- don't care          */
49
50 #define TOU0_CRO          0x4442u          /* 0100 0100 0100 0010B */
51          /* |||| |||| |||| |||+- TOU0_7 Continuous mode          */
52          /* |||| |||| |||| +++--- TOU0_6 Single-shot mode          */

```

```

53          /* |||| |||| ||+----- TOU0_5 Single-shot mode          */
54          /* |||| |||| ++----- TOU0_4 Single-shot pwm mode      */
55          /* |||| ||+----- TOU0_3 Single-shot mode            */
56          /* |||| ++----- TOU0_2 Single-shot pwm mode          */
57          /* ||+----- TOU0_1 Single-shot mode                  */
58          /* ++----- TOU0_0 Single-shot pwm mode                */
59
60 #define TOU0_CR1          0x4100u          /* 0100 0001 0000 0000B */
61          /* |||| |||| ++++ +---- Single-shot pwm mode            */
62          /* |||| ||+----- enable shorting prevention function */
63          /* ||++ +++----- No operation                          */
64          /* |+----- select BCLK                                */
65          /* +----- select prescaler3                          */
66
67 /*****
68 /*          Global variable                                     */
69 /*****
70 UCHAR    gSinPtr;          /* pointer of sine wave table */
71 ULONG    gAmp;            /* Amplitude coefficient */
72 ULONG    gLlevel100Percent; /* L level max time(count clock) */
73
74 UCHAR    g0100FlgU;       /* U phase duty 0% or 100% executing flag */
75 UCHAR    g0100FlgV;       /* V phase duty 0% or 100% executing flag */
76 UCHAR    g0100FlgW;       /* W phase duty 0% or 100% executing flag */
77          /* 0 : normal */
78          /* 1 : duty 0% */
79          /* 2 : duty 100% */
80
81 const SSHORT gaSinTbl[ 256 ] = {          /* sine wave table */
82     0,      804,    1608,    2410,    3212,    4011,    4808,    5602,    6393,    7179,    7962,    8739,
83     9512,   10278,   11039,   11793,   12539,   13279,   14010,   14732,   15446,   16151,   16846,   17530,
84     18204,   18868,   19519,   20159,   20787,   21403,   22005,   22594,   23170,   23731,   24279,   24811,
85     25329,   25832,   26319,   26790,   27245,   27683,   28105,   28510,   28898,   29268,   29621,   29956,
86     30273,   30571,   30852,   31113,   31356,   31580,   31785,   31971,   32137,   32285,   32412,   32521,
87     32609,   32678,   32728,   32757,   32767,   32757,   32728,   32678,   32609,   32521,   32412,   32285,
88     32137,   31971,   31785,   31580,   31356,   31113,   30852,   30571,   30273,   29956,   29621,   29268,
89     28898,   28510,   28105,   27683,   27245,   26790,   26319,   25832,   25329,   24811,   24279,   23731,
90     23170,   22594,   22005,   21403,   20787,   20159,   19519,   18868,   18204,   17530,   16846,   16151,
91     15446,   14732,   14010,   13279,   12539,   11793,   11039,   10278,   9512,    8739,    7962,    7179,
92     6393,    5602,    4808,    4011,    3212,    2410,    1608,    804,    0,      -804,   -1608,   -2410,
93     -3212,   -4011,   -4808,   -5602,   -6393,   -7179,   -7962,   -8739,   -9512,  -10278, -11039, -11793,
94     -12539, -13279, -14010, -14732, -15446, -16151, -16846, -17530, -18204, -18868, -19519, -20159,
95     -20787, -21403, -22005, -22594, -23170, -23731, -24279, -24811, -25329, -25832, -26319, -26790,
96     -27245, -27683, -28105, -28510, -28898, -29268, -29621, -29956, -30273, -30571, -30852, -31113,
97     -31356, -31580, -31785, -31971, -32137, -32285, -32412, -32521, -32609, -32678, -32728, -32757,
98     -32767, -32757, -32728, -32678, -32609, -32521, -32412, -32285, -32137, -31971, -31785, -31580,
99     -31356, -31113, -30852, -30571, -30273, -29956, -29621, -29268, -28898, -28510, -28105, -27683,
100    -27245, -26790, -26319, -25832, -25329, -24811, -24279, -23731, -23170, -22594, -22005, -21403,
101    -20787, -20159, -19519, -18868, -18204, -17530, -16846, -16151, -15446, -14732, -14010, -13279,
102    -12539, -11793, -11039, -10278, -9512, -8739, -7962, -7179, -6393, -5602, -4808, -4011,
103    -3212, -2410, -1608, -804
104 };
105
106 /*****FUNC COMMENT*****/
107 * Function name: port_init()
108 *-----
109 * Description : Initialize port
110 *-----
111 * Argument : -
112 *-----
113 * Returns : -
114 *-----
115 * Notes : -
116 *****/
117 void port_init(void)
118 {
119     /* Setting F/F */
120     FF2128P = 0x00;
121     FF2128D = 0x54;          /* 01010100B */
122     SHFF2126P = 0x00;
123     SHFF2126D = 0xA8;       /* 10101000B */
124
125     PICNT = PIEN0;          /* Enable port input */
126
127     /*** Error Output (LED) ***/
128     P11DATA = 0x00;        /* Output data (must be set prior to mode) */
129     P11DIR = 0xff;        /* P110-P117 : Output mode */

```

```

130     P11MOD = 0x00;                               /* P110-P117 : Input/output port */
131
132     /**/ Setting TO21-TO26 ***/
133     P8DATA = 0x00;                               /* Output data (must be set prior to mode) */
134     P8DIR  = 0xff;                               /* P82-P87 : Output mode */
135     P8MOD  = 0x00;                               /* P82-P87 : clear */
136     P8SMOD = 0x3f;                               /* P82-P87 : TOn select */
137     P8MOD  = 0x3f;                               /* P82-P87 : TO26 - TO21 */
138
139     /**/ Setting TIN16 ***/
140     P13DIR = 0x00;                               /* P130-P137 : Input mode */
141     P13MOD = 0x00;
142     P13SMOD = 0x80;                             /* Select P130 for TIN16 */
143     P13MOD |= 0x80u;                             /* Select P130 for TIN16 */
144     TINCR3 = 0x0200;                             /* TIN16 : falling edge */
145 }
146
147 /*"FUNC COMMENT"*****
148 * Function name: init_func()
149 *-----
150 * Description  : Call various initialization functions
151 *-----
152 * Argument    : -
153 *-----
154 * Returns     : -
155 *-----
156 * Notes      : -
157 *"FUNC COMMENT END"*****/
158 void init_func(void)
159 {
160     port_init();
161 }
162
163 /*"FUNC COMMENT"*****
164 * Function name: TOU0_init()
165 *-----
166 * Description  : -
167 *-----
168 * Argument    : -
169 *-----
170 * Returns     : -
171 *-----
172 * Notes      : The prescaler, clock bus, etc. are set separately from the above
173 *             : Must be executed while interrupts are disabled
174 *"FUNC COMMENT END"*****/
175 void TOU0_init( void )
176 {
177     TOU0CR0 = TOU0_CR0;                          /* Set TOU0_n operation mode */
178     TOU0CR1 = TOU0_CR1;                          /* Set supplied clock select ECLK */
179
180     TOU07CTW = CARRIER_COUNT - 1ul;
181     TOU07RLW = CARRIER_COUNT - 1ul;             /* TOU0_7 reload register */
182
183     TOU06RLW = (CARRIER_COUNT * 3ul / 4ul) - 80ul; /* TOU0_6 use for data setting */
184                                                     /* 80 : Interrupt processing time */
185
186     PRS3 = ( 1 - 1);                             /* Set prescaler3 (25ns@40MHz (ECLK)) */
187     TID0PRS3EN = TID0_PRS;
188
189     /**/ Setting PWM OFF */
190     PWMOFF0CR = PWMOFF0SP;                      /* PWMOFF0 writing control */
191     PWMOFF0CR = 0x02;                            /* PWMOFF0 falling edge */
192     PO0LVGACR = 0x00;                            /* "L"level enable */
193     PWMOFF0EN = 0x40;                            /* P87 - P82 PWM OFF enable */
194
195     /**/ Setting interrupt */
196     TINIR4 = 0x00;                               /* clear interrupt request */
197     TINIR5 = (~TINIM16) & 0xffu;               /* enable TIN16 */
198     TOU0IST = 0x00;                              /* clear interrupt request */
199     TOU0IMA = (~TOU0IM6) & 0xffu;              /* enable TOU0_6 */
200     ITOUOCR = 0x02;                              /* TOU0_n interrupt enable */
201     IMJTICR2 = 0x00;                             /* TIN16 interrupt enable */
202
203     /**/ Setting shorting prevention time */
204     TOU01RLW = DEAD_TIME - 3ul;
205     TOU03RLW = DEAD_TIME - 3ul;
206     TOU05RLW = DEAD_TIME - 3ul;

```

```

207 }
208
209 /*"FUNC COMMENT"*****
210 * Function name: void SetDuty( void )
211 *-----
212 * Description : Next cycle duty calculation and setting of reload registers
213 *-----
214 * Argument    : none
215 *-----
216 * Returns     : none
217 *-----
218 * Notes       : The change from 0 to 100% and the change from 100 to 0% are the prohibitions.
219 *"FUNC COMMENT END"*****/
220 void SetDuty( void )
221 {
222     UCHAR   SinPtrU, SinPtrV;
223     USHORT  DutyU_RL0, DutyU_RL1;
224     USHORT  DutyV_RL0, DutyV_RL1;
225     USHORT  DutyW_RL0, DutyW_RL1;
226     SSHORT  OrdVu, OrdVv, OrdVw;
227     SLONG   HtimeU, HtimeV, HtimeW;
228
229     /** Get sine wave table pointer **/
230     SinPtrU = gSinPtr;
231     SinPtrV = gSinPtr + 86;
232     /** U-phase increase and decrease amount calculation of "H" time **/
233     OrdVu = (gLlevel100Percent * gaSinTbl[ SinPtrU ]) >> 16;
234     HtimeU = OrdVu + H_MID;
235     /** V-phase increase and decrease amount calculation of "H" time **/
236     OrdVv = (gLlevel100Percent * gaSinTbl[ SinPtrV ]) >> 16;
237     HtimeV = OrdVv + H_MID;
238     /** W-phase increase and decrease amount calculation of "H" time **/
239     OrdVw = - OrdVu - OrdVv;
240     HtimeW = OrdVw + H_MID;
241
242     /** U-phase duty judgment and setting at the next cycle **/
243     if( HtimeU < H_MIN ){                               /* Duty 0% */
244         HtimeU = H_MIN;
245         if( g0100FlgU == 0 ){                            /* /U="H", U="L" fix */
246             SHFF2126P = 0x3F;
247             g0100FlgU = 1;                               /* Duty 0% memory */
248             SHFF2126D = 0x40u;                          /* '01xx xxxx' write */
249         }
250     }
251     else if( H_MAX < HtimeU ){                          /* Duty 100% */
252         HtimeU = H_MAX;
253         if( g0100FlgU == 0 ){                            /* /U="L", U="H" fix */
254             SHFF2126P = 0x3F;
255             g0100FlgU = 2;                               /* Duty 100% memory */
256             SHFF2126D = 0x80u;                          /* '10xx xxxx' write */
257         }
258     }
259     else{                                               /* normal */
260         if( g0100FlgU == 1 ){                            /* It was duty 0% last time */
261             SHFF2126P = 0x3F;
262             g0100FlgU = 0;
263             SHFF2126D = 0x80u;                          /* '01xx xxxx' write */
264         }
265         else if( g0100FlgU == 2 ){                      /* It was duty 100% last time */
266             SHFF2126P = 0x3F;
267             g0100FlgU = 0;
268             SHFF2126D = 0x40u;                          /* '10xx xxxx' write */
269         }
270     }
271     DutyU_RL1 = HtimeU + DEAD_TIME - 11;
272     DutyU_RL0 = ((CARRIER_COUNT - HtimeU) >> 1) - DEAD_TIME - 21;
273
274     /** V-phase duty judgment and setting at the next cycle **/
275     if( HtimeV < H_MIN ){                               /* Duty 0% */
276         HtimeV = H_MIN;
277         if( g0100FlgV == 0 ){                            /* /V="H", V="L" fix */
278             SHFF2126P = 0xCF;
279             g0100FlgV = 1;                               /* Duty 0% memory */
280             SHFF2126D = 0x10;                          /* 'xx10 xxxx' write */
281         }
282     }
283     else if( H_MAX < HtimeV ){                          /* Duty 100% */

```

```

284         HtimeV = H_MAX;
285         if( g0100FlgV == 0 ){                                /* /V="L", V="H" fix */
286             SHFF2126P = 0xCF;
287             g0100FlgV = 2;                                    /* Duty 100% memory */
288             SHFF2126D = 0x20;                                /* 'xx01 xxxx' write */
289         }
290     }
291     else{                                                    /* normal */
292         if( g0100FlgV == 1 ){                                /* It was duty 0% last time */
293             SHFF2126P = 0xCF;
294             g0100FlgV = 0;
295             SHFF2126D = 0x20;                                /* 'xx01 xxxx' write */
296         }
297         else if( g0100FlgV == 2 ){                            /* It was duty 100% last time */
298             SHFF2126P = 0xCF;
299             g0100FlgV = 0;
300             SHFF2126D = 0x10;                                /* 'xx10 xxxx' write */
301         }
302     }
303     DutyV_RL1 = HtimeV + DEAD_TIME - 11;
304     DutyV_RL0 = ((CARRIER_COUNT - HtimeV) >> 1) - DEAD_TIME - 21;
305
306     /** W-phase duty judgment and setting at the next cycle **/
307     if( HtimeW < H_MIN ){                                    /* Duty 0% */
308         HtimeW = H_MIN;
309         if( g0100FlgW == 0 ){                                /* /W="H", W="L" fix */
310             SHFF2126P = 0xF3;
311             g0100FlgW = 1;                                    /* Duty 0% memory */
312             SHFF2126D = 0x04u;                                /* 'xxxx 10xx' write */
313         }
314     }
315     else if( H_MAX < HtimeW ){                                /* Duty 100% */
316         HtimeW = H_MAX;
317         if( g0100FlgW == 0 ){                                /* /W="L", W="H" fix */
318             SHFF2126P = 0xF3;
319             g0100FlgW = 2;                                    /* Duty 100% memory */
320             SHFF2126D = 0x08u;                                /* 'xxxx 01xx' write */
321         }
322     }
323     else{                                                    /* normal */
324         if( g0100FlgW == 1 ){                                /* It was duty 0% last time */
325             SHFF2126P = 0xF3;
326             g0100FlgW = 0;
327             SHFF2126D = 0x08u;                                /* 'xxxx 01xx' write */
328         }
329         else if( g0100FlgW == 2 ){                            /* It was duty 100% last time */
330             SHFF2126P = 0xF3;
331             g0100FlgW = 0;
332             SHFF2126D = 0x04u;                                /* 'xxxx 10xx' write */
333         }
334     }
335     DutyW_RL1 = HtimeW + DEAD_TIME - 11;
336     DutyW_RL0 = ((CARRIER_COUNT - HtimeW) >> 1) - DEAD_TIME - 21;
337
338     /** Data setting **/
339     TOU00RL1 = DutyU_RL1;
340     TOU00RLO = DutyU_RLO;
341     TOU02RL1 = DutyV_RL1;
342     TOU02RLO = DutyV_RLO;
343     TOU04RL1 = DutyW_RL1;
344     TOU04RLO = DutyW_RLO;
345 }
346
347 /*"FUNC COMMENT"*****
348 * Function name: void SetPointer( void )
349 *-----
350 * Description : setting pointer of sine wave table
351 *-----
352 * Argument    : none
353 *-----
354 * Returns     : none
355 *-----
356 * Notes       : Only the increment is done for the simplification.
357 /*"FUNC COMMENT END"*****
358 void SetPointer( void )
359 {
360     gSinPtr++;

```

```

361 }
362
363 /*"FUNC COMMENT"*****
364 * Function name: main()
365 *-----
366 * Description : -
367 *-----
368 * Argument : -
369 *-----
370 * Returns : -
371 *-----
372 * Notes : -
373 *"FUNC COMMENT END"*****/
374 void main(void)
375 {
376     gSinPtr = 0;
377     gAmp = 40ul; /* Amplitude coefficient */
378
379     /* When the gAmp data is changed, it is necessary to calculate the "gLlevel100Percent" again */
380     if ( gAmp > AMP_MAX ){
381         gAmp = AMP_MAX;
382     }
383     gLlevel100Percent = gAmp * H_MAX / 100; /* L level max value(count clock) */
384
385     g0100FlgU = 0; /* duty 0% or 100% executing flags clear */
386     g0100FlgV = 0;
387     g0100FlgW = 0;
388
389     DisInt(); /* Disable interrupt */
390
391     init_func();
392
393     TOU0_init(); /* Initialize TOU0 */
394
395     EnInt(); /* Enable interrupt */
396
397     SetDuty();
398
399     TOU0PRO = 0xFE; /* TOU0_7 write enable */
400     TOU0CEN = 0x01; /* TOU0_7 start */
401
402     while( 1 ){
403         ;
404     }
405 }
406
407 /*"FUNC COMMENT"*****
408 * Function name: void Int_TOU0_7( void )
409 *-----
410 * Description : TOU0 counter under flow interrupt
411 *-----
412 * Argument : none
413 *-----
414 * Returns : none
415 *-----
416 * Notes : -
417 *"FUNC COMMENT END"*****/
418 void Int_TOU0_7( void )
419 {
420     /* TOU0_6 interrupt */
421     if( (TOU0IST & TOU0IS6) != 0u ){
422         TOU0IST = ~TOU0IS6 & 0xffu; /* clear TOU0_6 interrupt request */
423         SetPointer();
424         SetDuty();
425     }
426 }
427
428 /*"FUNC COMMENT"*****
429 * Function name: void Int_TIN1619( void )
430 *-----
431 * Description : TIN16 - TIN19 interrupt request
432 *-----
433 * Argument : none
434 *-----
435 * Returns : none
436 *-----

```

```

437 * Notes      : FO signal input proc
438 *""FUNC COMMENT END""*****
439 void Int_TIN1619( void )
440 {
441     if ( (TINIR4 & TINIS16) != 0u ){
442         TINIR4 = ~TINIS16 & 0xffu;          /* clear TIN16 interrupt request */
443
444         TOU0PRO = 0x00;                    /* TOU0_0-7 write enable */
445         TOUOCEN = 0x00;                    /* TOU0_0-7 stop */
446
447         TOUOIST = 0x00;                    /* clear interrupt request */
448         TOUOIMA = 0xff;                    /* disable TOU0_6 */
449         ITOUOCR = 0x07;                    /* TOU0_n interrupt disable */
450
451         /** Error output for LED **/
452         while(1){
453             SINT32 i;
454             for(i=0;i<0x100000;i++){
455                 ;                            /* wait */
456             }
457             P11DATA^=0x03u;
458         }
459     }
460 }

```


4.6.2 startup.ms (an extract)

(Omitted)

```

72 ;*****
73 ; ICU Vector Table
74 ;*****
75 ;
76     .SECTION          ICUVECT, DATA, ALIGN=4
77 ;
78     .IMPORT           $Int_TIN1619
79     .IMPORT           $Int_TOU0_7
80 ;
81 vectbl:
82     .DATA.W          EIT_reset          ; H'0000 0094    MJT Input Interrupt 4:TIN3-TIN6
83     .DATA.W          EIT_reset          ; H'0000 0098    MJT Input Interrupt 3:TIN20-TIN27
84     .DATA.W          $Int_TIN1619      ; H'0000 009C    MJT Input Interrupt 2:TIN16-TIN19
85     .DATA.W          EIT_reset          ; H'0000 00A0    MJT Input Interrupt 1:TIN0
86     .DATA.W          EIT_reset          ; H'0000 00A4    MJT Input Interrupt 0:TIN7-TIN10
87     .DATA.W          EIT_reset          ; H'0000 00A8    MJT Output Interrupt 7:TMS0,TMS1
88     .DATA.W          EIT_reset          ; H'0000 00AC    MJT Output Interrupt 6:TOP8, TOP9
89     .DATA.W          EIT_reset          ; H'0000 00B0    MJT Output Interrupt 5:TOP10
90     .DATA.W          EIT_reset          ; H'0000 00B4    MJT Output Interrupt 4:TIO4-TIO7
91     .DATA.W          EIT_reset          ; H'0000 00B8    MJT Output Interrupt 3:TIO8,TIO9
92     .DATA.W          EIT_reset          ; H'0000 00BC    MJT Output Interrupt 2:TOP0-TOP5
93     .DATA.W          EIT_reset          ; H'0000 00C0    MJT Output Interrupt 1:TOP6, TOP7
94     .DATA.W          EIT_reset          ; H'0000 00C4    MJT Output Interrupt 0:TIO0-TIO3
95     .DATA.W          EIT_reset          ; H'0000 00C8    DMAC0-4 Interrupt:DMA0-DMA4
96     .DATA.W          EIT_reset          ; H'0000 00CC    SIO1 Receive Interrupt
97     .DATA.W          EIT_reset          ; H'0000 00D0    SIO1 Transmit Interrupt
98     .DATA.W          EIT_reset          ; H'0000 00D4    SIO0 Receive Interrupt
99     .DATA.W          EIT_reset          ; H'0000 00D8    SIO0 Transmit Interrupt
100    .DATA.W          EIT_reset          ; H'0000 00DC    A/D0 Conversion Interrupt
101    .DATA.W          EIT_reset          ; H'0000 00E0    TID0 Output Interrupt
102    .DATA.W          $Int_TOU0_7        ; H'0000 00E4    TOD0 Output Interrupt
103    .DATA.W          EIT_reset          ; H'0000 00E8    DMAC5-9 Interrupt:DMA5-DMA9
104    .DATA.W          EIT_reset          ; H'0000 00EC    SIO2,3 Transmit/Receive Interrupt
105    .DATA.W          EIT_reset          ; H'0000 00F0    RTD Interrupt
106    .DATA.W          EIT_reset          ; H'0000 00F4    TID1 Output Interrupt
107    .DATA.W          EIT_reset          ; H'0000 00F8    TOU1 Output Interrupt:TOU1_0-
TOU1_7
108    .DATA.W          EIT_reset          ; H'0000 00FC    SIO4,5 Transmit/Receive Interrupt
109    .DATA.W          EIT_reset          ; H'0000 0100    Reserved
110    .DATA.W          EIT_reset          ; H'0000 0104    Reserved
111    .DATA.W          EIT_reset          ; H'0000 0108    TML1 Input Interrupt:TIN30-TIN33
112    .DATA.W          EIT_reset          ; H'0000 010C    CAN0 Transmit/Receive & Error
Interrupt
113    .DATA.W          EIT_reset          ; H'0000 0110    CAN1 Transmit/Receive & Error
Interrupt
114    .DATA.W          EIT_reset          ; H'0000 0114    DRI Transfer Interrupt
115    .DATA.W          EIT_reset          ; H'0000 0118    DRI Counter Interrupt:DECO-DEC4
116    .DATA.W          EIT_reset          ; H'0000 011C    DRI Event Detection
Interrupt:DIN0-DIN5
117    .DATA.W          EIT_reset          ; H'0000 0120    CAN0 Transmit/Receive Completion
Interrupt
118    .DATA.W          EIT_reset          ; H'0000 0124    CAN0 Single-Shot Interrupt
119    .DATA.W          EIT_reset          ; H'0000 0128    CAN0 Error Interrupt
120    .DATA.W          EIT_reset          ; H'0000 012C    CAN1 Transmit/Receive Completion
Interrupt
121    .DATA.W          EIT_reset          ; H'0000 0130    CAN1 Single-Shot Interrupt
122    .DATA.W          EIT_reset          ; H'0000 0134    CAN1 Error Interrupt
123    .DATA.W          EIT_reset          ; H'0000 0138    RAM Write Monitor Interrupt
124 ;
(Omitted)

```

5. Reference Documents

- 32192/32196 Group Hardware Manual (Rev.1.01)
- 32195 Group Datasheet (Rev.1.00)
- M3T-CC32R Version 5.00 User's Manual (Compiler)
- M3T-AS32R Version 5.00 User's Manual (Assembler)
- M32R-FPU Software Manual (Rev.1.01)

(Please get the latest one from Renesas Technology Corp. website.)

6. Homepage and Support Center

- Renesas Technology Corp. Website:
<http://www.renesas.com/>

- Inquires for all Renesas products and technical inquiries for the M32R Family products:
Customer Support Center: csc@renesas.com

Revision Record

Rev.	Date	Description	
		Page	Summary
1.00	Feb.22.06	—	First edition issued.

Keep safety first in your circuit designs!

1. Renesas Technology Corporation puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage. Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corporation product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corporation or a third party.
2. Renesas Technology Corporation assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corporation without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors. Renesas Technology Corporation assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corporation by various means, including the Renesas Technology Corporation Semiconductor home page (<http://www.renesas.com>).
4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corporation assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
5. Renesas Technology Corporation semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corporation or an authorized Renesas Technology Corporation product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
6. The prior written approval of Renesas Technology Corporation is necessary to reprint or reproduce in whole or in part these materials.
7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
8. Please contact Renesas Technology Corporation for further details on these materials or the products contained therein.