

To our customers,

Old Company Name in Catalogs and Other Documents

On April 1st, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: <http://www.renesas.com>

April 1st, 2010
Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (<http://www.renesas.com>)

Send any inquiries to <http://www.renesas.com/inquiry>.

Notice

1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
2. Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Renesas Electronics products or technical information described in this document. No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights of Renesas Electronics or others.
3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
7. Renesas Electronics products are classified according to the following three quality grades: “Standard”, “High Quality”, and “Specific”. The recommended applications for each Renesas Electronics product depends on the product’s quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as “Specific” without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as “Specific” or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is “Standard” unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
 - “Standard”: Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
 - “High Quality”: Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
 - “Specific”: Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics.
12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.

(Note 1) “Renesas Electronics” as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.

(Note 2) “Renesas Electronics product(s)” means any product developed or manufactured by or for Renesas Electronics.

M61880FP

Laser Diode Driver/Controller

REJ03F0068-0100Z

Rev.1.0

Sep.19.2003

Description

The M61880FP is a laser diode driver/controller that performs drive and laser power control of a type of semiconductor laser diode in which the semiconductor laser diode anode and monitoring photodiode cathode are connected to the stem.

The M61880FP has a sink type laser drive current output pin, is capable of high-speed switching at up to 200 Mbps, and can drive a laser diode at a maximum drive current of 100 mA (drive current = switching current + bias current).

A high-speed sample-and-hold circuit is incorporated, enabling a self-APC* system to be implemented without the need for laser power control from outside.

* Automatic Power Control


Features

- On-chip self-APC sample-and-hold circuit
 - High-speed sampling circuit
 - APC 1% variance response time = 1 μ s (C = 0.047 μ F)
 - High-impedance hold circuit
 - (1% error or less at C = 0.047 μ F, t = 1 ms)
- High-speed switching (200 Mbps max.)
- High drive current (100 mA max.)
- Bias current settable (40 mA max.)
- 5 V single power supply


Application

Semiconductor laser diode application systems (LBPs, PPCs, optical communications, measuring instruments, etc.)

Pin Configuration (Top View)



Block Diagram



Function Overview

The M61880FP is a semiconductor laser diode driver/controller that automatically performs drive and laser power control of a type of semiconductor laser diode in which the semiconductor laser diode (LD) anode and monitoring photodiode (PD) cathode are connected to the stem.

Laser power control operation is performed by connecting an external capacitance to the CH pin and applying a reference voltage to the Vr pin.

The PD current resulting from LD light emission flows to a resistance connected between 1RM and 2RM, and generates a voltage (VM). This VM voltage is compared with the voltage applied to the Vr pin, and if $VM < Vr$, the current from the CH pin is taken as a source current and an external capacitance is charged.

If $VM > Vr$, the current from the CH pin is taken as a sink current and the external capacitance charge is discharged.

This operation is performed when $\overline{S/H}$ input = "L" and \overline{DATA} input = "L" (sampling). When $\overline{S/H}$ input = "H", the CH pin goes to the high-impedance state (hold) irrespective of the state of VM, Vr, and the \overline{DATA} input.

The LD drive current is composed of switching current ISW controlled by \overline{DATA} input and LD bias current IB unrelated to the \overline{DATA} input state.

Pin Description

Pin No.	Symbol	Name	Function
1	Rs	Switching current setting resistance connection pin	Connects switching object current (ISW) setting resistance to GND.
2	GND1	Ground 1	Internal analog GND
3	RB	Bias current setting resistance connection pin	Connects bias current (IB) setting resistance to GND. Leave this pin open when IB is not used.
4	VB	Bias current setting voltage input	Bias current value (IB) is set by applying a voltage to this pin. Leave this pin open when IB is not used.
5	Vref	Reference voltage output	M61880 internal reference voltage (1.5 V typ.) output pin
6	Vr	Reference voltage input	Connected to non-reversed input pin of comparator in sample-and-hold circuit. Connect this pin to Vref pin when using M61880 internal reference voltage.
7	CH	Hold capacitance connection pin	Connects hold capacitance to GND. This pin is connected to sample-and-hold circuit output and ISW current source input in M61880.
8	\overline{S}/H	Sample-and-hold control input	Sampling when "H", hold when "L"
9	Vcc1	Power supply 1	Internal analog power supply. Connected to positive power supply (+5 V).
10	NC	NC	Not connected to internal circuitry.
11, 12	1RM 2RM	Monitoring load resistance connection pins	Connects load resistance for converting monitor photodiode current to voltage between 1RM and 2RM. (1RM pin is connected to GND in IC.)
13	\overline{ENB}	Laser current enable input	When "H", LD drive current source circuit is turned off. Also, CH pin is forcibly fixed at "L" level.
14	\overline{DATA}	Switching data input	ISW+IB current flows to laser diode when "+", and IB current when "H".
15	PD	Monitoring photodiode current input	Connects monitor photodiode anode.
16	GND2	Ground 2	Internal digital GND
17	LD	Laser current output	Connects semiconductor laser diode cathode.
18	NC	NC	Not connected to internal circuitry.
19	RO	Laser current load output	Connects laser current load resistance to Vcc.
20	Vcc2	Power supply 2	Internal digital power supply. Connected to positive power supply (+5 V).

Operation

1. Laser drive current setting method

The laser drive current consists of switching current ISW + bias current IB.

(1) Switching current ISW setting method

- a. Decide the maximum current value ILD(MAX) to flow in the laser diode (LD). This is decided taking account of the LD type, dispersion, temperature changes, secular changes, etc.
- b. Find ISW (initial set value) from the following equation.

$$ISW \text{ (initial set value)} = ILD(MAX)/1.9$$
- c. Find switching current setting resistance RS from the following equation.

$$R_s \text{ [k}\Omega\text{]} \doteq 30 \times V_{ref} \text{ (1.5V) [V]} / I_{sw} \text{ (initial set value) [mA]}$$

In this case the LD current can be controlled in a range of 10% to 90% of ISW (initial set value).

(2) Bias current IB setting method

Bias current IB [A] is set by deciding bias current setting resistance RB and bias current setting voltage VB.

$$I_B [A] \doteq V_B [V] / R_B [\Omega]$$

where $1.2 \text{ V} \leq V_B \leq V_{CC} - 2.7\text{V}$, $I_B (\text{max.}) = 40\text{mA}$

2. Switching operation

When $\overline{\text{DATA}} = \text{"L"}$, the LD drive current is ISW+IB, and when $\overline{\text{DATA}} = \text{"H"}$, the LD drive current is IB.

3. $\overline{\text{ENB}}$ input

In laser drive current control by $\overline{\text{DATA}}$ input, the drive current to the laser is controlled when the M61880 internal current source is on, while control by $\overline{\text{ENB}}$ turns LD drive current source operation on/off.

Power is turned on when $\overline{\text{ENB}} = \text{"H"}$, and the current secure is turned off when $\overline{\text{ENB}} = \text{"L"}$. When $\overline{\text{ENB}} = \text{"H"}$, the CH pin is forcibly fixed at the "L" level, and the capacitor connected to the CH pin is forcibly discharged.

When changing the $\overline{\text{ENB}}$ pin from "H" to "L", in order to prevent an abnormal current from flowing in the LD, drive the $\overline{\text{DATA}}$ pin to the "H" state, then wait 10 μsec or more after the $\overline{\text{ENB}}$ pin changes from "H" to "L" before changing the $\overline{\text{DATA}}$ pin from "H" to "L".

4. Internal reset operation

The M61880 incorporates a reset circuit for preventing an overcurrent in the laser when power is turned on. In the range $V_{CC} < 3.5 \text{ V}$ (typ.), the internal current source is turned off and the CH pin is forcibly fixed at the "H" level.

5. RO pin

The RO pin connects the drive current load resistance, and a current virtually equal to ISW flows from this pin.

The load resistance is connected between this pin and VCC, thereby reducing power consumption in the IC.

For reasons relating to circuit operation, the voltage at this pin must be 2.5 V or higher. Therefore, if the maximum value of ISW is designated ISW(max.), maximum value RO(max.) of load resistance RO is as follows:

$$R_S (\text{max.}) [\Omega] = \frac{V_{CC} (\text{min.}) [V] - 2.5 [V]}{I_{SW} (\text{max.}) [A]}$$

For example, if $V_{CC}(\text{min.}) = 4.75 \text{ V}$ and $I_{SW}(\text{max.}) = 100 \text{ mA}$, $R_O(\text{max.}) = 22 \Omega$. That is to say, when the RS value is set so that ISW is a maximum of 100 mA, RO must not exceed 22 Ω .


6. Sample-and-hold circuit

(1) Overview of circuit operation

The operation of the sample-and-hold circuit incorporated in the M61880 is outlined below.

The PD current resulting from LD light emission flows to resistance RM connected between 1RM and 2RM, and generates a voltage (VM). This VM voltage is compared with the voltage applied to the Vr pin, and if $VM < V_r$, the current from the CH pin is taken as a source current and an external capacitance is charged. If $VM > V_r$, the current from the CH pin is taken as a sink current and the external capacitance charge is discharged.

This operation is performed when $\overline{\text{S/H}} \text{ input} = \text{"L"}$ and $\overline{\text{DATA}} \text{ input} = \text{"L"}$ (sampling). When $\overline{\text{S/H}} \text{ input} = \text{"H"}$, the CH pin goes to the high-impedance state (hold) irrespective of the state of VM, Vr, and the $\overline{\text{DATA}}$ input.



Conceptual Diagram of Sample-and-Hold Circuit

Operation Function Table


Input		Switch State					Output (CH Pin)
ENB	S/H	DATA	VM, Vr	SW1	SW2	Tr1	
H	X	X	X	OFF	OFF	ON	Fixed at "L"
L	H	X	X	OFF	OFF	OFF	High-impedance state (hold)
L	L	H	X	OFF	OFF	OFF	High-impedance state (hold)
		L	VM < Vr	ON	OFF	OFF	Current source (sample)
			VM > Vr	OFF	ON	OFF	Current sink (sample)

X: Don't Care

(2) APC timing chart

An example of a timing chart of APC operation by means of the sample-and-hold control signals is shown below.

In this example, a case is shown in which the direction of the CH pin leakage current in the hold state is assumed to be the direction of flow to the M61880 (forward direction).



Example of Sample-and-Hold Type APC Circuit Operation Timing Chart

7. VCC and GND pins

Power supply related pins are the VCC1 and VCC2 pins and the GND1 and GND2 pins. In terms of the internal circuitry, these are connected as follows. (Basically, a single power supply should be used.)

VCC1, GND1: Connected to analog system.

VCC2, GND2: Connected to digital system.

The main points to be noted with regard to actual wiring are as follows.

- (1) Make the wiring as wide as possible and avoid lengthy, circuitous wiring.
- (2) Locate an electrolytic capacitor for voltage stabilization close to VCC1 and GND1.
- (3) Locate a bypass capacitor close to VCC2 and GND2.

Also ensure that M61880 power is supplied while laser diode power is being supplied.

Note on Wiring of Peripheral Elements

Peripheral elements necessary for M61880 operation should be located as close as possible to the M61880.

Power Consumption Calculation Method

M61880 power consumption P is given approximately by the following equation:

$$P = I_{CC} \times V_{CC} + I(RO) \times V(RO) + I(LD) \times V(LD)$$

where V(RO): RO pin voltage V(LD): LD pin voltage

I(RO): RO pin load current I(LD): LD pin load current

For example, when VCC = 5.25 V, V(RO) = V(LD) = 2.5 V, and I(RO) = I(LD) = 100 mA, the power consumption values when the laser is on and off are as follows.

- (1) When laser is on, (\overline{DATA} = "L", ICC = 55 mA)

$$PON = 55 \times 5.25 + 0 + 100 \times 2.5 = 538.8 \text{ (mW)}$$

- (2) When laser is off, (\overline{DATA} = "H", ICC = 55 mA)

$$PON = 55 \times 5.25 + 100 \times 2.5 = 538.8 \text{ (mW)}$$

Absolute Maximum Ratings

Item	Symbol	Ratings	Unit	Conditions
Power supply voltage	VCC	-0.3 to +5.5	V	
Input voltage	CH, Vr	-0.3 to Vcc	V	
	DATA, ENB, S/H	-0.3 to Vcc		
Output voltage	RO	-0.3 to Vcc	V	
Switching current	Isw	120	mA	
Bias current	IB	50	mA	
Power consumption	Pd	980	mW	When mounted on board. When Ta = 25°C (Note)
Storage temperature	Tstg	-60 to +150	°C	

Note: When Ta ≥ 25°C, 9.8 mW/°C derating should be applied.

Recommended Operating Conditions

(Unless otherwise noted, Ta = -20°C to +70°C) Absolute Maximum Ratings

Item	Symbol	Limits			Unit
		Min.	Typ.	Max.	
Power supply voltage	Vcc	4.75	5.0	5.25	V
Switching current	Isw			100	mA
Bias current	IB			40	mA
Operating ambient temperature	Topr	-20		70	°C

Note: ISW+IB ≤ 100 mA

Electrical Characteristics

(Unless specified otherwise noted, VCC = 5 V ±5%, Ta = -20°C to +70°C)

Item		Symbol	Limits			Unit	Test Conditions
			Min.	Typ.	Max.		
“H” input voltage	DATA	VIH	2.0			V	
	ENB, S/H		2.0			V	
“L” input voltage	DATA	VIL			0.8	V	
	ENB, S/H				0.8	V	
Reference voltage input	Vr	Vr	0.35	1.5	2.0	V	
Reference voltage output	Vref	Vref	1.4	1.5	1.6	V	Io = ±10μA
	Temperature coefficient			0.1		mV/°C	Ta = -20 to 25°C
				-0.1			Ta = 25 to 70°C
Operating voltage range	LD	VLD	2.5		Vcc	V	ILD = 75mA
Effective voltage upper limit	CH	VI	2.7	3.0		V	
“H” output voltage	CH	VOH	Vcc-1.6			V	ENB = “L”, IOH = (-0.6mA)
“L” output voltage	CH	VOL			0.6	V	ENB = “L”, IOL = (0.6mA)
Input voltage	DATA, ENB	II			20	μA	VI = 2.7V
					-0.2		mA
Switching current (Note)	LD	Isw		75		mA	CH = 3.5V, Rs = 1.2kΩ, VLD = 3V
Bias current (Note)	LD	IB		20		mA	VB = 1.4V, RB = 70kΩ, VLD = 3V
Load charge current	CH	Icg	-0.2	-0.1	-0.66	mA	ENB = “L”, Vo = (0.6 to Vcc-1.6V)
Load discharge current	CH	Idg	0.66	1.0	2.0	mA	ENB = “L”, Vo = (0.6 to Vcc-1.6V)
Off-state output current	CH	Ioz	-0.5		0.5	μA	Vo = 2.0 to 3.0V, hold state
Off output current	LD	LOFF			50	μA	ENB = “L”, DATA = “H”, Isw = 50mA
					50	μA	ENB = “H”, DATA = “L”, Isw = 50mA
Power supply current		Icc		43	63	mA	Vcc = 5.25V, ENB = DATA = 0V
				43	63		0V, CH = 2.5V, DATA = 4.5V VB = 1.5V, Rs = 820Ω, RB = 75 Ω Ro = LD = 5.0V

* Reference values are values when Ta = 25°C and VCC = 5 V.


Note: These items indicate input voltage/output current conversion characteristics. The M61880 should be used with ISW and IB within the Specification Value range given in “Recommended Operating Conditions.”

Switching Characteristics


(Unless specified otherwise noted, Ta = 25°C and VCC = 5 V)

Item	Symbol	Test Pins		Limits			Unit	Test Conditions
		Input	Output	Min.	Typ.	Max.		
Operating frequency	fop			—	100	2.0	Mbps	
LD current rise time (*)	tr	$\overline{\text{DATA}}$ voltage	LD current	—	1.0	2.0	nsec	ILD (H) = 50mA, ILD (L) = 0mA
LD current fall time (*)	tf	$\overline{\text{DATA}}$ voltage	LD current		1.0		nsec	Rs = 840Ω, CH = 0.047μF, APC adjustment; RM = adjustment (CH = 2.5V), Vr = 1.5V (Note 1)
APC circuit response time 1 (1% variance response time)	tRP1	Vr voltage	LD current		1		μsec	ILD (H) = 50mA, Rs = 840Ω, CH = 0.047μF, DATA = 0V
APC circuit response time 2 (50% variance response time)	tRP2	Vr voltage	LD current		3		μsec	APC adjustment; RM = adjustment (CH = 2.5V), Vr = 1.5V ± 0.5% (Note 1)
Circuit on time	tON	$\overline{\text{ENB}}$ voltage	LD current			350	μsec	ILD (H) = 50mA (Note 2)
Circuit off time	tOFF	$\overline{\text{ENB}}$ voltage	LD current			5	μsec	ILD (H) = 50mA (Note 2)

Note 1: Test Circuit




Note 2: Test Circuit



Application Example

1. Example of sample-and-hold type self-APC circuit



2. Example of controlling sample-and-hold circuit by means of $\overline{\text{DATA}}$ signal

When the M61880 is used in optical communications, etc., (when the $\overline{\text{S/H}}$ signal cannot be supplied), the $\overline{\text{DATA}}$ signal can be used as a sample-and-hold control signal.

In this case, the $\overline{\text{S/H}}$ pin should be fixed at "L". If value CH of the hold capacitor connected to the CH pin is $0.047\mu\text{F}$, switching at around 20 Mbps is possible.

3. Examples of varying LD switching drive current by means of external control

(1) Varying the monitoring load resistance value (resistance connected between pins 11 and 12)

The LD drive current can be varied by varying the resistance between pins 11 and 12 in the circuit in 1. above.

(2) Varying the voltage applied to the V_r pin

The LD drive current can be varied by applying an external voltage (within the reference voltage input range) to pin 6 in the circuit in 1. above. A maximum multiplication factor of $2/0.35 = 5.7$ times can be obtained as the LD drive current ratio in this case.

Sample-and-Hold Type APC Operation

A timing chart for a case where a sample-and-hold type APC circuit is configured using an M61880FP (Figure 1) is shown in Figure 2 on the following page.

The operation of a sample-and-hold type APC circuit will be described here using the timing chart in Figure 2. It is assumed that the laser drive current is set to 50 mA (bias current = 0 mA), and the values shown in Figure 1 are used as constants required for calculation purposes.




Figure 1 Example of Sample-and-Hold Type APC Circuit Application

1. Initial sampling period (T1)

When sampling starts, the CH pin voltage is 0 V, and therefore the laser diode (LD) is not emitting light. Consequently, the voltage of the COMP input pin (pin 12) is also 0 V. Next, COMP starts charging the hold capacitor connected to CH (current also starts flowing in the LD in proportion to the rise of the CH pin voltage, and the pin 12 voltage also rises), and charging is performed until the pin 12 voltage reaches comparison voltage Vr.

In this case, the CH pin voltage rises from 0 V to VCH due to the M61880FP’s CH pin load charge current (Icg). Time t required for this is given by the following equation.

$$t = \frac{CH \times VCH}{Icg} \dots\dots\dots \text{Equation (1)}$$

In Equation (1), if CH = 0.047μF, VCH = 2.5 V, and Icg = 0.66 mA (*), then t = 178μs.

* Minimum Icg specification value in “Electrical Characteristics” in this Specification.

2. Hold periods (T2, T4)

In these periods, the CH pin goes to the high-impedance state. However, the charge current does not become absolutely 0, and a slight leakage current is present. The hold capacitor is charged or discharged by the CH pin off-state leakage current (Ioz).

Assuming that a leakage current (Ioz) is generated in the direction in which the hold capacitor is discharged, the change in the CH pin current (ΔV) is given by the following equation.

$$\Delta V = \frac{I_{oz} (0.5\mu A) \times T2 (4)}{C_H \times (0.047\mu F)} \dots\dots\dots \text{Equation (2)}$$

(T2(4) is the hold time.)

When the CH pin voltage decreases by ΔV , the laser drive current also decreases.

3. Sampling periods (T3, T5)

In these periods, the LD light quantity that changed during a hold period (T2, T4) is corrected.

Taking only the influence of the CH pin leakage current into consideration (actually, LD temperature variations also have an effect), making substitutions of $I_{oz} = 0.5\mu A$, $T = 1 \text{ ms}$, and $C_H = 0.047\mu F$ in Equation (2) gives a result of $\Delta V = 10 \text{ mV}$.

The time required to compensate for this ΔV value (10 mV) is given by the following equation.

$$t = \frac{C_H \times \Delta V}{I_{cg}} \dots\dots\dots \text{Equation (3)}$$

From Equation (3), $t = 0.7\mu s$.




Figure 2 Sample-and-Hold Type APC Circuit Operation Timing Chart

Description of Laser Switching Current Setting Circuit




Figure 1 Switching Current Setting Equivalent Circuit

1. Switching current initial setting circuit

The switching current initial set value is set by switching current setting resistance Rs in a V-I conversion circuit using an op-amp.

$$I_{SW0} [mA] = 30 \times \frac{V_{ref} (1.5V) [V]}{R_s [k\Omega]} \dots\dots\dots (1)$$

2. Switching current varying circuit

If the potential difference between the CH pin voltage and internal reference voltage is designated ΔV (= VCH – 2.5 V), Id flowing in a 2 kΩ resistance due to this ΔV voltage is as follows.

$$I_d = \frac{\Delta V}{2k\Omega} \dots\dots\dots (2)$$

Therefore, the I1 and I2 currents are given by the following equations.

$$\left(\begin{array}{l} I_1 = 250 \mu A - I_d \\ I_2 = 250 \mu A + I_d \end{array} \right) \dots\dots\dots (3)$$

Next, the relationship between I1, I2, ISW1, and ISW2 due to a Gilbert circuit comprising D1, D2, Q1, and Q2, is given by the following equation.

$$\frac{I_1}{I_2} = \frac{I_{SW1}}{I_{SW2}} \dots\dots\dots (4)$$

Also, the relationship between ISW1, ISW2, and ISW0 is given by the following equation.

$$I_{SW1} + I_{SW2} = 2 \cdot I_{SW0} \dots\dots\dots (5)$$

Finding ISW2 from Equations (4) and (5),

$$I_{SW2} = 2 \cdot I_{SW0} \times \frac{I_1}{I_1 + I_2} \dots\dots\dots (6)$$

Meanwhile, ISW can be expressed as follows.

$$I_{sw} = 2 \cdot I_{sw0} - I_{sw2} \dots\dots\dots (7)$$

The relationship between ISW and ΔV is found as shown below.

Substituting Equation (6) in Equation (7),

$$I_{sw} = 2 \cdot I_{sw0} \left(\frac{I_2}{I_1 + I_2} \right) \dots\dots\dots (8)$$

and further substituting Equation (3),







$$I_{sw} = I_{sw0} \left(1 + \frac{I_d}{250\mu A} \right) \dots\dots\dots (9)$$

Next, substituting Equation (2) gives the relationship between ISW and ΔV as follows.


$$I_{sw} = I_{sw0} \left(1 + \frac{\Delta V / 2k\Omega}{250\mu A} \right) \dots\dots\dots (10)$$

A characteristic curve of the CH pin voltage and switching current is shown toward the end of “Electrical Characteristic Graphs” following.


Electrical Characteristic Graphs



CH Pin Voltage - Switching Current Characteristic



APC Comparator Input Voltage - Offset Voltage Characteristic









Package Dimensions

20P2N-A

(MMP)

Plastic 20pin 300mil SOP

EIAJ Package Code SOP20-P-300-1.27	JEDEC Code -	Weight(g) 0.26	Lead Material Cu Alloy
---------------------------------------	-----------------	-------------------	---------------------------



Recommended Mount Pad

Symbol	Dimension in Millimeters		
	Min	Nom	Max
A	-	-	2.1
A1	0	0.1	0.2
A2	-	1.8	-
b	0.35	0.4	0.5
c	0.18	0.2	0.25
D	12.5	12.6	12.7
E	5.2	5.3	5.4
e	-	1.27	-
HE	7.5	7.8	8.1
L	0.4	0.6	0.8
L1	-	1.25	-
Z	-	0.585	-
Z1	-	-	0.735
x	-	-	0.25
y	-	-	0.1
theta	0°	-	8°
b2	-	0.76	-
e1	-	7.62	-
l2	1.27	-	-

RENESAS Technology Corp. Sales Strategic Planning Div. Nippon Bldg., 2-6-2, Ohte-machi, Chiyoda-ku, Tokyo 100-0004, Japan

Keep safety first in your circuit designs!

1. Renesas Technology Corp. puts the maximum effort into making semiconductor products better and more reliable, but there is always the possibility that trouble may occur with them. Trouble with semiconductors may lead to personal injury, fire or property damage.
Remember to give due consideration to safety when making your circuit designs, with appropriate measures such as (i) placement of substitutive, auxiliary circuits, (ii) use of nonflammable material or (iii) prevention against any malfunction or mishap.

Notes regarding these materials

1. These materials are intended as a reference to assist our customers in the selection of the Renesas Technology Corp. product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Renesas Technology Corp. or a third party.
 2. Renesas Technology Corp. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.
 3. All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Renesas Technology Corp. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor for the latest product information before purchasing a product listed herein.
The information described here may contain technical inaccuracies or typographical errors.
Renesas Technology Corp. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors.
Please also pay attention to information published by Renesas Technology Corp. by various means, including the Renesas Technology Corp. Semiconductor home page (<http://www.renesas.com>).
 4. When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Renesas Technology Corp. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.
 5. Renesas Technology Corp. semiconductors are not designed or manufactured for use in a device or system that is used under circumstances in which human life is potentially at stake. Please contact Renesas Technology Corp. or an authorized Renesas Technology Corp. product distributor when considering the use of a product contained herein for any specific purposes, such as apparatus or systems for transportation, vehicular, medical, aerospace, nuclear, or undersea repeater use.
 6. The prior written approval of Renesas Technology Corp. is necessary to reprint or reproduce in whole or in part these materials.
 7. If these products or technologies are subject to the Japanese export control restrictions, they must be exported under a license from the Japanese government and cannot be imported into a country other than the approved destination.
Any diversion or reexport contrary to the export control laws and regulations of Japan and/or the country of destination is prohibited.
 8. Please contact Renesas Technology Corp. for further details on these materials or the products contained therein.
-



RENESAS SALES OFFICES

<http://www.renesas.com>

Renesas Technology America, Inc.
450 Holger Way, San Jose, CA 95134-1368, U.S.A
Tel: <1> (408) 382-7500 Fax: <1> (408) 382-7501

Renesas Technology Europe Limited.
Dukes Meadow, Millboard Road, Bourne End, Buckinghamshire, SL8 5FH, United Kingdom
Tel: <44> (1628) 585 100, Fax: <44> (1628) 585 900

Renesas Technology Europe GmbH
Dornacher Str. 3, D-85622 Feldkirchen, Germany
Tel: <49> (89) 380 70 0, Fax: <49> (89) 929 30 11

Renesas Technology Hong Kong Ltd.
7/F., North Tower, World Finance Centre, Harbour City, Canton Road, Hong Kong
Tel: <852> 2265-6688, Fax: <852> 2375-6836

Renesas Technology Taiwan Co., Ltd.
FL 10, #99, Fu-Hsing N. Rd., Taipei, Taiwan
Tel: <886> (2) 2715-2888, Fax: <886> (2) 2713-2999

Renesas Technology (Shanghai) Co., Ltd.
26/F., Ruijin Building, No.205 Maoming Road (S), Shanghai 200020, China
Tel: <86> (21) 6472-1001, Fax: <86> (21) 6415-2952

Renesas Technology Singapore Pte. Ltd.
1, Harbour Front Avenue, #06-10, Keppel Bay Tower, Singapore 098632
Tel: <65> 6213-0200, Fax: <65> 6278-8001