

Technical Data of Ceramic Resonator

Type CSA8.00MTZ

CST8.00MTW




Applied to μ PD780032A

TOYAMA MURATA MANUFACTURING CO., LTD.

Product Engineering Service Section I

Engineering Service Department


Piezoelectric Components Group

Approved by	Checked by	Checked by	Issued by	Issued Date	TCD No.
 S.Iwasaki	 K.Kuramoto	 M.Kurosaka	 Y.Ishiho	Feb 1, 1999	TCD-99-6A21

Contents

1.	Test Circuit	1
2.	Temperature Characteristics of Oscillating Frequency, Oscillating Voltage	2
3.	Rise Time, Oscillating Frequency, Oscillating Voltage vs Vdd Characteristics	3
4.	Oscillating Frequency, Oscillating Voltage vs (C1,C2) Characteristics	4
5.	Oscillating Frequency, Oscillating Voltage, Rise Time, Oscillating Voltage vs C(C1=C2) Characteristics	5

Test Circuit



H:10,24,35,36,38

L:9,25 ~34,39,42


Recommendable Value

CERALOCK® : CSA8.00MTZ


C1 = 30 [pF]

C2 = 30 [pF]


Temperature Characteristics of Oscillating Frequency
MODEL : CSA8.00MTZ with μ PD780032A




Temperature Characteristics of Oscillating Voltage
MODEL : CSA8.00MTZ with μ PD780032A




Rise Time vs Vdd Characteristics
MODEL : CSA8.00MTZ with μ PD780032A




Oscillating Frequency vs Vdd Characteristics
MODEL : CSA8.00MTZ with μ PD780032A




Oscillating Voltage vs Vdd Characteristics
MODEL : CSA8.00MTZ with μ PD780032A




Oscillating Frequency vs (C1,C2) Characteristics
MODEL : CSA8.00MTZ with μ PD780032A




Oscillating Frequency vs (C1,C2) Characteristics
MODEL : CSA8.00MTZ with μ PD780032A




Oscillating Voltage vs (C1,C2) Characteristics
MODEL : CSA8.00MTZ with μ PD780032A




Oscillating Voltage vs (C1,C2) Characteristics
MODEL : CSA8.00MTZ with μ PD780032A




Oscillating Frequency vs C(C1=C2) Characteristics
MODEL : CSA8.00MTZ with μ PD780032A




Oscillating Voltage vs C(C1=C2) Characteristics
MODEL : CSA8.00MTZ with μ PD780032A



Rise Time vs C(C1=C2) Characteristics
MODEL : CSA8.00MTZ with μ PD780032A



Starting Voltage vs C(C1=C2) Characteristics
MODEL : CSA8.00MTZ with μ PD780032A



Appendixes



6.	Comparison Table	6
7.	Frequency Correlation Data	7
8.	Rise Time vs Vdd Characteristics (Ta;Variable), Temperature Characteristics of Starting Voltage IC : W03	8
9.	Rise Time vs Vdd Characteristics (Ta;Variable), Temperature Characteristics of Starting Voltage IC : W05	9
10.	Rise Time vs Vdd Characteristics (Ta;Variable), Temperature Characteristics of Starting Voltage IC : W07	10
11.	Rise Time vs Vdd Characteristics (Ta;Variable), Temperature Characteristics of Starting Voltage IC : W09	11
12.	Rise Time vs Vdd Characteristics (Ta;Variable), Temperature Characteristics of Starting Voltage IC : W15	12
13.	Rs vs Vdd Characteritics	13
14.	Rs vs C(C1=C2) Characteritics	14



Comparison Table

IC : No	V1H [V]	V1L [V]	V1p-p [V]	V2H [V]	V2L [V]	V2p-p [V]	Fosc [kHz]	Trise [ms]	Vstart [V]
W03	5.13	-0.40	5.53	5.50	0.13	5.37	8152.114	0.048	1.35
W05	5.16	-0.34	5.50	5.50	0.19	5.31	8152.219	0.059	1.26
W07	5.09	-0.40	5.49	5.50	0.06	5.44	8152.367	0.050	1.48
W09	5.16	-0.28	5.44	5.56	0.19	5.37	8152.315	0.064	1.24
W15	5.16	-0.34	5.50	5.50	0.13	5.37	8152.075	0.055	1.37


Ref.

Performance described page 2 to 5 were measured with IC No. W15







Rise Time vs Vdd Characteristics (Ta : Variable , CERALOCK® : Vst. Worst Sample)
MODEL : CSA8.00MTZ with μ PD780032A(W07)




Temperature Characteristics of Starting Voltage (CERALOCK® : Vst. Worst Sample)
MODEL : CSA8.00MTZ with μ PD780032A(W07)





Rise Time vs Vdd Characteristics (Ta : Variable , CERALOCK® : Vst. Worst Sample)
MODEL : CSA8.00MTZ with μ PD780032A(W09)




Temperature Characteristics of Starting Voltage (CERALOCK® : Vst. Worst Sample)
MODEL : CSA8.00MTZ with μ PD780032A(W09)





Rs vs Vdd Characteristics
MODEL : CSA8.00MTZ with uPD780032A



Rs vs C(C1=C2) Characteristics

MODEL : CSA8.00MTZ with uPD780032A

Vdd=+5.0V

